

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332472-840

Luminaire Tested: **S123RDIW-S1165D460U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332472-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S1165D460U840-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 460 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6285.7 lumens
Efficiency: N/A
Efficacy: 120.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 52.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332472-840

CATALOG NUMBER: S123RDIW-S1165D460U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332472-840

CATALOG NUMBER: S123RDIW-S1165D460U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	112	112	112	112	106	106	106	106	95	95	95	84	84	84	75	75	75	70																				
1	103	99	95	91	97	93	90	87	84	81	79	75	73	71	67	65	64	60																				
2	94	87	80	75	89	82	77	72	74	70	66	66	63	60	59	57	55	51																				
3	86	77	69	63	81	73	66	61	66	60	56	59	55	52	53	50	47	44																				
4	79	68	60	54	75	65	58	52	59	53	48	53	48	45	48	44	41	38																				
5	73	61	53	47	69	58	51	45	53	47	42	48	43	39	43	39	36	33																				
6	67	55	47	41	64	53	45	40	48	42	37	43	38	34	39	35	32	29																				
7	62	50	42	36	59	48	40	35	44	37	33	40	35	31	36	32	29	26																				
8	58	46	38	32	55	44	36	31	40	34	29	36	31	28	33	29	26	24																				
9	54	42	34	29	51	40	33	28	37	31	27	34	29	25	31	26	23	21																				
10	51	39	31	26	48	37	30	26	34	28	24	31	26	23	29	24	21	19																				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	21068	21068	21068
5°	21149	20857	20977
10°	21029	20595	20525
15°	20803	20113	19900
20°	20492	19511	19057
25°	20173	18834	18231
30°	19750	18053	17066
35°	19316	17270	16000
40°	18916	16350	14677
45°	18389	15440	13484
50°	17811	14408	12149
55°	17220	13226	10903
60°	16678	11961	9535
65°	15969	10593	8166
70°	15087	8894	6593
75°	13795	6995	6209
80°	12298	6199	5709
85°	10387	5483	5101



TEST NUMBER: P332472-840

CATALOG NUMBER: S123RDIW-S1165D460U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.8	2.9
10°-20°	511.4	8.1
20°-30°	736.4	11.7
30°-40°	829.4	13.2
40°-50°	793.5	12.6
50°-60°	649.8	10.3
60°-70°	438.4	7.0
70°-80°	220.6	3.5
80°-90°	60.1	1.0
90°-100°	22.2	0.4
100°-110°	105.8	1.7
110°-120°	254.2	4.0
120°-130°	323.7	5.1
130°-140°	345.8	5.5
140°-150°	323.4	5.1
150°-160°	260.8	4.1
160°-170°	168.4	2.7
170°-180°	58.0	0.9
0°-30°	1431.6	22.8
0°-40°	2261.0	36.0
0°-60°	3704.3	58.9
0°-90°	4423.4	70.4
90°-120°	382.2	6.1
90°-150°	1375.1	21.9
90°-180°	1862.0	29.6
0°-180°	6285.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1957	1957	1957	1957	1957	
5°	1957	1949	1930	1944	1941	186
15°	1867	1848	1805	1797	1786	526
25°	1698	1657	1586	1553	1535	781
35°	1470	1411	1314	1248	1218	920
45°	1208	1134	1014	927	886	932
55°	918	837	705	616	581	822
65°	627	538	416	342	321	620
75°	332	255	168	153	149	354
85°	84	51	44	41	41	94
90°	0	5	11	13	14	5
95°	28	10	14	17	17	34
105°	135	138	99	24	20	143
115°	254	256	260	265	267	250
125°	358	361	363	364	365	319
135°	445	448	450	451	450	343
145°	514	517	518	519	519	321
155°	566	565	565	567	565	261
165°	597	595	595	598	595	169
175°	611	608	609	612	608	58
180°	611	611	611	611	611	



TEST NUMBER: P332472-840

CATALOG NUMBER: S123RDIW-S1165D460U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3
2.5°	1963.7	1962.5	1961.4	1960.2	1959.1	1956.8	1953.5	1950.0	1946.7	1943.3	1946.4
5°	1957.3	1955.5	1953.8	1952.0	1950.3	1947.2	1943.0	1938.7	1934.5	1930.3	1933.5
7.5°	1939.1	1937.3	1935.4	1933.5	1931.6	1927.8	1922.4	1916.8	1911.4	1905.8	1907.6
10°	1924.0	1921.5	1919.0	1916.5	1914.1	1909.7	1903.3	1896.9	1890.6	1884.3	1884.6
12.5°	1902.4	1899.7	1896.8	1894.1	1891.4	1886.1	1878.3	1870.6	1862.8	1855.0	1854.8
15°	1866.8	1862.9	1859.1	1855.1	1851.3	1844.4	1834.5	1824.6	1814.7	1804.9	1803.1
17.5°	1822.0	1817.6	1813.0	1808.5	1804.0	1795.4	1782.9	1770.3	1757.8	1745.2	1741.5
20°	1789.0	1783.4	1777.8	1772.1	1766.5	1757.0	1743.5	1730.1	1716.7	1703.3	1698.7
22.5°	1752.2	1745.7	1739.2	1732.7	1726.3	1715.9	1701.6	1687.4	1673.1	1658.8	1653.1
25°	1698.5	1689.7	1680.9	1672.0	1663.2	1650.7	1634.5	1618.3	1602.0	1585.8	1578.4
27.5°	1633.5	1623.8	1614.0	1604.3	1594.5	1580.6	1562.6	1544.5	1526.4	1508.3	1498.0
30°	1589.0	1578.4	1567.8	1557.2	1546.7	1531.5	1511.8	1492.0	1472.3	1452.5	1440.5
32.5°	1544.6	1532.6	1520.6	1508.5	1496.6	1480.2	1459.3	1438.4	1417.4	1396.6	1383.5
35°	1470.0	1457.2	1444.5	1431.9	1419.2	1401.9	1380.0	1358.2	1336.3	1314.3	1299.2
37.5°	1394.4	1380.3	1366.1	1352.0	1338.0	1319.2	1295.9	1272.5	1249.2	1225.8	1208.6
40°	1346.2	1330.6	1315.0	1299.6	1284.0	1263.7	1238.7	1213.7	1188.6	1163.6	1145.2
42.5°	1291.5	1276.0	1260.5	1245.0	1229.4	1208.7	1182.9	1156.9	1131.0	1105.2	1085.1
45°	1208.0	1192.1	1176.3	1160.4	1144.5	1123.0	1095.8	1068.6	1041.5	1014.3	994.2
47.5°	1124.5	1107.1	1089.6	1072.3	1054.8	1032.5	1005.3	978.2	951.0	923.9	902.0
50°	1063.6	1047.0	1030.4	1013.8	997.2	974.7	946.1	917.6	889.0	860.4	838.5
52.5°	1009.0	991.0	973.0	955.0	937.0	913.8	885.6	857.3	829.0	800.7	778.0
55°	917.6	900.2	882.9	865.7	848.4	824.8	794.8	764.8	734.8	704.8	684.4
57.5°	833.0	814.3	795.4	776.6	757.7	733.3	703.2	673.0	642.9	612.8	593.4
60°	774.7	755.3	735.9	716.5	697.0	672.7	643.4	614.2	584.9	555.6	536.5
62.5°	716.2	696.8	677.4	658.0	638.6	614.3	585.0	555.7	526.4	497.2	479.3
65°	627.0	607.6	588.2	568.9	549.5	525.9	498.5	470.9	443.4	415.9	398.6
67.5°	537.9	518.2	498.6	479.0	459.4	436.4	410.0	383.5	357.2	330.8	317.9
70°	479.4	460.4	441.3	422.2	403.2	381.3	356.7	331.9	307.3	282.6	270.2
72.5°	421.0	402.2	383.4	364.7	345.9	325.3	302.9	280.4	258.0	235.6	225.5
75°	331.7	314.9	297.9	280.9	264.1	245.9	226.5	207.0	187.6	168.2	164.7
77.5°	250.4	235.2	219.8	204.6	189.2	175.3	162.9	150.4	137.8	125.4	123.5
80°	198.4	184.0	169.5	155.0	140.6	129.7	122.2	114.8	107.4	100.0	99.0
82.5°	148.9	136.4	123.9	111.4	99.0	91.0	87.6	84.0	80.6	77.2	76.0
85°	84.1	76.3	68.6	60.9	53.1	48.7	47.7	46.6	45.5	44.4	43.7
87.5°	30.6	27.7	24.7	21.8	19.0	17.7	17.9	18.2	18.4	18.7	18.5
90°	0.4	1.4	2.4	3.4	4.4	5.7	7.0	8.3	9.6	10.9	11.3
92.5°	8.5	8.2	7.9	7.6	7.3	7.7	8.7	9.6	10.6	11.6	12.2
95°	27.7	23.5	19.4	15.2	11.1	9.6	10.7	11.8	12.9	14.0	14.7
97.5°	55.6	53.7	51.9	50.1	48.2	43.6	36.4	29.1	21.9	14.6	15.5
100°	76.6	78.7	80.7	82.7	84.7	77.9	62.2	46.5	30.7	14.9	15.8
102.5°	100.6	102.1	103.5	105.0	106.4	98.6	81.4	64.2	47.1	29.9	27.4
105°	135.2	136.3	137.4	138.6	139.7	135.6	126.5	117.5	108.5	99.4	81.5
107.5°	171.7	172.6	173.5	174.3	175.2	176.4	177.8	179.3	180.7	182.1	169.1
110°	196.0	196.8	197.6	198.4	199.2	200.2	201.3	202.4	203.5	204.6	201.3



TEST NUMBER: P332472-840

CATALOG NUMBER: S123RDIW-S1165D460U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	219.2	219.9	220.7	221.4	222.2	223.1	224.2	225.3	226.4	227.5	227.5
115°	253.6	254.2	254.8	255.4	256.0	256.8	257.7	258.6	259.5	260.4	261.5
117.5°	286.9	287.7	288.4	289.1	289.9	290.5	290.9	291.4	292.0	292.4	293.2
120°	307.6	308.5	309.4	310.3	311.2	311.8	312.1	312.5	312.8	313.1	313.9
122.5°	328.7	329.4	330.1	330.9	331.6	332.2	332.6	333.0	333.4	333.8	334.3
125°	357.5	358.3	359.1	359.9	360.7	361.3	361.7	362.1	362.5	362.9	363.1
127.5°	385.5	386.3	387.1	387.9	388.7	389.3	389.8	390.3	390.8	391.3	391.6
130°	402.9	403.7	404.6	405.4	406.2	406.8	407.2	407.6	408.0	408.3	408.7
132.5°	419.6	420.4	421.2	422.0	422.8	423.3	423.7	424.0	424.3	424.6	425.1
135°	445.0	445.7	446.3	446.9	447.5	448.0	448.4	448.8	449.2	449.6	449.9
137.5°	466.9	467.7	468.4	469.2	469.9	470.4	470.7	470.9	471.1	471.3	471.8
140°	481.4	482.0	482.6	483.2	483.8	484.2	484.5	484.8	485.1	485.4	485.8
142.5°	494.8	495.4	496.0	496.7	497.3	497.7	498.0	498.3	498.6	498.9	499.2
145°	513.6	514.3	515.0	515.7	516.4	516.8	517.1	517.3	517.5	517.7	517.9
147.5°	531.3	531.8	532.2	532.7	533.1	533.5	533.7	533.9	534.1	534.3	534.5
150°	542.2	542.5	542.8	543.1	543.4	543.6	543.8	544.0	544.2	544.4	544.6
152.5°	552.0	552.1	552.3	552.4	552.6	552.7	552.8	552.9	553.0	553.2	553.5
155°	565.7	565.5	565.3	565.2	565.0	564.9	565.0	565.1	565.2	565.3	565.8
157.5°	576.5	576.4	576.4	576.4	576.4	576.3	576.2	576.1	576.0	575.9	576.5
160°	583.0	582.9	582.8	582.7	582.6	582.5	582.4	582.3	582.2	582.1	582.7
162.5°	589.2	589.0	588.7	588.4	588.1	587.9	587.8	587.7	587.6	587.5	588.2
165°	596.6	596.3	596.0	595.7	595.4	595.2	595.1	595.0	594.9	594.8	595.6
167.5°	602.5	602.1	601.7	601.3	600.9	600.7	600.7	600.7	600.7	600.7	601.5
170°	605.7	605.3	604.9	604.5	604.1	603.9	603.9	603.9	603.9	603.9	604.7
172.5°	607.8	607.4	606.9	606.4	605.9	605.7	605.8	605.9	606.0	606.0	606.8
175°	610.7	610.2	609.7	609.2	608.6	608.4	608.5	608.6	608.7	608.8	609.6
177.5°	611.4	611.0	610.6	610.2	609.8	609.7	609.8	609.8	609.9	610.0	610.6
180°	610.7	610.7	610.7	610.7	610.7	610.7	610.7	610.7	610.7	610.7	610.7



TEST NUMBER: P332472-840

CATALOG NUMBER: S123RDIW-S1165D460U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3
2.5°	1949.5	1952.7	1955.7	1957.0	1956.4	1955.9	1955.3	1954.7
5°	1936.6	1939.8	1943.0	1944.2	1943.5	1942.8	1942.1	1941.4
7.5°	1909.4	1911.2	1912.9	1913.2	1912.0	1910.8	1909.6	1908.3
10°	1885.0	1885.3	1885.7	1885.0	1883.2	1881.5	1879.7	1877.9
12.5°	1854.6	1854.4	1854.2	1853.1	1851.1	1849.0	1846.9	1844.9
15°	1801.4	1799.6	1797.9	1795.7	1793.2	1790.8	1788.3	1785.8
17.5°	1737.8	1733.9	1730.2	1726.6	1722.8	1719.2	1715.6	1711.8
20°	1694.1	1689.5	1685.0	1680.5	1676.3	1672.0	1667.9	1663.7
22.5°	1647.4	1641.7	1636.0	1631.1	1627.2	1623.3	1619.3	1615.4
25°	1571.0	1563.6	1556.2	1550.5	1546.7	1542.8	1538.9	1535.0
27.5°	1487.7	1477.4	1467.1	1459.1	1453.1	1447.2	1441.3	1435.3
30°	1428.5	1416.5	1404.5	1395.7	1390.1	1384.4	1378.8	1373.1
32.5°	1370.4	1357.3	1344.1	1334.6	1328.7	1322.7	1316.9	1310.9
35°	1284.0	1268.9	1253.7	1242.9	1236.6	1230.2	1223.9	1217.6
37.5°	1191.3	1174.2	1156.9	1144.4	1136.6	1128.7	1121.0	1113.1
40°	1126.9	1108.5	1090.3	1077.0	1068.8	1060.8	1052.7	1044.5
42.5°	1065.1	1045.0	1025.0	1011.4	1004.1	996.8	989.6	982.3
45°	974.1	954.0	933.9	919.7	911.2	902.7	894.2	885.8
47.5°	880.1	858.3	836.4	821.7	814.2	806.6	799.0	791.5
50°	816.7	794.8	772.8	757.9	749.8	741.6	733.6	725.5
52.5°	755.3	732.6	709.8	694.8	687.5	680.3	673.1	665.8
55°	663.9	643.4	623.0	609.3	602.2	595.1	588.0	581.0
57.5°	574.1	554.7	535.4	522.7	516.7	510.8	504.7	498.8
60°	517.5	498.5	479.4	466.9	460.9	454.8	448.9	442.9
62.5°	461.3	443.4	425.5	413.4	407.1	400.8	394.6	388.3
65°	381.3	364.1	346.8	336.2	332.3	328.4	324.6	320.6
67.5°	305.0	292.1	279.1	270.6	266.5	262.3	258.1	254.0
70°	257.8	245.5	233.2	225.1	221.2	217.3	213.4	209.5
72.5°	215.4	205.3	195.2	189.3	187.7	186.1	184.5	182.9
75°	161.2	157.6	154.1	152.1	151.4	150.7	150.0	149.3
77.5°	121.6	119.7	117.8	116.4	115.7	115.0	114.3	113.6
80°	97.9	96.8	95.7	94.9	94.2	93.5	92.8	92.1
82.5°	75.0	74.0	72.9	72.3	72.2	72.0	71.9	71.8
85°	43.0	42.3	41.6	41.3	41.3	41.3	41.3	41.3
87.5°	18.3	18.1	17.9	17.7	17.4	17.2	17.0	16.7
90°	11.7	12.1	12.5	12.8	13.0	13.2	13.4	13.6
92.5°	12.9	13.5	14.2	14.5	14.7	14.8	14.9	15.0
95°	15.5	16.2	16.9	17.3	17.3	17.3	17.3	17.3
97.5°	16.3	17.1	17.9	18.3	18.4	18.5	18.6	18.7
100°	16.6	17.4	18.2	18.7	18.8	18.9	19.0	19.1
102.5°	24.8	22.3	19.9	18.7	18.9	19.1	19.2	19.4
105°	63.6	45.8	28.0	19.2	19.4	19.6	19.8	20.0
107.5°	155.9	142.9	129.8	116.5	103.0	89.6	76.1	62.7
110°	197.9	194.6	191.3	182.5	168.0	153.6	139.2	124.8



TEST NUMBER: P332472-840

CATALOG NUMBER: S123RDIW-S1165D460U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	227.6	227.6	227.7	226.2	223.2	220.2	217.1	214.1
115°	262.5	263.5	264.5	265.2	265.6	266.0	266.4	266.8
117.5°	294.0	294.8	295.6	296.0	296.1	296.2	296.3	296.4
120°	314.7	315.5	316.3	316.7	316.7	316.7	316.7	316.7
122.5°	334.9	335.5	336.0	336.3	336.4	336.5	336.6	336.7
125°	363.3	363.6	363.8	364.0	364.2	364.4	364.6	364.8
127.5°	391.9	392.2	392.5	392.6	392.4	392.2	392.0	391.8
130°	409.1	409.5	409.9	410.0	409.8	409.6	409.4	409.2
132.5°	425.5	425.9	426.3	426.4	426.1	425.8	425.5	425.3
135°	450.2	450.5	450.8	450.8	450.5	450.2	449.9	449.6
137.5°	472.3	472.7	473.2	473.4	473.2	473.0	472.8	472.6
140°	486.3	486.7	487.1	487.2	487.0	486.8	486.6	486.4
142.5°	499.6	499.9	500.2	500.2	499.9	499.7	499.4	499.1
145°	518.1	518.3	518.5	518.6	518.6	518.6	518.6	518.6
147.5°	534.7	534.9	535.1	534.9	534.5	534.0	533.6	533.1
150°	544.8	545.0	545.2	545.2	544.9	544.6	544.3	544.0
152.5°	553.9	554.2	554.6	554.5	554.1	553.6	553.2	552.7
155°	566.3	566.8	567.3	567.2	566.6	566.0	565.4	564.9
157.5°	577.1	577.7	578.3	578.2	577.4	576.7	575.9	575.1
160°	583.3	583.9	584.5	584.5	583.8	583.1	582.4	581.7
162.5°	589.0	589.7	590.3	590.4	589.7	589.1	588.4	587.8
165°	596.4	597.2	598.0	598.0	597.3	596.7	596.0	595.3
167.5°	602.3	603.0	603.8	603.8	603.0	602.3	601.5	600.7
170°	605.5	606.3	607.1	607.1	606.3	605.5	604.7	603.9
172.5°	607.6	608.4	609.3	609.3	608.3	607.4	606.6	605.7
175°	610.3	611.0	611.7	611.7	610.9	610.1	609.3	608.4
177.5°	611.3	611.9	612.6	612.5	611.7	610.9	610.1	609.3
180°	610.7	610.7	610.7	610.7	610.7	610.7	610.7	610.7

(END OF REPORT)