

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333104-927

Luminaire Tested: **S124RDIW-S1195D1050U927-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333104-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S1195D1050U927-4F0-1E-UDD-A1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1050 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6850.2 lumens
Efficiency: N/A
Efficacy: 101.6 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 67.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333104-927

CATALOG NUMBER: S124RDIW-S1195D1050U927-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333104-927

CATALOG NUMBER: S124RDIW-S1195D1050U927-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	63	63	63	58																												
1	100	96	92	89	93	90	86	83	78	75	73	67	65	64	57	56	55	50																												
2	92	84	78	73	85	79	74	69	69	65	62	59	57	54	51	49	47	43																												
3	84	75	67	62	78	70	64	59	61	56	52	53	49	46	45	43	40	37																												
4	77	66	59	53	72	62	55	50	55	49	45	48	43	40	41	38	35	32																												
5	71	59	51	46	66	56	49	43	49	43	39	43	38	35	37	34	31	28																												
6	65	54	46	40	61	50	43	38	44	39	34	39	34	31	34	30	27	25																												
7	61	48	41	35	56	46	39	34	40	35	31	36	31	28	31	27	25	22																												
8	56	44	36	31	53	42	35	30	37	31	27	33	28	25	28	25	22	20																												
9	53	40	33	28	49	38	31	27	34	28	25	30	26	22	26	23	20	18																												
10	49	37	30	25	46	35	29	24	31	26	22	28	23	20	24	21	18	16																												

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	12674	12674	12674	12674
5°	14699	12712	11235	12712
10°	17390	12656	10027	12656
15°	20088	12538	8616	12538
20°	22365	12378	7792	12378
25°	23087	12219	7234	12219
30°	20211	12028	6898	12028
35°	15733	11744	6695	11744
40°	11798	11418	6585	11418
45°	9315	10896	6528	10896
50°	7863	10295	6339	10295
55°	6854	9633	6000	9633
60°	6168	8946	5310	8946
65°	5436	8202	4567	8202
70°	4898	7435	4121	7435
75°	4105	6591	3512	6591
80°	3468	5616	3292	5616
85°	2927	4400	2927	4400



TEST NUMBER: P333104-927

CATALOG NUMBER: S124RDIW-S1195D1050U927-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	152.1	2.2
10°-20°	458.8	6.7
20°-30°	717.6	10.5
30°-40°	797.8	11.6
40°-50°	707.8	10.3
50°-60°	551.5	8.1
60°-70°	361.1	5.3
70°-80°	177.6	2.6
80°-90°	46.9	0.7
90°-100°	68.4	1.0
100°-110°	202.7	3.0
110°-120°	344.1	5.0
120°-130°	453.7	6.6
130°-140°	509.6	7.4
140°-150°	500.8	7.3
150°-160°	421.2	6.1
160°-170°	280.2	4.1
170°-180°	98.1	1.4
0°-30°	1328.5	19.4
0°-40°	2126.3	31.0
0°-60°	3385.7	49.4
0°-90°	3971.2	58.0
90°-120°	615.3	9.0
90°-150°	2079.4	30.4
90°-180°	2879.0	42.0
0°-180°	6850.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1570	1570	1570	1570	1570	
5°	1814	1569	1386	1569	1814	183
15°	2404	1500	1031	1500	2404	683
25°	2592	1372	812	1372	2592	1150
35°	1596	1192	679	1192	1596	1001
45°	816	954	572	954	816	646
55°	487	684	426	684	487	443
65°	285	429	239	429	285	286
75°	132	211	113	211	132	145
85°	32	48	32	48	32	36
90°	24	2	24	2	24	14
95°	63	48	63	48	63	66
105°	196	187	196	187	196	206
115°	347	350	347	350	347	343
125°	506	510	506	510	506	451
135°	658	657	658	657	658	508
145°	799	798	799	798	799	500
155°	914	915	914	915	914	421
165°	994	996	994	996	994	280
175°	1031	1036	1031	1036	1031	98
180°	1038	1038	1038	1038	1038	



TEST NUMBER: P333104-927

CATALOG NUMBER: S124RDIW-S1195D1050U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9
2.5°	1655.8	1660.4	1655.8	1655.3	1650.3	1648.8	1646.7	1640.1	1628.0	1621.0	1622.5
5°	1813.9	1829.8	1820.9	1819.6	1805.8	1791.8	1783.0	1762.8	1741.2	1726.7	1714.7
7.5°	1996.9	2006.0	2000.4	1991.5	1969.0	1956.3	1935.8	1909.1	1870.5	1841.0	1814.1
10°	2121.4	2128.9	2126.5	2110.0	2093.5	2060.0	2041.1	2003.7	1955.0	1916.4	1880.4
12.5°	2243.8	2251.9	2229.7	2230.4	2199.3	2172.9	2142.8	2095.8	2039.6	1989.8	1944.6
15°	2403.5	2393.3	2393.3	2380.7	2345.9	2309.2	2278.2	2228.9	2158.1	2098.6	2036.0
17.5°	2528.4	2532.0	2526.7	2497.0	2469.6	2431.7	2374.9	2317.3	2251.5	2171.7	2107.7
20°	2603.3	2603.3	2597.6	2577.4	2542.0	2501.5	2440.2	2377.5	2294.0	2213.7	2141.6
22.5°	2633.7	2635.7	2629.0	2612.3	2580.5	2540.9	2488.7	2425.1	2339.1	2248.6	2159.3
25°	2591.9	2604.0	2605.2	2600.8	2591.3	2567.2	2522.4	2457.2	2380.0	2282.0	2185.9
27.5°	2379.6	2394.8	2408.2	2430.0	2459.1	2474.3	2476.3	2443.2	2375.8	2281.5	2184.8
30°	2168.1	2180.8	2221.9	2275.7	2317.5	2355.4	2388.3	2397.1	2359.2	2274.4	2172.6
32.5°	1933.4	1950.6	1991.7	2049.5	2119.1	2183.3	2257.2	2294.9	2293.9	2243.1	2148.8
35°	1596.4	1609.1	1647.0	1707.7	1791.2	1886.7	2003.7	2094.8	2156.8	2152.4	2094.8
37.5°	1287.5	1301.8	1340.1	1390.4	1471.4	1589.7	1702.9	1828.4	1943.0	2007.4	1988.1
40°	1119.5	1120.1	1157.5	1209.3	1285.2	1388.3	1511.6	1650.7	1778.5	1882.9	1903.1
42.5°	986.9	987.1	1011.7	1067.6	1122.3	1219.3	1337.0	1475.2	1624.8	1745.3	1798.9
45°	815.9	821.6	841.9	875.4	918.4	1000.6	1094.8	1223.2	1390.8	1533.7	1622.9
47.5°	690.9	699.3	712.2	739.5	773.8	828.5	906.5	1021.8	1158.2	1315.4	1442.3
50°	626.1	627.4	643.9	659.0	688.8	732.5	800.7	896.8	1022.1	1173.2	1314.3
52.5°	570.5	570.2	580.1	599.4	623.5	657.5	712.6	800.2	911.2	1046.8	1192.4
55°	487.0	490.2	497.7	512.9	531.3	555.3	599.0	664.7	752.0	867.8	1000.0
57.5°	423.5	425.2	431.1	437.5	454.4	471.8	504.6	550.2	623.9	718.7	841.9
60°	382.0	382.6	384.5	394.0	407.3	423.7	445.9	484.5	546.4	633.1	730.6
62.5°	341.5	342.7	345.6	352.5	362.8	374.1	397.4	428.3	479.7	553.7	641.4
65°	284.6	285.3	289.7	292.2	300.4	310.5	327.6	348.5	383.9	445.9	512.3
67.5°	237.8	237.8	238.1	241.5	247.2	253.9	264.1	280.8	307.5	345.6	404.2
70°	207.5	207.5	208.7	210.6	213.8	219.4	225.1	237.8	257.5	288.4	333.4
72.5°	179.1	179.6	180.9	181.3	182.9	187.6	191.8	199.9	214.4	237.8	274.1
75°	131.6	133.5	136.7	139.2	142.3	141.6	146.1	151.1	155.6	169.5	190.4
77.5°	97.9	96.9	97.3	99.4	99.8	100.4	103.6	107.5	110.8	117.4	124.8
80°	74.6	74.6	76.5	77.2	76.5	77.2	80.3	82.2	83.5	86.0	93.0
82.5°	56.4	57.4	56.8	57.4	57.8	58.5	61.1	61.5	62.7	63.8	66.7
85°	31.6	32.2	32.9	31.6	31.6	31.6	32.9	33.5	34.8	34.1	35.4
87.5°	15.9	15.4	15.8	15.8	16.2	15.5	15.8	16.6	15.4	15.7	15.4
90°	24.1	23.7	23.4	23.0	22.7	21.9	20.8	19.8	18.7	17.7	16.2
92.5°	35.6	35.4	35.2	35.0	34.8	34.4	33.7	33.0	32.4	31.8	30.8
95°	63.4	63.4	63.4	63.4	63.4	63.1	62.6	62.0	61.6	61.0	59.7
97.5°	99.3	99.3	99.3	99.3	99.3	99.0	98.4	97.8	97.1	96.5	95.0
100°	124.4	124.4	124.4	124.4	124.4	124.2	123.8	123.5	123.1	122.8	121.2
102.5°	152.7	152.5	152.3	152.2	152.1	151.8	151.2	150.8	150.3	149.7	148.3
105°	195.8	195.3	194.7	194.2	193.7	193.1	192.6	192.1	191.5	191.0	190.3
107.5°	237.9	237.9	238.0	238.0	238.0	237.8	237.3	236.8	236.3	235.8	235.7
110°	268.1	267.5	267.0	266.4	265.9	265.8	266.2	266.5	266.9	267.2	267.4



TEST NUMBER: P333104-927

CATALOG NUMBER: S124RDIW-S1195D1050U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	298.9	298.7	298.7	298.6	298.4	298.4	298.5	298.6	298.7	298.7	299.0
115°	346.7	346.9	347.1	347.2	347.4	347.6	347.8	347.9	348.1	348.3	348.6
117.5°	392.3	392.6	393.0	393.3	393.7	394.2	394.7	395.4	396.0	396.6	396.9
120°	426.9	426.6	426.2	425.9	425.5	425.8	426.7	427.5	428.5	429.4	429.9
122.5°	455.8	456.5	457.1	457.7	458.4	459.0	459.6	460.3	460.8	461.4	461.7
125°	505.6	506.0	506.3	506.7	507.0	507.4	507.7	508.1	508.4	508.8	509.0
127.5°	551.7	551.9	552.2	552.5	552.8	553.1	553.5	553.8	554.2	554.5	554.8
130°	581.9	582.6	583.3	584.0	584.7	585.2	585.6	585.9	586.3	586.6	586.6
132.5°	613.9	614.2	614.5	614.8	615.1	615.4	615.8	616.1	616.5	616.8	617.0
135°	658.1	658.6	659.1	659.7	660.2	660.7	661.0	661.4	661.7	662.1	662.1
137.5°	704.4	704.3	704.3	704.1	704.0	704.2	704.6	705.1	705.6	706.1	705.8
140°	732.7	732.8	733.1	733.2	733.4	733.6	733.8	734.0	734.1	734.3	734.3
142.5°	761.0	761.0	761.0	761.0	761.0	761.1	761.1	761.2	761.2	761.3	761.4
145°	799.3	799.9	800.3	800.9	801.5	801.8	802.0	802.2	802.3	802.5	802.3
147.5°	838.1	838.3	838.5	838.7	838.8	839.0	839.2	839.3	839.5	839.6	839.7
150°	861.9	862.1	862.3	862.4	862.6	862.7	862.7	862.7	862.7	862.7	862.7
152.5°	883.8	884.2	884.6	885.1	885.6	885.6	885.2	884.7	884.3	883.9	883.8
155°	914.1	914.8	915.5	916.2	917.0	917.0	916.2	915.5	914.8	914.1	914.3
157.5°	941.2	941.8	942.4	943.0	943.6	943.6	943.1	942.6	942.1	941.5	941.5
160°	956.6	957.5	958.4	959.3	960.1	960.4	959.8	959.3	958.7	958.2	958.4
162.5°	972.6	973.5	974.5	975.3	976.2	976.2	975.2	974.2	973.3	972.3	972.5
165°	993.5	994.2	994.9	995.6	996.3	996.2	995.1	994.0	993.0	991.9	992.3
167.5°	1008.4	1009.6	1010.7	1011.8	1012.9	1012.9	1011.8	1010.7	1009.6	1008.6	1008.5
170°	1016.8	1018.0	1019.3	1020.6	1021.8	1021.8	1020.8	1019.7	1018.7	1017.6	1017.4
172.5°	1023.8	1025.1	1026.4	1027.6	1028.8	1028.9	1027.6	1026.4	1025.2	1024.0	1024.0
175°	1031.3	1032.5	1033.7	1035.0	1036.3	1036.3	1035.0	1033.7	1032.5	1031.3	1031.4
177.5°	1035.1	1036.3	1037.4	1038.5	1039.7	1039.7	1038.7	1037.8	1036.7	1035.7	1035.7
180°	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7



TEST NUMBER: P333104-927

CATALOG NUMBER: S124RDIW-S1195D1050U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9
2.5°	1617.4	1610.3	1606.8	1598.7	1589.0	1584.0	1579.5	1572.9	1564.2	1555.1	1548.6
5°	1699.5	1684.3	1665.3	1642.6	1622.3	1602.7	1585.6	1568.6	1549.0	1528.8	1508.5
7.5°	1783.8	1753.9	1721.6	1684.3	1648.0	1615.0	1584.6	1555.5	1522.7	1493.2	1466.3
10°	1842.5	1802.0	1757.1	1709.6	1662.2	1621.0	1580.6	1543.9	1503.4	1467.4	1437.0
12.5°	1890.0	1842.5	1788.4	1729.3	1672.3	1622.5	1576.0	1528.2	1482.2	1443.1	1402.6
15°	1968.9	1903.8	1831.1	1760.2	1686.2	1618.5	1555.9	1500.2	1447.8	1392.7	1354.2
17.5°	2023.2	1945.9	1857.5	1772.3	1685.0	1605.1	1532.9	1466.6	1406.0	1349.9	1303.9
20°	2055.6	1970.2	1872.2	1775.4	1677.4	1592.0	1514.2	1440.8	1378.2	1317.5	1270.0
22.5°	2073.8	1979.3	1872.2	1770.8	1669.3	1576.8	1491.4	1415.0	1346.8	1286.1	1233.6
25°	2079.6	1978.4	1869.0	1752.6	1641.3	1543.3	1454.7	1371.8	1295.9	1235.2	1179.6
27.5°	2071.6	1952.3	1840.3	1720.9	1606.0	1502.7	1409.7	1322.6	1246.7	1181.5	1124.4
30°	2059.4	1931.6	1811.4	1687.5	1571.1	1471.8	1373.7	1290.3	1211.2	1143.5	1086.0
32.5°	2033.1	1906.3	1777.0	1650.0	1532.2	1429.8	1336.8	1252.8	1175.3	1106.1	1045.0
35°	1980.9	1852.5	1712.1	1581.8	1466.1	1359.9	1272.6	1191.6	1117.6	1043.6	979.1
37.5°	1912.2	1781.1	1641.4	1498.7	1382.8	1282.5	1202.5	1126.5	1054.2	986.7	915.2
40°	1847.5	1728.0	1583.7	1442.1	1323.2	1226.4	1152.4	1083.5	1010.7	943.6	872.2
42.5°	1769.1	1667.2	1521.5	1379.3	1261.9	1168.7	1099.8	1032.4	966.2	901.2	826.6
45°	1638.2	1561.0	1424.3	1287.8	1169.5	1077.1	1013.9	954.4	896.2	834.2	764.1
47.5°	1488.1	1435.8	1318.0	1178.1	1068.7	985.6	924.5	875.8	826.6	764.7	703.1
50°	1383.9	1350.4	1236.5	1108.7	1004.4	927.9	865.2	819.7	778.6	719.1	664.1
52.5°	1272.6	1254.7	1158.6	1036.4	935.6	860.5	807.1	766.0	724.5	675.1	623.6
55°	1103.0	1112.5	1030.9	925.3	830.4	767.2	718.5	684.4	649.0	607.2	567.4
57.5°	929.8	964.4	909.7	816.9	728.0	669.6	632.9	604.1	574.4	539.8	505.7
60°	826.0	855.1	824.1	742.5	664.7	610.4	576.2	554.1	524.3	492.7	466.8
62.5°	724.8	756.0	737.6	671.7	599.4	552.7	522.5	501.9	479.8	452.3	425.3
65°	597.7	617.9	609.1	563.6	512.3	472.5	444.7	429.4	409.2	389.0	365.0
67.5°	457.8	496.9	491.7	467.5	423.3	392.1	373.9	360.5	342.1	327.0	310.7
70°	376.4	412.4	411.8	392.1	368.1	339.0	326.4	315.0	298.5	284.0	270.7
72.5°	308.0	341.0	345.9	330.9	314.5	292.5	280.4	272.5	256.5	246.5	235.8
75°	215.7	239.7	246.1	246.1	238.4	227.0	216.3	211.3	199.9	191.0	184.7
77.5°	141.4	156.6	166.4	168.7	169.9	166.1	157.2	153.7	145.0	141.8	135.7
80°	99.9	110.0	121.4	125.2	128.4	127.1	123.3	120.8	112.6	109.4	106.9
82.5°	69.1	74.6	84.0	92.4	91.4	94.7	91.4	89.4	83.3	82.1	79.5
85°	36.0	36.7	37.9	43.6	46.8	48.1	48.7	47.5	45.6	45.6	41.1
87.5°	15.1	14.3	15.1	14.7	14.8	16.5	17.6	17.7	16.6	15.4	14.3
90°	14.8	13.4	12.0	10.2	8.3	6.3	4.4	2.4	4.4	6.3	8.3
92.5°	29.8	28.8	27.8	26.1	23.9	21.7	19.4	17.2	19.4	21.7	23.9
95°	58.5	57.3	56.0	54.6	53.0	51.3	49.7	48.2	49.7	51.3	53.0
97.5°	93.6	92.1	90.6	89.3	87.9	86.7	85.4	84.1	85.4	86.7	87.9
100°	119.5	118.0	116.4	115.2	114.5	113.8	113.0	112.3	113.0	113.8	114.5
102.5°	146.8	145.4	143.9	143.0	142.8	142.4	142.2	141.9	142.2	142.4	142.8
105°	189.6	188.9	188.1	187.7	187.5	187.4	187.2	187.0	187.2	187.4	187.5
107.5°	235.6	235.4	235.4	235.2	235.0	234.7	234.6	234.3	234.6	234.7	235.0
110°	267.6	267.8	267.9	267.8	267.5	267.1	266.8	266.4	266.8	267.1	267.5



TEST NUMBER: P333104-927

CATALOG NUMBER: S124RDIW-S1195D1050U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	299.4	299.7	300.0	300.1	300.0	300.0	299.9	299.8	299.9	300.0	300.0
115°	349.0	349.4	349.7	349.9	349.9	349.9	349.9	349.9	349.9	349.9	349.9
117.5°	397.1	397.4	397.6	397.7	397.5	397.4	397.2	397.1	397.2	397.4	397.5
120°	430.4	430.9	431.5	431.4	430.7	430.0	429.3	428.6	429.3	430.0	430.7
122.5°	461.9	462.2	462.5	462.4	462.2	461.8	461.6	461.3	461.6	461.8	462.2
125°	509.1	509.3	509.5	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6
127.5°	555.1	555.4	555.7	555.6	555.0	554.4	554.0	553.4	554.0	554.4	555.0
130°	586.6	586.6	586.6	586.4	585.8	585.3	584.8	584.2	584.8	585.3	585.8
132.5°	617.1	617.3	617.3	617.3	616.9	616.5	616.1	615.7	616.1	616.5	616.9
135°	662.1	662.1	662.1	661.6	660.4	659.4	658.3	657.3	658.3	659.4	660.4
137.5°	705.5	705.2	704.9	704.5	704.0	703.5	703.0	702.5	703.0	703.5	704.0
140°	734.3	734.3	734.3	734.1	733.8	733.4	733.1	732.7	733.1	733.4	733.8
142.5°	761.5	761.7	761.8	761.8	761.4	761.0	760.7	760.3	760.7	761.0	761.4
145°	802.2	802.0	801.8	801.4	800.7	799.9	799.2	798.5	799.2	799.9	800.7
147.5°	839.9	840.0	840.2	839.8	838.9	838.1	837.3	836.4	837.3	838.1	838.9
150°	862.7	862.7	862.7	862.4	861.7	860.9	860.2	859.5	860.2	860.9	861.7
152.5°	883.6	883.4	883.3	883.0	882.6	882.2	881.8	881.3	881.8	882.2	882.6
155°	914.4	914.6	914.8	914.9	914.9	914.9	914.9	914.9	914.9	914.9	914.9
157.5°	941.6	941.6	941.7	941.8	942.1	942.5	942.8	943.1	942.8	942.5	942.1
160°	958.5	958.7	958.9	959.1	959.3	959.4	959.6	959.8	959.6	959.4	959.3
162.5°	972.7	972.9	973.0	973.4	973.8	974.3	974.8	975.2	974.8	974.3	973.8
165°	992.6	993.0	993.3	993.8	994.3	994.8	995.4	995.9	995.4	994.8	994.3
167.5°	1008.5	1008.5	1008.4	1008.8	1009.6	1010.3	1011.1	1011.8	1011.1	1010.3	1009.6
170°	1017.2	1017.1	1016.8	1017.2	1018.1	1019.0	1019.9	1020.8	1019.9	1019.0	1018.1
172.5°	1024.0	1023.9	1023.9	1024.2	1025.0	1025.7	1026.4	1027.2	1026.4	1025.7	1025.0
175°	1031.6	1031.7	1032.0	1032.5	1033.4	1034.3	1035.1	1036.0	1035.1	1034.3	1033.4
177.5°	1035.7	1035.7	1035.7	1036.1	1036.8	1037.5	1038.2	1038.9	1038.2	1037.5	1036.8
180°	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7



TEST NUMBER: P333104-927

CATALOG NUMBER: S124RDIW-S1195D1050U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9
2.5°	1541.5	1536.4	1529.9	1522.3	1513.1	1505.1	1501.5	1504.6	1506.1	1502.1	1501.5
5°	1494.5	1478.8	1466.1	1447.2	1431.9	1419.3	1410.5	1406.7	1407.9	1397.8	1395.3
7.5°	1441.9	1423.1	1402.3	1379.8	1358.8	1340.2	1330.5	1325.2	1314.5	1309.9	1302.2
10°	1407.9	1382.6	1362.4	1335.8	1311.8	1289.7	1278.9	1270.0	1259.3	1254.2	1243.5
12.5°	1373.0	1343.6	1321.4	1293.8	1269.2	1242.6	1232.3	1215.9	1199.0	1188.4	1174.6
15°	1323.8	1288.4	1261.2	1228.3	1199.2	1168.9	1141.6	1111.3	1099.9	1075.9	1061.9
17.5°	1266.2	1230.3	1196.7	1152.5	1107.6	1069.9	1040.9	1011.9	994.4	979.1	972.0
20°	1228.3	1195.4	1148.6	1097.3	1047.4	1005.7	982.2	963.3	944.3	933.6	926.0
22.5°	1192.4	1150.3	1096.0	1040.7	990.7	958.1	938.3	918.8	903.3	893.1	883.0
25°	1132.2	1077.1	1019.5	956.3	922.2	893.7	872.2	856.3	846.9	833.6	828.5
27.5°	1070.3	1003.6	940.2	897.6	862.1	836.0	817.3	805.4	793.4	784.9	778.3
30°	1022.7	955.1	898.1	857.6	821.6	800.1	784.9	771.0	761.5	754.6	749.5
32.5°	975.7	908.0	860.2	816.7	788.2	767.2	751.0	740.6	733.2	724.2	721.1
35°	907.6	847.6	805.8	766.6	737.4	718.5	705.8	695.1	688.8	686.3	684.4
37.5°	842.2	793.0	748.1	716.0	690.1	675.1	660.2	654.9	650.5	646.0	648.1
40°	800.7	754.6	714.7	680.6	659.7	643.3	634.4	628.0	624.2	624.2	624.2
42.5°	764.8	719.6	680.8	650.2	629.3	615.4	605.5	600.2	599.0	598.5	601.5
45°	709.0	667.3	628.0	602.8	585.0	571.2	565.5	561.0	561.0	563.6	564.2
47.5°	653.7	614.7	583.1	554.8	538.6	529.9	525.0	522.7	522.9	525.5	528.4
50°	619.8	581.2	550.2	525.0	509.8	501.5	497.1	495.9	497.1	497.1	501.5
52.5°	582.9	548.3	517.8	496.6	479.4	471.7	469.3	467.5	468.3	470.3	472.2
55°	528.8	497.7	468.7	448.5	435.8	430.7	425.0	425.6	424.4	425.6	425.6
57.5°	474.5	446.6	419.6	403.5	392.4	385.1	378.8	380.6	378.7	378.5	377.5
60°	439.6	409.2	387.7	373.2	360.5	354.2	348.5	349.7	347.8	346.6	344.0
62.5°	401.6	376.4	355.8	341.8	331.7	324.3	318.6	317.3	313.0	308.6	303.1
65°	346.6	325.7	307.4	294.1	284.6	278.9	274.5	270.7	261.2	251.1	246.1
67.5°	293.1	278.1	260.9	249.7	242.0	234.6	226.1	219.6	210.7	205.2	202.0
70°	258.6	244.2	229.6	218.8	210.6	203.7	194.2	189.7	183.4	180.9	177.8
72.5°	225.8	212.2	198.8	189.0	180.2	174.8	167.4	163.0	160.2	159.1	156.0
75°	175.9	165.1	155.0	146.1	139.2	135.4	132.2	129.0	127.8	122.1	118.9
77.5°	128.3	121.2	114.9	108.5	103.6	101.1	95.0	91.3	89.2	86.5	85.9
80°	99.9	94.9	88.6	84.8	77.8	75.3	72.7	72.1	71.5	70.8	70.2
82.5°	75.2	70.1	63.8	61.5	59.6	58.1	56.6	55.9	55.3	55.7	55.5
85°	37.9	35.4	35.4	34.8	34.1	33.5	32.9	32.9	32.2	32.9	32.2
87.5°	14.7	14.5	14.8	14.1	14.9	15.1	14.9	15.1	15.8	15.1	15.1
90°	10.2	12.0	13.4	14.8	16.2	17.7	18.7	19.8	20.8	21.9	22.7
92.5°	26.1	27.8	28.8	29.8	30.8	31.8	32.4	33.0	33.7	34.4	34.8
95°	54.6	56.0	57.3	58.5	59.7	61.0	61.6	62.0	62.6	63.1	63.4
97.5°	89.3	90.6	92.1	93.6	95.0	96.5	97.1	97.8	98.4	99.0	99.3
100°	115.2	116.4	118.0	119.5	121.2	122.8	123.1	123.5	123.8	124.2	124.4
102.5°	143.0	143.9	145.4	146.8	148.3	149.7	150.3	150.8	151.2	151.8	152.1
105°	187.7	188.1	188.9	189.6	190.3	191.0	191.5	192.1	192.6	193.1	193.7
107.5°	235.2	235.4	235.4	235.6	235.7	235.8	236.3	236.8	237.3	237.8	238.0
110°	267.8	267.9	267.8	267.6	267.4	267.2	266.9	266.5	266.2	265.8	265.9



TEST NUMBER: P333104-927

CATALOG NUMBER: S124RDIW-S1195D1050U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	300.1	300.0	299.7	299.4	299.0	298.7	298.7	298.6	298.5	298.4	298.4
115°	349.9	349.7	349.4	349.0	348.6	348.3	348.1	347.9	347.8	347.6	347.4
117.5°	397.7	397.6	397.4	397.1	396.9	396.6	396.0	395.4	394.7	394.2	393.7
120°	431.4	431.5	430.9	430.4	429.9	429.4	428.5	427.5	426.7	425.8	425.5
122.5°	462.4	462.5	462.2	461.9	461.7	461.4	460.8	460.3	459.6	459.0	458.4
125°	509.6	509.5	509.3	509.1	509.0	508.8	508.4	508.1	507.7	507.4	507.0
127.5°	555.6	555.7	555.4	555.1	554.8	554.5	554.2	553.8	553.5	553.1	552.8
130°	586.4	586.6	586.6	586.6	586.6	586.6	586.3	585.9	585.6	585.2	584.7
132.5°	617.3	617.3	617.3	617.1	617.0	616.8	616.5	616.1	615.8	615.4	615.1
135°	661.6	662.1	662.1	662.1	662.1	662.1	661.7	661.4	661.0	660.7	660.2
137.5°	704.5	704.9	705.2	705.5	705.8	706.1	705.6	705.1	704.6	704.2	704.0
140°	734.1	734.3	734.3	734.3	734.3	734.3	734.1	734.0	733.8	733.6	733.4
142.5°	761.8	761.8	761.7	761.5	761.4	761.3	761.2	761.2	761.1	761.1	761.0
145°	801.4	801.8	802.0	802.2	802.3	802.5	802.3	802.2	802.0	801.8	801.5
147.5°	839.8	840.2	840.0	839.9	839.7	839.6	839.5	839.3	839.2	839.0	838.8
150°	862.4	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.6
152.5°	883.0	883.3	883.4	883.6	883.8	883.9	884.3	884.7	885.2	885.6	885.6
155°	914.9	914.8	914.6	914.4	914.3	914.1	914.8	915.5	916.2	917.0	917.0
157.5°	941.8	941.7	941.6	941.6	941.5	941.5	942.1	942.6	943.1	943.6	943.6
160°	959.1	958.9	958.7	958.5	958.4	958.2	958.7	959.3	959.8	960.4	960.1
162.5°	973.4	973.0	972.9	972.7	972.5	972.3	973.3	974.2	975.2	976.2	976.2
165°	993.8	993.3	993.0	992.6	992.3	991.9	993.0	994.0	995.1	996.2	996.3
167.5°	1008.8	1008.4	1008.5	1008.5	1008.5	1008.6	1009.6	1010.7	1011.8	1012.9	1012.9
170°	1017.2	1016.8	1017.1	1017.2	1017.4	1017.6	1018.7	1019.7	1020.8	1021.8	1021.8
172.5°	1024.2	1023.9	1023.9	1024.0	1024.0	1024.0	1025.2	1026.4	1027.6	1028.9	1028.8
175°	1032.5	1032.0	1031.7	1031.6	1031.4	1031.3	1032.5	1033.7	1035.0	1036.3	1036.3
177.5°	1036.1	1035.7	1035.7	1035.7	1035.7	1035.7	1036.7	1037.8	1038.7	1039.7	1039.7
180°	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7



TEST NUMBER: P333104-927

CATALOG NUMBER: S124RDIW-S1195D1050U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9
2.5°	1498.5	1499.5	1496.0	1494.9	1496.0	1499.5	1498.5	1501.5	1502.1	1506.1	1504.6
5°	1390.2	1388.9	1385.8	1386.4	1385.8	1388.9	1390.2	1395.3	1397.8	1407.9	1406.7
7.5°	1297.6	1292.7	1294.0	1289.0	1294.0	1292.7	1297.6	1302.2	1309.9	1314.5	1325.2
10°	1241.0	1234.0	1228.3	1223.2	1228.3	1234.0	1241.0	1243.5	1254.2	1259.3	1270.0
12.5°	1163.6	1157.5	1149.9	1151.4	1149.9	1157.5	1163.6	1174.6	1188.4	1199.0	1215.9
15°	1053.7	1044.3	1029.0	1030.9	1029.0	1044.3	1053.7	1061.9	1075.9	1099.9	1111.3
17.5°	960.8	960.8	953.9	955.5	953.9	960.8	960.8	972.0	979.1	994.4	1011.9
20°	912.7	908.2	908.9	907.0	908.9	908.2	912.7	926.0	933.6	944.3	963.3
22.5°	879.2	873.9	869.4	865.5	869.4	873.9	879.2	883.0	893.1	903.3	918.8
25°	822.8	819.0	813.4	812.1	813.4	819.0	822.8	828.5	833.6	846.9	856.3
27.5°	773.2	772.5	770.2	767.3	770.2	772.5	773.2	778.3	784.9	793.4	805.4
30°	744.4	743.1	741.9	740.0	741.9	743.1	744.4	749.5	754.6	761.5	771.0
32.5°	718.7	717.9	716.6	716.8	716.6	717.9	718.7	721.1	724.2	733.2	740.6
35°	681.8	681.2	679.9	679.3	679.9	681.2	681.8	684.4	686.3	688.8	695.1
37.5°	647.5	649.0	648.3	648.2	648.3	649.0	647.5	648.1	646.0	650.5	654.9
40°	623.6	624.2	625.5	624.9	625.5	624.2	623.6	624.2	624.2	624.2	628.0
42.5°	603.9	604.0	605.8	603.6	605.8	604.0	603.9	601.5	598.5	599.0	600.2
45°	568.6	572.4	571.8	571.8	571.8	572.4	568.6	564.2	563.6	561.0	561.0
47.5°	530.0	533.3	534.2	534.1	534.2	533.3	530.0	528.4	525.5	522.9	522.7
50°	504.7	503.4	505.3	504.7	505.3	503.4	504.7	501.5	497.1	497.1	495.9
52.5°	473.9	474.1	474.0	473.3	474.0	474.1	473.9	472.2	470.3	468.3	467.5
55°	426.3	426.9	425.6	426.3	425.6	426.9	426.3	425.6	425.6	424.4	425.6
57.5°	374.7	371.6	372.9	371.4	372.9	371.6	374.7	377.5	378.5	378.7	380.6
60°	337.8	332.7	331.4	328.9	331.4	332.7	337.8	344.0	346.6	347.8	349.7
62.5°	296.3	292.7	288.4	290.4	288.4	292.7	296.3	303.1	308.6	313.0	317.3
65°	241.0	238.4	236.5	239.1	236.5	238.4	241.0	246.1	251.1	261.2	270.7
67.5°	199.5	198.1	198.1	196.9	198.1	198.1	199.5	202.0	205.2	210.7	219.6
70°	177.8	175.9	175.9	174.6	175.9	175.9	177.8	177.8	180.9	183.4	189.7
72.5°	155.4	153.6	154.1	153.3	154.1	153.6	155.4	156.0	159.1	160.2	163.0
75°	115.1	111.9	111.9	112.6	111.9	111.9	115.1	118.9	122.1	127.8	129.0
77.5°	85.9	85.2	86.1	85.0	86.1	85.2	85.9	85.9	86.5	89.2	91.3
80°	70.2	69.6	68.9	70.8	68.9	69.6	70.2	70.2	70.8	71.5	72.1
82.5°	54.5	54.4	54.3	56.6	54.3	54.4	54.5	55.5	55.7	55.3	55.9
85°	32.9	31.6	32.9	31.6	32.9	31.6	32.9	32.2	32.9	32.2	32.9
87.5°	16.2	15.8	15.4	15.9	15.4	15.8	16.2	15.1	15.1	15.8	15.1
90°	23.0	23.4	23.7	24.1	23.7	23.4	23.0	22.7	21.9	20.8	19.8
92.5°	35.0	35.2	35.4	35.6	35.4	35.2	35.0	34.8	34.4	33.7	33.0
95°	63.4	63.4	63.4	63.4	63.4	63.4	63.4	63.4	63.1	62.6	62.0
97.5°	99.3	99.3	99.3	99.3	99.3	99.3	99.3	99.3	99.0	98.4	97.8
100°	124.4	124.4	124.4	124.4	124.4	124.4	124.4	124.4	124.2	123.8	123.5
102.5°	152.2	152.3	152.5	152.7	152.5	152.3	152.2	152.1	151.8	151.2	150.8
105°	194.2	194.7	195.3	195.8	195.3	194.7	194.2	193.7	193.1	192.6	192.1
107.5°	238.0	238.0	237.9	237.9	237.9	238.0	238.0	238.0	237.8	237.3	236.8
110°	266.4	267.0	267.5	268.1	267.5	267.0	266.4	265.9	265.8	266.2	266.5



TEST NUMBER: P333104-927

CATALOG NUMBER: S124RDIW-S1195D1050U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	298.6	298.7	298.7	298.9	298.7	298.7	298.6	298.4	298.4	298.5	298.6
115°	347.2	347.1	346.9	346.7	346.9	347.1	347.2	347.4	347.6	347.8	347.9
117.5°	393.3	393.0	392.6	392.3	392.6	393.0	393.3	393.7	394.2	394.7	395.4
120°	425.9	426.2	426.6	426.9	426.6	426.2	425.9	425.5	425.8	426.7	427.5
122.5°	457.7	457.1	456.5	455.8	456.5	457.1	457.7	458.4	459.0	459.6	460.3
125°	506.7	506.3	506.0	505.6	506.0	506.3	506.7	507.0	507.4	507.7	508.1
127.5°	552.5	552.2	551.9	551.7	551.9	552.2	552.5	552.8	553.1	553.5	553.8
130°	584.0	583.3	582.6	581.9	582.6	583.3	584.0	584.7	585.2	585.6	585.9
132.5°	614.8	614.5	614.2	613.9	614.2	614.5	614.8	615.1	615.4	615.8	616.1
135°	659.7	659.1	658.6	658.1	658.6	659.1	659.7	660.2	660.7	661.0	661.4
137.5°	704.1	704.3	704.3	704.4	704.3	704.3	704.1	704.0	704.2	704.6	705.1
140°	733.2	733.1	732.8	732.7	732.8	733.1	733.2	733.4	733.6	733.8	734.0
142.5°	761.0	761.0	761.0	761.0	761.0	761.0	761.0	761.0	761.1	761.1	761.2
145°	800.9	800.3	799.9	799.3	799.9	800.3	800.9	801.5	801.8	802.0	802.2
147.5°	838.7	838.5	838.3	838.1	838.3	838.5	838.7	838.8	839.0	839.2	839.3
150°	862.4	862.3	862.1	861.9	862.1	862.3	862.4	862.6	862.7	862.7	862.7
152.5°	885.1	884.6	884.2	883.8	884.2	884.6	885.1	885.6	885.6	885.2	884.7
155°	916.2	915.5	914.8	914.1	914.8	915.5	916.2	917.0	917.0	916.2	915.5
157.5°	943.0	942.4	941.8	941.2	941.8	942.4	943.0	943.6	943.6	943.1	942.6
160°	959.3	958.4	957.5	956.6	957.5	958.4	959.3	960.1	960.4	959.8	959.3
162.5°	975.3	974.5	973.5	972.6	973.5	974.5	975.3	976.2	976.2	975.2	974.2
165°	995.6	994.9	994.2	993.5	994.2	994.9	995.6	996.3	996.2	995.1	994.0
167.5°	1011.8	1010.7	1009.6	1008.4	1009.6	1010.7	1011.8	1012.9	1012.9	1011.8	1010.7
170°	1020.6	1019.3	1018.0	1016.8	1018.0	1019.3	1020.6	1021.8	1021.8	1020.8	1019.7
172.5°	1027.6	1026.4	1025.1	1023.8	1025.1	1026.4	1027.6	1028.8	1028.9	1027.6	1026.4
175°	1035.0	1033.7	1032.5	1031.3	1032.5	1033.7	1035.0	1036.3	1036.3	1035.0	1033.7
177.5°	1038.5	1037.4	1036.3	1035.1	1036.3	1037.4	1038.5	1039.7	1039.7	1038.7	1037.8
180°	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7



TEST NUMBER: P333104-927

CATALOG NUMBER: S124RDIW-S1195D1050U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9
2.5°	1501.5	1505.1	1513.1	1522.3	1529.9	1536.4	1541.5	1548.6	1555.1	1564.2	1572.9
5°	1410.5	1419.3	1431.9	1447.2	1466.1	1478.8	1494.5	1508.5	1528.8	1549.0	1568.6
7.5°	1330.5	1340.2	1358.8	1379.8	1402.3	1423.1	1441.9	1466.3	1493.2	1522.7	1555.5
10°	1278.9	1289.7	1311.8	1335.8	1362.4	1382.6	1407.9	1437.0	1467.4	1503.4	1543.9
12.5°	1232.3	1242.6	1269.2	1293.8	1321.4	1343.6	1373.0	1402.6	1443.1	1482.2	1528.2
15°	1141.6	1168.9	1199.2	1228.3	1261.2	1288.4	1323.8	1354.2	1392.7	1447.8	1500.2
17.5°	1040.9	1069.9	1107.6	1152.5	1196.7	1230.3	1266.2	1303.9	1349.9	1406.0	1466.6
20°	982.2	1005.7	1047.4	1097.3	1148.6	1195.4	1228.3	1270.0	1317.5	1378.2	1440.8
22.5°	938.3	958.1	990.7	1040.7	1096.0	1150.3	1192.4	1233.6	1286.1	1346.8	1415.0
25°	872.2	893.7	922.2	956.3	1019.5	1077.1	1132.2	1179.6	1235.2	1295.9	1371.8
27.5°	817.3	836.0	862.1	897.6	940.2	1003.6	1070.3	1124.4	1181.5	1246.7	1322.6
30°	784.9	800.1	821.6	857.6	898.1	955.1	1022.7	1086.0	1143.5	1211.2	1290.3
32.5°	751.0	767.2	788.2	816.7	860.2	908.0	975.7	1045.0	1106.1	1175.3	1252.8
35°	705.8	718.5	737.4	766.6	805.8	847.6	907.6	979.1	1043.6	1117.6	1191.6
37.5°	660.2	675.1	690.1	716.0	748.1	793.0	842.2	915.2	986.7	1054.2	1126.5
40°	634.4	643.3	659.7	680.6	714.7	754.6	800.7	872.2	943.6	1010.7	1083.5
42.5°	605.5	615.4	629.3	650.2	680.8	719.6	764.8	826.6	901.2	966.2	1032.4
45°	565.5	571.2	585.0	602.8	628.0	667.3	709.0	764.1	834.2	896.2	954.4
47.5°	525.0	529.9	538.6	554.8	583.1	614.7	653.7	703.1	764.7	826.6	875.8
50°	497.1	501.5	509.8	525.0	550.2	581.2	619.8	664.1	719.1	778.6	819.7
52.5°	469.3	471.7	479.4	496.6	517.8	548.3	582.9	623.6	675.1	724.5	766.0
55°	425.0	430.7	435.8	448.5	468.7	497.7	528.8	567.4	607.2	649.0	684.4
57.5°	378.8	385.1	392.4	403.5	419.6	446.6	474.5	505.7	539.8	574.4	604.1
60°	348.5	354.2	360.5	373.2	387.7	409.2	439.6	466.8	492.7	524.3	554.1
62.5°	318.6	324.3	331.7	341.8	355.8	376.4	401.6	425.3	452.3	479.8	501.9
65°	274.5	278.9	284.6	294.1	307.4	325.7	346.6	365.0	389.0	409.2	429.4
67.5°	226.1	234.6	242.0	249.7	260.9	278.1	293.1	310.7	327.0	342.1	360.5
70°	194.2	203.7	210.6	218.8	229.6	244.2	258.6	270.7	284.0	298.5	315.0
72.5°	167.4	174.8	180.2	189.0	198.8	212.2	225.8	235.8	246.5	256.5	272.5
75°	132.2	135.4	139.2	146.1	155.0	165.1	175.9	184.7	191.0	199.9	211.3
77.5°	95.0	101.1	103.6	108.5	114.9	121.2	128.3	135.7	141.8	145.0	153.7
80°	72.7	75.3	77.8	84.8	88.6	94.9	99.9	106.9	109.4	112.6	120.8
82.5°	56.6	58.1	59.6	61.5	63.8	70.1	75.2	79.5	82.1	83.3	89.4
85°	32.9	33.5	34.1	34.8	35.4	35.4	37.9	41.1	45.6	45.6	47.5
87.5°	14.9	15.1	14.9	14.1	14.8	14.5	14.7	14.3	15.4	16.6	17.7
90°	18.7	17.7	16.2	14.8	13.4	12.0	10.2	8.3	6.3	4.4	2.4
92.5°	32.4	31.8	30.8	29.8	28.8	27.8	26.1	23.9	21.7	19.4	17.2
95°	61.6	61.0	59.7	58.5	57.3	56.0	54.6	53.0	51.3	49.7	48.2
97.5°	97.1	96.5	95.0	93.6	92.1	90.6	89.3	87.9	86.7	85.4	84.1
100°	123.1	122.8	121.2	119.5	118.0	116.4	115.2	114.5	113.8	113.0	112.3
102.5°	150.3	149.7	148.3	146.8	145.4	143.9	143.0	142.8	142.4	142.2	141.9
105°	191.5	191.0	190.3	189.6	188.9	188.1	187.7	187.5	187.4	187.2	187.0
107.5°	236.3	235.8	235.7	235.6	235.4	235.4	235.2	235.0	234.7	234.6	234.3
110°	266.9	267.2	267.4	267.6	267.8	267.9	267.8	267.5	267.1	266.8	266.4



TEST NUMBER: P333104-927

CATALOG NUMBER: S124RDIW-S1195D1050U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	298.7	298.7	299.0	299.4	299.7	300.0	300.1	300.0	300.0	299.9	299.8
115°	348.1	348.3	348.6	349.0	349.4	349.7	349.9	349.9	349.9	349.9	349.9
117.5°	396.0	396.6	396.9	397.1	397.4	397.6	397.7	397.5	397.4	397.2	397.1
120°	428.5	429.4	429.9	430.4	430.9	431.5	431.4	430.7	430.0	429.3	428.6
122.5°	460.8	461.4	461.7	461.9	462.2	462.5	462.4	462.2	461.8	461.6	461.3
125°	508.4	508.8	509.0	509.1	509.3	509.5	509.6	509.6	509.6	509.6	509.6
127.5°	554.2	554.5	554.8	555.1	555.4	555.7	555.6	555.0	554.4	554.0	553.4
130°	586.3	586.6	586.6	586.6	586.6	586.6	586.4	585.8	585.3	584.8	584.2
132.5°	616.5	616.8	617.0	617.1	617.3	617.3	617.3	616.9	616.5	616.1	615.7
135°	661.7	662.1	662.1	662.1	662.1	662.1	661.6	660.4	659.4	658.3	657.3
137.5°	705.6	706.1	705.8	705.5	705.2	704.9	704.5	704.0	703.5	703.0	702.5
140°	734.1	734.3	734.3	734.3	734.3	734.3	734.1	733.8	733.4	733.1	732.7
142.5°	761.2	761.3	761.4	761.5	761.7	761.8	761.8	761.4	761.0	760.7	760.3
145°	802.3	802.5	802.3	802.2	802.0	801.8	801.4	800.7	799.9	799.2	798.5
147.5°	839.5	839.6	839.7	839.9	840.0	840.2	839.8	838.9	838.1	837.3	836.4
150°	862.7	862.7	862.7	862.7	862.7	862.7	862.4	861.7	860.9	860.2	859.5
152.5°	884.3	883.9	883.8	883.6	883.4	883.3	883.0	882.6	882.2	881.8	881.3
155°	914.8	914.1	914.3	914.4	914.6	914.8	914.9	914.9	914.9	914.9	914.9
157.5°	942.1	941.5	941.5	941.6	941.6	941.7	941.8	942.1	942.5	942.8	943.1
160°	958.7	958.2	958.4	958.5	958.7	958.9	959.1	959.3	959.4	959.6	959.8
162.5°	973.3	972.3	972.5	972.7	972.9	973.0	973.4	973.8	974.3	974.8	975.2
165°	993.0	991.9	992.3	992.6	993.0	993.3	993.8	994.3	994.8	995.4	995.9
167.5°	1009.6	1008.6	1008.5	1008.5	1008.5	1008.4	1008.8	1009.6	1010.3	1011.1	1011.8
170°	1018.7	1017.6	1017.4	1017.2	1017.1	1016.8	1017.2	1018.1	1019.0	1019.9	1020.8
172.5°	1025.2	1024.0	1024.0	1024.0	1023.9	1023.9	1024.2	1025.0	1025.7	1026.4	1027.2
175°	1032.5	1031.3	1031.4	1031.6	1031.7	1032.0	1032.5	1033.4	1034.3	1035.1	1036.0
177.5°	1036.7	1035.7	1035.7	1035.7	1035.7	1035.7	1036.1	1036.8	1037.5	1038.2	1038.9
180°	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7



TEST NUMBER: P333104-927

CATALOG NUMBER: S124RDIW-S1195D1050U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9
2.5°	1579.5	1584.0	1589.0	1598.7	1606.8	1610.3	1617.4	1622.5	1621.0	1628.0	1640.1
5°	1585.6	1602.7	1622.3	1642.6	1665.3	1684.3	1699.5	1714.7	1726.7	1741.2	1762.8
7.5°	1584.6	1615.0	1648.0	1684.3	1721.6	1753.9	1783.8	1814.1	1841.0	1870.5	1909.1
10°	1580.6	1621.0	1662.2	1709.6	1757.1	1802.0	1842.5	1880.4	1916.4	1955.0	2003.7
12.5°	1576.0	1622.5	1672.3	1729.3	1788.4	1842.5	1890.0	1944.6	1989.8	2039.6	2095.8
15°	1555.9	1618.5	1686.2	1760.2	1831.1	1903.8	1968.9	2036.0	2098.6	2158.1	2228.9
17.5°	1532.9	1605.1	1685.0	1772.3	1857.5	1945.9	2023.2	2107.7	2171.7	2251.5	2317.3
20°	1514.2	1592.0	1677.4	1775.4	1872.2	1970.2	2055.6	2141.6	2213.7	2294.0	2377.5
22.5°	1491.4	1576.8	1669.3	1770.8	1872.2	1979.3	2073.8	2159.3	2248.6	2339.1	2425.1
25°	1454.7	1543.3	1641.3	1752.6	1869.0	1978.4	2079.6	2185.9	2282.0	2380.0	2457.2
27.5°	1409.7	1502.7	1606.0	1720.9	1840.3	1952.3	2071.6	2184.8	2281.5	2375.8	2443.2
30°	1373.7	1471.8	1571.1	1687.5	1811.4	1931.6	2059.4	2172.6	2274.4	2359.2	2397.1
32.5°	1336.8	1429.8	1532.2	1650.0	1777.0	1906.3	2033.1	2148.8	2243.1	2293.9	2294.9
35°	1272.6	1359.9	1466.1	1581.8	1712.1	1852.5	1980.9	2094.8	2152.4	2156.8	2094.8
37.5°	1202.5	1282.5	1382.8	1498.7	1641.4	1781.1	1912.2	1988.1	2007.4	1943.0	1828.4
40°	1152.4	1226.4	1323.2	1442.1	1583.7	1728.0	1847.5	1903.1	1882.9	1778.5	1650.7
42.5°	1099.8	1168.7	1261.9	1379.3	1521.5	1667.2	1769.1	1798.9	1745.3	1624.8	1475.2
45°	1013.9	1077.1	1169.5	1287.8	1424.3	1561.0	1638.2	1622.9	1533.7	1390.8	1223.2
47.5°	924.5	985.6	1068.7	1178.1	1318.0	1435.8	1488.1	1442.3	1315.4	1158.2	1021.8
50°	865.2	927.9	1004.4	1108.7	1236.5	1350.4	1383.9	1314.3	1173.2	1022.1	896.8
52.5°	807.1	860.5	935.6	1036.4	1158.6	1254.7	1272.6	1192.4	1046.8	911.2	800.2
55°	718.5	767.2	830.4	925.3	1030.9	1112.5	1103.0	1000.0	867.8	752.0	664.7
57.5°	632.9	669.6	728.0	816.9	909.7	964.4	929.8	841.9	718.7	623.9	550.2
60°	576.2	610.4	664.7	742.5	824.1	855.1	826.0	730.6	633.1	546.4	484.5
62.5°	522.5	552.7	599.4	671.7	737.6	756.0	724.8	641.4	553.7	479.7	428.3
65°	444.7	472.5	512.3	563.6	609.1	617.9	597.7	512.3	445.9	383.9	348.5
67.5°	373.9	392.1	423.3	467.5	491.7	496.9	457.8	404.2	345.6	307.5	280.8
70°	326.4	339.0	368.1	392.1	411.8	412.4	376.4	333.4	288.4	257.5	237.8
72.5°	280.4	292.5	314.5	330.9	345.9	341.0	308.0	274.1	237.8	214.4	199.9
75°	216.3	227.0	238.4	246.1	246.1	239.7	215.7	190.4	169.5	155.6	151.1
77.5°	157.2	166.1	169.9	168.7	166.4	156.6	141.4	124.8	117.4	110.8	107.5
80°	123.3	127.1	128.4	125.2	121.4	110.0	99.9	93.0	86.0	83.5	82.2
82.5°	91.4	94.7	91.4	92.4	84.0	74.6	69.1	66.7	63.8	62.7	61.5
85°	48.7	48.1	46.8	43.6	37.9	36.7	36.0	35.4	34.1	34.8	33.5
87.5°	17.6	16.5	14.8	14.7	15.1	14.3	15.1	15.4	15.7	15.4	16.6
90°	4.4	6.3	8.3	10.2	12.0	13.4	14.8	16.2	17.7	18.7	19.8
92.5°	19.4	21.7	23.9	26.1	27.8	28.8	29.8	30.8	31.8	32.4	33.0
95°	49.7	51.3	53.0	54.6	56.0	57.3	58.5	59.7	61.0	61.6	62.0
97.5°	85.4	86.7	87.9	89.3	90.6	92.1	93.6	95.0	96.5	97.1	97.8
100°	113.0	113.8	114.5	115.2	116.4	118.0	119.5	121.2	122.8	123.1	123.5
102.5°	142.2	142.4	142.8	143.0	143.9	145.4	146.8	148.3	149.7	150.3	150.8
105°	187.2	187.4	187.5	187.7	188.1	188.9	189.6	190.3	191.0	191.5	192.1
107.5°	234.6	234.7	235.0	235.2	235.4	235.4	235.6	235.7	235.8	236.3	236.8
110°	266.8	267.1	267.5	267.8	267.9	267.8	267.6	267.4	267.2	266.9	266.5



TEST NUMBER: P333104-927

CATALOG NUMBER: S124RDIW-S1195D1050U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	299.9	300.0	300.0	300.1	300.0	299.7	299.4	299.0	298.7	298.7	298.6
115°	349.9	349.9	349.9	349.9	349.7	349.4	349.0	348.6	348.3	348.1	347.9
117.5°	397.2	397.4	397.5	397.7	397.6	397.4	397.1	396.9	396.6	396.0	395.4
120°	429.3	430.0	430.7	431.4	431.5	430.9	430.4	429.9	429.4	428.5	427.5
122.5°	461.6	461.8	462.2	462.4	462.5	462.2	461.9	461.7	461.4	460.8	460.3
125°	509.6	509.6	509.6	509.6	509.5	509.3	509.1	509.0	508.8	508.4	508.1
127.5°	554.0	554.4	555.0	555.6	555.7	555.4	555.1	554.8	554.5	554.2	553.8
130°	584.8	585.3	585.8	586.4	586.6	586.6	586.6	586.6	586.6	586.3	585.9
132.5°	616.1	616.5	616.9	617.3	617.3	617.3	617.1	617.0	616.8	616.5	616.1
135°	658.3	659.4	660.4	661.6	662.1	662.1	662.1	662.1	662.1	661.7	661.4
137.5°	703.0	703.5	704.0	704.5	704.9	705.2	705.5	705.8	706.1	705.6	705.1
140°	733.1	733.4	733.8	734.1	734.3	734.3	734.3	734.3	734.3	734.1	734.0
142.5°	760.7	761.0	761.4	761.8	761.8	761.7	761.5	761.4	761.3	761.2	761.2
145°	799.2	799.9	800.7	801.4	801.8	802.0	802.2	802.3	802.5	802.3	802.2
147.5°	837.3	838.1	838.9	839.8	840.2	840.0	839.9	839.7	839.6	839.5	839.3
150°	860.2	860.9	861.7	862.4	862.7	862.7	862.7	862.7	862.7	862.7	862.7
152.5°	881.8	882.2	882.6	883.0	883.3	883.4	883.6	883.8	883.9	884.3	884.7
155°	914.9	914.9	914.9	914.9	914.8	914.6	914.4	914.3	914.1	914.8	915.5
157.5°	942.8	942.5	942.1	941.8	941.7	941.6	941.6	941.5	941.5	942.1	942.6
160°	959.6	959.4	959.3	959.1	958.9	958.7	958.5	958.4	958.2	958.7	959.3
162.5°	974.8	974.3	973.8	973.4	973.0	972.9	972.7	972.5	972.3	973.3	974.2
165°	995.4	994.8	994.3	993.8	993.3	993.0	992.6	992.3	991.9	993.0	994.0
167.5°	1011.1	1010.3	1009.6	1008.8	1008.4	1008.5	1008.5	1008.5	1008.6	1009.6	1010.7
170°	1019.9	1019.0	1018.1	1017.2	1016.8	1017.1	1017.2	1017.4	1017.6	1018.7	1019.7
172.5°	1026.4	1025.7	1025.0	1024.2	1023.9	1023.9	1024.0	1024.0	1024.0	1025.2	1026.4
175°	1035.1	1034.3	1033.4	1032.5	1032.0	1031.7	1031.6	1031.4	1031.3	1032.5	1033.7
177.5°	1038.2	1037.5	1036.8	1036.1	1035.7	1035.7	1035.7	1035.7	1035.7	1036.7	1037.8
180°	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7



TEST NUMBER: P333104-927

CATALOG NUMBER: S124RDIW-S1195D1050U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9
2.5°	1646.7	1648.8	1650.3	1655.3	1655.8	1660.4	1655.8
5°	1783.0	1791.8	1805.8	1819.6	1820.9	1829.8	1813.9
7.5°	1935.8	1956.3	1969.0	1991.5	2000.4	2006.0	1996.9
10°	2041.1	2060.0	2093.5	2110.0	2126.5	2128.9	2121.4
12.5°	2142.8	2172.9	2199.3	2230.4	2229.7	2251.9	2243.8
15°	2278.2	2309.2	2345.9	2380.7	2393.3	2393.3	2403.5
17.5°	2374.9	2431.7	2469.6	2497.0	2526.7	2532.0	2528.4
20°	2440.2	2501.5	2542.0	2577.4	2597.6	2603.3	2603.3
22.5°	2488.7	2540.9	2580.5	2612.3	2629.0	2635.7	2633.7
25°	2522.4	2567.2	2591.3	2600.8	2605.2	2604.0	2591.9
27.5°	2476.3	2474.3	2459.1	2430.0	2408.2	2394.8	2379.6
30°	2388.3	2355.4	2317.5	2275.7	2221.9	2180.8	2168.1
32.5°	2257.2	2183.3	2119.1	2049.5	1991.7	1950.6	1933.4
35°	2003.7	1886.7	1791.2	1707.7	1647.0	1609.1	1596.4
37.5°	1702.9	1589.7	1471.4	1390.4	1340.1	1301.8	1287.5
40°	1511.6	1388.3	1285.2	1209.3	1157.5	1120.1	1119.5
42.5°	1337.0	1219.3	1122.3	1067.6	1011.7	987.1	986.9
45°	1094.8	1000.6	918.4	875.4	841.9	821.6	815.9
47.5°	906.5	828.5	773.8	739.5	712.2	699.3	690.9
50°	800.7	732.5	688.8	659.0	643.9	627.4	626.1
52.5°	712.6	657.5	623.5	599.4	580.1	570.2	570.5
55°	599.0	555.3	531.3	512.9	497.7	490.2	487.0
57.5°	504.6	471.8	454.4	437.5	431.1	425.2	423.5
60°	445.9	423.7	407.3	394.0	384.5	382.6	382.0
62.5°	397.4	374.1	362.8	352.5	345.6	342.7	341.5
65°	327.6	310.5	300.4	292.2	289.7	285.3	284.6
67.5°	264.1	253.9	247.2	241.5	238.1	237.8	237.8
70°	225.1	219.4	213.8	210.6	208.7	207.5	207.5
72.5°	191.8	187.6	182.9	181.3	180.9	179.6	179.1
75°	146.1	141.6	142.3	139.2	136.7	133.5	131.6
77.5°	103.6	100.4	99.8	99.4	97.3	96.9	97.9
80°	80.3	77.2	76.5	77.2	76.5	74.6	74.6
82.5°	61.1	58.5	57.8	57.4	56.8	57.4	56.4
85°	32.9	31.6	31.6	31.6	32.9	32.2	31.6
87.5°	15.8	15.5	16.2	15.8	15.8	15.4	15.9
90°	20.8	21.9	22.7	23.0	23.4	23.7	24.1
92.5°	33.7	34.4	34.8	35.0	35.2	35.4	35.6
95°	62.6	63.1	63.4	63.4	63.4	63.4	63.4
97.5°	98.4	99.0	99.3	99.3	99.3	99.3	99.3
100°	123.8	124.2	124.4	124.4	124.4	124.4	124.4
102.5°	151.2	151.8	152.1	152.2	152.3	152.5	152.7
105°	192.6	193.1	193.7	194.2	194.7	195.3	195.8
107.5°	237.3	237.8	238.0	238.0	238.0	237.9	237.9
110°	266.2	265.8	265.9	266.4	267.0	267.5	268.1



TEST NUMBER: P333104-927

CATALOG NUMBER: S124RDIW-S1195D1050U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	298.5	298.4	298.4	298.6	298.7	298.7	298.9
115°	347.8	347.6	347.4	347.2	347.1	346.9	346.7
117.5°	394.7	394.2	393.7	393.3	393.0	392.6	392.3
120°	426.7	425.8	425.5	425.9	426.2	426.6	426.9
122.5°	459.6	459.0	458.4	457.7	457.1	456.5	455.8
125°	507.7	507.4	507.0	506.7	506.3	506.0	505.6
127.5°	553.5	553.1	552.8	552.5	552.2	551.9	551.7
130°	585.6	585.2	584.7	584.0	583.3	582.6	581.9
132.5°	615.8	615.4	615.1	614.8	614.5	614.2	613.9
135°	661.0	660.7	660.2	659.7	659.1	658.6	658.1
137.5°	704.6	704.2	704.0	704.1	704.3	704.3	704.4
140°	733.8	733.6	733.4	733.2	733.1	732.8	732.7
142.5°	761.1	761.1	761.0	761.0	761.0	761.0	761.0
145°	802.0	801.8	801.5	800.9	800.3	799.9	799.3
147.5°	839.2	839.0	838.8	838.7	838.5	838.3	838.1
150°	862.7	862.7	862.6	862.4	862.3	862.1	861.9
152.5°	885.2	885.6	885.6	885.1	884.6	884.2	883.8
155°	916.2	917.0	917.0	916.2	915.5	914.8	914.1
157.5°	943.1	943.6	943.6	943.0	942.4	941.8	941.2
160°	959.8	960.4	960.1	959.3	958.4	957.5	956.6
162.5°	975.2	976.2	976.2	975.3	974.5	973.5	972.6
165°	995.1	996.2	996.3	995.6	994.9	994.2	993.5
167.5°	1011.8	1012.9	1012.9	1011.8	1010.7	1009.6	1008.4
170°	1020.8	1021.8	1021.8	1020.6	1019.3	1018.0	1016.8
172.5°	1027.6	1028.9	1028.8	1027.6	1026.4	1025.1	1023.8
175°	1035.0	1036.3	1036.3	1035.0	1033.7	1032.5	1031.3
177.5°	1038.7	1039.7	1039.7	1038.5	1037.4	1036.3	1035.1
180°	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7

(END OF REPORT)