

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332473-840

Luminaire Tested: **S123RDIW-S1165D460U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332473-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIW-S1165D460U840-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 460 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6037.5 lumens  
Efficiency: N/A  
Efficacy: 115.2 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 52.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332473-840

CATALOG NUMBER: S123RDIW-S1165D460U840-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332473-840

CATALOG NUMBER: S123RDIW-S1165D460U840-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77	73
1	103	99	95	92	98	94	91	88	85	83	80	77	75	73	69	68	66	63
2	95	87	81	76	90	83	78	73	75	71	67	68	65	62	62	59	57	53
3	87	77	70	64	82	74	67	62	67	62	57	61	56	53	55	52	49	46
4	80	69	61	55	75	66	58	53	60	54	49	54	50	46	49	46	42	40
5	73	62	53	47	69	59	51	46	54	48	43	49	44	40	45	41	37	35
6	68	55	47	41	64	53	46	40	49	42	38	45	39	35	41	36	33	31
7	63	50	42	37	60	48	41	36	44	38	34	41	35	32	37	33	30	27
8	59	46	38	33	56	44	37	32	41	34	30	37	32	28	34	30	27	25
9	55	42	35	29	52	41	33	29	38	31	27	35	29	26	32	27	24	22
10	51	39	32	27	49	37	31	26	35	29	25	32	27	23	30	25	22	20

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	21068	21068	21068
5°	21149	20857	20977
10°	21029	20595	20525
15°	20803	20113	19900
20°	20492	19511	19057
25°	20173	18834	18231
30°	19750	18053	17066
35°	19316	17270	16000
40°	18916	16350	14677
45°	18389	15440	13484
50°	17811	14408	12149
55°	17220	13226	10903
60°	16678	11961	9535
65°	15969	10593	8166
70°	15087	8894	6593
75°	13795	6995	6209
80°	12298	6199	5709
85°	10387	5483	5101



TEST NUMBER: P332473-840

CATALOG NUMBER: S123RDIW-S1165D460U840-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	183.8	3.0
10°-20°	511.4	8.5
20°-30°	736.4	12.2
30°-40°	829.4	13.7
40°-50°	793.5	13.1
50°-60°	649.8	10.8
60°-70°	438.4	7.3
70°-80°	220.6	3.7
80°-90°	60.1	1.0
90°-100°	37.9	0.6
100°-110°	113.6	1.9
110°-120°	193.2	3.2
120°-130°	254.1	4.2
130°-140°	285.6	4.7
140°-150°	280.8	4.7
150°-160°	236.4	3.9
160°-170°	157.3	2.6
170°-180°	55.1	0.9
0°-30°	1431.6	23.7
0°-40°	2261.0	37.4
0°-60°	3704.3	61.4
0°-90°	4423.4	73.3
90°-120°	344.8	5.7
90°-150°	1165.3	19.3
90°-180°	1614.0	26.7
0°-180°	6037.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1957	1957	1957	1957	1957	
5°	1957	1949	1930	1944	1941	186
15°	1867	1848	1805	1797	1786	526
25°	1698	1657	1586	1553	1535	781
35°	1470	1411	1314	1248	1218	920
45°	1208	1134	1014	927	886	932
55°	918	837	705	616	581	822
65°	627	538	416	342	321	620
75°	332	255	168	153	149	354
85°	84	51	44	41	41	94
90°	0	5	11	13	14	6
95°	27	30	34	36	36	30
105°	103	104	108	108	109	110
115°	194	196	195	195	195	192
125°	285	286	285	283	281	254
135°	369	372	372	370	369	284
145°	448	449	450	450	448	280
155°	513	513	514	515	512	236
165°	559	557	557	560	557	157
175°	581	580	579	582	579	55
180°	583	583	583	583	583	



TEST NUMBER: P332473-840

CATALOG NUMBER: S123RDIW-S1165D460U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3
2.5°	1963.7	1962.5	1961.4	1960.2	1959.1	1956.8	1953.5	1950.0	1946.7	1943.3	1946.4
5°	1957.3	1955.5	1953.8	1952.0	1950.3	1947.2	1943.0	1938.7	1934.5	1930.3	1933.5
7.5°	1939.1	1937.3	1935.4	1933.5	1931.6	1927.8	1922.4	1916.8	1911.4	1905.8	1907.6
10°	1924.0	1921.5	1919.0	1916.5	1914.1	1909.7	1903.3	1896.9	1890.6	1884.3	1884.6
12.5°	1902.4	1899.7	1896.8	1894.1	1891.4	1886.1	1878.3	1870.6	1862.8	1855.0	1854.8
15°	1866.8	1862.9	1859.1	1855.1	1851.3	1844.4	1834.5	1824.6	1814.7	1804.9	1803.1
17.5°	1822.0	1817.6	1813.0	1808.5	1804.0	1795.4	1782.9	1770.3	1757.8	1745.2	1741.5
20°	1789.0	1783.4	1777.8	1772.1	1766.5	1757.0	1743.5	1730.1	1716.7	1703.3	1698.7
22.5°	1752.2	1745.7	1739.2	1732.7	1726.3	1715.9	1701.6	1687.4	1673.1	1658.8	1653.1
25°	1698.5	1689.7	1680.9	1672.0	1663.2	1650.7	1634.5	1618.3	1602.0	1585.8	1578.4
27.5°	1633.5	1623.8	1614.0	1604.3	1594.5	1580.6	1562.6	1544.5	1526.4	1508.3	1498.0
30°	1589.0	1578.4	1567.8	1557.2	1546.7	1531.5	1511.8	1492.0	1472.3	1452.5	1440.5
32.5°	1544.6	1532.6	1520.6	1508.5	1496.6	1480.2	1459.3	1438.4	1417.4	1396.6	1383.5
35°	1470.0	1457.2	1444.5	1431.9	1419.2	1401.9	1380.0	1358.2	1336.3	1314.3	1299.2
37.5°	1394.4	1380.3	1366.1	1352.0	1338.0	1319.2	1295.9	1272.5	1249.2	1225.8	1208.6
40°	1346.2	1330.6	1315.0	1299.6	1284.0	1263.7	1238.7	1213.7	1188.6	1163.6	1145.2
42.5°	1291.5	1276.0	1260.5	1245.0	1229.4	1208.7	1182.9	1156.9	1131.0	1105.2	1085.1
45°	1208.0	1192.1	1176.3	1160.4	1144.5	1123.0	1095.8	1068.6	1041.5	1014.3	994.2
47.5°	1124.5	1107.1	1089.6	1072.3	1054.8	1032.5	1005.3	978.2	951.0	923.9	902.0
50°	1063.6	1047.0	1030.4	1013.8	997.2	974.7	946.1	917.6	889.0	860.4	838.5
52.5°	1009.0	991.0	973.0	955.0	937.0	913.8	885.6	857.3	829.0	800.7	778.0
55°	917.6	900.2	882.9	865.7	848.4	824.8	794.8	764.8	734.8	704.8	684.4
57.5°	833.0	814.3	795.4	776.6	757.7	733.3	703.2	673.0	642.9	612.8	593.4
60°	774.7	755.3	735.9	716.5	697.0	672.7	643.4	614.2	584.9	555.6	536.5
62.5°	716.2	696.8	677.4	658.0	638.6	614.3	585.0	555.7	526.4	497.2	479.3
65°	627.0	607.6	588.2	568.9	549.5	525.9	498.5	470.9	443.4	415.9	398.6
67.5°	537.9	518.2	498.6	479.0	459.4	436.4	410.0	383.5	357.2	330.8	317.9
70°	479.4	460.4	441.3	422.2	403.2	381.3	356.7	331.9	307.3	282.6	270.2
72.5°	421.0	402.2	383.4	364.7	345.9	325.3	302.9	280.4	258.0	235.6	225.5
75°	331.7	314.9	297.9	280.9	264.1	245.9	226.5	207.0	187.6	168.2	164.7
77.5°	250.4	235.2	219.8	204.6	189.2	175.3	162.9	150.4	137.8	125.4	123.5
80°	198.4	184.0	169.5	155.0	140.6	129.7	122.2	114.8	107.4	100.0	99.0
82.5°	148.9	136.4	123.9	111.4	99.0	91.0	87.6	84.0	80.6	77.2	76.0
85°	84.1	76.3	68.6	60.9	53.1	48.7	47.7	46.6	45.5	44.4	43.7
87.5°	30.6	27.7	24.7	21.9	19.0	17.7	17.9	18.2	18.5	18.7	18.5
90°	0.5	1.5	2.5	3.5	4.5	5.7	7.0	8.4	9.7	11.0	11.4
92.5°	11.1	11.8	12.4	13.1	13.8	14.5	15.3	16.1	16.9	17.6	17.9
95°	27.0	27.7	28.4	29.2	29.9	30.6	31.4	32.2	33.0	33.8	34.2
97.5°	48.0	48.5	49.0	49.6	50.1	50.6	51.2	51.8	52.4	53.0	53.4
100°	62.2	62.8	63.4	64.0	64.6	65.2	65.7	66.2	66.8	67.3	67.6
102.5°	78.7	79.1	79.5	79.8	80.2	80.7	81.4	82.0	82.7	83.4	83.7
105°	103.0	103.2	103.4	103.6	103.8	104.3	105.2	106.1	107.0	108.0	108.0
107.5°	131.2	131.3	131.4	131.5	131.7	131.9	132.3	132.6	133.0	133.4	133.7
110°	148.8	149.0	149.2	149.4	149.6	149.8	150.0	150.2	150.4	150.6	151.0



TEST NUMBER: P332473-840

CATALOG NUMBER: S123RDIW-S1165D460U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	167.0	167.1	167.3	167.4	167.5	167.6	167.6	167.7	167.7	167.7	168.2
115°	194.5	194.8	195.1	195.4	195.7	195.8	195.6	195.4	195.2	195.0	195.1
117.5°	222.2	222.4	222.6	222.8	223.0	222.9	222.7	222.4	222.2	221.9	221.9
120°	239.3	239.9	240.5	241.2	241.8	241.9	241.4	240.9	240.3	239.8	239.7
122.5°	257.3	257.7	258.2	258.6	259.0	259.1	258.9	258.6	258.4	258.1	257.8
125°	284.7	285.0	285.3	285.6	285.9	285.9	285.7	285.5	285.3	285.1	284.7
127.5°	309.9	310.5	311.2	311.8	312.6	312.8	312.6	312.3	312.0	311.8	311.2
130°	326.8	327.6	328.4	329.2	330.0	330.2	329.9	329.6	329.3	329.0	328.6
132.5°	343.6	344.4	345.3	346.1	346.9	347.2	346.9	346.7	346.5	346.3	345.8
135°	369.3	369.9	370.5	371.1	371.7	372.0	371.9	371.8	371.7	371.6	371.2
137.5°	393.1	393.6	394.2	394.7	395.2	395.6	395.8	396.1	396.4	396.6	396.2
140°	409.6	410.1	410.6	411.1	411.6	411.9	412.0	412.1	412.2	412.3	412.2
142.5°	424.6	425.2	425.7	426.2	426.7	427.0	427.2	427.4	427.6	427.7	427.6
145°	448.1	448.3	448.5	448.7	448.9	449.1	449.4	449.7	450.0	450.3	450.2
147.5°	468.6	468.9	469.3	469.6	470.0	470.3	470.6	470.9	471.2	471.5	471.5
150°	482.8	483.0	483.2	483.4	483.6	483.8	484.0	484.2	484.4	484.6	484.6
152.5°	494.5	494.8	495.1	495.3	495.6	495.8	495.9	496.1	496.2	496.3	496.6
155°	513.0	513.0	513.0	513.0	513.0	513.1	513.2	513.3	513.4	513.5	513.9
157.5°	528.8	528.7	528.6	528.4	528.3	528.3	528.4	528.5	528.5	528.6	529.0
160°	538.7	538.5	538.3	538.1	537.9	537.8	537.8	537.8	537.8	537.8	538.3
162.5°	547.4	547.1	546.8	546.5	546.3	546.2	546.2	546.3	546.4	546.5	547.0
165°	558.8	558.5	558.2	557.8	557.5	557.4	557.4	557.4	557.4	557.4	558.1
167.5°	567.8	567.4	567.0	566.6	566.2	566.0	566.1	566.2	566.3	566.3	567.0
170°	573.0	572.6	572.2	571.8	571.4	571.2	571.2	571.2	571.2	571.2	571.9
172.5°	577.0	576.6	576.2	575.8	575.3	575.1	575.1	575.1	575.1	575.1	575.8
175°	581.2	580.8	580.4	580.0	579.6	579.4	579.4	579.4	579.4	579.4	580.0
177.5°	583.0	582.6	582.3	582.0	581.7	581.5	581.5	581.5	581.5	581.5	582.0
180°	582.6	582.6	582.6	582.6	582.6	582.6	582.6	582.6	582.6	582.6	582.6



TEST NUMBER: P332473-840

CATALOG NUMBER: S123RDIW-S1165D460U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3	1957.3
2.5°	1949.5	1952.7	1955.7	1957.0	1956.4	1955.9	1955.3	1954.7
5°	1936.6	1939.8	1943.0	1944.2	1943.5	1942.8	1942.1	1941.4
7.5°	1909.4	1911.2	1912.9	1913.2	1912.0	1910.8	1909.6	1908.3
10°	1885.0	1885.3	1885.7	1885.0	1883.2	1881.5	1879.7	1877.9
12.5°	1854.6	1854.4	1854.2	1853.1	1851.1	1849.0	1846.9	1844.9
15°	1801.4	1799.6	1797.9	1795.7	1793.2	1790.8	1788.3	1785.8
17.5°	1737.8	1733.9	1730.2	1726.6	1722.8	1719.2	1715.6	1711.8
20°	1694.1	1689.5	1685.0	1680.5	1676.3	1672.0	1667.9	1663.7
22.5°	1647.4	1641.7	1636.0	1631.1	1627.2	1623.3	1619.3	1615.4
25°	1571.0	1563.6	1556.2	1550.5	1546.7	1542.8	1538.9	1535.0
27.5°	1487.7	1477.4	1467.1	1459.1	1453.1	1447.2	1441.3	1435.3
30°	1428.5	1416.5	1404.5	1395.7	1390.1	1384.4	1378.8	1373.1
32.5°	1370.4	1357.3	1344.1	1334.6	1328.7	1322.7	1316.9	1310.9
35°	1284.0	1268.9	1253.7	1242.9	1236.6	1230.2	1223.9	1217.6
37.5°	1191.3	1174.2	1156.9	1144.4	1136.6	1128.7	1121.0	1113.1
40°	1126.9	1108.5	1090.3	1077.0	1068.8	1060.8	1052.7	1044.5
42.5°	1065.1	1045.0	1025.0	1011.4	1004.1	996.8	989.6	982.3
45°	974.1	954.0	933.9	919.7	911.2	902.7	894.2	885.8
47.5°	880.1	858.3	836.4	821.7	814.2	806.6	799.0	791.5
50°	816.7	794.8	772.8	757.9	749.8	741.6	733.6	725.5
52.5°	755.3	732.6	709.8	694.8	687.5	680.3	673.1	665.8
55°	663.9	643.4	623.0	609.3	602.2	595.1	588.0	581.0
57.5°	574.1	554.7	535.4	522.7	516.7	510.8	504.7	498.8
60°	517.5	498.5	479.4	466.9	460.9	454.8	448.9	442.9
62.5°	461.3	443.4	425.5	413.4	407.1	400.8	394.6	388.3
65°	381.3	364.1	346.8	336.2	332.3	328.4	324.6	320.6
67.5°	305.0	292.1	279.1	270.6	266.5	262.3	258.1	254.0
70°	257.8	245.5	233.2	225.1	221.2	217.3	213.4	209.5
72.5°	215.4	205.3	195.2	189.3	187.7	186.1	184.5	182.9
75°	161.2	157.6	154.1	152.1	151.4	150.7	150.0	149.3
77.5°	121.6	119.7	117.8	116.4	115.7	115.0	114.3	113.6
80°	97.9	96.8	95.7	94.9	94.2	93.5	92.8	92.1
82.5°	75.0	74.0	72.9	72.3	72.2	72.0	71.9	71.8
85°	43.0	42.3	41.6	41.3	41.3	41.3	41.3	41.3
87.5°	18.3	18.1	17.9	17.7	17.5	17.2	17.0	16.8
90°	11.8	12.2	12.6	12.9	13.1	13.3	13.5	13.7
92.5°	18.2	18.6	18.9	19.0	18.9	18.7	18.6	18.5
95°	34.6	35.0	35.4	35.6	35.6	35.6	35.6	35.6
97.5°	53.9	54.4	54.8	55.0	55.0	55.0	54.9	54.9
100°	67.9	68.2	68.5	68.8	69.0	69.2	69.4	69.6
102.5°	84.0	84.3	84.6	84.7	84.7	84.6	84.6	84.5
105°	108.0	108.0	108.0	108.1	108.4	108.6	108.8	109.0
107.5°	134.0	134.3	134.6	134.7	134.6	134.5	134.4	134.3
110°	151.4	151.8	152.2	152.3	152.1	151.9	151.7	151.5





TEST NUMBER: P332473-840

CATALOG NUMBER: S123RDIW-S1165D460U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	168.7	169.3	169.8	170.0	169.9	169.9	169.9	169.8
115°	195.2	195.3	195.4	195.4	195.3	195.2	195.1	195.0
117.5°	221.9	221.8	221.8	221.7	221.4	221.1	220.8	220.5
120°	239.6	239.5	239.4	239.2	239.0	238.8	238.6	238.4
122.5°	257.6	257.3	257.0	256.8	256.5	256.2	255.9	255.6
125°	284.3	283.9	283.5	283.1	282.7	282.3	281.9	281.4
127.5°	310.7	310.1	309.5	309.0	308.6	308.1	307.6	307.2
130°	328.2	327.8	327.4	326.9	326.2	325.5	324.8	324.0
132.5°	345.3	344.8	344.3	343.8	343.3	342.6	342.1	341.5
135°	370.8	370.4	370.0	369.7	369.5	369.3	369.1	368.9
137.5°	395.8	395.4	394.9	394.5	394.0	393.7	393.3	392.9
140°	412.1	412.0	411.9	411.5	410.8	410.1	409.4	408.7
142.5°	427.5	427.4	427.3	427.0	426.5	425.9	425.4	424.7
145°	450.1	450.0	449.9	449.7	449.3	448.9	448.5	448.1
147.5°	471.5	471.5	471.5	471.2	470.6	469.9	469.3	468.7
150°	484.6	484.6	484.6	484.3	483.7	483.1	482.5	481.9
152.5°	496.7	496.9	497.1	496.9	496.3	495.7	495.2	494.7
155°	514.3	514.7	515.1	514.9	514.2	513.5	512.8	512.1
157.5°	529.5	529.9	530.3	530.2	529.7	529.1	528.5	528.0
160°	538.8	539.3	539.8	539.8	539.4	539.0	538.6	538.2
162.5°	547.5	548.1	548.6	548.5	547.9	547.1	546.5	545.8
165°	558.7	559.3	559.9	559.8	559.1	558.4	557.6	556.9
167.5°	567.6	568.3	568.9	568.9	568.3	567.6	567.0	566.3
170°	572.6	573.3	574.0	574.0	573.3	572.6	571.9	571.2
172.5°	576.4	577.0	577.6	577.6	576.9	576.2	575.5	574.8
175°	580.6	581.2	581.8	581.8	581.1	580.4	579.7	579.0
177.5°	582.5	583.0	583.4	583.4	582.8	582.3	581.7	581.1
180°	582.6	582.6	582.6	582.6	582.6	582.6	582.6	582.6

(END OF REPORT)