

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333107-927

Luminaire Tested: **S124RDIW-S1195D1340U927-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333107-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S1195D1340U927-4F0-1E-UDD-A  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1195 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1340 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 8221.6 lumens  
Efficiency: N/A  
Efficacy: 107.9 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 76.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333107-927

CATALOG NUMBER: S124RDIW-S1195D1340U927-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P333107-927

CATALOG NUMBER: S124RDIW-S1195D1340U927-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	55	55	55	48
1	98	94	90	87	90	86	83	80	73	71	69	60	59	57	49	48	47	42
2	89	82	76	71	82	76	71	67	64	61	57	54	51	49	44	42	40	36
3	82	73	66	60	75	67	61	56	57	53	49	48	44	42	39	37	35	31
4	75	65	57	51	69	60	53	48	51	46	42	43	39	36	35	32	30	27
5	69	58	50	44	63	54	47	41	46	40	36	39	35	31	32	29	27	23
6	64	52	44	38	59	48	41	36	41	36	32	35	31	28	29	26	24	21
7	59	47	39	34	54	44	37	32	38	32	28	32	28	25	26	23	21	18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	17
9	51	39	32	27	47	36	30	25	32	26	23	27	23	20	23	19	17	15
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	21	18	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	12674	12674	12674	12674
5°	14699	12712	11235	12712
10°	17390	12656	10027	12656
15°	20088	12538	8616	12538
20°	22365	12378	7792	12378
25°	23087	12219	7234	12219
30°	20211	12028	6898	12028
35°	15733	11744	6695	11744
40°	11798	11418	6585	11418
45°	9315	10896	6528	10896
50°	7863	10295	6339	10295
55°	6854	9633	6000	9633
60°	6168	8946	5310	8946
65°	5436	8202	4567	8202
70°	4898	7435	4121	7435
75°	4105	6591	3512	6591
80°	3468	5616	3292	5616
85°	2927	4400	2927	4400



TEST NUMBER: P333107-927

CATALOG NUMBER: S124RDIW-S1195D1340U927-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	152.1	1.9
10°-20°	458.8	5.6
20°-30°	717.6	8.7
30°-40°	797.8	9.7
40°-50°	707.8	8.6
50°-60°	551.5	6.7
60°-70°	361.1	4.4
70°-80°	177.6	2.2
80°-90°	47.8	0.6
90°-100°	47.0	0.6
100°-110°	299.6	3.6
110°-120°	573.1	7.0
120°-130°	727.5	8.8
130°-140°	778.4	9.5
140°-150°	727.9	8.9
150°-160°	587.0	7.1
160°-170°	378.6	4.6
170°-180°	130.5	1.6
0°-30°	1328.5	16.2
0°-40°	2126.3	25.9
0°-60°	3385.7	41.2
0°-90°	3972.1	48.3
90°-120°	919.7	11.2
90°-150°	3153.4	38.4
90°-180°	4250.0	51.7
0°-180°	8221.6	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1570	1570	1570	1570	1570	
5°	1814	1569	1386	1569	1814	183
15°	2404	1500	1031	1500	2404	683
25°	2592	1372	812	1372	2592	1150
35°	1596	1192	679	1192	1596	1001
45°	816	954	572	954	816	646
55°	487	684	426	684	487	443
65°	285	429	239	429	285	286
75°	132	211	113	211	132	145
85°	32	48	32	48	32	36
90°	31	3	31	3	31	15
95°	30	56	30	56	30	24
105°	293	309	293	309	293	255
115°	582	577	582	577	582	576
125°	818	812	818	812	818	728
135°	1014	1007	1014	1007	1014	781
145°	1167	1161	1167	1161	1167	729
155°	1272	1273	1272	1273	1272	587
165°	1337	1343	1337	1343	1337	378
175°	1366	1374	1366	1374	1366	130
180°	1374	1374	1374	1374	1374	



TEST NUMBER: P333107-927

CATALOG NUMBER: S124RDIW-S1195D1340U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9
2.5°	1655.8	1660.4	1655.8	1655.3	1650.3	1648.8	1646.7	1640.1	1628.0	1621.0	1622.5
5°	1813.9	1829.8	1820.9	1819.6	1805.8	1791.8	1783.0	1762.8	1741.2	1726.7	1714.7
7.5°	1996.9	2006.0	2000.4	1991.5	1969.0	1956.3	1935.8	1909.1	1870.5	1841.0	1814.1
10°	2121.4	2128.9	2126.5	2110.0	2093.5	2060.0	2041.1	2003.7	1955.0	1916.4	1880.4
12.5°	2243.8	2251.9	2229.7	2230.4	2199.3	2172.9	2142.8	2095.8	2039.6	1989.8	1944.6
15°	2403.5	2393.3	2393.3	2380.7	2345.9	2309.2	2278.2	2228.9	2158.1	2098.6	2036.0
17.5°	2528.4	2532.0	2526.7	2497.0	2469.6	2431.7	2374.9	2317.3	2251.5	2171.7	2107.7
20°	2603.3	2603.3	2597.6	2577.4	2542.0	2501.5	2440.2	2377.5	2294.0	2213.7	2141.6
22.5°	2633.7	2635.7	2629.0	2612.3	2580.5	2540.9	2488.7	2425.1	2339.1	2248.6	2159.3
25°	2591.9	2604.0	2605.2	2600.8	2591.3	2567.2	2522.4	2457.2	2380.0	2282.0	2185.9
27.5°	2379.6	2394.8	2408.2	2430.0	2459.1	2474.3	2476.3	2443.2	2375.8	2281.5	2184.8
30°	2168.1	2180.8	2221.9	2275.7	2317.5	2355.4	2388.3	2397.1	2359.2	2274.4	2172.6
32.5°	1933.4	1950.6	1991.7	2049.5	2119.1	2183.3	2257.2	2294.9	2293.9	2243.1	2148.8
35°	1596.4	1609.1	1647.0	1707.7	1791.2	1886.7	2003.7	2094.8	2156.8	2152.4	2094.8
37.5°	1287.5	1301.8	1340.1	1390.4	1471.4	1589.7	1702.9	1828.4	1943.0	2007.4	1988.1
40°	1119.5	1120.1	1157.5	1209.3	1285.2	1388.3	1511.6	1650.7	1778.5	1882.9	1903.1
42.5°	986.9	987.1	1011.7	1067.6	1122.3	1219.3	1337.0	1475.2	1624.8	1745.3	1798.9
45°	815.9	821.6	841.9	875.4	918.4	1000.6	1094.8	1223.2	1390.8	1533.7	1622.9
47.5°	690.9	699.3	712.2	739.5	773.8	828.5	906.5	1021.8	1158.2	1315.4	1442.3
50°	626.1	627.4	643.9	659.0	688.8	732.5	800.7	896.8	1022.1	1173.2	1314.3
52.5°	570.5	570.2	580.1	599.4	623.5	657.5	712.6	800.2	911.2	1046.8	1192.4
55°	487.0	490.2	497.7	512.9	531.3	555.3	599.0	664.7	752.0	867.8	1000.0
57.5°	423.5	425.2	431.1	437.5	454.4	471.8	504.6	550.2	623.9	718.7	841.9
60°	382.0	382.6	384.5	394.0	407.3	423.7	445.9	484.5	546.4	633.1	730.6
62.5°	341.5	342.7	345.6	352.5	362.8	374.1	397.4	428.3	479.7	553.7	641.4
65°	284.6	285.3	289.7	292.2	300.4	310.5	327.6	348.5	383.9	445.9	512.3
67.5°	237.8	237.8	238.1	241.5	247.2	253.9	264.1	280.8	307.5	345.6	404.2
70°	207.5	207.5	208.7	210.6	213.8	219.4	225.1	237.8	257.5	288.4	333.4
72.5°	179.1	179.6	180.9	181.3	182.9	187.6	191.8	199.9	214.4	237.8	274.1
75°	131.6	133.5	136.7	139.2	142.3	141.6	146.1	151.1	155.6	169.5	190.4
77.5°	97.9	96.9	97.3	99.4	99.8	100.4	103.6	107.5	110.8	117.4	124.8
80°	74.6	74.6	76.5	77.2	76.5	77.2	80.3	82.2	83.5	86.0	93.0
82.5°	56.4	57.4	56.8	57.4	57.8	58.5	61.1	61.5	62.7	63.8	66.7
85°	31.6	32.2	32.9	31.6	31.6	31.6	32.9	33.5	34.8	34.1	35.4
87.5°	17.3	16.7	17.1	17.0	17.4	16.7	17.0	17.7	16.4	16.6	16.3
90°	30.8	30.3	29.9	29.5	29.0	28.1	26.7	25.3	24.0	22.6	20.8
92.5°	28.4	28.3	28.2	28.1	28.0	27.3	25.9	24.6	23.1	21.8	20.0
95°	29.8	29.5	29.3	29.1	28.9	28.1	26.7	25.3	24.0	22.6	22.3
97.5°	28.8	28.5	28.3	28.1	27.9	27.6	27.6	27.4	27.3	27.1	52.6
100°	28.8	28.5	28.3	28.1	27.9	29.7	33.6	37.5	41.4	45.2	76.7
102.5°	29.6	29.5	29.5	29.5	29.4	50.3	92.2	134.1	175.9	217.9	222.0
105°	292.9	301.0	309.3	317.5	325.7	328.8	326.8	324.7	322.7	320.6	319.4
107.5°	408.1	407.3	406.4	405.5	404.6	403.7	402.7	401.7	400.7	399.7	398.2
110°	458.3	457.6	456.9	456.2	455.5	455.0	454.5	454.1	453.6	453.1	451.8



TEST NUMBER: P333107-927

CATALOG NUMBER: S124RDIW-S1195D1340U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	508.4	507.6	506.7	505.8	504.9	504.5	504.6	504.7	504.9	504.9	504.3
115°	581.5	581.5	581.5	581.5	581.5	581.3	580.9	580.4	580.0	579.5	579.7
117.5°	655.9	656.1	656.2	656.2	656.3	656.4	656.5	656.6	656.7	656.8	656.2
120°	702.8	703.3	703.7	704.2	704.6	704.6	704.2	703.7	703.3	702.8	703.1
122.5°	748.8	749.3	749.7	750.2	750.7	750.8	750.5	750.2	750.0	749.6	749.3
125°	817.9	817.7	817.5	817.2	817.0	816.5	815.9	815.2	814.4	813.8	814.2
127.5°	878.5	878.7	878.8	879.1	879.2	879.4	879.6	879.7	879.8	880.0	878.9
130°	919.6	919.6	919.6	919.6	919.6	919.5	919.2	919.0	918.9	918.6	917.9
132.5°	957.4	957.6	957.8	958.0	958.1	958.1	957.9	957.7	957.4	957.2	956.3
135°	1014.2	1013.7	1013.2	1012.8	1012.3	1011.9	1011.4	1011.0	1010.5	1010.0	1009.2
137.5°	1062.6	1062.8	1063.0	1063.0	1063.2	1063.0	1062.5	1062.0	1061.5	1061.0	1060.0
140°	1096.4	1096.1	1095.9	1095.7	1095.4	1095.0	1094.3	1093.6	1092.9	1092.3	1091.8
142.5°	1124.3	1124.3	1124.2	1124.2	1124.1	1123.9	1123.3	1122.8	1122.4	1121.8	1121.6
145°	1167.3	1166.8	1166.3	1165.9	1165.5	1165.1	1164.8	1164.6	1164.4	1164.2	1164.2
147.5°	1202.8	1202.5	1202.4	1202.1	1201.9	1201.7	1201.5	1201.3	1201.1	1200.9	1201.2
150°	1225.8	1225.6	1225.3	1225.1	1224.9	1224.8	1224.8	1224.8	1224.8	1224.8	1225.0
152.5°	1245.5	1245.7	1245.8	1245.9	1246.1	1245.9	1245.6	1245.2	1244.9	1244.5	1244.9
155°	1272.1	1272.7	1273.4	1274.1	1274.8	1274.7	1273.7	1272.9	1271.9	1271.1	1271.7
157.5°	1294.3	1295.5	1296.6	1297.8	1299.0	1299.0	1297.8	1296.6	1295.5	1294.3	1295.1
160°	1309.1	1310.4	1311.8	1313.1	1314.5	1314.5	1313.1	1311.8	1310.4	1309.1	1309.2
162.5°	1320.6	1322.1	1323.7	1325.2	1326.7	1326.8	1325.5	1324.1	1322.7	1321.4	1321.6
165°	1336.8	1338.9	1340.9	1343.0	1345.0	1345.1	1343.3	1341.5	1339.7	1337.8	1337.8
167.5°	1348.9	1351.2	1353.4	1355.7	1358.0	1358.2	1356.1	1354.2	1352.2	1350.1	1350.3
170°	1356.3	1358.6	1360.9	1363.2	1365.4	1365.6	1363.8	1362.0	1360.2	1358.4	1358.1
172.5°	1360.4	1362.9	1365.3	1367.8	1370.3	1370.6	1368.8	1366.9	1365.1	1363.3	1363.0
175°	1365.6	1368.3	1371.0	1373.8	1376.5	1376.9	1374.8	1372.8	1370.7	1368.7	1368.4
177.5°	1368.8	1371.0	1373.2	1375.4	1377.6	1378.0	1376.5	1375.1	1373.6	1372.1	1371.7
180°	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8



TEST NUMBER: P333107-927

CATALOG NUMBER: S124RDIW-S1195D1340U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9
2.5°	1617.4	1610.3	1606.8	1598.7	1589.0	1584.0	1579.5	1572.9	1564.2	1555.1	1548.6
5°	1699.5	1684.3	1665.3	1642.6	1622.3	1602.7	1585.6	1568.6	1549.0	1528.8	1508.5
7.5°	1783.8	1753.9	1721.6	1684.3	1648.0	1615.0	1584.6	1555.5	1522.7	1493.2	1466.3
10°	1842.5	1802.0	1757.1	1709.6	1662.2	1621.0	1580.6	1543.9	1503.4	1467.4	1437.0
12.5°	1890.0	1842.5	1788.4	1729.3	1672.3	1622.5	1576.0	1528.2	1482.2	1443.1	1402.6
15°	1968.9	1903.8	1831.1	1760.2	1686.2	1618.5	1555.9	1500.2	1447.8	1392.7	1354.2
17.5°	2023.2	1945.9	1857.5	1772.3	1685.0	1605.1	1532.9	1466.6	1406.0	1349.9	1303.9
20°	2055.6	1970.2	1872.2	1775.4	1677.4	1592.0	1514.2	1440.8	1378.2	1317.5	1270.0
22.5°	2073.8	1979.3	1872.2	1770.8	1669.3	1576.8	1491.4	1415.0	1346.8	1286.1	1233.6
25°	2079.6	1978.4	1869.0	1752.6	1641.3	1543.3	1454.7	1371.8	1295.9	1235.2	1179.6
27.5°	2071.6	1952.3	1840.3	1720.9	1606.0	1502.7	1409.7	1322.6	1246.7	1181.5	1124.4
30°	2059.4	1931.6	1811.4	1687.5	1571.1	1471.8	1373.7	1290.3	1211.2	1143.5	1086.0
32.5°	2033.1	1906.3	1777.0	1650.0	1532.2	1429.8	1336.8	1252.8	1175.3	1106.1	1045.0
35°	1980.9	1852.5	1712.1	1581.8	1466.1	1359.9	1272.6	1191.6	1117.6	1043.6	979.1
37.5°	1912.2	1781.1	1641.4	1498.7	1382.8	1282.5	1202.5	1126.5	1054.2	986.7	915.2
40°	1847.5	1728.0	1583.7	1442.1	1323.2	1226.4	1152.4	1083.5	1010.7	943.6	872.2
42.5°	1769.1	1667.2	1521.5	1379.3	1261.9	1168.7	1099.8	1032.4	966.2	901.2	826.6
45°	1638.2	1561.0	1424.3	1287.8	1169.5	1077.1	1013.9	954.4	896.2	834.2	764.1
47.5°	1488.1	1435.8	1318.0	1178.1	1068.7	985.6	924.5	875.8	826.6	764.7	703.1
50°	1383.9	1350.4	1236.5	1108.7	1004.4	927.9	865.2	819.7	778.6	719.1	664.1
52.5°	1272.6	1254.7	1158.6	1036.4	935.6	860.5	807.1	766.0	724.5	675.1	623.6
55°	1103.0	1112.5	1030.9	925.3	830.4	767.2	718.5	684.4	649.0	607.2	567.4
57.5°	929.8	964.4	909.7	816.9	728.0	669.6	632.9	604.1	574.4	539.8	505.7
60°	826.0	855.1	824.1	742.5	664.7	610.4	576.2	554.1	524.3	492.7	466.8
62.5°	724.8	756.0	737.6	671.7	599.4	552.7	522.5	501.9	479.8	452.3	425.3
65°	597.7	617.9	609.1	563.6	512.3	472.5	444.7	429.4	409.2	389.0	365.0
67.5°	457.8	496.9	491.7	467.5	423.3	392.1	373.9	360.5	342.1	327.0	310.7
70°	376.4	412.4	411.8	392.1	368.1	339.0	326.4	315.0	298.5	284.0	270.7
72.5°	308.0	341.0	345.9	330.9	314.5	292.5	280.4	272.5	256.5	246.5	235.8
75°	215.7	239.7	246.1	246.1	238.4	227.0	216.3	211.3	199.9	191.0	184.7
77.5°	141.4	156.6	166.4	168.7	169.9	166.1	157.2	153.7	145.0	141.8	135.7
80°	99.9	110.0	121.4	125.2	128.4	127.1	123.3	120.8	112.6	109.4	106.9
82.5°	69.1	74.6	84.0	92.4	91.4	94.7	91.4	89.4	83.3	82.1	79.5
85°	36.0	36.7	37.9	43.6	46.8	48.1	48.7	47.5	45.6	45.6	41.1
87.5°	15.9	15.1	15.7	15.3	15.3	16.8	17.8	17.8	16.8	15.8	14.7
90°	18.9	17.1	15.3	13.2	10.6	8.1	5.6	3.1	5.6	8.1	10.6
92.5°	18.1	16.3	14.5	13.5	13.4	13.2	13.1	12.9	13.1	13.2	13.4
95°	22.2	21.9	21.7	25.4	33.2	41.0	48.7	56.5	48.7	41.0	33.2
97.5°	78.1	103.5	129.0	139.3	134.5	129.7	124.8	120.0	124.8	129.7	134.5
100°	108.2	139.7	171.3	185.0	180.9	176.7	172.6	168.5	172.6	176.7	180.9
102.5°	226.1	230.1	234.2	234.8	231.8	228.8	225.8	222.8	225.8	228.8	231.8
105°	318.3	317.2	316.0	314.7	313.4	312.0	310.6	309.3	310.6	312.0	313.4
107.5°	396.6	395.1	393.5	392.4	391.7	391.0	390.3	389.6	390.3	391.0	391.7
110°	450.4	449.0	447.7	446.6	445.9	445.3	444.6	443.9	444.6	445.3	445.9





TEST NUMBER: P333107-927

CATALOG NUMBER: S124RDIW-S1195D1340U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	503.7	503.0	502.3	501.5	500.2	499.0	497.7	496.5	497.7	499.0	500.2
115°	580.0	580.2	580.4	580.2	579.5	578.8	578.1	577.4	578.1	578.8	579.5
117.5°	655.8	655.3	654.7	654.0	653.2	652.2	651.3	650.4	651.3	652.2	653.2
120°	703.3	703.5	703.7	703.4	702.5	701.6	700.6	699.7	700.6	701.6	702.5
122.5°	749.0	748.7	748.4	748.0	747.4	746.9	746.3	745.8	746.3	746.9	747.4
125°	814.7	815.2	815.6	815.4	814.4	813.6	812.6	811.7	812.6	813.6	814.4
127.5°	877.8	876.8	875.8	875.1	874.9	874.6	874.4	874.2	874.4	874.6	874.9
130°	917.2	916.6	915.8	915.4	915.1	915.0	914.7	914.5	914.7	915.0	915.1
132.5°	955.5	954.7	953.8	953.1	952.7	952.3	951.9	951.5	951.9	952.3	952.7
135°	1008.2	1007.3	1006.4	1006.1	1006.3	1006.5	1006.7	1006.9	1006.7	1006.5	1006.3
137.5°	1059.0	1058.0	1057.0	1056.5	1056.4	1056.2	1056.1	1056.1	1056.1	1056.2	1056.4
140°	1091.3	1090.8	1090.4	1090.0	1089.5	1089.0	1088.6	1088.1	1088.6	1089.0	1089.5
142.5°	1121.3	1121.0	1120.7	1120.2	1119.4	1118.6	1117.7	1116.9	1117.7	1118.6	1119.4
145°	1164.2	1164.2	1164.2	1163.8	1163.2	1162.4	1161.7	1161.1	1161.7	1162.4	1163.2
147.5°	1201.4	1201.7	1201.9	1201.3	1200.1	1198.8	1197.5	1196.2	1197.5	1198.8	1200.1
150°	1225.3	1225.5	1225.7	1225.3	1224.5	1223.5	1222.7	1221.7	1222.7	1223.5	1224.5
152.5°	1245.3	1245.8	1246.2	1246.0	1245.2	1244.5	1243.8	1243.1	1243.8	1244.5	1245.2
155°	1272.4	1273.1	1273.7	1274.0	1273.7	1273.5	1273.3	1273.1	1273.3	1273.5	1273.7
157.5°	1295.8	1296.6	1297.4	1297.8	1297.9	1298.1	1298.2	1298.4	1298.2	1298.1	1297.9
160°	1309.5	1309.7	1310.0	1310.4	1311.1	1311.8	1312.5	1313.1	1312.5	1311.8	1311.1
162.5°	1321.8	1322.1	1322.3	1322.9	1323.7	1324.6	1325.4	1326.3	1325.4	1324.6	1323.7
165°	1337.8	1337.8	1337.8	1338.4	1339.5	1340.7	1341.8	1343.0	1341.8	1340.7	1339.5
167.5°	1350.4	1350.6	1350.7	1351.4	1352.6	1353.8	1354.9	1356.1	1354.9	1353.8	1352.6
170°	1357.9	1357.6	1357.5	1358.0	1359.4	1360.7	1362.2	1363.5	1362.2	1360.7	1359.4
172.5°	1362.9	1362.6	1362.4	1362.9	1364.3	1365.7	1367.1	1368.4	1367.1	1365.7	1364.3
175°	1368.2	1367.9	1367.7	1368.3	1369.7	1371.0	1372.4	1373.8	1372.4	1371.0	1369.7
177.5°	1371.4	1371.0	1370.6	1371.1	1372.4	1373.6	1375.0	1376.3	1375.0	1373.6	1372.4
180°	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8



TEST NUMBER: P333107-927

CATALOG NUMBER: S124RDIW-S1195D1340U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9
2.5°	1541.5	1536.4	1529.9	1522.3	1513.1	1505.1	1501.5	1504.6	1506.1	1502.1	1501.5
5°	1494.5	1478.8	1466.1	1447.2	1431.9	1419.3	1410.5	1406.7	1407.9	1397.8	1395.3
7.5°	1441.9	1423.1	1402.3	1379.8	1358.8	1340.2	1330.5	1325.2	1314.5	1309.9	1302.2
10°	1407.9	1382.6	1362.4	1335.8	1311.8	1289.7	1278.9	1270.0	1259.3	1254.2	1243.5
12.5°	1373.0	1343.6	1321.4	1293.8	1269.2	1242.6	1232.3	1215.9	1199.0	1188.4	1174.6
15°	1323.8	1288.4	1261.2	1228.3	1199.2	1168.9	1141.6	1111.3	1099.9	1075.9	1061.9
17.5°	1266.2	1230.3	1196.7	1152.5	1107.6	1069.9	1040.9	1011.9	994.4	979.1	972.0
20°	1228.3	1195.4	1148.6	1097.3	1047.4	1005.7	982.2	963.3	944.3	933.6	926.0
22.5°	1192.4	1150.3	1096.0	1040.7	990.7	958.1	938.3	918.8	903.3	893.1	883.0
25°	1132.2	1077.1	1019.5	956.3	922.2	893.7	872.2	856.3	846.9	833.6	828.5
27.5°	1070.3	1003.6	940.2	897.6	862.1	836.0	817.3	805.4	793.4	784.9	778.3
30°	1022.7	955.1	898.1	857.6	821.6	800.1	784.9	771.0	761.5	754.6	749.5
32.5°	975.7	908.0	860.2	816.7	788.2	767.2	751.0	740.6	733.2	724.2	721.1
35°	907.6	847.6	805.8	766.6	737.4	718.5	705.8	695.1	688.8	686.3	684.4
37.5°	842.2	793.0	748.1	716.0	690.1	675.1	660.2	654.9	650.5	646.0	648.1
40°	800.7	754.6	714.7	680.6	659.7	643.3	634.4	628.0	624.2	624.2	624.2
42.5°	764.8	719.6	680.8	650.2	629.3	615.4	605.5	600.2	599.0	598.5	601.5
45°	709.0	667.3	628.0	602.8	585.0	571.2	565.5	561.0	561.0	563.6	564.2
47.5°	653.7	614.7	583.1	554.8	538.6	529.9	525.0	522.7	522.9	525.5	528.4
50°	619.8	581.2	550.2	525.0	509.8	501.5	497.1	495.9	497.1	497.1	501.5
52.5°	582.9	548.3	517.8	496.6	479.4	471.7	469.3	467.5	468.3	470.3	472.2
55°	528.8	497.7	468.7	448.5	435.8	430.7	425.0	425.6	424.4	425.6	425.6
57.5°	474.5	446.6	419.6	403.5	392.4	385.1	378.8	380.6	378.7	378.5	377.5
60°	439.6	409.2	387.7	373.2	360.5	354.2	348.5	349.7	347.8	346.6	344.0
62.5°	401.6	376.4	355.8	341.8	331.7	324.3	318.6	317.3	313.0	308.6	303.1
65°	346.6	325.7	307.4	294.1	284.6	278.9	274.5	270.7	261.2	251.1	246.1
67.5°	293.1	278.1	260.9	249.7	242.0	234.6	226.1	219.6	210.7	205.2	202.0
70°	258.6	244.2	229.6	218.8	210.6	203.7	194.2	189.7	183.4	180.9	177.8
72.5°	225.8	212.2	198.8	189.0	180.2	174.8	167.4	163.0	160.2	159.1	156.0
75°	175.9	165.1	155.0	146.1	139.2	135.4	132.2	129.0	127.8	122.1	118.9
77.5°	128.3	121.2	114.9	108.5	103.6	101.1	95.0	91.3	89.2	86.5	85.9
80°	99.9	94.9	88.6	84.8	77.8	75.3	72.7	72.1	71.5	70.8	70.2
82.5°	75.2	70.1	63.8	61.5	59.6	58.1	56.6	55.9	55.3	55.7	55.5
85°	37.9	35.4	35.4	34.8	34.1	33.5	32.9	32.9	32.2	32.9	32.2
87.5°	15.3	15.2	15.6	14.9	15.8	16.2	15.9	16.2	17.0	16.2	16.4
90°	13.2	15.3	17.1	18.9	20.8	22.6	24.0	25.3	26.7	28.1	29.0
92.5°	13.5	14.5	16.3	18.1	20.0	21.8	23.1	24.6	25.9	27.3	28.0
95°	25.4	21.7	21.9	22.2	22.3	22.6	24.0	25.3	26.7	28.1	28.9
97.5°	139.3	129.0	103.5	78.1	52.6	27.1	27.3	27.4	27.6	27.6	27.9
100°	185.0	171.3	139.7	108.2	76.7	45.2	41.4	37.5	33.6	29.7	27.9
102.5°	234.8	234.2	230.1	226.1	222.0	217.9	175.9	134.1	92.2	50.3	29.4
105°	314.7	316.0	317.2	318.3	319.4	320.6	322.7	324.7	326.8	328.8	325.7
107.5°	392.4	393.5	395.1	396.6	398.2	399.7	400.7	401.7	402.7	403.7	404.6
110°	446.6	447.7	449.0	450.4	451.8	453.1	453.6	454.1	454.5	455.0	455.5



TEST NUMBER: P333107-927

CATALOG NUMBER: S124RDIW-S1195D1340U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	501.5	502.3	503.0	503.7	504.3	504.9	504.9	504.7	504.6	504.5	504.9
115°	580.2	580.4	580.2	580.0	579.7	579.5	580.0	580.4	580.9	581.3	581.5
117.5°	654.0	654.7	655.3	655.8	656.2	656.8	656.7	656.6	656.5	656.4	656.3
120°	703.4	703.7	703.5	703.3	703.1	702.8	703.3	703.7	704.2	704.6	704.6
122.5°	748.0	748.4	748.7	749.0	749.3	749.6	750.0	750.2	750.5	750.8	750.7
125°	815.4	815.6	815.2	814.7	814.2	813.8	814.4	815.2	815.9	816.5	817.0
127.5°	875.1	875.8	876.8	877.8	878.9	880.0	879.8	879.7	879.6	879.4	879.2
130°	915.4	915.8	916.6	917.2	917.9	918.6	918.9	919.0	919.2	919.5	919.6
132.5°	953.1	953.8	954.7	955.5	956.3	957.2	957.4	957.7	957.9	958.1	958.1
135°	1006.1	1006.4	1007.3	1008.2	1009.2	1010.0	1010.5	1011.0	1011.4	1011.9	1012.3
137.5°	1056.5	1057.0	1058.0	1059.0	1060.0	1061.0	1061.5	1062.0	1062.5	1063.0	1063.2
140°	1090.0	1090.4	1090.8	1091.3	1091.8	1092.3	1092.9	1093.6	1094.3	1095.0	1095.4
142.5°	1120.2	1120.7	1121.0	1121.3	1121.6	1121.8	1122.4	1122.8	1123.3	1123.9	1124.1
145°	1163.8	1164.2	1164.2	1164.2	1164.2	1164.2	1164.4	1164.6	1164.8	1165.1	1165.5
147.5°	1201.3	1201.9	1201.7	1201.4	1201.2	1200.9	1201.1	1201.3	1201.5	1201.7	1201.9
150°	1225.3	1225.7	1225.5	1225.3	1225.0	1224.8	1224.8	1224.8	1224.8	1224.8	1224.9
152.5°	1246.0	1246.2	1245.8	1245.3	1244.9	1244.5	1244.9	1245.2	1245.6	1245.9	1246.1
155°	1274.0	1273.7	1273.1	1272.4	1271.7	1271.1	1271.9	1272.9	1273.7	1274.7	1274.8
157.5°	1297.8	1297.4	1296.6	1295.8	1295.1	1294.3	1295.5	1296.6	1297.8	1299.0	1299.0
160°	1310.4	1310.0	1309.7	1309.5	1309.2	1309.1	1310.4	1311.8	1313.1	1314.5	1314.5
162.5°	1322.9	1322.3	1322.1	1321.8	1321.6	1321.4	1322.7	1324.1	1325.5	1326.8	1326.7
165°	1338.4	1337.8	1337.8	1337.8	1337.8	1337.8	1339.7	1341.5	1343.3	1345.1	1345.0
167.5°	1351.4	1350.7	1350.6	1350.4	1350.3	1350.1	1352.2	1354.2	1356.1	1358.2	1358.0
170°	1358.0	1357.5	1357.6	1357.9	1358.1	1358.4	1360.2	1362.0	1363.8	1365.6	1365.4
172.5°	1362.9	1362.4	1362.6	1362.9	1363.0	1363.3	1365.1	1366.9	1368.8	1370.6	1370.3
175°	1368.3	1367.7	1367.9	1368.2	1368.4	1368.7	1370.7	1372.8	1374.8	1376.9	1376.5
177.5°	1371.1	1370.6	1371.0	1371.4	1371.7	1372.1	1373.6	1375.1	1376.5	1378.0	1377.6
180°	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8



TEST NUMBER: P333107-927

CATALOG NUMBER: S124RDIW-S1195D1340U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9
2.5°	1498.5	1499.5	1496.0	1494.9	1496.0	1499.5	1498.5	1501.5	1502.1	1506.1	1504.6
5°	1390.2	1388.9	1385.8	1386.4	1385.8	1388.9	1390.2	1395.3	1397.8	1407.9	1406.7
7.5°	1297.6	1292.7	1294.0	1289.0	1294.0	1292.7	1297.6	1302.2	1309.9	1314.5	1325.2
10°	1241.0	1234.0	1228.3	1223.2	1228.3	1234.0	1241.0	1243.5	1254.2	1259.3	1270.0
12.5°	1163.6	1157.5	1149.9	1151.4	1149.9	1157.5	1163.6	1174.6	1188.4	1199.0	1215.9
15°	1053.7	1044.3	1029.0	1030.9	1029.0	1044.3	1053.7	1061.9	1075.9	1099.9	1111.3
17.5°	960.8	960.8	953.9	955.5	953.9	960.8	960.8	972.0	979.1	994.4	1011.9
20°	912.7	908.2	908.9	907.0	908.9	908.2	912.7	926.0	933.6	944.3	963.3
22.5°	879.2	873.9	869.4	865.5	869.4	873.9	879.2	883.0	893.1	903.3	918.8
25°	822.8	819.0	813.4	812.1	813.4	819.0	822.8	828.5	833.6	846.9	856.3
27.5°	773.2	772.5	770.2	767.3	770.2	772.5	773.2	778.3	784.9	793.4	805.4
30°	744.4	743.1	741.9	740.0	741.9	743.1	744.4	749.5	754.6	761.5	771.0
32.5°	718.7	717.9	716.6	716.8	716.6	717.9	718.7	721.1	724.2	733.2	740.6
35°	681.8	681.2	679.9	679.3	679.9	681.2	681.8	684.4	686.3	688.8	695.1
37.5°	647.5	649.0	648.3	648.2	648.3	649.0	647.5	648.1	646.0	650.5	654.9
40°	623.6	624.2	625.5	624.9	625.5	624.2	623.6	624.2	624.2	624.2	628.0
42.5°	603.9	604.0	605.8	603.6	605.8	604.0	603.9	601.5	598.5	599.0	600.2
45°	568.6	572.4	571.8	571.8	571.8	572.4	568.6	564.2	563.6	561.0	561.0
47.5°	530.0	533.3	534.2	534.1	534.2	533.3	530.0	528.4	525.5	522.9	522.7
50°	504.7	503.4	505.3	504.7	505.3	503.4	504.7	501.5	497.1	497.1	495.9
52.5°	473.9	474.1	474.0	473.3	474.0	474.1	473.9	472.2	470.3	468.3	467.5
55°	426.3	426.9	425.6	426.3	425.6	426.9	426.3	425.6	425.6	424.4	425.6
57.5°	374.7	371.6	372.9	371.4	372.9	371.6	374.7	377.5	378.5	378.7	380.6
60°	337.8	332.7	331.4	328.9	331.4	332.7	337.8	344.0	346.6	347.8	349.7
62.5°	296.3	292.7	288.4	290.4	288.4	292.7	296.3	303.1	308.6	313.0	317.3
65°	241.0	238.4	236.5	239.1	236.5	238.4	241.0	246.1	251.1	261.2	270.7
67.5°	199.5	198.1	198.1	196.9	198.1	198.1	199.5	202.0	205.2	210.7	219.6
70°	177.8	175.9	175.9	174.6	175.9	175.9	177.8	177.8	180.9	183.4	189.7
72.5°	155.4	153.6	154.1	153.3	154.1	153.6	155.4	156.0	159.1	160.2	163.0
75°	115.1	111.9	111.9	112.6	111.9	111.9	115.1	118.9	122.1	127.8	129.0
77.5°	85.9	85.2	86.1	85.0	86.1	85.2	85.9	85.9	86.5	89.2	91.3
80°	70.2	69.6	68.9	70.8	68.9	69.6	70.2	70.2	70.8	71.5	72.1
82.5°	54.5	54.4	54.3	56.6	54.3	54.4	54.5	55.5	55.7	55.3	55.9
85°	32.9	31.6	32.9	31.6	32.9	31.6	32.9	32.2	32.9	32.2	32.9
87.5°	17.5	17.1	16.7	17.3	16.7	17.1	17.5	16.4	16.2	17.0	16.2
90°	29.5	29.9	30.3	30.8	30.3	29.9	29.5	29.0	28.1	26.7	25.3
92.5°	28.1	28.2	28.3	28.4	28.3	28.2	28.1	28.0	27.3	25.9	24.6
95°	29.1	29.3	29.5	29.8	29.5	29.3	29.1	28.9	28.1	26.7	25.3
97.5°	28.1	28.3	28.5	28.8	28.5	28.3	28.1	27.9	27.6	27.6	27.4
100°	28.1	28.3	28.5	28.8	28.5	28.3	28.1	27.9	29.7	33.6	37.5
102.5°	29.5	29.5	29.5	29.6	29.5	29.5	29.5	29.4	50.3	92.2	134.1
105°	317.5	309.3	301.0	292.9	301.0	309.3	317.5	325.7	328.8	326.8	324.7
107.5°	405.5	406.4	407.3	408.1	407.3	406.4	405.5	404.6	403.7	402.7	401.7
110°	456.2	456.9	457.6	458.3	457.6	456.9	456.2	455.5	455.0	454.5	454.1



TEST NUMBER: P333107-927

CATALOG NUMBER: S124RDIW-S1195D1340U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	505.8	506.7	507.6	508.4	507.6	506.7	505.8	504.9	504.5	504.6	504.7
115°	581.5	581.5	581.5	581.5	581.5	581.5	581.5	581.5	581.3	580.9	580.4
117.5°	656.2	656.2	656.1	655.9	656.1	656.2	656.2	656.3	656.4	656.5	656.6
120°	704.2	703.7	703.3	702.8	703.3	703.7	704.2	704.6	704.6	704.2	703.7
122.5°	750.2	749.7	749.3	748.8	749.3	749.7	750.2	750.7	750.8	750.5	750.2
125°	817.2	817.5	817.7	817.9	817.7	817.5	817.2	817.0	816.5	815.9	815.2
127.5°	879.1	878.8	878.7	878.5	878.7	878.8	879.1	879.2	879.4	879.6	879.7
130°	919.6	919.6	919.6	919.6	919.6	919.6	919.6	919.6	919.5	919.2	919.0
132.5°	958.0	957.8	957.6	957.4	957.6	957.8	958.0	958.1	958.1	957.9	957.7
135°	1012.8	1013.2	1013.7	1014.2	1013.7	1013.2	1012.8	1012.3	1011.9	1011.4	1011.0
137.5°	1063.0	1063.0	1062.8	1062.6	1062.8	1063.0	1063.0	1063.2	1063.0	1062.5	1062.0
140°	1095.7	1095.9	1096.1	1096.4	1096.1	1095.9	1095.7	1095.4	1095.0	1094.3	1093.6
142.5°	1124.2	1124.2	1124.3	1124.3	1124.3	1124.2	1124.2	1124.1	1123.9	1123.3	1122.8
145°	1165.9	1166.3	1166.8	1167.3	1166.8	1166.3	1165.9	1165.5	1165.1	1164.8	1164.6
147.5°	1202.1	1202.4	1202.5	1202.8	1202.5	1202.4	1202.1	1201.9	1201.7	1201.5	1201.3
150°	1225.1	1225.3	1225.6	1225.8	1225.6	1225.3	1225.1	1224.9	1224.8	1224.8	1224.8
152.5°	1245.9	1245.8	1245.7	1245.5	1245.7	1245.8	1245.9	1246.1	1245.9	1245.6	1245.2
155°	1274.1	1273.4	1272.7	1272.1	1272.7	1273.4	1274.1	1274.8	1274.7	1273.7	1272.9
157.5°	1297.8	1296.6	1295.5	1294.3	1295.5	1296.6	1297.8	1299.0	1299.0	1297.8	1296.6
160°	1313.1	1311.8	1310.4	1309.1	1310.4	1311.8	1313.1	1314.5	1314.5	1313.1	1311.8
162.5°	1325.2	1323.7	1322.1	1320.6	1322.1	1323.7	1325.2	1326.7	1326.8	1325.5	1324.1
165°	1343.0	1340.9	1338.9	1336.8	1338.9	1340.9	1343.0	1345.0	1345.1	1343.3	1341.5
167.5°	1355.7	1353.4	1351.2	1348.9	1351.2	1353.4	1355.7	1358.0	1358.2	1356.1	1354.2
170°	1363.2	1360.9	1358.6	1356.3	1358.6	1360.9	1363.2	1365.4	1365.6	1363.8	1362.0
172.5°	1367.8	1365.3	1362.9	1360.4	1362.9	1365.3	1367.8	1370.3	1370.6	1368.8	1366.9
175°	1373.8	1371.0	1368.3	1365.6	1368.3	1371.0	1373.8	1376.5	1376.9	1374.8	1372.8
177.5°	1375.4	1373.2	1371.0	1368.8	1371.0	1373.2	1375.4	1377.6	1378.0	1376.5	1375.1
180°	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8



TEST NUMBER: P333107-927

CATALOG NUMBER: S124RDIW-S1195D1340U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9
2.5°	1501.5	1505.1	1513.1	1522.3	1529.9	1536.4	1541.5	1548.6	1555.1	1564.2	1572.9
5°	1410.5	1419.3	1431.9	1447.2	1466.1	1478.8	1494.5	1508.5	1528.8	1549.0	1568.6
7.5°	1330.5	1340.2	1358.8	1379.8	1402.3	1423.1	1441.9	1466.3	1493.2	1522.7	1555.5
10°	1278.9	1289.7	1311.8	1335.8	1362.4	1382.6	1407.9	1437.0	1467.4	1503.4	1543.9
12.5°	1232.3	1242.6	1269.2	1293.8	1321.4	1343.6	1373.0	1402.6	1443.1	1482.2	1528.2
15°	1141.6	1168.9	1199.2	1228.3	1261.2	1288.4	1323.8	1354.2	1392.7	1447.8	1500.2
17.5°	1040.9	1069.9	1107.6	1152.5	1196.7	1230.3	1266.2	1303.9	1349.9	1406.0	1466.6
20°	982.2	1005.7	1047.4	1097.3	1148.6	1195.4	1228.3	1270.0	1317.5	1378.2	1440.8
22.5°	938.3	958.1	990.7	1040.7	1096.0	1150.3	1192.4	1233.6	1286.1	1346.8	1415.0
25°	872.2	893.7	922.2	956.3	1019.5	1077.1	1132.2	1179.6	1235.2	1295.9	1371.8
27.5°	817.3	836.0	862.1	897.6	940.2	1003.6	1070.3	1124.4	1181.5	1246.7	1322.6
30°	784.9	800.1	821.6	857.6	898.1	955.1	1022.7	1086.0	1143.5	1211.2	1290.3
32.5°	751.0	767.2	788.2	816.7	860.2	908.0	975.7	1045.0	1106.1	1175.3	1252.8
35°	705.8	718.5	737.4	766.6	805.8	847.6	907.6	979.1	1043.6	1117.6	1191.6
37.5°	660.2	675.1	690.1	716.0	748.1	793.0	842.2	915.2	986.7	1054.2	1126.5
40°	634.4	643.3	659.7	680.6	714.7	754.6	800.7	872.2	943.6	1010.7	1083.5
42.5°	605.5	615.4	629.3	650.2	680.8	719.6	764.8	826.6	901.2	966.2	1032.4
45°	565.5	571.2	585.0	602.8	628.0	667.3	709.0	764.1	834.2	896.2	954.4
47.5°	525.0	529.9	538.6	554.8	583.1	614.7	653.7	703.1	764.7	826.6	875.8
50°	497.1	501.5	509.8	525.0	550.2	581.2	619.8	664.1	719.1	778.6	819.7
52.5°	469.3	471.7	479.4	496.6	517.8	548.3	582.9	623.6	675.1	724.5	766.0
55°	425.0	430.7	435.8	448.5	468.7	497.7	528.8	567.4	607.2	649.0	684.4
57.5°	378.8	385.1	392.4	403.5	419.6	446.6	474.5	505.7	539.8	574.4	604.1
60°	348.5	354.2	360.5	373.2	387.7	409.2	439.6	466.8	492.7	524.3	554.1
62.5°	318.6	324.3	331.7	341.8	355.8	376.4	401.6	425.3	452.3	479.8	501.9
65°	274.5	278.9	284.6	294.1	307.4	325.7	346.6	365.0	389.0	409.2	429.4
67.5°	226.1	234.6	242.0	249.7	260.9	278.1	293.1	310.7	327.0	342.1	360.5
70°	194.2	203.7	210.6	218.8	229.6	244.2	258.6	270.7	284.0	298.5	315.0
72.5°	167.4	174.8	180.2	189.0	198.8	212.2	225.8	235.8	246.5	256.5	272.5
75°	132.2	135.4	139.2	146.1	155.0	165.1	175.9	184.7	191.0	199.9	211.3
77.5°	95.0	101.1	103.6	108.5	114.9	121.2	128.3	135.7	141.8	145.0	153.7
80°	72.7	75.3	77.8	84.8	88.6	94.9	99.9	106.9	109.4	112.6	120.8
82.5°	56.6	58.1	59.6	61.5	63.8	70.1	75.2	79.5	82.1	83.3	89.4
85°	32.9	33.5	34.1	34.8	35.4	35.4	37.9	41.1	45.6	45.6	47.5
87.5°	15.9	16.2	15.8	14.9	15.6	15.2	15.3	14.7	15.8	16.8	17.8
90°	24.0	22.6	20.8	18.9	17.1	15.3	13.2	10.6	8.1	5.6	3.1
92.5°	23.1	21.8	20.0	18.1	16.3	14.5	13.5	13.4	13.2	13.1	12.9
95°	24.0	22.6	22.3	22.2	21.9	21.7	25.4	33.2	41.0	48.7	56.5
97.5°	27.3	27.1	52.6	78.1	103.5	129.0	139.3	134.5	129.7	124.8	120.0
100°	41.4	45.2	76.7	108.2	139.7	171.3	185.0	180.9	176.7	172.6	168.5
102.5°	175.9	217.9	222.0	226.1	230.1	234.2	234.8	231.8	228.8	225.8	222.8
105°	322.7	320.6	319.4	318.3	317.2	316.0	314.7	313.4	312.0	310.6	309.3
107.5°	400.7	399.7	398.2	396.6	395.1	393.5	392.4	391.7	391.0	390.3	389.6
110°	453.6	453.1	451.8	450.4	449.0	447.7	446.6	445.9	445.3	444.6	443.9



TEST NUMBER: P333107-927

CATALOG NUMBER: S124RDIW-S1195D1340U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	504.9	504.9	504.3	503.7	503.0	502.3	501.5	500.2	499.0	497.7	496.5
115°	580.0	579.5	579.7	580.0	580.2	580.4	580.2	579.5	578.8	578.1	577.4
117.5°	656.7	656.8	656.2	655.8	655.3	654.7	654.0	653.2	652.2	651.3	650.4
120°	703.3	702.8	703.1	703.3	703.5	703.7	703.4	702.5	701.6	700.6	699.7
122.5°	750.0	749.6	749.3	749.0	748.7	748.4	748.0	747.4	746.9	746.3	745.8
125°	814.4	813.8	814.2	814.7	815.2	815.6	815.4	814.4	813.6	812.6	811.7
127.5°	879.8	880.0	878.9	877.8	876.8	875.8	875.1	874.9	874.6	874.4	874.2
130°	918.9	918.6	917.9	917.2	916.6	915.8	915.4	915.1	915.0	914.7	914.5
132.5°	957.4	957.2	956.3	955.5	954.7	953.8	953.1	952.7	952.3	951.9	951.5
135°	1010.5	1010.0	1009.2	1008.2	1007.3	1006.4	1006.1	1006.3	1006.5	1006.7	1006.9
137.5°	1061.5	1061.0	1060.0	1059.0	1058.0	1057.0	1056.5	1056.4	1056.2	1056.1	1056.1
140°	1092.9	1092.3	1091.8	1091.3	1090.8	1090.4	1090.0	1089.5	1089.0	1088.6	1088.1
142.5°	1122.4	1121.8	1121.6	1121.3	1121.0	1120.7	1120.2	1119.4	1118.6	1117.7	1116.9
145°	1164.4	1164.2	1164.2	1164.2	1164.2	1164.2	1163.8	1163.2	1162.4	1161.7	1161.1
147.5°	1201.1	1200.9	1201.2	1201.4	1201.7	1201.9	1201.3	1200.1	1198.8	1197.5	1196.2
150°	1224.8	1224.8	1225.0	1225.3	1225.5	1225.7	1225.3	1224.5	1223.5	1222.7	1221.7
152.5°	1244.9	1244.5	1244.9	1245.3	1245.8	1246.2	1246.0	1245.2	1244.5	1243.8	1243.1
155°	1271.9	1271.1	1271.7	1272.4	1273.1	1273.7	1274.0	1273.7	1273.5	1273.3	1273.1
157.5°	1295.5	1294.3	1295.1	1295.8	1296.6	1297.4	1297.8	1297.9	1298.1	1298.2	1298.4
160°	1310.4	1309.1	1309.2	1309.5	1309.7	1310.0	1310.4	1311.1	1311.8	1312.5	1313.1
162.5°	1322.7	1321.4	1321.6	1321.8	1322.1	1322.3	1322.9	1323.7	1324.6	1325.4	1326.3
165°	1339.7	1337.8	1337.8	1337.8	1337.8	1337.8	1338.4	1339.5	1340.7	1341.8	1343.0
167.5°	1352.2	1350.1	1350.3	1350.4	1350.6	1350.7	1351.4	1352.6	1353.8	1354.9	1356.1
170°	1360.2	1358.4	1358.1	1357.9	1357.6	1357.5	1358.0	1359.4	1360.7	1362.2	1363.5
172.5°	1365.1	1363.3	1363.0	1362.9	1362.6	1362.4	1362.9	1364.3	1365.7	1367.1	1368.4
175°	1370.7	1368.7	1368.4	1368.2	1367.9	1367.7	1368.3	1369.7	1371.0	1372.4	1373.8
177.5°	1373.6	1372.1	1371.7	1371.4	1371.0	1370.6	1371.1	1372.4	1373.6	1375.0	1376.3
180°	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8



TEST NUMBER: P333107-927

CATALOG NUMBER: S124RDIW-S1195D1340U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9
2.5°	1579.5	1584.0	1589.0	1598.7	1606.8	1610.3	1617.4	1622.5	1621.0	1628.0	1640.1
5°	1585.6	1602.7	1622.3	1642.6	1665.3	1684.3	1699.5	1714.7	1726.7	1741.2	1762.8
7.5°	1584.6	1615.0	1648.0	1684.3	1721.6	1753.9	1783.8	1814.1	1841.0	1870.5	1909.1
10°	1580.6	1621.0	1662.2	1709.6	1757.1	1802.0	1842.5	1880.4	1916.4	1955.0	2003.7
12.5°	1576.0	1622.5	1672.3	1729.3	1788.4	1842.5	1890.0	1944.6	1989.8	2039.6	2095.8
15°	1555.9	1618.5	1686.2	1760.2	1831.1	1903.8	1968.9	2036.0	2098.6	2158.1	2228.9
17.5°	1532.9	1605.1	1685.0	1772.3	1857.5	1945.9	2023.2	2107.7	2171.7	2251.5	2317.3
20°	1514.2	1592.0	1677.4	1775.4	1872.2	1970.2	2055.6	2141.6	2213.7	2294.0	2377.5
22.5°	1491.4	1576.8	1669.3	1770.8	1872.2	1979.3	2073.8	2159.3	2248.6	2339.1	2425.1
25°	1454.7	1543.3	1641.3	1752.6	1869.0	1978.4	2079.6	2185.9	2282.0	2380.0	2457.2
27.5°	1409.7	1502.7	1606.0	1720.9	1840.3	1952.3	2071.6	2184.8	2281.5	2375.8	2443.2
30°	1373.7	1471.8	1571.1	1687.5	1811.4	1931.6	2059.4	2172.6	2274.4	2359.2	2397.1
32.5°	1336.8	1429.8	1532.2	1650.0	1777.0	1906.3	2033.1	2148.8	2243.1	2293.9	2294.9
35°	1272.6	1359.9	1466.1	1581.8	1712.1	1852.5	1980.9	2094.8	2152.4	2156.8	2094.8
37.5°	1202.5	1282.5	1382.8	1498.7	1641.4	1781.1	1912.2	1988.1	2007.4	1943.0	1828.4
40°	1152.4	1226.4	1323.2	1442.1	1583.7	1728.0	1847.5	1903.1	1882.9	1778.5	1650.7
42.5°	1099.8	1168.7	1261.9	1379.3	1521.5	1667.2	1769.1	1798.9	1745.3	1624.8	1475.2
45°	1013.9	1077.1	1169.5	1287.8	1424.3	1561.0	1638.2	1622.9	1533.7	1390.8	1223.2
47.5°	924.5	985.6	1068.7	1178.1	1318.0	1435.8	1488.1	1442.3	1315.4	1158.2	1021.8
50°	865.2	927.9	1004.4	1108.7	1236.5	1350.4	1383.9	1314.3	1173.2	1022.1	896.8
52.5°	807.1	860.5	935.6	1036.4	1158.6	1254.7	1272.6	1192.4	1046.8	911.2	800.2
55°	718.5	767.2	830.4	925.3	1030.9	1112.5	1103.0	1000.0	867.8	752.0	664.7
57.5°	632.9	669.6	728.0	816.9	909.7	964.4	929.8	841.9	718.7	623.9	550.2
60°	576.2	610.4	664.7	742.5	824.1	855.1	826.0	730.6	633.1	546.4	484.5
62.5°	522.5	552.7	599.4	671.7	737.6	756.0	724.8	641.4	553.7	479.7	428.3
65°	444.7	472.5	512.3	563.6	609.1	617.9	597.7	512.3	445.9	383.9	348.5
67.5°	373.9	392.1	423.3	467.5	491.7	496.9	457.8	404.2	345.6	307.5	280.8
70°	326.4	339.0	368.1	392.1	411.8	412.4	376.4	333.4	288.4	257.5	237.8
72.5°	280.4	292.5	314.5	330.9	345.9	341.0	308.0	274.1	237.8	214.4	199.9
75°	216.3	227.0	238.4	246.1	246.1	239.7	215.7	190.4	169.5	155.6	151.1
77.5°	157.2	166.1	169.9	168.7	166.4	156.6	141.4	124.8	117.4	110.8	107.5
80°	123.3	127.1	128.4	125.2	121.4	110.0	99.9	93.0	86.0	83.5	82.2
82.5°	91.4	94.7	91.4	92.4	84.0	74.6	69.1	66.7	63.8	62.7	61.5
85°	48.7	48.1	46.8	43.6	37.9	36.7	36.0	35.4	34.1	34.8	33.5
87.5°	17.8	16.8	15.3	15.3	15.7	15.1	15.9	16.3	16.6	16.4	17.7
90°	5.6	8.1	10.6	13.2	15.3	17.1	18.9	20.8	22.6	24.0	25.3
92.5°	13.1	13.2	13.4	13.5	14.5	16.3	18.1	20.0	21.8	23.1	24.6
95°	48.7	41.0	33.2	25.4	21.7	21.9	22.2	22.3	22.6	24.0	25.3
97.5°	124.8	129.7	134.5	139.3	129.0	103.5	78.1	52.6	27.1	27.3	27.4
100°	172.6	176.7	180.9	185.0	171.3	139.7	108.2	76.7	45.2	41.4	37.5
102.5°	225.8	228.8	231.8	234.8	234.2	230.1	226.1	222.0	217.9	175.9	134.1
105°	310.6	312.0	313.4	314.7	316.0	317.2	318.3	319.4	320.6	322.7	324.7
107.5°	390.3	391.0	391.7	392.4	393.5	395.1	396.6	398.2	399.7	400.7	401.7
110°	444.6	445.3	445.9	446.6	447.7	449.0	450.4	451.8	453.1	453.6	454.1





TEST NUMBER: P333107-927

CATALOG NUMBER: S124RDIW-S1195D1340U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	497.7	499.0	500.2	501.5	502.3	503.0	503.7	504.3	504.9	504.9	504.7
115°	578.1	578.8	579.5	580.2	580.4	580.2	580.0	579.7	579.5	580.0	580.4
117.5°	651.3	652.2	653.2	654.0	654.7	655.3	655.8	656.2	656.8	656.7	656.6
120°	700.6	701.6	702.5	703.4	703.7	703.5	703.3	703.1	702.8	703.3	703.7
122.5°	746.3	746.9	747.4	748.0	748.4	748.7	749.0	749.3	749.6	750.0	750.2
125°	812.6	813.6	814.4	815.4	815.6	815.2	814.7	814.2	813.8	814.4	815.2
127.5°	874.4	874.6	874.9	875.1	875.8	876.8	877.8	878.9	880.0	879.8	879.7
130°	914.7	915.0	915.1	915.4	915.8	916.6	917.2	917.9	918.6	918.9	919.0
132.5°	951.9	952.3	952.7	953.1	953.8	954.7	955.5	956.3	957.2	957.4	957.7
135°	1006.7	1006.5	1006.3	1006.1	1006.4	1007.3	1008.2	1009.2	1010.0	1010.5	1011.0
137.5°	1056.1	1056.2	1056.4	1056.5	1057.0	1058.0	1059.0	1060.0	1061.0	1061.5	1062.0
140°	1088.6	1089.0	1089.5	1090.0	1090.4	1090.8	1091.3	1091.8	1092.3	1092.9	1093.6
142.5°	1117.7	1118.6	1119.4	1120.2	1120.7	1121.0	1121.3	1121.6	1121.8	1122.4	1122.8
145°	1161.7	1162.4	1163.2	1163.8	1164.2	1164.2	1164.2	1164.2	1164.2	1164.4	1164.6
147.5°	1197.5	1198.8	1200.1	1201.3	1201.9	1201.7	1201.4	1201.2	1200.9	1201.1	1201.3
150°	1222.7	1223.5	1224.5	1225.3	1225.7	1225.5	1225.3	1225.0	1224.8	1224.8	1224.8
152.5°	1243.8	1244.5	1245.2	1246.0	1246.2	1245.8	1245.3	1244.9	1244.5	1244.9	1245.2
155°	1273.3	1273.5	1273.7	1274.0	1273.7	1273.1	1272.4	1271.7	1271.1	1271.9	1272.9
157.5°	1298.2	1298.1	1297.9	1297.8	1297.4	1296.6	1295.8	1295.1	1294.3	1295.5	1296.6
160°	1312.5	1311.8	1311.1	1310.4	1310.0	1309.7	1309.5	1309.2	1309.1	1310.4	1311.8
162.5°	1325.4	1324.6	1323.7	1322.9	1322.3	1322.1	1321.8	1321.6	1321.4	1322.7	1324.1
165°	1341.8	1340.7	1339.5	1338.4	1337.8	1337.8	1337.8	1337.8	1337.8	1339.7	1341.5
167.5°	1354.9	1353.8	1352.6	1351.4	1350.7	1350.6	1350.4	1350.3	1350.1	1352.2	1354.2
170°	1362.2	1360.7	1359.4	1358.0	1357.5	1357.6	1357.9	1358.1	1358.4	1360.2	1362.0
172.5°	1367.1	1365.7	1364.3	1362.9	1362.4	1362.6	1362.9	1363.0	1363.3	1365.1	1366.9
175°	1372.4	1371.0	1369.7	1368.3	1367.7	1367.9	1368.2	1368.4	1368.7	1370.7	1372.8
177.5°	1375.0	1373.6	1372.4	1371.1	1370.6	1371.0	1371.4	1371.7	1372.1	1373.6	1375.1
180°	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8



TEST NUMBER: P333107-927

CATALOG NUMBER: S124RDIW-S1195D1340U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9	1569.9
2.5°	1646.7	1648.8	1650.3	1655.3	1655.8	1660.4	1655.8
5°	1783.0	1791.8	1805.8	1819.6	1820.9	1829.8	1813.9
7.5°	1935.8	1956.3	1969.0	1991.5	2000.4	2006.0	1996.9
10°	2041.1	2060.0	2093.5	2110.0	2126.5	2128.9	2121.4
12.5°	2142.8	2172.9	2199.3	2230.4	2229.7	2251.9	2243.8
15°	2278.2	2309.2	2345.9	2380.7	2393.3	2393.3	2403.5
17.5°	2374.9	2431.7	2469.6	2497.0	2526.7	2532.0	2528.4
20°	2440.2	2501.5	2542.0	2577.4	2597.6	2603.3	2603.3
22.5°	2488.7	2540.9	2580.5	2612.3	2629.0	2635.7	2633.7
25°	2522.4	2567.2	2591.3	2600.8	2605.2	2604.0	2591.9
27.5°	2476.3	2474.3	2459.1	2430.0	2408.2	2394.8	2379.6
30°	2388.3	2355.4	2317.5	2275.7	2221.9	2180.8	2168.1
32.5°	2257.2	2183.3	2119.1	2049.5	1991.7	1950.6	1933.4
35°	2003.7	1886.7	1791.2	1707.7	1647.0	1609.1	1596.4
37.5°	1702.9	1589.7	1471.4	1390.4	1340.1	1301.8	1287.5
40°	1511.6	1388.3	1285.2	1209.3	1157.5	1120.1	1119.5
42.5°	1337.0	1219.3	1122.3	1067.6	1011.7	987.1	986.9
45°	1094.8	1000.6	918.4	875.4	841.9	821.6	815.9
47.5°	906.5	828.5	773.8	739.5	712.2	699.3	690.9
50°	800.7	732.5	688.8	659.0	643.9	627.4	626.1
52.5°	712.6	657.5	623.5	599.4	580.1	570.2	570.5
55°	599.0	555.3	531.3	512.9	497.7	490.2	487.0
57.5°	504.6	471.8	454.4	437.5	431.1	425.2	423.5
60°	445.9	423.7	407.3	394.0	384.5	382.6	382.0
62.5°	397.4	374.1	362.8	352.5	345.6	342.7	341.5
65°	327.6	310.5	300.4	292.2	289.7	285.3	284.6
67.5°	264.1	253.9	247.2	241.5	238.1	237.8	237.8
70°	225.1	219.4	213.8	210.6	208.7	207.5	207.5
72.5°	191.8	187.6	182.9	181.3	180.9	179.6	179.1
75°	146.1	141.6	142.3	139.2	136.7	133.5	131.6
77.5°	103.6	100.4	99.8	99.4	97.3	96.9	97.9
80°	80.3	77.2	76.5	77.2	76.5	74.6	74.6
82.5°	61.1	58.5	57.8	57.4	56.8	57.4	56.4
85°	32.9	31.6	31.6	31.6	32.9	32.2	31.6
87.5°	17.0	16.7	17.4	17.0	17.1	16.7	17.3
90°	26.7	28.1	29.0	29.5	29.9	30.3	30.8
92.5°	25.9	27.3	28.0	28.1	28.2	28.3	28.4
95°	26.7	28.1	28.9	29.1	29.3	29.5	29.8
97.5°	27.6	27.6	27.9	28.1	28.3	28.5	28.8
100°	33.6	29.7	27.9	28.1	28.3	28.5	28.8
102.5°	92.2	50.3	29.4	29.5	29.5	29.5	29.6
105°	326.8	328.8	325.7	317.5	309.3	301.0	292.9
107.5°	402.7	403.7	404.6	405.5	406.4	407.3	408.1
110°	454.5	455.0	455.5	456.2	456.9	457.6	458.3



TEST NUMBER: P333107-927

CATALOG NUMBER: S124RDIW-S1195D1340U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	504.6	504.5	504.9	505.8	506.7	507.6	508.4
115°	580.9	581.3	581.5	581.5	581.5	581.5	581.5
117.5°	656.5	656.4	656.3	656.2	656.2	656.1	655.9
120°	704.2	704.6	704.6	704.2	703.7	703.3	702.8
122.5°	750.5	750.8	750.7	750.2	749.7	749.3	748.8
125°	815.9	816.5	817.0	817.2	817.5	817.7	817.9
127.5°	879.6	879.4	879.2	879.1	878.8	878.7	878.5
130°	919.2	919.5	919.6	919.6	919.6	919.6	919.6
132.5°	957.9	958.1	958.1	958.0	957.8	957.6	957.4
135°	1011.4	1011.9	1012.3	1012.8	1013.2	1013.7	1014.2
137.5°	1062.5	1063.0	1063.2	1063.0	1063.0	1062.8	1062.6
140°	1094.3	1095.0	1095.4	1095.7	1095.9	1096.1	1096.4
142.5°	1123.3	1123.9	1124.1	1124.2	1124.2	1124.3	1124.3
145°	1164.8	1165.1	1165.5	1165.9	1166.3	1166.8	1167.3
147.5°	1201.5	1201.7	1201.9	1202.1	1202.4	1202.5	1202.8
150°	1224.8	1224.8	1224.9	1225.1	1225.3	1225.6	1225.8
152.5°	1245.6	1245.9	1246.1	1245.9	1245.8	1245.7	1245.5
155°	1273.7	1274.7	1274.8	1274.1	1273.4	1272.7	1272.1
157.5°	1297.8	1299.0	1299.0	1297.8	1296.6	1295.5	1294.3
160°	1313.1	1314.5	1314.5	1313.1	1311.8	1310.4	1309.1
162.5°	1325.5	1326.8	1326.7	1325.2	1323.7	1322.1	1320.6
165°	1343.3	1345.1	1345.0	1343.0	1340.9	1338.9	1336.8
167.5°	1356.1	1358.2	1358.0	1355.7	1353.4	1351.2	1348.9
170°	1363.8	1365.6	1365.4	1363.2	1360.9	1358.6	1356.3
172.5°	1368.8	1370.6	1370.3	1367.8	1365.3	1362.9	1360.4
175°	1374.8	1376.9	1376.5	1373.8	1371.0	1368.3	1365.6
177.5°	1376.5	1378.0	1377.6	1375.4	1373.2	1371.0	1368.8
180°	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8

(END OF REPORT)