

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332398-840

Luminaire Tested: **S123RDIW-S340D1030U840-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332398-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S340D1030U840-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1030 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5535.7 lumens
Efficiency: N/A
Efficacy: 145.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 38
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332398-840

CATALOG NUMBER: S123RDIW-S340D1030U840-4F0-1E-UDD-A

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270° - - - 135°-315°



TEST NUMBER: P332398-840

CATALOG NUMBER: S123RDIW-S340D1030U840-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	33	33	33	25
1	92	88	85	81	82	79	76	73	61	59	57	45	43	42	30	29	28	21
2	84	77	72	67	75	69	64	60	54	51	48	39	37	36	26	25	24	18
3	77	68	61	56	68	61	55	51	48	44	40	35	33	31	24	22	21	16
4	71	60	53	47	63	54	48	43	42	38	35	31	29	26	21	20	18	14
5	65	54	46	41	57	48	42	37	38	33	30	28	25	23	19	17	16	12
6	60	48	41	35	53	43	37	32	34	29	26	26	22	20	17	16	14	11
7	55	43	36	31	49	39	33	28	31	26	23	23	20	18	16	14	13	10
8	51	39	32	27	45	35	29	25	28	23	20	21	18	16	15	13	11	9
9	47	36	29	24	42	32	26	22	26	21	18	19	16	14	14	12	10	8
10	44	33	26	21	39	30	24	20	24	19	16	18	15	13	13	11	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5916	5916	5916	5916
5°	7052	5942	5232	5942
10°	8805	5908	4726	5908
15°	10336	5846	4310	5846
20°	11535	5756	3956	5756
25°	11351	5662	3739	5662
30°	8158	5574	3515	5574
35°	5447	5460	3369	5460
40°	4013	5323	3219	5323
45°	3367	5083	3073	5083
50°	2971	4767	2869	4767
55°	2607	4406	2586	4406
60°	2321	4060	2370	4060
65°	2038	3691	2203	3691
70°	1599	3361	2014	3361
75°	1406	2936	1838	2936
80°	1227	2492	1810	2492
85°	988	2013	1927	2013



TEST NUMBER: P332398-840

CATALOG NUMBER: S123RDIW-S340D1030U840-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.0	1.0
10°-20°	168.9	3.1
20°-30°	265.3	4.8
30°-40°	276.8	5.0
40°-50°	236.9	4.3
50°-60°	180.5	3.3
60°-70°	115.7	2.1
70°-80°	55.7	1.0
80°-90°	18.6	0.3
90°-100°	49.6	0.9
100°-110°	236.6	4.3
110°-120°	568.2	10.3
120°-130°	723.6	13.1
130°-140°	773.1	14.0
140°-150°	723.0	13.1
150°-160°	583.2	10.5
160°-170°	376.4	6.8
170°-180°	129.7	2.3
0°-30°	488.2	8.8
0°-40°	764.9	13.8
0°-60°	1182.3	21.4
0°-90°	1372.3	24.8
90°-120°	854.5	15.4
90°-150°	3074.2	55.5
90°-180°	4163.0	75.2
0°-180°	5535.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	550	550	550	550	550	
5°	653	550	484	550	653	67
15°	928	525	387	525	928	263
25°	956	477	315	477	956	411
35°	414	416	256	416	414	272
45°	221	334	202	334	221	174
55°	139	235	138	235	139	126
65°	80	145	86	145	80	79
75°	34	71	44	71	34	36
85°	8	16	16	16	8	10
90°	30	1	30	1	30	14
95°	39	62	39	62	39	32
105°	45	302	45	302	45	102
115°	596	567	596	567	596	551
125°	816	799	816	799	816	728
135°	1005	995	1005	995	1005	775
145°	1159	1148	1159	1148	1159	724
155°	1263	1265	1263	1265	1263	582
165°	1331	1334	1331	1334	1331	376
175°	1360	1365	1360	1365	1360	129
180°	1365	1365	1365	1365	1365	



TEST NUMBER: P332398-840

CATALOG NUMBER: S123RDIW-S340D1030U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6
2.5°	585.4	586.1	583.7	583.3	580.5	579.8	579.8	575.7	573.3	570.2	568.3
5°	652.7	656.4	654.5	650.4	643.3	641.6	637.1	630.1	622.1	612.2	607.5
7.5°	736.7	741.8	739.8	733.4	725.9	719.9	707.3	695.6	679.2	664.8	652.5
10°	805.6	800.2	796.0	789.6	782.7	771.7	758.5	740.4	719.5	703.0	684.7
12.5°	857.2	856.3	850.9	844.3	834.8	824.3	808.0	786.0	761.6	737.8	716.8
15°	927.5	928.9	925.3	918.6	904.8	886.3	861.8	852.6	817.8	791.9	766.1
17.5°	976.1	975.8	975.3	965.9	952.0	938.8	916.0	891.9	860.4	823.9	789.1
20°	1007.0	1004.6	1005.1	994.5	984.2	968.9	946.7	911.7	885.9	843.7	807.7
22.5°	1006.2	1005.7	1007.5	1003.9	996.4	984.7	967.2	937.7	904.6	862.1	821.6
25°	955.7	953.8	964.8	968.0	980.0	982.1	976.8	960.7	929.4	885.6	835.5
27.5°	799.8	798.8	819.3	845.1	877.6	902.9	927.4	939.2	929.4	898.0	847.8
30°	656.4	678.5	688.9	726.1	767.5	816.9	860.2	901.3	911.5	897.8	856.7
32.5°	545.0	564.3	573.0	604.8	643.5	701.4	766.3	824.6	865.8	876.2	851.4
35°	414.5	414.8	434.5	448.7	484.4	543.9	607.0	685.1	762.8	821.6	827.7
37.5°	330.8	331.9	344.0	358.0	384.9	416.3	471.8	536.7	626.4	716.7	769.7
40°	285.6	287.7	296.7	310.5	329.8	353.7	396.9	458.1	532.9	633.4	715.5
42.5°	256.6	260.0	264.7	275.4	287.3	309.6	344.6	391.8	459.9	554.9	649.6
45°	221.2	223.1	226.6	231.6	242.4	257.8	281.3	313.2	369.6	446.1	540.9
47.5°	195.1	194.1	197.8	201.8	209.0	219.6	235.4	261.3	301.5	362.9	443.3
50°	177.4	177.1	179.8	182.8	189.7	197.4	210.4	229.8	261.9	312.7	386.4
52.5°	160.9	161.7	163.6	167.3	172.3	178.5	190.2	204.3	231.8	275.6	337.0
55°	138.9	139.6	142.1	144.2	147.7	154.1	161.4	173.2	192.0	222.6	273.2
57.5°	120.2	119.9	122.3	122.9	126.8	132.0	137.6	146.8	160.5	183.2	217.2
60°	107.8	107.0	109.2	110.8	112.9	117.1	121.9	130.8	141.7	158.3	187.5
62.5°	96.4	96.1	97.7	99.4	101.1	104.9	108.9	115.7	124.3	138.4	161.6
65°	80.0	80.7	81.4	82.1	83.0	85.4	89.2	93.9	99.8	109.7	126.3
67.5°	62.9	63.6	63.8	65.2	67.3	68.8	71.1	75.2	79.4	87.7	97.1
70°	50.8	50.6	50.8	51.5	54.1	56.7	59.8	62.8	65.4	71.3	79.3
72.5°	43.6	43.2	43.8	44.0	45.2	45.9	47.9	50.8	54.1	58.1	63.8
75°	33.8	33.8	33.8	33.8	34.8	35.2	36.0	36.7	37.9	39.8	44.0
77.5°	25.0	25.0	25.4	25.7	25.9	26.2	26.6	27.3	27.7	28.7	30.5
80°	19.8	20.0	19.8	20.0	20.0	20.5	20.7	21.4	21.6	22.8	23.5
82.5°	14.8	14.7	14.8	15.1	15.1	15.6	15.7	16.2	16.2	16.8	17.5
85°	8.0	7.6	8.0	7.8	8.3	7.8	8.0	8.5	8.5	8.7	9.7
87.5°	8.0	8.3	7.8	7.9	7.8	7.9	7.7	7.5	7.7	7.3	7.0
90°	30.4	30.0	29.5	29.1	28.6	28.0	27.1	26.2	25.2	24.3	21.4
92.5°	33.6	33.4	33.1	32.8	32.6	31.7	30.3	28.9	27.4	26.0	23.7
95°	38.6	38.6	38.6	38.6	38.6	37.8	36.2	34.6	33.0	31.4	29.0
97.5°	41.8	41.6	41.3	41.1	40.9	39.9	38.1	36.3	34.4	32.6	48.9
100°	42.6	42.4	42.1	41.9	41.7	40.7	38.9	37.1	35.2	33.4	68.7
102.5°	43.4	43.0	42.6	42.2	41.8	44.3	50.0	55.5	61.2	66.8	105.1
105°	44.6	44.1	43.7	43.3	42.8	62.5	102.4	142.4	182.3	222.2	242.5
107.5°	140.2	170.3	200.4	230.4	260.4	290.1	319.4	348.6	377.9	407.2	403.9
110°	278.9	311.1	343.4	375.7	407.9	427.7	435.2	442.6	450.0	457.5	454.9



TEST NUMBER: P332398-840

CATALOG NUMBER: S123RDIW-S340D1030U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	478.6	485.3	492.2	499.0	505.7	509.1	509.0	508.9	508.7	508.6	506.1
115°	596.4	595.5	594.6	593.7	592.8	591.3	589.0	586.7	584.5	582.2	580.2
117.5°	662.6	662.4	662.2	662.0	661.9	660.9	659.0	657.2	655.4	653.6	652.6
120°	708.0	708.0	708.0	708.0	708.0	707.1	705.3	703.5	701.7	699.8	699.2
122.5°	752.7	752.5	752.2	752.0	751.9	751.1	749.9	748.6	747.4	746.1	745.3
125°	815.5	815.1	814.6	814.2	813.7	813.2	812.8	812.3	811.9	811.4	810.5
127.5°	876.0	876.5	876.9	877.3	877.8	877.7	876.9	876.2	875.5	874.7	873.6
130°	914.9	915.3	915.8	916.3	916.8	916.5	915.5	914.7	913.8	912.9	912.0
132.5°	950.6	951.3	951.9	952.5	953.1	953.0	952.1	951.2	950.3	949.4	948.7
135°	1005.2	1005.8	1006.5	1007.2	1007.8	1007.8	1007.2	1006.5	1005.8	1005.2	1004.3
137.5°	1056.5	1056.9	1057.4	1057.8	1058.3	1058.0	1056.9	1055.8	1054.7	1053.7	1053.2
140°	1087.3	1087.8	1088.2	1088.7	1089.1	1088.9	1088.0	1087.1	1086.2	1085.3	1084.6
142.5°	1115.7	1116.4	1117.0	1117.6	1118.2	1118.2	1117.5	1116.8	1116.1	1115.3	1114.7
145°	1159.3	1159.3	1159.3	1159.3	1159.3	1159.1	1158.7	1158.2	1157.8	1157.3	1156.9
147.5°	1191.8	1192.9	1193.9	1195.0	1196.0	1196.3	1195.8	1195.4	1194.9	1194.5	1194.0
150°	1216.2	1216.9	1217.5	1218.2	1218.9	1219.0	1218.5	1218.1	1217.6	1217.2	1216.7
152.5°	1235.7	1236.7	1237.7	1238.7	1239.8	1239.9	1239.1	1238.3	1237.5	1236.7	1236.4
155°	1262.8	1264.1	1265.6	1266.9	1268.2	1268.4	1267.2	1266.1	1265.0	1263.8	1263.6
157.5°	1285.8	1287.5	1289.3	1291.0	1292.7	1292.9	1291.6	1290.3	1288.9	1287.6	1287.8
160°	1300.3	1301.9	1303.5	1305.0	1306.7	1306.8	1305.5	1304.0	1302.7	1301.4	1301.6
162.5°	1314.1	1315.6	1317.0	1318.4	1319.7	1319.7	1318.2	1316.6	1315.0	1313.5	1313.7
165°	1330.8	1332.3	1333.9	1335.5	1337.1	1337.0	1335.1	1333.3	1331.6	1329.8	1330.0
167.5°	1342.7	1344.5	1346.4	1348.2	1350.0	1350.0	1348.2	1346.4	1344.5	1342.7	1342.7
170°	1350.1	1351.8	1353.6	1355.4	1357.3	1357.3	1355.4	1353.6	1351.8	1350.1	1350.1
172.5°	1354.1	1356.0	1358.1	1360.1	1362.0	1362.1	1360.3	1358.6	1356.8	1354.9	1354.7
175°	1360.2	1362.0	1363.8	1365.6	1367.5	1367.6	1365.9	1364.3	1362.8	1361.2	1361.0
177.5°	1362.0	1363.8	1365.6	1367.5	1369.3	1369.4	1368.0	1366.5	1365.1	1363.6	1363.4
180°	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2



TEST NUMBER: P332398-840

CATALOG NUMBER: S123RDIW-S340D1030U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6
2.5°	567.4	566.9	564.3	561.3	557.3	554.7	552.6	551.5	548.1	543.9	541.2
5°	602.6	595.5	587.9	578.8	570.3	561.6	556.2	549.9	542.1	533.4	527.3
7.5°	640.1	626.2	611.4	595.9	580.8	567.1	555.0	544.7	532.4	519.9	511.2
10°	668.9	648.6	627.7	606.3	586.8	568.5	554.3	540.5	525.6	511.3	500.4
12.5°	695.1	668.4	644.3	617.9	593.0	571.1	550.8	534.4	516.5	501.3	489.0
15°	728.2	700.8	671.8	631.7	598.5	570.8	546.0	524.6	503.0	484.2	472.2
17.5°	759.1	718.1	678.8	645.5	602.4	567.7	537.6	512.0	488.2	468.3	453.4
20°	771.9	732.2	689.6	647.0	604.7	565.8	530.8	502.5	477.9	455.2	441.6
22.5°	779.6	734.7	689.7	644.0	599.1	558.7	524.0	492.9	466.2	444.7	427.9
25°	788.6	735.0	685.6	640.5	594.5	550.8	509.6	476.7	447.8	425.0	407.1
27.5°	794.6	731.4	673.1	622.9	576.3	532.8	495.0	460.1	430.7	406.6	387.4
30°	795.7	728.6	663.5	609.2	561.9	521.8	481.8	448.5	417.4	391.7	373.9
32.5°	797.2	721.6	650.5	592.8	544.3	504.7	468.5	436.6	404.8	379.5	361.2
35°	791.0	717.8	630.8	564.4	515.9	477.6	444.9	415.5	384.3	359.7	341.1
37.5°	764.3	702.6	610.4	532.5	481.8	446.4	419.7	394.0	365.4	338.9	321.4
40°	737.4	687.5	594.5	513.1	460.2	423.7	399.7	378.8	351.0	326.3	307.5
42.5°	697.3	666.9	579.5	492.8	435.8	400.6	380.3	360.7	336.4	311.2	293.6
45°	623.7	627.7	548.7	460.4	401.8	366.6	347.5	333.9	312.3	291.5	273.4
47.5°	531.5	568.9	512.5	426.0	366.2	333.1	316.4	304.5	289.8	269.5	253.0
50°	471.3	524.6	483.5	402.8	343.8	310.8	294.4	284.7	272.0	256.0	240.2
52.5°	415.8	473.1	448.5	377.0	319.4	289.3	273.3	265.3	255.2	240.1	225.9
55°	339.0	397.2	391.5	338.1	283.1	256.0	243.8	234.8	228.0	216.7	205.4
57.5°	274.3	329.3	332.2	294.8	251.0	224.2	213.7	206.9	202.5	194.0	183.5
60°	233.4	284.0	293.9	265.6	228.0	204.5	194.1	188.6	185.2	178.3	170.4
62.5°	199.5	242.6	253.8	233.5	206.0	183.9	175.8	170.7	168.2	162.4	155.3
65°	152.7	188.4	199.2	188.0	173.6	156.0	149.4	144.9	142.8	139.6	134.3
67.5°	114.8	140.9	152.8	144.8	139.6	128.5	124.3	121.9	120.0	117.8	113.4
70°	92.2	111.5	123.7	121.7	117.4	111.5	108.5	106.8	104.9	103.0	99.3
72.5°	74.1	87.5	98.9	100.0	96.5	95.3	92.6	91.9	90.8	88.6	86.4
75°	49.2	58.4	66.3	69.4	70.8	72.0	70.8	70.6	70.4	68.5	67.3
77.5°	32.2	37.2	42.2	47.5	49.7	51.2	51.6	52.5	51.8	50.9	50.3
80°	24.7	25.9	29.4	33.8	37.4	38.8	39.8	40.2	40.0	39.8	38.8
82.5°	18.0	18.9	20.6	23.7	26.7	29.0	29.6	29.5	30.0	30.2	29.4
85°	9.7	9.9	10.4	10.8	12.4	15.0	15.8	16.3	16.7	16.7	15.2
87.5°	6.7	6.0	5.8	5.3	5.4	5.0	5.8	6.3	6.9	6.6	7.0
90°	18.5	15.6	12.6	10.0	7.8	5.6	3.2	1.0	3.2	5.6	7.8
92.5°	21.5	19.4	17.2	16.4	17.0	17.6	18.3	18.9	18.3	17.6	17.0
95°	26.5	24.0	21.5	24.9	34.1	43.4	52.6	61.9	52.6	43.4	34.1
97.5°	65.1	81.4	97.6	107.8	111.9	116.0	120.2	124.3	120.2	116.0	111.9
100°	103.8	139.0	174.1	189.5	184.9	180.5	175.9	171.4	175.9	180.5	184.9
102.5°	143.6	182.0	220.4	237.9	234.7	231.5	228.2	225.0	228.2	231.5	234.7
105°	262.7	283.0	303.3	312.1	309.7	307.2	304.8	302.3	304.8	307.2	309.7
107.5°	400.7	397.6	394.4	391.7	389.8	387.8	385.8	383.8	385.8	387.8	389.8
110°	452.5	450.0	447.6	445.4	443.6	441.8	440.0	438.2	440.0	441.8	443.6



TEST NUMBER: P332398-840

CATALOG NUMBER: S123RDIW-S340D1030U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	503.6	501.1	498.7	496.7	495.0	493.3	491.7	490.1	491.7	493.3	495.0
115°	578.1	576.1	574.1	572.4	571.1	569.7	568.4	567.0	568.4	569.7	571.1
117.5°	651.6	650.6	649.4	648.1	646.4	644.8	643.1	641.5	643.1	644.8	646.4
120°	698.5	697.8	697.2	695.8	693.8	691.8	689.7	687.7	689.7	691.8	693.8
122.5°	744.4	743.6	742.7	741.4	739.7	738.1	736.4	734.8	736.4	738.1	739.7
125°	809.6	808.7	807.9	806.5	804.7	802.8	801.1	799.3	801.1	802.8	804.7
127.5°	872.6	871.5	870.4	869.0	867.2	865.4	863.5	861.7	863.5	865.4	867.2
130°	911.1	910.2	909.3	908.0	906.2	904.3	902.5	900.7	902.5	904.3	906.2
132.5°	948.0	947.3	946.5	945.2	943.4	941.6	939.9	938.1	939.9	941.6	943.4
135°	1003.4	1002.5	1001.6	1000.5	999.1	997.7	996.4	995.0	996.4	997.7	999.1
137.5°	1052.7	1052.2	1051.7	1050.6	1048.8	1047.1	1045.4	1043.7	1045.4	1047.1	1048.8
140°	1084.0	1083.3	1082.6	1081.6	1080.3	1078.9	1077.5	1076.2	1077.5	1078.9	1080.3
142.5°	1114.0	1113.3	1112.7	1111.7	1110.2	1108.9	1107.5	1106.2	1107.5	1108.9	1110.2
145°	1156.4	1156.0	1155.5	1154.5	1153.0	1151.3	1149.7	1148.2	1149.7	1151.3	1153.0
147.5°	1193.6	1193.1	1192.7	1191.9	1190.8	1189.8	1188.8	1187.8	1188.8	1189.8	1190.8
150°	1216.3	1215.8	1215.4	1214.8	1214.2	1213.5	1212.7	1212.1	1212.7	1213.5	1214.2
152.5°	1236.1	1235.9	1235.6	1235.3	1235.0	1234.7	1234.4	1234.1	1234.4	1234.7	1235.0
155°	1263.3	1263.1	1262.9	1263.0	1263.5	1263.9	1264.4	1264.9	1264.4	1263.9	1263.5
157.5°	1288.0	1288.3	1288.5	1288.6	1288.7	1288.7	1288.8	1288.8	1288.8	1288.7	1288.7
160°	1301.8	1302.0	1302.2	1302.5	1302.7	1302.9	1303.1	1303.4	1303.1	1302.9	1302.7
162.5°	1314.0	1314.2	1314.4	1314.8	1315.5	1316.1	1316.6	1317.2	1316.6	1316.1	1315.5
165°	1330.2	1330.4	1330.7	1331.1	1331.8	1332.5	1333.1	1333.8	1333.1	1332.5	1331.8
167.5°	1342.7	1342.7	1342.7	1343.2	1344.1	1345.0	1345.9	1346.8	1345.9	1345.0	1344.1
170°	1350.1	1350.1	1350.1	1350.5	1351.4	1352.3	1353.2	1354.1	1353.2	1352.3	1351.4
172.5°	1354.5	1354.3	1354.2	1354.6	1355.7	1356.9	1357.9	1359.0	1357.9	1356.9	1355.7
175°	1360.8	1360.5	1360.3	1360.8	1361.9	1363.0	1364.1	1365.2	1364.1	1363.0	1361.9
177.5°	1363.3	1363.1	1362.9	1363.3	1364.2	1365.1	1365.9	1366.9	1365.9	1365.1	1364.2
180°	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2



TEST NUMBER: P332398-840

CATALOG NUMBER: S123RDIW-S340D1030U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6
2.5°	540.2	537.8	536.0	532.3	529.9	527.3	524.6	526.2	526.0	525.9	525.9
5°	522.1	516.6	511.7	505.3	501.4	496.4	492.7	492.2	493.1	489.9	488.0
7.5°	504.1	496.8	489.7	482.7	475.2	469.3	465.6	463.8	461.5	459.5	457.4
10°	491.5	482.8	475.9	467.3	459.3	452.2	447.8	444.6	443.0	441.4	438.3
12.5°	478.5	470.0	461.3	451.4	443.8	435.7	432.3	428.9	425.8	423.8	419.7
15°	459.5	448.5	439.3	428.9	420.4	412.4	407.8	400.9	400.0	397.6	393.3
17.5°	440.4	428.5	415.8	408.1	398.6	390.2	383.0	380.8	374.1	371.5	367.8
20°	425.4	414.3	404.7	394.6	380.7	372.9	367.3	364.3	358.8	355.5	353.1
22.5°	412.4	401.1	390.0	378.2	366.8	358.0	353.9	349.1	346.2	341.5	339.0
25°	393.8	381.6	368.2	355.5	347.3	340.7	334.1	329.8	325.6	323.5	318.8
27.5°	372.3	359.5	347.0	337.3	327.2	320.7	314.8	311.0	305.9	302.4	299.7
30°	360.4	345.4	334.6	325.9	313.0	306.8	302.4	297.6	293.9	290.1	287.5
32.5°	346.7	333.0	322.8	311.9	302.1	295.3	289.5	285.4	282.2	278.6	276.0
35°	325.2	313.7	303.1	292.3	284.9	278.1	271.2	267.7	264.7	261.4	259.0
37.5°	305.7	294.9	284.8	274.6	265.5	259.9	254.5	251.8	247.6	245.4	243.1
40°	293.7	283.1	272.3	262.4	253.0	248.7	243.8	239.7	236.0	234.3	231.8
42.5°	280.4	269.8	260.7	250.1	242.4	236.6	232.1	227.7	224.9	222.5	221.1
45°	260.9	251.6	242.6	232.0	224.7	219.7	214.6	210.6	208.0	206.3	203.8
47.5°	242.0	232.6	223.5	214.3	207.2	201.6	196.3	193.6	190.2	188.1	186.4
50°	228.2	219.7	210.2	201.7	194.6	188.9	184.7	181.2	178.1	175.5	174.3
52.5°	215.6	206.6	198.2	190.4	182.9	176.5	172.7	169.0	166.6	163.7	162.3
55°	194.8	186.1	179.0	171.3	164.0	158.5	153.9	150.6	148.2	144.9	143.1
57.5°	175.3	167.4	159.1	152.3	144.8	140.3	136.3	131.9	129.0	126.4	124.5
60°	162.1	153.2	145.8	139.6	132.9	127.0	123.5	120.0	116.9	114.3	112.7
62.5°	148.3	140.6	133.6	126.7	120.7	115.5	111.5	108.6	105.8	104.2	102.5
65°	127.2	121.2	114.1	108.5	102.8	99.1	95.7	93.2	91.3	90.1	88.7
67.5°	107.9	102.0	95.8	90.3	86.4	83.6	81.5	79.3	78.3	76.7	75.8
70°	95.3	89.2	83.7	79.5	75.7	73.6	72.2	70.6	69.7	67.8	66.9
72.5°	81.6	77.2	73.2	69.8	66.8	64.8	63.0	61.0	59.5	57.4	56.5
75°	64.2	60.2	57.2	54.8	52.9	50.4	47.8	45.6	44.9	44.2	44.0
77.5°	47.6	45.0	42.8	40.8	38.5	36.7	36.1	35.5	35.4	35.0	35.0
80°	37.4	35.0	33.4	31.1	29.7	29.7	29.7	29.2	29.4	29.4	29.4
82.5°	27.8	25.7	24.7	23.9	23.6	23.8	23.8	23.9	23.7	24.1	23.9
85°	14.3	14.5	15.0	14.8	15.0	15.0	15.6	15.2	15.6	15.0	15.6
87.5°	7.3	8.4	9.1	9.9	10.7	11.1	11.4	11.6	12.0	12.2	12.3
90°	10.0	12.6	15.6	18.5	21.4	24.3	25.2	26.2	27.1	28.0	28.6
92.5°	16.4	17.2	19.4	21.5	23.7	26.0	27.4	28.9	30.3	31.7	32.6
95°	24.9	21.5	24.0	26.5	29.0	31.4	33.0	34.6	36.2	37.8	38.6
97.5°	107.8	97.6	81.4	65.1	48.9	32.6	34.4	36.3	38.1	39.9	40.9
100°	189.5	174.1	139.0	103.8	68.7	33.4	35.2	37.1	38.9	40.7	41.7
102.5°	237.9	220.4	182.0	143.6	105.1	66.8	61.2	55.5	50.0	44.3	41.8
105°	312.1	303.3	283.0	262.7	242.5	222.2	182.3	142.4	102.4	62.5	42.8
107.5°	391.7	394.4	397.6	400.7	403.9	407.2	377.9	348.6	319.4	290.1	260.4
110°	445.4	447.6	450.0	452.5	454.9	457.5	450.0	442.6	435.2	427.7	407.9



TEST NUMBER: P332398-840

CATALOG NUMBER: S123RDIW-S340D1030U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	496.7	498.7	501.1	503.6	506.1	508.6	508.7	508.9	509.0	509.1	505.7
115°	572.4	574.1	576.1	578.1	580.2	582.2	584.5	586.7	589.0	591.3	592.8
117.5°	648.1	649.4	650.6	651.6	652.6	653.6	655.4	657.2	659.0	660.9	661.9
120°	695.8	697.2	697.8	698.5	699.2	699.8	701.7	703.5	705.3	707.1	708.0
122.5°	741.4	742.7	743.6	744.4	745.3	746.1	747.4	748.6	749.9	751.1	751.9
125°	806.5	807.9	808.7	809.6	810.5	811.4	811.9	812.3	812.8	813.2	813.7
127.5°	869.0	870.4	871.5	872.6	873.6	874.7	875.5	876.2	876.9	877.7	877.8
130°	908.0	909.3	910.2	911.1	912.0	912.9	913.8	914.7	915.5	916.5	916.8
132.5°	945.2	946.5	947.3	948.0	948.7	949.4	950.3	951.2	952.1	953.0	953.1
135°	1000.5	1001.6	1002.5	1003.4	1004.3	1005.2	1005.8	1006.5	1007.2	1007.8	1007.8
137.5°	1050.6	1051.7	1052.2	1052.7	1053.2	1053.7	1054.7	1055.8	1056.9	1058.0	1058.3
140°	1081.6	1082.6	1083.3	1084.0	1084.6	1085.3	1086.2	1087.1	1088.0	1088.9	1089.1
142.5°	1111.7	1112.7	1113.3	1114.0	1114.7	1115.3	1116.1	1116.8	1117.5	1118.2	1118.2
145°	1154.5	1155.5	1156.0	1156.4	1156.9	1157.3	1157.8	1158.2	1158.7	1159.1	1159.3
147.5°	1191.9	1192.7	1193.1	1193.6	1194.0	1194.5	1194.9	1195.4	1195.8	1196.3	1196.0
150°	1214.8	1215.4	1215.8	1216.3	1216.7	1217.2	1217.6	1218.1	1218.5	1219.0	1218.9
152.5°	1235.3	1235.6	1235.9	1236.1	1236.4	1236.7	1237.5	1238.3	1239.1	1239.9	1239.8
155°	1263.0	1262.9	1263.1	1263.3	1263.6	1263.8	1265.0	1266.1	1267.2	1268.4	1268.2
157.5°	1288.6	1288.5	1288.3	1288.0	1287.8	1287.6	1288.9	1290.3	1291.6	1292.9	1292.7
160°	1302.5	1302.2	1302.0	1301.8	1301.6	1301.4	1302.7	1304.0	1305.5	1306.8	1306.7
162.5°	1314.8	1314.4	1314.2	1314.0	1313.7	1313.5	1315.0	1316.6	1318.2	1319.7	1319.7
165°	1331.1	1330.7	1330.4	1330.2	1330.0	1329.8	1331.6	1333.3	1335.1	1337.0	1337.1
167.5°	1343.2	1342.7	1342.7	1342.7	1342.7	1342.7	1344.5	1346.4	1348.2	1350.0	1350.0
170°	1350.5	1350.1	1350.1	1350.1	1350.1	1350.1	1351.8	1353.6	1355.4	1357.3	1357.3
172.5°	1354.6	1354.2	1354.3	1354.5	1354.7	1354.9	1356.8	1358.6	1360.3	1362.1	1362.0
175°	1360.8	1360.3	1360.5	1360.8	1361.0	1361.2	1362.8	1364.3	1365.9	1367.6	1367.5
177.5°	1363.3	1362.9	1363.1	1363.3	1363.4	1363.6	1365.1	1366.5	1368.0	1369.4	1369.3
180°	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2



TEST NUMBER: P332398-840

CATALOG NUMBER: S123RDIW-S340D1030U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6
2.5°	523.6	523.4	523.6	522.9	523.6	523.4	523.6	525.9	525.9	526.0	526.2
5°	487.3	487.1	486.4	484.2	486.4	487.1	487.3	488.0	489.9	493.1	492.2
7.5°	455.4	455.1	453.1	453.1	453.1	455.1	455.4	457.4	459.5	461.5	463.8
10°	436.7	436.9	434.0	432.4	434.0	436.9	436.7	438.3	441.4	443.0	444.6
12.5°	418.4	417.4	415.1	413.2	415.1	417.4	418.4	419.7	423.8	425.8	428.9
15°	394.4	391.9	386.4	386.8	386.4	391.9	394.4	393.3	397.6	400.0	400.9
17.5°	366.0	364.3	364.2	360.8	364.2	364.3	366.0	367.8	371.5	374.1	380.8
20°	349.4	348.2	348.7	345.4	348.7	348.2	349.4	353.1	355.5	358.8	364.3
22.5°	336.4	335.2	333.3	332.2	333.3	335.2	336.4	339.0	341.5	346.2	349.1
25°	317.4	315.5	313.7	314.8	313.7	315.5	317.4	318.8	323.5	325.6	329.8
27.5°	298.4	297.0	295.1	294.9	295.1	297.0	298.4	299.7	302.4	305.9	311.0
30°	286.3	284.9	284.0	282.8	284.0	284.9	286.3	287.5	290.1	293.9	297.6
32.5°	274.1	273.8	272.2	271.9	272.2	273.8	274.1	276.0	278.6	282.2	285.4
35°	258.1	256.7	256.2	256.4	256.2	256.7	258.1	259.0	261.4	264.7	267.7
37.5°	242.9	241.1	240.1	239.3	240.1	241.1	242.9	243.1	245.4	247.6	251.8
40°	232.0	230.1	229.6	229.1	229.6	230.1	232.0	231.8	234.3	236.0	239.7
42.5°	219.7	219.0	218.7	217.8	218.7	219.0	219.7	221.1	222.5	224.9	227.7
45°	203.1	202.8	201.4	201.9	201.4	202.8	203.1	203.8	206.3	208.0	210.6
47.5°	185.4	184.4	183.4	184.1	183.4	184.4	185.4	186.4	188.1	190.2	193.6
50°	173.4	172.9	170.8	171.3	170.8	172.9	173.4	174.3	175.5	178.1	181.2
52.5°	161.4	159.6	158.8	158.4	158.8	159.6	161.4	162.3	163.7	166.6	169.0
55°	141.4	139.3	138.4	137.8	138.4	139.3	141.4	143.1	144.9	148.2	150.6
57.5°	121.8	121.3	120.5	121.0	120.5	121.3	121.8	124.5	126.4	129.0	131.9
60°	110.4	110.4	110.4	110.1	110.4	110.4	110.4	112.7	114.3	116.9	120.0
62.5°	101.5	100.9	100.8	101.1	100.8	100.9	101.5	102.5	104.2	105.8	108.6
65°	88.0	87.8	86.8	86.5	86.8	87.8	88.0	88.7	90.1	91.3	93.2
67.5°	75.2	74.4	74.1	73.8	74.1	74.4	75.2	75.8	76.7	78.3	79.3
70°	65.6	65.1	63.7	64.0	63.7	65.1	65.6	66.9	67.8	69.7	70.6
72.5°	55.3	54.8	54.5	54.2	54.5	54.8	55.3	56.5	57.4	59.5	61.0
75°	43.7	43.5	43.3	44.2	43.3	43.5	43.7	44.0	44.2	44.9	45.6
77.5°	35.0	35.0	35.2	34.8	35.2	35.0	35.0	35.0	35.0	35.4	35.5
80°	29.4	29.4	29.2	29.2	29.2	29.4	29.4	29.4	29.4	29.4	29.2
82.5°	23.5	23.7	23.9	23.5	23.9	23.7	23.5	23.9	24.1	23.7	23.9
85°	15.6	15.2	15.8	15.6	15.8	15.2	15.6	15.6	15.0	15.6	15.2
87.5°	12.8	12.5	12.6	12.8	12.6	12.5	12.8	12.3	12.2	12.0	11.6
90°	29.1	29.5	30.0	30.4	30.0	29.5	29.1	28.6	28.0	27.1	26.2
92.5°	32.8	33.1	33.4	33.6	33.4	33.1	32.8	32.6	31.7	30.3	28.9
95°	38.6	38.6	38.6	38.6	38.6	38.6	38.6	38.6	37.8	36.2	34.6
97.5°	41.1	41.3	41.6	41.8	41.6	41.3	41.1	40.9	39.9	38.1	36.3
100°	41.9	42.1	42.4	42.6	42.4	42.1	41.9	41.7	40.7	38.9	37.1
102.5°	42.2	42.6	43.0	43.4	43.0	42.6	42.2	41.8	44.3	50.0	55.5
105°	43.3	43.7	44.1	44.6	44.1	43.7	43.3	42.8	62.5	102.4	142.4
107.5°	230.4	200.4	170.3	140.2	170.3	200.4	230.4	260.4	290.1	319.4	348.6
110°	375.7	343.4	311.1	278.9	311.1	343.4	375.7	407.9	427.7	435.2	442.6



TEST NUMBER: P332398-840

CATALOG NUMBER: S123RDIW-S340D1030U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	499.0	492.2	485.3	478.6	485.3	492.2	499.0	505.7	509.1	509.0	508.9
115°	593.7	594.6	595.5	596.4	595.5	594.6	593.7	592.8	591.3	589.0	586.7
117.5°	662.0	662.2	662.4	662.6	662.4	662.2	662.0	661.9	660.9	659.0	657.2
120°	708.0	708.0	708.0	708.0	708.0	708.0	708.0	708.0	707.1	705.3	703.5
122.5°	752.0	752.2	752.5	752.7	752.5	752.2	752.0	751.9	751.1	749.9	748.6
125°	814.2	814.6	815.1	815.5	815.1	814.6	814.2	813.7	813.2	812.8	812.3
127.5°	877.3	876.9	876.5	876.0	876.5	876.9	877.3	877.8	877.7	876.9	876.2
130°	916.3	915.8	915.3	914.9	915.3	915.8	916.3	916.8	916.5	915.5	914.7
132.5°	952.5	951.9	951.3	950.6	951.3	951.9	952.5	953.1	953.0	952.1	951.2
135°	1007.2	1006.5	1005.8	1005.2	1005.8	1006.5	1007.2	1007.8	1007.8	1007.2	1006.5
137.5°	1057.8	1057.4	1056.9	1056.5	1056.9	1057.4	1057.8	1058.3	1058.0	1056.9	1055.8
140°	1088.7	1088.2	1087.8	1087.3	1087.8	1088.2	1088.7	1089.1	1088.9	1088.0	1087.1
142.5°	1117.6	1117.0	1116.4	1115.7	1116.4	1117.0	1117.6	1118.2	1118.2	1117.5	1116.8
145°	1159.3	1159.3	1159.3	1159.3	1159.3	1159.3	1159.3	1159.3	1159.1	1158.7	1158.2
147.5°	1195.0	1193.9	1192.9	1191.8	1192.9	1193.9	1195.0	1196.0	1196.3	1195.8	1195.4
150°	1218.2	1217.5	1216.9	1216.2	1216.9	1217.5	1218.2	1218.9	1219.0	1218.5	1218.1
152.5°	1238.7	1237.7	1236.7	1235.7	1236.7	1237.7	1238.7	1239.8	1239.9	1239.1	1238.3
155°	1266.9	1265.6	1264.1	1262.8	1264.1	1265.6	1266.9	1268.2	1268.4	1267.2	1266.1
157.5°	1291.0	1289.3	1287.5	1285.8	1287.5	1289.3	1291.0	1292.7	1292.9	1291.6	1290.3
160°	1305.0	1303.5	1301.9	1300.3	1301.9	1303.5	1305.0	1306.7	1306.8	1305.5	1304.0
162.5°	1318.4	1317.0	1315.6	1314.1	1315.6	1317.0	1318.4	1319.7	1319.7	1318.2	1316.6
165°	1335.5	1333.9	1332.3	1330.8	1332.3	1333.9	1335.5	1337.1	1337.0	1335.1	1333.3
167.5°	1348.2	1346.4	1344.5	1342.7	1344.5	1346.4	1348.2	1350.0	1350.0	1348.2	1346.4
170°	1355.4	1353.6	1351.8	1350.1	1351.8	1353.6	1355.4	1357.3	1357.3	1355.4	1353.6
172.5°	1360.1	1358.1	1356.0	1354.1	1356.0	1358.1	1360.1	1362.0	1362.1	1360.3	1358.6
175°	1365.6	1363.8	1362.0	1360.2	1362.0	1363.8	1365.6	1367.5	1367.6	1365.9	1364.3
177.5°	1367.5	1365.6	1363.8	1362.0	1363.8	1365.6	1367.5	1369.3	1369.4	1368.0	1366.5
180°	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2



TEST NUMBER: P332398-840

CATALOG NUMBER: S123RDIW-S340D1030U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6
2.5°	524.6	527.3	529.9	532.3	536.0	537.8	540.2	541.2	543.9	548.1	551.5
5°	492.7	496.4	501.4	505.3	511.7	516.6	522.1	527.3	533.4	542.1	549.9
7.5°	465.6	469.3	475.2	482.7	489.7	496.8	504.1	511.2	519.9	532.4	544.7
10°	447.8	452.2	459.3	467.3	475.9	482.8	491.5	500.4	511.3	525.6	540.5
12.5°	432.3	435.7	443.8	451.4	461.3	470.0	478.5	489.0	501.3	516.5	534.4
15°	407.8	412.4	420.4	428.9	439.3	448.5	459.5	472.2	484.2	503.0	524.6
17.5°	383.0	390.2	398.6	408.1	415.8	428.5	440.4	453.4	468.3	488.2	512.0
20°	367.3	372.9	380.7	394.6	404.7	414.3	425.4	441.6	455.2	477.9	502.5
22.5°	353.9	358.0	366.8	378.2	390.0	401.1	412.4	427.9	444.7	466.2	492.9
25°	334.1	340.7	347.3	355.5	368.2	381.6	393.8	407.1	425.0	447.8	476.7
27.5°	314.8	320.7	327.2	337.3	347.0	359.5	372.3	387.4	406.6	430.7	460.1
30°	302.4	306.8	313.0	325.9	334.6	345.4	360.4	373.9	391.7	417.4	448.5
32.5°	289.5	295.3	302.1	311.9	322.8	333.0	346.7	361.2	379.5	404.8	436.6
35°	271.2	278.1	284.9	292.3	303.1	313.7	325.2	341.1	359.7	384.3	415.5
37.5°	254.5	259.9	265.5	274.6	284.8	294.9	305.7	321.4	338.9	365.4	394.0
40°	243.8	248.7	253.0	262.4	272.3	283.1	293.7	307.5	326.3	351.0	378.8
42.5°	232.1	236.6	242.4	250.1	260.7	269.8	280.4	293.6	311.2	336.4	360.7
45°	214.6	219.7	224.7	232.0	242.6	251.6	260.9	273.4	291.5	312.3	333.9
47.5°	196.3	201.6	207.2	214.3	223.5	232.6	242.0	253.0	269.5	289.8	304.5
50°	184.7	188.9	194.6	201.7	210.2	219.7	228.2	240.2	256.0	272.0	284.7
52.5°	172.7	176.5	182.9	190.4	198.2	206.6	215.6	225.9	240.1	255.2	265.3
55°	153.9	158.5	164.0	171.3	179.0	186.1	194.8	205.4	216.7	228.0	234.8
57.5°	136.3	140.3	144.8	152.3	159.1	167.4	175.3	183.5	194.0	202.5	206.9
60°	123.5	127.0	132.9	139.6	145.8	153.2	162.1	170.4	178.3	185.2	188.6
62.5°	111.5	115.5	120.7	126.7	133.6	140.6	148.3	155.3	162.4	168.2	170.7
65°	95.7	99.1	102.8	108.5	114.1	121.2	127.2	134.3	139.6	142.8	144.9
67.5°	81.5	83.6	86.4	90.3	95.8	102.0	107.9	113.4	117.8	120.0	121.9
70°	72.2	73.6	75.7	79.5	83.7	89.2	95.3	99.3	103.0	104.9	106.8
72.5°	63.0	64.8	66.8	69.8	73.2	77.2	81.6	86.4	88.6	90.8	91.9
75°	47.8	50.4	52.9	54.8	57.2	60.2	64.2	67.3	68.5	70.4	70.6
77.5°	36.1	36.7	38.5	40.8	42.8	45.0	47.6	50.3	50.9	51.8	52.5
80°	29.7	29.7	29.7	31.1	33.4	35.0	37.4	38.8	39.8	40.0	40.2
82.5°	23.8	23.8	23.6	23.9	24.7	25.7	27.8	29.4	30.2	30.0	29.5
85°	15.6	15.0	15.0	14.8	15.0	14.5	14.3	15.2	16.7	16.7	16.3
87.5°	11.4	11.1	10.7	9.9	9.1	8.4	7.3	7.0	6.6	6.9	6.3
90°	25.2	24.3	21.4	18.5	15.6	12.6	10.0	7.8	5.6	3.2	1.0
92.5°	27.4	26.0	23.7	21.5	19.4	17.2	16.4	17.0	17.6	18.3	18.9
95°	33.0	31.4	29.0	26.5	24.0	21.5	24.9	34.1	43.4	52.6	61.9
97.5°	34.4	32.6	48.9	65.1	81.4	97.6	107.8	111.9	116.0	120.2	124.3
100°	35.2	33.4	68.7	103.8	139.0	174.1	189.5	184.9	180.5	175.9	171.4
102.5°	61.2	66.8	105.1	143.6	182.0	220.4	237.9	234.7	231.5	228.2	225.0
105°	182.3	222.2	242.5	262.7	283.0	303.3	312.1	309.7	307.2	304.8	302.3
107.5°	377.9	407.2	403.9	400.7	397.6	394.4	391.7	389.8	387.8	385.8	383.8
110°	450.0	457.5	454.9	452.5	450.0	447.6	445.4	443.6	441.8	440.0	438.2



TEST NUMBER: P332398-840

CATALOG NUMBER: S123RDIW-S340D1030U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	508.7	508.6	506.1	503.6	501.1	498.7	496.7	495.0	493.3	491.7	490.1
115°	584.5	582.2	580.2	578.1	576.1	574.1	572.4	571.1	569.7	568.4	567.0
117.5°	655.4	653.6	652.6	651.6	650.6	649.4	648.1	646.4	644.8	643.1	641.5
120°	701.7	699.8	699.2	698.5	697.8	697.2	695.8	693.8	691.8	689.7	687.7
122.5°	747.4	746.1	745.3	744.4	743.6	742.7	741.4	739.7	738.1	736.4	734.8
125°	811.9	811.4	810.5	809.6	808.7	807.9	806.5	804.7	802.8	801.1	799.3
127.5°	875.5	874.7	873.6	872.6	871.5	870.4	869.0	867.2	865.4	863.5	861.7
130°	913.8	912.9	912.0	911.1	910.2	909.3	908.0	906.2	904.3	902.5	900.7
132.5°	950.3	949.4	948.7	948.0	947.3	946.5	945.2	943.4	941.6	939.9	938.1
135°	1005.8	1005.2	1004.3	1003.4	1002.5	1001.6	1000.5	999.1	997.7	996.4	995.0
137.5°	1054.7	1053.7	1053.2	1052.7	1052.2	1051.7	1050.6	1048.8	1047.1	1045.4	1043.7
140°	1086.2	1085.3	1084.6	1084.0	1083.3	1082.6	1081.6	1080.3	1078.9	1077.5	1076.2
142.5°	1116.1	1115.3	1114.7	1114.0	1113.3	1112.7	1111.7	1110.2	1108.9	1107.5	1106.2
145°	1157.8	1157.3	1156.9	1156.4	1156.0	1155.5	1154.5	1153.0	1151.3	1149.7	1148.2
147.5°	1194.9	1194.5	1194.0	1193.6	1193.1	1192.7	1191.9	1190.8	1189.8	1188.8	1187.8
150°	1217.6	1217.2	1216.7	1216.3	1215.8	1215.4	1214.8	1214.2	1213.5	1212.7	1212.1
152.5°	1237.5	1236.7	1236.4	1236.1	1235.9	1235.6	1235.3	1235.0	1234.7	1234.4	1234.1
155°	1265.0	1263.8	1263.6	1263.3	1263.1	1262.9	1263.0	1263.5	1263.9	1264.4	1264.9
157.5°	1288.9	1287.6	1287.8	1288.0	1288.3	1288.5	1288.6	1288.7	1288.7	1288.8	1288.8
160°	1302.7	1301.4	1301.6	1301.8	1302.0	1302.2	1302.5	1302.7	1302.9	1303.1	1303.4
162.5°	1315.0	1313.5	1313.7	1314.0	1314.2	1314.4	1314.8	1315.5	1316.1	1316.6	1317.2
165°	1331.6	1329.8	1330.0	1330.2	1330.4	1330.7	1331.1	1331.8	1332.5	1333.1	1333.8
167.5°	1344.5	1342.7	1342.7	1342.7	1342.7	1342.7	1343.2	1344.1	1345.0	1345.9	1346.8
170°	1351.8	1350.1	1350.1	1350.1	1350.1	1350.1	1350.5	1351.4	1352.3	1353.2	1354.1
172.5°	1356.8	1354.9	1354.7	1354.5	1354.3	1354.2	1354.6	1355.7	1356.9	1357.9	1359.0
175°	1362.8	1361.2	1361.0	1360.8	1360.5	1360.3	1360.8	1361.9	1363.0	1364.1	1365.2
177.5°	1365.1	1363.6	1363.4	1363.3	1363.1	1362.9	1363.3	1364.2	1365.1	1365.9	1366.9
180°	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2



TEST NUMBER: P332398-840

CATALOG NUMBER: S123RDIW-S340D1030U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6	549.6
2.5°	552.6	554.7	557.3	561.3	564.3	566.9	567.4	568.3	570.2	573.3	575.7
5°	556.2	561.6	570.3	578.8	587.9	595.5	602.6	607.5	612.2	622.1	630.1
7.5°	555.0	567.1	580.8	595.9	611.4	626.2	640.1	652.5	664.8	679.2	695.6
10°	554.3	568.5	586.8	606.3	627.7	648.6	668.9	684.7	703.0	719.5	740.4
12.5°	550.8	571.1	593.0	617.9	644.3	668.4	695.1	716.8	737.8	761.6	786.0
15°	546.0	570.8	598.5	631.7	671.8	700.8	728.2	766.1	791.9	817.8	852.6
17.5°	537.6	567.7	602.4	645.5	678.8	718.1	759.1	789.1	823.9	860.4	891.9
20°	530.8	565.8	604.7	647.0	689.6	732.2	771.9	807.7	843.7	885.9	911.7
22.5°	524.0	558.7	599.1	644.0	689.7	734.7	779.6	821.6	862.1	904.6	937.7
25°	509.6	550.8	594.5	640.5	685.6	735.0	788.6	835.5	885.6	929.4	960.7
27.5°	495.0	532.8	576.3	622.9	673.1	731.4	794.6	847.8	898.0	929.4	939.2
30°	481.8	521.8	561.9	609.2	663.5	728.6	795.7	856.7	897.8	911.5	901.3
32.5°	468.5	504.7	544.3	592.8	650.5	721.6	797.2	851.4	876.2	865.8	824.6
35°	444.9	477.6	515.9	564.4	630.8	717.8	791.0	827.7	821.6	762.8	685.1
37.5°	419.7	446.4	481.8	532.5	610.4	702.6	764.3	769.7	716.7	626.4	536.7
40°	399.7	423.7	460.2	513.1	594.5	687.5	737.4	715.5	633.4	532.9	458.1
42.5°	380.3	400.6	435.8	492.8	579.5	666.9	697.3	649.6	554.9	459.9	391.8
45°	347.5	366.6	401.8	460.4	548.7	627.7	623.7	540.9	446.1	369.6	313.2
47.5°	316.4	333.1	366.2	426.0	512.5	568.9	531.5	443.3	362.9	301.5	261.3
50°	294.4	310.8	343.8	402.8	483.5	524.6	471.3	386.4	312.7	261.9	229.8
52.5°	273.3	289.3	319.4	377.0	448.5	473.1	415.8	337.0	275.6	231.8	204.3
55°	243.8	256.0	283.1	338.1	391.5	397.2	339.0	273.2	222.6	192.0	173.2
57.5°	213.7	224.2	251.0	294.8	332.2	329.3	274.3	217.2	183.2	160.5	146.8
60°	194.1	204.5	228.0	265.6	293.9	284.0	233.4	187.5	158.3	141.7	130.8
62.5°	175.8	183.9	206.0	233.5	253.8	242.6	199.5	161.6	138.4	124.3	115.7
65°	149.4	156.0	173.6	188.0	199.2	188.4	152.7	126.3	109.7	99.8	93.9
67.5°	124.3	128.5	139.6	144.8	152.8	140.9	114.8	97.1	87.7	79.4	75.2
70°	108.5	111.5	117.4	121.7	123.7	111.5	92.2	79.3	71.3	65.4	62.8
72.5°	92.6	95.3	96.5	100.0	98.9	87.5	74.1	63.8	58.1	54.1	50.8
75°	70.8	72.0	70.8	69.4	66.3	58.4	49.2	44.0	39.8	37.9	36.7
77.5°	51.6	51.2	49.7	47.5	42.2	37.2	32.2	30.5	28.7	27.7	27.3
80°	39.8	38.8	37.4	33.8	29.4	25.9	24.7	23.5	22.8	21.6	21.4
82.5°	29.6	29.0	26.7	23.7	20.6	18.9	18.0	17.5	16.8	16.2	16.2
85°	15.8	15.0	12.4	10.8	10.4	9.9	9.7	9.7	8.7	8.5	8.5
87.5°	5.8	5.0	5.4	5.3	5.8	6.0	6.7	7.0	7.3	7.7	7.5
90°	3.2	5.6	7.8	10.0	12.6	15.6	18.5	21.4	24.3	25.2	26.2
92.5°	18.3	17.6	17.0	16.4	17.2	19.4	21.5	23.7	26.0	27.4	28.9
95°	52.6	43.4	34.1	24.9	21.5	24.0	26.5	29.0	31.4	33.0	34.6
97.5°	120.2	116.0	111.9	107.8	97.6	81.4	65.1	48.9	32.6	34.4	36.3
100°	175.9	180.5	184.9	189.5	174.1	139.0	103.8	68.7	33.4	35.2	37.1
102.5°	228.2	231.5	234.7	237.9	220.4	182.0	143.6	105.1	66.8	61.2	55.5
105°	304.8	307.2	309.7	312.1	303.3	283.0	262.7	242.5	222.2	182.3	142.4
107.5°	385.8	387.8	389.8	391.7	394.4	397.6	400.7	403.9	407.2	377.9	348.6
110°	440.0	441.8	443.6	445.4	447.6	450.0	452.5	454.9	457.5	450.0	442.6



TEST NUMBER: P332398-840

CATALOG NUMBER: S123RDIW-S340D1030U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	491.7	493.3	495.0	496.7	498.7	501.1	503.6	506.1	508.6	508.7	508.9
115°	568.4	569.7	571.1	572.4	574.1	576.1	578.1	580.2	582.2	584.5	586.7
117.5°	643.1	644.8	646.4	648.1	649.4	650.6	651.6	652.6	653.6	655.4	657.2
120°	689.7	691.8	693.8	695.8	697.2	697.8	698.5	699.2	699.8	701.7	703.5
122.5°	736.4	738.1	739.7	741.4	742.7	743.6	744.4	745.3	746.1	747.4	748.6
125°	801.1	802.8	804.7	806.5	807.9	808.7	809.6	810.5	811.4	811.9	812.3
127.5°	863.5	865.4	867.2	869.0	870.4	871.5	872.6	873.6	874.7	875.5	876.2
130°	902.5	904.3	906.2	908.0	909.3	910.2	911.1	912.0	912.9	913.8	914.7
132.5°	939.9	941.6	943.4	945.2	946.5	947.3	948.0	948.7	949.4	950.3	951.2
135°	996.4	997.7	999.1	1000.5	1001.6	1002.5	1003.4	1004.3	1005.2	1005.8	1006.5
137.5°	1045.4	1047.1	1048.8	1050.6	1051.7	1052.2	1052.7	1053.2	1053.7	1054.7	1055.8
140°	1077.5	1078.9	1080.3	1081.6	1082.6	1083.3	1084.0	1084.6	1085.3	1086.2	1087.1
142.5°	1107.5	1108.9	1110.2	1111.7	1112.7	1113.3	1114.0	1114.7	1115.3	1116.1	1116.8
145°	1149.7	1151.3	1153.0	1154.5	1155.5	1156.0	1156.4	1156.9	1157.3	1157.8	1158.2
147.5°	1188.8	1189.8	1190.8	1191.9	1192.7	1193.1	1193.6	1194.0	1194.5	1194.9	1195.4
150°	1212.7	1213.5	1214.2	1214.8	1215.4	1215.8	1216.3	1216.7	1217.2	1217.6	1218.1
152.5°	1234.4	1234.7	1235.0	1235.3	1235.6	1235.9	1236.1	1236.4	1236.7	1237.5	1238.3
155°	1264.4	1263.9	1263.5	1263.0	1262.9	1263.1	1263.3	1263.6	1263.8	1265.0	1266.1
157.5°	1288.8	1288.7	1288.7	1288.6	1288.5	1288.3	1288.0	1287.8	1287.6	1288.9	1290.3
160°	1303.1	1302.9	1302.7	1302.5	1302.2	1302.0	1301.8	1301.6	1301.4	1302.7	1304.0
162.5°	1316.6	1316.1	1315.5	1314.8	1314.4	1314.2	1314.0	1313.7	1313.5	1315.0	1316.6
165°	1333.1	1332.5	1331.8	1331.1	1330.7	1330.4	1330.2	1330.0	1329.8	1331.6	1333.3
167.5°	1345.9	1345.0	1344.1	1343.2	1342.7	1342.7	1342.7	1342.7	1342.7	1344.5	1346.4
170°	1353.2	1352.3	1351.4	1350.5	1350.1	1350.1	1350.1	1350.1	1350.1	1351.8	1353.6
172.5°	1357.9	1356.9	1355.7	1354.6	1354.2	1354.3	1354.5	1354.7	1354.9	1356.8	1358.6
175°	1364.1	1363.0	1361.9	1360.8	1360.3	1360.5	1360.8	1361.0	1361.2	1362.8	1364.3
177.5°	1365.9	1365.1	1364.2	1363.3	1362.9	1363.1	1363.3	1363.4	1363.6	1365.1	1366.5
180°	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2



TEST NUMBER: P332398-840

CATALOG NUMBER: S123RDIW-S340D1030U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	549.6	549.6	549.6	549.6	549.6	549.6	549.6
2.5°	579.8	579.8	580.5	583.3	583.7	586.1	585.4
5°	637.1	641.6	643.3	650.4	654.5	656.4	652.7
7.5°	707.3	719.9	725.9	733.4	739.8	741.8	736.7
10°	758.5	771.7	782.7	789.6	796.0	800.2	805.6
12.5°	808.0	824.3	834.8	844.3	850.9	856.3	857.2
15°	861.8	886.3	904.8	918.6	925.3	928.9	927.5
17.5°	916.0	938.8	952.0	965.9	975.3	975.8	976.1
20°	946.7	968.9	984.2	994.5	1005.1	1004.6	1007.0
22.5°	967.2	984.7	996.4	1003.9	1007.5	1005.7	1006.2
25°	976.8	982.1	980.0	968.0	964.8	953.8	955.7
27.5°	927.4	902.9	877.6	845.1	819.3	798.8	799.8
30°	860.2	816.9	767.5	726.1	688.9	678.5	656.4
32.5°	766.3	701.4	643.5	604.8	573.0	564.3	545.0
35°	607.0	543.9	484.4	448.7	434.5	414.8	414.5
37.5°	471.8	416.3	384.9	358.0	344.0	331.9	330.8
40°	396.9	353.7	329.8	310.5	296.7	287.7	285.6
42.5°	344.6	309.6	287.3	275.4	264.7	260.0	256.6
45°	281.3	257.8	242.4	231.6	226.6	223.1	221.2
47.5°	235.4	219.6	209.0	201.8	197.8	194.1	195.1
50°	210.4	197.4	189.7	182.8	179.8	177.1	177.4
52.5°	190.2	178.5	172.3	167.3	163.6	161.7	160.9
55°	161.4	154.1	147.7	144.2	142.1	139.6	138.9
57.5°	137.6	132.0	126.8	122.9	122.3	119.9	120.2
60°	121.9	117.1	112.9	110.8	109.2	107.0	107.8
62.5°	108.9	104.9	101.1	99.4	97.7	96.1	96.4
65°	89.2	85.4	83.0	82.1	81.4	80.7	80.0
67.5°	71.1	68.8	67.3	65.2	63.8	63.6	62.9
70°	59.8	56.7	54.1	51.5	50.8	50.6	50.8
72.5°	47.9	45.9	45.2	44.0	43.8	43.2	43.6
75°	36.0	35.2	34.8	33.8	33.8	33.8	33.8
77.5°	26.6	26.2	25.9	25.7	25.4	25.0	25.0
80°	20.7	20.5	20.0	20.0	19.8	20.0	19.8
82.5°	15.7	15.6	15.1	15.1	14.8	14.7	14.8
85°	8.0	7.8	8.3	7.8	8.0	7.6	8.0
87.5°	7.7	7.9	7.8	7.9	7.8	8.3	8.0
90°	27.1	28.0	28.6	29.1	29.5	30.0	30.4
92.5°	30.3	31.7	32.6	32.8	33.1	33.4	33.6
95°	36.2	37.8	38.6	38.6	38.6	38.6	38.6
97.5°	38.1	39.9	40.9	41.1	41.3	41.6	41.8
100°	38.9	40.7	41.7	41.9	42.1	42.4	42.6
102.5°	50.0	44.3	41.8	42.2	42.6	43.0	43.4
105°	102.4	62.5	42.8	43.3	43.7	44.1	44.6
107.5°	319.4	290.1	260.4	230.4	200.4	170.3	140.2
110°	435.2	427.7	407.9	375.7	343.4	311.1	278.9



TEST NUMBER: P332398-840

CATALOG NUMBER: S123RDIW-S340D1030U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	509.0	509.1	505.7	499.0	492.2	485.3	478.6
115°	589.0	591.3	592.8	593.7	594.6	595.5	596.4
117.5°	659.0	660.9	661.9	662.0	662.2	662.4	662.6
120°	705.3	707.1	708.0	708.0	708.0	708.0	708.0
122.5°	749.9	751.1	751.9	752.0	752.2	752.5	752.7
125°	812.8	813.2	813.7	814.2	814.6	815.1	815.5
127.5°	876.9	877.7	877.8	877.3	876.9	876.5	876.0
130°	915.5	916.5	916.8	916.3	915.8	915.3	914.9
132.5°	952.1	953.0	953.1	952.5	951.9	951.3	950.6
135°	1007.2	1007.8	1007.8	1007.2	1006.5	1005.8	1005.2
137.5°	1056.9	1058.0	1058.3	1057.8	1057.4	1056.9	1056.5
140°	1088.0	1088.9	1089.1	1088.7	1088.2	1087.8	1087.3
142.5°	1117.5	1118.2	1118.2	1117.6	1117.0	1116.4	1115.7
145°	1158.7	1159.1	1159.3	1159.3	1159.3	1159.3	1159.3
147.5°	1195.8	1196.3	1196.0	1195.0	1193.9	1192.9	1191.8
150°	1218.5	1219.0	1218.9	1218.2	1217.5	1216.9	1216.2
152.5°	1239.1	1239.9	1239.8	1238.7	1237.7	1236.7	1235.7
155°	1267.2	1268.4	1268.2	1266.9	1265.6	1264.1	1262.8
157.5°	1291.6	1292.9	1292.7	1291.0	1289.3	1287.5	1285.8
160°	1305.5	1306.8	1306.7	1305.0	1303.5	1301.9	1300.3
162.5°	1318.2	1319.7	1319.7	1318.4	1317.0	1315.6	1314.1
165°	1335.1	1337.0	1337.1	1335.5	1333.9	1332.3	1330.8
167.5°	1348.2	1350.0	1350.0	1348.2	1346.4	1344.5	1342.7
170°	1355.4	1357.3	1357.3	1355.4	1353.6	1351.8	1350.1
172.5°	1360.3	1362.1	1362.0	1360.1	1358.1	1356.0	1354.1
175°	1365.9	1367.6	1367.5	1365.6	1363.8	1362.0	1360.2
177.5°	1368.0	1369.4	1369.3	1367.5	1365.6	1363.8	1362.0
180°	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2	1365.2

(END OF REPORT)