

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332405-840

Luminaire Tested: **S123RDIW-S340D1320U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332405-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S340D1320U840-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1320 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5935.2 lumens
Efficiency: N/A
Efficacy: 127.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 46.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332405-840

CATALOG NUMBER: S123RDIW-S340D1320U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332405-840

CATALOG NUMBER: S123RDIW-S340D1320U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	89	89	89	89	68	68	68	48	48	48	31	31	31	22
1	92	88	84	81	81	78	75	72	59	58	56	43	41	40	27	27	26	19
2	84	77	71	66	74	68	63	59	52	49	46	38	36	34	24	23	22	16
3	76	67	60	55	67	60	54	50	46	42	39	33	31	29	21	20	19	14
4	70	60	52	46	62	53	47	42	41	37	33	30	27	25	19	18	16	12
5	64	53	45	40	56	47	41	36	37	32	29	27	24	21	17	16	14	10
6	59	47	40	34	52	42	36	31	33	28	25	24	21	19	16	14	13	9
7	54	43	35	30	48	38	32	27	30	25	22	22	19	16	14	13	11	8
8	50	38	31	26	44	35	28	24	27	22	19	20	17	15	13	11	10	7
9	47	35	28	23	41	31	25	21	25	20	17	18	15	13	12	10	9	7
10	43	32	25	21	38	29	23	19	23	18	15	17	14	12	11	9	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6245	6245	6245
5°	6269	6183	6218
10°	6233	6105	6084
15°	6167	5962	5899
20°	6074	5783	5648
25°	5980	5583	5404
30°	5854	5351	5059
35°	5727	5119	4742
40°	5606	4846	4350
45°	5451	4576	3997
50°	5280	4270	3600
55°	5104	3920	3232
60°	4943	3546	2827
65°	4735	3140	2420
70°	4472	2634	1954
75°	4092	2075	1838
80°	3645	1841	1692
85°	3075	1618	1507



TEST NUMBER: P332405-840

CATALOG NUMBER: S123RDIW-S340D1320U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.5	0.9
10°-20°	151.6	2.6
20°-30°	218.3	3.7
30°-40°	245.9	4.1
40°-50°	235.2	4.0
50°-60°	192.6	3.2
60°-70°	130.0	2.2
70°-80°	65.4	1.1
80°-90°	22.2	0.4
90°-100°	108.6	1.8
100°-110°	325.1	5.5
110°-120°	553.0	9.3
120°-130°	727.3	12.3
130°-140°	817.5	13.8
140°-150°	803.6	13.5
150°-160°	676.5	11.4
160°-170°	450.3	7.6
170°-180°	157.7	2.7
0°-30°	424.3	7.1
0°-40°	670.2	11.3
0°-60°	1098.1	18.5
0°-90°	1315.6	22.2
90°-120°	986.7	16.6
90°-150°	3335.1	56.2
90°-180°	4620.0	77.8
0°-180°	5935.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	580	580	580	580	580	
5°	580	578	572	576	576	55
15°	553	548	535	533	529	156
25°	504	491	470	460	455	231
35°	436	418	390	370	361	273
45°	358	336	301	275	263	276
55°	272	248	209	183	172	244
65°	186	159	123	101	95	184
75°	98	76	50	45	44	105
85°	25	15	13	12	12	28
90°	1	15	31	37	39	6
95°	77	87	97	102	102	87
105°	295	298	309	309	312	316
115°	557	560	558	559	558	551
125°	815	818	816	811	806	726
135°	1057	1064	1064	1058	1056	814
145°	1282	1285	1289	1287	1282	801
155°	1468	1468	1470	1474	1466	676
165°	1599	1596	1595	1602	1594	451
175°	1663	1658	1658	1665	1657	158
180°	1667	1667	1667	1667	1667	



TEST NUMBER: P332405-840

CATALOG NUMBER: S123RDIW-S340D1320U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	580.2	580.2	580.2	580.2	580.2	580.2	580.2	580.2	580.2	580.2	580.2
2.5°	582.1	581.7	581.4	581.1	580.8	580.1	579.1	578.0	577.0	576.0	576.9
5°	580.2	579.7	579.2	578.7	578.0	577.2	575.9	574.7	573.4	572.2	573.1
7.5°	574.8	574.2	573.7	573.1	572.6	571.5	569.9	568.3	566.5	564.9	565.4
10°	570.3	569.6	568.9	568.2	567.3	566.0	564.2	562.3	560.4	558.6	558.7
12.5°	563.9	563.1	562.3	561.5	560.7	559.1	556.7	554.5	552.2	549.9	549.8
15°	553.4	552.2	551.1	549.9	548.8	546.7	543.8	540.9	538.0	535.0	534.5
17.5°	540.1	538.8	537.5	536.0	534.7	532.2	528.5	524.7	521.1	517.4	516.2
20°	530.3	528.7	526.9	525.3	523.6	520.8	516.8	512.8	508.9	504.9	503.5
22.5°	519.4	517.5	515.5	513.6	511.7	508.7	504.4	500.2	495.9	491.7	490.0
25°	503.5	500.9	498.3	495.6	493.0	489.3	484.5	479.7	474.8	470.1	467.9
27.5°	484.2	481.3	478.4	475.5	472.6	468.6	463.2	457.8	452.4	447.1	444.0
30°	471.0	467.9	464.7	461.6	458.5	453.9	448.1	442.2	436.4	430.5	427.0
32.5°	457.9	454.2	450.7	447.2	443.6	438.8	432.5	426.4	420.2	413.9	410.1
35°	435.8	431.9	428.2	424.4	420.7	415.6	409.1	402.5	396.1	389.6	385.2
37.5°	413.3	409.1	405.0	400.8	396.6	391.0	384.2	377.2	370.3	363.3	358.3
40°	399.0	394.5	389.8	385.3	380.6	374.6	367.2	359.7	352.3	344.9	339.5
42.5°	382.8	378.2	373.7	369.0	364.5	358.3	350.6	343.0	335.3	327.6	321.6
45°	358.1	353.4	348.7	344.0	339.2	332.9	324.9	316.8	308.7	300.6	294.7
47.5°	333.4	328.2	323.0	317.8	312.7	306.1	298.0	289.9	282.0	273.9	267.4
50°	315.3	310.3	305.5	300.5	295.6	288.9	280.4	272.0	263.5	255.0	248.5
52.5°	299.1	293.8	288.4	283.1	277.7	270.8	262.5	254.1	245.7	237.3	230.7
55°	272.0	266.8	261.8	256.6	251.5	244.5	235.6	226.7	217.8	208.9	202.9
57.5°	246.9	241.4	235.8	230.1	224.6	217.3	208.4	199.4	190.6	181.7	175.9
60°	229.6	223.9	218.1	212.4	206.6	199.4	190.8	182.1	173.4	164.7	159.1
62.5°	212.3	206.5	200.8	195.1	189.3	182.1	173.4	164.7	156.0	147.3	142.1
65°	185.9	180.2	174.4	168.6	162.9	155.9	147.7	139.6	131.5	123.3	118.2
67.5°	159.5	153.6	147.7	142.0	136.1	129.4	121.5	113.7	105.8	98.1	94.2
70°	142.1	136.4	130.8	125.1	119.6	113.0	105.7	98.4	91.1	83.7	80.1
72.5°	124.8	119.3	113.7	108.1	102.5	96.4	89.8	83.1	76.4	69.8	66.9
75°	98.4	93.3	88.3	83.3	78.3	72.9	67.2	61.4	55.6	49.9	48.9
77.5°	74.2	69.7	65.1	60.6	56.1	52.0	48.3	44.5	40.9	37.2	36.7
80°	58.8	54.5	50.3	45.9	41.7	38.5	36.3	34.0	31.8	29.7	29.3
82.5°	44.1	40.4	36.8	33.0	29.3	27.0	26.0	24.9	23.9	22.8	22.5
85°	24.9	22.6	20.3	18.1	15.8	14.4	14.1	13.8	13.5	13.1	12.9
87.5°	9.3	9.0	8.6	8.3	8.0	8.2	8.9	9.7	10.4	11.2	11.3
90°	1.3	4.2	7.2	10.0	12.9	16.3	20.1	23.8	27.7	31.4	32.6
92.5°	31.7	33.6	35.6	37.7	39.6	41.7	43.8	45.9	48.2	50.3	51.2
95°	77.3	79.3	81.4	83.4	85.4	87.7	90.0	92.3	94.6	96.9	98.1
97.5°	137.2	138.8	140.3	141.8	143.3	144.9	146.6	148.2	150.0	151.7	153.0
100°	178.1	179.9	181.6	183.4	185.1	186.7	188.1	189.7	191.1	192.6	193.4
102.5°	225.3	226.3	227.4	228.4	229.4	231.0	232.9	234.8	236.7	238.6	239.5
105°	294.7	295.3	295.9	296.4	297.0	298.6	301.2	303.9	306.5	309.1	309.1
107.5°	375.4	375.8	376.1	376.5	376.8	377.5	378.5	379.6	380.6	381.6	382.6
110°	425.7	426.3	426.9	427.4	428.0	428.6	429.2	429.8	430.3	430.9	432.1



TEST NUMBER: P332405-840

CATALOG NUMBER: S123RDIW-S340D1320U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	478.1	478.4	478.8	479.1	479.5	479.7	479.8	479.9	480.1	480.2	481.6
115°	556.6	557.5	558.4	559.3	560.2	560.3	559.7	559.2	558.6	558.0	558.3
117.5°	635.8	636.3	636.9	637.5	638.1	638.0	637.2	636.5	635.7	635.0	634.9
120°	685.0	686.7	688.5	690.2	692.0	692.2	690.6	689.2	687.8	686.3	686.0
122.5°	736.4	737.6	738.9	740.2	741.4	741.7	740.9	740.2	739.4	738.7	737.9
125°	814.7	815.6	816.4	817.3	818.2	818.3	817.7	817.2	816.6	816.0	814.9
127.5°	887.0	888.9	890.7	892.5	894.4	895.0	894.4	893.7	893.1	892.5	890.8
130°	935.1	937.5	939.9	942.2	944.5	945.2	944.3	943.5	942.6	941.7	940.6
132.5°	983.4	985.7	988.1	990.4	992.7	993.5	992.9	992.3	991.6	991.0	989.6
135°	1057.0	1058.7	1060.5	1062.2	1064.0	1064.7	1064.4	1064.1	1063.8	1063.5	1062.4
137.5°	1125.1	1126.5	1128.0	1129.4	1130.9	1132.1	1132.8	1133.6	1134.3	1135.1	1133.8
140°	1172.3	1173.7	1175.2	1176.6	1178.1	1178.9	1179.2	1179.5	1179.8	1180.1	1179.8
142.5°	1215.2	1216.7	1218.1	1219.6	1221.0	1222.0	1222.5	1223.0	1223.6	1224.2	1223.9
145°	1282.2	1282.8	1283.4	1284.0	1284.5	1285.4	1286.2	1287.1	1288.0	1288.8	1288.5
147.5°	1340.9	1342.0	1343.0	1344.1	1345.1	1346.0	1346.9	1347.7	1348.5	1349.3	1349.3
150°	1381.8	1382.4	1383.0	1383.5	1384.1	1384.7	1385.3	1385.8	1386.4	1387.0	1387.0
152.5°	1415.3	1416.1	1416.9	1417.7	1418.6	1419.2	1419.6	1419.9	1420.3	1420.6	1421.1
155°	1468.2	1468.2	1468.2	1468.2	1468.2	1468.4	1468.6	1468.9	1469.3	1469.6	1470.8
157.5°	1513.3	1513.0	1512.6	1512.3	1511.9	1511.9	1512.1	1512.3	1512.6	1512.8	1514.0
160°	1541.6	1541.1	1540.4	1539.8	1539.2	1538.9	1538.9	1538.9	1538.9	1538.9	1540.4
162.5°	1566.7	1565.9	1565.1	1564.3	1563.5	1563.2	1563.5	1563.7	1563.9	1564.1	1565.6
165°	1599.2	1598.3	1597.5	1596.6	1595.8	1595.3	1595.3	1595.3	1595.3	1595.3	1597.0
167.5°	1625.2	1624.0	1622.9	1621.6	1620.5	1620.0	1620.2	1620.5	1620.7	1620.9	1622.8
170°	1639.8	1638.7	1637.5	1636.4	1635.2	1634.6	1634.6	1634.6	1634.6	1634.6	1636.6
172.5°	1651.3	1650.2	1649.0	1647.9	1646.7	1646.1	1646.1	1646.1	1646.1	1646.1	1647.9
175°	1663.4	1662.2	1661.1	1659.9	1658.7	1658.2	1658.2	1658.2	1658.2	1658.2	1659.9
177.5°	1668.4	1667.5	1666.5	1665.6	1664.7	1664.2	1664.2	1664.2	1664.2	1664.2	1665.6
180°	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4



TEST NUMBER: P332405-840

CATALOG NUMBER: S123RDIW-S340D1320U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	580.2	580.2	580.2	580.2	580.2	580.2	580.2	580.2
2.5°	577.8	578.8	579.8	580.1	580.0	579.8	579.6	579.5
5°	574.1	575.0	575.9	576.3	576.1	575.9	575.7	575.5
7.5°	566.0	566.5	567.0	567.1	566.7	566.4	566.0	565.7
10°	558.8	558.9	559.0	558.8	558.3	557.7	557.1	556.6
12.5°	549.8	549.7	549.7	549.3	548.7	548.1	547.4	546.8
15°	533.9	533.4	532.9	532.3	531.6	530.8	530.1	529.4
17.5°	515.1	514.0	512.9	511.8	510.7	509.6	508.6	507.5
20°	502.2	500.8	499.5	498.2	496.9	495.6	494.4	493.1
22.5°	488.4	486.7	484.9	483.5	482.3	481.2	480.0	478.9
25°	465.6	463.5	461.3	459.6	458.5	457.4	456.2	455.0
27.5°	441.0	438.0	434.9	432.5	430.7	429.0	427.3	425.5
30°	423.4	419.9	416.4	413.7	412.0	410.4	408.7	407.0
32.5°	406.2	402.3	398.4	395.6	393.8	392.1	390.3	388.6
35°	380.6	376.1	371.6	368.4	366.6	364.7	362.7	360.9
37.5°	353.1	348.0	343.0	339.2	336.9	334.6	332.2	329.9
40°	334.1	328.6	323.2	319.2	316.8	314.5	312.0	309.6
42.5°	315.7	309.8	303.9	299.8	297.6	295.5	293.4	291.1
45°	288.7	282.8	276.8	272.6	270.1	267.6	265.1	262.6
47.5°	260.8	254.4	247.9	243.6	241.4	239.1	236.8	234.6
50°	242.1	235.6	229.1	224.7	222.3	219.8	217.4	215.0
52.5°	223.9	217.1	210.5	206.0	203.8	201.7	199.5	197.3
55°	196.8	190.8	184.7	180.6	178.5	176.4	174.3	172.2
57.5°	170.2	164.4	158.8	154.9	153.2	151.4	149.7	147.8
60°	153.4	147.7	142.1	138.4	136.6	134.8	133.1	131.3
62.5°	136.7	131.5	126.1	122.5	120.7	118.9	116.9	115.1
65°	113.0	108.0	102.8	99.7	98.5	97.4	96.2	95.0
67.5°	90.4	86.5	82.7	80.2	79.0	77.8	76.5	75.3
70°	76.4	72.8	69.1	66.8	65.5	64.4	63.2	62.1
72.5°	63.8	60.9	57.9	56.1	55.6	55.1	54.7	54.2
75°	47.8	46.8	45.6	45.0	44.8	44.6	44.4	44.2
77.5°	36.1	35.4	34.9	34.5	34.3	34.1	33.9	33.7
80°	29.0	28.7	28.4	28.2	27.9	27.7	27.5	27.3
82.5°	22.2	21.9	21.6	21.4	21.4	21.3	21.3	21.3
85°	12.7	12.5	12.3	12.2	12.2	12.2	12.2	12.2
87.5°	11.5	11.6	11.8	11.9	11.9	11.9	11.9	12.0
90°	33.7	34.9	36.1	37.0	37.6	38.2	38.7	39.3
92.5°	52.1	53.1	54.0	54.3	53.9	53.6	53.2	52.9
95°	99.3	100.4	101.6	102.2	102.2	102.2	102.2	102.2
97.5°	154.3	155.7	157.0	157.6	157.5	157.4	157.3	157.1
100°	194.3	195.1	196.0	196.7	197.3	197.9	198.5	199.0
102.5°	240.3	241.3	242.2	242.5	242.4	242.3	242.2	242.1
105°	309.1	309.1	309.1	309.4	310.0	310.5	311.1	311.7
107.5°	383.5	384.5	385.4	385.7	385.4	385.0	384.7	384.3
110°	433.2	434.4	435.6	435.9	435.3	434.7	434.1	433.5



TEST NUMBER: P332405-840

CATALOG NUMBER: S123RDIW-S340D1320U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	482.9	484.3	485.7	486.4	486.3	486.1	486.0	485.9
115°	558.6	558.9	559.2	559.2	558.9	558.6	558.3	558.0
117.5°	634.9	634.8	634.7	634.3	633.5	632.7	631.9	631.1
120°	685.7	685.5	685.2	684.7	684.2	683.6	683.0	682.4
122.5°	737.2	736.4	735.7	734.9	734.1	733.3	732.5	731.6
125°	813.6	812.5	811.3	810.2	809.0	807.8	806.7	805.5
127.5°	889.2	887.6	886.0	884.4	883.1	881.8	880.5	879.1
130°	939.4	938.3	937.1	935.4	933.4	931.4	929.4	927.4
132.5°	988.2	986.7	985.4	983.9	982.3	980.8	979.2	977.7
135°	1061.2	1060.1	1058.8	1058.0	1057.4	1056.8	1056.2	1055.7
137.5°	1132.6	1131.4	1130.1	1129.0	1127.9	1126.8	1125.7	1124.6
140°	1179.5	1179.2	1178.9	1177.8	1175.8	1173.7	1171.6	1169.6
142.5°	1223.6	1223.2	1222.9	1222.0	1220.4	1218.9	1217.3	1215.8
145°	1288.2	1288.0	1287.7	1287.0	1285.8	1284.5	1283.4	1282.2
147.5°	1349.3	1349.3	1349.3	1348.5	1346.8	1344.9	1343.2	1341.5
150°	1387.0	1387.0	1387.0	1386.1	1384.4	1382.7	1380.9	1379.2
152.5°	1421.5	1422.0	1422.4	1421.9	1420.4	1418.9	1417.3	1415.8
155°	1471.9	1473.1	1474.2	1473.8	1471.8	1469.8	1467.6	1465.6
157.5°	1515.2	1516.4	1517.7	1517.4	1515.8	1514.2	1512.6	1511.0
160°	1541.9	1543.4	1544.8	1545.0	1543.8	1542.7	1541.5	1540.2
162.5°	1567.0	1568.5	1569.9	1569.7	1567.9	1566.0	1564.2	1562.3
165°	1598.8	1600.5	1602.3	1602.2	1600.1	1598.1	1596.0	1594.0
167.5°	1624.6	1626.4	1628.2	1628.2	1626.4	1624.6	1622.8	1620.9
170°	1638.7	1640.7	1642.7	1642.7	1640.7	1638.7	1636.6	1634.6
172.5°	1649.7	1651.5	1653.4	1653.3	1651.2	1649.1	1647.1	1645.1
175°	1661.6	1663.4	1665.2	1665.0	1662.9	1660.9	1658.9	1656.9
177.5°	1667.0	1668.4	1669.8	1669.7	1668.0	1666.4	1664.8	1663.1
180°	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4

(END OF REPORT)