

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332396-840

Luminaire Tested: **S123RDIW-S340D755U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332396-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S340D755U840-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 755 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4363.7 lumens
Efficiency: N/A
Efficacy: 143.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 30.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332396-840

CATALOG NUMBER: S123RDIW-S340D755U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332396-840

CATALOG NUMBER: S123RDIW-S340D755U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	38	38	38	30
1	94	89	86	82	84	80	77	74	63	61	60	48	47	45	34	33	32	26
2	85	78	72	68	76	70	66	61	56	52	50	42	40	38	30	29	27	22
3	78	69	62	56	70	62	56	51	49	45	42	38	35	33	27	25	24	19
4	71	61	53	48	64	55	49	44	44	39	36	34	30	28	24	22	20	16
5	65	54	47	41	58	49	42	37	39	34	31	30	27	24	22	20	18	14
6	60	49	41	35	54	44	37	32	35	30	27	27	24	21	20	17	16	13
7	56	44	36	31	50	40	33	28	32	27	24	25	21	19	18	16	14	11
8	51	40	32	27	46	36	30	25	29	24	21	23	19	17	16	14	13	10
9	48	36	29	24	43	33	27	22	27	22	19	21	17	15	15	13	11	9
10	45	33	26	21	40	30	24	20	24	20	17	19	16	13	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6245	6245	6245
5°	6269	6183	6218
10°	6233	6105	6084
15°	6167	5962	5899
20°	6074	5783	5648
25°	5980	5583	5404
30°	5854	5351	5059
35°	5727	5119	4742
40°	5606	4846	4350
45°	5451	4576	3997
50°	5280	4270	3600
55°	5104	3920	3232
60°	4943	3546	2827
65°	4735	3140	2420
70°	4472	2634	1954
75°	4092	2075	1838
80°	3645	1841	1692
85°	3075	1618	1507



TEST NUMBER: P332396-840

CATALOG NUMBER: S123RDIW-S340D755U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.5	1.2
10°-20°	151.6	3.5
20°-30°	218.3	5.0
30°-40°	245.9	5.6
40°-50°	235.2	5.4
50°-60°	192.6	4.4
60°-70°	130.0	3.0
70°-80°	65.4	1.5
80°-90°	20.1	0.5
90°-100°	36.4	0.8
100°-110°	173.3	4.0
110°-120°	416.3	9.5
120°-130°	530.1	12.1
130°-140°	566.4	13.0
140°-150°	529.7	12.1
150°-160°	427.3	9.8
160°-170°	275.7	6.3
170°-180°	95.0	2.2
0°-30°	424.3	9.7
0°-40°	670.2	15.4
0°-60°	1098.1	25.2
0°-90°	1313.5	30.1
90°-120°	626.0	14.3
90°-150°	2252.2	51.6
90°-180°	3050.0	69.9
0°-180°	4363.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	580	580	580	580	580	
5°	580	578	572	576	576	55
15°	553	548	535	533	529	156
25°	504	491	470	460	455	231
35°	436	418	390	370	361	273
45°	358	336	301	275	263	276
55°	272	248	209	183	172	244
65°	186	159	123	101	95	184
75°	98	76	50	45	44	105
85°	25	15	13	12	12	28
90°	1	8	18	21	22	3
95°	45	17	23	28	28	56
105°	222	225	163	39	33	235
115°	415	420	427	434	437	410
125°	586	591	594	596	597	523
135°	729	733	736	738	736	561
145°	841	846	848	849	849	526
155°	927	925	926	929	925	427
165°	977	975	974	980	975	276
175°	1000	997	997	1002	996	95
180°	1000	1000	1000	1000	1000	



TEST NUMBER: P332396-840

CATALOG NUMBER: S123RDIW-S340D755U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	580.2	580.2	580.2	580.2	580.2	580.2	580.2	580.2	580.2	580.2	580.2
2.5°	582.1	581.7	581.4	581.1	580.8	580.1	579.1	578.0	577.0	576.0	576.9
5°	580.2	579.7	579.2	578.7	578.0	577.2	575.9	574.7	573.4	572.2	573.1
7.5°	574.8	574.2	573.7	573.1	572.6	571.5	569.9	568.3	566.5	564.9	565.4
10°	570.3	569.6	568.9	568.2	567.3	566.0	564.2	562.3	560.4	558.6	558.7
12.5°	563.9	563.1	562.3	561.5	560.7	559.1	556.7	554.5	552.2	549.9	549.8
15°	553.4	552.2	551.1	549.9	548.8	546.7	543.8	540.9	538.0	535.0	534.5
17.5°	540.1	538.8	537.5	536.0	534.7	532.2	528.5	524.7	521.1	517.4	516.2
20°	530.3	528.7	526.9	525.3	523.6	520.8	516.8	512.8	508.9	504.9	503.5
22.5°	519.4	517.5	515.5	513.6	511.7	508.7	504.4	500.2	495.9	491.7	490.0
25°	503.5	500.9	498.3	495.6	493.0	489.3	484.5	479.7	474.8	470.1	467.9
27.5°	484.2	481.3	478.4	475.5	472.6	468.6	463.2	457.8	452.4	447.1	444.0
30°	471.0	467.9	464.7	461.6	458.5	453.9	448.1	442.2	436.4	430.5	427.0
32.5°	457.9	454.2	450.7	447.2	443.6	438.8	432.5	426.4	420.2	413.9	410.1
35°	435.8	431.9	428.2	424.4	420.7	415.6	409.1	402.5	396.1	389.6	385.2
37.5°	413.3	409.1	405.0	400.8	396.6	391.0	384.2	377.2	370.3	363.3	358.3
40°	399.0	394.5	389.8	385.3	380.6	374.6	367.2	359.7	352.3	344.9	339.5
42.5°	382.8	378.2	373.7	369.0	364.5	358.3	350.6	343.0	335.3	327.6	321.6
45°	358.1	353.4	348.7	344.0	339.2	332.9	324.9	316.8	308.7	300.6	294.7
47.5°	333.4	328.2	323.0	317.8	312.7	306.1	298.0	289.9	282.0	273.9	267.4
50°	315.3	310.3	305.5	300.5	295.6	288.9	280.4	272.0	263.5	255.0	248.5
52.5°	299.1	293.8	288.4	283.1	277.7	270.8	262.5	254.1	245.7	237.3	230.7
55°	272.0	266.8	261.8	256.6	251.5	244.5	235.6	226.7	217.8	208.9	202.9
57.5°	246.9	241.4	235.8	230.1	224.6	217.3	208.4	199.4	190.6	181.7	175.9
60°	229.6	223.9	218.1	212.4	206.6	199.4	190.8	182.1	173.4	164.7	159.1
62.5°	212.3	206.5	200.8	195.1	189.3	182.1	173.4	164.7	156.0	147.3	142.1
65°	185.9	180.2	174.4	168.6	162.9	155.9	147.7	139.6	131.5	123.3	118.2
67.5°	159.5	153.6	147.7	142.0	136.1	129.4	121.5	113.7	105.8	98.1	94.2
70°	142.1	136.4	130.8	125.1	119.6	113.0	105.7	98.4	91.1	83.7	80.1
72.5°	124.8	119.3	113.7	108.1	102.5	96.4	89.8	83.1	76.4	69.8	66.9
75°	98.4	93.3	88.3	83.3	78.3	72.9	67.2	61.4	55.6	49.9	48.9
77.5°	74.2	69.7	65.1	60.6	56.1	52.0	48.3	44.5	40.9	37.2	36.7
80°	58.8	54.5	50.3	45.9	41.7	38.5	36.3	34.0	31.8	29.7	29.3
82.5°	44.1	40.4	36.8	33.0	29.3	27.0	26.0	24.9	23.9	22.8	22.5
85°	24.9	22.6	20.3	18.1	15.8	14.4	14.1	13.8	13.5	13.1	12.9
87.5°	9.2	8.6	8.0	7.4	6.9	6.8	7.2	7.6	8.1	8.5	8.5
90°	0.7	2.4	4.0	5.7	7.4	9.3	11.4	13.5	15.7	17.9	18.5
92.5°	13.8	13.3	12.9	12.4	12.0	12.5	14.1	15.8	17.4	19.0	20.1
95°	45.3	38.6	31.8	25.0	18.3	15.8	17.6	19.4	21.2	23.0	24.2
97.5°	91.1	88.1	85.0	82.0	79.0	71.5	59.6	47.7	35.9	23.9	25.2
100°	125.6	128.9	132.2	135.5	138.8	127.5	101.8	76.0	50.3	24.5	25.9
102.5°	164.8	167.2	169.6	172.0	174.3	161.5	133.3	105.1	77.1	48.9	44.8
105°	221.5	223.3	225.1	226.9	228.7	222.2	207.3	192.5	177.6	162.8	133.5
107.5°	281.1	282.7	284.1	285.6	287.0	288.9	291.2	293.6	296.0	298.3	276.8
110°	321.0	322.3	323.7	325.0	326.3	327.9	329.7	331.5	333.4	335.2	329.7



TEST NUMBER: P332396-840

CATALOG NUMBER: S123RDIW-S340D755U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	359.1	360.2	361.4	362.6	363.9	365.4	367.2	369.0	370.8	372.6	372.7
115°	415.4	416.4	417.4	418.4	419.4	420.6	422.1	423.5	425.1	426.6	428.2
117.5°	470.0	471.2	472.4	473.6	474.8	475.8	476.6	477.4	478.1	478.9	480.2
120°	503.8	505.3	506.9	508.3	509.8	510.8	511.3	511.8	512.3	512.7	514.1
122.5°	538.4	539.6	540.8	542.0	543.2	544.1	544.7	545.4	546.0	546.6	547.5
125°	585.6	586.9	588.2	589.6	590.9	591.9	592.5	593.2	593.8	594.5	594.8
127.5°	631.4	632.7	634.0	635.3	636.6	637.7	638.5	639.2	640.1	640.9	641.4
130°	659.8	661.3	662.6	663.9	665.2	666.2	666.8	667.5	668.1	668.8	669.4
132.5°	687.2	688.5	689.8	691.2	692.6	693.5	694.0	694.5	695.0	695.6	696.2
135°	729.0	730.0	730.9	732.0	733.0	733.8	734.5	735.1	735.8	736.4	736.9
137.5°	764.7	765.9	767.2	768.4	769.7	770.5	770.8	771.2	771.6	771.9	772.7
140°	788.4	789.4	790.4	791.4	792.4	793.1	793.7	794.2	794.7	795.2	795.8
142.5°	810.4	811.4	812.4	813.4	814.5	815.2	815.7	816.2	816.7	817.2	817.7
145°	841.2	842.3	843.5	844.7	845.9	846.6	846.9	847.3	847.6	847.9	848.2
147.5°	870.2	870.9	871.7	872.4	873.2	873.7	874.1	874.4	874.7	875.0	875.5
150°	888.1	888.5	889.0	889.5	890.0	890.4	890.8	891.1	891.4	891.7	892.1
152.5°	904.0	904.3	904.5	904.7	905.0	905.2	905.4	905.6	905.8	906.1	906.6
155°	926.7	926.3	926.0	925.6	925.3	925.2	925.4	925.6	925.7	925.9	926.8
157.5°	944.2	944.2	944.1	944.1	944.1	944.0	943.8	943.6	943.5	943.3	944.3
160°	954.9	954.7	954.6	954.4	954.2	954.1	953.9	953.7	953.6	953.4	954.4
162.5°	965.0	964.6	964.1	963.7	963.3	963.0	962.8	962.7	962.5	962.3	963.5
165°	977.2	976.7	976.2	975.7	975.2	974.9	974.7	974.5	974.4	974.2	975.5
167.5°	986.7	986.0	985.4	984.7	984.1	983.7	983.7	983.7	983.7	983.7	985.0
170°	992.1	991.4	990.8	990.1	989.5	989.1	989.1	989.1	989.1	989.1	990.4
172.5°	995.6	994.8	994.0	993.3	992.5	992.1	992.3	992.4	992.5	992.7	994.0
175°	1000.3	999.4	998.6	997.7	996.9	996.6	996.7	996.9	997.1	997.2	998.5
177.5°	1001.4	1000.8	1000.1	999.5	998.8	998.6	998.7	998.8	999.0	999.1	1000.1
180°	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3



TEST NUMBER: P332396-840

CATALOG NUMBER: S123RDIW-S340D755U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	580.2	580.2	580.2	580.2	580.2	580.2	580.2	580.2
2.5°	577.8	578.8	579.8	580.1	580.0	579.8	579.6	579.5
5°	574.1	575.0	575.9	576.3	576.1	575.9	575.7	575.5
7.5°	566.0	566.5	567.0	567.1	566.7	566.4	566.0	565.7
10°	558.8	558.9	559.0	558.8	558.3	557.7	557.1	556.6
12.5°	549.8	549.7	549.7	549.3	548.7	548.1	547.4	546.8
15°	533.9	533.4	532.9	532.3	531.6	530.8	530.1	529.4
17.5°	515.1	514.0	512.9	511.8	510.7	509.6	508.6	507.5
20°	502.2	500.8	499.5	498.2	496.9	495.6	494.4	493.1
22.5°	488.4	486.7	484.9	483.5	482.3	481.2	480.0	478.9
25°	465.6	463.5	461.3	459.6	458.5	457.4	456.2	455.0
27.5°	441.0	438.0	434.9	432.5	430.7	429.0	427.3	425.5
30°	423.4	419.9	416.4	413.7	412.0	410.4	408.7	407.0
32.5°	406.2	402.3	398.4	395.6	393.8	392.1	390.3	388.6
35°	380.6	376.1	371.6	368.4	366.6	364.7	362.7	360.9
37.5°	353.1	348.0	343.0	339.2	336.9	334.6	332.2	329.9
40°	334.1	328.6	323.2	319.2	316.8	314.5	312.0	309.6
42.5°	315.7	309.8	303.9	299.8	297.6	295.5	293.4	291.1
45°	288.7	282.8	276.8	272.6	270.1	267.6	265.1	262.6
47.5°	260.8	254.4	247.9	243.6	241.4	239.1	236.8	234.6
50°	242.1	235.6	229.1	224.7	222.3	219.8	217.4	215.0
52.5°	223.9	217.1	210.5	206.0	203.8	201.7	199.5	197.3
55°	196.8	190.8	184.7	180.6	178.5	176.4	174.3	172.2
57.5°	170.2	164.4	158.8	154.9	153.2	151.4	149.7	147.8
60°	153.4	147.7	142.1	138.4	136.6	134.8	133.1	131.3
62.5°	136.7	131.5	126.1	122.5	120.7	118.9	116.9	115.1
65°	113.0	108.0	102.8	99.7	98.5	97.4	96.2	95.0
67.5°	90.4	86.5	82.7	80.2	79.0	77.8	76.5	75.3
70°	76.4	72.8	69.1	66.8	65.5	64.4	63.2	62.1
72.5°	63.8	60.9	57.9	56.1	55.6	55.1	54.7	54.2
75°	47.8	46.8	45.6	45.0	44.8	44.6	44.4	44.2
77.5°	36.1	35.4	34.9	34.5	34.3	34.1	33.9	33.7
80°	29.0	28.7	28.4	28.2	27.9	27.7	27.5	27.3
82.5°	22.2	21.9	21.6	21.4	21.4	21.3	21.3	21.3
85°	12.7	12.5	12.3	12.2	12.2	12.2	12.2	12.2
87.5°	8.6	8.6	8.7	8.7	8.7	8.7	8.6	8.6
90°	19.2	19.8	20.5	21.0	21.3	21.6	21.9	22.3
92.5°	21.1	22.2	23.2	23.8	24.0	24.2	24.4	24.6
95°	25.3	26.5	27.7	28.3	28.3	28.3	28.3	28.3
97.5°	26.6	27.9	29.2	30.0	30.1	30.3	30.5	30.6
100°	27.2	28.5	29.8	30.6	30.7	30.9	31.0	31.2
102.5°	40.7	36.7	32.5	30.6	30.9	31.2	31.5	31.8
105°	104.3	75.0	45.8	31.4	31.7	32.0	32.4	32.7
107.5°	255.4	234.0	212.6	190.9	168.7	146.7	124.7	102.7
110°	324.3	318.8	313.4	298.8	275.2	251.6	227.9	204.4



TEST NUMBER: P332396-840

CATALOG NUMBER: S123RDIW-S340D755U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	372.8	372.9	373.0	370.5	365.6	360.6	355.6	350.6
115°	429.9	431.5	433.1	434.3	434.9	435.7	436.3	437.0
117.5°	481.5	482.8	484.1	484.8	485.0	485.1	485.2	485.4
120°	515.4	516.7	518.1	518.7	518.7	518.7	518.7	518.7
122.5°	548.5	549.4	550.4	550.9	551.0	551.1	551.3	551.4
125°	595.1	595.5	595.8	596.1	596.5	596.8	597.1	597.4
127.5°	642.0	642.5	643.0	643.1	642.8	642.4	642.1	641.8
130°	670.1	670.8	671.5	671.7	671.3	671.0	670.7	670.2
132.5°	696.9	697.5	698.2	698.3	697.8	697.4	696.9	696.4
135°	737.4	737.9	738.4	738.4	737.9	737.4	736.9	736.4
137.5°	773.6	774.4	775.2	775.4	775.1	774.7	774.4	774.1
140°	796.5	797.1	797.8	798.0	797.6	797.3	797.0	796.6
142.5°	818.2	818.7	819.2	819.3	818.8	818.4	817.9	817.4
145°	848.6	848.9	849.2	849.4	849.4	849.4	849.4	849.4
147.5°	875.8	876.1	876.5	876.2	875.5	874.6	873.9	873.1
150°	892.4	892.7	893.0	893.0	892.5	892.0	891.5	891.0
152.5°	907.2	907.8	908.4	908.3	907.6	906.8	906.1	905.2
155°	927.6	928.4	929.3	929.2	928.2	927.2	926.1	925.1
157.5°	945.3	946.2	947.3	947.2	945.8	944.5	943.3	942.0
160°	955.4	956.4	957.4	957.4	956.1	955.0	953.8	952.7
162.5°	964.6	965.7	966.8	966.8	965.8	964.8	963.8	962.8
165°	976.8	978.2	979.5	979.6	978.5	977.2	976.1	974.9
167.5°	986.3	987.7	989.1	989.1	987.7	986.3	985.0	983.7
170°	991.7	993.1	994.4	994.4	993.1	991.7	990.4	989.1
172.5°	995.3	996.6	997.9	997.8	996.4	995.0	993.5	992.1
175°	999.6	1000.8	1001.9	1001.8	1000.5	999.2	997.8	996.5
177.5°	1001.2	1002.2	1003.3	1003.1	1001.8	1000.5	999.2	997.8
180°	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3

(END OF REPORT)