

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333102-927

Luminaire Tested: **S124RDIW-S1195D770U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333102-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S1195D770U927-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5928.4 lumens
Efficiency: N/A
Efficacy: 99.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 59.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333102-927

CATALOG NUMBER: S124RDIW-S1195D770U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333102-927

CATALOG NUMBER: S124RDIW-S1195D770U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	69	69	69	64
1	101	97	93	90	95	91	88	85	81	78	76	71	69	67	62	61	59	55
2	93	85	79	74	87	80	75	70	71	67	63	63	60	57	55	53	50	47
3	85	75	68	62	79	71	64	59	63	58	54	56	52	48	49	46	43	40
4	78	67	59	53	73	63	56	51	56	51	46	50	45	42	44	40	38	34
5	71	60	52	46	67	57	49	44	51	45	40	45	40	36	40	36	33	30
6	66	54	46	40	62	51	44	38	46	40	35	41	36	32	36	32	29	27
7	61	49	41	35	57	46	39	34	42	36	31	37	32	29	33	29	26	24
8	57	44	37	31	53	42	35	30	38	32	28	34	29	26	30	26	23	21
9	53	41	33	28	50	39	32	27	35	29	25	32	27	23	28	24	21	19
10	50	37	30	25	47	36	29	24	32	27	23	29	24	21	26	22	19	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13337	13337	13337
5°	13367	13203	13285
10°	13283	13045	13045
15°	13131	12771	12676
20°	12921	12411	12182
25°	12653	11989	11685
30°	12393	11544	11060
35°	12105	11083	10435
40°	11758	10559	9759
45°	11439	10038	9070
50°	11074	9437	8341
55°	10683	8812	7548
60°	10253	8128	6739
65°	9859	7272	5945
70°	9286	6331	5046
75°	8562	5250	4105
80°	7471	3998	3766
85°	6326	3631	3399



TEST NUMBER: P333102-927

CATALOG NUMBER: S124RDIW-S1195D770U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.2	2.6
10°-20°	432.8	7.3
20°-30°	624.9	10.5
30°-40°	708.3	11.9
40°-50°	684.0	11.5
50°-60°	568.8	9.6
60°-70°	392.8	6.6
70°-80°	199.1	3.4
80°-90°	53.3	0.9
90°-100°	50.1	0.8
100°-110°	148.5	2.5
110°-120°	252.1	4.3
120°-130°	332.4	5.6
130°-140°	373.3	6.3
140°-150°	366.9	6.2
150°-160°	308.6	5.2
160°-170°	205.3	3.5
170°-180°	71.9	1.2
0°-30°	1212.9	20.5
0°-40°	1921.2	32.4
0°-60°	3174.0	53.5
0°-90°	3819.2	64.4
90°-120°	450.8	7.6
90°-150°	1523.4	25.7
90°-180°	2109.0	35.6
0°-180°	5928.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1652	1652	1652	1652	1652	
5°	1650	1644	1629	1641	1639	156
15°	1571	1559	1528	1525	1517	442
25°	1420	1396	1346	1325	1312	654
35°	1228	1186	1125	1083	1059	767
45°	1002	953	879	819	794	772
55°	759	707	626	563	536	679
65°	516	460	381	328	311	509
75°	274	227	168	140	132	290
85°	68	44	39	37	37	77
90°	2	8	13	16	18	5
95°	35	40	45	46	46	39
105°	137	138	140	142	144	145
115°	256	256	255	255	254	253
125°	373	373	373	372	370	333
135°	482	485	485	484	482	372
145°	585	587	588	587	586	366
155°	670	670	670	672	670	308
165°	730	728	727	730	728	206
175°	759	756	756	759	756	72
180°	760	760	760	760	760	



TEST NUMBER: P333102-927

CATALOG NUMBER: S124RDIW-S1195D770U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1652.0	1652.0	1652.0	1652.0	1652.0	1652.0	1652.0	1652.0	1652.0	1652.0	1652.0
2.5°	1656.1	1655.2	1654.3	1653.4	1652.5	1650.8	1648.4	1645.8	1643.4	1640.9	1643.4
5°	1649.5	1648.4	1647.3	1646.2	1645.0	1642.7	1639.4	1636.0	1632.7	1629.3	1632.1
7.5°	1634.6	1633.4	1632.2	1631.0	1629.8	1627.1	1622.7	1618.3	1613.9	1609.6	1611.4
10°	1620.4	1619.0	1617.6	1616.2	1614.8	1611.5	1606.5	1601.5	1596.4	1591.3	1592.4
12.5°	1602.2	1600.6	1598.9	1597.3	1595.7	1591.9	1585.9	1580.0	1574.0	1568.0	1568.8
15°	1571.1	1568.5	1566.1	1563.5	1561.0	1556.2	1549.2	1542.1	1535.1	1528.0	1527.5
17.5°	1533.4	1529.7	1526.1	1522.4	1518.8	1512.8	1504.3	1495.9	1487.4	1479.0	1477.4
20°	1504.0	1500.4	1496.7	1493.1	1489.5	1482.8	1473.3	1463.7	1454.1	1444.6	1442.3
22.5°	1471.6	1467.6	1463.5	1459.4	1455.2	1448.1	1437.8	1427.6	1417.4	1407.2	1403.7
25°	1420.5	1415.5	1410.4	1405.4	1400.3	1392.0	1380.5	1369.0	1357.5	1345.9	1341.2
27.5°	1366.9	1360.6	1354.2	1347.9	1341.5	1332.2	1319.9	1307.6	1295.2	1282.9	1277.0
30°	1329.5	1322.5	1315.4	1308.4	1301.4	1291.3	1278.0	1264.8	1251.6	1238.4	1231.4
32.5°	1290.0	1282.1	1274.1	1266.2	1258.3	1247.5	1233.8	1220.2	1206.5	1192.9	1184.7
35°	1228.3	1219.2	1210.3	1201.3	1192.3	1180.7	1166.7	1152.7	1138.6	1124.6	1115.0
37.5°	1162.3	1152.9	1143.7	1134.4	1125.1	1112.7	1097.2	1081.6	1066.0	1050.4	1039.7
40°	1115.7	1106.4	1097.2	1087.9	1078.6	1066.0	1050.0	1033.9	1017.9	1001.9	990.1
42.5°	1071.2	1061.4	1051.7	1042.0	1032.3	1019.1	1002.3	985.6	969.0	952.3	940.2
45°	1001.9	991.4	981.0	970.7	960.3	946.6	929.8	912.9	896.0	879.2	865.4
47.5°	930.3	919.5	908.8	898.0	887.3	873.1	855.6	838.0	820.5	803.0	788.7
50°	881.7	870.7	859.8	848.8	837.8	823.3	805.3	787.3	769.4	751.4	737.4
52.5°	832.1	821.3	810.6	799.9	789.2	774.5	756.1	737.7	719.2	700.8	686.5
55°	759.0	747.7	736.5	725.2	714.0	699.3	681.0	662.7	644.4	626.1	611.6
57.5°	686.6	674.9	663.2	651.6	639.8	625.0	607.0	589.0	571.0	553.0	538.2
60°	635.0	623.8	612.5	601.3	590.0	575.4	557.5	539.5	521.4	503.4	488.9
62.5°	588.4	576.8	565.1	553.4	541.7	526.6	508.2	489.7	471.3	452.9	439.3
65°	516.1	504.0	491.9	479.8	467.8	452.7	434.7	416.8	398.8	380.7	368.7
67.5°	440.9	429.4	417.8	406.2	394.7	380.5	363.8	347.1	330.4	313.7	303.3
70°	393.4	381.6	369.8	358.0	346.2	332.2	316.2	300.2	284.2	268.2	258.9
72.5°	342.8	332.2	321.5	310.8	300.1	287.2	272.0	256.9	241.8	226.6	218.7
75°	274.5	264.1	253.7	243.3	232.9	221.1	207.9	194.6	181.5	168.3	161.8
77.5°	205.2	196.4	187.5	178.7	169.8	160.1	149.4	138.8	128.1	117.4	113.6
80°	160.7	152.5	144.3	136.2	128.0	119.8	111.3	102.9	94.4	86.0	85.2
82.5°	122.2	114.7	107.3	99.7	92.3	86.1	81.3	76.4	71.6	66.8	66.1
85°	68.3	62.7	57.0	51.4	45.8	42.6	41.7	40.9	40.1	39.2	38.7
87.5°	23.6	22.1	20.6	19.1	17.6	16.8	16.8	16.8	16.8	16.7	16.7
90°	1.7	3.2	4.7	6.1	7.5	8.8	9.8	10.9	11.9	12.9	13.7
92.5°	12.6	14.3	15.8	17.5	19.2	20.4	21.1	21.8	22.6	23.3	23.8
95°	35.3	36.4	37.6	38.8	40.0	41.0	41.9	42.9	43.8	44.7	45.1
97.5°	61.6	62.6	63.5	64.4	65.4	66.4	67.5	68.5	69.6	70.7	71.1
100°	82.3	82.9	83.3	83.9	84.4	85.2	86.4	87.6	88.8	90.0	90.2
102.5°	103.9	104.2	104.3	104.6	104.8	105.4	106.5	107.6	108.6	109.7	110.1
105°	137.0	137.1	137.3	137.4	137.5	137.8	138.4	138.9	139.4	139.9	140.3
107.5°	171.7	171.8	172.0	172.1	172.3	172.5	172.5	172.6	172.7	172.8	173.1
110°	195.2	195.4	195.7	196.0	196.2	196.3	196.1	196.1	195.9	195.7	195.5



TEST NUMBER: P333102-927

CATALOG NUMBER: S124RDIW-S1195D770U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	219.7	219.7	219.8	219.8	219.8	219.8	219.5	219.3	219.0	218.8	218.8
115°	256.4	256.4	256.4	256.4	256.4	256.2	256.0	255.7	255.4	255.2	255.0
117.5°	290.9	291.0	291.1	291.2	291.4	291.3	291.1	291.0	290.7	290.6	290.1
120°	313.9	314.5	315.0	315.5	316.1	316.1	315.8	315.4	315.0	314.6	313.9
122.5°	337.9	338.2	338.3	338.6	338.8	338.8	338.7	338.4	338.3	338.1	337.6
125°	373.4	373.4	373.4	373.4	373.4	373.3	373.1	373.0	372.9	372.7	372.5
127.5°	405.4	405.8	406.2	406.6	407.0	407.1	406.9	406.7	406.5	406.3	406.0
130°	428.0	428.4	428.8	429.2	429.6	429.8	429.8	429.8	429.8	429.8	429.5
132.5°	451.1	451.4	451.6	451.9	452.3	452.3	452.2	452.1	452.0	451.9	451.6
135°	481.6	482.3	483.1	483.9	484.7	485.1	485.1	485.1	485.1	485.1	484.8
137.5°	514.7	515.1	515.4	515.8	516.2	516.4	516.7	516.8	517.1	517.3	516.9
140°	536.8	537.0	537.3	537.6	537.8	538.0	538.0	538.0	538.0	538.0	537.8
142.5°	557.0	557.3	557.5	557.8	558.1	558.2	558.0	557.9	557.9	557.7	557.7
145°	585.0	585.5	586.1	586.6	587.1	587.4	587.6	587.7	587.8	588.0	587.8
147.5°	612.8	613.4	614.0	614.7	615.3	615.5	615.4	615.3	615.2	615.1	615.0
150°	629.7	630.2	630.7	631.3	631.8	632.1	632.1	632.1	632.1	632.1	632.1
152.5°	645.7	646.0	646.3	646.7	647.0	647.1	647.2	647.4	647.5	647.5	647.8
155°	670.3	670.3	670.3	670.3	670.3	670.2	670.0	669.9	669.8	669.7	670.2
157.5°	690.9	690.7	690.5	690.2	690.0	689.9	689.8	689.8	689.8	689.8	690.1
160°	703.2	703.1	702.9	702.8	702.7	702.5	702.4	702.3	702.1	702.0	702.4
162.5°	714.5	714.2	713.8	713.4	713.1	712.9	712.7	712.6	712.5	712.3	713.0
165°	729.7	729.3	728.9	728.5	728.1	727.8	727.5	727.2	727.0	726.7	727.5
167.5°	741.2	740.8	740.2	739.7	739.1	738.8	738.9	738.9	738.9	738.9	739.7
170°	747.9	747.2	746.6	745.9	745.3	745.0	745.1	745.3	745.4	745.5	746.3
172.5°	752.6	752.0	751.5	750.9	750.4	750.1	750.1	750.2	750.2	750.2	751.1
175°	759.1	758.4	757.7	757.1	756.5	756.1	755.9	755.7	755.7	755.5	756.5
177.5°	761.1	760.7	760.1	759.6	759.1	758.8	758.8	758.8	758.8	758.8	759.5
180°	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2



TEST NUMBER: P333102-927

CATALOG NUMBER: S124RDIW-S1195D770U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1652.0	1652.0	1652.0	1652.0	1652.0	1652.0	1652.0	1652.0
2.5°	1645.8	1648.4	1650.8	1651.9	1651.7	1651.5	1651.2	1651.1
5°	1634.9	1637.7	1640.5	1641.6	1641.1	1640.5	1640.0	1639.4
7.5°	1613.1	1614.9	1616.8	1617.2	1616.3	1615.4	1614.5	1613.6
10°	1593.6	1594.7	1595.9	1595.9	1594.7	1593.6	1592.4	1591.3
12.5°	1569.4	1570.1	1570.7	1570.3	1568.8	1567.2	1565.6	1564.0
15°	1526.9	1526.4	1525.8	1524.6	1522.6	1520.6	1518.7	1516.7
17.5°	1475.8	1474.3	1472.7	1470.4	1467.4	1464.4	1461.5	1458.5
20°	1440.1	1437.8	1435.6	1432.7	1429.0	1425.4	1421.7	1418.0
22.5°	1400.4	1397.0	1393.7	1390.5	1387.5	1384.5	1381.6	1378.6
25°	1336.3	1331.6	1326.8	1323.0	1320.2	1317.4	1314.5	1311.8
27.5°	1271.1	1265.2	1259.3	1254.3	1250.3	1246.3	1242.2	1238.2
30°	1224.3	1217.3	1210.3	1204.5	1200.0	1195.6	1191.0	1186.5
32.5°	1176.5	1168.4	1160.2	1154.1	1149.8	1145.5	1141.2	1136.9
35°	1105.4	1095.9	1086.3	1079.0	1074.0	1068.9	1063.8	1058.8
37.5°	1029.0	1018.4	1007.7	999.8	994.7	989.7	984.7	979.6
40°	978.3	966.5	954.7	946.2	941.1	936.0	931.1	926.0
42.5°	928.2	916.2	904.1	895.5	890.2	884.9	879.6	874.3
45°	851.6	837.8	824.0	814.6	809.6	804.5	799.5	794.4
47.5°	774.4	760.2	745.9	735.9	730.4	724.8	719.2	713.7
50°	723.3	709.2	695.1	685.5	680.2	674.8	669.5	664.1
52.5°	672.2	658.0	643.6	633.7	628.2	622.7	617.0	611.5
55°	596.9	582.3	567.7	557.7	552.4	547.0	541.7	536.3
57.5°	523.4	508.5	493.7	484.3	480.2	476.1	472.1	468.0
60°	474.2	459.6	445.0	435.5	430.9	426.4	421.9	417.4
62.5°	425.9	412.4	398.9	390.3	386.7	383.2	379.5	376.0
65°	356.6	344.5	332.4	324.6	321.3	317.9	314.6	311.2
67.5°	292.9	282.5	272.1	265.1	261.3	257.6	253.9	250.2
70°	249.6	240.3	231.1	225.1	222.2	219.4	216.6	213.8
72.5°	210.8	202.9	195.0	189.7	187.1	184.6	182.0	179.4
75°	155.3	148.9	142.4	138.3	136.7	134.9	133.2	131.6
77.5°	109.9	106.1	102.3	100.2	99.7	99.2	98.7	98.2
80°	84.4	83.5	82.6	82.1	81.8	81.5	81.3	81.0
82.5°	65.6	65.0	64.3	63.8	63.6	63.3	63.1	62.7
85°	38.1	37.5	37.0	36.7	36.7	36.7	36.7	36.7
87.5°	16.6	16.6	16.5	16.6	16.9	17.1	17.4	17.7
90°	14.5	15.3	16.1	16.6	16.9	17.1	17.3	17.7
92.5°	24.2	24.7	25.2	25.5	25.7	25.8	26.0	26.1
95°	45.5	45.9	46.3	46.4	46.4	46.4	46.4	46.4
97.5°	71.6	72.1	72.6	72.8	72.8	72.8	72.8	72.8
100°	90.5	90.7	91.0	91.1	91.1	91.1	91.1	91.1
102.5°	110.4	110.8	111.1	111.4	111.5	111.6	111.7	111.9
105°	140.7	141.1	141.5	141.9	142.3	142.7	143.1	143.5
107.5°	173.5	173.8	174.2	174.4	174.4	174.4	174.3	174.3
110°	195.3	195.0	194.7	194.8	195.2	195.6	196.0	196.4



TEST NUMBER: P333102-927

CATALOG NUMBER: S124RDIW-S1195D770U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	218.7	218.6	218.6	218.6	218.7	218.8	218.9	219.0
115°	254.9	254.8	254.6	254.5	254.4	254.3	254.1	254.0
117.5°	289.7	289.2	288.8	288.4	288.2	287.9	287.6	287.4
120°	313.2	312.6	312.0	311.7	312.0	312.3	312.5	312.8
122.5°	337.2	336.8	336.3	335.8	335.3	334.9	334.5	334.0
125°	372.2	372.0	371.7	371.5	371.2	370.9	370.7	370.4
127.5°	405.8	405.5	405.2	405.0	404.8	404.6	404.3	404.2
130°	429.3	429.0	428.7	428.3	427.9	427.3	426.7	426.3
132.5°	451.4	451.1	450.8	450.6	450.4	450.2	450.0	449.8
135°	484.5	484.3	484.0	483.7	483.3	482.9	482.5	482.1
137.5°	516.6	516.3	515.9	515.8	515.9	515.9	516.0	516.1
140°	537.7	537.6	537.4	537.3	537.2	537.0	536.9	536.8
142.5°	557.7	557.6	557.6	557.6	557.5	557.5	557.5	557.5
145°	587.7	587.6	587.4	587.2	586.8	586.4	586.0	585.6
147.5°	614.9	614.8	614.7	614.6	614.4	614.3	614.2	614.0
150°	632.1	632.1	632.1	632.0	631.8	631.7	631.6	631.4
152.5°	648.2	648.5	648.8	648.8	648.5	648.2	647.8	647.5
155°	670.7	671.2	671.8	671.8	671.2	670.7	670.2	669.7
157.5°	690.5	690.9	691.3	691.3	690.9	690.5	690.0	689.5
160°	702.8	703.2	703.6	703.5	702.8	702.1	701.5	700.8
162.5°	713.8	714.5	715.2	715.2	714.5	713.9	713.3	712.6
165°	728.3	729.0	729.8	730.0	729.4	728.9	728.4	727.9
167.5°	740.5	741.2	742.0	742.0	741.2	740.5	739.7	738.8
170°	747.1	747.9	748.7	748.6	747.7	746.8	745.8	745.0
172.5°	752.0	752.9	753.8	753.8	752.8	751.9	751.0	750.1
175°	757.3	758.3	759.1	759.1	758.3	757.3	756.5	755.5
177.5°	760.3	761.0	761.8	761.7	760.8	760.0	759.1	758.4
180°	760.2	760.2	760.2	760.2	760.2	760.2	760.2	760.2

(END OF REPORT)