

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332421-840

Luminaire Tested: **S123RDIW-S560D1030U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332421-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S560D1030U840-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1030 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5767.2 lumens
Efficiency: N/A
Efficacy: 127.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 45.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332421-840

CATALOG NUMBER: S123RDIW-S560D1030U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332421-840

CATALOG NUMBER: S123RDIW-S560D1030U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	45	45	45	37				
1	95	91	87	84	86	83	80	77	67	65	63	53	51	50	40	39	38	32				
2	87	80	74	69	79	73	68	63	59	56	53	47	44	42	35	34	32	27				
3	79	70	63	58	72	64	58	53	52	48	44	41	38	36	31	29	28	23				
4	73	62	55	49	66	57	50	45	47	42	38	37	34	31	28	26	24	20				
5	67	55	48	42	60	51	44	39	42	37	33	33	30	27	25	23	21	18				
6	61	50	42	36	56	46	39	34	38	32	29	30	26	24	23	21	19	16				
7	57	45	37	32	51	41	34	30	34	29	25	27	24	21	21	19	17	14				
8	53	41	33	28	48	37	31	26	31	26	22	25	21	19	20	17	15	13				
9	49	37	30	25	44	34	28	23	28	24	20	23	19	17	18	15	14	11				
10	46	34	27	22	42	31	25	21	26	21	18	21	18	15	17	14	12	10				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10267	10267	10267
5°	10306	10164	10222
10°	10248	10037	10002
15°	10137	9802	9698
20°	9986	9507	9286
25°	9830	9178	8884
30°	9625	8797	8316
35°	9412	8418	7796
40°	9218	7967	7152
45°	8961	7524	6570
50°	8679	7021	5921
55°	8392	6446	5315
60°	8127	5828	4646
65°	7784	5163	3978
70°	7352	4334	3213
75°	6725	3410	3023
80°	5994	3025	2777
85°	5064	2668	2482



TEST NUMBER: P332421-840

CATALOG NUMBER: S123RDIW-S560D1030U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.6	1.6
10°-20°	249.2	4.3
20°-30°	358.8	6.2
30°-40°	404.2	7.0
40°-50°	386.7	6.7
50°-60°	316.7	5.5
60°-70°	213.7	3.7
70°-80°	107.5	1.9
80°-90°	32.3	0.6
90°-100°	84.9	1.5
100°-110°	254.0	4.4
110°-120°	431.9	7.5
120°-130°	568.1	9.9
130°-140°	638.6	11.1
140°-150°	627.7	10.9
150°-160°	528.4	9.2
160°-170°	351.8	6.1
170°-180°	123.2	2.1
0°-30°	697.6	12.1
0°-40°	1101.8	19.1
0°-60°	1805.2	31.3
0°-90°	2158.6	37.4
90°-120°	770.8	13.4
90°-150°	2605.2	45.2
90°-180°	3609.0	62.6
0°-180°	5767.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	954	954	954	954	954	
5°	954	950	941	947	946	90
15°	910	900	880	876	870	256
25°	828	808	773	757	748	381
35°	716	687	641	608	593	448
45°	589	552	494	452	432	454
55°	447	408	344	300	283	401
65°	306	262	203	166	156	302
75°	162	124	82	75	73	172
85°	41	25	22	20	20	46
90°	1	11	24	29	31	6
95°	60	68	76	80	80	68
105°	230	233	242	242	244	247
115°	435	438	436	437	436	430
125°	636	639	637	633	629	567
135°	826	831	831	827	825	636
145°	1002	1004	1007	1006	1002	625
155°	1147	1147	1148	1151	1145	528
165°	1249	1246	1246	1252	1245	352
175°	1299	1296	1295	1301	1294	123
180°	1302	1302	1302	1302	1302	



TEST NUMBER: P332421-840

CATALOG NUMBER: S123RDIW-S560D1030U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	953.8	953.8	953.8	953.8	953.8	953.8	953.8	953.8	953.8	953.8	953.8
2.5°	956.9	956.3	955.8	955.2	954.7	953.6	952.0	950.3	948.7	947.1	948.6
5°	953.8	953.0	952.1	951.3	950.4	949.0	946.8	944.8	942.7	940.7	942.2
7.5°	945.0	944.1	943.1	942.2	941.3	939.5	936.9	934.1	931.4	928.8	929.6
10°	937.6	936.3	935.1	933.9	932.8	930.6	927.6	924.4	921.3	918.3	918.4
12.5°	927.1	925.7	924.3	923.0	921.7	919.2	915.3	911.6	907.8	904.0	903.9
15°	909.7	907.9	905.9	904.0	902.2	898.8	894.0	889.2	884.3	879.6	878.7
17.5°	887.9	885.8	883.5	881.3	879.1	874.9	868.8	862.7	856.6	850.5	848.7
20°	871.8	869.1	866.4	863.5	860.8	856.2	849.6	843.1	836.6	830.0	827.8
22.5°	853.8	850.7	847.6	844.3	841.2	836.2	829.2	822.2	815.4	808.4	805.6
25°	827.7	823.4	819.1	814.9	810.5	804.5	796.5	788.6	780.7	772.8	769.2
27.5°	796.0	791.2	786.5	781.7	777.0	770.2	761.4	752.7	743.9	735.1	730.0
30°	774.4	769.2	764.1	758.9	753.8	746.3	736.7	727.1	717.4	707.8	702.0
32.5°	752.7	746.9	741.0	735.2	729.3	721.3	711.1	700.9	690.7	680.5	674.2
35°	716.3	710.1	704.0	697.8	691.6	683.2	672.5	661.9	651.2	640.6	633.1
37.5°	679.5	672.7	665.8	658.8	652.0	642.9	631.5	620.2	608.7	597.3	589.0
40°	656.0	648.4	640.9	633.3	625.7	615.8	603.7	591.5	579.3	567.0	558.1
42.5°	629.3	621.8	614.3	606.7	599.2	589.1	576.4	563.8	551.2	538.6	528.8
45°	588.7	581.0	573.2	565.5	557.7	547.2	534.0	520.8	507.6	494.3	484.5
47.5°	548.0	539.5	531.0	522.5	514.0	503.2	489.9	476.7	463.4	450.2	439.6
50°	518.3	510.2	502.1	494.0	485.9	474.9	461.0	447.2	433.2	419.3	408.6
52.5°	491.7	482.9	474.1	465.3	456.7	445.4	431.5	417.8	403.9	390.2	379.1
55°	447.2	438.7	430.3	421.8	413.4	401.9	387.3	372.7	358.1	343.5	333.5
57.5°	406.0	396.8	387.6	378.4	369.2	357.3	342.6	328.0	313.3	298.6	289.2
60°	377.5	368.1	358.6	349.1	339.7	327.8	313.6	299.3	285.0	270.7	261.5
62.5°	349.0	339.6	330.1	320.6	311.2	299.3	285.1	270.8	256.5	242.3	233.6
65°	305.6	296.1	286.7	277.2	267.7	256.3	242.9	229.5	216.1	202.7	194.3
67.5°	262.1	252.6	243.0	233.4	223.9	212.7	199.8	186.9	174.1	161.2	154.9
70°	233.6	224.3	215.1	205.8	196.5	185.8	173.8	161.8	149.8	137.7	131.7
72.5°	205.1	196.0	186.8	177.7	168.5	158.5	147.6	136.6	125.7	114.8	109.9
75°	161.7	153.4	145.2	136.9	128.7	119.8	110.4	100.9	91.5	82.0	80.3
77.5°	122.1	114.6	107.1	99.7	92.2	85.4	79.4	73.3	67.2	61.1	60.2
80°	96.7	89.7	82.6	75.5	68.5	63.2	59.6	55.9	52.3	48.8	48.2
82.5°	72.6	66.4	60.4	54.3	48.2	44.3	42.6	41.0	39.3	37.6	37.1
85°	41.0	37.3	33.4	29.7	25.9	23.7	23.2	22.7	22.2	21.6	21.3
87.5°	15.0	14.0	12.9	11.9	10.8	10.6	11.2	11.8	12.3	12.9	13.0
90°	1.0	3.3	5.6	7.9	10.1	12.7	15.7	18.7	21.6	24.5	25.4
92.5°	24.7	26.3	27.9	29.4	30.9	32.5	34.2	36.0	37.6	39.3	40.0
95°	60.4	61.9	63.5	65.1	66.8	68.5	70.3	72.1	73.9	75.7	76.6
97.5°	107.2	108.4	109.6	110.8	112.0	113.2	114.5	115.8	117.1	118.5	119.6
100°	139.2	140.5	141.9	143.2	144.6	145.8	147.0	148.1	149.3	150.4	151.1
102.5°	176.0	176.8	177.6	178.4	179.3	180.4	181.9	183.4	184.9	186.4	187.1
105°	230.2	230.7	231.2	231.6	232.1	233.3	235.3	237.3	239.4	241.5	241.5
107.5°	293.3	293.5	293.8	294.1	294.3	294.9	295.7	296.5	297.3	298.1	298.8
110°	332.5	333.0	333.5	333.9	334.4	334.8	335.3	335.7	336.2	336.6	337.5



TEST NUMBER: P332421-840

CATALOG NUMBER: S123RDIW-S560D1030U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	373.4	373.8	374.0	374.3	374.6	374.7	374.8	374.9	375.0	375.1	376.2
115°	434.8	435.5	436.2	436.9	437.6	437.7	437.2	436.8	436.3	435.9	436.1
117.5°	496.7	497.1	497.6	498.0	498.5	498.4	497.8	497.2	496.6	496.0	495.9
120°	535.1	536.4	537.9	539.2	540.6	540.7	539.5	538.4	537.2	536.1	535.8
122.5°	575.2	576.2	577.2	578.1	579.2	579.4	578.9	578.2	577.6	577.0	576.4
125°	636.4	637.0	637.7	638.4	639.1	639.2	638.7	638.3	637.8	637.4	636.5
127.5°	692.9	694.3	695.8	697.2	698.6	699.1	698.6	698.1	697.6	697.1	695.9
130°	730.5	732.4	734.2	736.0	737.8	738.3	737.7	737.0	736.3	735.6	734.7
132.5°	768.1	769.9	771.7	773.7	775.5	776.1	775.6	775.1	774.6	774.1	773.0
135°	825.7	827.0	828.4	829.7	831.1	831.6	831.4	831.2	831.0	830.7	829.8
137.5°	878.9	880.0	881.1	882.2	883.4	884.2	884.8	885.4	886.1	886.7	885.7
140°	915.6	916.9	918.0	919.1	920.2	920.9	921.1	921.4	921.6	921.8	921.6
142.5°	949.3	950.4	951.5	952.6	953.8	954.5	954.9	955.3	955.8	956.2	955.9
145°	1001.6	1002.1	1002.5	1003.0	1003.4	1004.0	1004.7	1005.4	1006.0	1006.7	1006.5
147.5°	1047.4	1048.2	1049.0	1050.0	1050.8	1051.5	1052.1	1052.8	1053.4	1054.0	1054.0
150°	1079.3	1079.8	1080.3	1080.8	1081.2	1081.7	1082.1	1082.6	1083.0	1083.5	1083.5
152.5°	1105.6	1106.2	1106.8	1107.5	1108.1	1108.5	1108.8	1109.1	1109.4	1109.6	1110.0
155°	1146.9	1146.9	1146.9	1146.9	1146.9	1147.0	1147.2	1147.5	1147.7	1147.9	1148.8
157.5°	1182.1	1181.8	1181.5	1181.2	1181.0	1180.9	1181.1	1181.3	1181.5	1181.6	1182.7
160°	1204.2	1203.8	1203.3	1202.9	1202.3	1202.1	1202.1	1202.1	1202.1	1202.1	1203.3
162.5°	1223.9	1223.2	1222.5	1221.9	1221.3	1221.0	1221.2	1221.4	1221.6	1221.8	1222.9
165°	1249.2	1248.5	1247.9	1247.2	1246.5	1246.2	1246.2	1246.2	1246.2	1246.2	1247.5
167.5°	1269.5	1268.6	1267.7	1266.8	1265.9	1265.5	1265.7	1265.9	1266.1	1266.2	1267.6
170°	1280.9	1280.0	1279.1	1278.2	1277.3	1276.9	1276.9	1276.9	1276.9	1276.9	1278.4
172.5°	1289.9	1289.0	1288.1	1287.2	1286.3	1285.9	1285.9	1285.9	1285.9	1285.9	1287.3
175°	1299.4	1298.5	1297.6	1296.7	1295.8	1295.3	1295.3	1295.3	1295.3	1295.3	1296.7
177.5°	1303.2	1302.5	1301.8	1301.0	1300.3	1300.0	1300.0	1300.0	1300.0	1300.0	1301.0
180°	1302.4	1302.4	1302.4	1302.4	1302.4	1302.4	1302.4	1302.4	1302.4	1302.4	1302.4



TEST NUMBER: P332421-840

CATALOG NUMBER: S123RDIW-S560D1030U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	953.8	953.8	953.8	953.8	953.8	953.8	953.8	953.8
2.5°	950.1	951.6	953.1	953.7	953.4	953.1	952.9	952.6
5°	943.7	945.3	946.8	947.5	947.2	946.7	946.4	946.0
7.5°	930.5	931.3	932.2	932.3	931.7	931.2	930.6	930.0
10°	918.6	918.8	918.9	918.6	917.8	916.9	916.0	915.1
12.5°	903.8	903.7	903.6	903.0	902.0	901.0	900.1	899.1
15°	877.9	877.0	876.2	875.0	873.8	872.7	871.5	870.3
17.5°	846.9	845.1	843.1	841.4	839.6	837.8	836.0	834.2
20°	825.6	823.3	821.1	819.0	816.9	814.9	812.7	810.7
22.5°	802.8	800.0	797.3	794.9	792.9	791.0	789.1	787.2
25°	765.6	761.9	758.4	755.6	753.8	751.8	749.9	748.0
27.5°	725.0	720.0	715.0	711.0	708.1	705.3	702.4	699.4
30°	696.1	690.2	684.5	680.1	677.4	674.7	671.9	669.1
32.5°	667.8	661.4	655.0	650.4	647.5	644.6	641.7	638.8
35°	625.7	618.3	611.0	605.7	602.6	599.6	596.4	593.3
37.5°	580.6	572.2	563.8	557.7	553.9	550.1	546.2	542.4
40°	549.2	540.2	531.3	524.8	520.9	516.9	513.0	509.0
42.5°	519.1	509.3	499.5	492.8	489.3	485.7	482.2	478.7
45°	474.7	464.9	455.1	448.2	444.0	439.9	435.8	431.6
47.5°	428.9	418.3	407.6	400.4	396.8	393.0	389.4	385.7
50°	398.0	387.3	376.7	369.3	365.4	361.4	357.5	353.6
52.5°	368.1	357.0	345.9	338.6	335.1	331.5	328.0	324.5
55°	323.6	313.6	303.6	296.9	293.5	290.0	286.6	283.2
57.5°	279.7	270.3	260.9	254.8	251.9	248.9	246.0	243.1
60°	252.2	242.9	233.6	227.5	224.6	221.7	218.7	215.8
62.5°	224.8	216.1	207.3	201.5	198.4	195.3	192.3	189.2
65°	185.8	177.4	169.0	163.8	162.0	160.1	158.1	156.2
67.5°	148.7	142.3	136.0	131.9	129.9	127.8	125.8	123.8
70°	125.6	119.7	113.6	109.7	107.8	105.9	104.0	102.1
72.5°	104.9	100.1	95.1	92.3	91.5	90.7	89.9	89.1
75°	78.6	76.9	75.1	74.1	73.7	73.4	73.0	72.7
77.5°	59.3	58.4	57.4	56.8	56.5	56.0	55.7	55.3
80°	47.7	47.2	46.7	46.3	45.9	45.5	45.2	44.8
82.5°	36.6	36.1	35.5	35.2	35.1	35.1	35.0	34.9
85°	21.0	20.6	20.3	20.1	20.1	20.1	20.1	20.1
87.5°	13.0	13.1	13.1	13.1	13.1	13.0	13.0	12.9
90°	26.4	27.3	28.2	28.9	29.3	29.8	30.2	30.7
92.5°	40.7	41.5	42.2	42.4	42.1	41.9	41.6	41.3
95°	77.6	78.5	79.4	79.8	79.8	79.8	79.8	79.8
97.5°	120.6	121.6	122.7	123.1	123.0	123.0	122.9	122.8
100°	151.8	152.5	153.1	153.7	154.1	154.6	155.0	155.5
102.5°	187.7	188.4	189.1	189.5	189.3	189.2	189.1	189.0
105°	241.5	241.5	241.5	241.7	242.2	242.6	243.1	243.5
107.5°	299.6	300.3	301.0	301.2	301.0	300.7	300.4	300.1
110°	338.4	339.3	340.2	340.4	340.0	339.5	339.1	338.6



TEST NUMBER: P332421-840

CATALOG NUMBER: S123RDIW-S560D1030U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	377.3	378.3	379.4	379.9	379.8	379.7	379.7	379.6
115°	436.3	436.6	436.8	436.8	436.6	436.3	436.1	435.9
117.5°	495.9	495.8	495.8	495.4	494.8	494.2	493.5	492.9
120°	535.6	535.4	535.2	534.8	534.4	533.9	533.5	533.0
122.5°	575.8	575.2	574.7	574.0	573.4	572.8	572.2	571.5
125°	635.6	634.7	633.8	632.9	632.0	631.1	630.2	629.2
127.5°	694.6	693.4	692.1	690.8	689.8	688.8	687.7	686.7
130°	733.8	732.9	732.0	730.7	729.1	727.5	726.0	724.4
132.5°	771.9	770.8	769.7	768.6	767.3	766.1	764.9	763.7
135°	828.9	828.0	827.1	826.5	826.0	825.6	825.1	824.7
137.5°	884.7	883.7	882.8	881.9	881.0	880.2	879.3	878.5
140°	921.4	921.1	920.9	920.0	918.4	916.9	915.2	913.6
142.5°	955.7	955.5	955.3	954.5	953.3	952.1	950.9	949.7
145°	1006.3	1006.0	1005.8	1005.2	1004.3	1003.4	1002.5	1001.6
147.5°	1054.0	1054.0	1054.0	1053.3	1052.0	1050.6	1049.2	1047.8
150°	1083.5	1083.5	1083.5	1082.8	1081.5	1080.1	1078.7	1077.3
152.5°	1110.3	1110.8	1111.2	1110.8	1109.5	1108.3	1107.1	1106.0
155°	1149.7	1150.6	1151.5	1151.2	1149.6	1148.0	1146.5	1144.9
157.5°	1183.6	1184.6	1185.5	1185.4	1184.1	1182.9	1181.5	1180.2
160°	1204.5	1205.6	1206.7	1206.8	1205.9	1205.0	1204.1	1203.2
162.5°	1224.1	1225.2	1226.4	1226.2	1224.8	1223.2	1221.8	1220.3
165°	1248.9	1250.2	1251.6	1251.5	1249.9	1248.3	1246.7	1245.2
167.5°	1269.0	1270.4	1271.8	1271.8	1270.4	1269.0	1267.6	1266.2
170°	1280.0	1281.6	1283.2	1283.2	1281.6	1280.0	1278.4	1276.9
172.5°	1288.7	1290.1	1291.5	1291.4	1289.8	1288.2	1286.6	1285.1
175°	1298.0	1299.4	1300.7	1300.6	1299.0	1297.4	1295.9	1294.2
177.5°	1302.1	1303.2	1304.3	1304.2	1302.9	1301.7	1300.4	1299.2
180°	1302.4	1302.4	1302.4	1302.4	1302.4	1302.4	1302.4	1302.4

(END OF REPORT)