

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332424-840

Luminaire Tested: **S123RDIW-S560D1320U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332424-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S560D1320U840-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1320 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7489.6 lumens
Efficiency: N/A
Efficacy: 139.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332424-840

CATALOG NUMBER: S123RDIW-S560D1320U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332424-840

CATALOG NUMBER: S123RDIW-S560D1320U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	72	72	72	53	53	53	37	37	37
1	93	89	85	82	83	80	77	74	63	61	59	47	46	45	33	32	31
2	85	78	72	67	76	70	65	61	55	52	49	42	39	38	29	28	27
3	78	69	62	56	69	62	56	51	49	45	41	37	34	32	26	24	23
4	71	61	53	47	63	55	48	43	43	39	35	33	30	27	23	21	20
5	65	54	46	41	58	49	42	37	39	34	30	30	26	24	21	19	17
6	60	48	41	35	54	44	37	32	35	30	26	27	23	21	19	17	15
7	55	44	36	31	49	39	33	28	32	27	23	24	21	18	17	15	14
8	51	39	32	27	46	36	29	25	29	24	21	22	19	16	16	14	12
9	48	36	29	24	43	33	26	22	26	22	18	20	17	15	15	13	11
10	44	33	26	21	40	30	24	20	24	20	16	19	15	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10267	10267	10267
5°	10306	10164	10222
10°	10248	10037	10002
15°	10137	9802	9698
20°	9986	9507	9286
25°	9830	9178	8884
30°	9625	8797	8316
35°	9412	8418	7796
40°	9218	7967	7152
45°	8961	7524	6570
50°	8679	7021	5921
55°	8392	6446	5315
60°	8127	5828	4646
65°	7784	5163	3978
70°	7352	4334	3213
75°	6725	3410	3023
80°	5994	3025	2777
85°	5064	2668	2482



TEST NUMBER: P332424-840

CATALOG NUMBER: S123RDIW-S560D1320U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.6	1.2
10°-20°	249.2	3.3
20°-30°	358.8	4.8
30°-40°	404.2	5.4
40°-50°	386.7	5.2
50°-60°	316.7	4.2
60°-70°	213.7	2.9
70°-80°	107.5	1.4
80°-90°	33.3	0.4
90°-100°	63.5	0.8
100°-110°	302.9	4.0
110°-120°	727.5	9.7
120°-130°	926.3	12.4
130°-140°	989.8	13.2
140°-150°	925.5	12.4
150°-160°	746.6	10.0
160°-170°	481.8	6.4
170°-180°	166.1	2.2
0°-30°	697.6	9.3
0°-40°	1101.8	14.7
0°-60°	1805.2	24.1
0°-90°	2159.6	28.8
90°-120°	1093.9	14.6
90°-150°	3935.5	52.5
90°-180°	5330.0	71.2
0°-180°	7489.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	954	954	954	954	954	
5°	954	950	941	947	946	90
15°	910	900	880	876	870	256
25°	828	808	773	757	748	381
35°	716	687	641	608	593	448
45°	589	552	494	452	432	454
55°	447	408	344	300	283	401
65°	306	262	203	166	156	302
75°	162	124	82	75	73	172
85°	41	25	22	20	20	46
90°	1	14	31	36	39	6
95°	79	30	40	49	49	98
105°	387	394	284	67	57	410
115°	726	734	745	758	764	716
125°	1023	1033	1039	1041	1044	913
135°	1274	1282	1287	1290	1287	980
145°	1470	1479	1482	1484	1484	920
155°	1619	1617	1618	1624	1617	746
165°	1708	1704	1702	1712	1704	482
175°	1748	1742	1743	1751	1741	166
180°	1748	1748	1748	1748	1748	



TEST NUMBER: P332424-840

CATALOG NUMBER: S123RDIW-S560D1320U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	953.8	953.8	953.8	953.8	953.8	953.8	953.8	953.8	953.8	953.8	953.8
2.5°	956.9	956.3	955.8	955.2	954.7	953.6	952.0	950.3	948.7	947.1	948.6
5°	953.8	953.0	952.1	951.3	950.4	949.0	946.8	944.8	942.7	940.7	942.2
7.5°	945.0	944.1	943.1	942.2	941.3	939.5	936.9	934.1	931.4	928.8	929.6
10°	937.6	936.3	935.1	933.9	932.8	930.6	927.6	924.4	921.3	918.3	918.4
12.5°	927.1	925.7	924.3	923.0	921.7	919.2	915.3	911.6	907.8	904.0	903.9
15°	909.7	907.9	905.9	904.0	902.2	898.8	894.0	889.2	884.3	879.6	878.7
17.5°	887.9	885.8	883.5	881.3	879.1	874.9	868.8	862.7	856.6	850.5	848.7
20°	871.8	869.1	866.4	863.5	860.8	856.2	849.6	843.1	836.6	830.0	827.8
22.5°	853.8	850.7	847.6	844.3	841.2	836.2	829.2	822.2	815.4	808.4	805.6
25°	827.7	823.4	819.1	814.9	810.5	804.5	796.5	788.6	780.7	772.8	769.2
27.5°	796.0	791.2	786.5	781.7	777.0	770.2	761.4	752.7	743.9	735.1	730.0
30°	774.4	769.2	764.1	758.9	753.8	746.3	736.7	727.1	717.4	707.8	702.0
32.5°	752.7	746.9	741.0	735.2	729.3	721.3	711.1	700.9	690.7	680.5	674.2
35°	716.3	710.1	704.0	697.8	691.6	683.2	672.5	661.9	651.2	640.6	633.1
37.5°	679.5	672.7	665.8	658.8	652.0	642.9	631.5	620.2	608.7	597.3	589.0
40°	656.0	648.4	640.9	633.3	625.7	615.8	603.7	591.5	579.3	567.0	558.1
42.5°	629.3	621.8	614.3	606.7	599.2	589.1	576.4	563.8	551.2	538.6	528.8
45°	588.7	581.0	573.2	565.5	557.7	547.2	534.0	520.8	507.6	494.3	484.5
47.5°	548.0	539.5	531.0	522.5	514.0	503.2	489.9	476.7	463.4	450.2	439.6
50°	518.3	510.2	502.1	494.0	485.9	474.9	461.0	447.2	433.2	419.3	408.6
52.5°	491.7	482.9	474.1	465.3	456.7	445.4	431.5	417.8	403.9	390.2	379.1
55°	447.2	438.7	430.3	421.8	413.4	401.9	387.3	372.7	358.1	343.5	333.5
57.5°	406.0	396.8	387.6	378.4	369.2	357.3	342.6	328.0	313.3	298.6	289.2
60°	377.5	368.1	358.6	349.1	339.7	327.8	313.6	299.3	285.0	270.7	261.5
62.5°	349.0	339.6	330.1	320.6	311.2	299.3	285.1	270.8	256.5	242.3	233.6
65°	305.6	296.1	286.7	277.2	267.7	256.3	242.9	229.5	216.1	202.7	194.3
67.5°	262.1	252.6	243.0	233.4	223.9	212.7	199.8	186.9	174.1	161.2	154.9
70°	233.6	224.3	215.1	205.8	196.5	185.8	173.8	161.8	149.8	137.7	131.7
72.5°	205.1	196.0	186.8	177.7	168.5	158.5	147.6	136.6	125.7	114.8	109.9
75°	161.7	153.4	145.2	136.9	128.7	119.8	110.4	100.9	91.5	82.0	80.3
77.5°	122.1	114.6	107.1	99.7	92.2	85.4	79.4	73.3	67.2	61.1	60.2
80°	96.7	89.7	82.6	75.5	68.5	63.2	59.6	55.9	52.3	48.8	48.2
82.5°	72.6	66.4	60.4	54.3	48.2	44.3	42.6	41.0	39.3	37.6	37.1
85°	41.0	37.3	33.4	29.7	25.9	23.7	23.2	22.7	22.2	21.6	21.3
87.5°	15.1	14.1	13.2	12.3	11.4	11.3	12.0	12.8	13.5	14.2	14.3
90°	1.3	4.1	7.1	10.0	12.8	16.2	19.9	23.6	27.4	31.2	32.3
92.5°	24.1	23.3	22.5	21.7	20.9	21.9	24.7	27.6	30.4	33.2	35.0
95°	79.2	67.4	55.5	43.7	31.9	27.6	30.7	33.9	37.1	40.3	42.3
97.5°	159.2	153.9	148.6	143.3	137.9	124.9	104.1	83.4	62.6	41.8	44.1
100°	219.4	225.2	231.0	236.7	242.6	222.9	177.9	132.9	87.9	42.8	45.1
102.5°	288.0	292.2	296.3	300.4	304.7	282.2	233.0	183.8	134.6	85.4	78.3
105°	387.0	390.1	393.3	396.5	399.6	388.3	362.2	336.3	310.3	284.4	233.3
107.5°	491.4	493.9	496.4	499.0	501.5	504.8	509.0	513.0	517.2	521.2	483.7
110°	561.0	563.3	565.5	567.8	570.2	572.9	576.1	579.3	582.5	585.6	576.1



TEST NUMBER: P332424-840

CATALOG NUMBER: S123RDIW-S560D1320U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	627.4	629.5	631.6	633.7	635.7	638.3	641.6	644.7	647.9	651.1	651.3
115°	725.9	727.6	729.3	731.0	732.8	735.0	737.5	740.1	742.8	745.4	748.2
117.5°	821.2	823.3	825.5	827.6	829.7	831.4	832.7	834.1	835.5	836.8	839.1
120°	880.4	883.0	885.6	888.2	890.8	892.5	893.3	894.2	895.1	896.0	898.3
122.5°	940.7	942.8	944.9	947.1	949.2	950.8	951.9	953.0	954.1	955.2	956.8
125°	1023.2	1025.5	1027.8	1030.2	1032.5	1034.2	1035.3	1036.5	1037.6	1038.8	1039.4
127.5°	1103.2	1105.5	1107.8	1110.1	1112.5	1114.3	1115.7	1117.1	1118.4	1119.8	1120.7
130°	1153.1	1155.4	1157.7	1160.0	1162.4	1164.1	1165.2	1166.4	1167.5	1168.6	1169.8
132.5°	1200.8	1203.2	1205.5	1207.8	1210.1	1211.7	1212.6	1213.6	1214.5	1215.4	1216.6
135°	1273.8	1275.6	1277.3	1279.0	1280.8	1282.2	1283.3	1284.5	1285.7	1286.9	1287.7
137.5°	1336.2	1338.4	1340.6	1342.7	1344.9	1346.4	1347.0	1347.7	1348.3	1348.9	1350.3
140°	1377.8	1379.5	1381.2	1382.9	1384.6	1385.9	1386.8	1387.7	1388.6	1389.4	1390.6
142.5°	1416.1	1417.9	1419.7	1421.4	1423.1	1424.4	1425.2	1426.1	1426.9	1427.8	1428.8
145°	1470.0	1472.0	1474.0	1476.0	1478.0	1479.3	1479.9	1480.5	1481.1	1481.6	1482.2
147.5°	1520.6	1521.9	1523.2	1524.5	1525.9	1526.8	1527.4	1527.9	1528.5	1529.1	1529.7
150°	1551.8	1552.6	1553.5	1554.3	1555.2	1555.9	1556.5	1557.0	1557.6	1558.2	1558.8
152.5°	1579.7	1580.1	1580.5	1580.9	1581.3	1581.8	1582.2	1582.5	1582.8	1583.2	1584.2
155°	1619.2	1618.7	1618.1	1617.5	1616.9	1616.8	1617.1	1617.4	1617.7	1617.9	1619.4
157.5°	1649.9	1649.8	1649.8	1649.7	1649.6	1649.5	1649.2	1648.9	1648.6	1648.3	1650.0
160°	1668.6	1668.3	1668.0	1667.7	1667.4	1667.2	1666.9	1666.6	1666.3	1666.0	1667.7
162.5°	1686.3	1685.5	1684.8	1683.9	1683.2	1682.7	1682.4	1682.1	1681.8	1681.5	1683.5
165°	1707.6	1706.7	1705.8	1705.0	1704.0	1703.5	1703.2	1702.9	1702.6	1702.3	1704.7
167.5°	1724.1	1723.0	1721.8	1720.7	1719.5	1719.0	1719.0	1719.0	1719.0	1719.0	1721.3
170°	1733.5	1732.3	1731.2	1730.1	1728.9	1728.3	1728.3	1728.3	1728.3	1728.3	1730.6
172.5°	1739.8	1738.4	1737.0	1735.6	1734.2	1733.6	1733.8	1734.1	1734.3	1734.5	1736.9
175°	1747.8	1746.4	1744.9	1743.4	1742.0	1741.4	1741.7	1742.0	1742.3	1742.6	1744.6
177.5°	1749.9	1748.7	1747.6	1746.5	1745.2	1744.8	1745.0	1745.2	1745.5	1745.8	1747.6
180°	1747.8	1747.8	1747.8	1747.8	1747.8	1747.8	1747.8	1747.8	1747.8	1747.8	1747.8



TEST NUMBER: P332424-840

CATALOG NUMBER: S123RDIW-S560D1320U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	953.8	953.8	953.8	953.8	953.8	953.8	953.8	953.8
2.5°	950.1	951.6	953.1	953.7	953.4	953.1	952.9	952.6
5°	943.7	945.3	946.8	947.5	947.2	946.7	946.4	946.0
7.5°	930.5	931.3	932.2	932.3	931.7	931.2	930.6	930.0
10°	918.6	918.8	918.9	918.6	917.8	916.9	916.0	915.1
12.5°	903.8	903.7	903.6	903.0	902.0	901.0	900.1	899.1
15°	877.9	877.0	876.2	875.0	873.8	872.7	871.5	870.3
17.5°	846.9	845.1	843.1	841.4	839.6	837.8	836.0	834.2
20°	825.6	823.3	821.1	819.0	816.9	814.9	812.7	810.7
22.5°	802.8	800.0	797.3	794.9	792.9	791.0	789.1	787.2
25°	765.6	761.9	758.4	755.6	753.8	751.8	749.9	748.0
27.5°	725.0	720.0	715.0	711.0	708.1	705.3	702.4	699.4
30°	696.1	690.2	684.5	680.1	677.4	674.7	671.9	669.1
32.5°	667.8	661.4	655.0	650.4	647.5	644.6	641.7	638.8
35°	625.7	618.3	611.0	605.7	602.6	599.6	596.4	593.3
37.5°	580.6	572.2	563.8	557.7	553.9	550.1	546.2	542.4
40°	549.2	540.2	531.3	524.8	520.9	516.9	513.0	509.0
42.5°	519.1	509.3	499.5	492.8	489.3	485.7	482.2	478.7
45°	474.7	464.9	455.1	448.2	444.0	439.9	435.8	431.6
47.5°	428.9	418.3	407.6	400.4	396.8	393.0	389.4	385.7
50°	398.0	387.3	376.7	369.3	365.4	361.4	357.5	353.6
52.5°	368.1	357.0	345.9	338.6	335.1	331.5	328.0	324.5
55°	323.6	313.6	303.6	296.9	293.5	290.0	286.6	283.2
57.5°	279.7	270.3	260.9	254.8	251.9	248.9	246.0	243.1
60°	252.2	242.9	233.6	227.5	224.6	221.7	218.7	215.8
62.5°	224.8	216.1	207.3	201.5	198.4	195.3	192.3	189.2
65°	185.8	177.4	169.0	163.8	162.0	160.1	158.1	156.2
67.5°	148.7	142.3	136.0	131.9	129.9	127.8	125.8	123.8
70°	125.6	119.7	113.6	109.7	107.8	105.9	104.0	102.1
72.5°	104.9	100.1	95.1	92.3	91.5	90.7	89.9	89.1
75°	78.6	76.9	75.1	74.1	73.7	73.4	73.0	72.7
77.5°	59.3	58.4	57.4	56.8	56.5	56.0	55.7	55.3
80°	47.7	47.2	46.7	46.3	45.9	45.5	45.2	44.8
82.5°	36.6	36.1	35.5	35.2	35.1	35.1	35.0	34.9
85°	21.0	20.6	20.3	20.1	20.1	20.1	20.1	20.1
87.5°	14.4	14.5	14.6	14.6	14.6	14.6	14.6	14.6
90°	33.4	34.6	35.7	36.7	37.3	37.8	38.4	39.0
92.5°	37.0	38.8	40.6	41.7	42.1	42.4	42.7	43.1
95°	44.3	46.4	48.4	49.4	49.4	49.4	49.4	49.4
97.5°	46.5	48.8	51.0	52.3	52.6	52.9	53.2	53.5
100°	47.5	49.8	52.1	53.4	53.6	53.9	54.2	54.5
102.5°	71.1	63.9	56.9	53.5	54.0	54.5	55.0	55.5
105°	182.2	131.2	80.1	54.8	55.4	55.9	56.6	57.2
107.5°	446.4	408.9	371.4	333.5	295.0	256.4	217.9	179.5
110°	566.5	557.0	547.5	522.1	480.9	439.6	398.4	357.1



TEST NUMBER: P332424-840

CATALOG NUMBER: S123RDIW-S560D1320U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	651.5	651.6	651.8	647.5	638.7	630.1	621.4	612.7
115°	751.1	754.0	756.9	758.9	760.0	761.2	762.3	763.6
117.5°	841.4	843.6	846.0	847.3	847.5	847.7	848.0	848.2
120°	900.6	902.9	905.2	906.4	906.4	906.4	906.4	906.4
122.5°	958.5	960.1	961.7	962.6	962.8	963.0	963.3	963.5
125°	1040.0	1040.6	1041.1	1041.7	1042.3	1042.9	1043.4	1044.0
127.5°	1121.7	1122.6	1123.6	1123.7	1123.2	1122.6	1122.0	1121.4
130°	1170.9	1172.2	1173.3	1173.6	1173.0	1172.5	1171.8	1171.2
132.5°	1217.7	1218.9	1220.0	1220.2	1219.4	1218.6	1217.8	1217.0
135°	1288.6	1289.4	1290.3	1290.3	1289.4	1288.6	1287.7	1286.9
137.5°	1351.7	1353.0	1354.4	1354.8	1354.2	1353.7	1353.1	1352.5
140°	1391.7	1392.9	1394.0	1394.3	1393.7	1393.1	1392.6	1392.0
142.5°	1429.7	1430.6	1431.6	1431.6	1430.8	1430.0	1429.2	1428.4
145°	1482.8	1483.3	1483.9	1484.2	1484.2	1484.2	1484.2	1484.2
147.5°	1530.2	1530.9	1531.5	1531.1	1529.7	1528.4	1527.1	1525.7
150°	1559.3	1559.9	1560.5	1560.3	1559.5	1558.6	1557.8	1556.9
152.5°	1585.2	1586.3	1587.3	1587.2	1585.8	1584.5	1583.2	1581.9
155°	1620.8	1622.2	1623.8	1623.6	1621.8	1620.1	1618.4	1616.7
157.5°	1651.8	1653.6	1655.3	1655.0	1652.7	1650.5	1648.2	1646.0
160°	1669.4	1671.2	1672.9	1672.7	1670.7	1668.7	1666.7	1664.7
162.5°	1685.5	1687.5	1689.4	1689.5	1687.7	1686.0	1684.2	1682.3
165°	1707.0	1709.3	1711.6	1711.7	1709.7	1707.7	1705.7	1703.6
167.5°	1723.6	1725.9	1728.2	1728.2	1725.9	1723.6	1721.3	1719.0
170°	1732.9	1735.3	1737.6	1737.6	1735.3	1732.9	1730.6	1728.3
172.5°	1739.2	1741.5	1743.8	1743.6	1741.1	1738.6	1736.1	1733.5
175°	1746.7	1748.7	1750.7	1750.5	1748.3	1746.0	1743.6	1741.3
177.5°	1749.4	1751.3	1753.1	1752.9	1750.6	1748.3	1746.0	1743.6
180°	1747.8	1747.8	1747.8	1747.8	1747.8	1747.8	1747.8	1747.8

(END OF REPORT)