

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332425-840

Luminaire Tested: **S123RDIW-S560D1320U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332425-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S560D1320U840-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1320 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6779.3 lumens
Efficiency: N/A
Efficacy: 126.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332425-840

CATALOG NUMBER: S123RDIW-S560D1320U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332425-840

CATALOG NUMBER: S123RDIW-S560D1320U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	73	73	73	56	56	56	39	39	39	32
1	94	90	86	83	84	81	78	75	64	62	60	49	48	47	35	34	34	27
2	86	79	73	68	77	71	66	62	57	53	50	43	41	39	31	30	29	23
3	78	69	62	57	70	63	57	52	50	46	42	38	36	33	28	26	25	20
4	72	61	54	48	64	55	49	44	45	40	36	34	31	29	25	23	21	17
5	66	55	47	41	59	49	43	38	40	35	31	31	28	25	23	20	19	15
6	60	49	41	36	54	44	38	33	36	31	27	28	24	22	20	18	16	13
7	56	44	36	31	50	40	33	29	32	28	24	25	22	19	19	16	15	12
8	52	40	32	27	47	36	30	25	30	25	21	23	20	17	17	15	13	11
9	48	36	29	24	43	33	27	23	27	22	19	21	18	15	16	14	12	10
10	45	33	26	22	40	30	24	20	25	20	17	20	16	14	15	12	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10267	10267	10267
5°	10306	10164	10222
10°	10248	10037	10002
15°	10137	9802	9698
20°	9986	9507	9286
25°	9830	9178	8884
30°	9625	8797	8316
35°	9412	8418	7796
40°	9218	7967	7152
45°	8961	7524	6570
50°	8679	7021	5921
55°	8392	6446	5315
60°	8127	5828	4646
65°	7784	5163	3978
70°	7352	4334	3213
75°	6725	3410	3023
80°	5994	3025	2777
85°	5064	2668	2482



TEST NUMBER: P332425-840

CATALOG NUMBER: S123RDIW-S560D1320U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.6	1.3
10°-20°	249.2	3.7
20°-30°	358.8	5.3
30°-40°	404.2	6.0
40°-50°	386.7	5.7
50°-60°	316.7	4.7
60°-70°	213.7	3.2
70°-80°	107.5	1.6
80°-90°	33.4	0.5
90°-100°	108.6	1.6
100°-110°	325.1	4.8
110°-120°	553.0	8.2
120°-130°	727.3	10.7
130°-140°	817.5	12.1
140°-150°	803.6	11.9
150°-160°	676.5	10.0
160°-170°	450.3	6.6
170°-180°	157.7	2.3
0°-30°	697.6	10.3
0°-40°	1101.8	16.3
0°-60°	1805.2	26.6
0°-90°	2159.7	31.9
90°-120°	986.7	14.6
90°-150°	3335.1	49.2
90°-180°	4620.0	68.1
0°-180°	6779.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	954	954	954	954	954	
5°	954	950	941	947	946	90
15°	910	900	880	876	870	256
25°	828	808	773	757	748	381
35°	716	687	641	608	593	448
45°	589	552	494	452	432	454
55°	447	408	344	300	283	401
65°	306	262	203	166	156	302
75°	162	124	82	75	73	172
85°	41	25	22	20	20	46
90°	1	15	31	37	39	7
95°	77	87	97	102	102	87
105°	295	298	309	309	312	316
115°	557	560	558	559	558	551
125°	815	818	816	811	806	726
135°	1057	1064	1064	1058	1056	814
145°	1282	1285	1289	1287	1282	801
155°	1468	1468	1470	1474	1466	676
165°	1599	1596	1595	1602	1594	451
175°	1663	1658	1658	1665	1657	158
180°	1667	1667	1667	1667	1667	



TEST NUMBER: P332425-840

CATALOG NUMBER: S123RDIW-S560D1320U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	953.8	953.8	953.8	953.8	953.8	953.8	953.8	953.8	953.8	953.8	953.8
2.5°	956.9	956.3	955.8	955.2	954.7	953.6	952.0	950.3	948.7	947.1	948.6
5°	953.8	953.0	952.1	951.3	950.4	949.0	946.8	944.8	942.7	940.7	942.2
7.5°	945.0	944.1	943.1	942.2	941.3	939.5	936.9	934.1	931.4	928.8	929.6
10°	937.6	936.3	935.1	933.9	932.8	930.6	927.6	924.4	921.3	918.3	918.4
12.5°	927.1	925.7	924.3	923.0	921.7	919.2	915.3	911.6	907.8	904.0	903.9
15°	909.7	907.9	905.9	904.0	902.2	898.8	894.0	889.2	884.3	879.6	878.7
17.5°	887.9	885.8	883.5	881.3	879.1	874.9	868.8	862.7	856.6	850.5	848.7
20°	871.8	869.1	866.4	863.5	860.8	856.2	849.6	843.1	836.6	830.0	827.8
22.5°	853.8	850.7	847.6	844.3	841.2	836.2	829.2	822.2	815.4	808.4	805.6
25°	827.7	823.4	819.1	814.9	810.5	804.5	796.5	788.6	780.7	772.8	769.2
27.5°	796.0	791.2	786.5	781.7	777.0	770.2	761.4	752.7	743.9	735.1	730.0
30°	774.4	769.2	764.1	758.9	753.8	746.3	736.7	727.1	717.4	707.8	702.0
32.5°	752.7	746.9	741.0	735.2	729.3	721.3	711.1	700.9	690.7	680.5	674.2
35°	716.3	710.1	704.0	697.8	691.6	683.2	672.5	661.9	651.2	640.6	633.1
37.5°	679.5	672.7	665.8	658.8	652.0	642.9	631.5	620.2	608.7	597.3	589.0
40°	656.0	648.4	640.9	633.3	625.7	615.8	603.7	591.5	579.3	567.0	558.1
42.5°	629.3	621.8	614.3	606.7	599.2	589.1	576.4	563.8	551.2	538.6	528.8
45°	588.7	581.0	573.2	565.5	557.7	547.2	534.0	520.8	507.6	494.3	484.5
47.5°	548.0	539.5	531.0	522.5	514.0	503.2	489.9	476.7	463.4	450.2	439.6
50°	518.3	510.2	502.1	494.0	485.9	474.9	461.0	447.2	433.2	419.3	408.6
52.5°	491.7	482.9	474.1	465.3	456.7	445.4	431.5	417.8	403.9	390.2	379.1
55°	447.2	438.7	430.3	421.8	413.4	401.9	387.3	372.7	358.1	343.5	333.5
57.5°	406.0	396.8	387.6	378.4	369.2	357.3	342.6	328.0	313.3	298.6	289.2
60°	377.5	368.1	358.6	349.1	339.7	327.8	313.6	299.3	285.0	270.7	261.5
62.5°	349.0	339.6	330.1	320.6	311.2	299.3	285.1	270.8	256.5	242.3	233.6
65°	305.6	296.1	286.7	277.2	267.7	256.3	242.9	229.5	216.1	202.7	194.3
67.5°	262.1	252.6	243.0	233.4	223.9	212.7	199.8	186.9	174.1	161.2	154.9
70°	233.6	224.3	215.1	205.8	196.5	185.8	173.8	161.8	149.8	137.7	131.7
72.5°	205.1	196.0	186.8	177.7	168.5	158.5	147.6	136.6	125.7	114.8	109.9
75°	161.7	153.4	145.2	136.9	128.7	119.8	110.4	100.9	91.5	82.0	80.3
77.5°	122.1	114.6	107.1	99.7	92.2	85.4	79.4	73.3	67.2	61.1	60.2
80°	96.7	89.7	82.6	75.5	68.5	63.2	59.6	55.9	52.3	48.8	48.2
82.5°	72.6	66.4	60.4	54.3	48.2	44.3	42.6	41.0	39.3	37.6	37.1
85°	41.0	37.3	33.4	29.7	25.9	23.7	23.2	22.7	22.2	21.6	21.3
87.5°	15.1	14.1	13.2	12.3	11.4	11.3	12.0	12.8	13.5	14.3	14.4
90°	1.3	4.2	7.2	10.0	12.9	16.3	20.1	23.8	27.7	31.4	32.6
92.5°	31.7	33.6	35.6	37.7	39.6	41.7	43.8	45.9	48.2	50.3	51.2
95°	77.3	79.3	81.4	83.4	85.4	87.7	90.0	92.3	94.6	96.9	98.1
97.5°	137.2	138.8	140.3	141.8	143.3	144.9	146.6	148.2	150.0	151.7	153.0
100°	178.1	179.9	181.6	183.4	185.1	186.7	188.1	189.7	191.1	192.6	193.4
102.5°	225.3	226.3	227.4	228.4	229.4	231.0	232.9	234.8	236.7	238.6	239.5
105°	294.7	295.3	295.9	296.4	297.0	298.6	301.2	303.9	306.5	309.1	309.1
107.5°	375.4	375.8	376.1	376.5	376.8	377.5	378.5	379.6	380.6	381.6	382.6
110°	425.7	426.3	426.9	427.4	428.0	428.6	429.2	429.8	430.3	430.9	432.1



TEST NUMBER: P332425-840

CATALOG NUMBER: S123RDIW-S560D1320U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	478.1	478.4	478.8	479.1	479.5	479.7	479.8	479.9	480.1	480.2	481.6
115°	556.6	557.5	558.4	559.3	560.2	560.3	559.7	559.2	558.6	558.0	558.3
117.5°	635.8	636.3	636.9	637.5	638.1	638.0	637.2	636.5	635.7	635.0	634.9
120°	685.0	686.7	688.5	690.2	692.0	692.2	690.6	689.2	687.8	686.3	686.0
122.5°	736.4	737.6	738.9	740.2	741.4	741.7	740.9	740.2	739.4	738.7	737.9
125°	814.7	815.6	816.4	817.3	818.2	818.3	817.7	817.2	816.6	816.0	814.9
127.5°	887.0	888.9	890.7	892.5	894.4	895.0	894.4	893.7	893.1	892.5	890.8
130°	935.1	937.5	939.9	942.2	944.5	945.2	944.3	943.5	942.6	941.7	940.6
132.5°	983.4	985.7	988.1	990.4	992.7	993.5	992.9	992.3	991.6	991.0	989.6
135°	1057.0	1058.7	1060.5	1062.2	1064.0	1064.7	1064.4	1064.1	1063.8	1063.5	1062.4
137.5°	1125.1	1126.5	1128.0	1129.4	1130.9	1132.1	1132.8	1133.6	1134.3	1135.1	1133.8
140°	1172.3	1173.7	1175.2	1176.6	1178.1	1178.9	1179.2	1179.5	1179.8	1180.1	1179.8
142.5°	1215.2	1216.7	1218.1	1219.6	1221.0	1222.0	1222.5	1223.0	1223.6	1224.2	1223.9
145°	1282.2	1282.8	1283.4	1284.0	1284.5	1285.4	1286.2	1287.1	1288.0	1288.8	1288.5
147.5°	1340.9	1342.0	1343.0	1344.1	1345.1	1346.0	1346.9	1347.7	1348.5	1349.3	1349.3
150°	1381.8	1382.4	1383.0	1383.5	1384.1	1384.7	1385.3	1385.8	1386.4	1387.0	1387.0
152.5°	1415.3	1416.1	1416.9	1417.7	1418.6	1419.2	1419.6	1419.9	1420.3	1420.6	1421.1
155°	1468.2	1468.2	1468.2	1468.2	1468.2	1468.4	1468.6	1468.9	1469.3	1469.6	1470.8
157.5°	1513.3	1513.0	1512.6	1512.3	1511.9	1511.9	1512.1	1512.3	1512.6	1512.8	1514.0
160°	1541.6	1541.1	1540.4	1539.8	1539.2	1538.9	1538.9	1538.9	1538.9	1538.9	1540.4
162.5°	1566.7	1565.9	1565.1	1564.3	1563.5	1563.2	1563.5	1563.7	1563.9	1564.1	1565.6
165°	1599.2	1598.3	1597.5	1596.6	1595.8	1595.3	1595.3	1595.3	1595.3	1595.3	1597.0
167.5°	1625.2	1624.0	1622.9	1621.6	1620.5	1620.0	1620.2	1620.5	1620.7	1620.9	1622.8
170°	1639.8	1638.7	1637.5	1636.4	1635.2	1634.6	1634.6	1634.6	1634.6	1634.6	1636.6
172.5°	1651.3	1650.2	1649.0	1647.9	1646.7	1646.1	1646.1	1646.1	1646.1	1646.1	1647.9
175°	1663.4	1662.2	1661.1	1659.9	1658.7	1658.2	1658.2	1658.2	1658.2	1658.2	1659.9
177.5°	1668.4	1667.5	1666.5	1665.6	1664.7	1664.2	1664.2	1664.2	1664.2	1664.2	1665.6
180°	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4



TEST NUMBER: P332425-840

CATALOG NUMBER: S123RDIW-S560D1320U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	953.8	953.8	953.8	953.8	953.8	953.8	953.8	953.8
2.5°	950.1	951.6	953.1	953.7	953.4	953.1	952.9	952.6
5°	943.7	945.3	946.8	947.5	947.2	946.7	946.4	946.0
7.5°	930.5	931.3	932.2	932.3	931.7	931.2	930.6	930.0
10°	918.6	918.8	918.9	918.6	917.8	916.9	916.0	915.1
12.5°	903.8	903.7	903.6	903.0	902.0	901.0	900.1	899.1
15°	877.9	877.0	876.2	875.0	873.8	872.7	871.5	870.3
17.5°	846.9	845.1	843.1	841.4	839.6	837.8	836.0	834.2
20°	825.6	823.3	821.1	819.0	816.9	814.9	812.7	810.7
22.5°	802.8	800.0	797.3	794.9	792.9	791.0	789.1	787.2
25°	765.6	761.9	758.4	755.6	753.8	751.8	749.9	748.0
27.5°	725.0	720.0	715.0	711.0	708.1	705.3	702.4	699.4
30°	696.1	690.2	684.5	680.1	677.4	674.7	671.9	669.1
32.5°	667.8	661.4	655.0	650.4	647.5	644.6	641.7	638.8
35°	625.7	618.3	611.0	605.7	602.6	599.6	596.4	593.3
37.5°	580.6	572.2	563.8	557.7	553.9	550.1	546.2	542.4
40°	549.2	540.2	531.3	524.8	520.9	516.9	513.0	509.0
42.5°	519.1	509.3	499.5	492.8	489.3	485.7	482.2	478.7
45°	474.7	464.9	455.1	448.2	444.0	439.9	435.8	431.6
47.5°	428.9	418.3	407.6	400.4	396.8	393.0	389.4	385.7
50°	398.0	387.3	376.7	369.3	365.4	361.4	357.5	353.6
52.5°	368.1	357.0	345.9	338.6	335.1	331.5	328.0	324.5
55°	323.6	313.6	303.6	296.9	293.5	290.0	286.6	283.2
57.5°	279.7	270.3	260.9	254.8	251.9	248.9	246.0	243.1
60°	252.2	242.9	233.6	227.5	224.6	221.7	218.7	215.8
62.5°	224.8	216.1	207.3	201.5	198.4	195.3	192.3	189.2
65°	185.8	177.4	169.0	163.8	162.0	160.1	158.1	156.2
67.5°	148.7	142.3	136.0	131.9	129.9	127.8	125.8	123.8
70°	125.6	119.7	113.6	109.7	107.8	105.9	104.0	102.1
72.5°	104.9	100.1	95.1	92.3	91.5	90.7	89.9	89.1
75°	78.6	76.9	75.1	74.1	73.7	73.4	73.0	72.7
77.5°	59.3	58.4	57.4	56.8	56.5	56.0	55.7	55.3
80°	47.7	47.2	46.7	46.3	45.9	45.5	45.2	44.8
82.5°	36.6	36.1	35.5	35.2	35.1	35.1	35.0	34.9
85°	21.0	20.6	20.3	20.1	20.1	20.1	20.1	20.1
87.5°	14.5	14.6	14.7	14.7	14.7	14.7	14.6	14.6
90°	33.7	34.9	36.1	37.0	37.6	38.2	38.7	39.3
92.5°	52.1	53.1	54.0	54.3	53.9	53.6	53.2	52.9
95°	99.3	100.4	101.6	102.2	102.2	102.2	102.2	102.2
97.5°	154.3	155.7	157.0	157.6	157.5	157.4	157.3	157.1
100°	194.3	195.1	196.0	196.7	197.3	197.9	198.5	199.0
102.5°	240.3	241.3	242.2	242.5	242.4	242.3	242.2	242.1
105°	309.1	309.1	309.1	309.4	310.0	310.5	311.1	311.7
107.5°	383.5	384.5	385.4	385.7	385.4	385.0	384.7	384.3
110°	433.2	434.4	435.6	435.9	435.3	434.7	434.1	433.5



TEST NUMBER: P332425-840

CATALOG NUMBER: S123RDIW-S560D1320U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	482.9	484.3	485.7	486.4	486.3	486.1	486.0	485.9
115°	558.6	558.9	559.2	559.2	558.9	558.6	558.3	558.0
117.5°	634.9	634.8	634.7	634.3	633.5	632.7	631.9	631.1
120°	685.7	685.5	685.2	684.7	684.2	683.6	683.0	682.4
122.5°	737.2	736.4	735.7	734.9	734.1	733.3	732.5	731.6
125°	813.6	812.5	811.3	810.2	809.0	807.8	806.7	805.5
127.5°	889.2	887.6	886.0	884.4	883.1	881.8	880.5	879.1
130°	939.4	938.3	937.1	935.4	933.4	931.4	929.4	927.4
132.5°	988.2	986.7	985.4	983.9	982.3	980.8	979.2	977.7
135°	1061.2	1060.1	1058.8	1058.0	1057.4	1056.8	1056.2	1055.7
137.5°	1132.6	1131.4	1130.1	1129.0	1127.9	1126.8	1125.7	1124.6
140°	1179.5	1179.2	1178.9	1177.8	1175.8	1173.7	1171.6	1169.6
142.5°	1223.6	1223.2	1222.9	1222.0	1220.4	1218.9	1217.3	1215.8
145°	1288.2	1288.0	1287.7	1287.0	1285.8	1284.5	1283.4	1282.2
147.5°	1349.3	1349.3	1349.3	1348.5	1346.8	1344.9	1343.2	1341.5
150°	1387.0	1387.0	1387.0	1386.1	1384.4	1382.7	1380.9	1379.2
152.5°	1421.5	1422.0	1422.4	1421.9	1420.4	1418.9	1417.3	1415.8
155°	1471.9	1473.1	1474.2	1473.8	1471.8	1469.8	1467.6	1465.6
157.5°	1515.2	1516.4	1517.7	1517.4	1515.8	1514.2	1512.6	1511.0
160°	1541.9	1543.4	1544.8	1545.0	1543.8	1542.7	1541.5	1540.2
162.5°	1567.0	1568.5	1569.9	1569.7	1567.9	1566.0	1564.2	1562.3
165°	1598.8	1600.5	1602.3	1602.2	1600.1	1598.1	1596.0	1594.0
167.5°	1624.6	1626.4	1628.2	1628.2	1626.4	1624.6	1622.8	1620.9
170°	1638.7	1640.7	1642.7	1642.7	1640.7	1638.7	1636.6	1634.6
172.5°	1649.7	1651.5	1653.4	1653.3	1651.2	1649.1	1647.1	1645.1
175°	1661.6	1663.4	1665.2	1665.0	1662.9	1660.9	1658.9	1656.9
177.5°	1667.0	1668.4	1669.8	1669.7	1668.0	1666.4	1664.8	1663.1
180°	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4	1667.4

(END OF REPORT)