

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333029-927

Luminaire Tested: **S124RDIW-S350D1340U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333029-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S350D1340U927-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1340 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5384.9 lumens
Efficiency: N/A
Efficacy: 115.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 46.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333029-927

CATALOG NUMBER: S124RDIW-S350D1340U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333029-927

CATALOG NUMBER: S124RDIW-S350D1340U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	100	100	100	100	89	89	89	89	67	67	67	48	48	48	30	30	30	21				
1	91	87	84	80	81	77	74	72	59	57	55	42	41	40	26	26	25	18				
2	83	76	71	66	73	68	63	59	52	48	46	37	35	33	23	22	21	15				
3	76	67	60	55	67	60	54	49	46	42	38	33	30	28	21	19	18	13				
4	69	59	52	46	61	53	46	42	40	36	33	29	26	24	18	17	16	11				
5	64	53	45	39	56	47	40	36	36	32	28	26	23	21	17	15	14	10				
6	58	47	39	34	52	42	35	31	32	28	24	23	20	18	15	13	12	9				
7	54	42	35	30	48	38	31	27	29	25	21	21	18	16	14	12	11	8				
8	50	38	31	26	44	34	28	24	27	22	19	19	16	14	13	11	10	7				
9	46	35	28	23	41	31	25	21	24	20	17	18	15	13	12	10	9	6				
10	43	32	25	20	38	28	23	19	22	18	15	16	13	11	11	9	8	6				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3953	3953	3953
5°	3962	3914	3938
10°	3937	3867	3867
15°	3892	3786	3758
20°	3830	3679	3611
25°	3751	3553	3463
30°	3674	3422	3278
35°	3588	3286	3094
40°	3485	3130	2893
45°	3391	2975	2689
50°	3282	2798	2473
55°	3167	2612	2238
60°	3039	2409	1997
65°	2923	2157	1761
70°	2752	1876	1496
75°	2539	1556	1216
80°	2213	1186	1116
85°	1880	1074	1010



TEST NUMBER: P333029-927

CATALOG NUMBER: S124RDIW-S350D1340U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.0	0.9
10°-20°	128.3	2.4
20°-30°	185.2	3.4
30°-40°	210.0	3.9
40°-50°	202.8	3.8
50°-60°	168.6	3.1
60°-70°	116.4	2.2
70°-80°	59.0	1.1
80°-90°	19.1	0.4
90°-100°	47.0	0.9
100°-110°	299.6	5.6
110°-120°	573.1	10.6
120°-130°	727.5	13.5
130°-140°	778.4	14.5
140°-150°	727.9	13.5
150°-160°	587.0	10.9
160°-170°	378.6	7.0
170°-180°	130.5	2.4
0°-30°	359.5	6.7
0°-40°	569.5	10.6
0°-60°	940.8	17.5
0°-90°	1135.4	21.1
90°-120°	919.7	17.1
90°-150°	3153.4	58.6
90°-180°	4250.0	78.9
0°-180°	5384.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	490	490	490	490	490	
5°	489	487	483	486	486	46
15°	466	462	453	452	450	131
25°	421	414	399	393	389	194
35°	364	352	333	321	314	227
45°	297	283	261	243	236	229
55°	225	209	186	167	159	201
65°	153	136	113	97	92	151
75°	81	67	50	42	39	86
85°	20	13	12	11	11	23
90°	3	14	23	29	31	4
95°	56	24	23	28	30	73
105°	309	315	321	327	293	324
115°	577	580	580	581	582	568
125°	812	816	814	817	818	724
135°	1007	1006	1010	1012	1014	776
145°	1161	1164	1164	1165	1167	725
155°	1273	1274	1271	1275	1272	587
165°	1343	1338	1338	1345	1337	379
175°	1374	1368	1369	1377	1366	131
180°	1374	1374	1374	1374	1374	



TEST NUMBER: P333029-927

CATALOG NUMBER: S124RDIW-S350D1340U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	489.7	489.7	489.7	489.7	489.7	489.7	489.7	489.7	489.7	489.7	489.7
2.5°	490.9	490.6	490.4	490.1	489.8	489.3	488.6	487.9	487.1	486.4	487.1
5°	488.9	488.6	488.3	488.0	487.6	487.0	485.9	485.0	483.9	483.0	483.8
7.5°	484.5	484.2	483.9	483.5	483.2	482.3	481.0	479.7	478.4	477.1	477.6
10°	480.3	479.9	479.5	479.1	478.6	477.7	476.2	474.7	473.2	471.7	472.1
12.5°	474.9	474.4	474.0	473.5	473.0	471.9	470.1	468.3	466.6	464.8	465.0
15°	465.7	464.9	464.2	463.4	462.7	461.3	459.2	457.1	455.0	453.0	452.8
17.5°	454.6	453.4	452.3	451.3	450.2	448.4	445.9	443.4	440.9	438.4	437.9
20°	445.8	444.7	443.7	442.6	441.5	439.6	436.7	433.9	431.0	428.2	427.5
22.5°	436.3	435.0	433.8	432.6	431.3	429.2	426.2	423.2	420.2	417.1	416.1
25°	421.1	419.6	418.1	416.6	415.1	412.6	409.2	405.8	402.3	398.9	397.5
27.5°	405.2	403.3	401.4	399.6	397.7	394.9	391.3	387.6	384.0	380.3	378.5
30°	394.1	392.0	389.9	387.9	385.8	382.8	378.8	374.9	371.0	367.1	365.0
32.5°	382.4	380.0	377.7	375.3	373.0	369.8	365.8	361.7	357.7	353.6	351.2
35°	364.1	361.4	358.8	356.1	353.4	350.0	345.9	341.7	337.5	333.4	330.5
37.5°	344.5	341.7	339.1	336.3	333.5	329.9	325.2	320.6	316.0	311.4	308.2
40°	330.7	328.0	325.2	322.5	319.7	316.0	311.2	306.5	301.7	297.0	293.5
42.5°	317.5	314.7	311.7	308.9	306.0	302.1	297.1	292.2	287.2	282.3	278.7
45°	297.0	293.9	290.8	287.7	284.6	280.6	275.6	270.6	265.6	260.6	256.5
47.5°	275.8	272.6	269.4	266.2	263.0	258.8	253.7	248.4	243.2	238.1	233.8
50°	261.3	258.1	254.8	251.6	248.3	244.1	238.8	233.4	228.1	222.8	218.6
52.5°	246.7	243.4	240.3	237.1	233.9	229.6	224.1	218.6	213.2	207.7	203.5
55°	225.0	221.7	218.3	215.0	211.7	207.2	201.8	196.5	191.0	185.6	181.3
57.5°	203.5	200.0	196.6	193.1	189.6	185.3	179.9	174.6	169.3	163.9	159.5
60°	188.2	184.9	181.6	178.2	174.9	170.6	165.2	159.9	154.6	149.2	144.9
62.5°	174.4	171.0	167.5	164.1	160.6	156.1	150.7	145.2	139.7	134.3	130.2
65°	153.0	149.4	145.8	142.3	138.6	134.2	128.9	123.5	118.2	112.9	109.3
67.5°	130.7	127.3	123.8	120.4	117.0	112.8	107.8	102.9	97.9	93.0	89.9
70°	116.6	113.1	109.6	106.2	102.6	98.5	93.7	89.0	84.2	79.5	76.8
72.5°	101.6	98.5	95.3	92.1	89.0	85.2	80.6	76.1	71.7	67.2	64.9
75°	81.4	78.3	75.2	72.1	69.0	65.5	61.6	57.7	53.8	49.9	47.9
77.5°	60.8	58.2	55.6	53.0	50.4	47.5	44.3	41.1	37.9	34.8	33.7
80°	47.6	45.2	42.8	40.4	37.9	35.5	33.0	30.5	28.0	25.5	25.3
82.5°	36.2	34.0	31.8	29.5	27.3	25.5	24.1	22.7	21.2	19.8	19.6
85°	20.3	18.6	17.0	15.2	13.5	12.6	12.4	12.1	11.9	11.6	11.5
87.5°	7.5	7.4	7.4	7.4	7.4	7.5	7.8	8.2	8.4	8.7	9.0
90°	3.1	5.6	8.1	10.6	13.2	15.3	17.1	18.9	20.8	22.6	24.0
92.5°	12.9	13.1	13.2	13.4	13.5	14.5	16.3	18.1	20.0	21.8	23.1
95°	56.5	48.7	41.0	33.2	25.4	21.7	21.9	22.2	22.3	22.6	24.0
97.5°	120.0	124.8	129.7	134.5	139.3	129.0	103.5	78.1	52.6	27.1	27.3
100°	168.5	172.6	176.7	180.9	185.0	171.3	139.7	108.2	76.7	45.2	41.4
102.5°	222.8	225.8	228.8	231.8	234.8	234.2	230.1	226.1	222.0	217.9	175.9
105°	309.3	310.6	312.0	313.4	314.7	316.0	317.2	318.3	319.4	320.6	322.7
107.5°	389.6	390.3	391.0	391.7	392.4	393.5	395.1	396.6	398.2	399.7	400.7
110°	443.9	444.6	445.3	445.9	446.6	447.7	449.0	450.4	451.8	453.1	453.6



TEST NUMBER: P333029-927

CATALOG NUMBER: S124RDIW-S350D1340U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	496.5	497.7	499.0	500.2	501.5	502.3	503.0	503.7	504.3	504.9	504.9
115°	577.4	578.1	578.8	579.5	580.2	580.4	580.2	580.0	579.7	579.5	580.0
117.5°	650.4	651.3	652.2	653.2	654.0	654.7	655.3	655.8	656.2	656.8	656.7
120°	699.7	700.6	701.6	702.5	703.4	703.7	703.5	703.3	703.1	702.8	703.3
122.5°	745.8	746.3	746.9	747.4	748.0	748.4	748.7	749.0	749.3	749.6	750.0
125°	811.7	812.6	813.6	814.4	815.4	815.6	815.2	814.7	814.2	813.8	814.4
127.5°	874.2	874.4	874.6	874.9	875.1	875.8	876.8	877.8	878.9	880.0	879.8
130°	914.5	914.7	915.0	915.1	915.4	915.8	916.6	917.2	917.9	918.6	918.9
132.5°	951.5	951.9	952.3	952.7	953.1	953.8	954.7	955.5	956.3	957.2	957.4
135°	1006.9	1006.7	1006.5	1006.3	1006.1	1006.4	1007.3	1008.2	1009.2	1010.0	1010.5
137.5°	1056.1	1056.1	1056.2	1056.4	1056.5	1057.0	1058.0	1059.0	1060.0	1061.0	1061.5
140°	1088.1	1088.6	1089.0	1089.5	1090.0	1090.4	1090.8	1091.3	1091.8	1092.3	1092.9
142.5°	1116.9	1117.7	1118.6	1119.4	1120.2	1120.7	1121.0	1121.3	1121.6	1121.8	1122.4
145°	1161.1	1161.7	1162.4	1163.2	1163.8	1164.2	1164.2	1164.2	1164.2	1164.2	1164.4
147.5°	1196.2	1197.5	1198.8	1200.1	1201.3	1201.9	1201.7	1201.4	1201.2	1200.9	1201.1
150°	1221.7	1222.7	1223.5	1224.5	1225.3	1225.7	1225.5	1225.3	1225.0	1224.8	1224.8
152.5°	1243.1	1243.8	1244.5	1245.2	1246.0	1246.2	1245.8	1245.3	1244.9	1244.5	1244.9
155°	1273.1	1273.3	1273.5	1273.7	1274.0	1273.7	1273.1	1272.4	1271.7	1271.1	1271.9
157.5°	1298.4	1298.2	1298.1	1297.9	1297.8	1297.4	1296.6	1295.8	1295.1	1294.3	1295.5
160°	1313.1	1312.5	1311.8	1311.1	1310.4	1310.0	1309.7	1309.5	1309.2	1309.1	1310.4
162.5°	1326.3	1325.4	1324.6	1323.7	1322.9	1322.3	1322.1	1321.8	1321.6	1321.4	1322.7
165°	1343.0	1341.8	1340.7	1339.5	1338.4	1337.8	1337.8	1337.8	1337.8	1337.8	1339.7
167.5°	1356.1	1354.9	1353.8	1352.6	1351.4	1350.7	1350.6	1350.4	1350.3	1350.1	1352.2
170°	1363.5	1362.2	1360.7	1359.4	1358.0	1357.5	1357.6	1357.9	1358.1	1358.4	1360.2
172.5°	1368.4	1367.1	1365.7	1364.3	1362.9	1362.4	1362.6	1362.9	1363.0	1363.3	1365.1
175°	1373.8	1372.4	1371.0	1369.7	1368.3	1367.7	1367.9	1368.2	1368.4	1368.7	1370.7
177.5°	1376.3	1375.0	1373.6	1372.4	1371.1	1370.6	1371.0	1371.4	1371.7	1372.1	1373.6
180°	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8



TEST NUMBER: P333029-927

CATALOG NUMBER: S124RDIW-S350D1340U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	489.7	489.7	489.7	489.7	489.7	489.7	489.7	489.7
2.5°	487.9	488.6	489.3	489.6	489.6	489.6	489.5	489.4
5°	484.7	485.4	486.3	486.6	486.5	486.3	486.1	485.9
7.5°	478.2	478.7	479.3	479.3	479.1	478.9	478.6	478.3
10°	472.4	472.7	473.0	473.0	472.7	472.4	472.1	471.7
12.5°	465.2	465.4	465.6	465.5	465.0	464.5	464.1	463.6
15°	452.7	452.5	452.3	451.9	451.3	450.8	450.2	449.6
17.5°	437.4	437.0	436.6	435.9	435.0	434.1	433.2	432.4
20°	426.9	426.2	425.6	424.7	423.6	422.5	421.4	420.3
22.5°	415.1	414.1	413.1	412.2	411.3	410.4	409.6	408.6
25°	396.1	394.7	393.3	392.2	391.3	390.5	389.7	388.8
27.5°	376.8	375.0	373.3	371.9	370.6	369.4	368.2	367.0
30°	362.9	360.8	358.8	357.0	355.7	354.4	353.1	351.7
32.5°	348.8	346.3	344.0	342.1	340.8	339.5	338.3	337.0
35°	327.6	324.9	322.0	319.9	318.4	316.9	315.4	313.9
37.5°	305.1	301.9	298.7	296.4	294.9	293.3	291.8	290.3
40°	289.9	286.5	283.0	280.5	279.0	277.5	276.0	274.5
42.5°	275.1	271.6	268.0	265.5	263.9	262.3	260.7	259.2
45°	252.5	248.3	244.2	241.5	240.0	238.4	236.9	235.5
47.5°	229.6	225.3	221.1	218.2	216.5	214.8	213.2	211.6
50°	214.4	210.2	206.0	203.2	201.6	200.0	198.4	196.9
52.5°	199.2	195.0	190.8	187.8	186.2	184.6	182.9	181.3
55°	177.0	172.6	168.3	165.3	163.7	162.2	160.6	159.0
57.5°	155.1	150.8	146.3	143.5	142.4	141.2	139.9	138.7
60°	140.5	136.3	131.9	129.0	127.7	126.4	125.1	123.7
62.5°	126.3	122.2	118.3	115.7	114.6	113.6	112.5	111.5
65°	105.7	102.1	98.5	96.3	95.2	94.3	93.2	92.2
67.5°	86.8	83.7	80.6	78.6	77.5	76.4	75.3	74.1
70°	74.0	71.2	68.5	66.7	65.8	65.0	64.2	63.4
72.5°	62.5	60.1	57.8	56.2	55.5	54.7	53.9	53.2
75°	46.0	44.1	42.2	41.0	40.5	40.0	39.5	39.0
77.5°	32.6	31.4	30.3	29.7	29.5	29.4	29.2	29.1
80°	25.0	24.7	24.5	24.3	24.2	24.2	24.1	24.0
82.5°	19.4	19.3	19.1	18.9	18.9	18.8	18.7	18.6
85°	11.3	11.1	10.9	10.9	10.9	10.9	10.9	10.9
87.5°	9.1	9.3	9.6	9.7	9.9	10.1	10.2	10.4
90°	25.3	26.7	28.1	29.0	29.5	29.9	30.3	30.8
92.5°	24.6	25.9	27.3	28.0	28.1	28.2	28.3	28.4
95°	25.3	26.7	28.1	28.9	29.1	29.3	29.5	29.8
97.5°	27.4	27.6	27.6	27.9	28.1	28.3	28.5	28.8
100°	37.5	33.6	29.7	27.9	28.1	28.3	28.5	28.8
102.5°	134.1	92.2	50.3	29.4	29.5	29.5	29.5	29.6
105°	324.7	326.8	328.8	325.7	317.5	309.3	301.0	292.9
107.5°	401.7	402.7	403.7	404.6	405.5	406.4	407.3	408.1
110°	454.1	454.5	455.0	455.5	456.2	456.9	457.6	458.3



TEST NUMBER: P333029-927

CATALOG NUMBER: S124RDIW-S350D1340U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	504.7	504.6	504.5	504.9	505.8	506.7	507.6	508.4
115°	580.4	580.9	581.3	581.5	581.5	581.5	581.5	581.5
117.5°	656.6	656.5	656.4	656.3	656.2	656.2	656.1	655.9
120°	703.7	704.2	704.6	704.6	704.2	703.7	703.3	702.8
122.5°	750.2	750.5	750.8	750.7	750.2	749.7	749.3	748.8
125°	815.2	815.9	816.5	817.0	817.2	817.5	817.7	817.9
127.5°	879.7	879.6	879.4	879.2	879.1	878.8	878.7	878.5
130°	919.0	919.2	919.5	919.6	919.6	919.6	919.6	919.6
132.5°	957.7	957.9	958.1	958.1	958.0	957.8	957.6	957.4
135°	1011.0	1011.4	1011.9	1012.3	1012.8	1013.2	1013.7	1014.2
137.5°	1062.0	1062.5	1063.0	1063.2	1063.0	1063.0	1062.8	1062.6
140°	1093.6	1094.3	1095.0	1095.4	1095.7	1095.9	1096.1	1096.4
142.5°	1122.8	1123.3	1123.9	1124.1	1124.2	1124.2	1124.3	1124.3
145°	1164.6	1164.8	1165.1	1165.5	1165.9	1166.3	1166.8	1167.3
147.5°	1201.3	1201.5	1201.7	1201.9	1202.1	1202.4	1202.5	1202.8
150°	1224.8	1224.8	1224.8	1224.9	1225.1	1225.3	1225.6	1225.8
152.5°	1245.2	1245.6	1245.9	1246.1	1245.9	1245.8	1245.7	1245.5
155°	1272.9	1273.7	1274.7	1274.8	1274.1	1273.4	1272.7	1272.1
157.5°	1296.6	1297.8	1299.0	1299.0	1297.8	1296.6	1295.5	1294.3
160°	1311.8	1313.1	1314.5	1314.5	1313.1	1311.8	1310.4	1309.1
162.5°	1324.1	1325.5	1326.8	1326.7	1325.2	1323.7	1322.1	1320.6
165°	1341.5	1343.3	1345.1	1345.0	1343.0	1340.9	1338.9	1336.8
167.5°	1354.2	1356.1	1358.2	1358.0	1355.7	1353.4	1351.2	1348.9
170°	1362.0	1363.8	1365.6	1365.4	1363.2	1360.9	1358.6	1356.3
172.5°	1366.9	1368.8	1370.6	1370.3	1367.8	1365.3	1362.9	1360.4
175°	1372.8	1374.8	1376.9	1376.5	1373.8	1371.0	1368.3	1365.6
177.5°	1375.1	1376.5	1378.0	1377.6	1375.4	1373.2	1371.0	1368.8
180°	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8

(END OF REPORT)