

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332412-840

Luminaire Tested: **S123RDIW-S560D460U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332412-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S560D460U840-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 460 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4018.8 lumens
Efficiency: N/A
Efficacy: 133.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 30.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332412-840

CATALOG NUMBER: S123RDIW-S560D460U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332412-840

CATALOG NUMBER: S123RDIW-S560D460U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	54
1	99	95	91	88	92	88	85	82	75	73	71	64	62	61	53	52	51	46
2	90	83	77	72	84	77	72	68	66	63	59	56	54	51	47	45	43	39
3	83	73	66	60	76	68	62	57	59	54	50	50	47	44	42	40	37	33
4	76	65	57	51	70	61	54	49	53	47	43	45	41	38	38	35	32	29
5	70	58	50	44	64	54	47	42	47	42	37	40	36	33	34	31	28	25
6	64	52	44	39	59	49	42	37	43	37	33	37	32	29	31	28	25	22
7	60	47	39	34	55	44	37	32	39	33	29	33	29	26	29	25	23	20
8	55	43	35	30	51	40	34	29	35	30	26	31	26	23	26	23	20	18
9	52	39	32	27	48	37	30	26	33	27	23	28	24	21	24	21	18	16
10	48	36	29	24	45	34	28	23	30	25	21	26	22	19	23	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10267	10267	10267
5°	10306	10164	10222
10°	10248	10037	10002
15°	10137	9802	9698
20°	9986	9507	9286
25°	9830	9178	8884
30°	9625	8797	8316
35°	9412	8418	7796
40°	9218	7967	7152
45°	8961	7524	6570
50°	8679	7021	5921
55°	8392	6446	5315
60°	8127	5828	4646
65°	7784	5163	3978
70°	7352	4334	3213
75°	6725	3410	3023
80°	5994	3025	2777
85°	5064	2668	2482



TEST NUMBER: P332412-840

CATALOG NUMBER: S123RDIW-S560D460U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.6	2.2
10°-20°	249.2	6.2
20°-30°	358.8	8.9
30°-40°	404.2	10.1
40°-50°	386.7	9.6
50°-60°	316.7	7.9
60°-70°	213.7	5.3
70°-80°	107.5	2.7
80°-90°	30.1	0.7
90°-100°	22.2	0.6
100°-110°	105.8	2.6
110°-120°	254.2	6.3
120°-130°	323.7	8.1
130°-140°	345.8	8.6
140°-150°	323.4	8.0
150°-160°	260.8	6.5
160°-170°	168.4	4.2
170°-180°	58.0	1.4
0°-30°	697.6	17.4
0°-40°	1101.8	27.4
0°-60°	1805.2	44.9
0°-90°	2156.5	53.7
90°-120°	382.2	9.5
90°-150°	1375.1	34.2
90°-180°	1862.0	46.3
0°-180°	4018.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	954	954	954	954	954	
5°	954	950	941	947	946	90
15°	910	900	880	876	870	256
25°	828	808	773	757	748	381
35°	716	687	641	608	593	448
45°	589	552	494	452	432	454
55°	447	408	344	300	283	401
65°	306	262	203	166	156	302
75°	162	124	82	75	73	172
85°	41	25	22	20	20	46
90°	0	5	11	13	14	3
95°	28	10	14	17	17	34
105°	135	138	99	24	20	143
115°	254	256	260	265	267	250
125°	358	361	363	364	365	319
135°	445	448	450	451	450	343
145°	514	517	518	519	519	321
155°	566	565	565	567	565	261
165°	597	595	595	598	595	169
175°	611	608	609	612	608	58
180°	611	611	611	611	611	



TEST NUMBER: P332412-840

CATALOG NUMBER: S123RDIW-S560D460U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	953.8	953.8	953.8	953.8	953.8	953.8	953.8	953.8	953.8	953.8	953.8
2.5°	956.9	956.3	955.8	955.2	954.7	953.6	952.0	950.3	948.7	947.1	948.6
5°	953.8	953.0	952.1	951.3	950.4	949.0	946.8	944.8	942.7	940.7	942.2
7.5°	945.0	944.1	943.1	942.2	941.3	939.5	936.9	934.1	931.4	928.8	929.6
10°	937.6	936.3	935.1	933.9	932.8	930.6	927.6	924.4	921.3	918.3	918.4
12.5°	927.1	925.7	924.3	923.0	921.7	919.2	915.3	911.6	907.8	904.0	903.9
15°	909.7	907.9	905.9	904.0	902.2	898.8	894.0	889.2	884.3	879.6	878.7
17.5°	887.9	885.8	883.5	881.3	879.1	874.9	868.8	862.7	856.6	850.5	848.7
20°	871.8	869.1	866.4	863.5	860.8	856.2	849.6	843.1	836.6	830.0	827.8
22.5°	853.8	850.7	847.6	844.3	841.2	836.2	829.2	822.2	815.4	808.4	805.6
25°	827.7	823.4	819.1	814.9	810.5	804.5	796.5	788.6	780.7	772.8	769.2
27.5°	796.0	791.2	786.5	781.7	777.0	770.2	761.4	752.7	743.9	735.1	730.0
30°	774.4	769.2	764.1	758.9	753.8	746.3	736.7	727.1	717.4	707.8	702.0
32.5°	752.7	746.9	741.0	735.2	729.3	721.3	711.1	700.9	690.7	680.5	674.2
35°	716.3	710.1	704.0	697.8	691.6	683.2	672.5	661.9	651.2	640.6	633.1
37.5°	679.5	672.7	665.8	658.8	652.0	642.9	631.5	620.2	608.7	597.3	589.0
40°	656.0	648.4	640.9	633.3	625.7	615.8	603.7	591.5	579.3	567.0	558.1
42.5°	629.3	621.8	614.3	606.7	599.2	589.1	576.4	563.8	551.2	538.6	528.8
45°	588.7	581.0	573.2	565.5	557.7	547.2	534.0	520.8	507.6	494.3	484.5
47.5°	548.0	539.5	531.0	522.5	514.0	503.2	489.9	476.7	463.4	450.2	439.6
50°	518.3	510.2	502.1	494.0	485.9	474.9	461.0	447.2	433.2	419.3	408.6
52.5°	491.7	482.9	474.1	465.3	456.7	445.4	431.5	417.8	403.9	390.2	379.1
55°	447.2	438.7	430.3	421.8	413.4	401.9	387.3	372.7	358.1	343.5	333.5
57.5°	406.0	396.8	387.6	378.4	369.2	357.3	342.6	328.0	313.3	298.6	289.2
60°	377.5	368.1	358.6	349.1	339.7	327.8	313.6	299.3	285.0	270.7	261.5
62.5°	349.0	339.6	330.1	320.6	311.2	299.3	285.1	270.8	256.5	242.3	233.6
65°	305.6	296.1	286.7	277.2	267.7	256.3	242.9	229.5	216.1	202.7	194.3
67.5°	262.1	252.6	243.0	233.4	223.9	212.7	199.8	186.9	174.1	161.2	154.9
70°	233.6	224.3	215.1	205.8	196.5	185.8	173.8	161.8	149.8	137.7	131.7
72.5°	205.1	196.0	186.8	177.7	168.5	158.5	147.6	136.6	125.7	114.8	109.9
75°	161.7	153.4	145.2	136.9	128.7	119.8	110.4	100.9	91.5	82.0	80.3
77.5°	122.1	114.6	107.1	99.7	92.2	85.4	79.4	73.3	67.2	61.1	60.2
80°	96.7	89.7	82.6	75.5	68.5	63.2	59.6	55.9	52.3	48.8	48.2
82.5°	72.6	66.4	60.4	54.3	48.2	44.3	42.6	41.0	39.3	37.6	37.1
85°	41.0	37.3	33.4	29.7	25.9	23.7	23.2	22.7	22.2	21.6	21.3
87.5°	14.9	13.6	12.3	11.0	9.7	9.2	9.4	9.7	10.0	10.2	10.2
90°	0.4	1.4	2.4	3.4	4.4	5.7	7.0	8.3	9.6	10.9	11.3
92.5°	8.5	8.2	7.9	7.6	7.3	7.7	8.7	9.6	10.6	11.6	12.2
95°	27.7	23.5	19.4	15.2	11.1	9.6	10.7	11.8	12.9	14.0	14.7
97.5°	55.6	53.7	51.9	50.1	48.2	43.6	36.4	29.1	21.9	14.6	15.5
100°	76.6	78.7	80.7	82.7	84.7	77.9	62.2	46.5	30.7	14.9	15.8
102.5°	100.6	102.1	103.5	105.0	106.4	98.6	81.4	64.2	47.1	29.9	27.4
105°	135.2	136.3	137.4	138.6	139.7	135.6	126.5	117.5	108.5	99.4	81.5
107.5°	171.7	172.6	173.5	174.3	175.2	176.4	177.8	179.3	180.7	182.1	169.1
110°	196.0	196.8	197.6	198.4	199.2	200.2	201.3	202.4	203.5	204.6	201.3



TEST NUMBER: P332412-840

CATALOG NUMBER: S123RDIW-S560D460U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	219.2	219.9	220.7	221.4	222.2	223.1	224.2	225.3	226.4	227.5	227.5
115°	253.6	254.2	254.8	255.4	256.0	256.8	257.7	258.6	259.5	260.4	261.5
117.5°	286.9	287.7	288.4	289.1	289.9	290.5	290.9	291.4	292.0	292.4	293.2
120°	307.6	308.5	309.4	310.3	311.2	311.8	312.1	312.5	312.8	313.1	313.9
122.5°	328.7	329.4	330.1	330.9	331.6	332.2	332.6	333.0	333.4	333.8	334.3
125°	357.5	358.3	359.1	359.9	360.7	361.3	361.7	362.1	362.5	362.9	363.1
127.5°	385.5	386.3	387.1	387.9	388.7	389.3	389.8	390.3	390.8	391.3	391.6
130°	402.9	403.7	404.6	405.4	406.2	406.8	407.2	407.6	408.0	408.3	408.7
132.5°	419.6	420.4	421.2	422.0	422.8	423.3	423.7	424.0	424.3	424.6	425.1
135°	445.0	445.7	446.3	446.9	447.5	448.0	448.4	448.8	449.2	449.6	449.9
137.5°	466.9	467.7	468.4	469.2	469.9	470.4	470.7	470.9	471.1	471.3	471.8
140°	481.4	482.0	482.6	483.2	483.8	484.2	484.5	484.8	485.1	485.4	485.8
142.5°	494.8	495.4	496.0	496.7	497.3	497.7	498.0	498.3	498.6	498.9	499.2
145°	513.6	514.3	515.0	515.7	516.4	516.8	517.1	517.3	517.5	517.7	517.9
147.5°	531.3	531.8	532.2	532.7	533.1	533.5	533.7	533.9	534.1	534.3	534.5
150°	542.2	542.5	542.8	543.1	543.4	543.6	543.8	544.0	544.2	544.4	544.6
152.5°	552.0	552.1	552.3	552.4	552.6	552.7	552.8	552.9	553.0	553.2	553.5
155°	565.7	565.5	565.3	565.2	565.0	564.9	565.0	565.1	565.2	565.3	565.8
157.5°	576.5	576.4	576.4	576.4	576.4	576.3	576.2	576.1	576.0	575.9	576.5
160°	583.0	582.9	582.8	582.7	582.6	582.5	582.4	582.3	582.2	582.1	582.7
162.5°	589.2	589.0	588.7	588.4	588.1	587.9	587.8	587.7	587.6	587.5	588.2
165°	596.6	596.3	596.0	595.7	595.4	595.2	595.1	595.0	594.9	594.8	595.6
167.5°	602.5	602.1	601.7	601.3	600.9	600.7	600.7	600.7	600.7	600.7	601.5
170°	605.7	605.3	604.9	604.5	604.1	603.9	603.9	603.9	603.9	603.9	604.7
172.5°	607.8	607.4	606.9	606.4	605.9	605.7	605.8	605.9	606.0	606.0	606.8
175°	610.7	610.2	609.7	609.2	608.6	608.4	608.5	608.6	608.7	608.8	609.6
177.5°	611.4	611.0	610.6	610.2	609.8	609.7	609.8	609.8	609.9	610.0	610.6
180°	610.7	610.7	610.7	610.7	610.7	610.7	610.7	610.7	610.7	610.7	610.7



TEST NUMBER: P332412-840

CATALOG NUMBER: S123RDIW-S560D460U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	953.8	953.8	953.8	953.8	953.8	953.8	953.8	953.8
2.5°	950.1	951.6	953.1	953.7	953.4	953.1	952.9	952.6
5°	943.7	945.3	946.8	947.5	947.2	946.7	946.4	946.0
7.5°	930.5	931.3	932.2	932.3	931.7	931.2	930.6	930.0
10°	918.6	918.8	918.9	918.6	917.8	916.9	916.0	915.1
12.5°	903.8	903.7	903.6	903.0	902.0	901.0	900.1	899.1
15°	877.9	877.0	876.2	875.0	873.8	872.7	871.5	870.3
17.5°	846.9	845.1	843.1	841.4	839.6	837.8	836.0	834.2
20°	825.6	823.3	821.1	819.0	816.9	814.9	812.7	810.7
22.5°	802.8	800.0	797.3	794.9	792.9	791.0	789.1	787.2
25°	765.6	761.9	758.4	755.6	753.8	751.8	749.9	748.0
27.5°	725.0	720.0	715.0	711.0	708.1	705.3	702.4	699.4
30°	696.1	690.2	684.5	680.1	677.4	674.7	671.9	669.1
32.5°	667.8	661.4	655.0	650.4	647.5	644.6	641.7	638.8
35°	625.7	618.3	611.0	605.7	602.6	599.6	596.4	593.3
37.5°	580.6	572.2	563.8	557.7	553.9	550.1	546.2	542.4
40°	549.2	540.2	531.3	524.8	520.9	516.9	513.0	509.0
42.5°	519.1	509.3	499.5	492.8	489.3	485.7	482.2	478.7
45°	474.7	464.9	455.1	448.2	444.0	439.9	435.8	431.6
47.5°	428.9	418.3	407.6	400.4	396.8	393.0	389.4	385.7
50°	398.0	387.3	376.7	369.3	365.4	361.4	357.5	353.6
52.5°	368.1	357.0	345.9	338.6	335.1	331.5	328.0	324.5
55°	323.6	313.6	303.6	296.9	293.5	290.0	286.6	283.2
57.5°	279.7	270.3	260.9	254.8	251.9	248.9	246.0	243.1
60°	252.2	242.9	233.6	227.5	224.6	221.7	218.7	215.8
62.5°	224.8	216.1	207.3	201.5	198.4	195.3	192.3	189.2
65°	185.8	177.4	169.0	163.8	162.0	160.1	158.1	156.2
67.5°	148.7	142.3	136.0	131.9	129.9	127.8	125.8	123.8
70°	125.6	119.7	113.6	109.7	107.8	105.9	104.0	102.1
72.5°	104.9	100.1	95.1	92.3	91.5	90.7	89.9	89.1
75°	78.6	76.9	75.1	74.1	73.7	73.4	73.0	72.7
77.5°	59.3	58.4	57.4	56.8	56.5	56.0	55.7	55.3
80°	47.7	47.2	46.7	46.3	45.9	45.5	45.2	44.8
82.5°	36.6	36.1	35.5	35.2	35.1	35.1	35.0	34.9
85°	21.0	20.6	20.3	20.1	20.1	20.1	20.1	20.1
87.5°	10.1	10.1	10.0	9.9	9.8	9.7	9.6	9.5
90°	11.7	12.1	12.5	12.8	13.0	13.2	13.4	13.6
92.5°	12.9	13.5	14.2	14.5	14.7	14.8	14.9	15.0
95°	15.5	16.2	16.9	17.3	17.3	17.3	17.3	17.3
97.5°	16.3	17.1	17.9	18.3	18.4	18.5	18.6	18.7
100°	16.6	17.4	18.2	18.7	18.8	18.9	19.0	19.1
102.5°	24.8	22.3	19.9	18.7	18.9	19.1	19.2	19.4
105°	63.6	45.8	28.0	19.2	19.4	19.6	19.8	20.0
107.5°	155.9	142.9	129.8	116.5	103.0	89.6	76.1	62.7
110°	197.9	194.6	191.3	182.5	168.0	153.6	139.2	124.8



TEST NUMBER: P332412-840

CATALOG NUMBER: S123RDIW-S560D460U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	227.6	227.6	227.7	226.2	223.2	220.2	217.1	214.1
115°	262.5	263.5	264.5	265.2	265.6	266.0	266.4	266.8
117.5°	294.0	294.8	295.6	296.0	296.1	296.2	296.3	296.4
120°	314.7	315.5	316.3	316.7	316.7	316.7	316.7	316.7
122.5°	334.9	335.5	336.0	336.3	336.4	336.5	336.6	336.7
125°	363.3	363.6	363.8	364.0	364.2	364.4	364.6	364.8
127.5°	391.9	392.2	392.5	392.6	392.4	392.2	392.0	391.8
130°	409.1	409.5	409.9	410.0	409.8	409.6	409.4	409.2
132.5°	425.5	425.9	426.3	426.4	426.1	425.8	425.5	425.3
135°	450.2	450.5	450.8	450.8	450.5	450.2	449.9	449.6
137.5°	472.3	472.7	473.2	473.4	473.2	473.0	472.8	472.6
140°	486.3	486.7	487.1	487.2	487.0	486.8	486.6	486.4
142.5°	499.6	499.9	500.2	500.2	499.9	499.7	499.4	499.1
145°	518.1	518.3	518.5	518.6	518.6	518.6	518.6	518.6
147.5°	534.7	534.9	535.1	534.9	534.5	534.0	533.6	533.1
150°	544.8	545.0	545.2	545.2	544.9	544.6	544.3	544.0
152.5°	553.9	554.2	554.6	554.5	554.1	553.6	553.2	552.7
155°	566.3	566.8	567.3	567.2	566.6	566.0	565.4	564.9
157.5°	577.1	577.7	578.3	578.2	577.4	576.7	575.9	575.1
160°	583.3	583.9	584.5	584.5	583.8	583.1	582.4	581.7
162.5°	589.0	589.7	590.3	590.4	589.7	589.1	588.4	587.8
165°	596.4	597.2	598.0	598.0	597.3	596.7	596.0	595.3
167.5°	602.3	603.0	603.8	603.8	603.0	602.3	601.5	600.7
170°	605.5	606.3	607.1	607.1	606.3	605.5	604.7	603.9
172.5°	607.6	608.4	609.3	609.3	608.3	607.4	606.6	605.7
175°	610.3	611.0	611.7	611.7	610.9	610.1	609.3	608.4
177.5°	611.3	611.9	612.6	612.5	611.7	610.9	610.1	609.3
180°	610.7	610.7	610.7	610.7	610.7	610.7	610.7	610.7

(END OF REPORT)