

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333034-927

Luminaire Tested: **S124RDIW-S350D1560U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333034-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S350D1560U927-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5421.0 lumens
Efficiency: N/A
Efficacy: 101.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333034-927

CATALOG NUMBER: S124RDIW-S350D1560U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333034-927

CATALOG NUMBER: S124RDIW-S350D1560U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	100	100	100	100	89	89	89	89	67	67	67	48	48	48	29	29	29	21				
1	91	87	84	80	81	77	74	72	59	57	55	42	41	40	26	26	25	18				
2	83	76	70	66	73	68	63	59	52	48	46	37	35	33	23	22	21	15				
3	76	67	60	55	67	60	54	49	46	42	38	33	30	28	21	19	18	13				
4	69	59	52	46	61	53	46	42	40	36	33	29	26	24	18	17	16	11				
5	64	53	45	39	56	47	40	36	36	32	28	26	23	21	17	15	14	10				
6	58	47	39	34	52	42	35	31	32	28	24	23	20	18	15	13	12	9				
7	54	42	35	30	48	38	31	27	29	25	21	21	18	16	14	12	11	8				
8	50	38	31	26	44	34	28	24	27	22	19	19	16	14	13	11	10	7				
9	46	35	28	23	41	31	25	21	24	20	17	18	15	13	12	10	9	6				
10	43	32	25	20	38	28	23	19	22	18	15	16	13	11	11	9	8	6				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3953	3953	3953
5°	3962	3914	3938
10°	3937	3867	3867
15°	3892	3786	3758
20°	3830	3679	3611
25°	3751	3553	3463
30°	3674	3422	3278
35°	3588	3286	3094
40°	3485	3130	2893
45°	3391	2975	2689
50°	3282	2798	2473
55°	3167	2612	2238
60°	3039	2409	1997
65°	2923	2157	1761
70°	2752	1876	1496
75°	2539	1556	1216
80°	2213	1186	1116
85°	1880	1074	1010



TEST NUMBER: P333034-927

CATALOG NUMBER: S124RDIW-S350D1560U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.0	0.8
10°-20°	128.3	2.4
20°-30°	185.2	3.4
30°-40°	210.0	3.9
40°-50°	202.8	3.7
50°-60°	168.6	3.1
60°-70°	116.4	2.1
70°-80°	59.0	1.1
80°-90°	19.8	0.4
90°-100°	101.9	1.9
100°-110°	301.8	5.6
110°-120°	512.2	9.4
120°-130°	675.4	12.5
130°-140°	758.5	14.0
140°-150°	745.3	13.7
150°-160°	626.9	11.6
160°-170°	417.1	7.7
170°-180°	146.1	2.7
0°-30°	359.5	6.6
0°-40°	569.5	10.5
0°-60°	940.8	17.4
0°-90°	1136.0	21.0
90°-120°	915.8	16.9
90°-150°	3095.0	57.1
90°-180°	4285.0	79.0
0°-180°	5421.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	490	490	490	490	490	
5°	489	487	483	486	486	46
15°	466	462	453	452	450	131
25°	421	414	399	393	389	194
35°	364	352	333	321	314	227
45°	297	283	261	243	236	229
55°	225	209	186	167	159	201
65°	153	136	113	97	92	151
75°	81	67	50	42	39	86
85°	20	13	12	11	11	23
90°	4	17	26	33	36	6
95°	72	82	91	94	94	80
105°	278	280	284	288	291	295
115°	521	521	518	517	516	513
125°	758	758	757	755	752	676
135°	978	985	986	983	980	757
145°	1188	1193	1194	1193	1190	743
155°	1362	1362	1360	1365	1360	626
165°	1482	1479	1476	1483	1479	418
175°	1542	1536	1535	1542	1535	146
180°	1544	1544	1544	1544	1544	



TEST NUMBER: P333034-927

CATALOG NUMBER: S124RDIW-S350D1560U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	489.7	489.7	489.7	489.7	489.7	489.7	489.7	489.7	489.7	489.7	489.7
2.5°	490.9	490.6	490.4	490.1	489.8	489.3	488.6	487.9	487.1	486.4	487.1
5°	488.9	488.6	488.3	488.0	487.6	487.0	485.9	485.0	483.9	483.0	483.8
7.5°	484.5	484.2	483.9	483.5	483.2	482.3	481.0	479.7	478.4	477.1	477.6
10°	480.3	479.9	479.5	479.1	478.6	477.7	476.2	474.7	473.2	471.7	472.1
12.5°	474.9	474.4	474.0	473.5	473.0	471.9	470.1	468.3	466.6	464.8	465.0
15°	465.7	464.9	464.2	463.4	462.7	461.3	459.2	457.1	455.0	453.0	452.8
17.5°	454.6	453.4	452.3	451.3	450.2	448.4	445.9	443.4	440.9	438.4	437.9
20°	445.8	444.7	443.7	442.6	441.5	439.6	436.7	433.9	431.0	428.2	427.5
22.5°	436.3	435.0	433.8	432.6	431.3	429.2	426.2	423.2	420.2	417.1	416.1
25°	421.1	419.6	418.1	416.6	415.1	412.6	409.2	405.8	402.3	398.9	397.5
27.5°	405.2	403.3	401.4	399.6	397.7	394.9	391.3	387.6	384.0	380.3	378.5
30°	394.1	392.0	389.9	387.9	385.8	382.8	378.8	374.9	371.0	367.1	365.0
32.5°	382.4	380.0	377.7	375.3	373.0	369.8	365.8	361.7	357.7	353.6	351.2
35°	364.1	361.4	358.8	356.1	353.4	350.0	345.9	341.7	337.5	333.4	330.5
37.5°	344.5	341.7	339.1	336.3	333.5	329.9	325.2	320.6	316.0	311.4	308.2
40°	330.7	328.0	325.2	322.5	319.7	316.0	311.2	306.5	301.7	297.0	293.5
42.5°	317.5	314.7	311.7	308.9	306.0	302.1	297.1	292.2	287.2	282.3	278.7
45°	297.0	293.9	290.8	287.7	284.6	280.6	275.6	270.6	265.6	260.6	256.5
47.5°	275.8	272.6	269.4	266.2	263.0	258.8	253.7	248.4	243.2	238.1	233.8
50°	261.3	258.1	254.8	251.6	248.3	244.1	238.8	233.4	228.1	222.8	218.6
52.5°	246.7	243.4	240.3	237.1	233.9	229.6	224.1	218.6	213.2	207.7	203.5
55°	225.0	221.7	218.3	215.0	211.7	207.2	201.8	196.5	191.0	185.6	181.3
57.5°	203.5	200.0	196.6	193.1	189.6	185.3	179.9	174.6	169.3	163.9	159.5
60°	188.2	184.9	181.6	178.2	174.9	170.6	165.2	159.9	154.6	149.2	144.9
62.5°	174.4	171.0	167.5	164.1	160.6	156.1	150.7	145.2	139.7	134.3	130.2
65°	153.0	149.4	145.8	142.3	138.6	134.2	128.9	123.5	118.2	112.9	109.3
67.5°	130.7	127.3	123.8	120.4	117.0	112.8	107.8	102.9	97.9	93.0	89.9
70°	116.6	113.1	109.6	106.2	102.6	98.5	93.7	89.0	84.2	79.5	76.8
72.5°	101.6	98.5	95.3	92.1	89.0	85.2	80.6	76.1	71.7	67.2	64.9
75°	81.4	78.3	75.2	72.1	69.0	65.5	61.6	57.7	53.8	49.9	47.9
77.5°	60.8	58.2	55.6	53.0	50.4	47.5	44.3	41.1	37.9	34.8	33.7
80°	47.6	45.2	42.8	40.4	37.9	35.5	33.0	30.5	28.0	25.5	25.3
82.5°	36.2	34.0	31.8	29.5	27.3	25.5	24.1	22.7	21.2	19.8	19.6
85°	20.3	18.6	17.0	15.2	13.5	12.6	12.4	12.1	11.9	11.6	11.5
87.5°	7.6	7.7	7.7	7.8	7.8	8.0	8.4	8.7	9.1	9.4	9.7
90°	3.6	6.5	9.4	12.4	15.3	17.8	19.9	22.0	24.2	26.3	27.9
92.5°	25.6	28.9	32.2	35.6	39.0	41.4	42.9	44.4	45.8	47.3	48.2
95°	71.7	74.1	76.4	78.8	81.2	83.3	85.2	87.1	89.0	90.8	91.6
97.5°	125.2	127.1	129.0	130.9	132.8	134.9	137.0	139.2	141.4	143.5	144.5
100°	167.2	168.3	169.4	170.4	171.5	173.2	175.6	178.0	180.4	182.8	183.3
102.5°	211.2	211.6	212.1	212.5	212.9	214.2	216.3	218.6	220.7	222.9	223.6
105°	278.3	278.6	278.8	279.1	279.4	280.0	281.1	282.2	283.2	284.3	285.1
107.5°	348.8	349.1	349.4	349.7	350.1	350.3	350.5	350.6	350.8	350.9	351.6
110°	396.6	397.1	397.6	398.2	398.7	398.9	398.5	398.3	398.0	397.8	397.2



TEST NUMBER: P333034-927

CATALOG NUMBER: S124RDIW-S350D1560U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	446.2	446.4	446.5	446.6	446.7	446.5	446.0	445.5	445.0	444.6	444.5
115°	520.8	520.8	520.8	520.8	520.8	520.5	520.0	519.4	519.0	518.4	518.2
117.5°	591.0	591.2	591.4	591.7	591.9	591.8	591.4	591.0	590.7	590.3	589.4
120°	637.9	638.9	640.0	641.0	642.1	642.2	641.4	640.6	639.8	639.1	637.7
122.5°	686.6	687.0	687.5	687.9	688.2	688.3	687.9	687.5	687.2	686.8	686.0
125°	758.5	758.5	758.5	758.5	758.5	758.4	758.1	757.8	757.6	757.3	756.8
127.5°	823.7	824.5	825.3	826.1	826.9	827.1	826.6	826.2	825.9	825.4	824.8
130°	869.6	870.4	871.2	872.0	872.7	873.1	873.1	873.1	873.1	873.1	872.7
132.5°	916.4	917.0	917.6	918.1	918.8	918.9	918.7	918.5	918.3	918.1	917.6
135°	978.3	979.9	981.4	983.1	984.7	985.5	985.5	985.5	985.5	985.5	984.9
137.5°	1045.7	1046.4	1047.1	1047.9	1048.6	1049.2	1049.6	1050.0	1050.5	1050.9	1050.2
140°	1090.6	1091.1	1091.6	1092.2	1092.7	1093.0	1093.0	1093.0	1093.0	1093.0	1092.7
142.5°	1131.6	1132.2	1132.7	1133.2	1133.8	1133.9	1133.7	1133.5	1133.3	1133.1	1133.1
145°	1188.5	1189.5	1190.6	1191.7	1192.8	1193.4	1193.7	1194.0	1194.2	1194.5	1194.2
147.5°	1244.9	1246.2	1247.4	1248.7	1250.0	1250.5	1250.3	1250.1	1249.9	1249.7	1249.4
150°	1279.3	1280.3	1281.4	1282.5	1283.6	1284.0	1284.0	1284.0	1284.0	1284.0	1284.0
152.5°	1311.8	1312.4	1313.0	1313.7	1314.3	1314.8	1314.9	1315.2	1315.4	1315.6	1316.2
155°	1361.7	1361.7	1361.7	1361.7	1361.7	1361.6	1361.3	1361.0	1360.8	1360.5	1361.6
157.5°	1403.7	1403.3	1402.8	1402.3	1401.8	1401.6	1401.5	1401.4	1401.4	1401.4	1402.2
160°	1428.6	1428.3	1428.1	1427.8	1427.5	1427.3	1427.0	1426.7	1426.5	1426.2	1427.0
162.5°	1451.5	1450.9	1450.2	1449.5	1448.7	1448.3	1448.0	1447.8	1447.5	1447.2	1448.7
165°	1482.3	1481.5	1480.7	1480.0	1479.2	1478.5	1478.0	1477.4	1476.9	1476.4	1478.0
167.5°	1506.0	1504.9	1503.8	1502.7	1501.6	1501.0	1501.1	1501.1	1501.2	1501.3	1502.8
170°	1519.4	1518.1	1516.7	1515.4	1514.1	1513.5	1513.8	1514.1	1514.3	1514.6	1516.2
172.5°	1528.9	1527.8	1526.7	1525.6	1524.5	1523.9	1524.0	1524.1	1524.1	1524.2	1526.0
175°	1542.1	1540.7	1539.4	1538.1	1536.8	1536.0	1535.7	1535.4	1535.2	1534.9	1536.8
177.5°	1546.3	1545.3	1544.3	1543.2	1542.1	1541.6	1541.6	1541.6	1541.6	1541.6	1543.1
180°	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4



TEST NUMBER: P333034-927

CATALOG NUMBER: S124RDIW-S350D1560U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	489.7	489.7	489.7	489.7	489.7	489.7	489.7	489.7
2.5°	487.9	488.6	489.3	489.6	489.6	489.6	489.5	489.4
5°	484.7	485.4	486.3	486.6	486.5	486.3	486.1	485.9
7.5°	478.2	478.7	479.3	479.3	479.1	478.9	478.6	478.3
10°	472.4	472.7	473.0	473.0	472.7	472.4	472.1	471.7
12.5°	465.2	465.4	465.6	465.5	465.0	464.5	464.1	463.6
15°	452.7	452.5	452.3	451.9	451.3	450.8	450.2	449.6
17.5°	437.4	437.0	436.6	435.9	435.0	434.1	433.2	432.4
20°	426.9	426.2	425.6	424.7	423.6	422.5	421.4	420.3
22.5°	415.1	414.1	413.1	412.2	411.3	410.4	409.6	408.6
25°	396.1	394.7	393.3	392.2	391.3	390.5	389.7	388.8
27.5°	376.8	375.0	373.3	371.9	370.6	369.4	368.2	367.0
30°	362.9	360.8	358.8	357.0	355.7	354.4	353.1	351.7
32.5°	348.8	346.3	344.0	342.1	340.8	339.5	338.3	337.0
35°	327.6	324.9	322.0	319.9	318.4	316.9	315.4	313.9
37.5°	305.1	301.9	298.7	296.4	294.9	293.3	291.8	290.3
40°	289.9	286.5	283.0	280.5	279.0	277.5	276.0	274.5
42.5°	275.1	271.6	268.0	265.5	263.9	262.3	260.7	259.2
45°	252.5	248.3	244.2	241.5	240.0	238.4	236.9	235.5
47.5°	229.6	225.3	221.1	218.2	216.5	214.8	213.2	211.6
50°	214.4	210.2	206.0	203.2	201.6	200.0	198.4	196.9
52.5°	199.2	195.0	190.8	187.8	186.2	184.6	182.9	181.3
55°	177.0	172.6	168.3	165.3	163.7	162.2	160.6	159.0
57.5°	155.1	150.8	146.3	143.5	142.4	141.2	139.9	138.7
60°	140.5	136.3	131.9	129.0	127.7	126.4	125.1	123.7
62.5°	126.3	122.2	118.3	115.7	114.6	113.6	112.5	111.5
65°	105.7	102.1	98.5	96.3	95.2	94.3	93.2	92.2
67.5°	86.8	83.7	80.6	78.6	77.5	76.4	75.3	74.1
70°	74.0	71.2	68.5	66.7	65.8	65.0	64.2	63.4
72.5°	62.5	60.1	57.8	56.2	55.5	54.7	53.9	53.2
75°	46.0	44.1	42.2	41.0	40.5	40.0	39.5	39.0
77.5°	32.6	31.4	30.3	29.7	29.5	29.4	29.2	29.1
80°	25.0	24.7	24.5	24.3	24.2	24.2	24.1	24.0
82.5°	19.4	19.3	19.1	18.9	18.9	18.8	18.7	18.6
85°	11.3	11.1	10.9	10.9	10.9	10.9	10.9	10.9
87.5°	10.0	10.2	10.5	10.7	10.9	11.0	11.2	11.3
90°	29.5	31.1	32.6	33.7	34.2	34.8	35.3	35.8
92.5°	49.2	50.1	51.1	51.7	52.0	52.4	52.7	53.0
95°	92.4	93.2	94.0	94.3	94.3	94.3	94.3	94.3
97.5°	145.5	146.5	147.4	147.9	147.9	147.9	147.9	147.9
100°	183.8	184.3	184.9	185.1	185.1	185.1	185.1	185.1
102.5°	224.3	225.1	225.9	226.3	226.6	226.8	227.0	227.2
105°	285.9	286.7	287.5	288.3	289.1	289.9	290.7	291.4
107.5°	352.4	353.2	353.9	354.3	354.2	354.2	354.1	354.0
110°	396.7	396.2	395.6	395.8	396.6	397.4	398.2	398.9



TEST NUMBER: P333034-927

CATALOG NUMBER: S124RDIW-S350D1560U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	444.3	444.3	444.2	444.2	444.3	444.5	444.7	444.8
115°	517.8	517.6	517.4	517.1	516.8	516.6	516.3	516.0
117.5°	588.5	587.6	586.7	586.0	585.4	584.9	584.4	583.8
120°	636.4	635.1	633.7	633.3	633.9	634.4	634.9	635.5
122.5°	685.0	684.1	683.3	682.3	681.4	680.4	679.5	678.5
125°	756.2	755.7	755.2	754.6	754.1	753.6	753.0	752.5
127.5°	824.3	823.8	823.2	822.8	822.4	822.0	821.5	821.1
130°	872.1	871.6	871.0	870.2	869.2	868.2	867.0	866.0
132.5°	917.0	916.5	915.9	915.4	915.0	914.7	914.2	913.8
135°	984.4	983.9	983.3	982.6	981.8	981.0	980.2	979.5
137.5°	1049.6	1048.8	1048.1	1047.9	1048.1	1048.2	1048.4	1048.5
140°	1092.4	1092.2	1091.9	1091.6	1091.4	1091.1	1090.8	1090.6
142.5°	1133.0	1132.9	1132.9	1132.8	1132.7	1132.7	1132.7	1132.6
145°	1194.0	1193.7	1193.4	1192.9	1192.1	1191.3	1190.5	1189.7
147.5°	1249.3	1249.0	1248.8	1248.6	1248.3	1248.1	1247.8	1247.5
150°	1284.0	1284.0	1284.0	1284.0	1283.7	1283.4	1283.2	1282.9
152.5°	1316.8	1317.5	1318.1	1318.1	1317.4	1316.8	1316.1	1315.3
155°	1362.6	1363.7	1364.8	1364.8	1363.7	1362.6	1361.6	1360.5
157.5°	1403.0	1403.7	1404.5	1404.5	1403.6	1402.7	1401.8	1400.9
160°	1427.8	1428.6	1429.4	1429.1	1427.8	1426.5	1425.1	1423.8
162.5°	1450.1	1451.5	1452.9	1453.0	1451.7	1450.4	1449.1	1447.7
165°	1479.6	1481.1	1482.7	1483.0	1481.9	1480.9	1479.8	1478.8
167.5°	1504.4	1506.0	1507.6	1507.6	1505.9	1504.3	1502.6	1500.9
170°	1517.8	1519.4	1521.0	1520.8	1519.0	1517.1	1515.3	1513.4
172.5°	1527.8	1529.5	1531.4	1531.4	1529.5	1527.6	1525.7	1523.9
175°	1538.7	1540.5	1542.4	1542.4	1540.5	1538.7	1536.8	1534.9
177.5°	1544.6	1546.0	1547.5	1547.4	1545.7	1544.0	1542.4	1540.6
180°	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4

(END OF REPORT)