

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333046-927

Luminaire Tested: **S124RDIW-S575D1050U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333046-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S575D1050U927-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1050 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4742.1 lumens
Efficiency: N/A
Efficacy: 104.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 45.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333046-927

CATALOG NUMBER: S124RDIW-S575D1050U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333046-927

CATALOG NUMBER: S124RDIW-S575D1050U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	96	91	88	84	87	83	80	77	68	66	64	54	53	51	41	40	39	34
2	87	80	74	69	79	73	68	64	60	56	53	48	45	43	36	35	34	28
3	80	70	63	58	72	64	58	53	53	49	45	42	39	37	33	30	29	24
4	73	62	55	49	66	57	50	45	47	42	38	38	34	32	29	27	25	21
5	67	56	48	42	61	51	44	39	42	37	33	34	30	27	26	24	22	18
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	24	21	19	16
7	57	45	37	32	52	41	35	30	34	29	25	28	24	21	22	19	17	14
8	53	41	33	28	48	38	31	26	31	26	23	26	22	19	20	17	15	13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12
10	46	34	27	22	42	32	25	21	26	22	18	22	18	15	17	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6500	6500	6500
5°	6514	6434	6474
10°	6473	6357	6357
15°	6399	6224	6177
20°	6296	6048	5936
25°	6167	5842	5694
30°	6039	5626	5390
35°	5899	5401	5084
40°	5730	5145	4755
45°	5574	4891	4419
50°	5397	4598	4064
55°	5206	4294	3678
60°	4996	3961	3284
65°	4804	3543	2896
70°	4525	3085	2460
75°	4173	2558	1999
80°	3640	1948	1836
85°	3084	1769	1658



TEST NUMBER: P333046-927

CATALOG NUMBER: S124RDIW-S575D1050U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.6	1.6
10°-20°	210.9	4.4
20°-30°	304.5	6.4
30°-40°	345.2	7.3
40°-50°	333.3	7.0
50°-60°	277.2	5.8
60°-70°	191.4	4.0
70°-80°	97.0	2.0
80°-90°	28.0	0.6
90°-100°	68.4	1.4
100°-110°	202.7	4.3
110°-120°	344.1	7.3
120°-130°	453.7	9.6
130°-140°	509.6	10.7
140°-150°	500.8	10.6
150°-160°	421.2	8.9
160°-170°	280.2	5.9
170°-180°	98.1	2.1
0°-30°	591.0	12.5
0°-40°	936.2	19.7
0°-60°	1546.7	32.6
0°-90°	1863.1	39.3
90°-120°	615.3	13.0
90°-150°	2079.4	43.9
90°-180°	2879.0	60.7
0°-180°	4742.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	805	805	805	805	805	
5°	804	801	794	800	799	76
15°	766	760	745	743	739	216
25°	692	680	656	646	639	319
35°	599	578	548	528	516	374
45°	488	465	428	399	387	376
55°	370	344	305	274	261	331
65°	252	224	186	160	152	248
75°	134	111	82	68	64	141
85°	33	22	19	18	18	38
90°	2	11	18	22	24	5
95°	48	55	61	63	63	54
105°	187	188	191	193	196	198
115°	350	350	348	348	347	345
125°	510	510	509	507	506	454
135°	657	662	662	660	658	508
145°	798	802	802	802	799	500
155°	915	915	914	917	914	421
165°	996	994	992	996	994	281
175°	1036	1032	1031	1036	1031	98
180°	1038	1038	1038	1038	1038	



TEST NUMBER: P333046-927

CATALOG NUMBER: S124RDIW-S575D1050U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	805.1	805.1	805.1	805.1	805.1	805.1	805.1	805.1	805.1	805.1	805.1
2.5°	807.1	806.6	806.2	805.7	805.3	804.5	803.3	802.1	800.8	799.6	800.8
5°	803.8	803.3	802.7	802.2	801.7	800.6	798.9	797.3	795.6	794.0	795.4
7.5°	796.5	796.0	795.4	794.9	794.2	792.9	790.8	788.6	786.5	784.3	785.2
10°	789.6	789.0	788.3	787.6	787.0	785.4	782.9	780.4	777.9	775.5	776.0
12.5°	780.8	780.0	779.2	778.4	777.6	775.8	772.9	769.9	767.1	764.1	764.5
15°	765.6	764.4	763.2	761.9	760.7	758.4	754.9	751.5	748.1	744.7	744.4
17.5°	747.3	745.4	743.7	741.9	740.1	737.2	733.1	729.0	724.8	720.7	720.0
20°	732.9	731.2	729.4	727.6	725.8	722.6	718.0	713.3	708.6	704.0	702.9
22.5°	717.2	715.2	713.2	711.1	709.2	705.7	700.7	695.7	690.7	685.7	684.0
25°	692.3	689.8	687.3	684.8	682.4	678.3	672.7	667.1	661.5	655.9	653.6
27.5°	666.1	663.1	660.0	656.9	653.7	649.2	643.2	637.2	631.2	625.2	622.3
30°	647.8	644.4	641.0	637.6	634.2	629.2	622.8	616.4	609.9	603.5	600.1
32.5°	628.7	624.8	620.9	617.0	613.2	607.9	601.3	594.6	588.0	581.3	577.3
35°	598.6	594.2	589.8	585.4	581.1	575.4	568.5	561.7	554.8	548.0	543.4
37.5°	566.4	561.9	557.4	552.9	548.3	542.2	534.6	527.0	519.5	511.9	506.7
40°	543.7	539.2	534.6	530.1	525.6	519.4	511.7	503.8	496.1	488.2	482.4
42.5°	522.0	517.3	512.5	507.8	503.0	496.6	488.5	480.3	472.2	464.1	458.2
45°	488.2	483.2	478.1	473.0	467.9	461.3	453.0	444.9	436.7	428.4	421.7
47.5°	453.4	448.1	442.8	437.6	432.4	425.5	416.9	408.4	399.9	391.3	384.4
50°	429.7	424.3	419.0	413.6	408.3	401.2	392.4	383.7	374.9	366.1	359.3
52.5°	405.5	400.3	395.1	389.8	384.5	377.5	368.4	359.5	350.5	341.5	334.5
55°	369.9	364.4	358.9	353.4	347.9	340.7	331.8	323.0	314.0	305.1	298.0
57.5°	334.6	328.9	323.2	317.5	311.8	304.6	295.8	287.0	278.3	269.5	262.3
60°	309.4	304.0	298.5	293.0	287.6	280.4	271.6	262.8	254.1	245.3	238.2
62.5°	286.8	281.1	275.4	269.7	264.0	256.7	247.6	238.7	229.7	220.7	214.1
65°	251.5	245.7	239.7	233.9	227.9	220.6	211.8	203.1	194.3	185.5	179.7
67.5°	214.9	209.2	203.6	198.0	192.3	185.4	177.3	169.1	161.1	152.9	147.8
70°	191.7	185.9	180.2	174.4	168.7	161.9	154.1	146.3	138.5	130.7	126.2
72.5°	167.1	161.8	156.6	151.5	146.2	140.0	132.6	125.2	117.8	110.4	106.6
75°	133.8	128.7	123.7	118.6	113.5	107.7	101.3	94.8	88.4	82.0	78.8
77.5°	100.0	95.7	91.4	87.1	82.8	78.0	72.8	67.7	62.4	57.2	55.4
80°	78.3	74.3	70.3	66.4	62.4	58.4	54.3	50.1	46.0	41.9	41.5
82.5°	59.6	55.9	52.3	48.6	45.0	42.0	39.6	37.2	34.9	32.6	32.2
85°	33.3	30.6	27.8	25.0	22.3	20.8	20.4	20.0	19.5	19.1	18.9
87.5°	11.8	11.3	10.9	10.4	9.9	9.7	9.9	10.1	10.3	10.5	10.5
90°	2.4	4.4	6.3	8.3	10.2	12.0	13.4	14.8	16.2	17.7	18.7
92.5°	17.2	19.4	21.7	23.9	26.1	27.8	28.8	29.8	30.8	31.8	32.4
95°	48.2	49.7	51.3	53.0	54.6	56.0	57.3	58.5	59.7	61.0	61.6
97.5°	84.1	85.4	86.7	87.9	89.3	90.6	92.1	93.6	95.0	96.5	97.1
100°	112.3	113.0	113.8	114.5	115.2	116.4	118.0	119.5	121.2	122.8	123.1
102.5°	141.9	142.2	142.4	142.8	143.0	143.9	145.4	146.8	148.3	149.7	150.3
105°	187.0	187.2	187.4	187.5	187.7	188.1	188.9	189.6	190.3	191.0	191.5
107.5°	234.3	234.6	234.7	235.0	235.2	235.4	235.4	235.6	235.7	235.8	236.3
110°	266.4	266.8	267.1	267.5	267.8	267.9	267.8	267.6	267.4	267.2	266.9



TEST NUMBER: P333046-927

CATALOG NUMBER: S124RDIW-S575D1050U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	299.8	299.9	300.0	300.0	300.1	300.0	299.7	299.4	299.0	298.7	298.7
115°	349.9	349.9	349.9	349.9	349.9	349.7	349.4	349.0	348.6	348.3	348.1
117.5°	397.1	397.2	397.4	397.5	397.7	397.6	397.4	397.1	396.9	396.6	396.0
120°	428.6	429.3	430.0	430.7	431.4	431.5	430.9	430.4	429.9	429.4	428.5
122.5°	461.3	461.6	461.8	462.2	462.4	462.5	462.2	461.9	461.7	461.4	460.8
125°	509.6	509.6	509.6	509.6	509.6	509.5	509.3	509.1	509.0	508.8	508.4
127.5°	553.4	554.0	554.4	555.0	555.6	555.7	555.4	555.1	554.8	554.5	554.2
130°	584.2	584.8	585.3	585.8	586.4	586.6	586.6	586.6	586.6	586.6	586.3
132.5°	615.7	616.1	616.5	616.9	617.3	617.3	617.3	617.1	617.0	616.8	616.5
135°	657.3	658.3	659.4	660.4	661.6	662.1	662.1	662.1	662.1	662.1	661.7
137.5°	702.5	703.0	703.5	704.0	704.5	704.9	705.2	705.5	705.8	706.1	705.6
140°	732.7	733.1	733.4	733.8	734.1	734.3	734.3	734.3	734.3	734.3	734.1
142.5°	760.3	760.7	761.0	761.4	761.8	761.8	761.7	761.5	761.4	761.3	761.2
145°	798.5	799.2	799.9	800.7	801.4	801.8	802.0	802.2	802.3	802.5	802.3
147.5°	836.4	837.3	838.1	838.9	839.8	840.2	840.0	839.9	839.7	839.6	839.5
150°	859.5	860.2	860.9	861.7	862.4	862.7	862.7	862.7	862.7	862.7	862.7
152.5°	881.3	881.8	882.2	882.6	883.0	883.3	883.4	883.6	883.8	883.9	884.3
155°	914.9	914.9	914.9	914.9	914.9	914.8	914.6	914.4	914.3	914.1	914.8
157.5°	943.1	942.8	942.5	942.1	941.8	941.7	941.6	941.6	941.5	941.5	942.1
160°	959.8	959.6	959.4	959.3	959.1	958.9	958.7	958.5	958.4	958.2	958.7
162.5°	975.2	974.8	974.3	973.8	973.4	973.0	972.9	972.7	972.5	972.3	973.3
165°	995.9	995.4	994.8	994.3	993.8	993.3	993.0	992.6	992.3	991.9	993.0
167.5°	1011.8	1011.1	1010.3	1009.6	1008.8	1008.4	1008.5	1008.5	1008.5	1008.6	1009.6
170°	1020.8	1019.9	1019.0	1018.1	1017.2	1016.8	1017.1	1017.2	1017.4	1017.6	1018.7
172.5°	1027.2	1026.4	1025.7	1025.0	1024.2	1023.9	1023.9	1024.0	1024.0	1024.0	1025.2
175°	1036.0	1035.1	1034.3	1033.4	1032.5	1032.0	1031.7	1031.6	1031.4	1031.3	1032.5
177.5°	1038.9	1038.2	1037.5	1036.8	1036.1	1035.7	1035.7	1035.7	1035.7	1035.7	1036.7
180°	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7



TEST NUMBER: P333046-927

CATALOG NUMBER: S124RDIW-S575D1050U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	805.1	805.1	805.1	805.1	805.1	805.1	805.1	805.1
2.5°	802.1	803.3	804.5	805.0	804.9	804.8	804.7	804.6
5°	796.7	798.1	799.5	800.0	799.7	799.5	799.2	798.9
7.5°	786.1	787.0	787.9	788.1	787.7	787.2	786.8	786.3
10°	776.6	777.1	777.7	777.7	777.1	776.6	776.0	775.5
12.5°	764.8	765.1	765.5	765.2	764.5	763.7	763.0	762.2
15°	744.1	743.9	743.5	743.0	742.0	741.0	740.1	739.1
17.5°	719.2	718.4	717.6	716.5	715.1	713.7	712.2	710.7
20°	701.8	700.7	699.6	698.2	696.4	694.6	692.8	691.0
22.5°	682.5	680.8	679.1	677.6	676.1	674.7	673.3	671.8
25°	651.3	648.9	646.6	644.8	643.3	642.0	640.6	639.2
27.5°	619.4	616.6	613.7	611.2	609.3	607.3	605.4	603.4
30°	596.7	593.2	589.8	587.0	584.8	582.6	580.4	578.2
32.5°	573.4	569.4	565.4	562.4	560.3	558.3	556.1	554.1
35°	538.7	534.0	529.4	525.9	523.4	520.9	518.4	515.9
37.5°	501.5	496.3	491.1	487.3	484.7	482.3	479.8	477.4
40°	476.7	471.0	465.2	461.1	458.6	456.1	453.7	451.2
42.5°	452.3	446.5	440.6	436.4	433.8	431.3	428.6	426.1
45°	415.0	408.3	401.6	397.0	394.5	392.1	389.6	387.1
47.5°	377.4	370.4	363.5	358.6	355.9	353.2	350.5	347.8
50°	352.4	345.6	338.7	334.1	331.4	328.8	326.2	323.6
52.5°	327.6	320.6	313.7	308.9	306.1	303.4	300.7	298.0
55°	290.9	283.8	276.6	271.8	269.2	266.6	264.0	261.3
57.5°	255.0	247.8	240.6	236.0	234.0	232.0	230.0	228.1
60°	231.1	223.9	216.8	212.2	210.0	207.8	205.7	203.4
62.5°	207.6	201.0	194.4	190.2	188.5	186.7	185.0	183.2
65°	173.8	167.9	162.0	158.2	156.6	155.0	153.3	151.6
67.5°	142.8	137.7	132.6	129.2	127.4	125.6	123.7	121.9
70°	121.7	117.2	112.6	109.6	108.3	106.9	105.5	104.2
72.5°	102.7	98.9	95.0	92.4	91.2	89.9	88.6	87.4
75°	75.7	72.6	69.4	67.4	66.5	65.8	65.0	64.1
77.5°	53.6	51.7	49.8	48.8	48.6	48.3	48.1	47.8
80°	41.1	40.7	40.2	40.0	39.8	39.7	39.6	39.5
82.5°	31.9	31.6	31.4	31.1	31.0	30.8	30.7	30.6
85°	18.5	18.3	18.0	17.9	17.9	17.9	17.9	17.9
87.5°	10.6	10.8	10.9	11.0	11.2	11.3	11.6	11.7
90°	19.8	20.8	21.9	22.7	23.0	23.4	23.7	24.1
92.5°	33.0	33.7	34.4	34.8	35.0	35.2	35.4	35.6
95°	62.0	62.6	63.1	63.4	63.4	63.4	63.4	63.4
97.5°	97.8	98.4	99.0	99.3	99.3	99.3	99.3	99.3
100°	123.5	123.8	124.2	124.4	124.4	124.4	124.4	124.4
102.5°	150.8	151.2	151.8	152.1	152.2	152.3	152.5	152.7
105°	192.1	192.6	193.1	193.7	194.2	194.7	195.3	195.8
107.5°	236.8	237.3	237.8	238.0	238.0	238.0	237.9	237.9
110°	266.5	266.2	265.8	265.9	266.4	267.0	267.5	268.1



TEST NUMBER: P333046-927

CATALOG NUMBER: S124RDIW-S575D1050U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	298.6	298.5	298.4	298.4	298.6	298.7	298.7	298.9
115°	347.9	347.8	347.6	347.4	347.2	347.1	346.9	346.7
117.5°	395.4	394.7	394.2	393.7	393.3	393.0	392.6	392.3
120°	427.5	426.7	425.8	425.5	425.9	426.2	426.6	426.9
122.5°	460.3	459.6	459.0	458.4	457.7	457.1	456.5	455.8
125°	508.1	507.7	507.4	507.0	506.7	506.3	506.0	505.6
127.5°	553.8	553.5	553.1	552.8	552.5	552.2	551.9	551.7
130°	585.9	585.6	585.2	584.7	584.0	583.3	582.6	581.9
132.5°	616.1	615.8	615.4	615.1	614.8	614.5	614.2	613.9
135°	661.4	661.0	660.7	660.2	659.7	659.1	658.6	658.1
137.5°	705.1	704.6	704.2	704.0	704.1	704.3	704.3	704.4
140°	734.0	733.8	733.6	733.4	733.2	733.1	732.8	732.7
142.5°	761.2	761.1	761.1	761.0	761.0	761.0	761.0	761.0
145°	802.2	802.0	801.8	801.5	800.9	800.3	799.9	799.3
147.5°	839.3	839.2	839.0	838.8	838.7	838.5	838.3	838.1
150°	862.7	862.7	862.7	862.6	862.4	862.3	862.1	861.9
152.5°	884.7	885.2	885.6	885.6	885.1	884.6	884.2	883.8
155°	915.5	916.2	917.0	917.0	916.2	915.5	914.8	914.1
157.5°	942.6	943.1	943.6	943.6	943.0	942.4	941.8	941.2
160°	959.3	959.8	960.4	960.1	959.3	958.4	957.5	956.6
162.5°	974.2	975.2	976.2	976.2	975.3	974.5	973.5	972.6
165°	994.0	995.1	996.2	996.3	995.6	994.9	994.2	993.5
167.5°	1010.7	1011.8	1012.9	1012.9	1011.8	1010.7	1009.6	1008.4
170°	1019.7	1020.8	1021.8	1021.8	1020.6	1019.3	1018.0	1016.8
172.5°	1026.4	1027.6	1028.9	1028.8	1027.6	1026.4	1025.1	1023.8
175°	1033.7	1035.0	1036.3	1036.3	1035.0	1033.7	1032.5	1031.3
177.5°	1037.8	1038.7	1039.7	1039.7	1038.5	1037.4	1036.3	1035.1
180°	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7	1037.7

(END OF REPORT)