

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332414-840

Luminaire Tested: **S123RDIW-S560D755U840-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332414-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S560D755U840-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 755 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5302.8 lumens
Efficiency: N/A
Efficacy: 141.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 37.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332414-840

CATALOG NUMBER: S123RDIW-S560D755U840-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332414-840

CATALOG NUMBER: S123RDIW-S560D755U840-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	49	49	49	42
1	97	93	89	86	88	85	82	79	70	68	66	57	55	54	44	43	42	37
2	88	81	76	71	81	75	70	65	62	58	55	50	48	46	40	38	37	32
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	35	33	32	27
4	74	64	56	51	68	59	52	47	49	44	40	40	37	34	32	30	28	24
5	68	57	49	44	62	53	46	41	44	39	35	36	33	30	29	26	24	21
6	63	51	44	38	57	47	41	36	40	35	31	33	29	26	26	24	22	19
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	24	22	19	17
8	54	42	35	30	49	39	32	28	33	28	24	28	24	21	22	20	17	15
9	50	39	31	26	46	36	29	25	30	25	22	25	22	19	21	18	16	14
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9725	9725	9725	9725
5°	11594	9767	8602	9767
10°	14476	9711	7770	9711
15°	16992	9611	7086	9611
20°	18963	9464	6504	9464
25°	18659	9308	6147	9308
30°	13412	9163	5778	9163
35°	8956	8976	5540	8976
40°	6598	8751	5295	8751
45°	5535	8356	5051	8356
50°	4883	7839	4716	7839
55°	4282	7246	4252	7246
60°	3813	6678	3899	6678
65°	3349	6067	3627	6067
70°	2628	5526	3311	5526
75°	2316	4824	3023	4824
80°	2015	4097	2975	4097
85°	1618	3298	3149	3298



TEST NUMBER: P332414-840

CATALOG NUMBER: S123RDIW-S560D755U840-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.9	1.7
10°-20°	277.6	5.2
20°-30°	436.1	8.2
30°-40°	455.0	8.6
40°-50°	389.4	7.3
50°-60°	296.8	5.6
60°-70°	190.2	3.6
70°-80°	91.5	1.7
80°-90°	27.0	0.5
90°-100°	36.4	0.7
100°-110°	173.3	3.3
110°-120°	416.3	7.9
120°-130°	530.1	10.0
130°-140°	566.4	10.7
140°-150°	529.7	10.0
150°-160°	427.3	8.1
160°-170°	275.7	5.2
170°-180°	95.0	1.8
0°-30°	802.6	15.1
0°-40°	1257.6	23.7
0°-60°	1943.7	36.7
0°-90°	2252.5	42.5
90°-120°	626.0	11.8
90°-150°	2252.2	42.5
90°-180°	3050.0	57.5
0°-180°	5302.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	904	904	904	904	904	
5°	1073	904	796	904	1073	111
15°	1525	862	636	862	1525	432
25°	1571	784	518	784	1571	675
35°	682	683	422	683	682	447
45°	364	549	332	549	364	286
55°	228	386	227	386	228	206
65°	132	238	142	238	132	129
75°	56	116	73	116	56	60
85°	13	27	26	27	13	16
90°	22	1	22	1	22	11
95°	28	45	28	45	28	24
105°	33	222	33	222	33	75
115°	437	415	437	415	437	404
125°	597	586	597	586	597	534
135°	736	729	736	729	736	568
145°	849	841	849	841	849	530
155°	925	927	925	927	925	427
165°	975	977	975	977	975	275
175°	996	1000	996	1000	996	95
180°	1000	1000	1000	1000	1000	



TEST NUMBER: P332414-840

CATALOG NUMBER: S123RDIW-S560D755U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5
2.5°	962.3	963.6	959.6	959.0	954.3	953.1	953.1	946.5	942.5	937.3	934.2
5°	1073.0	1079.1	1076.1	1069.1	1057.5	1054.8	1047.4	1035.8	1022.7	1006.4	998.8
7.5°	1211.1	1219.6	1216.3	1205.6	1193.5	1183.6	1162.9	1143.6	1116.6	1093.0	1072.7
10°	1324.4	1315.5	1308.6	1298.1	1286.9	1268.7	1247.1	1217.3	1182.9	1155.8	1125.6
12.5°	1409.2	1407.8	1398.9	1388.2	1372.3	1355.0	1328.4	1292.1	1252.1	1212.9	1178.5
15°	1524.8	1527.1	1521.3	1510.1	1487.6	1457.0	1416.8	1401.8	1344.5	1301.9	1259.4
17.5°	1604.8	1604.3	1603.5	1587.9	1565.1	1543.3	1506.0	1466.3	1414.5	1354.5	1297.3
20°	1655.5	1651.6	1652.4	1635.0	1618.0	1592.9	1556.5	1498.8	1456.3	1387.0	1327.9
22.5°	1654.3	1653.5	1656.4	1650.4	1638.1	1618.8	1590.2	1541.6	1487.2	1417.3	1350.8
25°	1571.1	1568.1	1586.3	1591.2	1611.0	1614.5	1606.0	1579.3	1527.8	1455.9	1373.5
27.5°	1314.9	1313.2	1347.0	1389.2	1442.8	1484.4	1524.6	1544.0	1527.8	1476.3	1393.8
30°	1079.1	1115.5	1132.6	1193.7	1261.7	1342.9	1414.1	1481.8	1498.4	1476.0	1408.4
32.5°	896.0	927.7	941.9	994.4	1057.8	1153.0	1259.7	1355.5	1423.3	1440.5	1399.7
35°	681.6	682.0	714.4	737.6	796.4	894.2	997.9	1126.3	1253.9	1350.7	1360.8
37.5°	543.8	545.7	565.4	588.5	632.7	684.4	775.7	882.4	1029.9	1178.3	1265.4
40°	469.6	473.0	487.8	510.6	542.3	581.4	652.6	753.1	876.1	1041.3	1176.3
42.5°	421.9	427.6	435.2	452.7	472.3	509.0	566.5	644.2	756.0	912.2	1067.9
45°	363.6	366.7	372.4	380.6	398.4	423.9	462.6	514.8	607.6	733.4	889.3
47.5°	320.7	319.1	325.2	331.8	343.7	361.0	387.0	429.6	495.8	596.6	728.9
50°	291.6	291.2	295.5	300.5	311.7	324.6	345.8	377.9	430.5	514.0	635.1
52.5°	264.4	265.9	268.9	275.2	283.3	293.6	312.7	335.8	381.0	453.1	554.0
55°	228.2	229.3	233.6	237.1	242.9	253.4	265.4	284.7	315.6	365.9	449.1
57.5°	197.5	197.0	201.2	202.0	208.5	217.0	226.3	241.4	263.8	301.1	357.2
60°	177.1	176.0	179.5	182.2	185.6	192.6	200.4	215.1	232.9	260.3	308.3
62.5°	158.5	158.0	160.6	163.3	166.1	172.5	179.0	190.3	204.4	227.5	265.6
65°	131.5	132.7	133.8	135.0	136.5	140.4	146.6	154.3	164.0	180.3	207.7
67.5°	103.3	104.5	104.9	107.2	110.6	113.0	116.8	123.7	130.5	144.1	159.8
70°	83.5	83.1	83.5	84.7	89.0	93.2	98.3	103.3	107.6	117.2	130.4
72.5°	71.8	71.1	72.1	72.3	74.4	75.5	78.8	83.5	89.0	95.5	105.0
75°	55.7	55.7	55.7	55.7	57.3	58.1	59.2	60.4	62.3	65.3	72.3
77.5°	41.2	41.2	41.8	42.1	42.5	42.9	43.6	44.8	45.4	47.2	50.1
80°	32.5	32.9	32.5	32.9	32.9	33.6	34.0	35.2	35.5	37.6	38.7
82.5°	24.4	24.2	24.4	24.8	24.8	25.7	25.7	26.6	26.7	27.6	28.8
85°	13.1	12.4	13.1	12.7	13.5	12.7	13.1	13.9	13.9	14.3	15.9
87.5°	7.6	8.1	7.4	7.7	7.6	7.8	7.7	7.6	8.1	7.6	7.5
90°	22.3	21.9	21.6	21.3	21.0	20.5	19.8	19.2	18.5	17.9	15.7
92.5°	24.6	24.4	24.2	24.0	23.8	23.2	22.2	21.1	20.1	19.0	17.4
95°	28.3	28.3	28.3	28.3	28.3	27.7	26.5	25.3	24.2	23.0	21.2
97.5°	30.6	30.5	30.3	30.1	30.0	29.2	27.9	26.6	25.2	23.9	35.9
100°	31.2	31.0	30.9	30.7	30.6	29.8	28.5	27.2	25.9	24.5	50.3
102.5°	31.8	31.5	31.2	30.9	30.6	32.5	36.7	40.7	44.8	48.9	77.1
105°	32.7	32.4	32.0	31.7	31.4	45.8	75.0	104.3	133.5	162.8	177.6
107.5°	102.7	124.7	146.7	168.7	190.9	212.6	234.0	255.4	276.8	298.3	296.0
110°	204.4	227.9	251.6	275.2	298.8	313.4	318.8	324.3	329.7	335.2	333.4



TEST NUMBER: P332414-840

CATALOG NUMBER: S123RDIW-S560D755U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	350.6	355.6	360.6	365.6	370.5	373.0	372.9	372.8	372.7	372.6	370.8
115°	437.0	436.3	435.7	434.9	434.3	433.1	431.5	429.9	428.2	426.6	425.1
117.5°	485.4	485.2	485.1	485.0	484.8	484.1	482.8	481.5	480.2	478.9	478.1
120°	518.7	518.7	518.7	518.7	518.7	518.1	516.7	515.4	514.1	512.7	512.3
122.5°	551.4	551.3	551.1	551.0	550.9	550.4	549.4	548.5	547.5	546.6	546.0
125°	597.4	597.1	596.8	596.5	596.1	595.8	595.5	595.1	594.8	594.5	593.8
127.5°	641.8	642.1	642.4	642.8	643.1	643.0	642.5	642.0	641.4	640.9	640.1
130°	670.2	670.7	671.0	671.3	671.7	671.5	670.8	670.1	669.4	668.8	668.1
132.5°	696.4	696.9	697.4	697.8	698.3	698.2	697.5	696.9	696.2	695.6	695.0
135°	736.4	736.9	737.4	737.9	738.4	738.4	737.9	737.4	736.9	736.4	735.8
137.5°	774.1	774.4	774.7	775.1	775.4	775.2	774.4	773.6	772.7	771.9	771.6
140°	796.6	797.0	797.3	797.6	798.0	797.8	797.1	796.5	795.8	795.2	794.7
142.5°	817.4	817.9	818.4	818.8	819.3	819.2	818.7	818.2	817.7	817.2	816.7
145°	849.4	849.4	849.4	849.4	849.4	849.2	848.9	848.6	848.2	847.9	847.6
147.5°	873.1	873.9	874.6	875.5	876.2	876.5	876.1	875.8	875.5	875.0	874.7
150°	891.0	891.5	892.0	892.5	893.0	893.0	892.7	892.4	892.1	891.7	891.4
152.5°	905.2	906.1	906.8	907.6	908.3	908.4	907.8	907.2	906.6	906.1	905.8
155°	925.1	926.1	927.2	928.2	929.2	929.3	928.4	927.6	926.8	925.9	925.7
157.5°	942.0	943.3	944.5	945.8	947.2	947.3	946.2	945.3	944.3	943.3	943.5
160°	952.7	953.8	955.0	956.1	957.4	957.4	956.4	955.4	954.4	953.4	953.6
162.5°	962.8	963.8	964.8	965.8	966.8	966.8	965.7	964.6	963.5	962.3	962.5
165°	974.9	976.1	977.2	978.5	979.6	979.5	978.2	976.8	975.5	974.2	974.4
167.5°	983.7	985.0	986.3	987.7	989.1	989.1	987.7	986.3	985.0	983.7	983.7
170°	989.1	990.4	991.7	993.1	994.4	994.4	993.1	991.7	990.4	989.1	989.1
172.5°	992.1	993.5	995.0	996.4	997.8	997.9	996.6	995.3	994.0	992.7	992.5
175°	996.5	997.8	999.2	1000.5	1001.8	1001.9	1000.8	999.6	998.5	997.2	997.1
177.5°	997.8	999.2	1000.5	1001.8	1003.1	1003.3	1002.2	1001.2	1000.1	999.1	999.0
180°	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3



TEST NUMBER: P332414-840

CATALOG NUMBER: S123RDIW-S560D755U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5
2.5°	932.9	932.0	927.7	922.7	916.3	911.9	908.5	906.7	901.1	894.2	889.6
5°	990.6	979.0	966.6	951.5	937.6	923.3	914.4	903.9	891.2	876.9	866.8
7.5°	1052.3	1029.6	1005.0	979.8	954.7	932.3	912.5	895.5	875.3	854.7	840.3
10°	1099.6	1066.4	1032.0	996.7	964.6	934.5	911.3	888.5	864.1	840.5	822.7
12.5°	1142.7	1098.9	1059.2	1015.9	974.9	938.9	905.4	878.6	849.3	824.2	803.9
15°	1197.1	1152.3	1104.3	1038.5	984.0	938.4	897.8	862.5	827.0	796.1	776.3
17.5°	1248.0	1180.5	1116.1	1061.2	990.4	933.3	883.7	841.6	802.6	769.8	745.5
20°	1269.1	1203.8	1133.7	1063.7	994.1	930.3	872.6	826.2	785.6	748.4	726.0
22.5°	1281.7	1207.7	1134.0	1058.7	984.8	918.5	861.5	810.4	766.4	731.1	703.5
25°	1296.6	1208.3	1127.1	1052.9	977.4	905.4	837.8	783.7	736.1	698.5	669.1
27.5°	1306.3	1202.5	1106.5	1024.0	947.5	875.9	813.9	756.4	708.1	668.4	636.9
30°	1308.2	1197.9	1090.8	1001.4	923.6	857.9	792.1	737.2	686.2	644.0	614.6
32.5°	1310.6	1186.5	1069.4	974.5	894.9	829.8	770.2	717.7	665.4	623.9	593.9
35°	1300.4	1180.1	1037.0	928.0	848.3	785.2	731.4	683.1	631.7	591.4	560.9
37.5°	1256.5	1155.0	1003.4	875.5	792.1	733.8	689.9	647.8	600.7	557.2	528.5
40°	1212.2	1130.2	977.4	843.6	756.6	696.6	657.1	622.8	577.1	536.4	505.5
42.5°	1146.3	1096.5	952.7	810.2	716.3	658.5	625.3	593.0	553.0	511.7	482.6
45°	1025.4	1032.0	902.0	757.0	660.7	602.6	571.3	548.9	513.3	479.3	449.5
47.5°	873.7	935.2	842.5	700.2	602.0	547.4	520.1	500.5	476.6	443.1	416.0
50°	774.8	862.5	794.9	662.2	565.1	511.0	483.9	468.1	447.2	420.8	395.0
52.5°	683.5	777.8	737.3	619.8	525.2	475.6	449.2	436.2	419.6	394.9	371.4
55°	557.3	652.9	643.6	555.8	465.3	420.8	400.7	386.1	374.8	356.3	337.7
57.5°	450.8	541.4	546.2	484.6	412.5	368.6	351.3	340.2	332.9	318.9	301.7
60°	383.7	466.9	483.1	436.7	374.8	336.1	319.1	310.2	304.4	293.2	280.0
62.5°	328.0	398.8	417.2	383.7	338.6	302.4	289.1	280.5	276.6	266.9	255.3
65°	251.1	309.8	327.6	309.0	285.5	256.4	245.6	238.2	234.8	229.3	220.9
67.5°	188.7	231.7	251.2	238.0	229.5	211.2	204.3	200.4	197.2	193.6	186.4
70°	151.6	183.4	203.5	200.0	193.0	183.4	178.3	175.6	172.5	169.5	163.2
72.5°	121.9	143.7	162.6	164.4	158.6	156.7	152.3	151.2	149.3	145.6	142.2
75°	80.9	95.9	109.1	114.1	116.4	118.4	116.4	116.0	115.6	112.6	110.6
77.5°	53.0	61.1	69.4	78.0	81.6	84.2	84.8	86.2	85.2	83.6	82.7
80°	40.6	42.5	48.4	55.7	61.5	63.8	65.3	66.1	65.7	65.3	63.8
82.5°	29.5	31.1	33.8	39.0	43.8	47.8	48.7	48.5	49.4	49.6	48.4
85°	15.9	16.3	17.1	17.8	20.5	24.7	26.0	26.7	27.5	27.5	25.1
87.5°	7.7	7.0	7.1	6.8	7.4	7.3	8.8	10.1	10.7	9.8	10.1
90°	13.5	11.4	9.3	7.4	5.7	4.0	2.4	0.7	2.4	4.0	5.7
92.5°	15.8	14.1	12.5	12.0	12.4	12.9	13.3	13.8	13.3	12.9	12.4
95°	19.4	17.6	15.8	18.3	25.0	31.8	38.6	45.3	38.6	31.8	25.0
97.5°	47.7	59.6	71.5	79.0	82.0	85.0	88.1	91.1	88.1	85.0	82.0
100°	76.0	101.8	127.5	138.8	135.5	132.2	128.9	125.6	128.9	132.2	135.5
102.5°	105.1	133.3	161.5	174.3	172.0	169.6	167.2	164.8	167.2	169.6	172.0
105°	192.5	207.3	222.2	228.7	226.9	225.1	223.3	221.5	223.3	225.1	226.9
107.5°	293.6	291.2	288.9	287.0	285.6	284.1	282.7	281.1	282.7	284.1	285.6
110°	331.5	329.7	327.9	326.3	325.0	323.7	322.3	321.0	322.3	323.7	325.0



TEST NUMBER: P332414-840

CATALOG NUMBER: S123RDIW-S560D755U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	369.0	367.2	365.4	363.9	362.6	361.4	360.2	359.1	360.2	361.4	362.6
115°	423.5	422.1	420.6	419.4	418.4	417.4	416.4	415.4	416.4	417.4	418.4
117.5°	477.4	476.6	475.8	474.8	473.6	472.4	471.2	470.0	471.2	472.4	473.6
120°	511.8	511.3	510.8	509.8	508.3	506.9	505.3	503.8	505.3	506.9	508.3
122.5°	545.4	544.7	544.1	543.2	542.0	540.8	539.6	538.4	539.6	540.8	542.0
125°	593.2	592.5	591.9	590.9	589.6	588.2	586.9	585.6	586.9	588.2	589.6
127.5°	639.2	638.5	637.7	636.6	635.3	634.0	632.7	631.4	632.7	634.0	635.3
130°	667.5	666.8	666.2	665.2	663.9	662.6	661.3	659.8	661.3	662.6	663.9
132.5°	694.5	694.0	693.5	692.6	691.2	689.8	688.5	687.2	688.5	689.8	691.2
135°	735.1	734.5	733.8	733.0	732.0	730.9	730.0	729.0	730.0	730.9	732.0
137.5°	771.2	770.8	770.5	769.7	768.4	767.2	765.9	764.7	765.9	767.2	768.4
140°	794.2	793.7	793.1	792.4	791.4	790.4	789.4	788.4	789.4	790.4	791.4
142.5°	816.2	815.7	815.2	814.5	813.4	812.4	811.4	810.4	811.4	812.4	813.4
145°	847.3	846.9	846.6	845.9	844.7	843.5	842.3	841.2	842.3	843.5	844.7
147.5°	874.4	874.1	873.7	873.2	872.4	871.7	870.9	870.2	870.9	871.7	872.4
150°	891.1	890.8	890.4	890.0	889.5	889.0	888.5	888.1	888.5	889.0	889.5
152.5°	905.6	905.4	905.2	905.0	904.7	904.5	904.3	904.0	904.3	904.5	904.7
155°	925.6	925.4	925.2	925.3	925.6	926.0	926.3	926.7	926.3	926.0	925.6
157.5°	943.6	943.8	944.0	944.1	944.1	944.1	944.2	944.2	944.2	944.1	944.1
160°	953.7	953.9	954.1	954.2	954.4	954.6	954.7	954.9	954.7	954.6	954.4
162.5°	962.7	962.8	963.0	963.3	963.7	964.1	964.6	965.0	964.6	964.1	963.7
165°	974.5	974.7	974.9	975.2	975.7	976.2	976.7	977.2	976.7	976.2	975.7
167.5°	983.7	983.7	983.7	984.1	984.7	985.4	986.0	986.7	986.0	985.4	984.7
170°	989.1	989.1	989.1	989.5	990.1	990.8	991.4	992.1	991.4	990.8	990.1
172.5°	992.4	992.3	992.1	992.5	993.3	994.0	994.8	995.6	994.8	994.0	993.3
175°	996.9	996.7	996.6	996.9	997.7	998.6	999.4	1000.3	999.4	998.6	997.7
177.5°	998.8	998.7	998.6	998.8	999.5	1000.1	1000.8	1001.4	1000.8	1000.1	999.5
180°	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3



TEST NUMBER: P332414-840

CATALOG NUMBER: S123RDIW-S560D755U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5
2.5°	888.1	884.0	881.3	875.0	871.1	866.8	862.4	865.2	864.8	864.5	864.5
5°	858.3	849.4	841.3	830.8	824.3	816.2	809.9	809.2	810.7	805.3	802.2
7.5°	828.8	816.6	805.1	793.6	781.3	771.5	765.5	762.7	758.7	755.4	751.8
10°	808.0	793.8	782.4	768.2	755.1	743.5	736.1	731.0	728.3	725.6	720.6
12.5°	786.7	772.6	758.3	742.1	729.6	716.2	710.7	705.1	699.8	696.8	689.9
15°	755.4	737.2	722.2	705.1	691.3	678.0	670.3	659.1	657.5	653.7	646.7
17.5°	724.1	704.4	683.6	671.0	655.2	641.6	629.8	626.0	614.9	610.8	604.7
20°	699.3	681.2	665.3	648.6	625.8	613.1	603.8	598.7	589.9	584.4	580.6
22.5°	678.0	659.4	641.2	621.8	602.9	588.7	581.8	574.0	569.2	561.6	557.3
25°	647.5	627.4	605.3	584.4	570.9	560.1	549.3	542.3	535.3	531.8	524.1
27.5°	612.1	591.1	570.5	554.6	538.0	527.3	517.5	511.3	502.9	497.1	492.8
30°	592.6	567.8	550.1	535.7	514.4	504.4	497.1	489.3	483.1	477.0	472.6
32.5°	570.0	547.3	530.5	512.8	496.4	485.5	475.9	469.2	463.9	458.1	453.8
35°	534.5	515.6	498.2	480.4	468.4	457.2	446.0	440.2	435.2	429.7	425.9
37.5°	502.5	484.8	468.3	451.4	436.6	427.4	418.4	413.9	407.2	403.5	399.6
40°	482.7	465.3	447.6	431.3	415.8	408.9	400.7	394.2	388.0	385.3	381.0
42.5°	461.1	443.6	428.7	411.1	398.5	389.0	381.5	374.4	369.7	365.8	363.3
45°	429.0	413.4	398.8	381.4	369.4	361.2	352.7	346.2	341.9	339.2	335.0
47.5°	397.8	382.3	367.4	352.2	340.6	331.3	322.9	318.2	312.7	309.3	306.4
50°	375.2	361.2	345.4	331.4	319.9	310.6	303.7	297.8	292.8	288.5	286.6
52.5°	354.5	339.6	325.9	313.0	300.7	290.1	283.9	277.7	274.0	269.0	266.8
55°	320.2	306.0	294.4	281.6	269.6	260.7	253.0	247.5	243.7	238.2	235.2
57.5°	288.1	275.3	261.5	250.4	238.0	230.6	224.1	216.7	212.1	207.8	204.8
60°	266.5	251.8	239.8	229.3	218.5	208.8	203.1	197.2	192.3	187.9	185.3
62.5°	243.9	231.1	219.7	208.3	198.4	190.0	183.3	178.3	174.0	171.3	168.5
65°	209.2	199.2	187.6	178.3	169.1	162.9	157.4	153.2	150.1	148.1	145.8
67.5°	177.4	167.6	157.5	148.3	142.2	137.4	133.9	130.3	128.8	126.2	124.7
70°	156.6	146.6	137.7	130.8	124.5	121.1	118.8	116.0	114.5	111.4	109.9
72.5°	134.1	126.8	120.4	114.6	109.7	106.5	103.6	100.3	97.8	94.4	92.8
75°	105.6	99.1	94.0	90.1	87.1	82.8	78.6	75.0	73.9	72.7	72.3
77.5°	78.2	74.0	70.4	67.2	63.3	60.2	59.3	58.5	58.3	57.7	57.7
80°	61.5	57.7	54.9	51.1	48.8	48.8	48.8	48.0	48.4	48.4	48.4
82.5°	45.7	42.1	40.7	39.3	38.9	39.2	39.2	39.3	39.1	39.7	39.4
85°	23.6	23.9	24.7	24.3	24.7	24.7	25.5	25.1	25.5	24.7	25.5
87.5°	10.1	11.4	12.2	12.9	13.6	13.7	14.2	14.3	14.7	14.9	15.0
90°	7.4	9.3	11.4	13.5	15.7	17.9	18.5	19.2	19.8	20.5	21.0
92.5°	12.0	12.5	14.1	15.8	17.4	19.0	20.1	21.1	22.2	23.2	23.8
95°	18.3	15.8	17.6	19.4	21.2	23.0	24.2	25.3	26.5	27.7	28.3
97.5°	79.0	71.5	59.6	47.7	35.9	23.9	25.2	26.6	27.9	29.2	30.0
100°	138.8	127.5	101.8	76.0	50.3	24.5	25.9	27.2	28.5	29.8	30.6
102.5°	174.3	161.5	133.3	105.1	77.1	48.9	44.8	40.7	36.7	32.5	30.6
105°	228.7	222.2	207.3	192.5	177.6	162.8	133.5	104.3	75.0	45.8	31.4
107.5°	287.0	288.9	291.2	293.6	296.0	298.3	276.8	255.4	234.0	212.6	190.9
110°	326.3	327.9	329.7	331.5	333.4	335.2	329.7	324.3	318.8	313.4	298.8



TEST NUMBER: P332414-840

CATALOG NUMBER: S123RDIW-S560D755U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	363.9	365.4	367.2	369.0	370.8	372.6	372.7	372.8	372.9	373.0	370.5
115°	419.4	420.6	422.1	423.5	425.1	426.6	428.2	429.9	431.5	433.1	434.3
117.5°	474.8	475.8	476.6	477.4	478.1	478.9	480.2	481.5	482.8	484.1	484.8
120°	509.8	510.8	511.3	511.8	512.3	512.7	514.1	515.4	516.7	518.1	518.7
122.5°	543.2	544.1	544.7	545.4	546.0	546.6	547.5	548.5	549.4	550.4	550.9
125°	590.9	591.9	592.5	593.2	593.8	594.5	594.8	595.1	595.5	595.8	596.1
127.5°	636.6	637.7	638.5	639.2	640.1	640.9	641.4	642.0	642.5	643.0	643.1
130°	665.2	666.2	666.8	667.5	668.1	668.8	669.4	670.1	670.8	671.5	671.7
132.5°	692.6	693.5	694.0	694.5	695.0	695.6	696.2	696.9	697.5	698.2	698.3
135°	733.0	733.8	734.5	735.1	735.8	736.4	736.9	737.4	737.9	738.4	738.4
137.5°	769.7	770.5	770.8	771.2	771.6	771.9	772.7	773.6	774.4	775.2	775.4
140°	792.4	793.1	793.7	794.2	794.7	795.2	795.8	796.5	797.1	797.8	798.0
142.5°	814.5	815.2	815.7	816.2	816.7	817.2	817.7	818.2	818.7	819.2	819.3
145°	845.9	846.6	846.9	847.3	847.6	847.9	848.2	848.6	848.9	849.2	849.4
147.5°	873.2	873.7	874.1	874.4	874.7	875.0	875.5	875.8	876.1	876.5	876.2
150°	890.0	890.4	890.8	891.1	891.4	891.7	892.1	892.4	892.7	893.0	893.0
152.5°	905.0	905.2	905.4	905.6	905.8	906.1	906.6	907.2	907.8	908.4	908.3
155°	925.3	925.2	925.4	925.6	925.7	925.9	926.8	927.6	928.4	929.3	929.2
157.5°	944.1	944.0	943.8	943.6	943.5	943.3	944.3	945.3	946.2	947.3	947.2
160°	954.2	954.1	953.9	953.7	953.6	953.4	954.4	955.4	956.4	957.4	957.4
162.5°	963.3	963.0	962.8	962.7	962.5	962.3	963.5	964.6	965.7	966.8	966.8
165°	975.2	974.9	974.7	974.5	974.4	974.2	975.5	976.8	978.2	979.5	979.6
167.5°	984.1	983.7	983.7	983.7	983.7	983.7	985.0	986.3	987.7	989.1	989.1
170°	989.5	989.1	989.1	989.1	989.1	989.1	990.4	991.7	993.1	994.4	994.4
172.5°	992.5	992.1	992.3	992.4	992.5	992.7	994.0	995.3	996.6	997.9	997.8
175°	996.9	996.6	996.7	996.9	997.1	997.2	998.5	999.6	1000.8	1001.9	1001.8
177.5°	998.8	998.6	998.7	998.8	999.0	999.1	1000.1	1001.2	1002.2	1003.3	1003.1
180°	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3



TEST NUMBER: P332414-840

CATALOG NUMBER: S123RDIW-S560D755U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5
2.5°	860.8	860.5	860.8	859.6	860.8	860.5	860.8	864.5	864.5	864.8	865.2
5°	801.0	800.6	799.5	796.1	799.5	800.6	801.0	802.2	805.3	810.7	809.2
7.5°	748.8	748.3	744.9	745.0	744.9	748.3	748.8	751.8	755.4	758.7	762.7
10°	717.9	718.3	713.7	710.9	713.7	718.3	717.9	720.6	725.6	728.3	731.0
12.5°	687.9	686.1	682.4	679.3	682.4	686.1	687.9	689.9	696.8	699.8	705.1
15°	648.2	644.4	635.1	635.9	635.1	644.4	648.2	646.7	653.7	657.5	659.1
17.5°	601.6	598.7	598.6	593.2	598.6	598.7	601.6	604.7	610.8	614.9	626.0
20°	574.4	572.5	573.2	567.8	573.2	572.5	574.4	580.6	584.4	589.9	598.7
22.5°	553.0	551.1	547.9	546.1	547.9	551.1	553.0	557.3	561.6	569.2	574.0
25°	521.8	518.7	515.6	517.6	515.6	518.7	521.8	524.1	531.8	535.3	542.3
27.5°	490.5	488.2	485.1	484.7	485.1	488.2	490.5	492.8	497.1	502.9	511.3
30°	470.7	468.4	466.9	464.9	466.9	468.4	470.7	472.6	477.0	483.1	489.3
32.5°	450.6	450.2	447.4	447.0	447.4	450.2	450.6	453.8	458.1	463.9	469.2
35°	424.3	422.0	421.2	421.6	421.2	422.0	424.3	425.9	429.7	435.2	440.2
37.5°	399.3	396.3	394.9	393.4	394.9	396.3	399.3	399.6	403.5	407.2	413.9
40°	381.4	378.3	377.5	376.8	377.5	378.3	381.4	381.0	385.3	388.0	394.2
42.5°	361.2	360.0	359.6	358.2	359.6	360.0	361.2	363.3	365.8	369.7	374.4
45°	333.8	333.5	331.1	331.8	331.1	333.5	333.8	335.0	339.2	341.9	346.2
47.5°	304.9	303.2	301.5	302.7	301.5	303.2	304.9	306.4	309.3	312.7	318.2
50°	285.1	284.3	280.8	281.6	280.8	284.3	285.1	286.6	288.5	292.8	297.8
52.5°	265.3	262.4	261.1	260.5	261.1	262.4	265.3	266.8	269.0	274.0	277.7
55°	232.5	228.9	227.4	226.6	227.4	228.9	232.5	235.2	238.2	243.7	247.5
57.5°	200.3	199.3	198.1	198.9	198.1	199.3	200.3	204.8	207.8	212.1	216.7
60°	181.4	181.4	181.4	181.1	181.4	181.4	181.4	185.3	187.9	192.3	197.2
62.5°	166.8	165.9	165.6	166.1	165.6	165.9	166.8	168.5	171.3	174.0	178.3
65°	144.6	144.3	142.7	142.4	142.7	144.3	144.6	145.8	148.1	150.1	153.2
67.5°	123.7	122.3	121.9	121.3	121.9	122.3	123.7	124.7	126.2	128.8	130.3
70°	108.0	107.1	104.8	105.2	104.8	107.1	108.0	109.9	111.4	114.5	116.0
72.5°	90.9	90.1	89.7	89.1	89.7	90.1	90.9	92.8	94.4	97.8	100.3
75°	71.9	71.6	71.2	72.7	71.2	71.6	71.9	72.3	72.7	73.9	75.0
77.5°	57.7	57.7	57.9	57.3	57.9	57.7	57.7	57.7	57.7	58.3	58.5
80°	48.4	48.4	48.0	48.0	48.0	48.4	48.4	48.4	48.4	48.4	48.0
82.5°	38.8	39.1	39.3	38.7	39.3	39.1	38.8	39.4	39.7	39.1	39.3
85°	25.5	25.1	26.0	25.5	26.0	25.1	25.5	25.5	24.7	25.5	25.1
87.5°	15.8	15.1	15.2	15.6	15.2	15.1	15.8	15.0	14.9	14.7	14.3
90°	21.3	21.6	21.9	22.3	21.9	21.6	21.3	21.0	20.5	19.8	19.2
92.5°	24.0	24.2	24.4	24.6	24.4	24.2	24.0	23.8	23.2	22.2	21.1
95°	28.3	28.3	28.3	28.3	28.3	28.3	28.3	28.3	27.7	26.5	25.3
97.5°	30.1	30.3	30.5	30.6	30.5	30.3	30.1	30.0	29.2	27.9	26.6
100°	30.7	30.9	31.0	31.2	31.0	30.9	30.7	30.6	29.8	28.5	27.2
102.5°	30.9	31.2	31.5	31.8	31.5	31.2	30.9	30.6	32.5	36.7	40.7
105°	31.7	32.0	32.4	32.7	32.4	32.0	31.7	31.4	45.8	75.0	104.3
107.5°	168.7	146.7	124.7	102.7	124.7	146.7	168.7	190.9	212.6	234.0	255.4
110°	275.2	251.6	227.9	204.4	227.9	251.6	275.2	298.8	313.4	318.8	324.3



TEST NUMBER: P332414-840

CATALOG NUMBER: S123RDIW-S560D755U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	365.6	360.6	355.6	350.6	355.6	360.6	365.6	370.5	373.0	372.9	372.8
115°	434.9	435.7	436.3	437.0	436.3	435.7	434.9	434.3	433.1	431.5	429.9
117.5°	485.0	485.1	485.2	485.4	485.2	485.1	485.0	484.8	484.1	482.8	481.5
120°	518.7	518.7	518.7	518.7	518.7	518.7	518.7	518.7	518.1	516.7	515.4
122.5°	551.0	551.1	551.3	551.4	551.3	551.1	551.0	550.9	550.4	549.4	548.5
125°	596.5	596.8	597.1	597.4	597.1	596.8	596.5	596.1	595.8	595.5	595.1
127.5°	642.8	642.4	642.1	641.8	642.1	642.4	642.8	643.1	643.0	642.5	642.0
130°	671.3	671.0	670.7	670.2	670.7	671.0	671.3	671.7	671.5	670.8	670.1
132.5°	697.8	697.4	696.9	696.4	696.9	697.4	697.8	698.3	698.2	697.5	696.9
135°	737.9	737.4	736.9	736.4	736.9	737.4	737.9	738.4	738.4	737.9	737.4
137.5°	775.1	774.7	774.4	774.1	774.4	774.7	775.1	775.4	775.2	774.4	773.6
140°	797.6	797.3	797.0	796.6	797.0	797.3	797.6	798.0	797.8	797.1	796.5
142.5°	818.8	818.4	817.9	817.4	817.9	818.4	818.8	819.3	819.2	818.7	818.2
145°	849.4	849.4	849.4	849.4	849.4	849.4	849.4	849.4	849.2	848.9	848.6
147.5°	875.5	874.6	873.9	873.1	873.9	874.6	875.5	876.2	876.5	876.1	875.8
150°	892.5	892.0	891.5	891.0	891.5	892.0	892.5	893.0	893.0	892.7	892.4
152.5°	907.6	906.8	906.1	905.2	906.1	906.8	907.6	908.3	908.4	907.8	907.2
155°	928.2	927.2	926.1	925.1	926.1	927.2	928.2	929.2	929.3	928.4	927.6
157.5°	945.8	944.5	943.3	942.0	943.3	944.5	945.8	947.2	947.3	946.2	945.3
160°	956.1	955.0	953.8	952.7	953.8	955.0	956.1	957.4	957.4	956.4	955.4
162.5°	965.8	964.8	963.8	962.8	963.8	964.8	965.8	966.8	966.8	965.7	964.6
165°	978.5	977.2	976.1	974.9	976.1	977.2	978.5	979.6	979.5	978.2	976.8
167.5°	987.7	986.3	985.0	983.7	985.0	986.3	987.7	989.1	989.1	987.7	986.3
170°	993.1	991.7	990.4	989.1	990.4	991.7	993.1	994.4	994.4	993.1	991.7
172.5°	996.4	995.0	993.5	992.1	993.5	995.0	996.4	997.8	997.9	996.6	995.3
175°	1000.5	999.2	997.8	996.5	997.8	999.2	1000.5	1001.8	1001.9	1000.8	999.6
177.5°	1001.8	1000.5	999.2	997.8	999.2	1000.5	1001.8	1003.1	1003.3	1002.2	1001.2
180°	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3



TEST NUMBER: P332414-840

CATALOG NUMBER: S123RDIW-S560D755U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5
2.5°	862.4	866.8	871.1	875.0	881.3	884.0	888.1	889.6	894.2	901.1	906.7
5°	809.9	816.2	824.3	830.8	841.3	849.4	858.3	866.8	876.9	891.2	903.9
7.5°	765.5	771.5	781.3	793.6	805.1	816.6	828.8	840.3	854.7	875.3	895.5
10°	736.1	743.5	755.1	768.2	782.4	793.8	808.0	822.7	840.5	864.1	888.5
12.5°	710.7	716.2	729.6	742.1	758.3	772.6	786.7	803.9	824.2	849.3	878.6
15°	670.3	678.0	691.3	705.1	722.2	737.2	755.4	776.3	796.1	827.0	862.5
17.5°	629.8	641.6	655.2	671.0	683.6	704.4	724.1	745.5	769.8	802.6	841.6
20°	603.8	613.1	625.8	648.6	665.3	681.2	699.3	726.0	748.4	785.6	826.2
22.5°	581.8	588.7	602.9	621.8	641.2	659.4	678.0	703.5	731.1	766.4	810.4
25°	549.3	560.1	570.9	584.4	605.3	627.4	647.5	669.1	698.5	736.1	783.7
27.5°	517.5	527.3	538.0	554.6	570.5	591.1	612.1	636.9	668.4	708.1	756.4
30°	497.1	504.4	514.4	535.7	550.1	567.8	592.6	614.6	644.0	686.2	737.2
32.5°	475.9	485.5	496.4	512.8	530.5	547.3	570.0	593.9	623.9	665.4	717.7
35°	446.0	457.2	468.4	480.4	498.2	515.6	534.5	560.9	591.4	631.7	683.1
37.5°	418.4	427.4	436.6	451.4	468.3	484.8	502.5	528.5	557.2	600.7	647.8
40°	400.7	408.9	415.8	431.3	447.6	465.3	482.7	505.5	536.4	577.1	622.8
42.5°	381.5	389.0	398.5	411.1	428.7	443.6	461.1	482.6	511.7	553.0	593.0
45°	352.7	361.2	369.4	381.4	398.8	413.4	429.0	449.5	479.3	513.3	548.9
47.5°	322.9	331.3	340.6	352.2	367.4	382.3	397.8	416.0	443.1	476.6	500.5
50°	303.7	310.6	319.9	331.4	345.4	361.2	375.2	395.0	420.8	447.2	468.1
52.5°	283.9	290.1	300.7	313.0	325.9	339.6	354.5	371.4	394.9	419.6	436.2
55°	253.0	260.7	269.6	281.6	294.4	306.0	320.2	337.7	356.3	374.8	386.1
57.5°	224.1	230.6	238.0	250.4	261.5	275.3	288.1	301.7	318.9	332.9	340.2
60°	203.1	208.8	218.5	229.3	239.8	251.8	266.5	280.0	293.2	304.4	310.2
62.5°	183.3	190.0	198.4	208.3	219.7	231.1	243.9	255.3	266.9	276.6	280.5
65°	157.4	162.9	169.1	178.3	187.6	199.2	209.2	220.9	229.3	234.8	238.2
67.5°	133.9	137.4	142.2	148.3	157.5	167.6	177.4	186.4	193.6	197.2	200.4
70°	118.8	121.1	124.5	130.8	137.7	146.6	156.6	163.2	169.5	172.5	175.6
72.5°	103.6	106.5	109.7	114.6	120.4	126.8	134.1	142.2	145.6	149.3	151.2
75°	78.6	82.8	87.1	90.1	94.0	99.1	105.6	110.6	112.6	115.6	116.0
77.5°	59.3	60.2	63.3	67.2	70.4	74.0	78.2	82.7	83.6	85.2	86.2
80°	48.8	48.8	48.8	51.1	54.9	57.7	61.5	63.8	65.3	65.7	66.1
82.5°	39.2	39.2	38.9	39.3	40.7	42.1	45.7	48.4	49.6	49.4	48.5
85°	25.5	24.7	24.7	24.3	24.7	23.9	23.6	25.1	27.5	27.5	26.7
87.5°	14.2	13.7	13.6	12.9	12.2	11.4	10.1	10.1	9.8	10.7	10.1
90°	18.5	17.9	15.7	13.5	11.4	9.3	7.4	5.7	4.0	2.4	0.7
92.5°	20.1	19.0	17.4	15.8	14.1	12.5	12.0	12.4	12.9	13.3	13.8
95°	24.2	23.0	21.2	19.4	17.6	15.8	18.3	25.0	31.8	38.6	45.3
97.5°	25.2	23.9	35.9	47.7	59.6	71.5	79.0	82.0	85.0	88.1	91.1
100°	25.9	24.5	50.3	76.0	101.8	127.5	138.8	135.5	132.2	128.9	125.6
102.5°	44.8	48.9	77.1	105.1	133.3	161.5	174.3	172.0	169.6	167.2	164.8
105°	133.5	162.8	177.6	192.5	207.3	222.2	228.7	226.9	225.1	223.3	221.5
107.5°	276.8	298.3	296.0	293.6	291.2	288.9	287.0	285.6	284.1	282.7	281.1
110°	329.7	335.2	333.4	331.5	329.7	327.9	326.3	325.0	323.7	322.3	321.0



TEST NUMBER: P332414-840

CATALOG NUMBER: S123RDIW-S560D755U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	372.7	372.6	370.8	369.0	367.2	365.4	363.9	362.6	361.4	360.2	359.1
115°	428.2	426.6	425.1	423.5	422.1	420.6	419.4	418.4	417.4	416.4	415.4
117.5°	480.2	478.9	478.1	477.4	476.6	475.8	474.8	473.6	472.4	471.2	470.0
120°	514.1	512.7	512.3	511.8	511.3	510.8	509.8	508.3	506.9	505.3	503.8
122.5°	547.5	546.6	546.0	545.4	544.7	544.1	543.2	542.0	540.8	539.6	538.4
125°	594.8	594.5	593.8	593.2	592.5	591.9	590.9	589.6	588.2	586.9	585.6
127.5°	641.4	640.9	640.1	639.2	638.5	637.7	636.6	635.3	634.0	632.7	631.4
130°	669.4	668.8	668.1	667.5	666.8	666.2	665.2	663.9	662.6	661.3	659.8
132.5°	696.2	695.6	695.0	694.5	694.0	693.5	692.6	691.2	689.8	688.5	687.2
135°	736.9	736.4	735.8	735.1	734.5	733.8	733.0	732.0	730.9	730.0	729.0
137.5°	772.7	771.9	771.6	771.2	770.8	770.5	769.7	768.4	767.2	765.9	764.7
140°	795.8	795.2	794.7	794.2	793.7	793.1	792.4	791.4	790.4	789.4	788.4
142.5°	817.7	817.2	816.7	816.2	815.7	815.2	814.5	813.4	812.4	811.4	810.4
145°	848.2	847.9	847.6	847.3	846.9	846.6	845.9	844.7	843.5	842.3	841.2
147.5°	875.5	875.0	874.7	874.4	874.1	873.7	873.2	872.4	871.7	870.9	870.2
150°	892.1	891.7	891.4	891.1	890.8	890.4	890.0	889.5	889.0	888.5	888.1
152.5°	906.6	906.1	905.8	905.6	905.4	905.2	905.0	904.7	904.5	904.3	904.0
155°	926.8	925.9	925.7	925.6	925.4	925.2	925.3	925.6	926.0	926.3	926.7
157.5°	944.3	943.3	943.5	943.6	943.8	944.0	944.1	944.1	944.1	944.2	944.2
160°	954.4	953.4	953.6	953.7	953.9	954.1	954.2	954.4	954.6	954.7	954.9
162.5°	963.5	962.3	962.5	962.7	962.8	963.0	963.3	963.7	964.1	964.6	965.0
165°	975.5	974.2	974.4	974.5	974.7	974.9	975.2	975.7	976.2	976.7	977.2
167.5°	985.0	983.7	983.7	983.7	983.7	983.7	984.1	984.7	985.4	986.0	986.7
170°	990.4	989.1	989.1	989.1	989.1	989.1	989.5	990.1	990.8	991.4	992.1
172.5°	994.0	992.7	992.5	992.4	992.3	992.1	992.5	993.3	994.0	994.8	995.6
175°	998.5	997.2	997.1	996.9	996.7	996.6	996.9	997.7	998.6	999.4	1000.3
177.5°	1000.1	999.1	999.0	998.8	998.7	998.6	998.8	999.5	1000.1	1000.8	1001.4
180°	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3



TEST NUMBER: P332414-840

CATALOG NUMBER: S123RDIW-S560D755U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5	903.5
2.5°	908.5	911.9	916.3	922.7	927.7	932.0	932.9	934.2	937.3	942.5	946.5
5°	914.4	923.3	937.6	951.5	966.6	979.0	990.6	998.8	1006.4	1022.7	1035.8
7.5°	912.5	932.3	954.7	979.8	1005.0	1029.6	1052.3	1072.7	1093.0	1116.6	1143.6
10°	911.3	934.5	964.6	996.7	1032.0	1066.4	1099.6	1125.6	1155.8	1182.9	1217.3
12.5°	905.4	938.9	974.9	1015.9	1059.2	1098.9	1142.7	1178.5	1212.9	1252.1	1292.1
15°	897.8	938.4	984.0	1038.5	1104.3	1152.3	1197.1	1259.4	1301.9	1344.5	1401.8
17.5°	883.7	933.3	990.4	1061.2	1116.1	1180.5	1248.0	1297.3	1354.5	1414.5	1466.3
20°	872.6	930.3	994.1	1063.7	1133.7	1203.8	1269.1	1327.9	1387.0	1456.3	1498.8
22.5°	861.5	918.5	984.8	1058.7	1134.0	1207.7	1281.7	1350.8	1417.3	1487.2	1541.6
25°	837.8	905.4	977.4	1052.9	1127.1	1208.3	1296.6	1373.5	1455.9	1527.8	1579.3
27.5°	813.9	875.9	947.5	1024.0	1106.5	1202.5	1306.3	1393.8	1476.3	1527.8	1544.0
30°	792.1	857.9	923.6	1001.4	1090.8	1197.9	1308.2	1408.4	1476.0	1498.4	1481.8
32.5°	770.2	829.8	894.9	974.5	1069.4	1186.5	1310.6	1399.7	1440.5	1423.3	1355.5
35°	731.4	785.2	848.3	928.0	1037.0	1180.1	1300.4	1360.8	1350.7	1253.9	1126.3
37.5°	689.9	733.8	792.1	875.5	1003.4	1155.0	1256.5	1265.4	1178.3	1029.9	882.4
40°	657.1	696.6	756.6	843.6	977.4	1130.2	1212.2	1176.3	1041.3	876.1	753.1
42.5°	625.3	658.5	716.3	810.2	952.7	1096.5	1146.3	1067.9	912.2	756.0	644.2
45°	571.3	602.6	660.7	757.0	902.0	1032.0	1025.4	889.3	733.4	607.6	514.8
47.5°	520.1	547.4	602.0	700.2	842.5	935.2	873.7	728.9	596.6	495.8	429.6
50°	483.9	511.0	565.1	662.2	794.9	862.5	774.8	635.1	514.0	430.5	377.9
52.5°	449.2	475.6	525.2	619.8	737.3	777.8	683.5	554.0	453.1	381.0	335.8
55°	400.7	420.8	465.3	555.8	643.6	652.9	557.3	449.1	365.9	315.6	284.7
57.5°	351.3	368.6	412.5	484.6	546.2	541.4	450.8	357.2	301.1	263.8	241.4
60°	319.1	336.1	374.8	436.7	483.1	466.9	383.7	308.3	260.3	232.9	215.1
62.5°	289.1	302.4	338.6	383.7	417.2	398.8	328.0	265.6	227.5	204.4	190.3
65°	245.6	256.4	285.5	309.0	327.6	309.8	251.1	207.7	180.3	164.0	154.3
67.5°	204.3	211.2	229.5	238.0	251.2	231.7	188.7	159.8	144.1	130.5	123.7
70°	178.3	183.4	193.0	200.0	203.5	183.4	151.6	130.4	117.2	107.6	103.3
72.5°	152.3	156.7	158.6	164.4	162.6	143.7	121.9	105.0	95.5	89.0	83.5
75°	116.4	118.4	116.4	114.1	109.1	95.9	80.9	72.3	65.3	62.3	60.4
77.5°	84.8	84.2	81.6	78.0	69.4	61.1	53.0	50.1	47.2	45.4	44.8
80°	65.3	63.8	61.5	55.7	48.4	42.5	40.6	38.7	37.6	35.5	35.2
82.5°	48.7	47.8	43.8	39.0	33.8	31.1	29.5	28.8	27.6	26.7	26.6
85°	26.0	24.7	20.5	17.8	17.1	16.3	15.9	15.9	14.3	13.9	13.9
87.5°	8.8	7.3	7.4	6.8	7.1	7.0	7.7	7.5	7.6	8.1	7.6
90°	2.4	4.0	5.7	7.4	9.3	11.4	13.5	15.7	17.9	18.5	19.2
92.5°	13.3	12.9	12.4	12.0	12.5	14.1	15.8	17.4	19.0	20.1	21.1
95°	38.6	31.8	25.0	18.3	15.8	17.6	19.4	21.2	23.0	24.2	25.3
97.5°	88.1	85.0	82.0	79.0	71.5	59.6	47.7	35.9	23.9	25.2	26.6
100°	128.9	132.2	135.5	138.8	127.5	101.8	76.0	50.3	24.5	25.9	27.2
102.5°	167.2	169.6	172.0	174.3	161.5	133.3	105.1	77.1	48.9	44.8	40.7
105°	223.3	225.1	226.9	228.7	222.2	207.3	192.5	177.6	162.8	133.5	104.3
107.5°	282.7	284.1	285.6	287.0	288.9	291.2	293.6	296.0	298.3	276.8	255.4
110°	322.3	323.7	325.0	326.3	327.9	329.7	331.5	333.4	335.2	329.7	324.3



TEST NUMBER: P332414-840

CATALOG NUMBER: S123RDIW-S560D755U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	360.2	361.4	362.6	363.9	365.4	367.2	369.0	370.8	372.6	372.7	372.8
115°	416.4	417.4	418.4	419.4	420.6	422.1	423.5	425.1	426.6	428.2	429.9
117.5°	471.2	472.4	473.6	474.8	475.8	476.6	477.4	478.1	478.9	480.2	481.5
120°	505.3	506.9	508.3	509.8	510.8	511.3	511.8	512.3	512.7	514.1	515.4
122.5°	539.6	540.8	542.0	543.2	544.1	544.7	545.4	546.0	546.6	547.5	548.5
125°	586.9	588.2	589.6	590.9	591.9	592.5	593.2	593.8	594.5	594.8	595.1
127.5°	632.7	634.0	635.3	636.6	637.7	638.5	639.2	640.1	640.9	641.4	642.0
130°	661.3	662.6	663.9	665.2	666.2	666.8	667.5	668.1	668.8	669.4	670.1
132.5°	688.5	689.8	691.2	692.6	693.5	694.0	694.5	695.0	695.6	696.2	696.9
135°	730.0	730.9	732.0	733.0	733.8	734.5	735.1	735.8	736.4	736.9	737.4
137.5°	765.9	767.2	768.4	769.7	770.5	770.8	771.2	771.6	771.9	772.7	773.6
140°	789.4	790.4	791.4	792.4	793.1	793.7	794.2	794.7	795.2	795.8	796.5
142.5°	811.4	812.4	813.4	814.5	815.2	815.7	816.2	816.7	817.2	817.7	818.2
145°	842.3	843.5	844.7	845.9	846.6	846.9	847.3	847.6	847.9	848.2	848.6
147.5°	870.9	871.7	872.4	873.2	873.7	874.1	874.4	874.7	875.0	875.5	875.8
150°	888.5	889.0	889.5	890.0	890.4	890.8	891.1	891.4	891.7	892.1	892.4
152.5°	904.3	904.5	904.7	905.0	905.2	905.4	905.6	905.8	906.1	906.6	907.2
155°	926.3	926.0	925.6	925.3	925.2	925.4	925.6	925.7	925.9	926.8	927.6
157.5°	944.2	944.1	944.1	944.1	944.0	943.8	943.6	943.5	943.3	944.3	945.3
160°	954.7	954.6	954.4	954.2	954.1	953.9	953.7	953.6	953.4	954.4	955.4
162.5°	964.6	964.1	963.7	963.3	963.0	962.8	962.7	962.5	962.3	963.5	964.6
165°	976.7	976.2	975.7	975.2	974.9	974.7	974.5	974.4	974.2	975.5	976.8
167.5°	986.0	985.4	984.7	984.1	983.7	983.7	983.7	983.7	983.7	985.0	986.3
170°	991.4	990.8	990.1	989.5	989.1	989.1	989.1	989.1	989.1	990.4	991.7
172.5°	994.8	994.0	993.3	992.5	992.1	992.3	992.4	992.5	992.7	994.0	995.3
175°	999.4	998.6	997.7	996.9	996.6	996.7	996.9	997.1	997.2	998.5	999.6
177.5°	1000.8	1000.1	999.5	998.8	998.6	998.7	998.8	999.0	999.1	1000.1	1001.2
180°	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3



TEST NUMBER: P332414-840

CATALOG NUMBER: S123RDIW-S560D755U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	903.5	903.5	903.5	903.5	903.5	903.5	903.5
2.5°	953.1	953.1	954.3	959.0	959.6	963.6	962.3
5°	1047.4	1054.8	1057.5	1069.1	1076.1	1079.1	1073.0
7.5°	1162.9	1183.6	1193.5	1205.6	1216.3	1219.6	1211.1
10°	1247.1	1268.7	1286.9	1298.1	1308.6	1315.5	1324.4
12.5°	1328.4	1355.0	1372.3	1388.2	1398.9	1407.8	1409.2
15°	1416.8	1457.0	1487.6	1510.1	1521.3	1527.1	1524.8
17.5°	1506.0	1543.3	1565.1	1587.9	1603.5	1604.3	1604.8
20°	1556.5	1592.9	1618.0	1635.0	1652.4	1651.6	1655.5
22.5°	1590.2	1618.8	1638.1	1650.4	1656.4	1653.5	1654.3
25°	1606.0	1614.5	1611.0	1591.2	1586.3	1568.1	1571.1
27.5°	1524.6	1484.4	1442.8	1389.2	1347.0	1313.2	1314.9
30°	1414.1	1342.9	1261.7	1193.7	1132.6	1115.5	1079.1
32.5°	1259.7	1153.0	1057.8	994.4	941.9	927.7	896.0
35°	997.9	894.2	796.4	737.6	714.4	682.0	681.6
37.5°	775.7	684.4	632.7	588.5	565.4	545.7	543.8
40°	652.6	581.4	542.3	510.6	487.8	473.0	469.6
42.5°	566.5	509.0	472.3	452.7	435.2	427.6	421.9
45°	462.6	423.9	398.4	380.6	372.4	366.7	363.6
47.5°	387.0	361.0	343.7	331.8	325.2	319.1	320.7
50°	345.8	324.6	311.7	300.5	295.5	291.2	291.6
52.5°	312.7	293.6	283.3	275.2	268.9	265.9	264.4
55°	265.4	253.4	242.9	237.1	233.6	229.3	228.2
57.5°	226.3	217.0	208.5	202.0	201.2	197.0	197.5
60°	200.4	192.6	185.6	182.2	179.5	176.0	177.1
62.5°	179.0	172.5	166.1	163.3	160.6	158.0	158.5
65°	146.6	140.4	136.5	135.0	133.8	132.7	131.5
67.5°	116.8	113.0	110.6	107.2	104.9	104.5	103.3
70°	98.3	93.2	89.0	84.7	83.5	83.1	83.5
72.5°	78.8	75.5	74.4	72.3	72.1	71.1	71.8
75°	59.2	58.1	57.3	55.7	55.7	55.7	55.7
77.5°	43.6	42.9	42.5	42.1	41.8	41.2	41.2
80°	34.0	33.6	32.9	32.9	32.5	32.9	32.5
82.5°	25.7	25.7	24.8	24.8	24.4	24.2	24.4
85°	13.1	12.7	13.5	12.7	13.1	12.4	13.1
87.5°	7.7	7.8	7.6	7.7	7.4	8.1	7.6
90°	19.8	20.5	21.0	21.3	21.6	21.9	22.3
92.5°	22.2	23.2	23.8	24.0	24.2	24.4	24.6
95°	26.5	27.7	28.3	28.3	28.3	28.3	28.3
97.5°	27.9	29.2	30.0	30.1	30.3	30.5	30.6
100°	28.5	29.8	30.6	30.7	30.9	31.0	31.2
102.5°	36.7	32.5	30.6	30.9	31.2	31.5	31.8
105°	75.0	45.8	31.4	31.7	32.0	32.4	32.7
107.5°	234.0	212.6	190.9	168.7	146.7	124.7	102.7
110°	318.8	313.4	298.8	275.2	251.6	227.9	204.4



TEST NUMBER: P332414-840

CATALOG NUMBER: S123RDIW-S560D755U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	372.9	373.0	370.5	365.6	360.6	355.6	350.6
115°	431.5	433.1	434.3	434.9	435.7	436.3	437.0
117.5°	482.8	484.1	484.8	485.0	485.1	485.2	485.4
120°	516.7	518.1	518.7	518.7	518.7	518.7	518.7
122.5°	549.4	550.4	550.9	551.0	551.1	551.3	551.4
125°	595.5	595.8	596.1	596.5	596.8	597.1	597.4
127.5°	642.5	643.0	643.1	642.8	642.4	642.1	641.8
130°	670.8	671.5	671.7	671.3	671.0	670.7	670.2
132.5°	697.5	698.2	698.3	697.8	697.4	696.9	696.4
135°	737.9	738.4	738.4	737.9	737.4	736.9	736.4
137.5°	774.4	775.2	775.4	775.1	774.7	774.4	774.1
140°	797.1	797.8	798.0	797.6	797.3	797.0	796.6
142.5°	818.7	819.2	819.3	818.8	818.4	817.9	817.4
145°	848.9	849.2	849.4	849.4	849.4	849.4	849.4
147.5°	876.1	876.5	876.2	875.5	874.6	873.9	873.1
150°	892.7	893.0	893.0	892.5	892.0	891.5	891.0
152.5°	907.8	908.4	908.3	907.6	906.8	906.1	905.2
155°	928.4	929.3	929.2	928.2	927.2	926.1	925.1
157.5°	946.2	947.3	947.2	945.8	944.5	943.3	942.0
160°	956.4	957.4	957.4	956.1	955.0	953.8	952.7
162.5°	965.7	966.8	966.8	965.8	964.8	963.8	962.8
165°	978.2	979.5	979.6	978.5	977.2	976.1	974.9
167.5°	987.7	989.1	989.1	987.7	986.3	985.0	983.7
170°	993.1	994.4	994.4	993.1	991.7	990.4	989.1
172.5°	996.6	997.9	997.8	996.4	995.0	993.5	992.1
175°	1000.8	1001.9	1001.8	1000.5	999.2	997.8	996.5
177.5°	1002.2	1003.3	1003.1	1001.8	1000.5	999.2	997.8
180°	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3	1000.3

(END OF REPORT)