

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333037-927

Luminaire Tested: **S124RDIW-S575D470U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333037-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S575D470U927-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 470 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3346.2 lumens
Efficiency: N/A
Efficacy: 110.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 30.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333037-927

CATALOG NUMBER: S124RDIW-S575D470U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333037-927

CATALOG NUMBER: S124RDIW-S575D470U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	56
1	99	95	91	88	92	89	85	82	76	74	72	65	63	62	55	53	52	47
2	91	83	77	72	84	78	72	68	67	63	60	57	55	52	48	46	45	40
3	83	74	66	61	77	69	62	57	60	55	51	51	47	44	43	41	38	34
4	76	65	57	51	70	61	54	49	53	48	43	46	42	38	39	36	33	30
5	70	58	50	44	65	55	47	42	48	42	38	41	37	33	35	32	29	26
6	64	52	44	39	60	49	42	37	43	37	33	37	33	29	32	28	26	23
7	60	47	40	34	55	45	37	32	39	33	29	34	29	26	29	26	23	20
8	55	43	35	30	52	41	34	29	36	30	26	31	27	23	27	23	21	18
9	52	40	32	27	48	37	30	26	33	27	23	29	24	21	25	21	19	17
10	48	36	29	24	45	34	28	23	30	25	21	27	22	19	23	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6500	6500	6500
5°	6514	6434	6474
10°	6473	6357	6357
15°	6399	6224	6177
20°	6296	6048	5936
25°	6167	5842	5694
30°	6039	5626	5390
35°	5899	5401	5084
40°	5730	5145	4755
45°	5574	4891	4419
50°	5397	4598	4064
55°	5206	4294	3678
60°	4996	3961	3284
65°	4804	3543	2896
70°	4525	3085	2460
75°	4173	2558	1999
80°	3640	1948	1836
85°	3084	1769	1658



TEST NUMBER: P333037-927

CATALOG NUMBER: S124RDIW-S575D470U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.6	2.3
10°-20°	210.9	6.3
20°-30°	304.5	9.1
30°-40°	345.2	10.3
40°-50°	333.3	10.0
50°-60°	277.2	8.3
60°-70°	191.4	5.7
70°-80°	97.0	2.9
80°-90°	26.3	0.8
90°-100°	16.4	0.5
100°-110°	104.7	3.1
110°-120°	200.2	6.0
120°-130°	254.2	7.6
130°-140°	272.0	8.1
140°-150°	254.3	7.6
150°-160°	205.1	6.1
160°-170°	132.3	4.0
170°-180°	45.6	1.4
0°-30°	591.0	17.7
0°-40°	936.2	28.0
0°-60°	1546.7	46.2
0°-90°	1861.4	55.6
90°-120°	321.3	9.6
90°-150°	1101.8	32.9
90°-180°	1485.0	44.4
0°-180°	3346.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	805	805	805	805	805	
5°	804	801	794	800	799	76
15°	766	760	745	743	739	216
25°	692	680	656	646	639	319
35°	599	578	548	528	516	374
45°	488	465	428	399	387	376
55°	370	344	305	274	261	331
65°	252	224	186	160	152	248
75°	134	111	82	68	64	141
85°	33	22	19	18	18	37
90°	1	5	8	10	11	3
95°	20	8	8	10	10	25
105°	108	110	112	114	102	113
115°	202	203	202	203	203	199
125°	284	285	284	285	286	253
135°	352	352	353	354	354	271
145°	406	407	407	407	408	253
155°	445	445	444	445	444	205
165°	469	468	468	470	467	133
175°	480	478	478	481	477	46
180°	480	480	480	480	480	



TEST NUMBER: P333037-927

CATALOG NUMBER: S124RDIW-S575D470U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	805.1	805.1	805.1	805.1	805.1	805.1	805.1	805.1	805.1	805.1	805.1
2.5°	807.1	806.6	806.2	805.7	805.3	804.5	803.3	802.1	800.8	799.6	800.8
5°	803.8	803.3	802.7	802.2	801.7	800.6	798.9	797.3	795.6	794.0	795.4
7.5°	796.5	796.0	795.4	794.9	794.2	792.9	790.8	788.6	786.5	784.3	785.2
10°	789.6	789.0	788.3	787.6	787.0	785.4	782.9	780.4	777.9	775.5	776.0
12.5°	780.8	780.0	779.2	778.4	777.6	775.8	772.9	769.9	767.1	764.1	764.5
15°	765.6	764.4	763.2	761.9	760.7	758.4	754.9	751.5	748.1	744.7	744.4
17.5°	747.3	745.4	743.7	741.9	740.1	737.2	733.1	729.0	724.8	720.7	720.0
20°	732.9	731.2	729.4	727.6	725.8	722.6	718.0	713.3	708.6	704.0	702.9
22.5°	717.2	715.2	713.2	711.1	709.2	705.7	700.7	695.7	690.7	685.7	684.0
25°	692.3	689.8	687.3	684.8	682.4	678.3	672.7	667.1	661.5	655.9	653.6
27.5°	666.1	663.1	660.0	656.9	653.7	649.2	643.2	637.2	631.2	625.2	622.3
30°	647.8	644.4	641.0	637.6	634.2	629.2	622.8	616.4	609.9	603.5	600.1
32.5°	628.7	624.8	620.9	617.0	613.2	607.9	601.3	594.6	588.0	581.3	577.3
35°	598.6	594.2	589.8	585.4	581.1	575.4	568.5	561.7	554.8	548.0	543.4
37.5°	566.4	561.9	557.4	552.9	548.3	542.2	534.6	527.0	519.5	511.9	506.7
40°	543.7	539.2	534.6	530.1	525.6	519.4	511.7	503.8	496.1	488.2	482.4
42.5°	522.0	517.3	512.5	507.8	503.0	496.6	488.5	480.3	472.2	464.1	458.2
45°	488.2	483.2	478.1	473.0	467.9	461.3	453.0	444.9	436.7	428.4	421.7
47.5°	453.4	448.1	442.8	437.6	432.4	425.5	416.9	408.4	399.9	391.3	384.4
50°	429.7	424.3	419.0	413.6	408.3	401.2	392.4	383.7	374.9	366.1	359.3
52.5°	405.5	400.3	395.1	389.8	384.5	377.5	368.4	359.5	350.5	341.5	334.5
55°	369.9	364.4	358.9	353.4	347.9	340.7	331.8	323.0	314.0	305.1	298.0
57.5°	334.6	328.9	323.2	317.5	311.8	304.6	295.8	287.0	278.3	269.5	262.3
60°	309.4	304.0	298.5	293.0	287.6	280.4	271.6	262.8	254.1	245.3	238.2
62.5°	286.8	281.1	275.4	269.7	264.0	256.7	247.6	238.7	229.7	220.7	214.1
65°	251.5	245.7	239.7	233.9	227.9	220.6	211.8	203.1	194.3	185.5	179.7
67.5°	214.9	209.2	203.6	198.0	192.3	185.4	177.3	169.1	161.1	152.9	147.8
70°	191.7	185.9	180.2	174.4	168.7	161.9	154.1	146.3	138.5	130.7	126.2
72.5°	167.1	161.8	156.6	151.5	146.2	140.0	132.6	125.2	117.8	110.4	106.6
75°	133.8	128.7	123.7	118.6	113.5	107.7	101.3	94.8	88.4	82.0	78.8
77.5°	100.0	95.7	91.4	87.1	82.8	78.0	72.8	67.7	62.4	57.2	55.4
80°	78.3	74.3	70.3	66.4	62.4	58.4	54.3	50.1	46.0	41.9	41.5
82.5°	59.6	55.9	52.3	48.6	45.0	42.0	39.6	37.2	34.9	32.6	32.2
85°	33.3	30.6	27.8	25.0	22.3	20.8	20.4	20.0	19.5	19.1	18.9
87.5°	11.6	10.9	10.1	9.4	8.7	8.4	8.4	8.5	8.5	8.5	8.5
90°	1.1	2.0	2.9	3.7	4.6	5.3	6.0	6.7	7.3	7.9	8.4
92.5°	4.5	4.6	4.6	4.7	4.8	5.1	5.7	6.3	7.0	7.6	8.1
95°	19.7	17.0	14.3	11.6	8.9	7.6	7.7	7.8	7.8	7.9	8.4
97.5°	41.9	43.6	45.3	47.0	48.7	45.1	36.2	27.3	18.4	9.5	9.5
100°	58.9	60.3	61.8	63.2	64.6	59.8	48.8	37.8	26.8	15.8	14.4
102.5°	77.9	78.9	79.9	81.0	82.1	81.8	80.4	79.0	77.6	76.1	61.5
105°	108.1	108.5	109.0	109.5	110.0	110.4	110.8	111.2	111.6	112.0	112.7
107.5°	136.2	136.4	136.7	136.9	137.1	137.5	138.0	138.6	139.1	139.7	140.0
110°	155.1	155.3	155.6	155.8	156.1	156.4	156.9	157.4	157.9	158.4	158.5



TEST NUMBER: P333037-927

CATALOG NUMBER: S124RDIW-S575D470U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	173.5	173.9	174.4	174.8	175.2	175.5	175.8	175.9	176.2	176.4	176.4
115°	201.8	202.0	202.2	202.5	202.7	202.8	202.7	202.6	202.6	202.5	202.6
117.5°	227.3	227.6	227.9	228.2	228.5	228.8	228.9	229.1	229.3	229.5	229.4
120°	244.5	244.8	245.1	245.4	245.7	245.9	245.8	245.7	245.7	245.6	245.7
122.5°	260.5	260.8	260.9	261.2	261.3	261.5	261.6	261.7	261.8	262.0	262.1
125°	283.6	283.9	284.2	284.6	284.9	284.9	284.8	284.6	284.5	284.3	284.6
127.5°	305.5	305.5	305.6	305.7	305.8	306.0	306.3	306.7	307.1	307.4	307.4
130°	319.5	319.6	319.7	319.8	319.9	320.0	320.3	320.5	320.8	321.0	321.1
132.5°	332.5	332.6	332.7	332.9	333.0	333.3	333.6	333.8	334.1	334.5	334.5
135°	351.8	351.7	351.6	351.6	351.5	351.6	352.0	352.3	352.6	352.9	353.1
137.5°	369.0	369.0	369.1	369.1	369.2	369.3	369.6	370.0	370.3	370.7	370.9
140°	380.2	380.3	380.5	380.6	380.8	381.0	381.1	381.4	381.5	381.7	381.9
142.5°	390.2	390.5	390.9	391.1	391.4	391.6	391.7	391.8	391.9	392.0	392.1
145°	405.7	405.9	406.2	406.4	406.6	406.8	406.8	406.8	406.8	406.8	406.9
147.5°	418.0	418.4	418.8	419.3	419.8	419.9	419.9	419.8	419.7	419.6	419.7
150°	426.9	427.2	427.5	427.9	428.2	428.3	428.2	428.1	428.0	427.9	427.9
152.5°	434.4	434.6	434.8	435.1	435.4	435.4	435.3	435.1	435.0	434.8	435.0
155°	444.8	444.9	445.0	445.0	445.1	445.0	444.8	444.6	444.3	444.1	444.4
157.5°	453.7	453.6	453.5	453.5	453.4	453.3	453.0	452.7	452.5	452.3	452.7
160°	458.8	458.6	458.4	458.1	457.9	457.7	457.6	457.6	457.5	457.4	457.9
162.5°	463.4	463.1	462.8	462.5	462.2	462.0	461.9	461.8	461.8	461.7	462.2
165°	469.2	468.8	468.4	468.0	467.6	467.5	467.5	467.5	467.5	467.5	468.1
167.5°	473.8	473.4	473.0	472.6	472.1	471.9	471.9	471.8	471.8	471.7	472.5
170°	476.4	475.9	475.5	475.0	474.5	474.3	474.4	474.4	474.5	474.6	475.2
172.5°	478.2	477.7	477.2	476.7	476.3	476.0	476.1	476.2	476.3	476.3	477.0
175°	480.0	479.5	479.0	478.6	478.1	477.9	478.0	478.1	478.2	478.2	479.0
177.5°	480.9	480.5	480.0	479.5	479.1	479.0	479.0	479.2	479.3	479.4	479.9
180°	480.0	480.0	480.0	480.0	480.0	480.0	480.0	480.0	480.0	480.0	480.0



TEST NUMBER: P333037-927

CATALOG NUMBER: S124RDIW-S575D470U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	805.1	805.1	805.1	805.1	805.1	805.1	805.1	805.1
2.5°	802.1	803.3	804.5	805.0	804.9	804.8	804.7	804.6
5°	796.7	798.1	799.5	800.0	799.7	799.5	799.2	798.9
7.5°	786.1	787.0	787.9	788.1	787.7	787.2	786.8	786.3
10°	776.6	777.1	777.7	777.7	777.1	776.6	776.0	775.5
12.5°	764.8	765.1	765.5	765.2	764.5	763.7	763.0	762.2
15°	744.1	743.9	743.5	743.0	742.0	741.0	740.1	739.1
17.5°	719.2	718.4	717.6	716.5	715.1	713.7	712.2	710.7
20°	701.8	700.7	699.6	698.2	696.4	694.6	692.8	691.0
22.5°	682.5	680.8	679.1	677.6	676.1	674.7	673.3	671.8
25°	651.3	648.9	646.6	644.8	643.3	642.0	640.6	639.2
27.5°	619.4	616.6	613.7	611.2	609.3	607.3	605.4	603.4
30°	596.7	593.2	589.8	587.0	584.8	582.6	580.4	578.2
32.5°	573.4	569.4	565.4	562.4	560.3	558.3	556.1	554.1
35°	538.7	534.0	529.4	525.9	523.4	520.9	518.4	515.9
37.5°	501.5	496.3	491.1	487.3	484.7	482.3	479.8	477.4
40°	476.7	471.0	465.2	461.1	458.6	456.1	453.7	451.2
42.5°	452.3	446.5	440.6	436.4	433.8	431.3	428.6	426.1
45°	415.0	408.3	401.6	397.0	394.5	392.1	389.6	387.1
47.5°	377.4	370.4	363.5	358.6	355.9	353.2	350.5	347.8
50°	352.4	345.6	338.7	334.1	331.4	328.8	326.2	323.6
52.5°	327.6	320.6	313.7	308.9	306.1	303.4	300.7	298.0
55°	290.9	283.8	276.6	271.8	269.2	266.6	264.0	261.3
57.5°	255.0	247.8	240.6	236.0	234.0	232.0	230.0	228.1
60°	231.1	223.9	216.8	212.2	210.0	207.8	205.7	203.4
62.5°	207.6	201.0	194.4	190.2	188.5	186.7	185.0	183.2
65°	173.8	167.9	162.0	158.2	156.6	155.0	153.3	151.6
67.5°	142.8	137.7	132.6	129.2	127.4	125.6	123.7	121.9
70°	121.7	117.2	112.6	109.6	108.3	106.9	105.5	104.2
72.5°	102.7	98.9	95.0	92.4	91.2	89.9	88.6	87.4
75°	75.7	72.6	69.4	67.4	66.5	65.8	65.0	64.1
77.5°	53.6	51.7	49.8	48.8	48.6	48.3	48.1	47.8
80°	41.1	40.7	40.2	40.0	39.8	39.7	39.6	39.5
82.5°	31.9	31.6	31.4	31.1	31.0	30.8	30.7	30.6
85°	18.5	18.3	18.0	17.9	17.9	17.9	17.9	17.9
87.5°	8.5	8.5	8.4	8.5	8.6	8.8	9.0	9.0
90°	8.9	9.3	9.8	10.1	10.3	10.5	10.6	10.8
92.5°	8.6	9.0	9.5	9.7	9.8	9.8	9.9	9.9
95°	8.9	9.3	9.8	10.1	10.1	10.2	10.3	10.4
97.5°	9.6	9.6	9.7	9.7	9.8	9.9	10.0	10.1
100°	13.1	11.7	10.4	9.7	9.8	9.9	10.0	10.1
102.5°	46.8	32.2	17.6	10.3	10.3	10.3	10.3	10.4
105°	113.4	114.2	114.9	113.8	110.9	108.1	105.2	102.3
107.5°	140.4	140.7	141.1	141.4	141.7	142.0	142.3	142.6
110°	158.7	158.8	159.0	159.1	159.4	159.6	159.9	160.1



TEST NUMBER: P333037-927

CATALOG NUMBER: S124RDIW-S575D470U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	176.3	176.3	176.3	176.4	176.7	177.1	177.4	177.6
115°	202.8	203.0	203.1	203.2	203.2	203.2	203.2	203.2
117.5°	229.4	229.4	229.3	229.3	229.3	229.3	229.3	229.2
120°	245.9	246.1	246.2	246.2	246.1	245.9	245.7	245.6
122.5°	262.1	262.2	262.3	262.3	262.1	262.0	261.8	261.7
125°	284.8	285.0	285.3	285.4	285.5	285.6	285.7	285.7
127.5°	307.4	307.3	307.3	307.2	307.1	307.0	307.0	307.0
130°	321.2	321.2	321.3	321.3	321.3	321.3	321.3	321.3
132.5°	334.6	334.7	334.8	334.8	334.7	334.7	334.6	334.5
135°	353.2	353.4	353.6	353.7	353.9	354.0	354.2	354.3
137.5°	371.1	371.2	371.5	371.5	371.5	371.4	371.4	371.3
140°	382.1	382.4	382.6	382.8	382.9	382.9	383.0	383.1
142.5°	392.3	392.5	392.7	392.8	392.8	392.8	392.8	392.8
145°	406.9	407.0	407.1	407.2	407.3	407.5	407.7	407.8
147.5°	419.8	419.8	419.9	419.9	420.0	420.1	420.2	420.3
150°	427.9	427.9	427.9	428.0	428.1	428.2	428.3	428.3
152.5°	435.1	435.2	435.4	435.4	435.4	435.3	435.2	435.2
155°	444.7	445.0	445.4	445.4	445.2	445.0	444.7	444.5
157.5°	453.0	453.4	453.8	453.8	453.4	453.0	452.7	452.3
160°	458.4	458.8	459.3	459.3	458.8	458.4	457.9	457.4
162.5°	462.6	463.1	463.6	463.6	463.0	462.5	461.9	461.4
165°	468.7	469.4	470.0	469.9	469.2	468.5	467.8	467.1
167.5°	473.2	473.9	474.6	474.5	473.7	472.9	472.1	471.3
170°	475.9	476.5	477.2	477.1	476.3	475.5	474.7	473.9
172.5°	477.6	478.2	478.9	478.8	477.9	477.1	476.2	475.3
175°	479.7	480.4	481.1	480.9	480.0	479.0	478.1	477.1
177.5°	480.5	480.9	481.5	481.3	480.6	479.8	479.0	478.3
180°	480.0	480.0	480.0	480.0	480.0	480.0	480.0	480.0

(END OF REPORT)