

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333068-927

Luminaire Tested: **S124RDIW-S795D1340U927-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333068-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S795D1340U927-4F0-1E-UDD-A1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6332.7 lumens
Efficiency: N/A
Efficacy: 103.1 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 61.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333068-927

CATALOG NUMBER: S124RDIW-S795D1340U927-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333068-927

CATALOG NUMBER: S124RDIW-S795D1340U927-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49	42
1	96	92	89	85	88	84	81	78	70	67	65	56	55	53	44	43	42	36
2	88	81	75	70	80	74	69	65	61	58	55	50	47	45	39	37	36	31
3	80	71	64	59	73	66	59	55	54	50	46	44	41	38	35	33	31	26
4	74	63	56	50	67	58	52	47	49	44	40	40	36	33	31	29	27	23
5	68	57	49	43	62	52	45	40	44	38	34	36	32	29	28	26	24	20
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	26	23	21	18
7	58	46	38	33	53	42	36	31	36	30	27	29	25	23	24	21	19	16
8	54	42	34	29	49	39	32	27	33	27	24	27	23	20	22	19	17	14
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15	13
10	47	35	28	23	43	32	26	22	27	23	19	23	19	16	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8442	8442	8442	8442
5°	9792	8468	7484	8468
10°	11584	8430	6679	8430
15°	13381	8352	5739	8352
20°	14898	8245	5191	8245
25°	15380	8141	4819	8141
30°	13463	8011	4595	8011
35°	10480	7823	4459	7823
40°	7860	7606	4387	7606
45°	6205	7258	4349	7258
50°	5238	6859	4222	6859
55°	4566	6415	3997	6415
60°	4108	5959	3538	5959
65°	3622	5465	3041	5465
70°	3262	4952	2745	4952
75°	2732	4389	2339	4389
80°	2311	3742	2194	3742
85°	1954	2927	1954	2927



TEST NUMBER: P333068-927

CATALOG NUMBER: S124RDIW-S795D1340U927-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	101.3	1.6
10°-20°	305.6	4.8
20°-30°	478.0	7.5
30°-40°	531.4	8.4
40°-50°	471.5	7.4
50°-60°	367.4	5.8
60°-70°	240.5	3.8
70°-80°	118.3	1.9
80°-90°	33.2	0.5
90°-100°	87.6	1.4
100°-110°	259.5	4.1
110°-120°	440.5	7.0
120°-130°	580.9	9.2
130°-140°	652.4	10.3
140°-150°	641.1	10.1
150°-160°	539.2	8.5
160°-170°	358.7	5.7
170°-180°	125.6	2.0
0°-30°	885.0	14.0
0°-40°	1416.4	22.4
0°-60°	2255.3	35.6
0°-90°	2647.2	41.8
90°-120°	787.7	12.4
90°-150°	2662.0	42.0
90°-180°	3686.0	58.2
0°-180°	6332.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1046	1046	1046	1046	1046	
5°	1208	1045	924	1045	1208	122
15°	1601	999	687	999	1601	455
25°	1727	914	541	914	1727	766
35°	1063	794	452	794	1063	667
45°	544	636	381	636	544	430
55°	324	456	284	456	324	295
65°	190	286	159	286	190	191
75°	88	141	75	141	88	96
85°	21	32	21	32	21	25
90°	31	3	31	3	31	17
95°	81	62	81	62	81	85
105°	251	239	251	239	251	264
115°	444	448	444	448	444	439
125°	647	652	647	652	647	577
135°	842	841	842	841	842	651
145°	1023	1022	1023	1022	1023	640
155°	1170	1171	1170	1171	1170	539
165°	1272	1275	1272	1275	1272	358
175°	1320	1326	1320	1326	1320	125
180°	1328	1328	1328	1328	1328	



TEST NUMBER: P333068-927

CATALOG NUMBER: S124RDIW-S795D1340U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7
2.5°	1103.0	1106.0	1103.0	1102.6	1099.3	1098.3	1096.9	1092.6	1084.4	1079.7	1080.8
5°	1208.3	1218.9	1213.0	1212.1	1202.8	1193.6	1187.6	1174.2	1159.8	1150.2	1142.2
7.5°	1330.2	1336.3	1332.5	1326.6	1311.6	1303.1	1289.4	1271.7	1246.0	1226.4	1208.4
10°	1413.1	1418.2	1416.4	1405.5	1394.6	1372.2	1359.5	1334.7	1302.3	1276.6	1252.6
12.5°	1494.6	1500.1	1485.2	1485.7	1465.0	1447.4	1427.4	1396.1	1358.6	1325.5	1295.4
15°	1601.0	1594.3	1594.3	1585.8	1562.7	1538.2	1517.6	1484.7	1437.5	1397.9	1356.2
17.5°	1684.3	1686.6	1683.1	1663.3	1645.0	1619.8	1581.9	1543.6	1499.8	1446.6	1404.0
20°	1734.1	1734.1	1730.4	1716.8	1693.3	1666.3	1625.4	1583.7	1528.1	1474.6	1426.6
22.5°	1754.4	1755.7	1751.2	1740.1	1718.9	1692.6	1657.8	1615.4	1558.1	1497.9	1438.4
25°	1726.6	1734.6	1735.4	1732.4	1726.1	1710.1	1680.2	1636.8	1585.4	1520.1	1456.0
27.5°	1585.2	1595.2	1604.1	1618.7	1638.1	1648.1	1649.5	1627.5	1582.6	1519.7	1455.3
30°	1444.2	1452.7	1480.0	1515.8	1543.7	1569.0	1590.9	1596.8	1571.5	1515.0	1447.2
32.5°	1287.9	1299.3	1326.7	1365.2	1411.6	1454.4	1503.6	1528.7	1528.0	1494.1	1431.4
35°	1063.4	1071.8	1097.1	1137.6	1193.2	1256.8	1334.7	1395.3	1436.7	1433.7	1395.3
37.5°	857.6	867.1	892.7	926.2	980.2	1058.9	1134.3	1217.9	1294.3	1337.1	1324.4
40°	745.8	746.2	771.0	805.6	856.1	924.8	1006.9	1099.6	1184.7	1254.3	1267.7
42.5°	657.4	657.5	673.9	711.1	747.6	812.2	890.7	982.7	1082.3	1162.6	1198.3
45°	543.5	547.3	560.8	583.1	611.7	666.5	729.3	814.8	926.5	1021.7	1081.1
47.5°	460.3	465.8	474.4	492.6	515.4	551.9	603.8	680.6	771.5	876.2	960.8
50°	417.1	418.0	428.9	439.0	458.8	487.9	533.4	597.4	680.8	781.6	875.5
52.5°	380.0	379.9	386.4	399.3	415.3	438.0	474.8	533.1	607.0	697.3	794.2
55°	324.4	326.5	331.6	341.7	353.9	369.9	398.9	442.8	501.0	578.1	666.1
57.5°	282.1	283.2	287.2	291.4	302.7	314.3	336.1	366.5	415.6	478.7	560.8
60°	254.4	254.9	256.2	262.4	271.3	282.3	297.0	322.7	364.0	421.8	486.6
62.5°	227.5	228.2	230.2	234.8	241.7	249.2	264.7	285.3	319.5	368.8	427.3
65°	189.6	190.0	193.0	194.6	200.1	206.8	218.2	232.1	255.7	297.0	341.3
67.5°	158.4	158.4	158.6	160.9	164.6	169.1	175.9	187.0	204.9	230.2	269.2
70°	138.2	138.2	139.0	140.3	142.4	146.2	150.0	158.4	171.5	192.1	222.0
72.5°	119.3	119.6	120.5	120.7	121.8	124.9	127.8	133.2	142.8	158.4	182.6
75°	87.6	88.9	91.0	92.7	94.8	94.3	97.4	100.7	103.6	112.9	126.8
77.5°	65.2	64.6	64.8	66.2	66.5	66.9	69.0	71.6	73.8	78.2	83.2
80°	49.7	49.7	51.0	51.4	51.0	51.4	53.5	54.7	55.6	57.3	61.9
82.5°	37.5	38.3	37.9	38.3	38.5	38.9	40.7	41.0	41.8	42.5	44.4
85°	21.1	21.5	21.9	21.1	21.1	21.1	21.9	22.3	23.2	22.7	23.6
87.5°	13.5	13.2	13.4	13.3	13.5	13.0	13.1	13.5	12.5	12.6	12.3
90°	30.8	30.3	29.9	29.5	29.0	28.0	26.7	25.3	24.0	22.6	20.8
92.5°	45.6	45.3	45.1	44.8	44.5	44.0	43.2	42.3	41.5	40.7	39.4
95°	81.2	81.2	81.2	81.2	81.2	80.8	80.2	79.5	78.7	78.1	76.4
97.5°	127.2	127.2	127.2	127.2	127.2	126.7	126.0	125.2	124.3	123.5	121.6
100°	159.2	159.2	159.2	159.2	159.2	159.0	158.6	158.1	157.6	157.2	155.1
102.5°	195.4	195.2	195.0	194.9	194.6	194.2	193.6	193.0	192.3	191.7	189.8
105°	250.6	250.0	249.3	248.6	248.0	247.2	246.6	245.9	245.2	244.5	243.6
107.5°	304.5	304.6	304.6	304.7	304.7	304.4	303.7	303.1	302.5	301.8	301.7
110°	343.2	342.5	341.7	341.1	340.4	340.3	340.7	341.2	341.7	342.1	342.4



TEST NUMBER: P333068-927

CATALOG NUMBER: S124RDIW-S795D1340U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	382.6	382.5	382.3	382.1	382.1	382.0	382.1	382.2	382.3	382.4	382.8
115°	443.9	444.0	444.3	444.5	444.7	445.0	445.2	445.4	445.7	445.8	446.3
117.5°	502.2	502.6	503.1	503.5	504.0	504.6	505.4	506.2	506.9	507.7	508.0
120°	546.5	546.1	545.7	545.2	544.7	545.1	546.2	547.4	548.5	549.6	550.3
122.5°	583.5	584.4	585.2	586.0	586.8	587.6	588.4	589.1	589.9	590.7	591.0
125°	647.2	647.7	648.2	648.6	649.0	649.5	650.0	650.5	650.9	651.3	651.6
127.5°	706.2	706.5	706.9	707.3	707.7	708.1	708.5	709.0	709.5	709.9	710.3
130°	744.8	745.8	746.6	747.6	748.5	749.2	749.6	750.1	750.5	751.0	751.0
132.5°	785.9	786.3	786.6	787.0	787.4	787.8	788.3	788.7	789.2	789.6	789.8
135°	842.4	843.1	843.8	844.5	845.2	845.7	846.2	846.7	847.2	847.6	847.6
137.5°	901.8	901.7	901.6	901.4	901.3	901.5	902.1	902.7	903.2	903.9	903.5
140°	938.0	938.2	938.4	938.7	938.9	939.1	939.4	939.6	939.8	940.0	940.0
142.5°	974.1	974.2	974.2	974.3	974.3	974.4	974.5	974.5	974.5	974.5	974.8
145°	1023.3	1024.0	1024.6	1025.3	1026.0	1026.4	1026.7	1026.9	1027.1	1027.4	1027.1
147.5°	1073.0	1073.2	1073.4	1073.6	1073.9	1074.1	1074.3	1074.4	1074.7	1074.8	1075.0
150°	1103.4	1103.6	1103.8	1104.1	1104.3	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4
152.5°	1131.3	1131.9	1132.5	1133.1	1133.7	1133.8	1133.2	1132.7	1132.1	1131.6	1131.4
155°	1170.2	1171.1	1172.0	1172.9	1173.9	1173.9	1172.9	1172.0	1171.1	1170.2	1170.4
157.5°	1204.9	1205.7	1206.4	1207.2	1208.0	1208.1	1207.4	1206.7	1206.0	1205.3	1205.4
160°	1224.6	1225.7	1226.9	1228.0	1229.2	1229.4	1228.8	1228.0	1227.3	1226.7	1226.9
162.5°	1245.2	1246.3	1247.4	1248.6	1249.7	1249.7	1248.5	1247.2	1246.0	1244.8	1245.0
165°	1271.8	1272.8	1273.7	1274.6	1275.6	1275.3	1273.9	1272.6	1271.2	1269.8	1270.3
167.5°	1291.0	1292.4	1293.8	1295.2	1296.6	1296.6	1295.3	1294.0	1292.6	1291.2	1291.2
170°	1301.7	1303.3	1304.9	1306.5	1308.1	1308.2	1306.8	1305.4	1304.1	1302.7	1302.5
172.5°	1310.7	1312.3	1313.9	1315.5	1317.1	1317.2	1315.6	1314.0	1312.5	1310.9	1310.9
175°	1320.2	1321.8	1323.3	1324.9	1326.6	1326.6	1324.9	1323.3	1321.8	1320.2	1320.4
177.5°	1325.1	1326.6	1328.0	1329.5	1330.9	1331.0	1329.8	1328.5	1327.2	1326.0	1326.0
180°	1328.4	1328.4	1328.4	1328.4	1328.4	1328.4	1328.4	1328.4	1328.4	1328.4	1328.4



TEST NUMBER: P333068-927

CATALOG NUMBER: S124RDIW-S795D1340U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7
2.5°	1077.4	1072.7	1070.3	1064.9	1058.5	1055.1	1052.1	1047.7	1042.0	1035.9	1031.5
5°	1132.0	1122.0	1109.3	1094.2	1080.7	1067.6	1056.2	1044.9	1031.8	1018.3	1004.8
7.5°	1188.2	1168.3	1146.8	1122.0	1097.8	1075.8	1055.6	1036.2	1014.2	994.7	976.8
10°	1227.2	1200.3	1170.4	1138.8	1107.2	1079.8	1052.9	1028.4	1001.5	977.5	957.2
12.5°	1258.9	1227.2	1191.3	1151.9	1114.0	1080.9	1049.8	1018.0	987.3	961.2	934.3
15°	1311.5	1268.1	1219.7	1172.5	1123.2	1078.2	1036.4	999.3	964.4	927.7	902.1
17.5°	1347.7	1296.2	1237.3	1180.6	1122.4	1069.2	1021.1	976.9	936.6	899.1	868.5
20°	1369.3	1312.4	1247.1	1182.6	1117.3	1060.4	1008.6	959.7	918.1	877.6	846.0
22.5°	1381.4	1318.4	1247.1	1179.6	1111.9	1050.4	993.5	942.5	897.1	856.7	821.7
25°	1385.3	1317.9	1245.0	1167.4	1093.3	1028.0	969.0	913.9	863.2	822.8	785.8
27.5°	1379.9	1300.5	1225.8	1146.3	1069.8	1000.9	939.1	881.1	830.4	787.0	749.0
30°	1371.8	1286.7	1206.7	1124.0	1046.6	980.4	915.0	859.4	806.8	761.8	723.4
32.5°	1354.2	1269.9	1183.7	1099.2	1020.6	952.4	890.5	834.6	782.9	736.8	696.1
35°	1319.5	1234.1	1140.5	1053.7	976.6	905.8	847.7	793.8	744.5	695.1	652.2
37.5°	1273.8	1186.5	1093.4	998.3	921.1	854.4	801.0	750.4	702.3	657.3	609.7
40°	1230.7	1151.0	1054.9	960.6	881.4	816.9	767.6	721.7	673.3	628.6	581.0
42.5°	1178.4	1110.6	1013.5	918.8	840.6	778.5	732.6	687.7	643.6	600.3	550.6
45°	1091.2	1039.8	948.8	857.8	779.0	717.5	675.3	635.7	597.0	555.7	509.0
47.5°	991.3	956.5	877.9	784.7	711.9	656.5	615.8	583.4	550.6	509.4	468.3
50°	921.9	899.5	823.6	738.6	669.1	618.1	576.4	546.1	518.6	479.0	442.4
52.5°	847.7	835.8	771.7	690.4	623.2	573.2	537.6	510.3	482.6	449.7	415.4
55°	734.7	741.1	686.7	616.4	553.2	511.0	478.6	455.8	432.3	404.5	378.0
57.5°	619.3	642.4	605.9	544.2	484.9	446.0	421.6	402.4	382.6	359.6	336.9
60°	550.2	569.6	549.0	494.6	442.8	406.5	383.8	369.1	349.3	328.2	310.9
62.5°	482.8	503.6	491.3	447.4	399.3	368.1	348.1	334.4	319.6	301.3	283.3
65°	398.2	411.6	405.8	375.4	341.3	314.7	296.2	286.1	272.6	259.1	243.1
67.5°	304.9	331.0	327.6	311.4	281.9	261.2	249.1	240.1	227.8	217.9	206.9
70°	250.6	274.7	274.3	261.2	245.2	225.9	217.4	209.8	198.8	189.2	180.3
72.5°	205.2	227.2	230.4	220.5	209.5	194.8	186.7	181.5	170.9	164.2	157.1
75°	143.7	159.7	163.9	163.9	158.8	151.2	144.1	140.7	133.2	127.2	123.0
77.5°	94.2	104.3	110.9	112.4	113.2	110.7	104.7	102.3	96.6	94.4	90.4
80°	66.5	73.3	80.9	83.4	85.6	84.7	82.1	80.5	75.0	72.9	71.2
82.5°	46.0	49.7	55.9	61.5	60.9	63.1	60.9	59.6	55.5	54.7	53.0
85°	24.0	24.4	25.3	29.1	31.2	32.0	32.5	31.6	30.3	30.3	27.4
87.5°	11.9	11.2	11.5	11.1	10.9	11.7	12.3	12.0	11.6	11.1	10.5
90°	18.9	17.1	15.3	13.2	10.6	8.1	5.6	3.1	5.6	8.1	10.6
92.5°	38.1	36.8	35.6	33.5	30.6	27.7	24.9	22.0	24.9	27.7	30.6
95°	74.9	73.3	71.7	69.9	67.8	65.8	63.7	61.6	63.7	65.8	67.8
97.5°	119.8	117.9	116.0	114.2	112.6	111.0	109.3	107.7	109.3	111.0	112.6
100°	153.0	151.0	148.9	147.5	146.6	145.7	144.7	143.9	144.7	145.7	146.6
102.5°	188.0	186.1	184.2	183.1	182.8	182.4	182.0	181.6	182.0	182.4	182.8
105°	242.7	241.8	240.8	240.3	240.0	239.9	239.6	239.4	239.6	239.9	240.0
107.5°	301.6	301.4	301.3	301.1	300.8	300.6	300.2	300.0	300.2	300.6	300.8
110°	342.5	342.8	343.0	342.9	342.5	342.0	341.5	341.1	341.5	342.0	342.5



TEST NUMBER: P333068-927

CATALOG NUMBER: S124RDIW-S795D1340U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	383.2	383.7	384.0	384.2	384.1	384.0	383.9	383.8	383.9	384.0	384.1
115°	446.8	447.3	447.7	447.9	447.9	447.9	447.9	447.9	447.9	447.9	447.9
117.5°	508.3	508.7	509.0	509.1	508.9	508.7	508.5	508.3	508.5	508.7	508.9
120°	551.0	551.7	552.4	552.2	551.4	550.4	549.5	548.6	549.5	550.4	551.4
122.5°	591.4	591.7	592.0	592.0	591.6	591.3	590.9	590.5	590.9	591.3	591.6
125°	651.8	652.0	652.3	652.4	652.4	652.4	652.4	652.4	652.4	652.4	652.4
127.5°	710.7	711.0	711.4	711.2	710.5	709.9	709.2	708.4	709.2	709.9	710.5
130°	751.0	751.0	751.0	750.7	750.0	749.3	748.6	747.9	748.6	749.3	750.0
132.5°	790.0	790.2	790.4	790.2	789.7	789.2	788.7	788.2	788.7	789.2	789.7
135°	847.6	847.6	847.6	846.9	845.5	844.1	842.8	841.4	842.8	844.1	845.5
137.5°	903.2	902.8	902.5	901.9	901.3	900.6	900.0	899.4	900.0	900.6	901.3
140°	940.0	940.0	940.0	939.8	939.4	938.9	938.4	938.0	938.4	938.9	939.4
142.5°	974.9	975.1	975.3	975.2	974.7	974.2	973.8	973.4	973.8	974.2	974.7
145°	1026.9	1026.7	1026.4	1025.9	1025.0	1024.1	1023.2	1022.2	1023.2	1024.1	1025.0
147.5°	1075.2	1075.4	1075.5	1075.1	1074.0	1072.9	1071.8	1070.7	1071.8	1072.9	1074.0
150°	1104.4	1104.4	1104.4	1104.0	1103.0	1102.2	1101.2	1100.3	1101.2	1102.2	1103.0
152.5°	1131.2	1131.0	1130.8	1130.4	1129.9	1129.3	1128.8	1128.2	1128.8	1129.3	1129.9
155°	1170.6	1170.8	1171.1	1171.2	1171.2	1171.2	1171.2	1171.2	1171.2	1171.2	1171.2
157.5°	1205.4	1205.5	1205.5	1205.7	1206.1	1206.6	1207.0	1207.4	1207.0	1206.6	1206.1
160°	1227.2	1227.3	1227.6	1227.8	1228.0	1228.3	1228.5	1228.8	1228.5	1228.3	1228.0
162.5°	1245.2	1245.5	1245.7	1246.1	1246.7	1247.3	1247.8	1248.5	1247.8	1247.3	1246.7
165°	1270.7	1271.2	1271.7	1272.2	1272.9	1273.6	1274.3	1274.9	1274.3	1273.6	1272.9
167.5°	1291.1	1291.1	1291.0	1291.5	1292.4	1293.4	1294.3	1295.3	1294.3	1293.4	1292.4
170°	1302.3	1302.0	1301.8	1302.3	1303.4	1304.6	1305.7	1306.8	1305.7	1304.6	1303.4
172.5°	1310.8	1310.8	1310.7	1311.2	1312.2	1313.1	1314.1	1315.0	1314.1	1313.1	1312.2
175°	1320.6	1320.9	1321.0	1321.8	1322.9	1324.1	1325.2	1326.4	1325.2	1324.1	1322.9
177.5°	1326.0	1326.0	1326.0	1326.4	1327.3	1328.2	1329.1	1330.0	1329.1	1328.2	1327.3
180°	1328.4	1328.4	1328.4	1328.4	1328.4	1328.4	1328.4	1328.4	1328.4	1328.4	1328.4



TEST NUMBER: P333068-927

CATALOG NUMBER: S124RDIW-S795D1340U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7
2.5°	1026.8	1023.4	1019.1	1014.0	1008.0	1002.6	1000.2	1002.2	1003.2	1000.5	1000.2
5°	995.5	985.0	976.6	963.9	953.9	945.4	939.5	937.0	937.9	931.1	929.4
7.5°	960.4	947.9	934.1	919.2	905.1	892.8	886.3	882.7	875.6	872.5	867.4
10°	937.9	921.0	907.5	889.8	873.8	859.0	851.9	846.0	838.8	835.4	828.3
12.5°	914.6	895.0	880.2	861.8	845.5	827.7	820.9	809.9	798.8	791.6	782.4
15°	881.8	858.3	840.1	818.2	798.8	778.6	760.5	740.2	732.7	716.7	707.4
17.5°	843.4	819.5	797.1	767.7	737.8	712.7	693.4	674.0	662.4	652.2	647.5
20°	818.2	796.3	765.1	730.9	697.7	669.9	654.3	641.7	629.0	621.9	616.8
22.5°	794.2	766.3	730.1	693.2	660.0	638.2	625.0	612.0	601.7	594.9	588.1
25°	754.2	717.5	679.1	637.0	614.3	595.3	581.0	570.5	564.1	555.3	551.9
27.5°	713.0	668.5	626.2	597.9	574.3	556.9	544.4	536.5	528.5	522.8	518.5
30°	681.3	636.2	598.3	571.3	547.3	533.0	522.8	513.6	507.2	502.6	499.2
32.5°	649.9	604.8	573.0	544.0	525.1	511.0	500.3	493.4	488.4	482.4	480.4
35°	604.6	564.6	536.8	510.6	491.2	478.6	470.2	463.0	458.8	457.1	455.8
37.5°	561.0	528.2	498.4	476.9	459.6	449.7	439.7	436.3	433.3	430.3	431.7
40°	533.4	502.6	476.1	453.4	439.4	428.5	422.6	418.4	415.8	415.8	415.8
42.5°	509.5	479.3	453.5	433.1	419.2	410.0	403.4	399.8	398.9	398.6	400.7
45°	472.3	444.5	418.4	401.5	389.7	380.4	376.7	373.7	373.7	375.4	375.8
47.5°	435.5	409.4	388.5	369.6	358.8	353.0	349.7	348.2	348.3	350.1	352.0
50°	412.9	387.2	366.5	349.7	339.6	334.1	331.1	330.3	331.1	331.1	334.1
52.5°	388.2	365.3	345.0	330.8	319.3	314.2	312.6	311.4	312.0	313.3	314.6
55°	352.2	331.6	312.2	298.7	290.3	286.9	283.1	283.5	282.7	283.5	283.5
57.5°	316.1	297.5	279.5	268.8	261.4	256.5	252.4	253.6	252.3	252.2	251.4
60°	292.8	272.6	258.3	248.6	240.1	235.9	232.1	233.0	231.7	230.8	229.2
62.5°	267.5	250.6	237.0	227.7	220.9	216.0	212.2	211.4	208.5	205.6	201.9
65°	230.8	217.0	204.8	195.9	189.6	185.8	182.8	180.3	174.0	167.2	163.9
67.5°	195.3	185.2	173.8	166.4	161.2	156.2	150.6	146.3	140.4	136.7	134.6
70°	172.3	162.6	153.0	145.8	140.3	135.7	129.4	126.4	122.2	120.5	118.4
72.5°	150.4	141.4	132.4	125.9	120.1	116.5	111.5	108.5	106.7	106.0	103.9
75°	117.2	110.0	103.2	97.4	92.7	90.2	88.1	86.0	85.1	81.3	79.2
77.5°	85.5	80.7	76.5	72.3	69.0	67.3	63.3	60.8	59.4	57.7	57.2
80°	66.5	63.2	59.0	56.5	51.8	50.1	48.5	48.0	47.6	47.2	46.7
82.5°	50.1	46.7	42.5	41.0	39.7	38.7	37.6	37.2	36.8	37.1	37.0
85°	25.3	23.6	23.6	23.2	22.7	22.3	21.9	21.9	21.5	21.9	21.5
87.5°	11.1	11.2	11.5	11.2	11.9	12.3	12.2	12.5	13.1	12.7	12.9
90°	13.2	15.3	17.1	18.9	20.8	22.6	24.0	25.3	26.7	28.0	29.0
92.5°	33.5	35.6	36.8	38.1	39.4	40.7	41.5	42.3	43.2	44.0	44.5
95°	69.9	71.7	73.3	74.9	76.4	78.1	78.7	79.5	80.2	80.8	81.2
97.5°	114.2	116.0	117.9	119.8	121.6	123.5	124.3	125.2	126.0	126.7	127.2
100°	147.5	148.9	151.0	153.0	155.1	157.2	157.6	158.1	158.6	159.0	159.2
102.5°	183.1	184.2	186.1	188.0	189.8	191.7	192.3	193.0	193.6	194.2	194.6
105°	240.3	240.8	241.8	242.7	243.6	244.5	245.2	245.9	246.6	247.2	248.0
107.5°	301.1	301.3	301.4	301.6	301.7	301.8	302.5	303.1	303.7	304.4	304.7
110°	342.9	343.0	342.8	342.5	342.4	342.1	341.7	341.2	340.7	340.3	340.4



TEST NUMBER: P333068-927

CATALOG NUMBER: S124RDIW-S795D1340U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	384.2	384.0	383.7	383.2	382.8	382.4	382.3	382.2	382.1	382.0	382.1
115°	447.9	447.7	447.3	446.8	446.3	445.8	445.7	445.4	445.2	445.0	444.7
117.5°	509.1	509.0	508.7	508.3	508.0	507.7	506.9	506.2	505.4	504.6	504.0
120°	552.2	552.4	551.7	551.0	550.3	549.6	548.5	547.4	546.2	545.1	544.7
122.5°	592.0	592.0	591.7	591.4	591.0	590.7	589.9	589.1	588.4	587.6	586.8
125°	652.4	652.3	652.0	651.8	651.6	651.3	650.9	650.5	650.0	649.5	649.0
127.5°	711.2	711.4	711.0	710.7	710.3	709.9	709.5	709.0	708.5	708.1	707.7
130°	750.7	751.0	751.0	751.0	751.0	751.0	750.5	750.1	749.6	749.2	748.5
132.5°	790.2	790.4	790.2	790.0	789.8	789.6	789.2	788.7	788.3	787.8	787.4
135°	846.9	847.6	847.6	847.6	847.6	847.6	847.2	846.7	846.2	845.7	845.2
137.5°	901.9	902.5	902.8	903.2	903.5	903.9	903.2	902.7	902.1	901.5	901.3
140°	939.8	940.0	940.0	940.0	940.0	940.0	939.8	939.6	939.4	939.1	938.9
142.5°	975.2	975.3	975.1	974.9	974.8	974.5	974.5	974.5	974.5	974.4	974.3
145°	1025.9	1026.4	1026.7	1026.9	1027.1	1027.4	1027.1	1026.9	1026.7	1026.4	1026.0
147.5°	1075.1	1075.5	1075.4	1075.2	1075.0	1074.8	1074.7	1074.4	1074.3	1074.1	1073.9
150°	1104.0	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4	1104.3
152.5°	1130.4	1130.8	1131.0	1131.2	1131.4	1131.6	1132.1	1132.7	1133.2	1133.8	1133.7
155°	1171.2	1171.1	1170.8	1170.6	1170.4	1170.2	1171.1	1172.0	1172.9	1173.9	1173.9
157.5°	1205.7	1205.5	1205.5	1205.4	1205.4	1205.3	1206.0	1206.7	1207.4	1208.1	1208.0
160°	1227.8	1227.6	1227.3	1227.2	1226.9	1226.7	1227.3	1228.0	1228.8	1229.4	1229.2
162.5°	1246.1	1245.7	1245.5	1245.2	1245.0	1244.8	1246.0	1247.2	1248.5	1249.7	1249.7
165°	1272.2	1271.7	1271.2	1270.7	1270.3	1269.8	1271.2	1272.6	1273.9	1275.3	1275.6
167.5°	1291.5	1291.0	1291.1	1291.1	1291.2	1291.2	1292.6	1294.0	1295.3	1296.6	1296.6
170°	1302.3	1301.8	1302.0	1302.3	1302.5	1302.7	1304.1	1305.4	1306.8	1308.2	1308.1
172.5°	1311.2	1310.7	1310.8	1310.8	1310.9	1310.9	1312.5	1314.0	1315.6	1317.2	1317.1
175°	1321.8	1321.0	1320.9	1320.6	1320.4	1320.2	1321.8	1323.3	1324.9	1326.6	1326.6
177.5°	1326.4	1326.0	1326.0	1326.0	1326.0	1326.0	1327.2	1328.5	1329.8	1331.0	1330.9
180°	1328.4	1328.4	1328.4	1328.4	1328.4	1328.4	1328.4	1328.4	1328.4	1328.4	1328.4



TEST NUMBER: P333068-927

CATALOG NUMBER: S124RDIW-S795D1340U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7
2.5°	998.1	998.9	996.5	995.8	996.5	998.9	998.1	1000.2	1000.5	1003.2	1002.2
5°	926.1	925.2	923.1	923.5	923.1	925.2	926.1	929.4	931.1	937.9	937.0
7.5°	864.4	861.1	862.0	858.6	862.0	861.1	864.4	867.4	872.5	875.6	882.7
10°	826.6	822.0	818.2	814.8	818.2	822.0	826.6	828.3	835.4	838.8	846.0
12.5°	775.1	771.1	766.0	767.0	766.0	771.1	775.1	782.4	791.6	798.8	809.9
15°	701.9	695.6	685.5	686.7	685.5	695.6	701.9	707.4	716.7	732.7	740.2
17.5°	640.0	640.1	635.4	636.5	635.4	640.1	640.0	647.5	652.2	662.4	674.0
20°	607.9	605.0	605.4	604.2	605.4	605.0	607.9	616.8	621.9	629.0	641.7
22.5°	585.7	582.1	579.2	576.6	579.2	582.1	585.7	588.1	594.9	601.7	612.0
25°	548.1	545.6	541.8	541.0	541.8	545.6	548.1	551.9	555.3	564.1	570.5
27.5°	515.1	514.6	513.1	511.1	513.1	514.6	515.1	518.5	522.8	528.5	536.5
30°	495.9	495.0	494.2	492.9	494.2	495.0	495.9	499.2	502.6	507.2	513.6
32.5°	478.7	478.2	477.4	477.4	477.4	478.2	478.7	480.4	482.4	488.4	493.4
35°	454.2	453.8	452.9	452.5	452.9	453.8	454.2	455.8	457.1	458.8	463.0
37.5°	431.3	432.4	431.8	431.7	431.8	432.4	431.3	431.7	430.3	433.3	436.3
40°	415.4	415.8	416.7	416.3	416.7	415.8	415.4	415.8	415.8	415.8	418.4
42.5°	402.3	402.3	403.5	402.1	403.5	402.3	402.3	400.7	398.6	398.9	399.8
45°	378.7	381.3	380.9	380.9	380.9	381.3	378.7	375.8	375.4	373.7	373.7
47.5°	353.1	355.2	355.8	355.8	355.8	355.2	353.1	352.0	350.1	348.3	348.2
50°	336.2	335.3	336.6	336.2	336.6	335.3	336.2	334.1	331.1	331.1	330.3
52.5°	315.7	315.8	315.8	315.3	315.8	315.8	315.7	314.6	313.3	312.0	311.4
55°	284.0	284.4	283.5	284.0	283.5	284.4	284.0	283.5	283.5	282.7	283.5
57.5°	249.6	247.6	248.4	247.4	248.4	247.6	249.6	251.4	252.2	252.3	253.6
60°	225.0	221.6	220.8	219.1	220.8	221.6	225.0	229.2	230.8	231.7	233.0
62.5°	197.3	195.0	192.1	193.5	192.1	195.0	197.3	201.9	205.6	208.5	211.4
65°	160.5	158.8	157.6	159.2	157.6	158.8	160.5	163.9	167.2	174.0	180.3
67.5°	132.8	132.0	132.0	131.1	132.0	132.0	132.8	134.6	136.7	140.4	146.3
70°	118.4	117.2	117.2	116.3	117.2	117.2	118.4	118.4	120.5	122.2	126.4
72.5°	103.5	102.3	102.7	102.1	102.7	102.3	103.5	103.9	106.0	106.7	108.5
75°	76.7	74.5	74.5	75.0	74.5	74.5	76.7	79.2	81.3	85.1	86.0
77.5°	57.2	56.8	57.4	56.6	57.4	56.8	57.2	57.2	57.7	59.4	60.8
80°	46.7	46.3	45.9	47.2	45.9	46.3	46.7	46.7	47.2	47.6	48.0
82.5°	36.3	36.2	36.1	37.8	36.1	36.2	36.3	37.0	37.1	36.8	37.2
85°	21.9	21.1	21.9	21.1	21.9	21.1	21.9	21.5	21.9	21.5	21.9
87.5°	13.6	13.4	13.2	13.5	13.2	13.4	13.6	12.9	12.7	13.1	12.5
90°	29.5	29.9	30.3	30.8	30.3	29.9	29.5	29.0	28.0	26.7	25.3
92.5°	44.8	45.1	45.3	45.6	45.3	45.1	44.8	44.5	44.0	43.2	42.3
95°	81.2	81.2	81.2	81.2	81.2	81.2	81.2	81.2	80.8	80.2	79.5
97.5°	127.2	127.2	127.2	127.2	127.2	127.2	127.2	127.2	126.7	126.0	125.2
100°	159.2	159.2	159.2	159.2	159.2	159.2	159.2	159.2	159.0	158.6	158.1
102.5°	194.9	195.0	195.2	195.4	195.2	195.0	194.9	194.6	194.2	193.6	193.0
105°	248.6	249.3	250.0	250.6	250.0	249.3	248.6	248.0	247.2	246.6	245.9
107.5°	304.7	304.6	304.6	304.5	304.6	304.6	304.7	304.7	304.4	303.7	303.1
110°	341.1	341.7	342.5	343.2	342.5	341.7	341.1	340.4	340.3	340.7	341.2



TEST NUMBER: P333068-927

CATALOG NUMBER: S124RDIW-S795D1340U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	382.1	382.3	382.5	382.6	382.5	382.3	382.1	382.1	382.0	382.1	382.2
115°	444.5	444.3	444.0	443.9	444.0	444.3	444.5	444.7	445.0	445.2	445.4
117.5°	503.5	503.1	502.6	502.2	502.6	503.1	503.5	504.0	504.6	505.4	506.2
120°	545.2	545.7	546.1	546.5	546.1	545.7	545.2	544.7	545.1	546.2	547.4
122.5°	586.0	585.2	584.4	583.5	584.4	585.2	586.0	586.8	587.6	588.4	589.1
125°	648.6	648.2	647.7	647.2	647.7	648.2	648.6	649.0	649.5	650.0	650.5
127.5°	707.3	706.9	706.5	706.2	706.5	706.9	707.3	707.7	708.1	708.5	709.0
130°	747.6	746.6	745.8	744.8	745.8	746.6	747.6	748.5	749.2	749.6	750.1
132.5°	787.0	786.6	786.3	785.9	786.3	786.6	787.0	787.4	787.8	788.3	788.7
135°	844.5	843.8	843.1	842.4	843.1	843.8	844.5	845.2	845.7	846.2	846.7
137.5°	901.4	901.6	901.7	901.8	901.7	901.6	901.4	901.3	901.5	902.1	902.7
140°	938.7	938.4	938.2	938.0	938.2	938.4	938.7	938.9	939.1	939.4	939.6
142.5°	974.3	974.2	974.2	974.1	974.2	974.2	974.3	974.3	974.4	974.5	974.5
145°	1025.3	1024.6	1024.0	1023.3	1024.0	1024.6	1025.3	1026.0	1026.4	1026.7	1026.9
147.5°	1073.6	1073.4	1073.2	1073.0	1073.2	1073.4	1073.6	1073.9	1074.1	1074.3	1074.4
150°	1104.1	1103.8	1103.6	1103.4	1103.6	1103.8	1104.1	1104.3	1104.4	1104.4	1104.4
152.5°	1133.1	1132.5	1131.9	1131.3	1131.9	1132.5	1133.1	1133.7	1133.8	1133.2	1132.7
155°	1172.9	1172.0	1171.1	1170.2	1171.1	1172.0	1172.9	1173.9	1173.9	1172.9	1172.0
157.5°	1207.2	1206.4	1205.7	1204.9	1205.7	1206.4	1207.2	1208.0	1208.1	1207.4	1206.7
160°	1228.0	1226.9	1225.7	1224.6	1225.7	1226.9	1228.0	1229.2	1229.4	1228.8	1228.0
162.5°	1248.6	1247.4	1246.3	1245.2	1246.3	1247.4	1248.6	1249.7	1249.7	1248.5	1247.2
165°	1274.6	1273.7	1272.8	1271.8	1272.8	1273.7	1274.6	1275.6	1275.3	1273.9	1272.6
167.5°	1295.2	1293.8	1292.4	1291.0	1292.4	1293.8	1295.2	1296.6	1296.6	1295.3	1294.0
170°	1306.5	1304.9	1303.3	1301.7	1303.3	1304.9	1306.5	1308.1	1308.2	1306.8	1305.4
172.5°	1315.5	1313.9	1312.3	1310.7	1312.3	1313.9	1315.5	1317.1	1317.2	1315.6	1314.0
175°	1324.9	1323.3	1321.8	1320.2	1321.8	1323.3	1324.9	1326.6	1326.6	1324.9	1323.3
177.5°	1329.5	1328.0	1326.6	1325.1	1326.6	1328.0	1329.5	1330.9	1331.0	1329.8	1328.5
180°	1328.4	1328.4	1328.4	1328.4	1328.4	1328.4	1328.4	1328.4	1328.4	1328.4	1328.4



TEST NUMBER: P333068-927

CATALOG NUMBER: S124RDIW-S795D1340U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7
2.5°	1000.2	1002.6	1008.0	1014.0	1019.1	1023.4	1026.8	1031.5	1035.9	1042.0	1047.7
5°	939.5	945.4	953.9	963.9	976.6	985.0	995.5	1004.8	1018.3	1031.8	1044.9
7.5°	886.3	892.8	905.1	919.2	934.1	947.9	960.4	976.8	994.7	1014.2	1036.2
10°	851.9	859.0	873.8	889.8	907.5	921.0	937.9	957.2	977.5	1001.5	1028.4
12.5°	820.9	827.7	845.5	861.8	880.2	895.0	914.6	934.3	961.2	987.3	1018.0
15°	760.5	778.6	798.8	818.2	840.1	858.3	881.8	902.1	927.7	964.4	999.3
17.5°	693.4	712.7	737.8	767.7	797.1	819.5	843.4	868.5	899.1	936.6	976.9
20°	654.3	669.9	697.7	730.9	765.1	796.3	818.2	846.0	877.6	918.1	959.7
22.5°	625.0	638.2	660.0	693.2	730.1	766.3	794.2	821.7	856.7	897.1	942.5
25°	581.0	595.3	614.3	637.0	679.1	717.5	754.2	785.8	822.8	863.2	913.9
27.5°	544.4	556.9	574.3	597.9	626.2	668.5	713.0	749.0	787.0	830.4	881.1
30°	522.8	533.0	547.3	571.3	598.3	636.2	681.3	723.4	761.8	806.8	859.4
32.5°	500.3	511.0	525.1	544.0	573.0	604.8	649.9	696.1	736.8	782.9	834.6
35°	470.2	478.6	491.2	510.6	536.8	564.6	604.6	652.2	695.1	744.5	793.8
37.5°	439.7	449.7	459.6	476.9	498.4	528.2	561.0	609.7	657.3	702.3	750.4
40°	422.6	428.5	439.4	453.4	476.1	502.6	533.4	581.0	628.6	673.3	721.7
42.5°	403.4	410.0	419.2	433.1	453.5	479.3	509.5	550.6	600.3	643.6	687.7
45°	376.7	380.4	389.7	401.5	418.4	444.5	472.3	509.0	555.7	597.0	635.7
47.5°	349.7	353.0	358.8	369.6	388.5	409.4	435.5	468.3	509.4	550.6	583.4
50°	331.1	334.1	339.6	349.7	366.5	387.2	412.9	442.4	479.0	518.6	546.1
52.5°	312.6	314.2	319.3	330.8	345.0	365.3	388.2	415.4	449.7	482.6	510.3
55°	283.1	286.9	290.3	298.7	312.2	331.6	352.2	378.0	404.5	432.3	455.8
57.5°	252.4	256.5	261.4	268.8	279.5	297.5	316.1	336.9	359.6	382.6	402.4
60°	232.1	235.9	240.1	248.6	258.3	272.6	292.8	310.9	328.2	349.3	369.1
62.5°	212.2	216.0	220.9	227.7	237.0	250.6	267.5	283.3	301.3	319.6	334.4
65°	182.8	185.8	189.6	195.9	204.8	217.0	230.8	243.1	259.1	272.6	286.1
67.5°	150.6	156.2	161.2	166.4	173.8	185.2	195.3	206.9	217.9	227.8	240.1
70°	129.4	135.7	140.3	145.8	153.0	162.6	172.3	180.3	189.2	198.8	209.8
72.5°	111.5	116.5	120.1	125.9	132.4	141.4	150.4	157.1	164.2	170.9	181.5
75°	88.1	90.2	92.7	97.4	103.2	110.0	117.2	123.0	127.2	133.2	140.7
77.5°	63.3	67.3	69.0	72.3	76.5	80.7	85.5	90.4	94.4	96.6	102.3
80°	48.5	50.1	51.8	56.5	59.0	63.2	66.5	71.2	72.9	75.0	80.5
82.5°	37.6	38.7	39.7	41.0	42.5	46.7	50.1	53.0	54.7	55.5	59.6
85°	21.9	22.3	22.7	23.2	23.6	23.6	25.3	27.4	30.3	30.3	31.6
87.5°	12.2	12.3	11.9	11.2	11.5	11.2	11.1	10.5	11.1	11.6	12.0
90°	24.0	22.6	20.8	18.9	17.1	15.3	13.2	10.6	8.1	5.6	3.1
92.5°	41.5	40.7	39.4	38.1	36.8	35.6	33.5	30.6	27.7	24.9	22.0
95°	78.7	78.1	76.4	74.9	73.3	71.7	69.9	67.8	65.8	63.7	61.6
97.5°	124.3	123.5	121.6	119.8	117.9	116.0	114.2	112.6	111.0	109.3	107.7
100°	157.6	157.2	155.1	153.0	151.0	148.9	147.5	146.6	145.7	144.7	143.9
102.5°	192.3	191.7	189.8	188.0	186.1	184.2	183.1	182.8	182.4	182.0	181.6
105°	245.2	244.5	243.6	242.7	241.8	240.8	240.3	240.0	239.9	239.6	239.4
107.5°	302.5	301.8	301.7	301.6	301.4	301.3	301.1	300.8	300.6	300.2	300.0
110°	341.7	342.1	342.4	342.5	342.8	343.0	342.9	342.5	342.0	341.5	341.1



TEST NUMBER: P333068-927

CATALOG NUMBER: S124RDIW-S795D1340U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	382.3	382.4	382.8	383.2	383.7	384.0	384.2	384.1	384.0	383.9	383.8
115°	445.7	445.8	446.3	446.8	447.3	447.7	447.9	447.9	447.9	447.9	447.9
117.5°	506.9	507.7	508.0	508.3	508.7	509.0	509.1	508.9	508.7	508.5	508.3
120°	548.5	549.6	550.3	551.0	551.7	552.4	552.2	551.4	550.4	549.5	548.6
122.5°	589.9	590.7	591.0	591.4	591.7	592.0	592.0	591.6	591.3	590.9	590.5
125°	650.9	651.3	651.6	651.8	652.0	652.3	652.4	652.4	652.4	652.4	652.4
127.5°	709.5	709.9	710.3	710.7	711.0	711.4	711.2	710.5	709.9	709.2	708.4
130°	750.5	751.0	751.0	751.0	751.0	751.0	750.7	750.0	749.3	748.6	747.9
132.5°	789.2	789.6	789.8	790.0	790.2	790.4	790.2	789.7	789.2	788.7	788.2
135°	847.2	847.6	847.6	847.6	847.6	847.6	846.9	845.5	844.1	842.8	841.4
137.5°	903.2	903.9	903.5	903.2	902.8	902.5	901.9	901.3	900.6	900.0	899.4
140°	939.8	940.0	940.0	940.0	940.0	940.0	939.8	939.4	938.9	938.4	938.0
142.5°	974.5	974.5	974.8	974.9	975.1	975.3	975.2	974.7	974.2	973.8	973.4
145°	1027.1	1027.4	1027.1	1026.9	1026.7	1026.4	1025.9	1025.0	1024.1	1023.2	1022.2
147.5°	1074.7	1074.8	1075.0	1075.2	1075.4	1075.5	1075.1	1074.0	1072.9	1071.8	1070.7
150°	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4	1104.0	1103.0	1102.2	1101.2	1100.3
152.5°	1132.1	1131.6	1131.4	1131.2	1131.0	1130.8	1130.4	1129.9	1129.3	1128.8	1128.2
155°	1171.1	1170.2	1170.4	1170.6	1170.8	1171.1	1171.2	1171.2	1171.2	1171.2	1171.2
157.5°	1206.0	1205.3	1205.4	1205.4	1205.5	1205.5	1205.7	1206.1	1206.6	1207.0	1207.4
160°	1227.3	1226.7	1226.9	1227.2	1227.3	1227.6	1227.8	1228.0	1228.3	1228.5	1228.8
162.5°	1246.0	1244.8	1245.0	1245.2	1245.5	1245.7	1246.1	1246.7	1247.3	1247.8	1248.5
165°	1271.2	1269.8	1270.3	1270.7	1271.2	1271.7	1272.2	1272.9	1273.6	1274.3	1274.9
167.5°	1292.6	1291.2	1291.2	1291.1	1291.1	1291.0	1291.5	1292.4	1293.4	1294.3	1295.3
170°	1304.1	1302.7	1302.5	1302.3	1302.0	1301.8	1302.3	1303.4	1304.6	1305.7	1306.8
172.5°	1312.5	1310.9	1310.9	1310.8	1310.8	1310.7	1311.2	1312.2	1313.1	1314.1	1315.0
175°	1321.8	1320.2	1320.4	1320.6	1320.9	1321.0	1321.8	1322.9	1324.1	1325.2	1326.4
177.5°	1327.2	1326.0	1326.0	1326.0	1326.0	1326.0	1326.4	1327.3	1328.2	1329.1	1330.0
180°	1328.4	1328.4	1328.4	1328.4	1328.4	1328.4	1328.4	1328.4	1328.4	1328.4	1328.4



TEST NUMBER: P333068-927

CATALOG NUMBER: S124RDIW-S795D1340U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7
2.5°	1052.1	1055.1	1058.5	1064.9	1070.3	1072.7	1077.4	1080.8	1079.7	1084.4	1092.6
5°	1056.2	1067.6	1080.7	1094.2	1109.3	1122.0	1132.0	1142.2	1150.2	1159.8	1174.2
7.5°	1055.6	1075.8	1097.8	1122.0	1146.8	1168.3	1188.2	1208.4	1226.4	1246.0	1271.7
10°	1052.9	1079.8	1107.2	1138.8	1170.4	1200.3	1227.2	1252.6	1276.6	1302.3	1334.7
12.5°	1049.8	1080.9	1114.0	1151.9	1191.3	1227.2	1258.9	1295.4	1325.5	1358.6	1396.1
15°	1036.4	1078.2	1123.2	1172.5	1219.7	1268.1	1311.5	1356.2	1397.9	1437.5	1484.7
17.5°	1021.1	1069.2	1122.4	1180.6	1237.3	1296.2	1347.7	1404.0	1446.6	1499.8	1543.6
20°	1008.6	1060.4	1117.3	1182.6	1247.1	1312.4	1369.3	1426.6	1474.6	1528.1	1583.7
22.5°	993.5	1050.4	1111.9	1179.6	1247.1	1318.4	1381.4	1438.4	1497.9	1558.1	1615.4
25°	969.0	1028.0	1093.3	1167.4	1245.0	1317.9	1385.3	1456.0	1520.1	1585.4	1636.8
27.5°	939.1	1000.9	1069.8	1146.3	1225.8	1300.5	1379.9	1455.3	1519.7	1582.6	1627.5
30°	915.0	980.4	1046.6	1124.0	1206.7	1286.7	1371.8	1447.2	1515.0	1571.5	1596.8
32.5°	890.5	952.4	1020.6	1099.2	1183.7	1269.9	1354.2	1431.4	1494.1	1528.0	1528.7
35°	847.7	905.8	976.6	1053.7	1140.5	1234.1	1319.5	1395.3	1433.7	1436.7	1395.3
37.5°	801.0	854.4	921.1	998.3	1093.4	1186.5	1273.8	1324.4	1337.1	1294.3	1217.9
40°	767.6	816.9	881.4	960.6	1054.9	1151.0	1230.7	1267.7	1254.3	1184.7	1099.6
42.5°	732.6	778.5	840.6	918.8	1013.5	1110.6	1178.4	1198.3	1162.6	1082.3	982.7
45°	675.3	717.5	779.0	857.8	948.8	1039.8	1091.2	1081.1	1021.7	926.5	814.8
47.5°	615.8	656.5	711.9	784.7	877.9	956.5	991.3	960.8	876.2	771.5	680.6
50°	576.4	618.1	669.1	738.6	823.6	899.5	921.9	875.5	781.6	680.8	597.4
52.5°	537.6	573.2	623.2	690.4	771.7	835.8	847.7	794.2	697.3	607.0	533.1
55°	478.6	511.0	553.2	616.4	686.7	741.1	734.7	666.1	578.1	501.0	442.8
57.5°	421.6	446.0	484.9	544.2	605.9	642.4	619.3	560.8	478.7	415.6	366.5
60°	383.8	406.5	442.8	494.6	549.0	569.6	550.2	486.6	421.8	364.0	322.7
62.5°	348.1	368.1	399.3	447.4	491.3	503.6	482.8	427.3	368.8	319.5	285.3
65°	296.2	314.7	341.3	375.4	405.8	411.6	398.2	341.3	297.0	255.7	232.1
67.5°	249.1	261.2	281.9	311.4	327.6	331.0	304.9	269.2	230.2	204.9	187.0
70°	217.4	225.9	245.2	261.2	274.3	274.7	250.6	222.0	192.1	171.5	158.4
72.5°	186.7	194.8	209.5	220.5	230.4	227.2	205.2	182.6	158.4	142.8	133.2
75°	144.1	151.2	158.8	163.9	163.9	159.7	143.7	126.8	112.9	103.6	100.7
77.5°	104.7	110.7	113.2	112.4	110.9	104.3	94.2	83.2	78.2	73.8	71.6
80°	82.1	84.7	85.6	83.4	80.9	73.3	66.5	61.9	57.3	55.6	54.7
82.5°	60.9	63.1	60.9	61.5	55.9	49.7	46.0	44.4	42.5	41.8	41.0
85°	32.5	32.0	31.2	29.1	25.3	24.4	24.0	23.6	22.7	23.2	22.3
87.5°	12.3	11.7	10.9	11.1	11.5	11.2	11.9	12.3	12.6	12.5	13.5
90°	5.6	8.1	10.6	13.2	15.3	17.1	18.9	20.8	22.6	24.0	25.3
92.5°	24.9	27.7	30.6	33.5	35.6	36.8	38.1	39.4	40.7	41.5	42.3
95°	63.7	65.8	67.8	69.9	71.7	73.3	74.9	76.4	78.1	78.7	79.5
97.5°	109.3	111.0	112.6	114.2	116.0	117.9	119.8	121.6	123.5	124.3	125.2
100°	144.7	145.7	146.6	147.5	148.9	151.0	153.0	155.1	157.2	157.6	158.1
102.5°	182.0	182.4	182.8	183.1	184.2	186.1	188.0	189.8	191.7	192.3	193.0
105°	239.6	239.9	240.0	240.3	240.8	241.8	242.7	243.6	244.5	245.2	245.9
107.5°	300.2	300.6	300.8	301.1	301.3	301.4	301.6	301.7	301.8	302.5	303.1
110°	341.5	342.0	342.5	342.9	343.0	342.8	342.5	342.4	342.1	341.7	341.2



TEST NUMBER: P333068-927

CATALOG NUMBER: S124RDIW-S795D1340U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	383.9	384.0	384.1	384.2	384.0	383.7	383.2	382.8	382.4	382.3	382.2
115°	447.9	447.9	447.9	447.9	447.7	447.3	446.8	446.3	445.8	445.7	445.4
117.5°	508.5	508.7	508.9	509.1	509.0	508.7	508.3	508.0	507.7	506.9	506.2
120°	549.5	550.4	551.4	552.2	552.4	551.7	551.0	550.3	549.6	548.5	547.4
122.5°	590.9	591.3	591.6	592.0	592.0	591.7	591.4	591.0	590.7	589.9	589.1
125°	652.4	652.4	652.4	652.4	652.3	652.0	651.8	651.6	651.3	650.9	650.5
127.5°	709.2	709.9	710.5	711.2	711.4	711.0	710.7	710.3	709.9	709.5	709.0
130°	748.6	749.3	750.0	750.7	751.0	751.0	751.0	751.0	751.0	750.5	750.1
132.5°	788.7	789.2	789.7	790.2	790.4	790.2	790.0	789.8	789.6	789.2	788.7
135°	842.8	844.1	845.5	846.9	847.6	847.6	847.6	847.6	847.6	847.2	846.7
137.5°	900.0	900.6	901.3	901.9	902.5	902.8	903.2	903.5	903.9	903.2	902.7
140°	938.4	938.9	939.4	939.8	940.0	940.0	940.0	940.0	940.0	939.8	939.6
142.5°	973.8	974.2	974.7	975.2	975.3	975.1	974.9	974.8	974.5	974.5	974.5
145°	1023.2	1024.1	1025.0	1025.9	1026.4	1026.7	1026.9	1027.1	1027.4	1027.1	1026.9
147.5°	1071.8	1072.9	1074.0	1075.1	1075.5	1075.4	1075.2	1075.0	1074.8	1074.7	1074.4
150°	1101.2	1102.2	1103.0	1104.0	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4
152.5°	1128.8	1129.3	1129.9	1130.4	1130.8	1131.0	1131.2	1131.4	1131.6	1132.1	1132.7
155°	1171.2	1171.2	1171.2	1171.2	1171.1	1170.8	1170.6	1170.4	1170.2	1171.1	1172.0
157.5°	1207.0	1206.6	1206.1	1205.7	1205.5	1205.5	1205.4	1205.4	1205.3	1206.0	1206.7
160°	1228.5	1228.3	1228.0	1227.8	1227.6	1227.3	1227.2	1226.9	1226.7	1227.3	1228.0
162.5°	1247.8	1247.3	1246.7	1246.1	1245.7	1245.5	1245.2	1245.0	1244.8	1246.0	1247.2
165°	1274.3	1273.6	1272.9	1272.2	1271.7	1271.2	1270.7	1270.3	1269.8	1271.2	1272.6
167.5°	1294.3	1293.4	1292.4	1291.5	1291.0	1291.1	1291.1	1291.2	1291.2	1292.6	1294.0
170°	1305.7	1304.6	1303.4	1302.3	1301.8	1302.0	1302.3	1302.5	1302.7	1304.1	1305.4
172.5°	1314.1	1313.1	1312.2	1311.2	1310.7	1310.8	1310.8	1310.9	1310.9	1312.5	1314.0
175°	1325.2	1324.1	1322.9	1321.8	1321.0	1320.9	1320.6	1320.4	1320.2	1321.8	1323.3
177.5°	1329.1	1328.2	1327.3	1326.4	1326.0	1326.0	1326.0	1326.0	1326.0	1327.2	1328.5
180°	1328.4	1328.4	1328.4	1328.4	1328.4	1328.4	1328.4	1328.4	1328.4	1328.4	1328.4



TEST NUMBER: P333068-927

CATALOG NUMBER: S124RDIW-S795D1340U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7	1045.7
2.5°	1096.9	1098.3	1099.3	1102.6	1103.0	1106.0	1103.0
5°	1187.6	1193.6	1202.8	1212.1	1213.0	1218.9	1208.3
7.5°	1289.4	1303.1	1311.6	1326.6	1332.5	1336.3	1330.2
10°	1359.5	1372.2	1394.6	1405.5	1416.4	1418.2	1413.1
12.5°	1427.4	1447.4	1465.0	1485.7	1485.2	1500.1	1494.6
15°	1517.6	1538.2	1562.7	1585.8	1594.3	1594.3	1601.0
17.5°	1581.9	1619.8	1645.0	1663.3	1683.1	1686.6	1684.3
20°	1625.4	1666.3	1693.3	1716.8	1730.4	1734.1	1734.1
22.5°	1657.8	1692.6	1718.9	1740.1	1751.2	1755.7	1754.4
25°	1680.2	1710.1	1726.1	1732.4	1735.4	1734.6	1726.6
27.5°	1649.5	1648.1	1638.1	1618.7	1604.1	1595.2	1585.2
30°	1590.9	1569.0	1543.7	1515.8	1480.0	1452.7	1444.2
32.5°	1503.6	1454.4	1411.6	1365.2	1326.7	1299.3	1287.9
35°	1334.7	1256.8	1193.2	1137.6	1097.1	1071.8	1063.4
37.5°	1134.3	1058.9	980.2	926.2	892.7	867.1	857.6
40°	1006.9	924.8	856.1	805.6	771.0	746.2	745.8
42.5°	890.7	812.2	747.6	711.1	673.9	657.5	657.4
45°	729.3	666.5	611.7	583.1	560.8	547.3	543.5
47.5°	603.8	551.9	515.4	492.6	474.4	465.8	460.3
50°	533.4	487.9	458.8	439.0	428.9	418.0	417.1
52.5°	474.8	438.0	415.3	399.3	386.4	379.9	380.0
55°	398.9	369.9	353.9	341.7	331.6	326.5	324.4
57.5°	336.1	314.3	302.7	291.4	287.2	283.2	282.1
60°	297.0	282.3	271.3	262.4	256.2	254.9	254.4
62.5°	264.7	249.2	241.7	234.8	230.2	228.2	227.5
65°	218.2	206.8	200.1	194.6	193.0	190.0	189.6
67.5°	175.9	169.1	164.6	160.9	158.6	158.4	158.4
70°	150.0	146.2	142.4	140.3	139.0	138.2	138.2
72.5°	127.8	124.9	121.8	120.7	120.5	119.6	119.3
75°	97.4	94.3	94.8	92.7	91.0	88.9	87.6
77.5°	69.0	66.9	66.5	66.2	64.8	64.6	65.2
80°	53.5	51.4	51.0	51.4	51.0	49.7	49.7
82.5°	40.7	38.9	38.5	38.3	37.9	38.3	37.5
85°	21.9	21.1	21.1	21.1	21.9	21.5	21.1
87.5°	13.1	13.0	13.5	13.3	13.4	13.2	13.5
90°	26.7	28.0	29.0	29.5	29.9	30.3	30.8
92.5°	43.2	44.0	44.5	44.8	45.1	45.3	45.6
95°	80.2	80.8	81.2	81.2	81.2	81.2	81.2
97.5°	126.0	126.7	127.2	127.2	127.2	127.2	127.2
100°	158.6	159.0	159.2	159.2	159.2	159.2	159.2
102.5°	193.6	194.2	194.6	194.9	195.0	195.2	195.4
105°	246.6	247.2	248.0	248.6	249.3	250.0	250.6
107.5°	303.7	304.4	304.7	304.7	304.6	304.6	304.5
110°	340.7	340.3	340.4	341.1	341.7	342.5	343.2



TEST NUMBER: P333068-927

CATALOG NUMBER: S124RDIW-S795D1340U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	382.1	382.0	382.1	382.1	382.3	382.5	382.6
115°	445.2	445.0	444.7	444.5	444.3	444.0	443.9
117.5°	505.4	504.6	504.0	503.5	503.1	502.6	502.2
120°	546.2	545.1	544.7	545.2	545.7	546.1	546.5
122.5°	588.4	587.6	586.8	586.0	585.2	584.4	583.5
125°	650.0	649.5	649.0	648.6	648.2	647.7	647.2
127.5°	708.5	708.1	707.7	707.3	706.9	706.5	706.2
130°	749.6	749.2	748.5	747.6	746.6	745.8	744.8
132.5°	788.3	787.8	787.4	787.0	786.6	786.3	785.9
135°	846.2	845.7	845.2	844.5	843.8	843.1	842.4
137.5°	902.1	901.5	901.3	901.4	901.6	901.7	901.8
140°	939.4	939.1	938.9	938.7	938.4	938.2	938.0
142.5°	974.5	974.4	974.3	974.3	974.2	974.2	974.1
145°	1026.7	1026.4	1026.0	1025.3	1024.6	1024.0	1023.3
147.5°	1074.3	1074.1	1073.9	1073.6	1073.4	1073.2	1073.0
150°	1104.4	1104.4	1104.3	1104.1	1103.8	1103.6	1103.4
152.5°	1133.2	1133.8	1133.7	1133.1	1132.5	1131.9	1131.3
155°	1172.9	1173.9	1173.9	1172.9	1172.0	1171.1	1170.2
157.5°	1207.4	1208.1	1208.0	1207.2	1206.4	1205.7	1204.9
160°	1228.8	1229.4	1229.2	1228.0	1226.9	1225.7	1224.6
162.5°	1248.5	1249.7	1249.7	1248.6	1247.4	1246.3	1245.2
165°	1273.9	1275.3	1275.6	1274.6	1273.7	1272.8	1271.8
167.5°	1295.3	1296.6	1296.6	1295.2	1293.8	1292.4	1291.0
170°	1306.8	1308.2	1308.1	1306.5	1304.9	1303.3	1301.7
172.5°	1315.6	1317.2	1317.1	1315.5	1313.9	1312.3	1310.7
175°	1324.9	1326.6	1326.6	1324.9	1323.3	1321.8	1320.2
177.5°	1329.8	1331.0	1330.9	1329.5	1328.0	1326.6	1325.1
180°	1328.4	1328.4	1328.4	1328.4	1328.4	1328.4	1328.4

(END OF REPORT)