

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333073-927

Luminaire Tested: **S124RDIW-S795D1560U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333073-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S795D1560U927-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7487.9 lumens
Efficiency: N/A
Efficacy: 110.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 68.1
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333073-927

CATALOG NUMBER: S124RDIW-S795D1560U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333073-927

CATALOG NUMBER: S124RDIW-S795D1560U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	34
1	94	90	87	83	85	82	78	76	65	63	61	51	49	48	37	36	35	29
2	86	79	73	68	77	71	67	62	57	54	51	45	42	40	33	31	30	25
3	79	69	62	57	71	63	57	52	51	47	43	40	37	34	29	27	26	21
4	72	62	54	48	65	56	49	44	45	40	37	35	32	29	26	24	22	18
5	66	55	47	41	59	50	43	38	40	35	32	32	28	25	24	21	19	16
6	61	49	41	36	55	45	38	33	36	31	28	29	25	22	21	19	17	14
7	56	44	37	31	51	40	34	29	33	28	24	26	22	20	20	17	15	12
8	52	40	33	27	47	37	30	25	30	25	22	24	20	18	18	16	14	11
9	48	37	29	24	44	33	27	23	27	23	19	22	18	16	17	14	12	10
10	45	33	26	22	41	31	24	20	25	21	17	20	17	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8884	8884	8884
5°	8904	8795	8849
10°	8848	8689	8689
15°	8747	8507	8444
20°	8607	8267	8115
25°	8429	7986	7783
30°	8255	7690	7368
35°	8064	7383	6951
40°	7832	7032	6500
45°	7618	6687	6042
50°	7376	6286	5556
55°	7116	5871	5029
60°	6830	5414	4490
65°	6567	4846	3960
70°	6187	4216	3361
75°	5702	3497	2732
80°	4974	2664	2506
85°	4215	2418	2260



TEST NUMBER: P333073-927

CATALOG NUMBER: S124RDIW-S795D1560U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.4	1.4
10°-20°	288.3	3.8
20°-30°	416.3	5.6
30°-40°	471.8	6.3
40°-50°	455.6	6.1
50°-60°	378.9	5.1
60°-70°	261.6	3.5
70°-80°	132.6	1.8
80°-90°	38.6	0.5
90°-100°	54.6	0.7
100°-110°	348.3	4.7
110°-120°	666.3	8.9
120°-130°	845.9	11.3
130°-140°	905.0	12.1
140°-150°	846.3	11.3
150°-160°	682.5	9.1
160°-170°	440.2	5.9
170°-180°	151.7	2.0
0°-30°	807.9	10.8
0°-40°	1279.7	17.1
0°-60°	2114.3	28.2
0°-90°	2547.1	34.0
90°-120°	1069.3	14.3
90°-150°	3666.4	49.0
90°-180°	4941.0	66.0
0°-180°	7487.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1100	1100	1100	1100	1100	
5°	1099	1095	1085	1093	1092	104
15°	1047	1038	1018	1016	1010	295
25°	946	930	896	883	874	436
35°	818	790	749	721	705	511
45°	667	635	586	546	529	514
55°	506	471	417	375	357	452
65°	344	307	254	219	207	339
75°	183	151	112	93	88	193
85°	46	29	26	24	24	51
90°	4	17	26	33	36	5
95°	66	27	26	33	35	84
105°	360	367	373	380	340	376
115°	671	675	674	676	676	660
125°	944	948	946	950	951	842
135°	1171	1170	1174	1177	1179	902
145°	1350	1353	1354	1355	1357	843
155°	1480	1481	1478	1482	1479	682
165°	1561	1556	1555	1564	1554	441
175°	1597	1591	1591	1601	1588	152
180°	1597	1597	1597	1597	1597	



TEST NUMBER: P333073-927

CATALOG NUMBER: S124RDIW-S795D1560U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5
2.5°	1103.2	1102.6	1101.9	1101.4	1100.7	1099.6	1098.0	1096.4	1094.7	1093.1	1094.7
5°	1098.8	1098.0	1097.3	1096.5	1095.7	1094.3	1092.0	1089.8	1087.5	1085.3	1087.2
7.5°	1088.9	1088.1	1087.3	1086.5	1085.7	1083.9	1080.9	1078.0	1075.1	1072.1	1073.3
10°	1079.4	1078.5	1077.5	1076.6	1075.6	1073.5	1070.2	1066.8	1063.4	1060.0	1060.7
12.5°	1067.2	1066.2	1065.1	1064.0	1063.0	1060.4	1056.5	1052.4	1048.5	1044.5	1045.0
15°	1046.6	1044.9	1043.1	1041.5	1039.8	1036.6	1031.9	1027.2	1022.5	1017.9	1017.5
17.5°	1021.4	1019.0	1016.5	1014.2	1011.7	1007.7	1002.0	996.4	990.8	985.2	984.1
20°	1001.9	999.4	997.0	994.6	992.1	987.8	981.4	975.0	968.6	962.3	960.8
22.5°	980.3	977.6	974.9	972.1	969.4	964.6	957.7	950.9	944.1	937.3	935.1
25°	946.3	942.9	939.5	936.1	932.8	927.2	919.6	911.9	904.2	896.5	893.3
27.5°	910.5	906.3	902.1	897.9	893.6	887.4	879.2	871.0	862.8	854.6	850.6
30°	885.6	880.9	876.2	871.6	866.9	860.2	851.4	842.6	833.7	824.9	820.2
32.5°	859.3	854.1	848.7	843.4	838.2	831.0	821.9	812.8	803.7	794.6	789.2
35°	818.2	812.2	806.2	800.2	794.2	786.6	777.2	767.8	758.4	749.1	742.8
37.5°	774.2	768.0	761.8	755.7	749.5	741.2	730.9	720.5	710.1	699.7	692.6
40°	743.2	737.0	730.9	724.7	718.5	710.0	699.3	688.7	678.0	667.3	659.5
42.5°	713.5	707.0	700.6	694.1	687.6	678.8	667.7	656.6	645.5	634.3	626.3
45°	667.3	660.4	653.5	646.6	639.6	630.6	619.3	608.1	596.8	585.7	576.5
47.5°	619.6	612.5	605.4	598.2	591.0	581.6	570.0	558.3	546.6	534.9	525.4
50°	587.3	580.0	572.7	565.4	558.1	548.4	536.5	524.5	512.5	500.5	491.2
52.5°	554.3	547.2	540.0	532.8	525.7	515.9	503.7	491.4	479.1	466.8	457.3
55°	505.6	498.0	490.6	483.1	475.6	465.8	453.6	441.4	429.3	417.1	407.3
57.5°	457.4	449.6	441.8	434.0	426.2	416.3	404.3	392.4	380.4	368.4	358.5
60°	423.0	415.5	408.1	400.5	393.0	383.3	371.3	359.3	347.4	335.3	325.6
62.5°	392.0	384.2	376.4	368.6	360.8	350.8	338.5	326.2	313.9	301.7	292.6
65°	343.8	335.7	327.6	319.6	311.6	301.6	289.5	277.6	265.6	253.7	245.6
67.5°	293.7	286.1	278.3	270.6	262.8	253.5	242.3	231.2	220.1	209.0	202.0
70°	262.1	254.2	246.3	238.4	230.6	221.3	210.6	199.9	189.3	178.6	172.5
72.5°	228.4	221.3	214.1	207.0	199.9	191.3	181.3	171.1	161.1	151.0	145.7
75°	182.8	175.9	169.0	162.1	155.1	147.3	138.5	129.7	120.9	112.1	107.7
77.5°	136.7	130.8	124.9	119.1	113.1	106.6	99.6	92.4	85.3	78.2	75.7
80°	107.0	101.6	96.2	90.7	85.3	79.8	74.1	68.5	62.9	57.3	56.7
82.5°	81.4	76.4	71.5	66.5	61.5	57.4	54.2	50.9	47.7	44.5	44.0
85°	45.5	41.7	38.0	34.3	30.5	28.4	27.8	27.3	26.7	26.1	25.7
87.5°	16.2	15.6	15.0	14.3	13.8	13.6	13.9	14.2	14.4	14.7	14.9
90°	3.6	6.5	9.4	12.4	15.3	17.8	19.9	22.0	24.2	26.3	27.9
92.5°	15.1	15.2	15.4	15.5	15.7	16.8	18.9	21.1	23.2	25.3	26.9
95°	65.7	56.6	47.7	38.7	29.6	25.2	25.5	25.7	26.0	26.3	27.9
97.5°	139.5	145.1	150.8	156.5	162.1	150.0	120.4	90.8	61.2	31.5	31.7
100°	195.9	200.7	205.5	210.2	215.0	199.1	162.5	125.8	89.2	52.6	48.1
102.5°	259.0	262.5	266.0	269.5	273.0	272.4	267.6	262.8	258.0	253.3	204.5
105°	359.6	361.2	362.7	364.4	366.0	367.4	368.8	370.1	371.4	372.7	375.1
107.5°	453.0	453.8	454.6	455.4	456.2	457.5	459.3	461.1	462.9	464.7	465.9
110°	516.1	516.9	517.7	518.5	519.3	520.5	522.0	523.6	525.2	526.8	527.4



TEST NUMBER: P333073-927

CATALOG NUMBER: S124RDIW-S795D1560U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	577.3	578.7	580.1	581.5	583.0	584.1	584.8	585.6	586.3	587.1	586.9
115°	671.4	672.2	673.0	673.8	674.5	674.9	674.5	674.3	674.1	673.8	674.3
117.5°	756.2	757.2	758.4	759.4	760.5	761.3	761.8	762.5	763.0	763.6	763.5
120°	813.6	814.6	815.7	816.7	817.8	818.2	817.9	817.7	817.4	817.1	817.7
122.5°	867.0	867.7	868.3	868.9	869.7	870.1	870.5	870.8	871.2	871.6	872.0
125°	943.8	944.8	945.9	947.0	948.0	948.2	947.8	947.2	946.7	946.2	947.0
127.5°	1016.4	1016.7	1016.9	1017.2	1017.5	1018.2	1019.5	1020.6	1021.8	1023.1	1022.9
130°	1063.3	1063.5	1063.7	1064.1	1064.3	1064.9	1065.6	1066.4	1067.2	1068.0	1068.3
132.5°	1106.2	1106.7	1107.2	1107.7	1108.2	1108.9	1109.9	1110.9	1111.9	1112.9	1113.2
135°	1170.8	1170.4	1170.2	1170.0	1169.7	1170.1	1171.2	1172.2	1173.3	1174.3	1174.9
137.5°	1227.9	1228.0	1228.0	1228.2	1228.3	1228.9	1230.1	1231.3	1232.4	1233.6	1234.1
140°	1265.1	1265.7	1266.2	1266.7	1267.3	1267.8	1268.3	1268.8	1269.4	1269.9	1270.7
142.5°	1298.5	1299.5	1300.5	1301.5	1302.4	1303.1	1303.4	1303.7	1304.0	1304.3	1304.9
145°	1350.0	1350.8	1351.5	1352.3	1353.1	1353.5	1353.5	1353.5	1353.5	1353.5	1353.8
147.5°	1390.8	1392.3	1393.8	1395.3	1396.8	1397.3	1397.1	1396.9	1396.5	1396.3	1396.5
150°	1420.5	1421.5	1422.5	1423.6	1424.7	1425.1	1424.8	1424.6	1424.3	1424.0	1424.0
152.5°	1445.3	1446.1	1447.0	1447.8	1448.7	1448.9	1448.3	1447.9	1447.4	1446.9	1447.4
155°	1480.2	1480.4	1480.7	1481.0	1481.2	1481.0	1480.2	1479.4	1478.6	1477.7	1478.8
157.5°	1509.6	1509.4	1509.3	1509.1	1508.9	1508.4	1507.4	1506.6	1505.7	1504.8	1506.2
160°	1526.8	1526.0	1525.2	1524.4	1523.6	1523.0	1522.7	1522.5	1522.3	1521.9	1523.6
162.5°	1542.1	1541.0	1540.0	1539.1	1538.0	1537.4	1537.1	1536.8	1536.6	1536.3	1537.9
165°	1561.4	1560.0	1558.8	1557.4	1556.1	1555.4	1555.4	1555.4	1555.4	1555.4	1557.5
167.5°	1576.7	1575.3	1573.9	1572.6	1571.1	1570.4	1570.3	1570.1	1569.9	1569.8	1572.1
170°	1585.3	1583.7	1582.1	1580.5	1578.9	1578.3	1578.5	1578.8	1579.1	1579.3	1581.4
172.5°	1591.0	1589.4	1587.9	1586.3	1584.7	1584.0	1584.3	1584.5	1584.8	1585.1	1587.1
175°	1597.2	1595.6	1594.0	1592.4	1590.9	1590.2	1590.5	1590.7	1591.0	1591.3	1593.6
177.5°	1600.1	1598.6	1597.1	1595.6	1594.2	1593.6	1594.0	1594.5	1594.9	1595.3	1597.0
180°	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2



TEST NUMBER: P333073-927

CATALOG NUMBER: S124RDIW-S795D1560U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5
2.5°	1096.4	1098.0	1099.6	1100.4	1100.3	1100.1	1099.9	1099.8
5°	1089.0	1090.9	1092.8	1093.5	1093.1	1092.8	1092.4	1092.0
7.5°	1074.5	1075.8	1077.0	1077.2	1076.7	1076.0	1075.5	1074.8
10°	1061.5	1062.2	1063.0	1063.0	1062.2	1061.5	1060.7	1060.0
12.5°	1045.4	1045.8	1046.3	1046.0	1045.0	1043.9	1042.8	1041.8
15°	1017.2	1016.8	1016.4	1015.6	1014.2	1012.9	1011.6	1010.3
17.5°	983.1	982.1	981.0	979.5	977.5	975.5	973.5	971.5
20°	959.3	957.7	956.2	954.3	951.9	949.4	947.0	944.6
22.5°	932.9	930.6	928.4	926.2	924.2	922.3	920.3	918.3
25°	890.2	887.0	883.8	881.3	879.4	877.6	875.7	873.8
27.5°	846.7	842.8	838.8	835.5	832.8	830.1	827.4	824.7
30°	815.6	810.9	806.2	802.3	799.4	796.4	793.4	790.4
32.5°	783.7	778.3	772.9	768.7	765.9	763.0	760.2	757.3
35°	736.3	730.0	723.7	718.7	715.4	712.0	708.6	705.3
37.5°	685.5	678.3	671.2	666.0	662.7	659.3	655.9	652.5
40°	651.6	643.7	635.9	630.3	626.9	623.5	620.2	616.8
42.5°	618.3	610.3	602.3	596.5	592.9	589.5	586.0	582.4
45°	567.3	558.1	548.9	542.6	539.2	535.9	532.5	529.2
47.5°	515.9	506.4	496.9	490.2	486.6	482.8	479.1	475.4
50°	481.8	472.5	463.0	456.6	453.0	449.5	445.9	442.4
52.5°	447.8	438.3	428.7	422.2	418.4	414.7	411.1	407.3
55°	397.6	387.9	378.2	371.5	368.0	364.4	360.8	357.3
57.5°	348.6	338.7	328.8	322.6	319.9	317.2	314.5	311.8
60°	315.9	306.2	296.4	290.0	287.1	284.1	281.1	278.1
62.5°	283.7	274.7	265.7	260.0	257.6	255.2	252.8	250.4
65°	237.5	229.5	221.4	216.3	214.0	211.8	209.5	207.3
67.5°	195.1	188.2	181.3	176.6	174.1	171.6	169.1	166.7
70°	166.3	160.1	153.9	149.9	148.1	146.2	144.3	142.4
72.5°	140.5	135.1	129.8	126.4	124.7	122.9	121.2	119.5
75°	103.5	99.2	94.8	92.1	91.0	89.9	88.7	87.6
77.5°	73.2	70.7	68.1	66.7	66.4	66.1	65.8	65.4
80°	56.2	55.6	55.1	54.7	54.5	54.3	54.1	53.9
82.5°	43.6	43.3	42.9	42.5	42.4	42.1	42.0	41.8
85°	25.3	25.0	24.6	24.4	24.4	24.4	24.4	24.4
87.5°	15.1	15.2	15.4	15.6	15.8	16.1	16.3	16.6
90°	29.5	31.1	32.6	33.7	34.2	34.8	35.3	35.8
92.5°	28.5	30.1	31.7	32.6	32.6	32.8	32.9	33.0
95°	29.5	31.1	32.6	33.6	33.8	34.1	34.4	34.6
97.5°	31.8	32.0	32.2	32.4	32.6	33.0	33.2	33.4
100°	43.6	39.1	34.5	32.4	32.6	33.0	33.2	33.4
102.5°	155.9	107.2	58.5	34.2	34.2	34.3	34.4	34.4
105°	377.5	379.9	382.3	378.7	369.2	359.6	350.1	340.5
107.5°	467.1	468.3	469.4	470.5	471.5	472.5	473.5	474.5
110°	527.9	528.5	528.9	529.7	530.4	531.2	532.0	532.8



TEST NUMBER: P333073-927

CATALOG NUMBER: S124RDIW-S795D1560U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	586.8	586.7	586.6	587.1	588.1	589.1	590.1	591.1
115°	674.9	675.3	675.9	676.2	676.2	676.2	676.2	676.2
117.5°	763.4	763.3	763.2	763.1	763.0	762.9	762.8	762.6
120°	818.2	818.7	819.3	819.3	818.7	818.2	817.7	817.1
122.5°	872.3	872.6	872.9	872.7	872.3	871.7	871.2	870.7
125°	947.8	948.6	949.4	949.9	950.1	950.4	950.7	950.9
127.5°	1022.8	1022.6	1022.5	1022.2	1022.1	1021.8	1021.6	1021.4
130°	1068.6	1068.8	1069.1	1069.2	1069.2	1069.2	1069.2	1069.2
132.5°	1113.5	1113.7	1114.0	1114.0	1113.8	1113.6	1113.4	1113.2
135°	1175.4	1175.9	1176.5	1177.0	1177.5	1178.1	1178.6	1179.1
137.5°	1234.8	1235.3	1236.0	1236.1	1236.0	1235.8	1235.6	1235.5
140°	1271.5	1272.3	1273.1	1273.6	1273.9	1274.1	1274.4	1274.7
142.5°	1305.5	1306.1	1306.6	1306.9	1307.0	1307.1	1307.1	1307.2
145°	1354.1	1354.3	1354.6	1355.0	1355.5	1356.1	1356.6	1357.1
147.5°	1396.7	1396.9	1397.2	1397.4	1397.6	1397.9	1398.2	1398.4
150°	1424.0	1424.0	1424.0	1424.2	1424.4	1424.7	1425.0	1425.2
152.5°	1447.8	1448.2	1448.7	1448.7	1448.6	1448.4	1448.3	1448.1
155°	1479.9	1481.0	1482.0	1482.2	1481.4	1480.6	1479.8	1479.0
157.5°	1507.5	1508.9	1510.3	1510.3	1508.9	1507.5	1506.2	1504.8
160°	1525.2	1526.8	1528.4	1528.4	1526.8	1525.2	1523.6	1521.9
162.5°	1539.5	1541.1	1542.7	1542.5	1540.8	1539.0	1537.2	1535.3
165°	1559.6	1561.8	1563.9	1563.8	1561.4	1559.0	1556.6	1554.3
167.5°	1574.5	1576.8	1579.1	1579.0	1576.3	1573.7	1571.0	1568.4
170°	1583.6	1585.7	1587.9	1587.5	1584.9	1582.2	1579.6	1576.9
172.5°	1589.3	1591.4	1593.6	1593.2	1590.3	1587.5	1584.6	1581.7
175°	1596.0	1598.5	1600.8	1600.4	1597.2	1594.0	1590.9	1587.7
177.5°	1598.7	1600.4	1602.1	1601.7	1599.2	1596.6	1594.0	1591.5
180°	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2	1597.2

(END OF REPORT)