

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332432-840

Luminaire Tested: **S123RDIW-S775D460U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332432-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S775D460U840-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 460 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4809.4 lumens
Efficiency: N/A
Efficacy: 127.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 37.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332432-840

CATALOG NUMBER: S123RDIW-S775D460U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332432-840

CATALOG NUMBER: S123RDIW-S775D460U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	66	66	66	61
1	101	96	93	89	94	90	87	84	79	77	75	69	67	65	59	58	57	52
2	92	85	79	74	86	80	74	70	70	66	62	61	58	55	53	51	49	45
3	84	75	68	62	79	70	64	59	62	57	53	54	50	47	47	44	42	38
4	77	67	59	53	72	63	56	50	55	50	45	49	44	41	42	39	36	33
5	71	60	51	45	66	56	49	43	50	44	39	44	39	36	38	35	32	29
6	66	54	45	40	61	51	43	38	45	39	35	40	35	31	35	31	28	26
7	61	49	41	35	57	46	39	34	41	35	31	36	32	28	32	28	25	23
8	57	44	36	31	53	42	35	30	37	32	27	33	29	25	29	26	23	21
9	53	41	33	28	49	38	32	27	34	29	25	31	26	23	27	23	21	19
10	49	37	30	25	46	35	29	24	32	26	22	28	24	21	25	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14034	14034	14034
5°	14088	13894	13973
10°	14008	13719	13672
15°	13857	13397	13256
20°	13651	12997	12693
25°	13438	12545	12144
30°	13155	12026	11368
35°	12867	11506	10657
40°	12600	10891	9777
45°	12250	10286	8983
50°	11863	9597	8092
55°	11470	8811	7263
60°	11108	7967	6351
65°	10639	7055	5440
70°	10049	5923	4393
75°	9191	4662	4134
80°	8195	4135	3800
85°	6916	3656	3396



TEST NUMBER: P332432-840

CATALOG NUMBER: S123RDIW-S775D460U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.4	2.5
10°-20°	340.6	7.1
20°-30°	490.5	10.2
30°-40°	552.5	11.5
40°-50°	528.6	11.0
50°-60°	432.9	9.0
60°-70°	292.0	6.1
70°-80°	146.9	3.1
80°-90°	40.6	0.8
90°-100°	22.2	0.5
100°-110°	105.8	2.2
110°-120°	254.2	5.3
120°-130°	323.7	6.7
130°-140°	345.8	7.2
140°-150°	323.4	6.7
150°-160°	260.8	5.4
160°-170°	168.4	3.5
170°-180°	58.0	1.2
0°-30°	953.6	19.8
0°-40°	1506.1	31.3
0°-60°	2467.5	51.3
0°-90°	2947.1	61.3
90°-120°	382.2	7.9
90°-150°	1375.1	28.6
90°-180°	1862.0	38.7
0°-180°	4809.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1304	1304	1304	1304	1304	
5°	1304	1298	1286	1295	1293	124
15°	1244	1231	1202	1197	1190	350
25°	1132	1104	1056	1035	1022	520
35°	979	940	876	832	811	613
45°	805	755	676	617	590	621
55°	611	557	470	410	387	548
65°	418	358	277	227	214	413
75°	221	170	112	102	99	236
85°	56	34	30	28	28	63
90°	0	5	11	13	14	4
95°	28	10	14	17	17	34
105°	135	138	99	24	20	143
115°	254	256	260	265	267	250
125°	358	361	363	364	365	319
135°	445	448	450	451	450	343
145°	514	517	518	519	519	321
155°	566	565	565	567	565	261
165°	597	595	595	598	595	169
175°	611	608	609	612	608	58
180°	611	611	611	611	611	



TEST NUMBER: P332432-840

CATALOG NUMBER: S123RDIW-S775D460U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8
2.5°	1308.0	1307.3	1306.5	1305.8	1305.0	1303.5	1301.2	1299.0	1296.8	1294.4	1296.6
5°	1303.8	1302.6	1301.4	1300.3	1299.1	1297.1	1294.2	1291.4	1288.6	1285.9	1287.9
7.5°	1291.7	1290.5	1289.2	1287.9	1286.7	1284.1	1280.5	1276.9	1273.2	1269.5	1270.7
10°	1281.6	1279.9	1278.3	1276.7	1275.0	1272.0	1267.8	1263.6	1259.4	1255.2	1255.4
12.5°	1267.2	1265.4	1263.5	1261.7	1259.9	1256.4	1251.2	1246.1	1240.8	1235.7	1235.6
15°	1243.5	1240.9	1238.3	1235.8	1233.1	1228.6	1222.0	1215.5	1208.8	1202.2	1201.1
17.5°	1213.7	1210.7	1207.7	1204.7	1201.6	1196.0	1187.6	1179.2	1170.8	1162.6	1160.0
20°	1191.7	1187.9	1184.2	1180.4	1176.7	1170.3	1161.3	1152.5	1143.6	1134.6	1131.6
22.5°	1167.2	1162.9	1158.5	1154.2	1149.8	1143.0	1133.5	1124.0	1114.5	1105.0	1101.2
25°	1131.5	1125.6	1119.6	1113.8	1107.9	1099.5	1088.7	1077.9	1067.1	1056.3	1051.4
27.5°	1088.0	1081.6	1075.1	1068.6	1062.2	1052.9	1040.9	1028.9	1016.7	1004.7	997.8
30°	1058.4	1051.4	1044.4	1037.3	1030.3	1020.2	1007.0	993.8	980.7	967.6	959.6
32.5°	1028.9	1020.9	1012.9	1004.9	996.9	985.9	972.0	958.2	944.2	930.3	921.6
35°	979.2	970.7	962.2	953.8	945.3	933.8	919.3	904.6	890.1	875.6	865.5
37.5°	928.9	919.4	910.0	900.6	891.2	878.8	863.2	847.7	832.1	816.6	805.1
40°	896.7	886.4	876.0	865.7	855.4	841.8	825.2	808.5	791.7	775.1	762.9
42.5°	860.3	850.0	839.6	829.3	819.0	805.2	787.9	770.6	753.5	736.2	722.9
45°	804.7	794.2	783.6	773.0	762.3	748.1	729.9	711.9	693.8	675.7	662.3
47.5°	749.1	737.5	725.9	714.3	702.7	687.8	669.7	651.6	633.5	615.4	600.9
50°	708.4	697.4	686.4	675.3	664.3	649.2	630.3	611.2	592.2	573.1	558.6
52.5°	672.1	660.1	648.1	636.1	624.2	608.7	589.9	571.1	552.2	533.3	518.3
55°	611.2	599.7	588.1	576.6	565.1	549.4	529.4	509.5	489.5	469.5	455.9
57.5°	554.9	542.4	529.9	517.3	504.7	488.5	468.4	448.3	428.2	408.2	395.3
60°	516.0	503.1	490.2	477.3	464.3	448.1	428.6	409.1	389.6	370.1	357.4
62.5°	477.1	464.1	451.2	438.3	425.5	409.2	389.7	370.2	350.7	331.1	319.2
65°	417.7	404.8	391.8	378.9	366.0	350.3	332.0	313.7	295.4	277.0	265.5
67.5°	358.3	345.2	332.1	319.0	306.0	290.6	273.1	255.5	237.9	220.4	211.8
70°	319.3	306.7	294.0	281.2	268.6	254.0	237.5	221.2	204.7	188.2	180.0
72.5°	280.4	267.9	255.4	242.9	230.5	216.7	201.8	186.8	171.9	156.9	150.2
75°	221.0	209.7	198.4	187.1	175.9	163.8	150.9	137.9	125.0	112.1	109.8
77.5°	166.8	156.6	146.4	136.2	126.0	116.8	108.5	100.2	91.9	83.5	82.3
80°	132.2	122.5	112.9	103.3	93.6	86.3	81.4	76.4	71.6	66.7	65.9
82.5°	99.2	90.9	82.5	74.2	65.9	60.6	58.3	55.9	53.7	51.4	50.7
85°	56.0	50.9	45.7	40.5	35.3	32.4	31.7	31.0	30.3	29.6	29.2
87.5°	20.4	18.5	16.7	14.7	12.9	12.1	12.4	12.6	12.9	13.1	13.0
90°	0.4	1.4	2.4	3.4	4.4	5.7	7.0	8.3	9.6	10.9	11.3
92.5°	8.5	8.2	7.9	7.6	7.3	7.7	8.7	9.6	10.6	11.6	12.2
95°	27.7	23.5	19.4	15.2	11.1	9.6	10.7	11.8	12.9	14.0	14.7
97.5°	55.6	53.7	51.9	50.1	48.2	43.6	36.4	29.1	21.9	14.6	15.5
100°	76.6	78.7	80.7	82.7	84.7	77.9	62.2	46.5	30.7	14.9	15.8
102.5°	100.6	102.1	103.5	105.0	106.4	98.6	81.4	64.2	47.1	29.9	27.4
105°	135.2	136.3	137.4	138.6	139.7	135.6	126.5	117.5	108.5	99.4	81.5
107.5°	171.7	172.6	173.5	174.3	175.2	176.4	177.8	179.3	180.7	182.1	169.1
110°	196.0	196.8	197.6	198.4	199.2	200.2	201.3	202.4	203.5	204.6	201.3



TEST NUMBER: P332432-840

CATALOG NUMBER: S123RDIW-S775D460U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	219.2	219.9	220.7	221.4	222.2	223.1	224.2	225.3	226.4	227.5	227.5
115°	253.6	254.2	254.8	255.4	256.0	256.8	257.7	258.6	259.5	260.4	261.5
117.5°	286.9	287.7	288.4	289.1	289.9	290.5	290.9	291.4	292.0	292.4	293.2
120°	307.6	308.5	309.4	310.3	311.2	311.8	312.1	312.5	312.8	313.1	313.9
122.5°	328.7	329.4	330.1	330.9	331.6	332.2	332.6	333.0	333.4	333.8	334.3
125°	357.5	358.3	359.1	359.9	360.7	361.3	361.7	362.1	362.5	362.9	363.1
127.5°	385.5	386.3	387.1	387.9	388.7	389.3	389.8	390.3	390.8	391.3	391.6
130°	402.9	403.7	404.6	405.4	406.2	406.8	407.2	407.6	408.0	408.3	408.7
132.5°	419.6	420.4	421.2	422.0	422.8	423.3	423.7	424.0	424.3	424.6	425.1
135°	445.0	445.7	446.3	446.9	447.5	448.0	448.4	448.8	449.2	449.6	449.9
137.5°	466.9	467.7	468.4	469.2	469.9	470.4	470.7	470.9	471.1	471.3	471.8
140°	481.4	482.0	482.6	483.2	483.8	484.2	484.5	484.8	485.1	485.4	485.8
142.5°	494.8	495.4	496.0	496.7	497.3	497.7	498.0	498.3	498.6	498.9	499.2
145°	513.6	514.3	515.0	515.7	516.4	516.8	517.1	517.3	517.5	517.7	517.9
147.5°	531.3	531.8	532.2	532.7	533.1	533.5	533.7	533.9	534.1	534.3	534.5
150°	542.2	542.5	542.8	543.1	543.4	543.6	543.8	544.0	544.2	544.4	544.6
152.5°	552.0	552.1	552.3	552.4	552.6	552.7	552.8	552.9	553.0	553.2	553.5
155°	565.7	565.5	565.3	565.2	565.0	564.9	565.0	565.1	565.2	565.3	565.8
157.5°	576.5	576.4	576.4	576.4	576.4	576.3	576.2	576.1	576.0	575.9	576.5
160°	583.0	582.9	582.8	582.7	582.6	582.5	582.4	582.3	582.2	582.1	582.7
162.5°	589.2	589.0	588.7	588.4	588.1	587.9	587.8	587.7	587.6	587.5	588.2
165°	596.6	596.3	596.0	595.7	595.4	595.2	595.1	595.0	594.9	594.8	595.6
167.5°	602.5	602.1	601.7	601.3	600.9	600.7	600.7	600.7	600.7	600.7	601.5
170°	605.7	605.3	604.9	604.5	604.1	603.9	603.9	603.9	603.9	603.9	604.7
172.5°	607.8	607.4	606.9	606.4	605.9	605.7	605.8	605.9	606.0	606.0	606.8
175°	610.7	610.2	609.7	609.2	608.6	608.4	608.5	608.6	608.7	608.8	609.6
177.5°	611.4	611.0	610.6	610.2	609.8	609.7	609.8	609.8	609.9	610.0	610.6
180°	610.7	610.7	610.7	610.7	610.7	610.7	610.7	610.7	610.7	610.7	610.7



TEST NUMBER: P332432-840

CATALOG NUMBER: S123RDIW-S775D460U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8	1303.8
2.5°	1298.6	1300.7	1302.7	1303.6	1303.2	1302.8	1302.4	1302.1
5°	1290.0	1292.1	1294.2	1295.1	1294.6	1294.1	1293.6	1293.2
7.5°	1271.9	1273.0	1274.2	1274.4	1273.6	1272.8	1272.0	1271.2
10°	1255.7	1255.9	1256.1	1255.7	1254.5	1253.2	1252.1	1250.9
12.5°	1235.4	1235.3	1235.2	1234.4	1233.0	1231.6	1230.3	1228.9
15°	1199.9	1198.7	1197.6	1196.2	1194.6	1192.9	1191.2	1189.6
17.5°	1157.5	1155.1	1152.6	1150.1	1147.6	1145.2	1142.8	1140.3
20°	1128.5	1125.4	1122.4	1119.4	1116.6	1113.8	1111.0	1108.1
22.5°	1097.4	1093.6	1089.7	1086.5	1083.9	1081.3	1078.6	1076.0
25°	1046.5	1041.6	1036.6	1032.9	1030.3	1027.6	1025.1	1022.5
27.5°	991.0	984.2	977.3	971.9	968.0	964.0	960.1	956.1
30°	951.6	943.5	935.5	929.7	925.9	922.2	918.4	914.6
32.5°	912.8	904.1	895.3	889.0	885.0	881.1	877.2	873.2
35°	855.4	845.3	835.2	828.0	823.7	819.5	815.3	811.0
37.5°	793.6	782.1	770.6	762.3	757.1	751.8	746.7	741.4
40°	750.6	738.4	726.2	717.4	712.0	706.6	701.1	695.8
42.5°	709.4	696.1	682.8	673.7	668.8	664.0	659.1	654.3
45°	648.9	635.5	622.1	612.6	606.9	601.3	595.7	590.1
47.5°	586.2	571.7	557.1	547.3	542.3	537.2	532.3	527.3
50°	544.0	529.4	514.8	504.8	499.5	494.0	488.7	483.2
52.5°	503.1	488.0	472.8	462.8	458.0	453.1	448.3	443.4
55°	442.2	428.6	415.0	405.8	401.1	396.4	391.7	387.0
57.5°	382.4	369.5	356.7	348.2	344.3	340.2	336.2	332.2
60°	344.7	332.0	319.3	311.0	307.0	303.0	299.0	295.0
62.5°	307.3	295.4	283.5	275.4	271.1	267.0	262.9	258.6
65°	254.0	242.5	231.0	223.9	221.4	218.7	216.2	213.6
67.5°	203.2	194.6	185.9	180.3	177.5	174.7	172.0	169.2
70°	171.8	163.5	155.3	150.0	147.3	144.7	142.2	139.6
72.5°	143.5	136.7	130.1	126.1	125.0	124.0	122.9	121.8
75°	107.3	105.0	102.7	101.3	100.8	100.4	99.9	99.4
77.5°	81.0	79.7	78.5	77.6	77.2	76.6	76.1	75.7
80°	65.2	64.5	63.8	63.2	62.7	62.3	61.8	61.3
82.5°	50.0	49.3	48.6	48.2	48.1	48.0	47.9	47.8
85°	28.7	28.2	27.8	27.5	27.5	27.5	27.5	27.5
87.5°	12.9	12.8	12.7	12.6	12.4	12.3	12.2	12.0
90°	11.7	12.1	12.5	12.8	13.0	13.2	13.4	13.6
92.5°	12.9	13.5	14.2	14.5	14.7	14.8	14.9	15.0
95°	15.5	16.2	16.9	17.3	17.3	17.3	17.3	17.3
97.5°	16.3	17.1	17.9	18.3	18.4	18.5	18.6	18.7
100°	16.6	17.4	18.2	18.7	18.8	18.9	19.0	19.1
102.5°	24.8	22.3	19.9	18.7	18.9	19.1	19.2	19.4
105°	63.6	45.8	28.0	19.2	19.4	19.6	19.8	20.0
107.5°	155.9	142.9	129.8	116.5	103.0	89.6	76.1	62.7
110°	197.9	194.6	191.3	182.5	168.0	153.6	139.2	124.8



TEST NUMBER: P332432-840

CATALOG NUMBER: S123RDIW-S775D460U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	227.6	227.6	227.7	226.2	223.2	220.2	217.1	214.1
115°	262.5	263.5	264.5	265.2	265.6	266.0	266.4	266.8
117.5°	294.0	294.8	295.6	296.0	296.1	296.2	296.3	296.4
120°	314.7	315.5	316.3	316.7	316.7	316.7	316.7	316.7
122.5°	334.9	335.5	336.0	336.3	336.4	336.5	336.6	336.7
125°	363.3	363.6	363.8	364.0	364.2	364.4	364.6	364.8
127.5°	391.9	392.2	392.5	392.6	392.4	392.2	392.0	391.8
130°	409.1	409.5	409.9	410.0	409.8	409.6	409.4	409.2
132.5°	425.5	425.9	426.3	426.4	426.1	425.8	425.5	425.3
135°	450.2	450.5	450.8	450.8	450.5	450.2	449.9	449.6
137.5°	472.3	472.7	473.2	473.4	473.2	473.0	472.8	472.6
140°	486.3	486.7	487.1	487.2	487.0	486.8	486.6	486.4
142.5°	499.6	499.9	500.2	500.2	499.9	499.7	499.4	499.1
145°	518.1	518.3	518.5	518.6	518.6	518.6	518.6	518.6
147.5°	534.7	534.9	535.1	534.9	534.5	534.0	533.6	533.1
150°	544.8	545.0	545.2	545.2	544.9	544.6	544.3	544.0
152.5°	553.9	554.2	554.6	554.5	554.1	553.6	553.2	552.7
155°	566.3	566.8	567.3	567.2	566.6	566.0	565.4	564.9
157.5°	577.1	577.7	578.3	578.2	577.4	576.7	575.9	575.1
160°	583.3	583.9	584.5	584.5	583.8	583.1	582.4	581.7
162.5°	589.0	589.7	590.3	590.4	589.7	589.1	588.4	587.8
165°	596.4	597.2	598.0	598.0	597.3	596.7	596.0	595.3
167.5°	602.3	603.0	603.8	603.8	603.0	602.3	601.5	600.7
170°	605.5	606.3	607.1	607.1	606.3	605.5	604.7	603.9
172.5°	607.6	608.4	609.3	609.3	608.3	607.4	606.6	605.7
175°	610.3	611.0	611.7	611.7	610.9	610.1	609.3	608.4
177.5°	611.3	611.9	612.6	612.5	611.7	610.9	610.1	609.3
180°	610.7	610.7	610.7	610.7	610.7	610.7	610.7	610.7

(END OF REPORT)