

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333074-927

Luminaire Tested: **S124RDIW-S795D1560U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333074-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S795D1560U927-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6832.1 lumens
Efficiency: N/A
Efficacy: 100.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 68.1
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333074-927

CATALOG NUMBER: S124RDIW-S795D1560U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333074-927

CATALOG NUMBER: S124RDIW-S795D1560U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	44	44	44	37
1	95	91	87	84	86	83	79	77	67	65	63	53	51	50	40	39	38	32
2	87	80	74	69	78	72	67	63	59	55	52	47	44	42	35	34	32	27
3	79	70	63	57	72	64	58	53	52	48	44	41	38	36	31	29	28	23
4	73	62	54	49	66	57	50	45	46	42	38	37	33	31	28	26	24	20
5	67	55	47	42	60	51	44	39	42	36	33	33	29	27	25	23	21	17
6	61	50	42	36	55	45	39	34	37	32	28	30	26	23	23	20	18	15
7	57	45	37	32	51	41	34	29	34	29	25	27	23	21	21	18	16	14
8	53	41	33	28	48	37	31	26	31	26	22	25	21	18	19	17	15	12
9	49	37	30	25	44	34	28	23	28	23	20	23	19	17	18	15	13	11
10	46	34	27	22	41	31	25	21	26	21	18	21	18	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8884	8884	8884
5°	8904	8795	8849
10°	8848	8689	8689
15°	8747	8507	8444
20°	8607	8267	8115
25°	8429	7986	7783
30°	8255	7690	7368
35°	8064	7383	6951
40°	7832	7032	6500
45°	7618	6687	6042
50°	7376	6286	5556
55°	7116	5871	5029
60°	6830	5414	4490
65°	6567	4846	3960
70°	6187	4216	3361
75°	5702	3497	2732
80°	4974	2664	2506
85°	4215	2418	2260



TEST NUMBER: P333074-927

CATALOG NUMBER: S124RDIW-S795D1560U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.4	1.5
10°-20°	288.3	4.2
20°-30°	416.3	6.1
30°-40°	471.8	6.9
40°-50°	455.6	6.7
50°-60°	378.9	5.5
60°-70°	261.6	3.8
70°-80°	132.6	1.9
80°-90°	38.6	0.6
90°-100°	101.9	1.5
100°-110°	301.8	4.4
110°-120°	512.2	7.5
120°-130°	675.4	9.9
130°-140°	758.5	11.1
140°-150°	745.3	10.9
150°-160°	626.9	9.2
160°-170°	417.1	6.1
170°-180°	146.1	2.1
0°-30°	807.9	11.8
0°-40°	1279.7	18.7
0°-60°	2114.3	30.9
0°-90°	2547.1	37.3
90°-120°	915.8	13.4
90°-150°	3095.0	45.3
90°-180°	4285.0	62.7
0°-180°	6832.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1100	1100	1100	1100	1100	
5°	1099	1095	1085	1093	1092	104
15°	1047	1038	1018	1016	1010	295
25°	946	930	896	883	874	436
35°	818	790	749	721	705	511
45°	667	635	586	546	529	514
55°	506	471	417	375	357	452
65°	344	307	254	219	207	339
75°	183	151	112	93	88	193
85°	46	29	26	24	24	51
90°	4	17	26	33	36	7
95°	72	82	91	94	94	80
105°	278	280	284	288	291	295
115°	521	521	518	517	516	513
125°	758	758	757	755	752	676
135°	978	985	986	983	980	757
145°	1188	1193	1194	1193	1190	743
155°	1362	1362	1360	1365	1360	626
165°	1482	1479	1476	1483	1479	418
175°	1542	1536	1535	1542	1535	146
180°	1544	1544	1544	1544	1544	



TEST NUMBER: P333074-927

CATALOG NUMBER: S124RDIW-S795D1560U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5
2.5°	1103.2	1102.6	1101.9	1101.4	1100.7	1099.6	1098.0	1096.4	1094.7	1093.1	1094.7
5°	1098.8	1098.0	1097.3	1096.5	1095.7	1094.3	1092.0	1089.8	1087.5	1085.3	1087.2
7.5°	1088.9	1088.1	1087.3	1086.5	1085.7	1083.9	1080.9	1078.0	1075.1	1072.1	1073.3
10°	1079.4	1078.5	1077.5	1076.6	1075.6	1073.5	1070.2	1066.8	1063.4	1060.0	1060.7
12.5°	1067.2	1066.2	1065.1	1064.0	1063.0	1060.4	1056.5	1052.4	1048.5	1044.5	1045.0
15°	1046.6	1044.9	1043.1	1041.5	1039.8	1036.6	1031.9	1027.2	1022.5	1017.9	1017.5
17.5°	1021.4	1019.0	1016.5	1014.2	1011.7	1007.7	1002.0	996.4	990.8	985.2	984.1
20°	1001.9	999.4	997.0	994.6	992.1	987.8	981.4	975.0	968.6	962.3	960.8
22.5°	980.3	977.6	974.9	972.1	969.4	964.6	957.7	950.9	944.1	937.3	935.1
25°	946.3	942.9	939.5	936.1	932.8	927.2	919.6	911.9	904.2	896.5	893.3
27.5°	910.5	906.3	902.1	897.9	893.6	887.4	879.2	871.0	862.8	854.6	850.6
30°	885.6	880.9	876.2	871.6	866.9	860.2	851.4	842.6	833.7	824.9	820.2
32.5°	859.3	854.1	848.7	843.4	838.2	831.0	821.9	812.8	803.7	794.6	789.2
35°	818.2	812.2	806.2	800.2	794.2	786.6	777.2	767.8	758.4	749.1	742.8
37.5°	774.2	768.0	761.8	755.7	749.5	741.2	730.9	720.5	710.1	699.7	692.6
40°	743.2	737.0	730.9	724.7	718.5	710.0	699.3	688.7	678.0	667.3	659.5
42.5°	713.5	707.0	700.6	694.1	687.6	678.8	667.7	656.6	645.5	634.3	626.3
45°	667.3	660.4	653.5	646.6	639.6	630.6	619.3	608.1	596.8	585.7	576.5
47.5°	619.6	612.5	605.4	598.2	591.0	581.6	570.0	558.3	546.6	534.9	525.4
50°	587.3	580.0	572.7	565.4	558.1	548.4	536.5	524.5	512.5	500.5	491.2
52.5°	554.3	547.2	540.0	532.8	525.7	515.9	503.7	491.4	479.1	466.8	457.3
55°	505.6	498.0	490.6	483.1	475.6	465.8	453.6	441.4	429.3	417.1	407.3
57.5°	457.4	449.6	441.8	434.0	426.2	416.3	404.3	392.4	380.4	368.4	358.5
60°	423.0	415.5	408.1	400.5	393.0	383.3	371.3	359.3	347.4	335.3	325.6
62.5°	392.0	384.2	376.4	368.6	360.8	350.8	338.5	326.2	313.9	301.7	292.6
65°	343.8	335.7	327.6	319.6	311.6	301.6	289.5	277.6	265.6	253.7	245.6
67.5°	293.7	286.1	278.3	270.6	262.8	253.5	242.3	231.2	220.1	209.0	202.0
70°	262.1	254.2	246.3	238.4	230.6	221.3	210.6	199.9	189.3	178.6	172.5
72.5°	228.4	221.3	214.1	207.0	199.9	191.3	181.3	171.1	161.1	151.0	145.7
75°	182.8	175.9	169.0	162.1	155.1	147.3	138.5	129.7	120.9	112.1	107.7
77.5°	136.7	130.8	124.9	119.1	113.1	106.6	99.6	92.4	85.3	78.2	75.7
80°	107.0	101.6	96.2	90.7	85.3	79.8	74.1	68.5	62.9	57.3	56.7
82.5°	81.4	76.4	71.5	66.5	61.5	57.4	54.2	50.9	47.7	44.5	44.0
85°	45.5	41.7	38.0	34.3	30.5	28.4	27.8	27.3	26.7	26.1	25.7
87.5°	16.2	15.6	15.0	14.3	13.8	13.6	13.9	14.2	14.4	14.7	14.9
90°	3.6	6.5	9.4	12.4	15.3	17.8	19.9	22.0	24.2	26.3	27.9
92.5°	25.6	28.9	32.2	35.6	39.0	41.4	42.9	44.4	45.8	47.3	48.2
95°	71.7	74.1	76.4	78.8	81.2	83.3	85.2	87.1	89.0	90.8	91.6
97.5°	125.2	127.1	129.0	130.9	132.8	134.9	137.0	139.2	141.4	143.5	144.5
100°	167.2	168.3	169.4	170.4	171.5	173.2	175.6	178.0	180.4	182.8	183.3
102.5°	211.2	211.6	212.1	212.5	212.9	214.2	216.3	218.6	220.7	222.9	223.6
105°	278.3	278.6	278.8	279.1	279.4	280.0	281.1	282.2	283.2	284.3	285.1
107.5°	348.8	349.1	349.4	349.7	350.1	350.3	350.5	350.6	350.8	350.9	351.6
110°	396.6	397.1	397.6	398.2	398.7	398.9	398.5	398.3	398.0	397.8	397.2



TEST NUMBER: P333074-927

CATALOG NUMBER: S124RDIW-S795D1560U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	446.2	446.4	446.5	446.6	446.7	446.5	446.0	445.5	445.0	444.6	444.5
115°	520.8	520.8	520.8	520.8	520.8	520.5	520.0	519.4	519.0	518.4	518.2
117.5°	591.0	591.2	591.4	591.7	591.9	591.8	591.4	591.0	590.7	590.3	589.4
120°	637.9	638.9	640.0	641.0	642.1	642.2	641.4	640.6	639.8	639.1	637.7
122.5°	686.6	687.0	687.5	687.9	688.2	688.3	687.9	687.5	687.2	686.8	686.0
125°	758.5	758.5	758.5	758.5	758.5	758.4	758.1	757.8	757.6	757.3	756.8
127.5°	823.7	824.5	825.3	826.1	826.9	827.1	826.6	826.2	825.9	825.4	824.8
130°	869.6	870.4	871.2	872.0	872.7	873.1	873.1	873.1	873.1	873.1	872.7
132.5°	916.4	917.0	917.6	918.1	918.8	918.9	918.7	918.5	918.3	918.1	917.6
135°	978.3	979.9	981.4	983.1	984.7	985.5	985.5	985.5	985.5	985.5	984.9
137.5°	1045.7	1046.4	1047.1	1047.9	1048.6	1049.2	1049.6	1050.0	1050.5	1050.9	1050.2
140°	1090.6	1091.1	1091.6	1092.2	1092.7	1093.0	1093.0	1093.0	1093.0	1093.0	1092.7
142.5°	1131.6	1132.2	1132.7	1133.2	1133.8	1133.9	1133.7	1133.5	1133.3	1133.1	1133.1
145°	1188.5	1189.5	1190.6	1191.7	1192.8	1193.4	1193.7	1194.0	1194.2	1194.5	1194.2
147.5°	1244.9	1246.2	1247.4	1248.7	1250.0	1250.5	1250.3	1250.1	1249.9	1249.7	1249.4
150°	1279.3	1280.3	1281.4	1282.5	1283.6	1284.0	1284.0	1284.0	1284.0	1284.0	1284.0
152.5°	1311.8	1312.4	1313.0	1313.7	1314.3	1314.8	1314.9	1315.2	1315.4	1315.6	1316.2
155°	1361.7	1361.7	1361.7	1361.7	1361.7	1361.6	1361.3	1361.0	1360.8	1360.5	1361.6
157.5°	1403.7	1403.3	1402.8	1402.3	1401.8	1401.6	1401.5	1401.4	1401.4	1401.4	1402.2
160°	1428.6	1428.3	1428.1	1427.8	1427.5	1427.3	1427.0	1426.7	1426.5	1426.2	1427.0
162.5°	1451.5	1450.9	1450.2	1449.5	1448.7	1448.3	1448.0	1447.8	1447.5	1447.2	1448.7
165°	1482.3	1481.5	1480.7	1480.0	1479.2	1478.5	1478.0	1477.4	1476.9	1476.4	1478.0
167.5°	1506.0	1504.9	1503.8	1502.7	1501.6	1501.0	1501.1	1501.1	1501.2	1501.3	1502.8
170°	1519.4	1518.1	1516.7	1515.4	1514.1	1513.5	1513.8	1514.1	1514.3	1514.6	1516.2
172.5°	1528.9	1527.8	1526.7	1525.6	1524.5	1523.9	1524.0	1524.1	1524.1	1524.2	1526.0
175°	1542.1	1540.7	1539.4	1538.1	1536.8	1536.0	1535.7	1535.4	1535.2	1534.9	1536.8
177.5°	1546.3	1545.3	1544.3	1543.2	1542.1	1541.6	1541.6	1541.6	1541.6	1541.6	1543.1
180°	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4



TEST NUMBER: P333074-927

CATALOG NUMBER: S124RDIW-S795D1560U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5	1100.5
2.5°	1096.4	1098.0	1099.6	1100.4	1100.3	1100.1	1099.9	1099.8
5°	1089.0	1090.9	1092.8	1093.5	1093.1	1092.8	1092.4	1092.0
7.5°	1074.5	1075.8	1077.0	1077.2	1076.7	1076.0	1075.5	1074.8
10°	1061.5	1062.2	1063.0	1063.0	1062.2	1061.5	1060.7	1060.0
12.5°	1045.4	1045.8	1046.3	1046.0	1045.0	1043.9	1042.8	1041.8
15°	1017.2	1016.8	1016.4	1015.6	1014.2	1012.9	1011.6	1010.3
17.5°	983.1	982.1	981.0	979.5	977.5	975.5	973.5	971.5
20°	959.3	957.7	956.2	954.3	951.9	949.4	947.0	944.6
22.5°	932.9	930.6	928.4	926.2	924.2	922.3	920.3	918.3
25°	890.2	887.0	883.8	881.3	879.4	877.6	875.7	873.8
27.5°	846.7	842.8	838.8	835.5	832.8	830.1	827.4	824.7
30°	815.6	810.9	806.2	802.3	799.4	796.4	793.4	790.4
32.5°	783.7	778.3	772.9	768.7	765.9	763.0	760.2	757.3
35°	736.3	730.0	723.7	718.7	715.4	712.0	708.6	705.3
37.5°	685.5	678.3	671.2	666.0	662.7	659.3	655.9	652.5
40°	651.6	643.7	635.9	630.3	626.9	623.5	620.2	616.8
42.5°	618.3	610.3	602.3	596.5	592.9	589.5	586.0	582.4
45°	567.3	558.1	548.9	542.6	539.2	535.9	532.5	529.2
47.5°	515.9	506.4	496.9	490.2	486.6	482.8	479.1	475.4
50°	481.8	472.5	463.0	456.6	453.0	449.5	445.9	442.4
52.5°	447.8	438.3	428.7	422.2	418.4	414.7	411.1	407.3
55°	397.6	387.9	378.2	371.5	368.0	364.4	360.8	357.3
57.5°	348.6	338.7	328.8	322.6	319.9	317.2	314.5	311.8
60°	315.9	306.2	296.4	290.0	287.1	284.1	281.1	278.1
62.5°	283.7	274.7	265.7	260.0	257.6	255.2	252.8	250.4
65°	237.5	229.5	221.4	216.3	214.0	211.8	209.5	207.3
67.5°	195.1	188.2	181.3	176.6	174.1	171.6	169.1	166.7
70°	166.3	160.1	153.9	149.9	148.1	146.2	144.3	142.4
72.5°	140.5	135.1	129.8	126.4	124.7	122.9	121.2	119.5
75°	103.5	99.2	94.8	92.1	91.0	89.9	88.7	87.6
77.5°	73.2	70.7	68.1	66.7	66.4	66.1	65.8	65.4
80°	56.2	55.6	55.1	54.7	54.5	54.3	54.1	53.9
82.5°	43.6	43.3	42.9	42.5	42.4	42.1	42.0	41.8
85°	25.3	25.0	24.6	24.4	24.4	24.4	24.4	24.4
87.5°	15.1	15.2	15.4	15.6	15.8	16.1	16.3	16.6
90°	29.5	31.1	32.6	33.7	34.2	34.8	35.3	35.8
92.5°	49.2	50.1	51.1	51.7	52.0	52.4	52.7	53.0
95°	92.4	93.2	94.0	94.3	94.3	94.3	94.3	94.3
97.5°	145.5	146.5	147.4	147.9	147.9	147.9	147.9	147.9
100°	183.8	184.3	184.9	185.1	185.1	185.1	185.1	185.1
102.5°	224.3	225.1	225.9	226.3	226.6	226.8	227.0	227.2
105°	285.9	286.7	287.5	288.3	289.1	289.9	290.7	291.4
107.5°	352.4	353.2	353.9	354.3	354.2	354.2	354.1	354.0
110°	396.7	396.2	395.6	395.8	396.6	397.4	398.2	398.9



TEST NUMBER: P333074-927

CATALOG NUMBER: S124RDIW-S795D1560U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	444.3	444.3	444.2	444.2	444.3	444.5	444.7	444.8
115°	517.8	517.6	517.4	517.1	516.8	516.6	516.3	516.0
117.5°	588.5	587.6	586.7	586.0	585.4	584.9	584.4	583.8
120°	636.4	635.1	633.7	633.3	633.9	634.4	634.9	635.5
122.5°	685.0	684.1	683.3	682.3	681.4	680.4	679.5	678.5
125°	756.2	755.7	755.2	754.6	754.1	753.6	753.0	752.5
127.5°	824.3	823.8	823.2	822.8	822.4	822.0	821.5	821.1
130°	872.1	871.6	871.0	870.2	869.2	868.2	867.0	866.0
132.5°	917.0	916.5	915.9	915.4	915.0	914.7	914.2	913.8
135°	984.4	983.9	983.3	982.6	981.8	981.0	980.2	979.5
137.5°	1049.6	1048.8	1048.1	1047.9	1048.1	1048.2	1048.4	1048.5
140°	1092.4	1092.2	1091.9	1091.6	1091.4	1091.1	1090.8	1090.6
142.5°	1133.0	1132.9	1132.9	1132.8	1132.7	1132.7	1132.7	1132.6
145°	1194.0	1193.7	1193.4	1192.9	1192.1	1191.3	1190.5	1189.7
147.5°	1249.3	1249.0	1248.8	1248.6	1248.3	1248.1	1247.8	1247.5
150°	1284.0	1284.0	1284.0	1284.0	1283.7	1283.4	1283.2	1282.9
152.5°	1316.8	1317.5	1318.1	1318.1	1317.4	1316.8	1316.1	1315.3
155°	1362.6	1363.7	1364.8	1364.8	1363.7	1362.6	1361.6	1360.5
157.5°	1403.0	1403.7	1404.5	1404.5	1403.6	1402.7	1401.8	1400.9
160°	1427.8	1428.6	1429.4	1429.1	1427.8	1426.5	1425.1	1423.8
162.5°	1450.1	1451.5	1452.9	1453.0	1451.7	1450.4	1449.1	1447.7
165°	1479.6	1481.1	1482.7	1483.0	1481.9	1480.9	1479.8	1478.8
167.5°	1504.4	1506.0	1507.6	1507.6	1505.9	1504.3	1502.6	1500.9
170°	1517.8	1519.4	1521.0	1520.8	1519.0	1517.1	1515.3	1513.4
172.5°	1527.8	1529.5	1531.4	1531.4	1529.5	1527.6	1525.7	1523.9
175°	1538.7	1540.5	1542.4	1542.4	1540.5	1538.7	1536.8	1534.9
177.5°	1544.6	1546.0	1547.5	1547.4	1545.7	1544.0	1542.4	1540.6
180°	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4	1544.4

(END OF REPORT)