

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332197-940

Luminaire Tested: **S123DIW-S1000D1030U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332197-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S1000D1030U940-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1030 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6862.5 lumens
Efficiency: N/A
Efficacy: 112.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 61.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332197-940

CATALOG NUMBER: S123DIW-S1000D1030U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332197-940

CATALOG NUMBER: S123DIW-S1000D1030U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	54
1	99	94	90	87	91	87	84	81	75	72	70	63	61	60	52	51	50	45
2	90	82	76	71	83	76	71	66	65	61	58	55	52	50	46	44	42	38
3	82	72	65	59	75	67	61	55	58	53	49	49	45	42	41	38	36	32
4	75	64	56	50	69	60	52	47	51	46	41	44	39	36	36	33	31	27
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	30	27	24
6	63	51	43	37	58	48	40	35	41	36	31	35	31	27	30	26	24	21
7	59	46	38	32	54	43	36	31	37	32	27	32	28	24	27	24	21	18
8	54	42	34	29	50	39	32	27	34	28	24	29	25	22	25	21	19	16
9	51	38	31	26	47	36	29	24	31	26	22	27	23	19	23	20	17	15
10	47	35	28	23	44	33	26	22	29	23	20	25	21	18	21	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15193	15193	15193
5°	15263	15055	15159
10°	15162	14924	15017
15°	14985	14755	14782
20°	14778	14513	14528
25°	14500	14226	14197
30°	14194	13908	13801
35°	13875	13571	13397
40°	13541	13198	12995
45°	13172	12858	12543
50°	12804	12439	12092
55°	12322	12003	11639
60°	11834	11496	11130
65°	11405	10942	10603
70°	10770	10313	9854
75°	9844	9491	9087
80°	8877	8498	8424
85°	7793	7497	7188



TEST NUMBER: P332197-940

CATALOG NUMBER: S123DIW-S1000D1030U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	133.0	1.9
10°-20°	375.4	5.5
20°-30°	554.6	8.1
30°-40°	647.8	9.4
40°-50°	651.3	9.5
50°-60°	572.1	8.3
60°-70°	426.2	6.2
70°-80°	242.8	3.5
80°-90°	73.1	1.1
90°-100°	74.9	1.1
100°-110°	224.2	3.3
110°-120°	381.4	5.6
120°-130°	501.7	7.3
130°-140°	563.9	8.2
140°-150°	554.3	8.1
150°-160°	466.6	6.8
160°-170°	310.6	4.5
170°-180°	108.8	1.6
0°-30°	1062.9	15.5
0°-40°	1710.7	24.9
0°-60°	2934.1	42.8
0°-90°	3676.2	53.6
90°-120°	680.6	9.9
90°-150°	2300.3	33.5
90°-180°	3186.0	46.4
0°-180°	6862.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1412	1412	1412	1412	1412	
5°	1413	1406	1393	1405	1403	134
15°	1345	1339	1324	1333	1326	379
25°	1221	1213	1198	1199	1195	562
35°	1056	1048	1033	1026	1020	660
45°	865	860	845	831	824	668
55°	657	655	640	627	620	588
65°	448	441	430	420	416	442
75°	237	232	228	222	218	253
85°	63	61	61	58	58	69
90°	1	10	22	25	27	7
95°	53	60	67	70	70	60
105°	203	205	213	213	215	218
115°	384	386	385	386	385	380
125°	562	564	563	559	556	501
135°	729	734	734	730	728	562
145°	884	886	889	888	884	552
155°	1013	1013	1014	1017	1011	466
165°	1103	1100	1100	1105	1100	311
175°	1147	1144	1144	1148	1143	109
180°	1150	1150	1150	1150	1150	



TEST NUMBER: P332197-940

CATALOG NUMBER: S123DIW-S1000D1030U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5
2.5°	1416.3	1415.5	1414.6	1413.7	1412.9	1411.2	1408.9	1406.5	1404.2	1401.8	1403.9
5°	1412.6	1411.3	1410.0	1408.6	1407.3	1405.2	1402.2	1399.2	1396.2	1393.3	1396.0
7.5°	1398.8	1397.5	1396.2	1394.8	1393.5	1391.2	1388.2	1385.1	1382.1	1378.9	1381.3
10°	1387.2	1385.9	1384.5	1383.1	1381.8	1379.4	1375.9	1372.3	1368.9	1365.4	1367.8
12.5°	1371.6	1370.6	1369.4	1368.2	1367.2	1364.9	1361.6	1358.3	1355.0	1351.7	1353.5
15°	1344.7	1343.6	1342.6	1341.5	1340.4	1338.1	1334.6	1331.1	1327.6	1324.1	1326.2
17.5°	1313.4	1312.0	1310.6	1309.2	1307.8	1305.4	1301.8	1298.3	1294.9	1291.3	1292.8
20°	1290.1	1288.5	1286.9	1285.2	1283.6	1281.0	1277.6	1274.1	1270.6	1267.0	1268.1
22.5°	1263.9	1262.3	1260.7	1259.0	1257.4	1254.9	1251.3	1247.9	1244.4	1240.8	1241.7
25°	1220.9	1219.3	1217.7	1216.1	1214.4	1211.9	1208.4	1204.9	1201.4	1197.8	1198.1
27.5°	1175.1	1173.5	1171.9	1170.4	1168.8	1166.1	1162.3	1158.6	1154.8	1151.0	1151.2
30°	1142.0	1140.7	1139.3	1138.0	1136.7	1134.1	1130.3	1126.5	1122.8	1119.0	1119.0
32.5°	1109.0	1107.2	1105.5	1103.7	1101.9	1099.6	1096.6	1093.8	1090.8	1087.9	1086.4
35°	1055.9	1054.3	1052.7	1051.1	1049.4	1046.9	1043.3	1039.8	1036.3	1032.8	1031.2
37.5°	1001.5	999.4	997.4	995.3	993.3	990.5	986.9	983.4	979.8	976.2	974.3
40°	963.7	962.0	960.4	958.8	957.2	954.5	950.7	946.9	943.2	939.3	937.2
42.5°	925.8	923.9	922.1	920.2	918.5	915.6	911.9	908.1	904.3	900.5	898.4
45°	865.3	864.2	863.2	862.1	861.0	858.7	855.2	851.7	848.2	844.7	841.5
47.5°	805.4	803.8	802.3	800.7	799.2	796.7	793.4	790.1	786.8	783.5	780.3
50°	764.6	763.2	761.9	760.5	759.2	756.8	753.2	749.8	746.3	742.8	739.8
52.5°	721.8	720.9	720.1	719.2	718.2	715.9	712.2	708.5	704.7	701.0	698.5
55°	656.6	656.3	656.0	655.8	655.5	653.6	650.1	646.6	643.1	639.6	636.6
57.5°	594.4	593.5	592.6	591.7	590.8	588.9	586.1	583.3	580.5	577.7	575.1
60°	549.7	549.5	549.2	548.9	548.7	547.0	543.7	540.5	537.3	534.0	531.5
62.5°	510.0	509.3	508.5	507.8	507.2	505.2	501.9	498.7	495.5	492.2	489.8
65°	447.8	446.5	445.1	443.8	442.5	440.4	437.7	435.1	432.3	429.6	427.5
67.5°	382.1	380.8	379.7	378.5	377.3	375.7	373.6	371.6	369.5	367.5	365.6
70°	342.2	340.6	339.0	337.4	335.8	334.1	332.5	330.9	329.3	327.7	325.8
72.5°	300.5	299.3	298.1	296.9	295.8	294.3	292.4	290.6	288.7	286.9	285.3
75°	236.7	235.6	234.5	233.4	232.4	231.4	230.6	229.8	229.0	228.2	226.9
77.5°	180.1	179.5	178.9	178.3	177.7	176.9	176.0	175.0	174.1	173.1	172.2
80°	143.2	142.4	141.6	140.8	140.0	139.3	138.8	138.2	137.7	137.1	136.9
82.5°	107.3	107.1	107.0	106.8	106.6	106.5	106.4	106.3	106.2	106.1	105.6
85°	63.1	62.6	62.1	61.5	61.0	60.7	60.7	60.7	60.7	60.7	60.1
87.5°	25.4	25.1	25.0	24.7	24.4	24.4	24.8	25.1	25.4	25.7	25.7
90°	0.9	2.9	4.9	7.0	8.9	11.2	13.8	16.5	19.1	21.7	22.5
92.5°	21.8	23.2	24.6	25.9	27.3	28.7	30.2	31.7	33.2	34.7	35.3
95°	53.3	54.7	56.1	57.5	58.9	60.5	62.1	63.7	65.3	66.9	67.7
97.5°	94.7	95.7	96.8	97.8	98.9	100.0	101.1	102.3	103.4	104.6	105.6
100°	122.9	124.0	125.3	126.4	127.7	128.8	129.8	130.8	131.8	132.8	133.4
102.5°	155.4	156.1	156.9	157.6	158.3	159.3	160.6	161.9	163.3	164.6	165.2
105°	203.3	203.7	204.1	204.5	204.9	206.0	207.8	209.6	211.4	213.2	213.2
107.5°	259.0	259.1	259.4	259.7	259.8	260.4	261.1	261.8	262.5	263.2	263.9
110°	293.6	294.0	294.4	294.8	295.2	295.6	296.0	296.4	296.9	297.2	298.0



TEST NUMBER: P332197-940

CATALOG NUMBER: S123DIW-S1000D1030U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	329.8	330.0	330.2	330.5	330.7	330.8	330.9	331.0	331.1	331.2	332.2
115°	384.0	384.5	385.1	385.8	386.4	386.5	386.0	385.7	385.2	384.9	385.0
117.5°	438.5	438.9	439.3	439.7	440.1	440.1	439.5	439.0	438.5	438.0	437.9
120°	472.5	473.7	474.9	476.1	477.3	477.4	476.4	475.4	474.4	473.4	473.1
122.5°	507.9	508.8	509.7	510.5	511.4	511.6	511.1	510.6	510.1	509.5	509.0
125°	562.0	562.5	563.1	563.7	564.4	564.5	564.0	563.7	563.2	562.8	562.0
127.5°	611.8	613.1	614.4	615.6	616.9	617.3	616.9	616.4	616.0	615.5	614.5
130°	645.1	646.7	648.3	649.9	651.5	651.9	651.4	650.8	650.1	649.5	648.7
132.5°	678.2	679.8	681.4	683.1	684.7	685.3	684.8	684.4	683.9	683.5	682.5
135°	729.1	730.2	731.5	732.6	733.9	734.3	734.1	734.0	733.8	733.5	732.7
137.5°	776.1	777.0	778.0	779.0	780.1	780.8	781.3	781.9	782.4	782.9	782.0
140°	808.5	809.6	810.6	811.5	812.5	813.2	813.3	813.6	813.8	814.0	813.8
142.5°	838.2	839.2	840.2	841.2	842.2	842.8	843.2	843.6	844.0	844.4	844.1
145°	884.4	884.8	885.2	885.6	886.0	886.5	887.2	887.8	888.3	888.9	888.8
147.5°	924.9	925.6	926.3	927.1	927.8	928.4	929.0	929.6	930.1	930.7	930.7
150°	953.1	953.5	953.9	954.3	954.7	955.1	955.5	955.9	956.3	956.7	956.7
152.5°	976.2	976.8	977.3	977.9	978.5	978.8	979.1	979.4	979.6	979.8	980.2
155°	1012.7	1012.7	1012.7	1012.7	1012.7	1012.8	1013.0	1013.3	1013.4	1013.6	1014.4
157.5°	1043.8	1043.6	1043.3	1043.0	1042.9	1042.8	1042.9	1043.1	1043.3	1043.4	1044.3
160°	1063.3	1062.9	1062.5	1062.1	1061.7	1061.5	1061.5	1061.5	1061.5	1061.5	1062.5
162.5°	1080.7	1080.1	1079.5	1079.0	1078.4	1078.2	1078.3	1078.5	1078.7	1078.9	1079.9
165°	1103.0	1102.4	1101.9	1101.3	1100.6	1100.4	1100.4	1100.4	1100.4	1100.4	1101.5
167.5°	1121.0	1120.2	1119.4	1118.6	1117.8	1117.4	1117.6	1117.8	1117.9	1118.0	1119.3
170°	1131.0	1130.2	1129.4	1128.6	1127.8	1127.5	1127.5	1127.5	1127.5	1127.5	1128.8
172.5°	1139.0	1138.2	1137.4	1136.6	1135.8	1135.4	1135.4	1135.4	1135.4	1135.4	1136.7
175°	1147.4	1146.6	1145.8	1145.0	1144.2	1143.7	1143.7	1143.7	1143.7	1143.7	1145.0
177.5°	1150.8	1150.1	1149.5	1148.8	1148.2	1147.9	1147.9	1147.9	1147.9	1147.9	1148.8
180°	1150.0	1150.0	1150.0	1150.0	1150.0	1150.0	1150.0	1150.0	1150.0	1150.0	1150.0



TEST NUMBER: P332197-940

CATALOG NUMBER: S123DIW-S1000D1030U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5
2.5°	1406.0	1408.3	1410.4	1411.4	1411.1	1411.0	1410.7	1410.5
5°	1398.6	1401.3	1404.1	1405.2	1404.6	1404.1	1403.6	1403.0
7.5°	1383.8	1386.3	1388.7	1389.7	1389.4	1389.1	1388.8	1388.4
10°	1370.2	1372.6	1375.1	1376.0	1375.5	1374.9	1374.4	1373.9
12.5°	1355.3	1357.1	1358.9	1359.6	1359.3	1359.0	1358.6	1358.3
15°	1328.4	1330.5	1332.8	1333.0	1331.4	1329.7	1328.1	1326.5
17.5°	1294.3	1295.8	1297.4	1297.8	1297.3	1296.6	1296.0	1295.5
20°	1269.2	1270.3	1271.4	1271.5	1270.7	1269.9	1269.1	1268.3
22.5°	1242.6	1243.4	1244.3	1244.2	1243.2	1242.2	1241.2	1240.1
25°	1198.4	1198.7	1199.0	1198.7	1197.8	1197.0	1196.2	1195.4
27.5°	1151.5	1151.6	1151.9	1151.5	1150.5	1149.4	1148.4	1147.4
30°	1119.0	1119.0	1119.0	1118.0	1116.2	1114.3	1112.4	1110.4
32.5°	1084.9	1083.4	1081.9	1080.6	1079.6	1078.5	1077.5	1076.5
35°	1029.6	1028.0	1026.4	1024.8	1023.5	1022.2	1020.8	1019.5
37.5°	972.4	970.4	968.5	967.1	966.3	965.4	964.5	963.7
40°	935.0	932.9	930.8	929.1	928.0	926.9	925.9	924.8
42.5°	896.2	894.0	891.9	890.3	889.2	888.1	887.1	886.0
45°	838.2	835.0	831.8	829.5	828.1	826.8	825.5	824.0
47.5°	777.1	774.0	770.8	768.7	767.4	766.2	765.1	763.8
50°	736.8	733.9	730.8	728.6	727.0	725.3	723.7	722.1
52.5°	695.9	693.4	690.9	688.8	687.2	685.5	683.9	682.3
55°	633.6	630.7	627.8	625.5	624.2	622.9	621.5	620.2
57.5°	572.4	569.8	567.1	565.0	563.5	561.9	560.4	558.7
60°	529.1	526.7	524.3	522.5	521.0	519.7	518.4	517.0
62.5°	487.4	485.0	482.5	480.9	479.9	479.0	478.1	477.2
65°	425.3	423.1	421.0	419.5	418.7	417.9	417.1	416.3
67.5°	363.7	361.9	360.0	358.5	357.3	356.1	355.0	353.9
70°	323.9	322.0	320.1	318.5	317.2	315.8	314.5	313.1
72.5°	283.6	281.9	280.2	279.0	278.3	277.6	277.0	276.3
75°	225.5	224.1	222.7	221.7	220.9	220.1	219.3	218.5
77.5°	171.2	170.3	169.4	169.0	169.0	169.0	169.0	169.0
80°	136.6	136.3	136.1	135.9	135.9	135.9	135.9	135.9
82.5°	105.1	104.6	104.2	103.8	103.5	103.3	103.2	102.9
85°	59.6	59.0	58.5	58.2	58.2	58.2	58.2	58.2
87.5°	25.6	25.5	25.5	25.5	25.6	25.7	25.8	25.8
90°	23.3	24.1	24.9	25.5	25.9	26.3	26.7	27.1
92.5°	35.9	36.6	37.3	37.5	37.2	37.0	36.7	36.5
95°	68.5	69.3	70.1	70.4	70.4	70.4	70.4	70.4
97.5°	106.5	107.4	108.3	108.7	108.6	108.6	108.5	108.4
100°	134.0	134.6	135.2	135.7	136.1	136.5	136.9	137.3
102.5°	165.8	166.4	167.0	167.3	167.2	167.1	167.0	166.9
105°	213.2	213.2	213.2	213.4	213.8	214.2	214.6	215.0
107.5°	264.6	265.2	265.8	266.0	265.8	265.6	265.3	265.0
110°	298.8	299.6	300.4	300.6	300.2	299.8	299.4	299.0



TEST NUMBER: P332197-940

CATALOG NUMBER: S123DIW-S1000D1030U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	333.1	334.0	335.0	335.5	335.4	335.3	335.3	335.2
115°	385.2	385.5	385.7	385.7	385.5	385.2	385.0	384.9
117.5°	437.9	437.8	437.8	437.5	436.9	436.4	435.8	435.2
120°	473.0	472.8	472.6	472.3	471.9	471.4	471.1	470.6
122.5°	508.5	507.9	507.5	506.8	506.3	505.8	505.2	504.6
125°	561.2	560.4	559.6	558.8	558.0	557.2	556.4	555.6
127.5°	613.3	612.2	611.1	610.0	609.1	608.2	607.3	606.4
130°	647.9	647.1	646.3	645.2	643.8	642.4	641.1	639.6
132.5°	681.6	680.6	679.7	678.7	677.5	676.5	675.4	674.3
135°	731.9	731.1	730.3	729.8	729.3	729.0	728.5	728.2
137.5°	781.2	780.3	779.5	778.7	777.9	777.2	776.4	775.7
140°	813.6	813.3	813.2	812.3	810.9	809.6	808.2	806.7
142.5°	843.9	843.7	843.6	842.8	841.8	840.7	839.6	838.6
145°	888.6	888.3	888.1	887.6	886.8	886.0	885.2	884.4
147.5°	930.7	930.7	930.7	930.1	928.9	927.6	926.5	925.2
150°	956.7	956.7	956.7	956.1	954.9	953.7	952.5	951.3
152.5°	980.4	980.8	981.1	980.8	979.7	978.7	977.6	976.6
155°	1015.2	1016.0	1016.8	1016.6	1015.1	1013.7	1012.4	1010.9
157.5°	1045.1	1046.0	1046.8	1046.7	1045.5	1044.5	1043.3	1042.1
160°	1063.5	1064.5	1065.5	1065.6	1064.8	1064.0	1063.2	1062.4
162.5°	1080.8	1081.8	1082.9	1082.7	1081.5	1080.1	1078.9	1077.5
165°	1102.8	1103.9	1105.2	1105.1	1103.7	1102.2	1100.8	1099.5
167.5°	1120.5	1121.8	1123.0	1123.0	1121.8	1120.5	1119.3	1118.0
170°	1130.2	1131.7	1133.1	1133.1	1131.7	1130.2	1128.8	1127.5
172.5°	1137.9	1139.2	1140.4	1140.3	1138.9	1137.5	1136.0	1134.7
175°	1146.1	1147.4	1148.5	1148.4	1147.0	1145.6	1144.2	1142.8
177.5°	1149.8	1150.8	1151.7	1151.6	1150.5	1149.4	1148.3	1147.2
180°	1150.0	1150.0	1150.0	1150.0	1150.0	1150.0	1150.0	1150.0

(END OF REPORT)