

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332822-830

Luminaire Tested: **S124DIW-S1020D1050U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332822-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S1020D1050U830-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1050 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7602.5 lumens
Efficiency: N/A
Efficacy: 124.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 61.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332822-830

CATALOG NUMBER: S124DIW-S1020D1050U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332822-830

CATALOG NUMBER: S124DIW-S1020D1050U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61
1	99	94	91	87	92	88	84	81	75	73	71	64	62	61	54	52	51
2	90	82	76	71	83	77	71	67	66	62	58	56	53	51	47	45	43
3	82	73	65	59	76	68	61	56	58	53	49	50	46	43	42	39	37
4	75	64	56	50	69	60	53	47	52	46	42	44	40	37	37	34	32
5	69	57	49	43	64	53	46	41	46	41	36	40	35	32	34	30	28
6	64	51	43	37	59	48	41	35	42	36	32	36	31	28	31	27	24
7	59	46	38	33	54	43	36	31	38	32	28	33	28	25	28	24	22
8	55	42	34	29	51	40	32	28	35	29	25	30	25	22	26	22	19
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	17
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13130	13130	13130
5°	13169	13011	13105
10°	13086	12904	12969
15°	12929	12721	12754
20°	12718	12494	12506
25°	12479	12235	12200
30°	12185	11929	11820
35°	11880	11610	11456
40°	11564	11248	11041
45°	11233	10891	10683
50°	10868	10574	10246
55°	10473	10162	9831
60°	10078	9700	9405
65°	9635	9259	8886
70°	9135	8674	8337
75°	8372	7966	7764
80°	7452	7146	6969
85°	6521	6280	6150



TEST NUMBER: P332822-830

CATALOG NUMBER: S124DIW-S1020D1050U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.2	2.0
10°-20°	431.5	5.7
20°-30°	635.2	8.4
30°-40°	738.4	9.7
40°-50°	738.4	9.7
50°-60°	645.9	8.5
60°-70°	479.7	6.3
70°-80°	272.5	3.6
80°-90°	82.3	1.1
90°-100°	81.4	1.1
100°-110°	241.2	3.2
110°-120°	409.4	5.4
120°-130°	539.9	7.1
130°-140°	606.3	8.0
140°-150°	595.8	7.8
150°-160°	501.1	6.6
160°-170°	333.4	4.4
170°-180°	116.7	1.5
0°-30°	1219.8	16.0
0°-40°	1958.2	25.8
0°-60°	3342.6	44.0
0°-90°	4177.1	54.9
90°-120°	732.1	9.6
90°-150°	2474.1	32.5
90°-180°	3425.0	45.1
0°-180°	7602.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1626	1626	1626	1626	1626	
5°	1625	1619	1606	1619	1617	154
15°	1547	1541	1522	1529	1526	436
25°	1401	1391	1374	1374	1370	644
35°	1205	1196	1178	1169	1162	753
45°	984	974	954	940	936	758
55°	744	739	722	707	698	666
65°	504	497	485	472	465	499
75°	268	262	255	250	249	285
85°	70	70	68	68	66	77
90°	3	13	21	27	29	7
95°	57	66	73	75	75	64
105°	222	224	227	230	233	236
115°	416	416	414	413	412	410
125°	606	606	605	603	602	540
135°	782	787	788	786	783	605
145°	950	954	955	954	951	594
155°	1088	1088	1088	1091	1088	501
165°	1185	1182	1180	1185	1182	334
175°	1233	1228	1227	1233	1227	117
180°	1235	1235	1235	1235	1235	



TEST NUMBER: P332822-830

CATALOG NUMBER: S124DIW-S1020D1050U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4
2.5°	1630.5	1629.8	1629.1	1628.4	1627.8	1626.1	1623.5	1621.0	1618.4	1615.9	1618.3
5°	1625.0	1623.9	1622.8	1621.6	1620.4	1618.3	1615.0	1611.8	1608.7	1605.5	1608.7
7.5°	1610.0	1608.7	1607.6	1606.5	1605.3	1603.0	1599.4	1595.9	1592.3	1588.8	1591.4
10°	1596.4	1595.3	1594.0	1592.9	1591.8	1589.3	1585.5	1581.8	1578.0	1574.2	1576.5
12.5°	1578.7	1577.5	1576.3	1575.2	1574.0	1571.4	1567.4	1563.5	1559.4	1555.5	1558.0
15°	1546.9	1545.7	1544.5	1543.4	1542.2	1539.5	1535.1	1530.8	1526.4	1522.1	1523.8
17.5°	1508.5	1507.1	1505.6	1504.2	1502.8	1500.0	1495.8	1491.8	1487.6	1483.6	1484.6
20°	1480.4	1478.9	1477.5	1476.0	1474.6	1471.7	1467.4	1463.0	1458.7	1454.3	1455.2
22.5°	1450.2	1448.2	1446.3	1444.4	1442.6	1439.4	1435.0	1430.7	1426.3	1422.0	1423.6
25°	1400.9	1398.9	1396.8	1394.8	1392.8	1389.8	1385.7	1381.7	1377.6	1373.6	1373.9
27.5°	1344.6	1342.6	1340.4	1338.3	1336.2	1333.3	1329.6	1325.8	1322.0	1318.2	1317.6
30°	1307.1	1304.8	1302.4	1300.1	1297.8	1294.8	1291.0	1287.2	1283.5	1279.7	1278.6
32.5°	1267.4	1265.4	1263.3	1261.2	1259.1	1256.0	1252.1	1248.1	1244.1	1240.1	1238.7
35°	1205.4	1203.4	1201.4	1199.4	1197.3	1194.3	1190.2	1186.2	1182.1	1178.1	1176.0
37.5°	1140.0	1138.1	1136.3	1134.4	1132.6	1129.5	1125.1	1120.8	1116.4	1112.1	1109.9
40°	1097.3	1095.0	1092.6	1090.3	1088.0	1084.7	1080.3	1076.0	1071.7	1067.3	1064.4
42.5°	1051.4	1050.0	1048.6	1047.3	1045.8	1042.7	1037.9	1033.1	1028.3	1023.5	1020.1
45°	983.9	981.8	979.9	977.8	975.8	972.4	967.8	963.2	958.6	953.9	950.7
47.5°	913.2	911.9	910.5	909.1	907.7	904.8	900.6	896.3	892.0	887.7	884.1
50°	865.3	864.1	863.0	861.9	860.6	858.1	854.0	850.0	845.9	841.9	837.8
52.5°	818.4	817.0	815.6	814.3	812.8	810.0	805.7	801.4	797.1	792.9	789.3
55°	744.1	743.2	742.3	741.5	740.6	738.2	734.1	730.1	726.0	722.0	718.5
57.5°	673.3	672.2	671.3	670.2	669.3	666.8	662.8	658.8	654.8	650.8	647.5
60°	624.2	622.7	621.3	619.9	618.4	615.9	612.1	608.3	604.5	600.8	598.1
62.5°	576.3	575.0	573.8	572.6	571.4	568.8	564.8	560.8	556.8	552.8	550.4
65°	504.4	502.8	501.4	500.0	498.5	496.3	493.4	490.6	487.7	484.7	481.9
67.5°	431.9	430.6	429.2	427.9	426.5	424.5	421.7	419.0	416.1	413.4	410.6
70°	387.0	385.0	383.0	381.0	378.9	376.7	374.5	372.1	369.9	367.5	365.1
72.5°	339.1	337.1	335.1	333.0	331.0	329.0	327.2	325.4	323.5	321.6	319.8
75°	268.4	267.0	265.5	264.1	262.7	261.2	259.8	258.4	256.8	255.4	254.3
77.5°	201.0	200.3	199.6	199.1	198.4	197.5	196.1	194.9	193.6	192.4	192.0
80°	160.3	159.4	158.5	157.7	156.8	156.1	155.5	155.0	154.4	153.7	153.2
82.5°	120.6	120.3	119.9	119.4	119.0	118.8	118.7	118.6	118.5	118.3	118.0
85°	70.4	70.4	70.4	70.4	70.4	70.1	69.5	68.9	68.3	67.8	67.8
87.5°	27.7	27.9	28.2	28.4	28.7	28.7	28.9	29.0	29.1	29.2	29.5
90°	2.8	5.2	7.5	9.9	12.2	14.2	15.9	17.6	19.3	21.0	22.2
92.5°	20.5	23.1	25.8	28.5	31.1	33.1	34.2	35.4	36.7	37.8	38.5
95°	57.3	59.2	61.1	63.1	64.9	66.6	68.1	69.6	71.1	72.6	73.2
97.5°	100.1	101.6	103.1	104.6	106.2	107.8	109.5	111.3	113.0	114.8	115.6
100°	133.7	134.5	135.3	136.2	137.0	138.5	140.3	142.2	144.2	146.1	146.5
102.5°	168.8	169.2	169.5	169.8	170.1	171.2	173.0	174.7	176.4	178.1	178.8
105°	222.4	222.7	222.9	223.1	223.3	223.9	224.7	225.6	226.4	227.2	227.9
107.5°	278.8	279.1	279.3	279.6	279.8	280.0	280.1	280.3	280.4	280.5	281.2
110°	317.0	317.4	317.8	318.3	318.7	318.8	318.8	318.4	318.2	317.9	317.5



TEST NUMBER: P332822-830

CATALOG NUMBER: S124DIW-S1020D1050U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	356.8	356.8	356.9	356.9	357.0	356.9	356.6	356.2	355.8	355.4	355.3
115°	416.3	416.3	416.3	416.3	416.3	416.1	415.7	415.3	414.8	414.4	414.2
117.5°	472.5	472.6	472.8	473.0	473.2	473.1	472.8	472.5	472.2	471.8	471.2
120°	509.9	510.8	511.6	512.5	513.3	513.4	512.7	512.1	511.5	510.9	509.8
122.5°	548.8	549.2	549.5	549.9	550.2	550.3	549.9	549.6	549.3	549.0	548.3
125°	606.3	606.3	606.3	606.3	606.3	606.2	606.0	605.8	605.6	605.4	604.9
127.5°	658.5	659.1	659.7	660.3	661.0	661.2	660.8	660.4	660.2	659.8	659.4
130°	695.1	695.8	696.4	697.0	697.7	698.0	698.0	698.0	698.0	698.0	697.6
132.5°	732.5	733.0	733.5	734.0	734.4	734.5	734.4	734.2	734.1	733.9	733.5
135°	782.0	783.3	784.6	785.8	787.1	787.8	787.8	787.8	787.8	787.8	787.3
137.5°	835.8	836.4	837.1	837.6	838.2	838.7	839.1	839.4	839.7	840.1	839.5
140°	871.8	872.2	872.6	873.1	873.5	873.6	873.6	873.6	873.6	873.6	873.5
142.5°	904.7	905.0	905.5	905.9	906.3	906.4	906.3	906.1	906.0	905.8	905.7
145°	950.1	950.9	951.8	952.6	953.5	953.9	954.2	954.4	954.6	954.8	954.6
147.5°	995.1	996.2	997.2	998.2	999.2	999.7	999.5	999.3	999.1	998.9	998.8
150°	1022.7	1023.5	1024.4	1025.2	1026.1	1026.4	1026.4	1026.4	1026.4	1026.4	1026.4
152.5°	1048.6	1049.1	1049.6	1050.1	1050.7	1050.9	1051.1	1051.3	1051.5	1051.7	1052.2
155°	1088.5	1088.5	1088.5	1088.5	1088.5	1088.4	1088.2	1088.0	1087.8	1087.6	1088.4
157.5°	1122.1	1121.7	1121.3	1121.0	1120.6	1120.4	1120.3	1120.3	1120.2	1120.2	1120.9
160°	1142.0	1141.8	1141.5	1141.3	1141.1	1140.9	1140.7	1140.5	1140.3	1140.1	1140.7
162.5°	1160.3	1159.8	1159.2	1158.7	1158.1	1157.7	1157.5	1157.3	1157.1	1156.9	1158.0
165°	1185.0	1184.3	1183.6	1183.1	1182.4	1181.9	1181.5	1181.0	1180.6	1180.2	1181.5
167.5°	1203.8	1203.0	1202.1	1201.2	1200.3	1199.9	1200.0	1200.0	1200.0	1200.0	1201.3
170°	1214.6	1213.5	1212.4	1211.4	1210.3	1209.8	1210.1	1210.3	1210.5	1210.7	1212.0
172.5°	1222.2	1221.3	1220.4	1219.6	1218.6	1218.2	1218.2	1218.3	1218.3	1218.3	1219.8
175°	1232.7	1231.6	1230.6	1229.5	1228.4	1227.9	1227.6	1227.4	1227.2	1227.0	1228.4
177.5°	1236.1	1235.3	1234.4	1233.6	1232.8	1232.3	1232.3	1232.3	1232.3	1232.3	1233.5
180°	1234.6	1234.6	1234.6	1234.6	1234.6	1234.6	1234.6	1234.6	1234.6	1234.6	1234.6



TEST NUMBER: P332822-830

CATALOG NUMBER: S124DIW-S1020D1050U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4
2.5°	1620.5	1622.9	1625.2	1626.3	1626.0	1625.8	1625.5	1625.3
5°	1611.8	1615.0	1618.3	1619.6	1619.0	1618.3	1617.8	1617.2
7.5°	1593.9	1596.5	1599.0	1600.2	1599.8	1599.4	1599.0	1598.7
10°	1578.9	1581.2	1583.5	1584.3	1583.8	1583.2	1582.6	1582.1
12.5°	1560.6	1563.1	1565.7	1566.5	1565.8	1564.9	1564.1	1563.3
15°	1525.6	1527.3	1529.1	1529.5	1528.6	1527.8	1526.9	1526.0
17.5°	1485.7	1486.9	1487.9	1488.2	1487.6	1487.0	1486.5	1485.8
20°	1456.0	1457.0	1457.8	1457.9	1457.4	1456.8	1456.2	1455.7
22.5°	1425.1	1426.7	1428.2	1428.5	1427.5	1426.4	1425.4	1424.4
25°	1374.1	1374.4	1374.7	1374.2	1373.1	1372.0	1370.7	1369.6
27.5°	1316.9	1316.2	1315.5	1314.5	1313.0	1311.5	1310.0	1308.6
30°	1277.4	1276.2	1275.1	1273.8	1272.3	1270.8	1269.4	1268.0
32.5°	1237.3	1236.0	1234.5	1233.1	1231.6	1230.2	1228.8	1227.3
35°	1174.0	1172.0	1170.0	1168.2	1166.8	1165.4	1163.9	1162.4
37.5°	1107.7	1105.5	1103.3	1101.3	1099.4	1097.4	1095.5	1093.6
40°	1061.5	1058.6	1055.7	1053.6	1052.1	1050.7	1049.2	1047.7
42.5°	1016.8	1013.4	1010.0	1007.9	1006.9	1005.9	1004.9	1004.0
45°	947.5	944.3	941.1	939.1	938.3	937.5	936.5	935.7
47.5°	880.5	876.9	873.4	870.4	868.3	866.0	863.8	861.7
50°	833.8	829.7	825.7	822.7	821.0	819.3	817.6	815.8
52.5°	785.7	782.0	778.4	775.6	773.4	771.2	769.0	766.8
55°	715.0	711.5	708.0	705.5	703.7	702.0	700.2	698.5
57.5°	644.2	640.9	637.6	635.1	633.4	631.8	630.1	628.4
60°	595.6	593.0	590.3	588.3	586.8	585.4	584.0	582.5
62.5°	548.1	545.6	543.3	541.4	540.0	538.5	537.1	535.6
65°	479.0	476.1	473.2	471.0	469.6	468.2	466.7	465.2
67.5°	407.8	405.0	402.3	400.7	400.2	399.8	399.4	399.1
70°	362.9	360.5	358.3	356.7	355.8	354.9	354.0	353.2
72.5°	317.9	316.0	314.2	312.8	312.0	311.1	310.3	309.3
75°	253.1	251.9	250.8	250.1	249.8	249.5	249.2	248.9
77.5°	191.6	191.3	191.0	190.4	189.6	188.9	188.1	187.4
80°	152.6	152.0	151.5	151.0	150.7	150.4	150.1	149.9
82.5°	117.6	117.3	117.0	116.6	116.3	116.0	115.7	115.5
85°	67.8	67.8	67.8	67.6	67.3	67.0	66.7	66.4
87.5°	29.7	30.0	30.3	30.4	30.5	30.5	30.6	30.7
90°	23.6	24.8	26.1	27.0	27.3	27.8	28.2	28.7
92.5°	39.3	40.1	40.9	41.4	41.7	41.8	42.1	42.4
95°	73.8	74.5	75.1	75.4	75.4	75.4	75.4	75.4
97.5°	116.3	117.1	117.8	118.2	118.2	118.2	118.2	118.2
100°	146.9	147.3	147.8	148.0	148.0	148.0	148.0	148.0
102.5°	179.4	179.9	180.6	181.0	181.1	181.3	181.4	181.6
105°	228.6	229.1	229.8	230.5	231.1	231.7	232.3	233.0
107.5°	281.7	282.3	283.0	283.1	283.1	283.1	283.0	283.0
110°	317.1	316.7	316.2	316.4	317.0	317.6	318.3	319.0



TEST NUMBER: P332822-830

CATALOG NUMBER: S124DIW-S1020D1050U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	355.2	355.2	355.1	355.1	355.2	355.3	355.4	355.6
115°	414.0	413.8	413.6	413.3	413.1	412.9	412.7	412.5
117.5°	470.4	469.7	469.0	468.4	468.0	467.6	467.1	466.7
120°	508.7	507.7	506.6	506.2	506.7	507.1	507.6	507.9
122.5°	547.6	546.9	546.1	545.4	544.6	543.8	543.1	542.3
125°	604.5	604.1	603.7	603.2	602.9	602.4	602.0	601.5
127.5°	658.9	658.6	658.1	657.7	657.3	657.0	656.7	656.4
130°	697.1	696.7	696.3	695.7	694.8	694.0	693.1	692.3
132.5°	733.0	732.6	732.2	731.8	731.5	731.1	730.8	730.5
135°	786.9	786.5	786.1	785.5	784.9	784.2	783.6	783.0
137.5°	839.0	838.4	837.8	837.6	837.7	837.9	838.0	838.1
140°	873.3	873.1	872.8	872.6	872.4	872.2	871.9	871.8
142.5°	905.7	905.6	905.6	905.5	905.5	905.5	905.4	905.4
145°	954.4	954.2	953.9	953.6	952.9	952.3	951.7	951.0
147.5°	998.6	998.4	998.2	998.1	997.9	997.7	997.4	997.2
150°	1026.4	1026.4	1026.4	1026.3	1026.1	1026.0	1025.7	1025.5
152.5°	1052.6	1053.2	1053.7	1053.7	1053.1	1052.5	1052.0	1051.5
155°	1089.3	1090.1	1091.0	1091.0	1090.1	1089.3	1088.4	1087.6
157.5°	1121.5	1122.1	1122.8	1122.8	1122.0	1121.2	1120.6	1119.8
160°	1141.3	1142.0	1142.6	1142.4	1141.3	1140.3	1139.3	1138.1
162.5°	1159.1	1160.3	1161.5	1161.5	1160.5	1159.4	1158.3	1157.3
165°	1182.7	1184.0	1185.2	1185.4	1184.6	1183.7	1182.9	1182.0
167.5°	1202.6	1203.8	1205.1	1205.1	1203.8	1202.5	1201.2	1199.9
170°	1213.2	1214.6	1215.8	1215.7	1214.3	1212.8	1211.3	1209.8
172.5°	1221.3	1222.7	1224.2	1224.1	1222.7	1221.2	1219.7	1218.1
175°	1229.9	1231.4	1232.9	1232.9	1231.4	1229.9	1228.4	1227.0
177.5°	1234.7	1235.9	1237.1	1237.0	1235.6	1234.3	1232.9	1231.5
180°	1234.6	1234.6	1234.6	1234.6	1234.6	1234.6	1234.6	1234.6

(END OF REPORT)