

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332199-940

Luminaire Tested: **S123DIW-S1000D1320U940-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332199-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S1000D1320U940-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1320 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7863.6 lumens
Efficiency: N/A
Efficacy: 112.7 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 69.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332199-940

CATALOG NUMBER: S123DIW-S1000D1320U940-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332199-940

CATALOG NUMBER: S123DIW-S1000D1320U940-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54	48	48	48	48	
1	98	93	90	86	90	86	83	80	73	70	68	60	58	57	48	47	46	41	41	41	41	
2	89	82	76	71	82	76	70	66	64	60	57	53	50	48	43	41	39	35	35	35	35	
3	81	72	65	59	75	67	60	55	56	52	48	47	44	41	38	36	34	30	30	30	30	
4	75	64	56	50	68	59	52	47	50	45	41	42	38	35	34	32	29	26	26	26	26	
5	68	57	49	43	63	53	46	41	45	40	35	38	34	31	31	28	26	22	22	22	22	
6	63	51	43	37	58	48	40	35	41	35	31	34	30	27	28	25	23	20	20	20	20	
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	26	23	20	18	18	18	18	
8	54	42	34	29	50	39	32	27	34	28	24	28	24	21	24	20	18	16	16	16	16	
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	19	16	14	14	14	14	
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15	13	13	13	13	

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13481	13481	13481	13481
5°	16077	13539	11998	13539
10°	20122	13470	10837	13470
15°	24681	13362	10089	13362
20°	29402	13192	9606	13192
25°	31220	12986	9499	12986
30°	26759	12837	9548	12837
35°	18611	12623	9648	12623
40°	14018	12372	9618	12372
45°	11639	12000	9496	12000
50°	10426	11238	9409	11238
55°	9747	10419	9293	10419
60°	9143	9563	9197	9563
65°	8593	8716	8904	8716
70°	8060	7755	8478	7755
75°	7216	6791	7773	6791
80°	6316	5566	6695	5566
85°	4940	4039	4495	4039



TEST NUMBER: P332199-940

CATALOG NUMBER: S123DIW-S1000D1320U940-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	123.4	1.6
10°-20°	395.6	5.0
20°-30°	664.0	8.4
30°-40°	751.8	9.6
40°-50°	674.2	8.6
50°-60°	544.1	6.9
60°-70°	379.1	4.8
70°-80°	199.3	2.5
80°-90°	53.1	0.7
90°-100°	95.9	1.2
100°-110°	287.1	3.7
110°-120°	488.2	6.2
120°-130°	642.2	8.2
130°-140°	721.9	9.2
140°-150°	709.6	9.0
150°-160°	597.3	7.6
160°-170°	397.6	5.1
170°-180°	139.2	1.8
0°-30°	1182.9	15.0
0°-40°	1934.7	24.6
0°-60°	3153.0	40.1
0°-90°	3784.5	48.1
90°-120°	871.3	11.1
90°-150°	2944.9	37.4
90°-180°	4079.0	51.9
0°-180°	7863.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1252	1252	1252	1252	1252	
5°	1488	1253	1110	1253	1488	154
15°	2215	1199	905	1199	2215	639
25°	2629	1093	800	1093	2629	1153
35°	1416	961	734	961	1416	920
45°	765	788	624	788	765	605
55°	519	555	495	555	519	466
65°	337	342	350	342	337	336
75°	174	163	187	163	174	186
85°	40	33	36	33	40	48
90°	35	1	35	1	35	19
95°	90	68	90	68	90	93
105°	275	260	275	260	275	292
115°	493	492	493	492	493	488
125°	711	719	711	719	711	636
135°	932	933	932	933	932	717
145°	1132	1132	1132	1132	1132	707
155°	1294	1296	1294	1296	1294	596
165°	1408	1412	1408	1412	1408	397
175°	1463	1469	1463	1469	1463	139
180°	1472	1472	1472	1472	1472	



TEST NUMBER: P332199-940

CATALOG NUMBER: S123DIW-S1000D1320U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4
2.5°	1329.1	1328.2	1325.7	1327.7	1323.8	1318.5	1317.9	1313.1	1299.0	1298.1	1294.2
5°	1487.9	1483.0	1482.4	1481.8	1473.3	1461.8	1439.9	1438.2	1409.0	1394.5	1376.8
7.5°	1693.4	1696.0	1687.1	1679.4	1653.4	1636.3	1612.8	1582.9	1547.1	1510.8	1486.7
10°	1841.0	1861.1	1836.2	1819.2	1803.4	1773.7	1739.1	1696.0	1653.0	1602.6	1564.3
12.5°	1999.3	2009.1	2004.1	1988.2	1963.6	1918.3	1857.1	1809.6	1770.0	1686.0	1652.2
15°	2214.8	2251.8	2228.2	2173.5	2174.8	2131.7	2051.6	1963.6	1916.9	1843.4	1743.4
17.5°	2444.4	2449.1	2439.0	2393.4	2363.1	2303.9	2230.0	2145.6	2051.0	1962.1	1856.0
20°	2566.8	2563.1	2541.9	2518.2	2466.0	2419.9	2339.2	2245.1	2123.8	2036.4	1920.6
22.5°	2634.7	2628.7	2618.6	2598.8	2555.4	2505.9	2433.4	2330.6	2215.1	2094.7	1960.8
25°	2628.7	2636.5	2637.8	2632.3	2617.2	2587.4	2530.3	2448.5	2333.2	2178.4	2038.9
27.5°	2390.8	2402.0	2434.4	2463.2	2495.3	2528.1	2523.7	2483.1	2397.7	2264.1	2093.5
30°	2152.9	2128.7	2188.7	2264.6	2316.1	2407.2	2458.2	2461.2	2413.2	2298.6	2132.3
32.5°	1822.8	1849.5	1876.1	1969.4	2082.1	2184.3	2285.8	2367.5	2376.9	2300.5	2155.1
35°	1416.3	1449.7	1498.2	1546.8	1668.1	1772.5	1950.9	2106.2	2230.0	2246.4	2157.1
37.5°	1141.3	1157.8	1188.5	1237.2	1316.5	1440.3	1578.3	1774.7	1954.0	2087.4	2093.2
40°	997.6	1002.5	1037.1	1074.1	1138.4	1240.3	1364.7	1538.2	1753.0	1939.4	2017.0
42.5°	889.8	900.4	915.2	950.7	1001.9	1078.6	1194.3	1337.7	1534.6	1749.0	1900.9
45°	764.6	776.7	785.8	809.5	845.9	897.4	978.2	1109.2	1259.1	1480.6	1685.1
47.5°	681.8	682.8	689.6	707.4	732.2	770.9	828.0	912.1	1049.7	1229.4	1439.3
50°	622.6	632.3	634.7	648.6	668.1	696.6	744.0	815.6	928.4	1086.2	1279.2
52.5°	580.9	583.7	590.6	600.7	617.6	639.8	680.8	736.9	825.5	959.9	1137.4
55°	519.4	519.4	526.1	534.0	543.7	563.7	591.0	632.3	699.6	804.1	950.8
57.5°	462.6	465.7	470.4	472.8	481.1	494.3	517.1	548.4	598.7	679.0	795.8
60°	424.7	430.3	429.6	434.4	441.8	452.1	471.4	497.0	541.9	606.2	704.5
62.5°	391.7	391.4	391.3	397.1	404.4	414.2	426.9	448.9	487.1	544.0	627.8
65°	337.4	336.2	340.5	344.0	346.5	353.7	363.5	382.9	408.4	450.8	515.8
67.5°	289.1	285.5	287.8	289.1	293.2	298.9	308.0	320.0	340.3	374.4	423.3
70°	256.1	253.1	252.4	253.6	257.3	261.5	268.2	279.7	298.5	325.8	361.7
72.5°	222.1	220.0	219.9	222.6	224.3	227.0	231.8	242.4	257.3	277.8	311.2
75°	173.5	173.5	173.5	174.2	175.9	178.4	182.0	187.5	199.0	213.6	236.0
77.5°	130.1	130.0	129.2	129.1	131.8	132.9	133.8	138.8	145.3	155.1	171.5
80°	101.9	98.9	100.1	101.9	103.2	103.8	105.6	106.8	112.3	117.7	129.2
82.5°	75.7	73.2	73.4	76.2	76.4	77.0	78.9	80.6	82.7	87.7	93.8
85°	40.0	40.0	40.7	40.7	41.3	40.7	42.4	43.1	43.1	46.1	49.8
87.5°	21.5	20.4	20.8	21.2	20.6	21.0	21.2	21.5	21.8	22.0	21.8
90°	34.7	34.2	33.7	33.2	32.6	31.8	30.9	29.8	28.8	27.7	24.4
92.5°	46.7	47.0	47.3	47.6	48.0	47.7	46.9	46.0	45.2	44.4	42.5
95°	90.2	90.2	90.2	90.2	90.2	89.7	88.6	87.7	86.6	85.6	83.6
97.5°	138.8	138.9	139.0	139.1	139.2	138.7	137.5	136.3	135.1	133.9	132.4
100°	175.8	175.3	174.8	174.2	173.7	173.1	172.3	171.6	170.8	170.0	168.7
102.5°	213.7	213.8	213.9	214.0	214.1	213.8	213.0	212.2	211.5	210.7	209.0
105°	275.3	274.7	274.2	273.8	273.2	273.0	273.0	273.0	273.0	273.0	270.6
107.5°	339.3	339.7	339.9	340.3	340.5	340.3	339.5	338.7	337.9	337.0	336.1
110°	382.8	383.3	383.9	384.3	384.9	384.6	383.6	382.5	381.6	380.5	380.0



TEST NUMBER: P332199-940

CATALOG NUMBER: S123DIW-S1000D1320U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	429.1	429.2	429.3	429.4	429.4	428.9	427.7	426.4	425.3	424.0	423.9
115°	492.7	492.9	493.2	493.5	493.7	493.7	493.5	493.2	492.9	492.7	493.2
117.5°	557.2	557.9	558.7	559.4	560.1	560.4	560.5	560.6	560.6	560.7	561.3
120°	602.5	603.1	603.6	604.1	604.6	605.0	605.3	605.5	605.7	606.0	607.3
122.5°	646.0	646.8	647.5	648.2	648.9	649.6	650.2	650.9	651.6	652.3	652.9
125°	711.2	712.3	713.3	714.3	715.4	716.4	717.5	718.5	719.5	720.5	721.0
127.5°	776.2	777.5	778.6	779.8	781.0	782.3	783.7	785.2	786.6	788.1	788.6
130°	818.9	820.6	822.4	824.2	826.0	827.4	828.5	829.5	830.5	831.5	832.3
132.5°	863.3	864.6	866.0	867.4	868.8	870.1	871.3	872.5	873.8	875.0	875.6
135°	932.2	932.6	933.2	933.7	934.2	935.0	936.0	937.0	938.1	939.1	939.3
137.5°	993.0	994.0	995.0	996.0	996.9	997.9	999.0	1000.1	1001.1	1002.3	1001.6
140°	1032.8	1034.6	1036.3	1038.2	1040.0	1041.0	1041.3	1041.5	1041.8	1042.1	1041.8
142.5°	1073.5	1074.9	1076.3	1077.6	1079.1	1079.9	1080.1	1080.4	1080.7	1080.9	1080.4
145°	1132.2	1133.3	1134.3	1135.3	1136.4	1137.0	1137.3	1137.5	1137.7	1138.0	1137.3
147.5°	1184.5	1186.1	1187.6	1189.2	1190.7	1191.4	1191.4	1191.4	1191.4	1191.4	1190.7
150°	1217.8	1219.3	1220.9	1222.4	1224.0	1224.8	1224.8	1224.8	1224.8	1224.8	1224.2
152.5°	1250.2	1251.5	1252.9	1254.2	1255.5	1256.0	1255.6	1255.2	1254.8	1254.4	1254.1
155°	1294.1	1295.9	1297.8	1299.6	1301.4	1301.7	1300.7	1299.7	1298.7	1297.6	1297.4
157.5°	1334.2	1335.6	1337.0	1338.5	1339.9	1340.2	1339.0	1337.9	1336.9	1335.8	1335.6
160°	1360.0	1361.1	1362.2	1363.2	1364.2	1364.1	1362.8	1361.5	1360.2	1358.9	1358.9
162.5°	1379.5	1381.2	1382.8	1384.5	1386.1	1386.3	1385.0	1383.7	1382.4	1381.1	1380.9
165°	1407.5	1409.3	1411.1	1412.9	1414.7	1414.8	1413.3	1411.8	1410.2	1408.6	1408.6
167.5°	1431.3	1432.9	1434.5	1436.1	1437.7	1437.7	1436.1	1434.5	1432.9	1431.3	1431.1
170°	1443.3	1445.1	1447.0	1448.8	1450.5	1450.5	1448.8	1447.0	1445.1	1443.3	1443.3
172.5°	1452.6	1454.4	1456.2	1458.0	1459.8	1459.9	1458.3	1456.7	1455.1	1453.5	1453.5
175°	1463.0	1464.8	1466.6	1468.4	1470.2	1470.3	1468.8	1467.2	1465.7	1464.2	1464.2
177.5°	1468.6	1470.0	1471.4	1472.8	1474.4	1474.4	1473.2	1471.9	1470.7	1469.5	1469.5
180°	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3



TEST NUMBER: P332199-940

CATALOG NUMBER: S123DIW-S1000D1320U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4
2.5°	1291.3	1287.4	1283.5	1276.8	1270.9	1262.7	1260.2	1257.3	1248.6	1240.8	1234.9
5°	1370.1	1355.6	1334.4	1314.9	1299.1	1277.9	1265.8	1253.0	1234.8	1218.4	1205.1
7.5°	1452.7	1424.1	1391.1	1355.3	1322.1	1290.0	1264.2	1241.2	1215.7	1191.5	1172.7
10°	1518.2	1476.9	1430.8	1381.1	1338.6	1297.4	1262.8	1232.4	1199.6	1171.1	1147.5
12.5°	1593.0	1531.8	1468.2	1407.7	1357.5	1300.3	1258.4	1219.8	1182.7	1148.3	1121.8
15°	1681.4	1603.7	1528.6	1445.4	1369.0	1297.4	1247.6	1199.1	1155.9	1120.8	1086.8
17.5°	1762.0	1674.0	1574.9	1473.8	1381.5	1296.6	1227.0	1172.1	1118.2	1075.1	1041.3
20°	1807.7	1707.5	1595.3	1490.3	1388.4	1293.7	1217.3	1151.7	1093.4	1047.9	1009.7
22.5°	1847.0	1729.8	1613.7	1501.5	1387.9	1285.9	1199.3	1131.8	1068.7	1024.1	983.5
25°	1887.8	1747.6	1631.1	1499.4	1372.6	1267.0	1169.9	1093.4	1030.4	978.2	936.3
27.5°	1922.7	1746.4	1608.1	1466.5	1348.5	1242.7	1139.1	1057.0	990.1	933.4	890.9
30°	1946.0	1748.8	1584.4	1444.2	1325.3	1216.0	1115.3	1032.8	962.4	904.7	864.7
32.5°	1960.6	1747.3	1562.5	1413.1	1288.3	1191.8	1089.6	1004.2	931.8	875.1	836.5
35°	1969.1	1736.7	1524.9	1348.9	1228.8	1134.7	1049.2	960.6	884.8	832.0	788.3
37.5°	1952.0	1714.2	1481.2	1287.0	1155.5	1062.8	990.9	915.4	842.8	784.7	747.1
40°	1925.4	1699.7	1447.2	1243.3	1105.0	1015.7	954.5	880.5	808.9	753.7	718.5
42.5°	1874.4	1670.0	1409.9	1194.8	1052.6	963.3	907.0	845.1	777.3	725.5	690.3
45°	1750.0	1605.6	1353.8	1122.0	975.1	882.9	833.1	788.3	726.9	676.5	646.2
47.5°	1577.4	1508.6	1272.7	1045.2	894.3	805.6	753.9	717.7	673.0	632.3	603.2
50°	1457.5	1429.1	1217.8	992.7	840.4	753.7	703.9	671.1	639.0	598.3	571.6
52.5°	1319.2	1336.8	1153.8	938.3	785.6	700.3	653.4	627.4	598.2	564.8	541.5
55°	1124.4	1188.1	1043.1	847.1	703.9	622.6	578.3	555.2	538.2	513.4	493.3
57.5°	942.0	1023.1	923.5	753.0	623.7	553.5	511.0	485.9	475.0	462.0	446.2
60°	833.7	913.8	838.0	689.9	569.8	503.0	465.4	444.2	433.3	424.2	410.8
62.5°	737.2	818.2	754.5	625.9	516.8	455.0	422.2	401.4	393.0	388.3	376.8
65°	604.4	674.1	631.7	526.1	441.1	386.6	356.8	342.2	334.4	332.5	325.2
67.5°	491.9	545.0	514.1	436.4	369.5	322.4	297.1	284.7	278.7	278.0	272.6
70°	418.1	467.9	444.2	373.8	316.1	279.1	257.3	246.4	242.7	242.1	239.1
72.5°	360.8	395.5	376.7	318.0	273.4	239.8	223.8	212.4	208.2	209.1	207.1
75°	267.0	293.1	282.1	241.5	205.7	183.9	170.5	163.3	159.6	161.4	159.0
77.5°	192.1	208.7	198.8	170.7	148.6	132.8	123.0	118.4	115.2	115.0	114.0
80°	145.0	154.7	149.3	132.2	114.0	100.8	92.8	89.8	88.0	87.4	86.8
82.5°	103.3	111.6	105.1	93.5	81.1	73.0	68.6	64.6	63.2	63.6	63.0
85°	52.2	55.2	52.8	45.5	40.7	37.0	34.6	32.7	31.6	32.2	30.9
87.5°	22.2	22.0	19.9	17.3	15.9	13.9	13.4	11.9	11.4	11.9	11.9
90°	21.0	17.7	14.4	11.4	8.8	6.3	3.7	1.2	3.7	6.3	8.8
92.5°	40.6	38.7	36.8	35.0	33.3	31.5	29.7	28.0	29.7	31.5	33.3
95°	81.5	79.5	77.4	75.4	73.7	71.9	70.0	68.2	70.0	71.9	73.7
97.5°	130.9	129.5	128.0	126.5	125.2	123.9	122.5	121.2	122.5	123.9	125.2
100°	167.5	166.1	164.9	163.5	161.9	160.3	158.8	157.3	158.8	160.3	161.9
102.5°	207.3	205.6	203.9	202.6	201.7	200.8	199.8	198.9	199.8	200.8	201.7
105°	268.3	266.0	263.7	262.3	261.7	261.3	260.7	260.2	260.7	261.3	261.7
107.5°	335.2	334.2	333.3	332.7	332.4	332.1	331.8	331.4	331.8	332.1	332.4
110°	379.5	379.0	378.4	377.9	377.4	376.9	376.4	375.9	376.4	376.9	377.4



TEST NUMBER: P332199-940

CATALOG NUMBER: S123DIW-S1000D1320U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	423.7	423.7	423.6	423.4	423.0	422.8	422.4	422.1	422.4	422.8	423.0
115°	493.7	494.2	494.7	494.6	493.8	493.0	492.3	491.5	492.3	493.0	493.8
117.5°	562.0	562.7	563.4	563.5	562.9	562.4	561.9	561.4	561.9	562.4	562.9
120°	608.6	609.8	611.2	611.0	609.5	608.0	606.4	604.8	606.4	608.0	609.5
122.5°	653.6	654.2	655.0	654.7	653.6	652.5	651.3	650.2	651.3	652.5	653.6
125°	721.6	722.0	722.6	722.5	721.7	720.9	720.1	719.3	720.1	720.9	721.7
127.5°	789.2	789.8	790.3	789.8	788.1	786.5	784.9	783.2	784.9	786.5	788.1
130°	833.1	833.8	834.6	834.0	832.0	829.9	827.8	825.7	827.8	829.9	832.0
132.5°	876.2	876.7	877.3	876.6	874.5	872.4	870.4	868.3	870.4	872.4	874.5
135°	939.6	939.9	940.1	939.5	937.9	936.4	934.9	933.4	934.9	936.4	937.9
137.5°	1000.9	1000.2	999.6	998.6	997.3	996.0	994.7	993.5	994.7	996.0	997.3
140°	1041.5	1041.3	1041.0	1040.3	1038.9	1037.7	1036.3	1035.1	1036.3	1037.7	1038.9
142.5°	1080.0	1079.5	1079.1	1078.2	1076.9	1075.6	1074.3	1073.0	1074.3	1075.6	1076.9
145°	1136.5	1135.7	1135.0	1134.3	1133.8	1133.3	1132.7	1132.2	1132.7	1133.3	1133.8
147.5°	1190.0	1189.3	1188.6	1187.8	1186.9	1185.9	1185.0	1184.0	1185.0	1185.9	1186.9
150°	1223.7	1223.2	1222.7	1222.2	1221.6	1221.2	1220.7	1220.1	1220.7	1221.2	1221.6
152.5°	1253.7	1253.5	1253.1	1252.6	1251.9	1251.2	1250.4	1249.7	1250.4	1251.2	1251.9
155°	1297.1	1296.8	1296.6	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5
157.5°	1335.3	1335.2	1335.0	1335.0	1335.3	1335.6	1336.0	1336.2	1336.0	1335.6	1335.3
160°	1358.9	1358.9	1358.9	1359.1	1359.7	1360.2	1360.8	1361.2	1360.8	1360.2	1359.7
162.5°	1380.7	1380.5	1380.3	1380.5	1381.3	1382.0	1382.7	1383.4	1382.7	1382.0	1381.3
165°	1408.6	1408.6	1408.6	1409.1	1409.8	1410.6	1411.3	1412.1	1411.3	1410.6	1409.8
167.5°	1430.9	1430.7	1430.5	1430.9	1431.9	1433.0	1434.0	1435.0	1434.0	1433.0	1431.9
170°	1443.3	1443.3	1443.3	1443.9	1444.9	1445.9	1447.0	1448.0	1447.0	1445.9	1444.9
172.5°	1453.5	1453.5	1453.5	1454.0	1455.1	1456.1	1457.1	1458.1	1457.1	1456.1	1455.1
175°	1464.2	1464.2	1464.2	1464.6	1465.7	1466.8	1467.8	1468.8	1467.8	1466.8	1465.7
177.5°	1469.5	1469.5	1469.5	1469.9	1470.7	1471.5	1472.4	1473.2	1472.4	1471.5	1470.7
180°	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3



TEST NUMBER: P332199-940

CATALOG NUMBER: S123DIW-S1000D1320U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4
2.5°	1231.5	1228.2	1223.3	1216.0	1210.2	1201.0	1201.0	1202.5	1202.5	1201.9	1201.0
5°	1194.2	1185.1	1174.2	1161.5	1148.1	1134.7	1132.3	1127.5	1123.8	1121.3	1118.3
7.5°	1154.8	1138.6	1122.7	1104.8	1088.6	1075.1	1065.8	1058.0	1053.0	1047.7	1043.8
10°	1128.0	1108.0	1089.2	1070.4	1049.7	1033.4	1023.1	1015.7	1010.3	1005.5	1003.1
12.5°	1096.4	1073.5	1052.8	1034.9	1012.4	995.5	985.7	982.3	975.9	965.6	960.3
15°	1050.3	1029.1	1004.2	977.0	966.0	945.4	933.9	928.4	924.8	916.9	914.4
17.5°	1010.9	983.1	955.2	934.9	914.5	897.9	891.4	884.6	879.8	873.3	871.4
20°	979.4	954.5	929.0	907.1	885.9	867.7	862.3	857.4	852.6	849.5	847.1
22.5°	947.4	922.5	901.3	880.9	858.3	846.3	840.4	835.1	831.7	829.6	827.2
25°	902.3	880.5	856.8	838.6	820.4	812.5	808.9	805.8	803.4	800.4	799.8
27.5°	862.0	838.2	819.0	802.1	789.0	782.4	778.9	777.4	777.9	779.0	779.7
30°	832.0	810.1	794.3	779.7	767.6	761.5	760.9	760.9	763.4	763.9	765.2
32.5°	804.2	786.3	770.5	756.4	747.3	743.1	745.4	745.4	747.3	748.9	751.1
35°	763.9	748.1	736.0	723.9	716.0	717.8	719.1	720.2	723.3	726.9	729.4
37.5°	725.5	711.8	699.2	689.6	686.1	689.3	692.2	694.8	698.3	701.1	703.6
40°	697.9	687.5	675.4	666.9	668.1	669.9	672.3	675.4	678.4	680.2	682.7
42.5°	672.1	661.3	652.1	645.1	646.8	649.1	650.5	652.1	655.6	658.9	660.3
45°	632.9	624.4	615.9	611.6	612.9	614.1	615.3	617.2	620.2	622.6	623.2
47.5°	588.8	582.9	577.2	573.1	575.0	574.5	576.1	580.0	580.9	582.4	585.8
50°	560.7	555.2	548.6	547.3	547.3	547.3	548.0	552.8	552.8	555.2	557.7
52.5°	529.6	526.1	521.8	519.7	518.7	518.7	521.2	523.7	524.7	528.1	530.5
55°	483.7	480.0	476.4	474.5	473.3	474.5	479.4	480.5	483.7	485.4	487.2
57.5°	435.7	432.9	430.0	429.0	428.7	430.3	433.0	436.7	437.4	443.0	445.8
60°	404.1	399.8	397.4	397.4	396.3	401.7	400.5	406.5	407.8	411.4	415.6
62.5°	371.6	365.9	364.9	364.9	366.7	368.2	369.9	372.6	375.8	380.3	383.6
65°	319.1	316.1	320.4	319.8	318.6	322.2	322.2	325.2	328.9	333.1	339.8
67.5°	269.6	268.0	268.3	268.3	270.2	272.2	273.9	276.6	281.0	285.4	289.8
70°	236.0	237.9	234.9	237.3	239.1	239.7	240.9	244.5	249.4	252.4	257.3
72.5°	203.5	203.4	203.8	204.7	206.5	207.7	208.8	213.0	218.3	220.9	224.8
75°	156.6	156.0	157.7	157.7	160.8	162.0	163.3	165.1	169.9	173.5	176.6
77.5°	114.3	115.0	114.7	116.7	115.9	116.1	119.9	121.7	122.3	129.4	131.0
80°	86.1	87.4	88.0	88.6	89.2	88.0	92.2	94.1	94.1	98.3	101.3
82.5°	61.9	62.6	64.2	64.8	64.9	66.2	66.5	67.9	69.3	71.2	75.1
85°	30.9	32.7	33.3	32.7	33.3	32.2	34.0	34.6	35.2	35.2	35.2
87.5°	12.0	13.1	13.3	14.4	14.6	15.8	16.0	15.2	15.4	17.0	15.2
90°	11.4	14.4	17.7	21.0	24.4	27.7	28.8	29.8	30.9	31.8	32.6
92.5°	35.0	36.8	38.7	40.6	42.5	44.4	45.2	46.0	46.9	47.7	48.0
95°	75.4	77.4	79.5	81.5	83.6	85.6	86.6	87.7	88.6	89.7	90.2
97.5°	126.5	128.0	129.5	130.9	132.4	133.9	135.1	136.3	137.5	138.7	139.2
100°	163.5	164.9	166.1	167.5	168.7	170.0	170.8	171.6	172.3	173.1	173.7
102.5°	202.6	203.9	205.6	207.3	209.0	210.7	211.5	212.2	213.0	213.8	214.1
105°	262.3	263.7	266.0	268.3	270.6	273.0	273.0	273.0	273.0	273.0	273.2
107.5°	332.7	333.3	334.2	335.2	336.1	337.0	337.9	338.7	339.5	340.3	340.5
110°	377.9	378.4	379.0	379.5	380.0	380.5	381.6	382.5	383.6	384.6	384.9



TEST NUMBER: P332199-940

CATALOG NUMBER: S123DIW-S1000D1320U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	423.4	423.6	423.7	423.7	423.9	424.0	425.3	426.4	427.7	428.9	429.4
115°	494.6	494.7	494.2	493.7	493.2	492.7	492.9	493.2	493.5	493.7	493.7
117.5°	563.5	563.4	562.7	562.0	561.3	560.7	560.6	560.6	560.5	560.4	560.1
120°	611.0	611.2	609.8	608.6	607.3	606.0	605.7	605.5	605.3	605.0	604.6
122.5°	654.7	655.0	654.2	653.6	652.9	652.3	651.6	650.9	650.2	649.6	648.9
125°	722.5	722.6	722.0	721.6	721.0	720.5	719.5	718.5	717.5	716.4	715.4
127.5°	789.8	790.3	789.8	789.2	788.6	788.1	786.6	785.2	783.7	782.3	781.0
130°	834.0	834.6	833.8	833.1	832.3	831.5	830.5	829.5	828.5	827.4	826.0
132.5°	876.6	877.3	876.7	876.2	875.6	875.0	873.8	872.5	871.3	870.1	868.8
135°	939.5	940.1	939.9	939.6	939.3	939.1	938.1	937.0	936.0	935.0	934.2
137.5°	998.6	999.6	1000.2	1000.9	1001.6	1002.3	1001.1	1000.1	999.0	997.9	996.9
140°	1040.3	1041.0	1041.3	1041.5	1041.8	1042.1	1041.8	1041.5	1041.3	1041.0	1040.0
142.5°	1078.2	1079.1	1079.5	1080.0	1080.4	1080.9	1080.7	1080.4	1080.1	1079.9	1079.1
145°	1134.3	1135.0	1135.7	1136.5	1137.3	1138.0	1137.7	1137.5	1137.3	1137.0	1136.4
147.5°	1187.8	1188.6	1189.3	1190.0	1190.7	1191.4	1191.4	1191.4	1191.4	1191.4	1190.7
150°	1222.2	1222.7	1223.2	1223.7	1224.2	1224.8	1224.8	1224.8	1224.8	1224.8	1224.0
152.5°	1252.6	1253.1	1253.5	1253.7	1254.1	1254.4	1254.8	1255.2	1255.6	1256.0	1255.5
155°	1296.5	1296.6	1296.8	1297.1	1297.4	1297.6	1298.7	1299.7	1300.7	1301.7	1301.4
157.5°	1335.0	1335.0	1335.2	1335.3	1335.6	1335.8	1336.9	1337.9	1339.0	1340.2	1339.9
160°	1359.1	1358.9	1358.9	1358.9	1358.9	1358.9	1360.2	1361.5	1362.8	1364.1	1364.2
162.5°	1380.5	1380.3	1380.5	1380.7	1380.9	1381.1	1382.4	1383.7	1385.0	1386.3	1386.1
165°	1409.1	1408.6	1408.6	1408.6	1408.6	1408.6	1410.2	1411.8	1413.3	1414.8	1414.7
167.5°	1430.9	1430.5	1430.7	1430.9	1431.1	1431.3	1432.9	1434.5	1436.1	1437.7	1437.7
170°	1443.9	1443.3	1443.3	1443.3	1443.3	1443.3	1445.1	1447.0	1448.8	1450.5	1450.5
172.5°	1454.0	1453.5	1453.5	1453.5	1453.5	1453.5	1455.1	1456.7	1458.3	1459.9	1459.8
175°	1464.6	1464.2	1464.2	1464.2	1464.2	1464.2	1465.7	1467.2	1468.8	1470.3	1470.2
177.5°	1469.9	1469.5	1469.5	1469.5	1469.5	1469.5	1470.7	1471.9	1473.2	1474.4	1474.4
180°	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3



TEST NUMBER: P332199-940

CATALOG NUMBER: S123DIW-S1000D1320U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4
2.5°	1197.6	1197.1	1200.5	1198.1	1200.5	1197.1	1197.6	1201.0	1201.9	1202.5	1202.5
5°	1114.7	1116.5	1110.4	1110.4	1110.4	1116.5	1114.7	1118.3	1121.3	1123.8	1127.5
7.5°	1040.9	1038.2	1038.5	1035.2	1038.5	1038.2	1040.9	1043.8	1047.7	1053.0	1058.0
10°	995.8	992.1	990.9	991.5	990.9	992.1	995.8	1003.1	1005.5	1010.3	1015.7
12.5°	958.4	957.7	949.7	949.8	949.7	957.7	958.4	960.3	965.6	975.9	982.3
15°	914.4	902.9	901.7	905.4	901.7	902.9	914.4	914.4	916.9	924.8	928.4
17.5°	870.4	864.3	864.7	862.9	864.7	864.3	870.4	871.4	873.3	879.8	884.6
20°	847.1	843.5	842.8	838.6	842.8	843.5	847.1	847.1	849.5	852.6	857.4
22.5°	825.7	824.6	824.9	820.2	824.9	824.6	825.7	827.2	829.6	831.7	835.1
25°	799.2	802.2	799.8	799.8	799.8	802.2	799.2	799.8	800.4	803.4	805.8
27.5°	781.2	781.0	779.9	779.9	779.9	781.0	781.2	779.7	779.0	777.9	777.4
30°	767.6	767.0	768.2	768.2	768.2	767.0	767.6	765.2	763.9	763.4	760.9
32.5°	754.0	754.8	755.1	755.5	755.1	754.8	754.0	751.1	748.9	747.3	745.4
35°	733.0	733.6	735.5	734.2	735.5	733.6	733.0	729.4	726.9	723.3	720.2
37.5°	704.6	707.4	706.8	707.8	706.8	707.4	704.6	703.6	701.1	698.3	694.8
40°	683.2	685.1	684.5	684.5	684.5	685.1	683.2	682.7	680.2	678.4	675.4
42.5°	661.4	662.7	661.2	660.2	661.2	662.7	661.4	660.3	658.9	655.6	652.1
45°	625.6	624.4	626.2	623.8	626.2	624.4	625.6	623.2	622.6	620.2	617.2
47.5°	585.6	586.7	587.3	589.1	587.3	586.7	585.6	585.8	582.4	580.9	580.0
50°	558.8	562.5	562.5	561.9	562.5	562.5	558.8	557.7	555.2	552.8	552.8
52.5°	532.6	534.3	536.8	536.6	536.8	534.3	532.6	530.5	528.1	524.7	523.7
55°	492.1	493.3	494.5	495.2	494.5	493.3	492.1	487.2	485.4	483.7	480.5
57.5°	450.1	449.6	452.5	453.4	452.5	449.6	450.1	445.8	443.0	437.4	436.7
60°	420.5	420.5	425.3	427.2	425.3	420.5	420.5	415.6	411.4	407.8	406.5
62.5°	389.0	390.9	395.7	393.2	395.7	390.9	389.0	383.6	380.3	375.8	372.6
65°	342.9	347.7	347.1	349.6	347.1	347.7	342.9	339.8	333.1	328.9	325.2
67.5°	294.6	297.7	302.0	302.5	302.0	297.7	294.6	289.8	285.4	281.0	276.6
70°	262.2	265.2	267.6	269.4	267.6	265.2	262.2	257.3	252.4	249.4	244.5
72.5°	230.6	232.2	238.0	235.4	238.0	232.2	230.6	224.8	220.9	218.3	213.0
75°	180.8	185.0	188.7	186.9	188.7	185.0	180.8	176.6	173.5	169.9	165.1
77.5°	133.8	137.9	139.6	138.1	139.6	137.9	133.8	131.0	129.4	122.3	121.7
80°	105.6	105.0	108.6	108.0	108.6	105.0	105.6	101.3	98.3	94.1	94.1
82.5°	77.4	76.9	78.6	78.9	78.6	76.9	77.4	75.1	71.2	69.3	67.9
85°	37.6	39.4	37.0	36.4	37.0	39.4	37.6	35.2	35.2	35.2	34.6
87.5°	15.3	15.5	15.1	14.7	15.1	15.5	15.3	15.2	17.0	15.4	15.2
90°	33.2	33.7	34.2	34.7	34.2	33.7	33.2	32.6	31.8	30.9	29.8
92.5°	47.6	47.3	47.0	46.7	47.0	47.3	47.6	48.0	47.7	46.9	46.0
95°	90.2	90.2	90.2	90.2	90.2	90.2	90.2	90.2	89.7	88.6	87.7
97.5°	139.1	139.0	138.9	138.8	138.9	139.0	139.1	139.2	138.7	137.5	136.3
100°	174.2	174.8	175.3	175.8	175.3	174.8	174.2	173.7	173.1	172.3	171.6
102.5°	214.0	213.9	213.8	213.7	213.8	213.9	214.0	214.1	213.8	213.0	212.2
105°	273.8	274.2	274.7	275.3	274.7	274.2	273.8	273.2	273.0	273.0	273.0
107.5°	340.3	339.9	339.7	339.3	339.7	339.9	340.3	340.5	340.3	339.5	338.7
110°	384.3	383.9	383.3	382.8	383.3	383.9	384.3	384.9	384.6	383.6	382.5



TEST NUMBER: P332199-940

CATALOG NUMBER: S123DIW-S1000D1320U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	429.4	429.3	429.2	429.1	429.2	429.3	429.4	429.4	428.9	427.7	426.4
115°	493.5	493.2	492.9	492.7	492.9	493.2	493.5	493.7	493.7	493.5	493.2
117.5°	559.4	558.7	557.9	557.2	557.9	558.7	559.4	560.1	560.4	560.5	560.6
120°	604.1	603.6	603.1	602.5	603.1	603.6	604.1	604.6	605.0	605.3	605.5
122.5°	648.2	647.5	646.8	646.0	646.8	647.5	648.2	648.9	649.6	650.2	650.9
125°	714.3	713.3	712.3	711.2	712.3	713.3	714.3	715.4	716.4	717.5	718.5
127.5°	779.8	778.6	777.5	776.2	777.5	778.6	779.8	781.0	782.3	783.7	785.2
130°	824.2	822.4	820.6	818.9	820.6	822.4	824.2	826.0	827.4	828.5	829.5
132.5°	867.4	866.0	864.6	863.3	864.6	866.0	867.4	868.8	870.1	871.3	872.5
135°	933.7	933.2	932.6	932.2	932.6	933.2	933.7	934.2	935.0	936.0	937.0
137.5°	996.0	995.0	994.0	993.0	994.0	995.0	996.0	996.9	997.9	999.0	1000.1
140°	1038.2	1036.3	1034.6	1032.8	1034.6	1036.3	1038.2	1040.0	1041.0	1041.3	1041.5
142.5°	1077.6	1076.3	1074.9	1073.5	1074.9	1076.3	1077.6	1079.1	1079.9	1080.1	1080.4
145°	1135.3	1134.3	1133.3	1132.2	1133.3	1134.3	1135.3	1136.4	1137.0	1137.3	1137.5
147.5°	1189.2	1187.6	1186.1	1184.5	1186.1	1187.6	1189.2	1190.7	1191.4	1191.4	1191.4
150°	1222.4	1220.9	1219.3	1217.8	1219.3	1220.9	1222.4	1224.0	1224.8	1224.8	1224.8
152.5°	1254.2	1252.9	1251.5	1250.2	1251.5	1252.9	1254.2	1255.5	1256.0	1255.6	1255.2
155°	1299.6	1297.8	1295.9	1294.1	1295.9	1297.8	1299.6	1301.4	1301.7	1300.7	1299.7
157.5°	1338.5	1337.0	1335.6	1334.2	1335.6	1337.0	1338.5	1339.9	1340.2	1339.0	1337.9
160°	1363.2	1362.2	1361.1	1360.0	1361.1	1362.2	1363.2	1364.2	1364.1	1362.8	1361.5
162.5°	1384.5	1382.8	1381.2	1379.5	1381.2	1382.8	1384.5	1386.1	1386.3	1385.0	1383.7
165°	1412.9	1411.1	1409.3	1407.5	1409.3	1411.1	1412.9	1414.7	1414.8	1413.3	1411.8
167.5°	1436.1	1434.5	1432.9	1431.3	1432.9	1434.5	1436.1	1437.7	1437.7	1436.1	1434.5
170°	1448.8	1447.0	1445.1	1443.3	1445.1	1447.0	1448.8	1450.5	1450.5	1448.8	1447.0
172.5°	1458.0	1456.2	1454.4	1452.6	1454.4	1456.2	1458.0	1459.8	1459.9	1458.3	1456.7
175°	1468.4	1466.6	1464.8	1463.0	1464.8	1466.6	1468.4	1470.2	1470.3	1468.8	1467.2
177.5°	1472.8	1471.4	1470.0	1468.6	1470.0	1471.4	1472.8	1474.4	1474.4	1473.2	1471.9
180°	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3



TEST NUMBER: P332199-940

CATALOG NUMBER: S123DIW-S1000D1320U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4
2.5°	1201.0	1201.0	1210.2	1216.0	1223.3	1228.2	1231.5	1234.9	1240.8	1248.6	1257.3
5°	1132.3	1134.7	1148.1	1161.5	1174.2	1185.1	1194.2	1205.1	1218.4	1234.8	1253.0
7.5°	1065.8	1075.1	1088.6	1104.8	1122.7	1138.6	1154.8	1172.7	1191.5	1215.7	1241.2
10°	1023.1	1033.4	1049.7	1070.4	1089.2	1108.0	1128.0	1147.5	1171.1	1199.6	1232.4
12.5°	985.7	995.5	1012.4	1034.9	1052.8	1073.5	1096.4	1121.8	1148.3	1182.7	1219.8
15°	933.9	945.4	966.0	977.0	1004.2	1029.1	1050.3	1086.8	1120.8	1155.9	1199.1
17.5°	891.4	897.9	914.5	934.9	955.2	983.1	1010.9	1041.3	1075.1	1118.2	1172.1
20°	862.3	867.7	885.9	907.1	929.0	954.5	979.4	1009.7	1047.9	1093.4	1151.7
22.5°	840.4	846.3	858.3	880.9	901.3	922.5	947.4	983.5	1024.1	1068.7	1131.8
25°	808.9	812.5	820.4	838.6	856.8	880.5	902.3	936.3	978.2	1030.4	1093.4
27.5°	778.9	782.4	789.0	802.1	819.0	838.2	862.0	890.9	933.4	990.1	1057.0
30°	760.9	761.5	767.6	779.7	794.3	810.1	832.0	864.7	904.7	962.4	1032.8
32.5°	745.4	743.1	747.3	756.4	770.5	786.3	804.2	836.5	875.1	931.8	1004.2
35°	719.1	717.8	716.0	723.9	736.0	748.1	763.9	788.3	832.0	884.8	960.6
37.5°	692.2	689.3	686.1	689.6	699.2	711.8	725.5	747.1	784.7	842.8	915.4
40°	672.3	669.9	668.1	666.9	675.4	687.5	697.9	718.5	753.7	808.9	880.5
42.5°	650.5	649.1	646.8	645.1	652.1	661.3	672.1	690.3	725.5	777.3	845.1
45°	615.3	614.1	612.9	611.6	615.9	624.4	632.9	646.2	676.5	726.9	788.3
47.5°	576.1	574.5	575.0	573.1	577.2	582.9	588.8	603.2	632.3	673.0	717.7
50°	548.0	547.3	547.3	547.3	548.6	555.2	560.7	571.6	598.3	639.0	671.1
52.5°	521.2	518.7	518.7	519.7	521.8	526.1	529.6	541.5	564.8	598.2	627.4
55°	479.4	474.5	473.3	474.5	476.4	480.0	483.7	493.3	513.4	538.2	555.2
57.5°	433.0	430.3	428.7	429.0	430.0	432.9	435.7	446.2	462.0	475.0	485.9
60°	400.5	401.7	396.3	397.4	397.4	399.8	404.1	410.8	424.2	433.3	444.2
62.5°	369.9	368.2	366.7	364.9	364.9	365.9	371.6	376.8	388.3	393.0	401.4
65°	322.2	322.2	318.6	319.8	320.4	316.1	319.1	325.2	332.5	334.4	342.2
67.5°	273.9	272.2	270.2	268.3	268.3	268.0	269.6	272.6	278.0	278.7	284.7
70°	240.9	239.7	239.1	237.3	234.9	237.9	236.0	239.1	242.1	242.7	246.4
72.5°	208.8	207.7	206.5	204.7	203.8	203.4	203.5	207.1	209.1	208.2	212.4
75°	163.3	162.0	160.8	157.7	157.7	156.0	156.6	159.0	161.4	159.6	163.3
77.5°	119.9	116.1	115.9	116.7	114.7	115.0	114.3	114.0	115.0	115.2	118.4
80°	92.2	88.0	89.2	88.6	88.0	87.4	86.1	86.8	87.4	88.0	89.8
82.5°	66.5	66.2	64.9	64.8	64.2	62.6	61.9	63.0	63.6	63.2	64.6
85°	34.0	32.2	33.3	32.7	33.3	32.7	30.9	30.9	32.2	31.6	32.7
87.5°	16.0	15.8	14.6	14.4	13.3	13.1	12.0	11.9	11.9	11.4	11.9
90°	28.8	27.7	24.4	21.0	17.7	14.4	11.4	8.8	6.3	3.7	1.2
92.5°	45.2	44.4	42.5	40.6	38.7	36.8	35.0	33.3	31.5	29.7	28.0
95°	86.6	85.6	83.6	81.5	79.5	77.4	75.4	73.7	71.9	70.0	68.2
97.5°	135.1	133.9	132.4	130.9	129.5	128.0	126.5	125.2	123.9	122.5	121.2
100°	170.8	170.0	168.7	167.5	166.1	164.9	163.5	161.9	160.3	158.8	157.3
102.5°	211.5	210.7	209.0	207.3	205.6	203.9	202.6	201.7	200.8	199.8	198.9
105°	273.0	273.0	270.6	268.3	266.0	263.7	262.3	261.7	261.3	260.7	260.2
107.5°	337.9	337.0	336.1	335.2	334.2	333.3	332.7	332.4	332.1	331.8	331.4
110°	381.6	380.5	380.0	379.5	379.0	378.4	377.9	377.4	376.9	376.4	375.9



TEST NUMBER: P332199-940

CATALOG NUMBER: S123DIW-S1000D1320U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	425.3	424.0	423.9	423.7	423.7	423.6	423.4	423.0	422.8	422.4	422.1
115°	492.9	492.7	493.2	493.7	494.2	494.7	494.6	493.8	493.0	492.3	491.5
117.5°	560.6	560.7	561.3	562.0	562.7	563.4	563.5	562.9	562.4	561.9	561.4
120°	605.7	606.0	607.3	608.6	609.8	611.2	611.0	609.5	608.0	606.4	604.8
122.5°	651.6	652.3	652.9	653.6	654.2	655.0	654.7	653.6	652.5	651.3	650.2
125°	719.5	720.5	721.0	721.6	722.0	722.6	722.5	721.7	720.9	720.1	719.3
127.5°	786.6	788.1	788.6	789.2	789.8	790.3	789.8	788.1	786.5	784.9	783.2
130°	830.5	831.5	832.3	833.1	833.8	834.6	834.0	832.0	829.9	827.8	825.7
132.5°	873.8	875.0	875.6	876.2	876.7	877.3	876.6	874.5	872.4	870.4	868.3
135°	938.1	939.1	939.3	939.6	939.9	940.1	939.5	937.9	936.4	934.9	933.4
137.5°	1001.1	1002.3	1001.6	1000.9	1000.2	999.6	998.6	997.3	996.0	994.7	993.5
140°	1041.8	1042.1	1041.8	1041.5	1041.3	1041.0	1040.3	1038.9	1037.7	1036.3	1035.1
142.5°	1080.7	1080.9	1080.4	1080.0	1079.5	1079.1	1078.2	1076.9	1075.6	1074.3	1073.0
145°	1137.7	1138.0	1137.3	1136.5	1135.7	1135.0	1134.3	1133.8	1133.3	1132.7	1132.2
147.5°	1191.4	1191.4	1190.7	1190.0	1189.3	1188.6	1187.8	1186.9	1185.9	1185.0	1184.0
150°	1224.8	1224.8	1224.2	1223.7	1223.2	1222.7	1222.2	1221.6	1221.2	1220.7	1220.1
152.5°	1254.8	1254.4	1254.1	1253.7	1253.5	1253.1	1252.6	1251.9	1251.2	1250.4	1249.7
155°	1298.7	1297.6	1297.4	1297.1	1296.8	1296.6	1296.5	1296.5	1296.5	1296.5	1296.5
157.5°	1336.9	1335.8	1335.6	1335.3	1335.2	1335.0	1335.0	1335.3	1335.6	1336.0	1336.2
160°	1360.2	1358.9	1358.9	1358.9	1358.9	1358.9	1359.1	1359.7	1360.2	1360.8	1361.2
162.5°	1382.4	1381.1	1380.9	1380.7	1380.5	1380.3	1380.5	1381.3	1382.0	1382.7	1383.4
165°	1410.2	1408.6	1408.6	1408.6	1408.6	1408.6	1409.1	1409.8	1410.6	1411.3	1412.1
167.5°	1432.9	1431.3	1431.1	1430.9	1430.7	1430.5	1430.9	1431.9	1433.0	1434.0	1435.0
170°	1445.1	1443.3	1443.3	1443.3	1443.3	1443.3	1443.9	1444.9	1445.9	1447.0	1448.0
172.5°	1455.1	1453.5	1453.5	1453.5	1453.5	1453.5	1454.0	1455.1	1456.1	1457.1	1458.1
175°	1465.7	1464.2	1464.2	1464.2	1464.2	1464.2	1464.6	1465.7	1466.8	1467.8	1468.8
177.5°	1470.7	1469.5	1469.5	1469.5	1469.5	1469.5	1469.9	1470.7	1471.5	1472.4	1473.2
180°	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3



TEST NUMBER: P332199-940

CATALOG NUMBER: S123DIW-S1000D1320U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4
2.5°	1260.2	1262.7	1270.9	1276.8	1283.5	1287.4	1291.3	1294.2	1298.1	1299.0	1313.1
5°	1265.8	1277.9	1299.1	1314.9	1334.4	1355.6	1370.1	1376.8	1394.5	1409.0	1438.2
7.5°	1264.2	1290.0	1322.1	1355.3	1391.1	1424.1	1452.7	1486.7	1510.8	1547.1	1582.9
10°	1262.8	1297.4	1338.6	1381.1	1430.8	1476.9	1518.2	1564.3	1602.6	1653.0	1696.0
12.5°	1258.4	1300.3	1357.5	1407.7	1468.2	1531.8	1593.0	1652.2	1686.0	1770.0	1809.6
15°	1247.6	1297.4	1369.0	1445.4	1528.6	1603.7	1681.4	1743.4	1843.4	1916.9	1963.6
17.5°	1227.0	1296.6	1381.5	1473.8	1574.9	1674.0	1762.0	1856.0	1962.1	2051.0	2145.6
20°	1217.3	1293.7	1388.4	1490.3	1595.3	1707.5	1807.7	1920.6	2036.4	2123.8	2245.1
22.5°	1199.3	1285.9	1387.9	1501.5	1613.7	1729.8	1847.0	1960.8	2094.7	2215.1	2330.6
25°	1169.9	1267.0	1372.6	1499.4	1631.1	1747.6	1887.8	2038.9	2178.4	2333.2	2448.5
27.5°	1139.1	1242.7	1348.5	1466.5	1608.1	1746.4	1922.7	2093.5	2264.1	2397.7	2483.1
30°	1115.3	1216.0	1325.3	1444.2	1584.4	1748.8	1946.0	2132.3	2298.6	2413.2	2461.2
32.5°	1089.6	1191.8	1288.3	1413.1	1562.5	1747.3	1960.6	2155.1	2300.5	2376.9	2367.5
35°	1049.2	1134.7	1228.8	1348.9	1524.9	1736.7	1969.1	2157.1	2246.4	2230.0	2106.2
37.5°	990.9	1062.8	1155.5	1287.0	1481.2	1714.2	1952.0	2093.2	2087.4	1954.0	1774.7
40°	954.5	1015.7	1105.0	1243.3	1447.2	1699.7	1925.4	2017.0	1939.4	1753.0	1538.2
42.5°	907.0	963.3	1052.6	1194.8	1409.9	1670.0	1874.4	1900.9	1749.0	1534.6	1337.7
45°	833.1	882.9	975.1	1122.0	1353.8	1605.6	1750.0	1685.1	1480.6	1259.1	1109.2
47.5°	753.9	805.6	894.3	1045.2	1272.7	1508.6	1577.4	1439.3	1229.4	1049.7	912.1
50°	703.9	753.7	840.4	992.7	1217.8	1429.1	1457.5	1279.2	1086.2	928.4	815.6
52.5°	653.4	700.3	785.6	938.3	1153.8	1336.8	1319.2	1137.4	959.9	825.5	736.9
55°	578.3	622.6	703.9	847.1	1043.1	1188.1	1124.4	950.8	804.1	699.6	632.3
57.5°	511.0	553.5	623.7	753.0	923.5	1023.1	942.0	795.8	679.0	598.7	548.4
60°	465.4	503.0	569.8	689.9	838.0	913.8	833.7	704.5	606.2	541.9	497.0
62.5°	422.2	455.0	516.8	625.9	754.5	818.2	737.2	627.8	544.0	487.1	448.9
65°	356.8	386.6	441.1	526.1	631.7	674.1	604.4	515.8	450.8	408.4	382.9
67.5°	297.1	322.4	369.5	436.4	514.1	545.0	491.9	423.3	374.4	340.3	320.0
70°	257.3	279.1	316.1	373.8	444.2	467.9	418.1	361.7	325.8	298.5	279.7
72.5°	223.8	239.8	273.4	318.0	376.7	395.5	360.8	311.2	277.8	257.3	242.4
75°	170.5	183.9	205.7	241.5	282.1	293.1	267.0	236.0	213.6	199.0	187.5
77.5°	123.0	132.8	148.6	170.7	198.8	208.7	192.1	171.5	155.1	145.3	138.8
80°	92.8	100.8	114.0	132.2	149.3	154.7	145.0	129.2	117.7	112.3	106.8
82.5°	68.6	73.0	81.1	93.5	105.1	111.6	103.3	93.8	87.7	82.7	80.6
85°	34.6	37.0	40.7	45.5	52.8	55.2	52.2	49.8	46.1	43.1	43.1
87.5°	13.4	13.9	15.9	17.3	19.9	22.0	22.2	21.8	22.0	21.8	21.5
90°	3.7	6.3	8.8	11.4	14.4	17.7	21.0	24.4	27.7	28.8	29.8
92.5°	29.7	31.5	33.3	35.0	36.8	38.7	40.6	42.5	44.4	45.2	46.0
95°	70.0	71.9	73.7	75.4	77.4	79.5	81.5	83.6	85.6	86.6	87.7
97.5°	122.5	123.9	125.2	126.5	128.0	129.5	130.9	132.4	133.9	135.1	136.3
100°	158.8	160.3	161.9	163.5	164.9	166.1	167.5	168.7	170.0	170.8	171.6
102.5°	199.8	200.8	201.7	202.6	203.9	205.6	207.3	209.0	210.7	211.5	212.2
105°	260.7	261.3	261.7	262.3	263.7	266.0	268.3	270.6	273.0	273.0	273.0
107.5°	331.8	332.1	332.4	332.7	333.3	334.2	335.2	336.1	337.0	337.9	338.7
110°	376.4	376.9	377.4	377.9	378.4	379.0	379.5	380.0	380.5	381.6	382.5



TEST NUMBER: P332199-940

CATALOG NUMBER: S123DIW-S1000D1320U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	422.4	422.8	423.0	423.4	423.6	423.7	423.7	423.9	424.0	425.3	426.4
115°	492.3	493.0	493.8	494.6	494.7	494.2	493.7	493.2	492.7	492.9	493.2
117.5°	561.9	562.4	562.9	563.5	563.4	562.7	562.0	561.3	560.7	560.6	560.6
120°	606.4	608.0	609.5	611.0	611.2	609.8	608.6	607.3	606.0	605.7	605.5
122.5°	651.3	652.5	653.6	654.7	655.0	654.2	653.6	652.9	652.3	651.6	650.9
125°	720.1	720.9	721.7	722.5	722.6	722.0	721.6	721.0	720.5	719.5	718.5
127.5°	784.9	786.5	788.1	789.8	790.3	789.8	789.2	788.6	788.1	786.6	785.2
130°	827.8	829.9	832.0	834.0	834.6	833.8	833.1	832.3	831.5	830.5	829.5
132.5°	870.4	872.4	874.5	876.6	877.3	876.7	876.2	875.6	875.0	873.8	872.5
135°	934.9	936.4	937.9	939.5	940.1	939.9	939.6	939.3	939.1	938.1	937.0
137.5°	994.7	996.0	997.3	998.6	999.6	1000.2	1000.9	1001.6	1002.3	1001.1	1000.1
140°	1036.3	1037.7	1038.9	1040.3	1041.0	1041.3	1041.5	1041.8	1042.1	1041.8	1041.5
142.5°	1074.3	1075.6	1076.9	1078.2	1079.1	1079.5	1080.0	1080.4	1080.9	1080.7	1080.4
145°	1132.7	1133.3	1133.8	1134.3	1135.0	1135.7	1136.5	1137.3	1138.0	1137.7	1137.5
147.5°	1185.0	1185.9	1186.9	1187.8	1188.6	1189.3	1190.0	1190.7	1191.4	1191.4	1191.4
150°	1220.7	1221.2	1221.6	1222.2	1222.7	1223.2	1223.7	1224.2	1224.8	1224.8	1224.8
152.5°	1250.4	1251.2	1251.9	1252.6	1253.1	1253.5	1253.7	1254.1	1254.4	1254.8	1255.2
155°	1296.5	1296.5	1296.5	1296.5	1296.6	1296.8	1297.1	1297.4	1297.6	1298.7	1299.7
157.5°	1336.0	1335.6	1335.3	1335.0	1335.0	1335.2	1335.3	1335.6	1335.8	1336.9	1337.9
160°	1360.8	1360.2	1359.7	1359.1	1358.9	1358.9	1358.9	1358.9	1358.9	1360.2	1361.5
162.5°	1382.7	1382.0	1381.3	1380.5	1380.3	1380.5	1380.7	1380.9	1381.1	1382.4	1383.7
165°	1411.3	1410.6	1409.8	1409.1	1408.6	1408.6	1408.6	1408.6	1408.6	1410.2	1411.8
167.5°	1434.0	1433.0	1431.9	1430.9	1430.5	1430.7	1430.9	1431.1	1431.3	1432.9	1434.5
170°	1447.0	1445.9	1444.9	1443.9	1443.3	1443.3	1443.3	1443.3	1443.3	1445.1	1447.0
172.5°	1457.1	1456.1	1455.1	1454.0	1453.5	1453.5	1453.5	1453.5	1453.5	1455.1	1456.7
175°	1467.8	1466.8	1465.7	1464.6	1464.2	1464.2	1464.2	1464.2	1464.2	1465.7	1467.2
177.5°	1472.4	1471.5	1470.7	1469.9	1469.5	1469.5	1469.5	1469.5	1469.5	1470.7	1471.9
180°	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3



TEST NUMBER: P332199-940

CATALOG NUMBER: S123DIW-S1000D1320U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4	1252.4
2.5°	1317.9	1318.5	1323.8	1327.7	1325.7	1328.2	1329.1
5°	1439.9	1461.8	1473.3	1481.8	1482.4	1483.0	1487.9
7.5°	1612.8	1636.3	1653.4	1679.4	1687.1	1696.0	1693.4
10°	1739.1	1773.7	1803.4	1819.2	1836.2	1861.1	1841.0
12.5°	1857.1	1918.3	1963.6	1988.2	2004.1	2009.1	1999.3
15°	2051.6	2131.7	2174.8	2173.5	2228.2	2251.8	2214.8
17.5°	2230.0	2303.9	2363.1	2393.4	2439.0	2449.1	2444.4
20°	2339.2	2419.9	2466.0	2518.2	2541.9	2563.1	2566.8
22.5°	2433.4	2505.9	2555.4	2598.8	2618.6	2628.7	2634.7
25°	2530.3	2587.4	2617.2	2632.3	2637.8	2636.5	2628.7
27.5°	2523.7	2528.1	2495.3	2463.2	2434.4	2402.0	2390.8
30°	2458.2	2407.2	2316.1	2264.6	2188.7	2128.7	2152.9
32.5°	2285.8	2184.3	2082.1	1969.4	1876.1	1849.5	1822.8
35°	1950.9	1772.5	1668.1	1546.8	1498.2	1449.7	1416.3
37.5°	1578.3	1440.3	1316.5	1237.2	1188.5	1157.8	1141.3
40°	1364.7	1240.3	1138.4	1074.1	1037.1	1002.5	997.6
42.5°	1194.3	1078.6	1001.9	950.7	915.2	900.4	889.8
45°	978.2	897.4	845.9	809.5	785.8	776.7	764.6
47.5°	828.0	770.9	732.2	707.4	689.6	682.8	681.8
50°	744.0	696.6	668.1	648.6	634.7	632.3	622.6
52.5°	680.8	639.8	617.6	600.7	590.6	583.7	580.9
55°	591.0	563.7	543.7	534.0	526.1	519.4	519.4
57.5°	517.1	494.3	481.1	472.8	470.4	465.7	462.6
60°	471.4	452.1	441.8	434.4	429.6	430.3	424.7
62.5°	426.9	414.2	404.4	397.1	391.3	391.4	391.7
65°	363.5	353.7	346.5	344.0	340.5	336.2	337.4
67.5°	308.0	298.9	293.2	289.1	287.8	285.5	289.1
70°	268.2	261.5	257.3	253.6	252.4	253.1	256.1
72.5°	231.8	227.0	224.3	222.6	219.9	220.0	222.1
75°	182.0	178.4	175.9	174.2	173.5	173.5	173.5
77.5°	133.8	132.9	131.8	129.1	129.2	130.0	130.1
80°	105.6	103.8	103.2	101.9	100.1	98.9	101.9
82.5°	78.9	77.0	76.4	76.2	73.4	73.2	75.7
85°	42.4	40.7	41.3	40.7	40.7	40.0	40.0
87.5°	21.2	21.0	20.6	21.2	20.8	20.4	21.5
90°	30.9	31.8	32.6	33.2	33.7	34.2	34.7
92.5°	46.9	47.7	48.0	47.6	47.3	47.0	46.7
95°	88.6	89.7	90.2	90.2	90.2	90.2	90.2
97.5°	137.5	138.7	139.2	139.1	139.0	138.9	138.8
100°	172.3	173.1	173.7	174.2	174.8	175.3	175.8
102.5°	213.0	213.8	214.1	214.0	213.9	213.8	213.7
105°	273.0	273.0	273.2	273.8	274.2	274.7	275.3
107.5°	339.5	340.3	340.5	340.3	339.9	339.7	339.3
110°	383.6	384.6	384.9	384.3	383.9	383.3	382.8



TEST NUMBER: P332199-940

CATALOG NUMBER: S123DIW-S1000D1320U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	427.7	428.9	429.4	429.4	429.3	429.2	429.1
115°	493.5	493.7	493.7	493.5	493.2	492.9	492.7
117.5°	560.5	560.4	560.1	559.4	558.7	557.9	557.2
120°	605.3	605.0	604.6	604.1	603.6	603.1	602.5
122.5°	650.2	649.6	648.9	648.2	647.5	646.8	646.0
125°	717.5	716.4	715.4	714.3	713.3	712.3	711.2
127.5°	783.7	782.3	781.0	779.8	778.6	777.5	776.2
130°	828.5	827.4	826.0	824.2	822.4	820.6	818.9
132.5°	871.3	870.1	868.8	867.4	866.0	864.6	863.3
135°	936.0	935.0	934.2	933.7	933.2	932.6	932.2
137.5°	999.0	997.9	996.9	996.0	995.0	994.0	993.0
140°	1041.3	1041.0	1040.0	1038.2	1036.3	1034.6	1032.8
142.5°	1080.1	1079.9	1079.1	1077.6	1076.3	1074.9	1073.5
145°	1137.3	1137.0	1136.4	1135.3	1134.3	1133.3	1132.2
147.5°	1191.4	1191.4	1190.7	1189.2	1187.6	1186.1	1184.5
150°	1224.8	1224.8	1224.0	1222.4	1220.9	1219.3	1217.8
152.5°	1255.6	1256.0	1255.5	1254.2	1252.9	1251.5	1250.2
155°	1300.7	1301.7	1301.4	1299.6	1297.8	1295.9	1294.1
157.5°	1339.0	1340.2	1339.9	1338.5	1337.0	1335.6	1334.2
160°	1362.8	1364.1	1364.2	1363.2	1362.2	1361.1	1360.0
162.5°	1385.0	1386.3	1386.1	1384.5	1382.8	1381.2	1379.5
165°	1413.3	1414.8	1414.7	1412.9	1411.1	1409.3	1407.5
167.5°	1436.1	1437.7	1437.7	1436.1	1434.5	1432.9	1431.3
170°	1448.8	1450.5	1450.5	1448.8	1447.0	1445.1	1443.3
172.5°	1458.3	1459.9	1459.8	1458.0	1456.2	1454.4	1452.6
175°	1468.8	1470.3	1470.2	1468.4	1466.6	1464.8	1463.0
177.5°	1473.2	1474.4	1474.4	1472.8	1471.4	1470.0	1468.6
180°	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3

(END OF REPORT)