

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332203-940

Luminaire Tested: **S123DIW-S1000D1320U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332203-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S1000D1320U940-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1320 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7756.2 lumens
Efficiency: N/A
Efficacy: 111.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 69.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332203-940

CATALOG NUMBER: S123DIW-S1000D1320U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332203-940

CATALOG NUMBER: S123DIW-S1000D1320U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	47
1	97	93	89	85	89	85	82	79	72	69	67	59	57	56	47	46	45	40
2	88	81	75	70	81	75	69	65	63	59	55	52	49	47	42	40	38	33
3	81	71	64	58	74	66	59	54	55	51	47	46	42	39	37	34	32	28
4	74	63	55	49	67	58	51	46	49	44	40	41	37	34	33	30	28	24
5	68	56	48	42	62	52	45	39	44	38	34	37	32	29	30	27	24	21
6	62	50	42	36	57	47	39	34	40	34	30	33	29	26	27	24	21	18
7	58	45	37	32	53	42	35	30	36	30	26	30	26	23	25	21	19	16
8	53	41	33	28	49	38	31	26	33	27	23	27	23	20	23	19	17	15
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	15	13
10	46	34	27	22	43	32	26	21	28	22	19	23	19	16	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15193	15193	15193
5°	15263	15055	15159
10°	15162	14924	15017
15°	14985	14755	14782
20°	14778	14513	14528
25°	14500	14226	14197
30°	14194	13908	13801
35°	13875	13571	13397
40°	13541	13198	12995
45°	13172	12858	12543
50°	12804	12439	12092
55°	12322	12003	11639
60°	11834	11496	11130
65°	11405	10942	10603
70°	10770	10313	9854
75°	9844	9491	9087
80°	8877	8498	8424
85°	7793	7497	7188



TEST NUMBER: P332203-940

CATALOG NUMBER: S123DIW-S1000D1320U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	133.0	1.7
10°-20°	375.4	4.8
20°-30°	554.6	7.1
30°-40°	647.8	8.4
40°-50°	651.3	8.4
50°-60°	572.1	7.4
60°-70°	426.2	5.5
70°-80°	242.8	3.1
80°-90°	74.0	1.0
90°-100°	95.9	1.2
100°-110°	287.1	3.7
110°-120°	488.2	6.3
120°-130°	642.2	8.3
130°-140°	721.9	9.3
140°-150°	709.6	9.1
150°-160°	597.3	7.7
160°-170°	397.6	5.1
170°-180°	139.2	1.8
0°-30°	1062.9	13.7
0°-40°	1710.7	22.1
0°-60°	2934.1	37.8
0°-90°	3677.1	47.4
90°-120°	871.3	11.2
90°-150°	2944.9	38.0
90°-180°	4079.0	52.6
0°-180°	7756.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1412	1412	1412	1412	1412	
5°	1413	1406	1393	1405	1403	134
15°	1345	1339	1324	1333	1326	379
25°	1221	1213	1198	1199	1195	562
35°	1056	1048	1033	1026	1020	660
45°	865	860	845	831	824	668
55°	657	655	640	627	620	588
65°	448	441	430	420	416	442
75°	237	232	228	222	218	253
85°	63	61	61	58	58	69
90°	1	13	28	32	35	8
95°	68	76	86	90	90	77
105°	260	263	273	273	275	279
115°	492	495	493	494	493	486
125°	719	723	720	716	711	641
135°	933	940	939	935	932	719
145°	1132	1135	1138	1137	1132	707
155°	1296	1297	1298	1302	1294	597
165°	1412	1409	1409	1415	1408	398
175°	1469	1464	1464	1470	1463	139
180°	1472	1472	1472	1472	1472	



TEST NUMBER: P332203-940

CATALOG NUMBER: S123DIW-S1000D1320U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5
2.5°	1416.3	1415.5	1414.6	1413.7	1412.9	1411.2	1408.9	1406.5	1404.2	1401.8	1403.9
5°	1412.6	1411.3	1410.0	1408.6	1407.3	1405.2	1402.2	1399.2	1396.2	1393.3	1396.0
7.5°	1398.8	1397.5	1396.2	1394.8	1393.5	1391.2	1388.2	1385.1	1382.1	1378.9	1381.3
10°	1387.2	1385.9	1384.5	1383.1	1381.8	1379.4	1375.9	1372.3	1368.9	1365.4	1367.8
12.5°	1371.6	1370.6	1369.4	1368.2	1367.2	1364.9	1361.6	1358.3	1355.0	1351.7	1353.5
15°	1344.7	1343.6	1342.6	1341.5	1340.4	1338.1	1334.6	1331.1	1327.6	1324.1	1326.2
17.5°	1313.4	1312.0	1310.6	1309.2	1307.8	1305.4	1301.8	1298.3	1294.9	1291.3	1292.8
20°	1290.1	1288.5	1286.9	1285.2	1283.6	1281.0	1277.6	1274.1	1270.6	1267.0	1268.1
22.5°	1263.9	1262.3	1260.7	1259.0	1257.4	1254.9	1251.3	1247.9	1244.4	1240.8	1241.7
25°	1220.9	1219.3	1217.7	1216.1	1214.4	1211.9	1208.4	1204.9	1201.4	1197.8	1198.1
27.5°	1175.1	1173.5	1171.9	1170.4	1168.8	1166.1	1162.3	1158.6	1154.8	1151.0	1151.2
30°	1142.0	1140.7	1139.3	1138.0	1136.7	1134.1	1130.3	1126.5	1122.8	1119.0	1119.0
32.5°	1109.0	1107.2	1105.5	1103.7	1101.9	1099.6	1096.6	1093.8	1090.8	1087.9	1086.4
35°	1055.9	1054.3	1052.7	1051.1	1049.4	1046.9	1043.3	1039.8	1036.3	1032.8	1031.2
37.5°	1001.5	999.4	997.4	995.3	993.3	990.5	986.9	983.4	979.8	976.2	974.3
40°	963.7	962.0	960.4	958.8	957.2	954.5	950.7	946.9	943.2	939.3	937.2
42.5°	925.8	923.9	922.1	920.2	918.5	915.6	911.9	908.1	904.3	900.5	898.4
45°	865.3	864.2	863.2	862.1	861.0	858.7	855.2	851.7	848.2	844.7	841.5
47.5°	805.4	803.8	802.3	800.7	799.2	796.7	793.4	790.1	786.8	783.5	780.3
50°	764.6	763.2	761.9	760.5	759.2	756.8	753.2	749.8	746.3	742.8	739.8
52.5°	721.8	720.9	720.1	719.2	718.2	715.9	712.2	708.5	704.7	701.0	698.5
55°	656.6	656.3	656.0	655.8	655.5	653.6	650.1	646.6	643.1	639.6	636.6
57.5°	594.4	593.5	592.6	591.7	590.8	588.9	586.1	583.3	580.5	577.7	575.1
60°	549.7	549.5	549.2	548.9	548.7	547.0	543.7	540.5	537.3	534.0	531.5
62.5°	510.0	509.3	508.5	507.8	507.2	505.2	501.9	498.7	495.5	492.2	489.8
65°	447.8	446.5	445.1	443.8	442.5	440.4	437.7	435.1	432.3	429.6	427.5
67.5°	382.1	380.8	379.7	378.5	377.3	375.7	373.6	371.6	369.5	367.5	365.6
70°	342.2	340.6	339.0	337.4	335.8	334.1	332.5	330.9	329.3	327.7	325.8
72.5°	300.5	299.3	298.1	296.9	295.8	294.3	292.4	290.6	288.7	286.9	285.3
75°	236.7	235.6	234.5	233.4	232.4	231.4	230.6	229.8	229.0	228.2	226.9
77.5°	180.1	179.5	178.9	178.3	177.7	176.9	176.0	175.0	174.1	173.1	172.2
80°	143.2	142.4	141.6	140.8	140.0	139.3	138.8	138.2	137.7	137.1	136.9
82.5°	107.3	107.1	107.0	106.8	106.6	106.5	106.4	106.3	106.2	106.1	105.6
85°	63.1	62.6	62.1	61.5	61.0	60.7	60.7	60.7	60.7	60.7	60.1
87.5°	25.5	25.3	25.2	25.1	25.0	25.1	25.6	26.0	26.5	26.9	26.9
90°	1.2	3.7	6.3	8.8	11.4	14.4	17.7	21.0	24.4	27.7	28.8
92.5°	28.0	29.7	31.5	33.3	35.0	36.8	38.7	40.6	42.5	44.4	45.2
95°	68.2	70.0	71.9	73.7	75.4	77.4	79.5	81.5	83.6	85.6	86.6
97.5°	121.2	122.5	123.9	125.2	126.5	128.0	129.5	130.9	132.4	133.9	135.1
100°	157.3	158.8	160.3	161.9	163.5	164.9	166.1	167.5	168.7	170.0	170.8
102.5°	198.9	199.8	200.8	201.7	202.6	203.9	205.6	207.3	209.0	210.7	211.5
105°	260.2	260.7	261.3	261.7	262.3	263.7	266.0	268.3	270.6	273.0	273.0
107.5°	331.4	331.8	332.1	332.4	332.7	333.3	334.2	335.2	336.1	337.0	337.9
110°	375.9	376.4	376.9	377.4	377.9	378.4	379.0	379.5	380.0	380.5	381.6



TEST NUMBER: P332203-940

CATALOG NUMBER: S123DIW-S1000D1320U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	422.1	422.4	422.8	423.0	423.4	423.6	423.7	423.7	423.9	424.0	425.3
115°	491.5	492.3	493.0	493.8	494.6	494.7	494.2	493.7	493.2	492.7	492.9
117.5°	561.4	561.9	562.4	562.9	563.5	563.4	562.7	562.0	561.3	560.7	560.6
120°	604.8	606.4	608.0	609.5	611.0	611.2	609.8	608.6	607.3	606.0	605.7
122.5°	650.2	651.3	652.5	653.6	654.7	655.0	654.2	653.6	652.9	652.3	651.6
125°	719.3	720.1	720.9	721.7	722.5	722.6	722.0	721.6	721.0	720.5	719.5
127.5°	783.2	784.9	786.5	788.1	789.8	790.3	789.8	789.2	788.6	788.1	786.6
130°	825.7	827.8	829.9	832.0	834.0	834.6	833.8	833.1	832.3	831.5	830.5
132.5°	868.3	870.4	872.4	874.5	876.6	877.3	876.7	876.2	875.6	875.0	873.8
135°	933.4	934.9	936.4	937.9	939.5	940.1	939.9	939.6	939.3	939.1	938.1
137.5°	993.5	994.7	996.0	997.3	998.6	999.6	1000.2	1000.9	1001.6	1002.3	1001.1
140°	1035.1	1036.3	1037.7	1038.9	1040.3	1041.0	1041.3	1041.5	1041.8	1042.1	1041.8
142.5°	1073.0	1074.3	1075.6	1076.9	1078.2	1079.1	1079.5	1080.0	1080.4	1080.9	1080.7
145°	1132.2	1132.7	1133.3	1133.8	1134.3	1135.0	1135.7	1136.5	1137.3	1138.0	1137.7
147.5°	1184.0	1185.0	1185.9	1186.9	1187.8	1188.6	1189.3	1190.0	1190.7	1191.4	1191.4
150°	1220.1	1220.7	1221.2	1221.6	1222.2	1222.7	1223.2	1223.7	1224.2	1224.8	1224.8
152.5°	1249.7	1250.4	1251.2	1251.9	1252.6	1253.1	1253.5	1253.7	1254.1	1254.4	1254.8
155°	1296.5	1296.5	1296.5	1296.5	1296.5	1296.6	1296.8	1297.1	1297.4	1297.6	1298.7
157.5°	1336.2	1336.0	1335.6	1335.3	1335.0	1335.0	1335.2	1335.3	1335.6	1335.8	1336.9
160°	1361.2	1360.8	1360.2	1359.7	1359.1	1358.9	1358.9	1358.9	1358.9	1358.9	1360.2
162.5°	1383.4	1382.7	1382.0	1381.3	1380.5	1380.3	1380.5	1380.7	1380.9	1381.1	1382.4
165°	1412.1	1411.3	1410.6	1409.8	1409.1	1408.6	1408.6	1408.6	1408.6	1408.6	1410.2
167.5°	1435.0	1434.0	1433.0	1431.9	1430.9	1430.5	1430.7	1430.9	1431.1	1431.3	1432.9
170°	1448.0	1447.0	1445.9	1444.9	1443.9	1443.3	1443.3	1443.3	1443.3	1443.3	1445.1
172.5°	1458.1	1457.1	1456.1	1455.1	1454.0	1453.5	1453.5	1453.5	1453.5	1453.5	1455.1
175°	1468.8	1467.8	1466.8	1465.7	1464.6	1464.2	1464.2	1464.2	1464.2	1464.2	1465.7
177.5°	1473.2	1472.4	1471.5	1470.7	1469.9	1469.5	1469.5	1469.5	1469.5	1469.5	1470.7
180°	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3



TEST NUMBER: P332203-940

CATALOG NUMBER: S123DIW-S1000D1320U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5	1411.5
2.5°	1406.0	1408.3	1410.4	1411.4	1411.1	1411.0	1410.7	1410.5
5°	1398.6	1401.3	1404.1	1405.2	1404.6	1404.1	1403.6	1403.0
7.5°	1383.8	1386.3	1388.7	1389.7	1389.4	1389.1	1388.8	1388.4
10°	1370.2	1372.6	1375.1	1376.0	1375.5	1374.9	1374.4	1373.9
12.5°	1355.3	1357.1	1358.9	1359.6	1359.3	1359.0	1358.6	1358.3
15°	1328.4	1330.5	1332.8	1333.0	1331.4	1329.7	1328.1	1326.5
17.5°	1294.3	1295.8	1297.4	1297.8	1297.3	1296.6	1296.0	1295.5
20°	1269.2	1270.3	1271.4	1271.5	1270.7	1269.9	1269.1	1268.3
22.5°	1242.6	1243.4	1244.3	1244.2	1243.2	1242.2	1241.2	1240.1
25°	1198.4	1198.7	1199.0	1198.7	1197.8	1197.0	1196.2	1195.4
27.5°	1151.5	1151.6	1151.9	1151.5	1150.5	1149.4	1148.4	1147.4
30°	1119.0	1119.0	1119.0	1118.0	1116.2	1114.3	1112.4	1110.4
32.5°	1084.9	1083.4	1081.9	1080.6	1079.6	1078.5	1077.5	1076.5
35°	1029.6	1028.0	1026.4	1024.8	1023.5	1022.2	1020.8	1019.5
37.5°	972.4	970.4	968.5	967.1	966.3	965.4	964.5	963.7
40°	935.0	932.9	930.8	929.1	928.0	926.9	925.9	924.8
42.5°	896.2	894.0	891.9	890.3	889.2	888.1	887.1	886.0
45°	838.2	835.0	831.8	829.5	828.1	826.8	825.5	824.0
47.5°	777.1	774.0	770.8	768.7	767.4	766.2	765.1	763.8
50°	736.8	733.9	730.8	728.6	727.0	725.3	723.7	722.1
52.5°	695.9	693.4	690.9	688.8	687.2	685.5	683.9	682.3
55°	633.6	630.7	627.8	625.5	624.2	622.9	621.5	620.2
57.5°	572.4	569.8	567.1	565.0	563.5	561.9	560.4	558.7
60°	529.1	526.7	524.3	522.5	521.0	519.7	518.4	517.0
62.5°	487.4	485.0	482.5	480.9	479.9	479.0	478.1	477.2
65°	425.3	423.1	421.0	419.5	418.7	417.9	417.1	416.3
67.5°	363.7	361.9	360.0	358.5	357.3	356.1	355.0	353.9
70°	323.9	322.0	320.1	318.5	317.2	315.8	314.5	313.1
72.5°	283.6	281.9	280.2	279.0	278.3	277.6	277.0	276.3
75°	225.5	224.1	222.7	221.7	220.9	220.1	219.3	218.5
77.5°	171.2	170.3	169.4	169.0	169.0	169.0	169.0	169.0
80°	136.6	136.3	136.1	135.9	135.9	135.9	135.9	135.9
82.5°	105.1	104.6	104.2	103.8	103.5	103.3	103.2	102.9
85°	59.6	59.0	58.5	58.2	58.2	58.2	58.2	58.2
87.5°	26.9	26.8	26.8	26.9	27.0	27.1	27.2	27.3
90°	29.8	30.9	31.8	32.6	33.2	33.7	34.2	34.7
92.5°	46.0	46.9	47.7	48.0	47.6	47.3	47.0	46.7
95°	87.7	88.6	89.7	90.2	90.2	90.2	90.2	90.2
97.5°	136.3	137.5	138.7	139.2	139.1	139.0	138.9	138.8
100°	171.6	172.3	173.1	173.7	174.2	174.8	175.3	175.8
102.5°	212.2	213.0	213.8	214.1	214.0	213.9	213.8	213.7
105°	273.0	273.0	273.0	273.2	273.8	274.2	274.7	275.3
107.5°	338.7	339.5	340.3	340.5	340.3	339.9	339.7	339.3
110°	382.5	383.6	384.6	384.9	384.3	383.9	383.3	382.8



TEST NUMBER: P332203-940

CATALOG NUMBER: S123DIW-S1000D1320U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	426.4	427.7	428.9	429.4	429.4	429.3	429.2	429.1
115°	493.2	493.5	493.7	493.7	493.5	493.2	492.9	492.7
117.5°	560.6	560.5	560.4	560.1	559.4	558.7	557.9	557.2
120°	605.5	605.3	605.0	604.6	604.1	603.6	603.1	602.5
122.5°	650.9	650.2	649.6	648.9	648.2	647.5	646.8	646.0
125°	718.5	717.5	716.4	715.4	714.3	713.3	712.3	711.2
127.5°	785.2	783.7	782.3	781.0	779.8	778.6	777.5	776.2
130°	829.5	828.5	827.4	826.0	824.2	822.4	820.6	818.9
132.5°	872.5	871.3	870.1	868.8	867.4	866.0	864.6	863.3
135°	937.0	936.0	935.0	934.2	933.7	933.2	932.6	932.2
137.5°	1000.1	999.0	997.9	996.9	996.0	995.0	994.0	993.0
140°	1041.5	1041.3	1041.0	1040.0	1038.2	1036.3	1034.6	1032.8
142.5°	1080.4	1080.1	1079.9	1079.1	1077.6	1076.3	1074.9	1073.5
145°	1137.5	1137.3	1137.0	1136.4	1135.3	1134.3	1133.3	1132.2
147.5°	1191.4	1191.4	1191.4	1190.7	1189.2	1187.6	1186.1	1184.5
150°	1224.8	1224.8	1224.8	1224.0	1222.4	1220.9	1219.3	1217.8
152.5°	1255.2	1255.6	1256.0	1255.5	1254.2	1252.9	1251.5	1250.2
155°	1299.7	1300.7	1301.7	1301.4	1299.6	1297.8	1295.9	1294.1
157.5°	1337.9	1339.0	1340.2	1339.9	1338.5	1337.0	1335.6	1334.2
160°	1361.5	1362.8	1364.1	1364.2	1363.2	1362.2	1361.1	1360.0
162.5°	1383.7	1385.0	1386.3	1386.1	1384.5	1382.8	1381.2	1379.5
165°	1411.8	1413.3	1414.8	1414.7	1412.9	1411.1	1409.3	1407.5
167.5°	1434.5	1436.1	1437.7	1437.7	1436.1	1434.5	1432.9	1431.3
170°	1447.0	1448.8	1450.5	1450.5	1448.8	1447.0	1445.1	1443.3
172.5°	1456.7	1458.3	1459.9	1459.8	1458.0	1456.2	1454.4	1452.6
175°	1467.2	1468.8	1470.3	1470.2	1468.4	1466.6	1464.8	1463.0
177.5°	1471.9	1473.2	1474.4	1474.4	1472.8	1471.4	1470.0	1468.6
180°	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3

(END OF REPORT)