

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332833-830

Luminaire Tested: **S124DIW-S1020D1560U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332833-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S1020D1560U830-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10057.5 lumens
Efficiency: N/A
Efficacy: 131.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332833-830

CATALOG NUMBER: S124DIW-S1020D1560U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332833-830

CATALOG NUMBER: S124DIW-S1020D1560U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48	42
1	96	92	88	84	87	84	80	77	69	67	64	55	54	52	43	42	41	35
2	87	80	74	69	79	73	68	63	60	57	53	48	46	44	38	36	34	29
3	80	70	63	57	72	64	58	53	53	49	45	43	40	37	33	31	29	25
4	73	62	54	48	66	57	50	45	47	42	38	38	34	32	30	27	25	21
5	67	55	47	41	61	51	44	38	42	37	33	34	30	27	27	24	22	18
6	61	50	42	36	56	46	38	33	38	33	29	31	27	24	24	21	19	16
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17	14
8	53	40	33	28	48	37	31	26	31	26	22	26	22	19	20	17	15	13
9	49	37	30	25	45	34	27	23	29	23	20	24	20	17	19	16	14	12
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13130	13130	13130
5°	13169	13011	13105
10°	13086	12904	12969
15°	12929	12721	12754
20°	12718	12494	12506
25°	12479	12235	12200
30°	12185	11929	11820
35°	11880	11610	11456
40°	11564	11248	11041
45°	11233	10891	10683
50°	10868	10574	10246
55°	10473	10162	9831
60°	10078	9700	9405
65°	9635	9259	8886
70°	9135	8674	8337
75°	8372	7966	7764
80°	7452	7146	6969
85°	6521	6280	6150



TEST NUMBER: P332833-830

CATALOG NUMBER: S124DIW-S1020D1560U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.2	1.5
10°-20°	431.5	4.3
20°-30°	635.2	6.3
30°-40°	738.4	7.3
40°-50°	738.4	7.3
50°-60°	645.9	6.4
60°-70°	479.7	4.8
70°-80°	272.5	2.7
80°-90°	84.1	0.8
90°-100°	65.0	0.6
100°-110°	414.4	4.1
110°-120°	792.8	7.9
120°-130°	1006.4	10.0
130°-140°	1076.8	10.7
140°-150°	1006.9	10.0
150°-160°	812.0	8.1
160°-170°	523.7	5.2
170°-180°	180.5	1.8
0°-30°	1219.8	12.1
0°-40°	1958.2	19.5
0°-60°	3342.6	33.2
0°-90°	4178.9	41.6
90°-120°	1272.2	12.6
90°-150°	4362.3	43.4
90°-180°	5879.0	58.5
0°-180°	10057.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1626	1626	1626	1626	1626	
5°	1625	1619	1606	1619	1617	154
15°	1547	1541	1522	1529	1526	436
25°	1401	1391	1374	1374	1370	644
35°	1205	1196	1178	1169	1162	753
45°	984	974	954	940	936	758
55°	744	739	722	707	698	666
65°	504	497	485	472	465	499
75°	268	262	255	250	249	285
85°	70	70	68	68	66	78
90°	4	20	31	40	43	7
95°	78	33	31	39	41	100
105°	428	436	444	453	405	448
115°	799	803	802	804	805	786
125°	1123	1128	1126	1130	1131	1002
135°	1393	1392	1397	1400	1403	1073
145°	1606	1610	1610	1612	1615	1003
155°	1761	1762	1758	1763	1760	812
165°	1858	1851	1851	1861	1849	525
175°	1900	1892	1893	1904	1889	181
180°	1900	1900	1900	1900	1900	



TEST NUMBER: P332833-830

CATALOG NUMBER: S124DIW-S1020D1560U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4
2.5°	1630.5	1629.8	1629.1	1628.4	1627.8	1626.1	1623.5	1621.0	1618.4	1615.9	1618.3
5°	1625.0	1623.9	1622.8	1621.6	1620.4	1618.3	1615.0	1611.8	1608.7	1605.5	1608.7
7.5°	1610.0	1608.7	1607.6	1606.5	1605.3	1603.0	1599.4	1595.9	1592.3	1588.8	1591.4
10°	1596.4	1595.3	1594.0	1592.9	1591.8	1589.3	1585.5	1581.8	1578.0	1574.2	1576.5
12.5°	1578.7	1577.5	1576.3	1575.2	1574.0	1571.4	1567.4	1563.5	1559.4	1555.5	1558.0
15°	1546.9	1545.7	1544.5	1543.4	1542.2	1539.5	1535.1	1530.8	1526.4	1522.1	1523.8
17.5°	1508.5	1507.1	1505.6	1504.2	1502.8	1500.0	1495.8	1491.8	1487.6	1483.6	1484.6
20°	1480.4	1478.9	1477.5	1476.0	1474.6	1471.7	1467.4	1463.0	1458.7	1454.3	1455.2
22.5°	1450.2	1448.2	1446.3	1444.4	1442.6	1439.4	1435.0	1430.7	1426.3	1422.0	1423.6
25°	1400.9	1398.9	1396.8	1394.8	1392.8	1389.8	1385.7	1381.7	1377.6	1373.6	1373.9
27.5°	1344.6	1342.6	1340.4	1338.3	1336.2	1333.3	1329.6	1325.8	1322.0	1318.2	1317.6
30°	1307.1	1304.8	1302.4	1300.1	1297.8	1294.8	1291.0	1287.2	1283.5	1279.7	1278.6
32.5°	1267.4	1265.4	1263.3	1261.2	1259.1	1256.0	1252.1	1248.1	1244.1	1240.1	1238.7
35°	1205.4	1203.4	1201.4	1199.4	1197.3	1194.3	1190.2	1186.2	1182.1	1178.1	1176.0
37.5°	1140.0	1138.1	1136.3	1134.4	1132.6	1129.5	1125.1	1120.8	1116.4	1112.1	1109.9
40°	1097.3	1095.0	1092.6	1090.3	1088.0	1084.7	1080.3	1076.0	1071.7	1067.3	1064.4
42.5°	1051.4	1050.0	1048.6	1047.3	1045.8	1042.7	1037.9	1033.1	1028.3	1023.5	1020.1
45°	983.9	981.8	979.9	977.8	975.8	972.4	967.8	963.2	958.6	953.9	950.7
47.5°	913.2	911.9	910.5	909.1	907.7	904.8	900.6	896.3	892.0	887.7	884.1
50°	865.3	864.1	863.0	861.9	860.6	858.1	854.0	850.0	845.9	841.9	837.8
52.5°	818.4	817.0	815.6	814.3	812.8	810.0	805.7	801.4	797.1	792.9	789.3
55°	744.1	743.2	742.3	741.5	740.6	738.2	734.1	730.1	726.0	722.0	718.5
57.5°	673.3	672.2	671.3	670.2	669.3	666.8	662.8	658.8	654.8	650.8	647.5
60°	624.2	622.7	621.3	619.9	618.4	615.9	612.1	608.3	604.5	600.8	598.1
62.5°	576.3	575.0	573.8	572.6	571.4	568.8	564.8	560.8	556.8	552.8	550.4
65°	504.4	502.8	501.4	500.0	498.5	496.3	493.4	490.6	487.7	484.7	481.9
67.5°	431.9	430.6	429.2	427.9	426.5	424.5	421.7	419.0	416.1	413.4	410.6
70°	387.0	385.0	383.0	381.0	378.9	376.7	374.5	372.1	369.9	367.5	365.1
72.5°	339.1	337.1	335.1	333.0	331.0	329.0	327.2	325.4	323.5	321.6	319.8
75°	268.4	267.0	265.5	264.1	262.7	261.2	259.8	258.4	256.8	255.4	254.3
77.5°	201.0	200.3	199.6	199.1	198.4	197.5	196.1	194.9	193.6	192.4	192.0
80°	160.3	159.4	158.5	157.7	156.8	156.1	155.5	155.0	154.4	153.7	153.2
82.5°	120.6	120.3	119.9	119.4	119.0	118.8	118.7	118.6	118.5	118.3	118.0
85°	70.4	70.4	70.4	70.4	70.4	70.1	69.5	68.9	68.3	67.8	67.8
87.5°	28.0	28.5	28.8	29.3	29.8	30.2	30.4	30.7	31.0	31.3	31.7
90°	4.2	7.7	11.2	14.7	18.2	21.2	23.7	26.2	28.7	31.3	33.2
92.5°	17.9	18.1	18.3	18.5	18.7	20.0	22.5	25.1	27.6	30.2	32.0
95°	78.1	67.4	56.7	46.0	35.3	30.0	30.3	30.6	30.9	31.3	33.2
97.5°	166.0	172.7	179.4	186.2	192.8	178.5	143.3	108.0	72.8	37.5	37.7
100°	233.1	238.8	244.5	250.2	255.8	236.9	193.3	149.7	106.1	62.6	57.2
102.5°	308.1	312.4	316.5	320.7	324.8	324.0	318.4	312.7	307.0	301.3	243.4
105°	427.8	429.7	431.6	433.6	435.5	437.2	438.8	440.4	441.9	443.5	446.3
107.5°	538.9	540.0	540.9	541.9	542.8	544.3	546.5	548.7	550.7	552.9	554.3
110°	614.1	615.0	616.0	616.9	617.8	619.3	621.1	623.0	624.9	626.8	627.5



TEST NUMBER: P332833-830

CATALOG NUMBER: S124DIW-S1020D1560U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	686.8	688.5	690.2	691.9	693.6	694.9	695.8	696.7	697.6	698.5	698.3
115°	798.8	799.7	800.7	801.6	802.6	803.0	802.6	802.3	802.0	801.6	802.3
117.5°	899.8	901.0	902.3	903.5	904.8	905.8	906.4	907.2	907.9	908.5	908.4
120°	968.0	969.2	970.5	971.8	973.0	973.5	973.2	972.9	972.5	972.2	972.9
122.5°	1031.6	1032.4	1033.1	1033.9	1034.7	1035.3	1035.8	1036.1	1036.6	1037.1	1037.5
125°	1122.9	1124.2	1125.4	1126.7	1127.9	1128.2	1127.7	1127.0	1126.3	1125.8	1126.7
127.5°	1209.3	1209.7	1209.9	1210.2	1210.6	1211.4	1213.0	1214.4	1215.8	1217.3	1217.1
130°	1265.1	1265.4	1265.6	1266.0	1266.3	1267.0	1267.9	1268.9	1269.8	1270.7	1271.0
132.5°	1316.2	1316.7	1317.4	1318.0	1318.5	1319.4	1320.6	1321.7	1323.0	1324.2	1324.5
135°	1393.0	1392.6	1392.3	1392.0	1391.7	1392.1	1393.5	1394.7	1396.0	1397.2	1397.9
137.5°	1460.9	1461.0	1461.1	1461.3	1461.4	1462.2	1463.6	1465.0	1466.3	1467.7	1468.4
140°	1505.2	1505.9	1506.6	1507.1	1507.8	1508.4	1509.0	1509.7	1510.3	1510.9	1511.9
142.5°	1545.0	1546.1	1547.4	1548.5	1549.6	1550.4	1550.8	1551.1	1551.5	1551.9	1552.6
145°	1606.2	1607.1	1608.1	1609.0	1610.0	1610.4	1610.4	1610.4	1610.4	1610.4	1610.7
147.5°	1654.8	1656.5	1658.3	1660.1	1661.9	1662.6	1662.3	1662.0	1661.6	1661.3	1661.6
150°	1690.1	1691.3	1692.5	1693.8	1695.1	1695.5	1695.3	1695.0	1694.6	1694.3	1694.3
152.5°	1719.6	1720.6	1721.6	1722.6	1723.6	1723.9	1723.3	1722.7	1722.1	1721.6	1722.1
155°	1761.1	1761.4	1761.7	1762.1	1762.4	1762.1	1761.1	1760.2	1759.3	1758.2	1759.5
157.5°	1796.1	1795.9	1795.7	1795.5	1795.4	1794.7	1793.6	1792.5	1791.5	1790.4	1792.1
160°	1816.6	1815.6	1814.7	1813.7	1812.8	1812.1	1811.8	1811.5	1811.2	1810.8	1812.8
162.5°	1834.8	1833.5	1832.3	1831.2	1829.9	1829.2	1828.8	1828.5	1828.2	1827.9	1829.8
165°	1857.8	1856.1	1854.6	1853.0	1851.4	1850.7	1850.7	1850.7	1850.7	1850.7	1853.1
167.5°	1875.9	1874.3	1872.6	1871.0	1869.3	1868.5	1868.3	1868.1	1867.9	1867.7	1870.5
170°	1886.2	1884.3	1882.4	1880.5	1878.6	1877.8	1878.1	1878.5	1878.8	1879.1	1881.6
172.5°	1893.0	1891.1	1889.2	1887.3	1885.5	1884.6	1885.0	1885.3	1885.6	1885.9	1888.4
175°	1900.4	1898.5	1896.6	1894.7	1892.8	1892.1	1892.3	1892.6	1893.0	1893.3	1896.1
177.5°	1903.8	1902.1	1900.3	1898.5	1896.8	1896.1	1896.6	1897.1	1897.6	1898.1	1900.2
180°	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4



TEST NUMBER: P332833-830

CATALOG NUMBER: S124DIW-S1020D1560U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4
2.5°	1620.5	1622.9	1625.2	1626.3	1626.0	1625.8	1625.5	1625.3
5°	1611.8	1615.0	1618.3	1619.6	1619.0	1618.3	1617.8	1617.2
7.5°	1593.9	1596.5	1599.0	1600.2	1599.8	1599.4	1599.0	1598.7
10°	1578.9	1581.2	1583.5	1584.3	1583.8	1583.2	1582.6	1582.1
12.5°	1560.6	1563.1	1565.7	1566.5	1565.8	1564.9	1564.1	1563.3
15°	1525.6	1527.3	1529.1	1529.5	1528.6	1527.8	1526.9	1526.0
17.5°	1485.7	1486.9	1487.9	1488.2	1487.6	1487.0	1486.5	1485.8
20°	1456.0	1457.0	1457.8	1457.9	1457.4	1456.8	1456.2	1455.7
22.5°	1425.1	1426.7	1428.2	1428.5	1427.5	1426.4	1425.4	1424.4
25°	1374.1	1374.4	1374.7	1374.2	1373.1	1372.0	1370.7	1369.6
27.5°	1316.9	1316.2	1315.5	1314.5	1313.0	1311.5	1310.0	1308.6
30°	1277.4	1276.2	1275.1	1273.8	1272.3	1270.8	1269.4	1268.0
32.5°	1237.3	1236.0	1234.5	1233.1	1231.6	1230.2	1228.8	1227.3
35°	1174.0	1172.0	1170.0	1168.2	1166.8	1165.4	1163.9	1162.4
37.5°	1107.7	1105.5	1103.3	1101.3	1099.4	1097.4	1095.5	1093.6
40°	1061.5	1058.6	1055.7	1053.6	1052.1	1050.7	1049.2	1047.7
42.5°	1016.8	1013.4	1010.0	1007.9	1006.9	1005.9	1004.9	1004.0
45°	947.5	944.3	941.1	939.1	938.3	937.5	936.5	935.7
47.5°	880.5	876.9	873.4	870.4	868.3	866.0	863.8	861.7
50°	833.8	829.7	825.7	822.7	821.0	819.3	817.6	815.8
52.5°	785.7	782.0	778.4	775.6	773.4	771.2	769.0	766.8
55°	715.0	711.5	708.0	705.5	703.7	702.0	700.2	698.5
57.5°	644.2	640.9	637.6	635.1	633.4	631.8	630.1	628.4
60°	595.6	593.0	590.3	588.3	586.8	585.4	584.0	582.5
62.5°	548.1	545.6	543.3	541.4	540.0	538.5	537.1	535.6
65°	479.0	476.1	473.2	471.0	469.6	468.2	466.7	465.2
67.5°	407.8	405.0	402.3	400.7	400.2	399.8	399.4	399.1
70°	362.9	360.5	358.3	356.7	355.8	354.9	354.0	353.2
72.5°	317.9	316.0	314.2	312.8	312.0	311.1	310.3	309.3
75°	253.1	251.9	250.8	250.1	249.8	249.5	249.2	248.9
77.5°	191.6	191.3	191.0	190.4	189.6	188.9	188.1	187.4
80°	152.6	152.0	151.5	151.0	150.7	150.4	150.1	149.9
82.5°	117.6	117.3	117.0	116.6	116.3	116.0	115.7	115.5
85°	67.8	67.8	67.8	67.6	67.3	67.0	66.7	66.4
87.5°	32.0	32.4	32.8	33.1	33.2	33.3	33.5	33.6
90°	35.1	36.9	38.8	40.2	40.7	41.4	42.0	42.6
92.5°	33.9	35.8	37.7	38.7	38.8	39.0	39.1	39.2
95°	35.1	36.9	38.8	40.0	40.2	40.6	40.9	41.2
97.5°	37.9	38.1	38.3	38.5	38.8	39.2	39.5	39.8
100°	51.8	46.5	41.1	38.5	38.8	39.2	39.5	39.8
102.5°	185.5	127.5	69.7	40.7	40.7	40.8	40.9	40.9
105°	449.1	452.0	454.9	450.5	439.2	427.8	416.5	405.1
107.5°	555.7	557.1	558.5	559.8	561.0	562.1	563.4	564.6
110°	628.1	628.8	629.3	630.2	631.1	632.1	633.0	634.0



TEST NUMBER: P332833-830

CATALOG NUMBER: S124DIW-S1020D1560U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	698.2	698.0	698.0	698.5	699.7	700.9	702.1	703.3
115°	803.0	803.5	804.2	804.6	804.6	804.6	804.6	804.6
117.5°	908.3	908.1	908.0	908.0	907.8	907.7	907.6	907.4
120°	973.5	974.1	974.8	974.8	974.1	973.5	972.9	972.2
122.5°	1037.8	1038.2	1038.6	1038.4	1037.8	1037.2	1036.5	1035.9
125°	1127.7	1128.6	1129.5	1130.2	1130.5	1130.8	1131.1	1131.4
127.5°	1216.9	1216.7	1216.5	1216.3	1216.1	1215.8	1215.5	1215.3
130°	1271.4	1271.7	1272.0	1272.1	1272.1	1272.1	1272.1	1272.1
132.5°	1324.8	1325.1	1325.4	1325.5	1325.2	1324.9	1324.7	1324.5
135°	1398.5	1399.1	1399.8	1400.4	1401.0	1401.7	1402.3	1402.9
137.5°	1469.1	1469.8	1470.6	1470.7	1470.6	1470.4	1470.2	1470.0
140°	1512.9	1513.8	1514.8	1515.3	1515.7	1516.0	1516.3	1516.6
142.5°	1553.3	1554.0	1554.6	1555.0	1555.1	1555.2	1555.2	1555.3
145°	1611.1	1611.4	1611.7	1612.2	1612.8	1613.4	1614.1	1614.7
147.5°	1661.8	1662.1	1662.4	1662.6	1662.9	1663.2	1663.6	1663.9
150°	1694.3	1694.3	1694.3	1694.5	1694.8	1695.1	1695.4	1695.7
152.5°	1722.6	1723.1	1723.6	1723.7	1723.5	1723.3	1723.2	1723.0
155°	1760.8	1762.1	1763.3	1763.5	1762.6	1761.6	1760.7	1759.7
157.5°	1793.7	1795.4	1797.0	1797.0	1795.4	1793.7	1792.1	1790.4
160°	1814.7	1816.6	1818.4	1818.4	1816.6	1814.7	1812.8	1810.8
162.5°	1831.7	1833.6	1835.5	1835.3	1833.2	1831.1	1828.9	1826.7
165°	1855.7	1858.2	1860.8	1860.6	1857.8	1854.9	1852.1	1849.3
167.5°	1873.3	1876.0	1878.9	1878.7	1875.5	1872.4	1869.2	1866.0
170°	1884.1	1886.7	1889.2	1888.9	1885.7	1882.5	1879.4	1876.2
172.5°	1890.9	1893.5	1896.0	1895.5	1892.2	1888.8	1885.4	1881.9
175°	1898.9	1901.9	1904.7	1904.2	1900.4	1896.6	1892.8	1889.0
177.5°	1902.1	1904.2	1906.2	1905.7	1902.7	1899.6	1896.6	1893.6
180°	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4

(END OF REPORT)