

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332809-830

Luminaire Tested: **S124DIW-S1020D470U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332809-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S1020D470U830-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 470 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5941.8 lumens
Efficiency: N/A
Efficacy: 128.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 46.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332809-830

CATALOG NUMBER: S124DIW-S1020D470U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332809-830

CATALOG NUMBER: S124DIW-S1020D470U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	95	95	95	84	84	84	75	75	75	70
1	102	98	94	90	97	93	89	86	83	80	78	74	72	70	66	64	63	59
2	93	85	79	74	88	81	75	70	73	68	64	65	62	59	58	55	53	49
3	85	75	67	61	80	71	64	59	64	59	54	58	53	50	51	48	45	42
4	78	67	58	52	73	63	56	50	57	51	46	51	47	43	46	42	39	36
5	72	59	51	45	67	57	49	43	51	45	40	46	41	37	41	37	34	31
6	66	53	45	39	62	51	43	38	46	40	35	42	37	32	38	33	30	27
7	61	48	40	34	58	46	39	33	42	36	31	38	33	29	34	30	27	24
8	57	44	36	31	54	42	35	30	38	32	28	35	30	26	32	27	24	22
9	53	40	33	27	50	39	31	27	35	29	25	32	27	23	29	25	22	20
10	50	37	30	25	47	36	29	24	33	27	23	30	25	21	27	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13130	13130	13130
5°	13169	13011	13105
10°	13086	12904	12969
15°	12929	12721	12754
20°	12718	12494	12506
25°	12479	12235	12200
30°	12185	11929	11820
35°	11880	11610	11456
40°	11564	11248	11041
45°	11233	10891	10683
50°	10868	10574	10246
55°	10473	10162	9831
60°	10078	9700	9405
65°	9635	9259	8886
70°	9135	8674	8337
75°	8372	7966	7764
80°	7452	7146	6969
85°	6521	6280	6150



TEST NUMBER: P332809-830

CATALOG NUMBER: S124DIW-S1020D470U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.2	2.6
10°-20°	431.5	7.3
20°-30°	635.2	10.7
30°-40°	738.4	12.4
40°-50°	738.4	12.4
50°-60°	645.9	10.9
60°-70°	479.7	8.1
70°-80°	272.5	4.6
80°-90°	80.3	1.4
90°-100°	19.5	0.3
100°-110°	124.6	2.1
110°-120°	238.3	4.0
120°-130°	302.4	5.1
130°-140°	323.6	5.4
140°-150°	302.6	5.1
150°-160°	244.0	4.1
160°-170°	157.4	2.6
170°-180°	54.2	0.9
0°-30°	1219.8	20.5
0°-40°	1958.2	33.0
0°-60°	3342.6	56.3
0°-90°	4175.1	70.3
90°-120°	382.4	6.4
90°-150°	1311.0	22.1
90°-180°	1767.0	29.7
0°-180°	5941.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1626	1626	1626	1626	1626	
5°	1625	1619	1606	1619	1617	154
15°	1547	1541	1522	1529	1526	436
25°	1401	1391	1374	1374	1370	644
35°	1205	1196	1178	1169	1162	753
45°	984	974	954	940	936	758
55°	744	739	722	707	698	666
65°	504	497	485	472	465	499
75°	268	262	255	250	249	285
85°	70	70	68	68	66	77
90°	1	6	9	12	13	5
95°	24	10	9	12	12	30
105°	129	131	133	136	122	135
115°	240	241	241	242	242	236
125°	337	339	338	340	340	301
135°	419	418	420	421	422	322
145°	483	484	484	484	485	301
155°	529	530	528	530	529	244
165°	558	556	556	559	556	158
175°	571	569	569	572	568	54
180°	571	571	571	571	571	



TEST NUMBER: P332809-830

CATALOG NUMBER: S124DIW-S1020D470U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4
2.5°	1630.5	1629.8	1629.1	1628.4	1627.8	1626.1	1623.5	1621.0	1618.4	1615.9	1618.3
5°	1625.0	1623.9	1622.8	1621.6	1620.4	1618.3	1615.0	1611.8	1608.7	1605.5	1608.7
7.5°	1610.0	1608.7	1607.6	1606.5	1605.3	1603.0	1599.4	1595.9	1592.3	1588.8	1591.4
10°	1596.4	1595.3	1594.0	1592.9	1591.8	1589.3	1585.5	1581.8	1578.0	1574.2	1576.5
12.5°	1578.7	1577.5	1576.3	1575.2	1574.0	1571.4	1567.4	1563.5	1559.4	1555.5	1558.0
15°	1546.9	1545.7	1544.5	1543.4	1542.2	1539.5	1535.1	1530.8	1526.4	1522.1	1523.8
17.5°	1508.5	1507.1	1505.6	1504.2	1502.8	1500.0	1495.8	1491.8	1487.6	1483.6	1484.6
20°	1480.4	1478.9	1477.5	1476.0	1474.6	1471.7	1467.4	1463.0	1458.7	1454.3	1455.2
22.5°	1450.2	1448.2	1446.3	1444.4	1442.6	1439.4	1435.0	1430.7	1426.3	1422.0	1423.6
25°	1400.9	1398.9	1396.8	1394.8	1392.8	1389.8	1385.7	1381.7	1377.6	1373.6	1373.9
27.5°	1344.6	1342.6	1340.4	1338.3	1336.2	1333.3	1329.6	1325.8	1322.0	1318.2	1317.6
30°	1307.1	1304.8	1302.4	1300.1	1297.8	1294.8	1291.0	1287.2	1283.5	1279.7	1278.6
32.5°	1267.4	1265.4	1263.3	1261.2	1259.1	1256.0	1252.1	1248.1	1244.1	1240.1	1238.7
35°	1205.4	1203.4	1201.4	1199.4	1197.3	1194.3	1190.2	1186.2	1182.1	1178.1	1176.0
37.5°	1140.0	1138.1	1136.3	1134.4	1132.6	1129.5	1125.1	1120.8	1116.4	1112.1	1109.9
40°	1097.3	1095.0	1092.6	1090.3	1088.0	1084.7	1080.3	1076.0	1071.7	1067.3	1064.4
42.5°	1051.4	1050.0	1048.6	1047.3	1045.8	1042.7	1037.9	1033.1	1028.3	1023.5	1020.1
45°	983.9	981.8	979.9	977.8	975.8	972.4	967.8	963.2	958.6	953.9	950.7
47.5°	913.2	911.9	910.5	909.1	907.7	904.8	900.6	896.3	892.0	887.7	884.1
50°	865.3	864.1	863.0	861.9	860.6	858.1	854.0	850.0	845.9	841.9	837.8
52.5°	818.4	817.0	815.6	814.3	812.8	810.0	805.7	801.4	797.1	792.9	789.3
55°	744.1	743.2	742.3	741.5	740.6	738.2	734.1	730.1	726.0	722.0	718.5
57.5°	673.3	672.2	671.3	670.2	669.3	666.8	662.8	658.8	654.8	650.8	647.5
60°	624.2	622.7	621.3	619.9	618.4	615.9	612.1	608.3	604.5	600.8	598.1
62.5°	576.3	575.0	573.8	572.6	571.4	568.8	564.8	560.8	556.8	552.8	550.4
65°	504.4	502.8	501.4	500.0	498.5	496.3	493.4	490.6	487.7	484.7	481.9
67.5°	431.9	430.6	429.2	427.9	426.5	424.5	421.7	419.0	416.1	413.4	410.6
70°	387.0	385.0	383.0	381.0	378.9	376.7	374.5	372.1	369.9	367.5	365.1
72.5°	339.1	337.1	335.1	333.0	331.0	329.0	327.2	325.4	323.5	321.6	319.8
75°	268.4	267.0	265.5	264.1	262.7	261.2	259.8	258.4	256.8	255.4	254.3
77.5°	201.0	200.3	199.6	199.1	198.4	197.5	196.1	194.9	193.6	192.4	192.0
80°	160.3	159.4	158.5	157.7	156.8	156.1	155.5	155.0	154.4	153.7	153.2
82.5°	120.6	120.3	119.9	119.4	119.0	118.8	118.7	118.6	118.5	118.3	118.0
85°	70.4	70.4	70.4	70.4	70.4	70.1	69.5	68.9	68.3	67.8	67.8
87.5°	27.3	27.3	27.3	27.3	27.2	27.2	27.1	27.1	27.0	26.9	27.1
90°	1.3	2.4	3.4	4.4	5.5	6.3	7.2	7.9	8.7	9.4	10.0
92.5°	5.4	5.5	5.5	5.6	5.7	6.0	6.8	7.5	8.3	9.0	9.6
95°	23.5	20.3	17.1	13.9	10.6	9.0	9.1	9.2	9.3	9.4	10.0
97.5°	49.9	51.9	53.9	55.9	58.0	53.6	43.1	32.4	21.9	11.3	11.3
100°	70.0	71.7	73.5	75.2	76.9	71.2	58.1	45.0	31.9	18.8	17.2
102.5°	92.7	93.9	95.1	96.3	97.6	97.4	95.7	94.0	92.3	90.6	73.1
105°	128.6	129.1	129.7	130.3	130.8	131.4	131.9	132.3	132.8	133.3	134.1
107.5°	162.0	162.3	162.6	162.9	163.2	163.6	164.2	164.9	165.5	166.2	166.5
110°	184.5	184.8	185.1	185.4	185.7	186.1	186.6	187.3	187.8	188.4	188.6



TEST NUMBER: P332809-830

CATALOG NUMBER: S124DIW-S1020D470U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	206.4	206.9	207.5	207.9	208.5	208.9	209.2	209.3	209.6	209.9	209.9
115°	240.1	240.3	240.6	240.9	241.2	241.3	241.2	241.1	241.0	240.9	241.1
117.5°	270.4	270.8	271.2	271.5	271.9	272.2	272.4	272.6	272.9	273.1	273.0
120°	290.9	291.2	291.6	292.0	292.4	292.6	292.5	292.4	292.3	292.2	292.4
122.5°	310.0	310.3	310.5	310.8	310.9	311.1	311.2	311.4	311.5	311.7	311.8
125°	337.4	337.8	338.2	338.6	338.9	339.0	338.8	338.7	338.5	338.3	338.6
127.5°	363.4	363.5	363.6	363.7	363.8	364.1	364.5	365.0	365.4	365.8	365.8
130°	380.1	380.2	380.4	380.5	380.6	380.8	381.1	381.4	381.6	381.9	382.0
132.5°	395.6	395.7	395.9	396.1	396.2	396.5	396.9	397.2	397.6	397.9	398.0
135°	418.6	418.5	418.4	418.3	418.2	418.4	418.8	419.1	419.5	419.9	420.1
137.5°	439.0	439.0	439.1	439.1	439.2	439.4	439.8	440.3	440.6	441.1	441.3
140°	452.3	452.5	452.7	452.9	453.1	453.3	453.5	453.7	453.9	454.1	454.4
142.5°	464.3	464.7	465.1	465.3	465.7	465.9	466.0	466.2	466.3	466.4	466.6
145°	482.7	483.0	483.2	483.5	483.8	484.0	484.0	484.0	484.0	484.0	484.1
147.5°	497.3	497.9	498.3	498.9	499.5	499.6	499.5	499.5	499.4	499.3	499.4
150°	507.9	508.3	508.7	509.1	509.4	509.5	509.4	509.3	509.3	509.2	509.2
152.5°	516.8	517.1	517.4	517.6	518.0	518.0	517.9	517.7	517.6	517.4	517.6
155°	529.2	529.3	529.4	529.5	529.6	529.5	529.2	529.0	528.7	528.4	528.8
157.5°	539.8	539.7	539.6	539.6	539.5	539.3	539.0	538.7	538.4	538.1	538.6
160°	545.9	545.6	545.4	545.1	544.8	544.6	544.5	544.4	544.3	544.2	544.8
162.5°	551.4	551.0	550.6	550.3	550.0	549.7	549.6	549.5	549.4	549.3	549.9
165°	558.3	557.8	557.3	556.9	556.4	556.2	556.2	556.2	556.2	556.2	556.9
167.5°	563.7	563.3	562.8	562.3	561.8	561.5	561.5	561.4	561.4	561.3	562.1
170°	566.8	566.3	565.7	565.1	564.6	564.3	564.4	564.5	564.6	564.7	565.4
172.5°	568.9	568.4	567.8	567.2	566.7	566.4	566.5	566.6	566.7	566.8	567.5
175°	571.1	570.5	570.0	569.4	568.8	568.6	568.7	568.8	568.9	569.0	569.9
177.5°	572.1	571.7	571.1	570.5	570.0	569.9	570.0	570.1	570.2	570.4	571.0
180°	571.1	571.1	571.1	571.1	571.1	571.1	571.1	571.1	571.1	571.1	571.1



TEST NUMBER: P332809-830

CATALOG NUMBER: S124DIW-S1020D470U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4
2.5°	1620.5	1622.9	1625.2	1626.3	1626.0	1625.8	1625.5	1625.3
5°	1611.8	1615.0	1618.3	1619.6	1619.0	1618.3	1617.8	1617.2
7.5°	1593.9	1596.5	1599.0	1600.2	1599.8	1599.4	1599.0	1598.7
10°	1578.9	1581.2	1583.5	1584.3	1583.8	1583.2	1582.6	1582.1
12.5°	1560.6	1563.1	1565.7	1566.5	1565.8	1564.9	1564.1	1563.3
15°	1525.6	1527.3	1529.1	1529.5	1528.6	1527.8	1526.9	1526.0
17.5°	1485.7	1486.9	1487.9	1488.2	1487.6	1487.0	1486.5	1485.8
20°	1456.0	1457.0	1457.8	1457.9	1457.4	1456.8	1456.2	1455.7
22.5°	1425.1	1426.7	1428.2	1428.5	1427.5	1426.4	1425.4	1424.4
25°	1374.1	1374.4	1374.7	1374.2	1373.1	1372.0	1370.7	1369.6
27.5°	1316.9	1316.2	1315.5	1314.5	1313.0	1311.5	1310.0	1308.6
30°	1277.4	1276.2	1275.1	1273.8	1272.3	1270.8	1269.4	1268.0
32.5°	1237.3	1236.0	1234.5	1233.1	1231.6	1230.2	1228.8	1227.3
35°	1174.0	1172.0	1170.0	1168.2	1166.8	1165.4	1163.9	1162.4
37.5°	1107.7	1105.5	1103.3	1101.3	1099.4	1097.4	1095.5	1093.6
40°	1061.5	1058.6	1055.7	1053.6	1052.1	1050.7	1049.2	1047.7
42.5°	1016.8	1013.4	1010.0	1007.9	1006.9	1005.9	1004.9	1004.0
45°	947.5	944.3	941.1	939.1	938.3	937.5	936.5	935.7
47.5°	880.5	876.9	873.4	870.4	868.3	866.0	863.8	861.7
50°	833.8	829.7	825.7	822.7	821.0	819.3	817.6	815.8
52.5°	785.7	782.0	778.4	775.6	773.4	771.2	769.0	766.8
55°	715.0	711.5	708.0	705.5	703.7	702.0	700.2	698.5
57.5°	644.2	640.9	637.6	635.1	633.4	631.8	630.1	628.4
60°	595.6	593.0	590.3	588.3	586.8	585.4	584.0	582.5
62.5°	548.1	545.6	543.3	541.4	540.0	538.5	537.1	535.6
65°	479.0	476.1	473.2	471.0	469.6	468.2	466.7	465.2
67.5°	407.8	405.0	402.3	400.7	400.2	399.8	399.4	399.1
70°	362.9	360.5	358.3	356.7	355.8	354.9	354.0	353.2
72.5°	317.9	316.0	314.2	312.8	312.0	311.1	310.3	309.3
75°	253.1	251.9	250.8	250.1	249.8	249.5	249.2	248.9
77.5°	191.6	191.3	191.0	190.4	189.6	188.9	188.1	187.4
80°	152.6	152.0	151.5	151.0	150.7	150.4	150.1	149.9
82.5°	117.6	117.3	117.0	116.6	116.3	116.0	115.7	115.5
85°	67.8	67.8	67.8	67.6	67.3	67.0	66.7	66.4
87.5°	27.1	27.2	27.3	27.4	27.4	27.5	27.5	27.6
90°	10.6	11.1	11.7	12.1	12.3	12.4	12.6	12.8
92.5°	10.2	10.7	11.3	11.6	11.7	11.7	11.8	11.8
95°	10.6	11.1	11.7	12.0	12.1	12.2	12.3	12.3
97.5°	11.4	11.4	11.5	11.6	11.7	11.8	11.9	12.0
100°	15.6	13.9	12.3	11.6	11.7	11.8	11.9	12.0
102.5°	55.7	38.4	20.9	12.3	12.3	12.3	12.3	12.3
105°	135.0	135.8	136.7	135.4	132.0	128.6	125.2	121.8
107.5°	167.0	167.4	167.9	168.2	168.6	168.9	169.3	169.7
110°	188.8	189.0	189.2	189.4	189.6	189.9	190.2	190.5



TEST NUMBER: P332809-830

CATALOG NUMBER: S124DIW-S1020D470U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	209.8	209.8	209.7	209.9	210.3	210.7	211.0	211.3
115°	241.3	241.5	241.7	241.8	241.8	241.8	241.8	241.8
117.5°	273.0	273.0	272.9	272.9	272.8	272.8	272.8	272.7
120°	292.6	292.8	292.9	292.9	292.8	292.6	292.4	292.2
122.5°	311.9	312.0	312.1	312.1	311.9	311.7	311.5	311.3
125°	338.8	339.1	339.4	339.6	339.7	339.8	339.9	340.0
127.5°	365.7	365.6	365.6	365.5	365.4	365.3	365.3	365.2
130°	382.1	382.2	382.3	382.3	382.3	382.3	382.3	382.3
132.5°	398.1	398.2	398.3	398.3	398.2	398.2	398.1	398.0
135°	420.3	420.5	420.7	420.8	421.0	421.2	421.4	421.6
137.5°	441.5	441.7	442.0	442.0	442.0	441.9	441.9	441.8
140°	454.7	455.0	455.2	455.4	455.5	455.6	455.7	455.8
142.5°	466.7	467.0	467.2	467.3	467.3	467.4	467.4	467.4
145°	484.2	484.3	484.4	484.5	484.7	484.8	485.0	485.2
147.5°	499.5	499.5	499.5	499.6	499.7	499.8	499.9	500.0
150°	509.2	509.2	509.2	509.3	509.3	509.4	509.5	509.6
152.5°	517.6	517.8	518.0	518.0	518.0	517.9	517.8	517.8
155°	529.1	529.5	529.9	530.0	529.7	529.4	529.1	528.9
157.5°	539.0	539.5	540.0	540.0	539.5	539.0	538.6	538.1
160°	545.4	545.9	546.5	546.5	545.9	545.4	544.8	544.2
162.5°	550.4	551.0	551.6	551.6	550.9	550.3	549.6	549.0
165°	557.7	558.5	559.2	559.1	558.3	557.4	556.6	555.7
167.5°	563.0	563.8	564.7	564.6	563.6	562.7	561.8	560.8
170°	566.2	566.9	567.8	567.7	566.7	565.7	564.8	563.8
172.5°	568.3	569.0	569.8	569.7	568.6	567.6	566.6	565.5
175°	570.7	571.6	572.4	572.2	571.1	570.0	568.8	567.7
177.5°	571.7	572.2	572.9	572.7	571.8	570.9	570.0	569.1
180°	571.1	571.1	571.1	571.1	571.1	571.1	571.1	571.1

(END OF REPORT)