

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332815-830

Luminaire Tested: **S124DIW-S1020D770U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332815-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIW-S1020D770U830-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 770 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7069.7 lumens  
Efficiency: N/A  
Efficacy: 131.9 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 53.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332815-830

CATALOG NUMBER: S124DIW-S1020D770U830-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332815-830

CATALOG NUMBER: S124DIW-S1020D770U830-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59
1	100	95	91	88	93	89	86	83	77	75	73	67	65	63	57	56	54	50
2	91	83	77	72	85	78	72	68	68	64	60	59	56	53	50	48	46	42
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	44	41	39	35
4	76	65	57	51	70	61	54	48	53	48	43	46	42	38	40	36	34	30
5	70	58	50	43	65	54	47	41	48	42	37	42	37	33	36	32	29	26
6	64	52	44	38	60	49	41	36	43	37	33	38	33	29	32	29	26	23
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	30	26	23	20
8	55	43	35	29	51	40	33	28	36	30	26	31	27	23	27	23	21	18
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	19	16
10	48	36	28	24	45	34	27	23	30	25	21	27	22	19	23	20	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13130	13130	13130
5°	13169	13011	13105
10°	13086	12904	12969
15°	12929	12721	12754
20°	12718	12494	12506
25°	12479	12235	12200
30°	12185	11929	11820
35°	11880	11610	11456
40°	11564	11248	11041
45°	11233	10891	10683
50°	10868	10574	10246
55°	10473	10162	9831
60°	10078	9700	9405
65°	9635	9259	8886
70°	9135	8674	8337
75°	8372	7966	7764
80°	7452	7146	6969
85°	6521	6280	6150



TEST NUMBER: P332815-830

CATALOG NUMBER: S124DIW-S1020D770U830-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	153.2	2.2
10°-20°	431.5	6.1
20°-30°	635.2	9.0
30°-40°	738.4	10.4
40°-50°	738.4	10.4
50°-60°	645.9	9.1
60°-70°	479.7	6.8
70°-80°	272.5	3.9
80°-90°	81.4	1.2
90°-100°	32.0	0.5
100°-110°	204.0	2.9
110°-120°	390.2	5.5
120°-130°	495.4	7.0
130°-140°	530.0	7.5
140°-150°	495.6	7.0
150°-160°	399.7	5.7
160°-170°	257.8	3.6
170°-180°	88.8	1.3
0°-30°	1219.8	17.3
0°-40°	1958.2	27.7
0°-60°	3342.6	47.3
0°-90°	4176.2	59.1
90°-120°	626.2	8.9
90°-150°	2147.2	30.4
90°-180°	2894.0	40.9
0°-180°	7069.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1626	1626	1626	1626	1626	
5°	1625	1619	1606	1619	1617	154
15°	1547	1541	1522	1529	1526	436
25°	1401	1391	1374	1374	1370	644
35°	1205	1196	1178	1169	1162	753
45°	984	974	954	940	936	758
55°	744	739	722	707	698	666
65°	504	497	485	472	465	499
75°	268	262	255	250	249	285
85°	70	70	68	68	66	77
90°	2	10	15	19	21	6
95°	38	16	15	19	20	49
105°	211	215	218	223	199	220
115°	393	395	394	396	396	387
125°	553	555	554	556	557	493
135°	686	685	688	689	690	528
145°	791	793	793	793	795	494
155°	867	867	865	868	866	400
165°	914	911	911	916	910	258
175°	935	932	932	937	930	89
180°	935	935	935	935	935	



TEST NUMBER: P332815-830

CATALOG NUMBER: S124DIW-S1020D770U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4
2.5°	1630.5	1629.8	1629.1	1628.4	1627.8	1626.1	1623.5	1621.0	1618.4	1615.9	1618.3
5°	1625.0	1623.9	1622.8	1621.6	1620.4	1618.3	1615.0	1611.8	1608.7	1605.5	1608.7
7.5°	1610.0	1608.7	1607.6	1606.5	1605.3	1603.0	1599.4	1595.9	1592.3	1588.8	1591.4
10°	1596.4	1595.3	1594.0	1592.9	1591.8	1589.3	1585.5	1581.8	1578.0	1574.2	1576.5
12.5°	1578.7	1577.5	1576.3	1575.2	1574.0	1571.4	1567.4	1563.5	1559.4	1555.5	1558.0
15°	1546.9	1545.7	1544.5	1543.4	1542.2	1539.5	1535.1	1530.8	1526.4	1522.1	1523.8
17.5°	1508.5	1507.1	1505.6	1504.2	1502.8	1500.0	1495.8	1491.8	1487.6	1483.6	1484.6
20°	1480.4	1478.9	1477.5	1476.0	1474.6	1471.7	1467.4	1463.0	1458.7	1454.3	1455.2
22.5°	1450.2	1448.2	1446.3	1444.4	1442.6	1439.4	1435.0	1430.7	1426.3	1422.0	1423.6
25°	1400.9	1398.9	1396.8	1394.8	1392.8	1389.8	1385.7	1381.7	1377.6	1373.6	1373.9
27.5°	1344.6	1342.6	1340.4	1338.3	1336.2	1333.3	1329.6	1325.8	1322.0	1318.2	1317.6
30°	1307.1	1304.8	1302.4	1300.1	1297.8	1294.8	1291.0	1287.2	1283.5	1279.7	1278.6
32.5°	1267.4	1265.4	1263.3	1261.2	1259.1	1256.0	1252.1	1248.1	1244.1	1240.1	1238.7
35°	1205.4	1203.4	1201.4	1199.4	1197.3	1194.3	1190.2	1186.2	1182.1	1178.1	1176.0
37.5°	1140.0	1138.1	1136.3	1134.4	1132.6	1129.5	1125.1	1120.8	1116.4	1112.1	1109.9
40°	1097.3	1095.0	1092.6	1090.3	1088.0	1084.7	1080.3	1076.0	1071.7	1067.3	1064.4
42.5°	1051.4	1050.0	1048.6	1047.3	1045.8	1042.7	1037.9	1033.1	1028.3	1023.5	1020.1
45°	983.9	981.8	979.9	977.8	975.8	972.4	967.8	963.2	958.6	953.9	950.7
47.5°	913.2	911.9	910.5	909.1	907.7	904.8	900.6	896.3	892.0	887.7	884.1
50°	865.3	864.1	863.0	861.9	860.6	858.1	854.0	850.0	845.9	841.9	837.8
52.5°	818.4	817.0	815.6	814.3	812.8	810.0	805.7	801.4	797.1	792.9	789.3
55°	744.1	743.2	742.3	741.5	740.6	738.2	734.1	730.1	726.0	722.0	718.5
57.5°	673.3	672.2	671.3	670.2	669.3	666.8	662.8	658.8	654.8	650.8	647.5
60°	624.2	622.7	621.3	619.9	618.4	615.9	612.1	608.3	604.5	600.8	598.1
62.5°	576.3	575.0	573.8	572.6	571.4	568.8	564.8	560.8	556.8	552.8	550.4
65°	504.4	502.8	501.4	500.0	498.5	496.3	493.4	490.6	487.7	484.7	481.9
67.5°	431.9	430.6	429.2	427.9	426.5	424.5	421.7	419.0	416.1	413.4	410.6
70°	387.0	385.0	383.0	381.0	378.9	376.7	374.5	372.1	369.9	367.5	365.1
72.5°	339.1	337.1	335.1	333.0	331.0	329.0	327.2	325.4	323.5	321.6	319.8
75°	268.4	267.0	265.5	264.1	262.7	261.2	259.8	258.4	256.8	255.4	254.3
77.5°	201.0	200.3	199.6	199.1	198.4	197.5	196.1	194.9	193.6	192.4	192.0
80°	160.3	159.4	158.5	157.7	156.8	156.1	155.5	155.0	154.4	153.7	153.2
82.5°	120.6	120.3	119.9	119.4	119.0	118.8	118.7	118.6	118.5	118.3	118.0
85°	70.4	70.4	70.4	70.4	70.4	70.1	69.5	68.9	68.3	67.8	67.8
87.5°	27.5	27.6	27.7	27.9	28.0	28.0	28.1	28.1	28.1	28.1	28.3
90°	2.1	3.8	5.6	7.3	9.0	10.5	11.7	12.9	14.1	15.4	16.3
92.5°	8.9	9.0	9.0	9.0	9.1	9.9	11.1	12.3	13.6	14.8	15.7
95°	38.5	33.2	27.9	22.6	17.3	14.8	14.9	15.1	15.3	15.4	16.3
97.5°	81.7	85.0	88.3	91.6	94.9	87.8	70.5	53.2	35.8	18.5	18.6
100°	114.7	117.5	120.4	123.1	125.9	116.6	95.2	73.7	52.2	30.8	28.2
102.5°	151.7	153.7	155.8	157.9	159.9	159.5	156.7	153.9	151.1	148.4	119.8
105°	210.6	211.5	212.4	213.4	214.3	215.2	215.9	216.7	217.5	218.3	219.7
107.5°	265.3	265.8	266.3	266.7	267.2	268.0	269.0	270.0	271.1	272.1	272.9
110°	302.3	302.7	303.2	303.7	304.1	304.8	305.8	306.7	307.6	308.5	308.9



TEST NUMBER: P332815-830

CATALOG NUMBER: S124DIW-S1020D770U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	338.1	338.9	339.8	340.5	341.4	342.0	342.5	342.9	343.4	343.8	343.7
115°	393.2	393.7	394.2	394.5	395.0	395.2	395.0	394.9	394.7	394.5	394.9
117.5°	442.9	443.5	444.1	444.7	445.4	445.8	446.2	446.5	446.9	447.2	447.1
120°	476.5	477.1	477.7	478.3	478.9	479.2	479.0	478.9	478.7	478.5	478.9
122.5°	507.8	508.1	508.5	508.9	509.3	509.5	509.8	510.0	510.2	510.5	510.7
125°	552.7	553.4	553.9	554.6	555.2	555.3	555.1	554.8	554.4	554.1	554.6
127.5°	595.2	595.4	595.6	595.7	595.9	596.3	597.0	597.8	598.4	599.2	599.1
130°	622.6	622.8	623.0	623.1	623.3	623.6	624.1	624.5	625.0	625.5	625.7
132.5°	647.9	648.2	648.5	648.7	648.9	649.4	650.0	650.6	651.2	651.8	652.0
135°	685.6	685.5	685.3	685.1	685.0	685.2	685.9	686.5	687.1	687.8	688.1
137.5°	719.1	719.2	719.3	719.3	719.3	719.7	720.4	721.0	721.8	722.5	722.7
140°	740.9	741.2	741.5	741.9	742.2	742.4	742.8	743.1	743.4	743.8	744.1
142.5°	760.5	761.1	761.7	762.1	762.7	763.1	763.3	763.5	763.6	763.8	764.2
145°	790.6	791.1	791.5	792.0	792.5	792.7	792.7	792.7	792.7	792.7	792.9
147.5°	814.5	815.4	816.2	817.1	818.0	818.3	818.2	818.0	817.8	817.7	817.8
150°	831.9	832.5	833.1	833.8	834.3	834.6	834.4	834.2	834.2	834.0	834.0
152.5°	846.4	846.9	847.4	847.9	848.4	848.5	848.2	848.0	847.7	847.4	847.6
155°	866.9	867.0	867.1	867.3	867.5	867.3	866.9	866.4	865.9	865.4	866.1
157.5°	884.1	884.0	883.9	883.8	883.7	883.4	882.9	882.3	881.7	881.3	882.0
160°	894.1	893.6	893.2	892.8	892.3	891.9	891.8	891.6	891.5	891.4	892.3
162.5°	903.1	902.5	901.9	901.4	900.7	900.3	900.2	900.0	899.8	899.8	900.7
165°	914.5	913.6	912.9	912.1	911.3	911.0	911.0	911.0	911.0	911.0	912.2
167.5°	923.4	922.6	921.8	921.0	920.1	919.7	919.6	919.5	919.5	919.4	920.7
170°	928.4	927.5	926.5	925.6	924.7	924.3	924.4	924.6	924.7	924.9	926.1
172.5°	931.8	930.9	929.9	929.0	928.0	927.7	927.8	927.9	928.1	928.3	929.5
175°	935.4	934.4	933.6	932.6	931.7	931.3	931.4	931.6	931.8	931.9	933.3
177.5°	937.1	936.2	935.4	934.4	933.6	933.3	933.6	933.8	934.1	934.2	935.3
180°	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4



TEST NUMBER: P332815-830

CATALOG NUMBER: S124DIW-S1020D770U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4	1626.4
2.5°	1620.5	1622.9	1625.2	1626.3	1626.0	1625.8	1625.5	1625.3
5°	1611.8	1615.0	1618.3	1619.6	1619.0	1618.3	1617.8	1617.2
7.5°	1593.9	1596.5	1599.0	1600.2	1599.8	1599.4	1599.0	1598.7
10°	1578.9	1581.2	1583.5	1584.3	1583.8	1583.2	1582.6	1582.1
12.5°	1560.6	1563.1	1565.7	1566.5	1565.8	1564.9	1564.1	1563.3
15°	1525.6	1527.3	1529.1	1529.5	1528.6	1527.8	1526.9	1526.0
17.5°	1485.7	1486.9	1487.9	1488.2	1487.6	1487.0	1486.5	1485.8
20°	1456.0	1457.0	1457.8	1457.9	1457.4	1456.8	1456.2	1455.7
22.5°	1425.1	1426.7	1428.2	1428.5	1427.5	1426.4	1425.4	1424.4
25°	1374.1	1374.4	1374.7	1374.2	1373.1	1372.0	1370.7	1369.6
27.5°	1316.9	1316.2	1315.5	1314.5	1313.0	1311.5	1310.0	1308.6
30°	1277.4	1276.2	1275.1	1273.8	1272.3	1270.8	1269.4	1268.0
32.5°	1237.3	1236.0	1234.5	1233.1	1231.6	1230.2	1228.8	1227.3
35°	1174.0	1172.0	1170.0	1168.2	1166.8	1165.4	1163.9	1162.4
37.5°	1107.7	1105.5	1103.3	1101.3	1099.4	1097.4	1095.5	1093.6
40°	1061.5	1058.6	1055.7	1053.6	1052.1	1050.7	1049.2	1047.7
42.5°	1016.8	1013.4	1010.0	1007.9	1006.9	1005.9	1004.9	1004.0
45°	947.5	944.3	941.1	939.1	938.3	937.5	936.5	935.7
47.5°	880.5	876.9	873.4	870.4	868.3	866.0	863.8	861.7
50°	833.8	829.7	825.7	822.7	821.0	819.3	817.6	815.8
52.5°	785.7	782.0	778.4	775.6	773.4	771.2	769.0	766.8
55°	715.0	711.5	708.0	705.5	703.7	702.0	700.2	698.5
57.5°	644.2	640.9	637.6	635.1	633.4	631.8	630.1	628.4
60°	595.6	593.0	590.3	588.3	586.8	585.4	584.0	582.5
62.5°	548.1	545.6	543.3	541.4	540.0	538.5	537.1	535.6
65°	479.0	476.1	473.2	471.0	469.6	468.2	466.7	465.2
67.5°	407.8	405.0	402.3	400.7	400.2	399.8	399.4	399.1
70°	362.9	360.5	358.3	356.7	355.8	354.9	354.0	353.2
72.5°	317.9	316.0	314.2	312.8	312.0	311.1	310.3	309.3
75°	253.1	251.9	250.8	250.1	249.8	249.5	249.2	248.9
77.5°	191.6	191.3	191.0	190.4	189.6	188.9	188.1	187.4
80°	152.6	152.0	151.5	151.0	150.7	150.4	150.1	149.9
82.5°	117.6	117.3	117.0	116.6	116.3	116.0	115.7	115.5
85°	67.8	67.8	67.8	67.6	67.3	67.0	66.7	66.4
87.5°	28.5	28.7	28.8	28.9	29.0	29.1	29.1	29.2
90°	17.2	18.2	19.1	19.7	20.1	20.4	20.6	21.0
92.5°	16.7	17.6	18.6	19.0	19.1	19.2	19.2	19.3
95°	17.2	18.2	19.1	19.7	19.8	20.0	20.2	20.3
97.5°	18.7	18.8	18.9	18.9	19.1	19.3	19.4	19.6
100°	25.5	22.8	20.2	18.9	19.1	19.3	19.4	19.6
102.5°	91.3	62.8	34.3	20.0	20.1	20.1	20.1	20.2
105°	221.1	222.4	223.9	221.8	216.2	210.6	205.0	199.4
107.5°	273.5	274.2	274.9	275.5	276.2	276.7	277.3	277.9
110°	309.2	309.4	309.8	310.2	310.7	311.1	311.6	312.1





TEST NUMBER: P332815-830

CATALOG NUMBER: S124DIW-S1020D770U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	343.7	343.7	343.6	343.8	344.4	345.0	345.6	346.2
115°	395.2	395.5	395.9	396.0	396.0	396.0	396.0	396.0
117.5°	447.0	447.0	447.0	446.9	446.9	446.8	446.7	446.7
120°	479.2	479.5	479.8	479.8	479.5	479.2	478.9	478.5
122.5°	510.9	511.0	511.2	511.1	510.9	510.5	510.2	509.9
125°	555.1	555.5	556.0	556.3	556.5	556.6	556.8	556.9
127.5°	599.0	598.9	598.8	598.7	598.6	598.4	598.3	598.2
130°	625.8	625.9	626.1	626.1	626.1	626.1	626.1	626.1
132.5°	652.1	652.2	652.4	652.4	652.3	652.1	652.1	652.0
135°	688.3	688.7	689.0	689.3	689.6	689.9	690.2	690.5
137.5°	723.1	723.5	723.8	724.0	723.9	723.8	723.7	723.6
140°	744.6	745.1	745.6	745.9	746.0	746.2	746.4	746.5
142.5°	764.6	764.9	765.3	765.4	765.4	765.4	765.5	765.5
145°	793.0	793.1	793.3	793.5	793.8	794.2	794.5	794.8
147.5°	817.9	818.1	818.2	818.4	818.5	818.7	818.9	819.0
150°	834.0	834.0	834.0	834.1	834.2	834.3	834.5	834.6
152.5°	847.9	848.1	848.4	848.5	848.4	848.3	848.2	848.1
155°	866.7	867.3	867.9	868.0	867.5	867.0	866.6	866.2
157.5°	882.9	883.7	884.5	884.5	883.7	882.9	882.0	881.3
160°	893.2	894.1	895.0	895.0	894.1	893.2	892.3	891.4
162.5°	901.6	902.5	903.4	903.4	902.4	901.3	900.2	899.2
165°	913.4	914.6	915.9	915.9	914.5	913.0	911.6	910.2
167.5°	922.1	923.4	924.8	924.7	923.1	921.6	920.0	918.5
170°	927.4	928.7	929.9	929.7	928.2	926.6	925.1	923.5
172.5°	930.8	932.0	933.2	933.0	931.3	929.7	928.0	926.3
175°	934.7	936.1	937.5	937.3	935.4	933.6	931.7	929.8
177.5°	936.3	937.3	938.3	938.0	936.5	935.0	933.6	932.1
180°	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4

(END OF REPORT)