

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332858-830

Luminaire Tested: **S124DIW-S1195D1340U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332858-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIW-S1195D1340U830-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9209.8 lumens  
Efficiency: N/A  
Efficacy: 120.9 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 76.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332858-830

CATALOG NUMBER: S124DIW-S1195D1340U830-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332858-830

CATALOG NUMBER: S124DIW-S1195D1340U830-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58	52
1	98	94	90	86	91	87	84	81	74	72	69	62	61	59	51	50	49	44
2	89	82	76	71	83	76	71	66	65	61	57	55	52	49	45	43	41	37
3	82	72	65	59	75	67	60	55	57	52	48	48	45	42	40	37	35	31
4	75	64	56	50	69	59	52	47	51	45	41	43	39	36	36	33	30	27
5	69	57	49	43	63	53	46	40	46	40	36	39	34	31	32	29	26	23
6	63	51	43	37	58	48	40	35	41	35	31	35	31	27	29	26	23	20
7	58	46	38	32	54	43	36	31	37	32	27	32	27	24	27	23	21	18
8	54	42	34	29	50	39	32	27	34	28	24	29	25	21	25	21	19	16
9	50	38	31	26	47	36	29	24	31	26	22	27	22	19	23	19	17	15
10	47	35	28	23	44	33	26	22	29	23	20	25	20	17	21	18	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	15163	15163	15163
5°	15209	15027	15135
10°	15114	14905	14978
15°	14931	14692	14730
20°	14689	14430	14442
25°	14412	14130	14091
30°	14072	13778	13651
35°	13720	13409	13232
40°	13354	12991	12752
45°	12973	12578	12337
50°	12552	12210	11833
55°	12096	11736	11354
60°	11641	11202	10863
65°	11127	10695	10264
70°	10551	10017	9626
75°	9669	9201	8968
80°	8605	8257	8047
85°	7521	7243	7104



TEST NUMBER: P332858-830

CATALOG NUMBER: S124DIW-S1195D1340U830-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	176.9	1.9
10°-20°	498.4	5.4
20°-30°	733.6	8.0
30°-40°	852.8	9.3
40°-50°	852.8	9.3
50°-60°	746.0	8.1
60°-70°	554.0	6.0
70°-80°	314.7	3.4
80°-90°	95.6	1.0
90°-100°	104.3	1.1
100°-110°	308.8	3.4
110°-120°	524.1	5.7
120°-130°	691.1	7.5
130°-140°	776.2	8.4
140°-150°	762.7	8.3
150°-160°	641.5	7.0
160°-170°	426.8	4.6
170°-180°	149.5	1.6
0°-30°	1408.8	15.3
0°-40°	2261.6	24.6
0°-60°	3860.5	41.9
0°-90°	4824.8	52.4
90°-120°	937.2	10.2
90°-150°	3167.3	34.4
90°-180°	4385.0	47.6
0°-180°	9209.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1878	1878	1878	1878	1878	
5°	1877	1870	1854	1870	1868	178
15°	1786	1780	1758	1766	1762	503
25°	1618	1607	1586	1587	1582	744
35°	1392	1381	1361	1350	1343	870
45°	1136	1125	1102	1086	1081	876
55°	859	854	834	816	807	769
65°	582	575	560	545	537	577
75°	310	302	295	289	288	329
85°	81	81	78	78	77	90
90°	4	17	27	34	37	9
95°	73	84	93	96	97	82
105°	285	286	291	295	298	302
115°	533	533	530	529	528	525
125°	776	776	775	772	770	692
135°	1001	1008	1008	1006	1002	774
145°	1216	1221	1222	1221	1218	761
155°	1394	1393	1392	1397	1392	641
165°	1517	1513	1511	1518	1513	427
175°	1578	1572	1571	1578	1571	150
180°	1580	1580	1580	1580	1580	



TEST NUMBER: P332858-830

CATALOG NUMBER: S124DIW-S1195D1340U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3
2.5°	1883.1	1882.4	1881.5	1880.7	1879.9	1878.0	1875.1	1872.2	1869.3	1866.3	1869.0
5°	1876.8	1875.5	1874.2	1872.8	1871.5	1869.0	1865.3	1861.6	1857.9	1854.3	1857.9
7.5°	1859.4	1858.0	1856.7	1855.3	1854.0	1851.3	1847.2	1843.1	1839.1	1834.9	1838.0
10°	1843.7	1842.4	1841.1	1839.7	1838.3	1835.5	1831.2	1826.8	1822.5	1818.2	1820.8
12.5°	1823.3	1821.9	1820.5	1819.2	1817.9	1814.9	1810.3	1805.7	1801.1	1796.5	1799.4
15°	1786.5	1785.2	1783.9	1782.5	1781.1	1778.0	1772.9	1767.9	1762.9	1757.9	1759.9
17.5°	1742.3	1740.6	1738.9	1737.3	1735.6	1732.4	1727.6	1722.9	1718.2	1713.4	1714.7
20°	1709.8	1708.1	1706.4	1704.8	1703.1	1699.7	1694.7	1689.7	1684.7	1679.6	1680.6
22.5°	1674.8	1672.6	1670.5	1668.2	1666.0	1662.4	1657.4	1652.4	1647.4	1642.3	1644.2
25°	1618.0	1615.6	1613.3	1610.9	1608.5	1605.1	1600.3	1595.7	1591.0	1586.3	1586.7
27.5°	1552.9	1550.5	1548.1	1545.7	1543.3	1539.9	1535.6	1531.3	1526.9	1522.5	1521.7
30°	1509.6	1506.9	1504.2	1501.6	1498.9	1495.3	1491.0	1486.7	1482.3	1478.0	1476.7
32.5°	1463.9	1461.4	1459.1	1456.6	1454.2	1450.7	1446.0	1441.4	1436.8	1432.2	1430.6
35°	1392.2	1389.9	1387.5	1385.2	1382.8	1379.3	1374.6	1370.0	1365.3	1360.6	1358.2
37.5°	1316.6	1314.5	1312.4	1310.2	1308.1	1304.5	1299.5	1294.5	1289.4	1284.4	1281.9
40°	1267.2	1264.6	1261.9	1259.2	1256.6	1252.7	1247.7	1242.6	1237.7	1232.7	1229.3
42.5°	1214.3	1212.7	1211.1	1209.5	1207.9	1204.3	1198.7	1193.2	1187.6	1182.0	1178.2
45°	1136.3	1134.0	1131.6	1129.3	1127.0	1123.1	1117.8	1112.4	1107.0	1101.7	1098.1
47.5°	1054.7	1053.1	1051.5	1049.9	1048.3	1045.1	1040.1	1035.2	1030.2	1025.3	1021.2
50°	999.4	998.1	996.6	995.3	994.0	991.0	986.3	981.7	976.9	972.2	967.6
52.5°	945.2	943.6	942.0	940.4	938.8	935.5	930.6	925.6	920.7	915.7	911.5
55°	859.4	858.4	857.4	856.4	855.4	852.5	847.8	843.2	838.5	833.8	829.8
57.5°	777.5	776.4	775.2	774.1	773.0	770.1	765.4	760.8	756.2	751.6	747.8
60°	721.0	719.3	717.6	716.0	714.3	711.2	706.9	702.6	698.1	693.8	690.8
62.5°	665.5	664.1	662.7	661.3	660.0	657.0	652.3	647.7	643.1	638.5	635.7
65°	582.5	580.8	579.1	577.4	575.8	573.3	570.0	566.6	563.3	559.9	556.6
67.5°	498.8	497.3	495.7	494.2	492.7	490.2	487.0	483.8	480.6	477.4	474.2
70°	447.0	444.7	442.3	440.0	437.6	435.2	432.4	429.8	427.1	424.4	421.8
72.5°	391.6	389.3	386.9	384.6	382.3	380.0	377.9	375.7	373.6	371.5	369.3
75°	310.0	308.4	306.7	305.0	303.3	301.7	300.0	298.3	296.7	295.0	293.7
77.5°	232.1	231.3	230.6	229.9	229.1	228.0	226.6	225.1	223.7	222.2	221.8
80°	185.1	184.1	183.1	182.1	181.2	180.3	179.6	178.9	178.2	177.6	176.9
82.5°	139.4	138.9	138.5	138.0	137.5	137.2	137.0	137.0	136.8	136.7	136.3
85°	81.2	81.2	81.2	81.2	81.2	81.0	80.3	79.6	78.9	78.2	78.2
87.5°	32.0	32.3	32.7	33.0	33.4	33.6	33.7	33.9	34.1	34.3	34.6
90°	3.7	6.7	9.6	12.6	15.6	18.2	20.4	22.5	24.7	26.9	28.6
92.5°	26.2	29.6	33.0	36.4	39.9	42.3	43.8	45.3	46.8	48.4	49.4
95°	73.3	75.8	78.2	80.7	83.1	85.3	87.2	89.1	91.0	92.9	93.7
97.5°	128.1	130.1	132.1	133.9	135.9	138.0	140.3	142.5	144.7	146.9	147.9
100°	171.2	172.2	173.3	174.4	175.5	177.2	179.6	182.1	184.5	187.0	187.6
102.5°	216.1	216.6	217.0	217.4	217.8	219.1	221.4	223.7	225.8	228.1	228.8
105°	284.8	285.1	285.4	285.6	285.9	286.5	287.7	288.8	289.8	291.0	291.7
107.5°	356.9	357.2	357.6	357.9	358.3	358.4	358.6	358.8	359.0	359.1	359.9
110°	405.9	406.3	406.9	407.5	408.0	408.1	407.8	407.6	407.4	407.1	406.5



TEST NUMBER: P332858-830

CATALOG NUMBER: S124DIW-S1195D1340U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	456.7	456.8	456.9	457.0	457.1	456.9	456.5	455.9	455.4	455.0	454.9
115°	532.9	532.9	532.9	532.9	532.9	532.7	532.2	531.6	531.0	530.5	530.3
117.5°	604.8	605.0	605.3	605.5	605.7	605.6	605.2	604.8	604.5	604.1	603.1
120°	652.7	653.8	654.9	656.0	657.0	657.2	656.4	655.6	654.8	653.9	652.6
122.5°	702.6	703.0	703.5	703.9	704.4	704.4	704.0	703.6	703.2	702.9	701.9
125°	776.2	776.2	776.2	776.2	776.2	776.1	775.8	775.5	775.2	775.0	774.4
127.5°	842.9	843.8	844.6	845.4	846.2	846.4	845.9	845.6	845.1	844.6	844.1
130°	889.9	890.7	891.6	892.3	893.2	893.5	893.5	893.5	893.5	893.5	893.0
132.5°	937.8	938.4	939.0	939.6	940.2	940.4	940.2	939.9	939.7	939.5	939.0
135°	1001.1	1002.8	1004.4	1006.0	1007.7	1008.4	1008.4	1008.4	1008.4	1008.4	1008.0
137.5°	1070.1	1070.8	1071.6	1072.3	1073.1	1073.7	1074.1	1074.6	1075.0	1075.4	1074.7
140°	1116.1	1116.5	1117.1	1117.7	1118.2	1118.4	1118.4	1118.4	1118.4	1118.4	1118.2
142.5°	1158.1	1158.6	1159.1	1159.7	1160.3	1160.4	1160.2	1160.0	1159.8	1159.5	1159.5
145°	1216.3	1217.4	1218.4	1219.6	1220.6	1221.3	1221.5	1221.8	1222.1	1222.4	1222.1
147.5°	1273.9	1275.3	1276.6	1277.9	1279.1	1279.7	1279.5	1279.3	1279.0	1278.8	1278.7
150°	1309.2	1310.2	1311.4	1312.4	1313.5	1314.0	1314.0	1314.0	1314.0	1314.0	1314.0
152.5°	1342.4	1343.0	1343.7	1344.3	1345.0	1345.5	1345.7	1345.9	1346.1	1346.3	1347.0
155°	1393.5	1393.5	1393.5	1393.5	1393.5	1393.4	1393.1	1392.8	1392.5	1392.3	1393.4
157.5°	1436.5	1436.1	1435.6	1435.0	1434.5	1434.3	1434.3	1434.2	1434.2	1434.1	1434.9
160°	1462.0	1461.7	1461.4	1461.1	1460.8	1460.6	1460.3	1460.1	1459.8	1459.5	1460.3
162.5°	1485.4	1484.7	1484.0	1483.3	1482.6	1482.1	1481.9	1481.6	1481.3	1481.0	1482.5
165°	1516.9	1516.2	1515.3	1514.5	1513.7	1513.1	1512.5	1511.9	1511.4	1510.8	1512.5
167.5°	1541.2	1540.0	1538.9	1537.8	1536.6	1536.1	1536.2	1536.2	1536.3	1536.3	1537.9
170°	1554.8	1553.5	1552.2	1550.8	1549.4	1548.9	1549.2	1549.4	1549.7	1549.9	1551.6
172.5°	1564.6	1563.5	1562.4	1561.2	1560.1	1559.5	1559.6	1559.6	1559.7	1559.7	1561.6
175°	1578.1	1576.7	1575.4	1574.0	1572.6	1571.8	1571.6	1571.3	1571.0	1570.7	1572.6
177.5°	1582.4	1581.4	1580.3	1579.2	1578.1	1577.6	1577.6	1577.6	1577.6	1577.6	1579.1
180°	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5



TEST NUMBER: P332858-830

CATALOG NUMBER: S124DIW-S1195D1340U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3
2.5°	1871.6	1874.3	1877.0	1878.2	1877.9	1877.6	1877.4	1877.1
5°	1861.6	1865.3	1869.0	1870.5	1869.8	1869.2	1868.5	1867.7
7.5°	1840.9	1843.8	1846.7	1848.0	1847.7	1847.2	1846.8	1846.4
10°	1823.4	1826.2	1828.8	1829.9	1829.2	1828.5	1827.8	1827.1
12.5°	1802.3	1805.3	1808.3	1809.2	1808.3	1807.3	1806.4	1805.4
15°	1761.9	1764.0	1765.9	1766.4	1765.5	1764.4	1763.4	1762.5
17.5°	1715.9	1717.2	1718.4	1718.7	1718.1	1717.4	1716.7	1716.1
20°	1681.7	1682.6	1683.7	1683.9	1683.2	1682.5	1681.9	1681.1
22.5°	1646.0	1647.8	1649.5	1649.8	1648.7	1647.5	1646.2	1645.0
25°	1587.1	1587.3	1587.7	1587.1	1585.8	1584.5	1583.2	1581.9
27.5°	1520.9	1520.1	1519.3	1518.1	1516.4	1514.8	1513.1	1511.4
30°	1475.3	1473.9	1472.6	1471.1	1469.4	1467.8	1466.1	1464.4
32.5°	1429.0	1427.4	1425.8	1424.2	1422.5	1420.8	1419.2	1417.5
35°	1355.9	1353.6	1351.2	1349.2	1347.6	1345.9	1344.2	1342.6
37.5°	1279.3	1276.8	1274.2	1271.9	1269.7	1267.4	1265.3	1263.0
40°	1226.0	1222.6	1219.3	1216.7	1215.1	1213.4	1211.7	1210.0
42.5°	1174.3	1170.4	1166.6	1164.0	1162.9	1161.8	1160.6	1159.5
45°	1094.4	1090.7	1087.0	1084.7	1083.6	1082.6	1081.7	1080.6
47.5°	1017.0	1012.9	1008.7	1005.3	1002.8	1000.2	997.7	995.1
50°	962.9	958.2	953.6	950.2	948.2	946.2	944.1	942.2
52.5°	907.4	903.2	899.1	895.8	893.2	890.7	888.2	885.6
55°	825.8	821.8	817.7	814.7	812.8	810.8	808.7	806.7
57.5°	744.0	740.2	736.4	733.5	731.6	729.6	727.6	725.8
60°	687.8	684.9	681.8	679.5	677.8	676.1	674.5	672.8
62.5°	632.9	630.2	627.5	625.3	623.6	621.9	620.3	618.6
65°	553.2	549.9	546.5	544.0	542.3	540.6	538.9	537.3
67.5°	471.0	467.8	464.6	462.7	462.2	461.8	461.3	460.8
70°	419.1	416.4	413.7	411.9	410.9	409.9	408.9	407.8
72.5°	367.2	365.0	362.9	361.3	360.3	359.3	358.3	357.3
75°	292.3	291.0	289.6	288.8	288.5	288.1	287.8	287.5
77.5°	221.3	220.9	220.6	219.9	219.0	218.2	217.3	216.4
80°	176.3	175.6	174.9	174.5	174.1	173.7	173.4	173.1
82.5°	135.8	135.4	135.1	134.7	134.3	134.0	133.7	133.4
85°	78.2	78.2	78.2	78.1	77.8	77.4	77.1	76.7
87.5°	35.0	35.3	35.5	35.8	35.9	36.0	36.1	36.2
90°	30.2	31.8	33.4	34.5	35.1	35.6	36.1	36.7
92.5°	50.3	51.4	52.3	53.0	53.3	53.6	53.9	54.3
95°	94.5	95.4	96.1	96.6	96.6	96.6	96.6	96.6
97.5°	148.9	149.9	150.8	151.4	151.4	151.4	151.4	151.4
100°	188.1	188.7	189.2	189.5	189.5	189.5	189.5	189.5
102.5°	229.6	230.4	231.1	231.6	231.9	232.1	232.2	232.5
105°	292.6	293.4	294.2	295.0	295.8	296.6	297.5	298.2
107.5°	360.6	361.4	362.2	362.5	362.5	362.4	362.4	362.3
110°	406.0	405.4	404.9	405.0	405.9	406.6	407.5	408.3





TEST NUMBER: P332858-830

CATALOG NUMBER: S124DIW-S1195D1340U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	454.8	454.7	454.5	454.6	454.7	454.9	455.1	455.2
115°	530.0	529.7	529.4	529.1	528.9	528.6	528.3	528.1
117.5°	602.3	601.3	600.4	599.6	599.1	598.6	598.0	597.5
120°	651.3	649.9	648.6	648.1	648.7	649.2	649.8	650.3
122.5°	701.0	700.1	699.2	698.2	697.2	696.3	695.3	694.3
125°	773.9	773.4	772.8	772.2	771.8	771.2	770.6	770.1
127.5°	843.6	843.0	842.4	842.0	841.6	841.1	840.7	840.3
130°	892.5	891.9	891.4	890.6	889.5	888.3	887.3	886.2
132.5°	938.4	937.9	937.4	936.9	936.4	935.9	935.6	935.1
135°	1007.4	1006.8	1006.3	1005.6	1004.8	1004.0	1003.1	1002.3
137.5°	1074.0	1073.4	1072.6	1072.3	1072.5	1072.7	1072.8	1073.0
140°	1117.9	1117.7	1117.4	1117.1	1116.8	1116.5	1116.3	1116.1
142.5°	1159.4	1159.4	1159.3	1159.2	1159.2	1159.1	1159.1	1159.0
145°	1221.8	1221.5	1221.3	1220.8	1219.9	1219.1	1218.3	1217.5
147.5°	1278.4	1278.2	1278.0	1277.7	1277.4	1277.1	1277.0	1276.7
150°	1314.0	1314.0	1314.0	1313.9	1313.6	1313.3	1313.1	1312.9
152.5°	1347.6	1348.3	1349.0	1348.9	1348.2	1347.5	1346.8	1346.0
155°	1394.5	1395.5	1396.7	1396.7	1395.5	1394.5	1393.4	1392.3
157.5°	1435.7	1436.5	1437.4	1437.3	1436.3	1435.4	1434.5	1433.6
160°	1461.1	1462.0	1462.7	1462.4	1461.1	1459.8	1458.4	1457.1
162.5°	1483.9	1485.4	1486.9	1487.0	1485.5	1484.2	1482.9	1481.5
165°	1514.1	1515.7	1517.4	1517.7	1516.6	1515.4	1514.4	1513.3
167.5°	1539.5	1541.2	1542.8	1542.8	1541.1	1539.4	1537.8	1536.1
170°	1553.2	1554.8	1556.5	1556.3	1554.4	1552.6	1550.7	1548.8
172.5°	1563.4	1565.3	1567.2	1567.1	1565.2	1563.3	1561.4	1559.5
175°	1574.5	1576.4	1578.4	1578.4	1576.4	1574.5	1572.6	1570.7
177.5°	1580.6	1582.2	1583.7	1583.6	1581.9	1580.1	1578.4	1576.6
180°	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5

(END OF REPORT)