

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332233-940

Luminaire Tested: **S123DIW-S1165D1320U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332233-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S1165D1320U940-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1320 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8325.3 lumens
Efficiency: N/A
Efficacy: 109.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332233-940

CATALOG NUMBER: S123DIW-S1165D1320U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332233-940

CATALOG NUMBER: S123DIW-S1165D1320U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	107	107	107	107	99	99	99	99	84	84	84		70	70	70		57	57	57	51
1	98	94	90	86	90	87	83	80	73	71	69		61	60	58		50	49	48	43
2	89	82	75	70	82	76	70	66	64	60	57		54	51	48		44	42	40	36
3	81	72	64	59	75	67	60	55	57	52	48		48	44	41		39	37	34	30
4	74	63	56	49	68	59	52	46	50	45	41		42	38	35		35	32	30	26
5	68	57	48	42	63	53	45	40	45	39	35		38	34	30		32	28	26	23
6	63	51	43	37	58	47	40	35	41	35	31		34	30	27		29	25	23	20
7	58	46	38	32	54	43	36	30	37	31	27		31	27	24		26	23	20	18
8	54	42	34	28	50	39	32	27	34	28	24		29	24	21		24	21	18	16
9	50	38	30	25	46	35	29	24	31	25	21		26	22	19		22	19	16	14
10	47	35	28	23	43	33	26	22	28	23	19		24	20	17		21	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17546	17546	17546
5°	17629	17386	17507
10°	17511	17235	17343
15°	17307	17041	17072
20°	17068	16763	16778
25°	16747	16431	16397
30°	16394	16063	15940
35°	16025	15674	15471
40°	15638	15244	15008
45°	15213	14850	14487
50°	14788	14364	13966
55°	14230	13863	13440
60°	13670	13276	12854
65°	13173	12638	12246
70°	12441	11909	11383
75°	11366	10959	10493
80°	10253	9819	9732
85°	9003	8657	8312



TEST NUMBER: P332233-940

CATALOG NUMBER: S123DIW-S1165D1320U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.6	1.8
10°-20°	433.6	5.2
20°-30°	640.5	7.7
30°-40°	748.2	9.0
40°-50°	752.2	9.0
50°-60°	660.7	7.9
60°-70°	492.2	5.9
70°-80°	280.4	3.4
80°-90°	84.8	1.0
90°-100°	95.9	1.2
100°-110°	287.1	3.4
110°-120°	488.2	5.9
120°-130°	642.2	7.7
130°-140°	721.9	8.7
140°-150°	709.6	8.5
150°-160°	597.3	7.2
160°-170°	397.6	4.8
170°-180°	139.2	1.7
0°-30°	1227.6	14.7
0°-40°	1975.8	23.7
0°-60°	3388.7	40.7
0°-90°	4246.2	51.0
90°-120°	871.3	10.5
90°-150°	2944.9	35.4
90°-180°	4079.0	49.0
0°-180°	8325.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1630	1630	1630	1630	1630	
5°	1632	1624	1609	1622	1620	155
15°	1553	1547	1529	1539	1532	438
25°	1410	1401	1384	1385	1381	649
35°	1220	1211	1193	1185	1177	763
45°	999	993	976	959	952	771
55°	758	756	739	724	716	679
65°	517	510	496	485	481	510
75°	273	268	264	257	252	292
85°	73	70	70	67	67	80
90°	1	13	28	32	35	8
95°	68	76	86	90	90	77
105°	260	263	273	273	275	279
115°	492	495	493	494	493	486
125°	719	723	720	716	711	641
135°	933	940	939	935	932	719
145°	1132	1135	1138	1137	1132	707
155°	1296	1297	1298	1302	1294	597
165°	1412	1409	1409	1415	1408	398
175°	1469	1464	1464	1470	1463	139
180°	1472	1472	1472	1472	1472	



TEST NUMBER: P332233-940

CATALOG NUMBER: S123DIW-S1165D1320U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1630.1	1630.1	1630.1	1630.1	1630.1	1630.1	1630.1	1630.1	1630.1	1630.1	1630.1
2.5°	1635.8	1634.8	1633.8	1632.8	1631.7	1629.9	1627.2	1624.4	1621.7	1618.9	1621.4
5°	1631.6	1630.0	1628.4	1626.9	1625.3	1622.8	1619.4	1616.0	1612.6	1609.1	1612.2
7.5°	1615.6	1614.0	1612.5	1610.9	1609.4	1606.8	1603.2	1599.7	1596.2	1592.6	1595.4
10°	1602.1	1600.5	1599.0	1597.4	1595.9	1593.1	1589.0	1585.0	1580.9	1576.9	1579.7
12.5°	1584.2	1582.9	1581.5	1580.3	1579.0	1576.4	1572.6	1568.8	1565.0	1561.2	1563.3
15°	1553.1	1551.8	1550.6	1549.3	1548.1	1545.4	1541.4	1537.3	1533.3	1529.2	1531.7
17.5°	1516.9	1515.3	1513.7	1512.1	1510.4	1507.6	1503.5	1499.5	1495.4	1491.4	1493.2
20°	1490.0	1488.1	1486.2	1484.3	1482.6	1479.5	1475.5	1471.5	1467.4	1463.4	1464.6
22.5°	1459.7	1457.9	1456.0	1454.1	1452.2	1449.3	1445.2	1441.2	1437.2	1433.1	1434.0
25°	1410.1	1408.2	1406.3	1404.4	1402.7	1399.6	1395.6	1391.6	1387.5	1383.5	1383.8
27.5°	1357.1	1355.3	1353.5	1351.7	1349.9	1346.8	1342.5	1338.1	1333.7	1329.4	1329.6
30°	1319.0	1317.4	1315.9	1314.3	1312.8	1309.8	1305.5	1301.1	1296.7	1292.4	1292.4
32.5°	1280.9	1278.8	1276.8	1274.7	1272.6	1269.9	1266.6	1263.2	1259.8	1256.5	1254.7
35°	1219.5	1217.6	1215.8	1213.9	1212.0	1209.1	1205.0	1201.0	1196.9	1192.8	1191.0
37.5°	1156.6	1154.3	1151.9	1149.6	1147.2	1144.0	1139.9	1135.8	1131.7	1127.5	1125.2
40°	1112.9	1111.1	1109.2	1107.3	1105.5	1102.3	1098.0	1093.6	1089.2	1084.9	1082.4
42.5°	1069.2	1067.1	1065.0	1062.8	1060.7	1057.5	1053.1	1048.7	1044.4	1040.1	1037.6
45°	999.4	998.2	996.9	995.7	994.4	991.8	987.7	983.6	979.6	975.5	971.9
47.5°	930.1	928.4	926.6	924.7	922.9	920.2	916.3	912.5	908.7	904.9	901.3
50°	883.1	881.5	879.9	878.4	876.8	874.1	870.0	865.9	861.8	857.8	854.4
52.5°	833.7	832.7	831.6	830.5	829.5	826.8	822.5	818.2	814.0	809.6	806.6
55°	758.3	758.0	757.7	757.4	757.1	754.9	750.8	746.8	742.7	738.7	735.3
57.5°	686.5	685.5	684.4	683.4	682.3	680.2	676.9	673.7	670.5	667.2	664.1
60°	635.0	634.6	634.4	634.0	633.7	631.7	627.9	624.2	620.5	616.7	613.9
62.5°	589.0	588.2	587.4	586.6	585.8	583.4	579.7	576.0	572.3	568.6	565.7
65°	517.2	515.7	514.1	512.6	511.0	508.6	505.5	502.4	499.3	496.2	493.7
67.5°	441.2	439.9	438.5	437.1	435.8	433.9	431.5	429.2	426.8	424.5	422.2
70°	395.3	393.4	391.6	389.7	387.8	385.9	384.1	382.2	380.3	378.4	376.3
72.5°	347.1	345.7	344.3	343.0	341.6	339.8	337.7	335.6	333.5	331.4	329.4
75°	273.3	272.1	270.8	269.6	268.3	267.2	266.4	265.4	264.5	263.5	262.0
77.5°	208.0	207.3	206.6	206.0	205.3	204.4	203.2	202.2	201.0	199.9	198.9
80°	165.4	164.4	163.5	162.6	161.7	160.9	160.2	159.6	159.0	158.4	158.1
82.5°	123.9	123.7	123.5	123.3	123.1	123.0	122.9	122.8	122.6	122.5	122.0
85°	72.9	72.2	71.6	71.0	70.4	70.1	70.1	70.1	70.1	70.1	69.5
87.5°	29.4	29.2	28.9	28.7	28.4	28.5	29.0	29.4	29.8	30.2	30.1
90°	1.2	3.7	6.3	8.8	11.4	14.4	17.7	21.0	24.4	27.7	28.8
92.5°	28.0	29.7	31.5	33.3	35.0	36.8	38.7	40.6	42.5	44.4	45.2
95°	68.2	70.0	71.9	73.7	75.4	77.4	79.5	81.5	83.6	85.6	86.6
97.5°	121.2	122.5	123.9	125.2	126.5	128.0	129.5	130.9	132.4	133.9	135.1
100°	157.3	158.8	160.3	161.9	163.5	164.9	166.1	167.5	168.7	170.0	170.8
102.5°	198.9	199.8	200.8	201.7	202.6	203.9	205.6	207.3	209.0	210.7	211.5
105°	260.2	260.7	261.3	261.7	262.3	263.7	266.0	268.3	270.6	273.0	273.0
107.5°	331.4	331.8	332.1	332.4	332.7	333.3	334.2	335.2	336.1	337.0	337.9
110°	375.9	376.4	376.9	377.4	377.9	378.4	379.0	379.5	380.0	380.5	381.6



TEST NUMBER: P332233-940

CATALOG NUMBER: S123DIW-S1165D1320U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	422.1	422.4	422.8	423.0	423.4	423.6	423.7	423.7	423.9	424.0	425.3
115°	491.5	492.3	493.0	493.8	494.6	494.7	494.2	493.7	493.2	492.7	492.9
117.5°	561.4	561.9	562.4	562.9	563.5	563.4	562.7	562.0	561.3	560.7	560.6
120°	604.8	606.4	608.0	609.5	611.0	611.2	609.8	608.6	607.3	606.0	605.7
122.5°	650.2	651.3	652.5	653.6	654.7	655.0	654.2	653.6	652.9	652.3	651.6
125°	719.3	720.1	720.9	721.7	722.5	722.6	722.0	721.6	721.0	720.5	719.5
127.5°	783.2	784.9	786.5	788.1	789.8	790.3	789.8	789.2	788.6	788.1	786.6
130°	825.7	827.8	829.9	832.0	834.0	834.6	833.8	833.1	832.3	831.5	830.5
132.5°	868.3	870.4	872.4	874.5	876.6	877.3	876.7	876.2	875.6	875.0	873.8
135°	933.4	934.9	936.4	937.9	939.5	940.1	939.9	939.6	939.3	939.1	938.1
137.5°	993.5	994.7	996.0	997.3	998.6	999.6	1000.2	1000.9	1001.6	1002.3	1001.1
140°	1035.1	1036.3	1037.7	1038.9	1040.3	1041.0	1041.3	1041.5	1041.8	1042.1	1041.8
142.5°	1073.0	1074.3	1075.6	1076.9	1078.2	1079.1	1079.5	1080.0	1080.4	1080.9	1080.7
145°	1132.2	1132.7	1133.3	1133.8	1134.3	1135.0	1135.7	1136.5	1137.3	1138.0	1137.7
147.5°	1184.0	1185.0	1185.9	1186.9	1187.8	1188.6	1189.3	1190.0	1190.7	1191.4	1191.4
150°	1220.1	1220.7	1221.2	1221.6	1222.2	1222.7	1223.2	1223.7	1224.2	1224.8	1224.8
152.5°	1249.7	1250.4	1251.2	1251.9	1252.6	1253.1	1253.5	1253.7	1254.1	1254.4	1254.8
155°	1296.5	1296.5	1296.5	1296.5	1296.5	1296.6	1296.8	1297.1	1297.4	1297.6	1298.7
157.5°	1336.2	1336.0	1335.6	1335.3	1335.0	1335.0	1335.2	1335.3	1335.6	1335.8	1336.9
160°	1361.2	1360.8	1360.2	1359.7	1359.1	1358.9	1358.9	1358.9	1358.9	1358.9	1360.2
162.5°	1383.4	1382.7	1382.0	1381.3	1380.5	1380.3	1380.5	1380.7	1380.9	1381.1	1382.4
165°	1412.1	1411.3	1410.6	1409.8	1409.1	1408.6	1408.6	1408.6	1408.6	1408.6	1410.2
167.5°	1435.0	1434.0	1433.0	1431.9	1430.9	1430.5	1430.7	1430.9	1431.1	1431.3	1432.9
170°	1448.0	1447.0	1445.9	1444.9	1443.9	1443.3	1443.3	1443.3	1443.3	1443.3	1445.1
172.5°	1458.1	1457.1	1456.1	1455.1	1454.0	1453.5	1453.5	1453.5	1453.5	1453.5	1455.1
175°	1468.8	1467.8	1466.8	1465.7	1464.6	1464.2	1464.2	1464.2	1464.2	1464.2	1465.7
177.5°	1473.2	1472.4	1471.5	1470.7	1469.9	1469.5	1469.5	1469.5	1469.5	1469.5	1470.7
180°	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3



TEST NUMBER: P332233-940

CATALOG NUMBER: S123DIW-S1165D1320U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1630.1	1630.1	1630.1	1630.1	1630.1	1630.1	1630.1	1630.1
2.5°	1623.9	1626.4	1628.9	1630.0	1629.8	1629.5	1629.2	1629.1
5°	1615.3	1618.5	1621.6	1622.8	1622.2	1621.6	1621.0	1620.3
7.5°	1598.2	1601.0	1603.8	1605.0	1604.6	1604.3	1603.9	1603.6
10°	1582.5	1585.3	1588.1	1589.2	1588.6	1588.0	1587.3	1586.7
12.5°	1565.3	1567.4	1569.4	1570.3	1569.9	1569.5	1569.1	1568.8
15°	1534.2	1536.7	1539.2	1539.5	1537.7	1535.8	1533.9	1532.0
17.5°	1494.9	1496.6	1498.3	1498.9	1498.3	1497.5	1496.8	1496.2
20°	1465.9	1467.1	1468.4	1468.5	1467.6	1466.6	1465.7	1464.7
22.5°	1435.1	1436.1	1437.1	1437.0	1435.8	1434.6	1433.4	1432.3
25°	1384.1	1384.4	1384.7	1384.4	1383.5	1382.5	1381.6	1380.6
27.5°	1329.9	1330.1	1330.3	1329.9	1328.7	1327.5	1326.3	1325.2
30°	1292.4	1292.4	1292.4	1291.3	1289.1	1286.9	1284.7	1282.5
32.5°	1252.9	1251.2	1249.5	1248.0	1246.9	1245.6	1244.5	1243.3
35°	1189.1	1187.2	1185.4	1183.7	1182.1	1180.5	1178.9	1177.4
37.5°	1123.0	1120.8	1118.6	1117.0	1115.9	1114.9	1113.9	1112.9
40°	1080.0	1077.5	1075.0	1073.1	1071.8	1070.6	1069.3	1068.1
42.5°	1035.1	1032.6	1030.1	1028.2	1027.0	1025.7	1024.5	1023.2
45°	968.1	964.4	960.6	958.0	956.4	954.8	953.3	951.7
47.5°	897.6	893.9	890.2	887.7	886.4	884.9	883.6	882.3
50°	851.0	847.6	844.1	841.5	839.6	837.8	835.9	834.0
52.5°	803.8	800.8	797.9	795.5	793.6	791.8	789.9	788.0
55°	731.8	728.4	725.0	722.5	720.9	719.3	717.8	716.2
57.5°	661.1	658.1	655.0	652.6	650.8	649.0	647.1	645.3
60°	611.2	608.3	605.6	603.3	601.8	600.2	598.7	597.1
62.5°	562.9	560.1	557.3	555.4	554.3	553.2	552.2	551.2
65°	491.2	488.7	486.2	484.6	483.6	482.7	481.7	480.8
67.5°	420.1	417.9	415.7	413.9	412.7	411.3	410.0	408.8
70°	374.1	371.9	369.7	367.8	366.3	364.7	363.2	361.7
72.5°	327.5	325.6	323.6	322.3	321.5	320.7	319.9	319.1
75°	260.4	258.9	257.3	256.0	255.1	254.1	253.2	252.3
77.5°	197.8	196.7	195.6	195.1	195.1	195.1	195.1	195.1
80°	157.7	157.5	157.1	157.0	157.0	157.0	157.0	157.0
82.5°	121.4	120.8	120.3	119.8	119.6	119.4	119.1	118.9
85°	68.8	68.2	67.6	67.3	67.3	67.3	67.3	67.3
87.5°	30.1	30.1	30.1	30.1	30.1	30.3	30.4	30.5
90°	29.8	30.9	31.8	32.6	33.2	33.7	34.2	34.7
92.5°	46.0	46.9	47.7	48.0	47.6	47.3	47.0	46.7
95°	87.7	88.6	89.7	90.2	90.2	90.2	90.2	90.2
97.5°	136.3	137.5	138.7	139.2	139.1	139.0	138.9	138.8
100°	171.6	172.3	173.1	173.7	174.2	174.8	175.3	175.8
102.5°	212.2	213.0	213.8	214.1	214.0	213.9	213.8	213.7
105°	273.0	273.0	273.0	273.2	273.8	274.2	274.7	275.3
107.5°	338.7	339.5	340.3	340.5	340.3	339.9	339.7	339.3
110°	382.5	383.6	384.6	384.9	384.3	383.9	383.3	382.8



TEST NUMBER: P332233-940

CATALOG NUMBER: S123DIW-S1165D1320U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	426.4	427.7	428.9	429.4	429.4	429.3	429.2	429.1
115°	493.2	493.5	493.7	493.7	493.5	493.2	492.9	492.7
117.5°	560.6	560.5	560.4	560.1	559.4	558.7	557.9	557.2
120°	605.5	605.3	605.0	604.6	604.1	603.6	603.1	602.5
122.5°	650.9	650.2	649.6	648.9	648.2	647.5	646.8	646.0
125°	718.5	717.5	716.4	715.4	714.3	713.3	712.3	711.2
127.5°	785.2	783.7	782.3	781.0	779.8	778.6	777.5	776.2
130°	829.5	828.5	827.4	826.0	824.2	822.4	820.6	818.9
132.5°	872.5	871.3	870.1	868.8	867.4	866.0	864.6	863.3
135°	937.0	936.0	935.0	934.2	933.7	933.2	932.6	932.2
137.5°	1000.1	999.0	997.9	996.9	996.0	995.0	994.0	993.0
140°	1041.5	1041.3	1041.0	1040.0	1038.2	1036.3	1034.6	1032.8
142.5°	1080.4	1080.1	1079.9	1079.1	1077.6	1076.3	1074.9	1073.5
145°	1137.5	1137.3	1137.0	1136.4	1135.3	1134.3	1133.3	1132.2
147.5°	1191.4	1191.4	1191.4	1190.7	1189.2	1187.6	1186.1	1184.5
150°	1224.8	1224.8	1224.8	1224.0	1222.4	1220.9	1219.3	1217.8
152.5°	1255.2	1255.6	1256.0	1255.5	1254.2	1252.9	1251.5	1250.2
155°	1299.7	1300.7	1301.7	1301.4	1299.6	1297.8	1295.9	1294.1
157.5°	1337.9	1339.0	1340.2	1339.9	1338.5	1337.0	1335.6	1334.2
160°	1361.5	1362.8	1364.1	1364.2	1363.2	1362.2	1361.1	1360.0
162.5°	1383.7	1385.0	1386.3	1386.1	1384.5	1382.8	1381.2	1379.5
165°	1411.8	1413.3	1414.8	1414.7	1412.9	1411.1	1409.3	1407.5
167.5°	1434.5	1436.1	1437.7	1437.7	1436.1	1434.5	1432.9	1431.3
170°	1447.0	1448.8	1450.5	1450.5	1448.8	1447.0	1445.1	1443.3
172.5°	1456.7	1458.3	1459.9	1459.8	1458.0	1456.2	1454.4	1452.6
175°	1467.2	1468.8	1470.3	1470.2	1468.4	1466.6	1464.8	1463.0
177.5°	1471.9	1473.2	1474.4	1474.4	1472.8	1471.4	1470.0	1468.6
180°	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3

(END OF REPORT)