

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332864-830

Luminaire Tested: **S124DIW-S1195D1560U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332864-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIW-S1195D1560U830-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9923.9 lumens  
Efficiency: N/A  
Efficacy: 119.7 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 82.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332864-830

CATALOG NUMBER: S124DIW-S1195D1560U830-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332864-830

CATALOG NUMBER: S124DIW-S1195D1560U830-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49				
1	97	93	89	86	90	86	83	79	72	70	68	60	58	57	48	47	46	41				
2	89	81	75	70	81	75	70	65	63	59	56	53	50	47	43	41	39	34				
3	81	71	64	58	74	66	60	54	56	51	47	46	43	40	38	35	33	29				
4	74	63	55	49	68	59	52	46	50	44	40	41	37	34	34	31	29	25				
5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	30	27	25	22				
6	63	50	42	37	57	47	40	34	40	34	30	34	29	26	28	24	22	19				
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	25	22	19	17				
8	54	41	34	28	49	39	32	27	33	28	24	28	24	20	23	20	17	15				
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16	14				
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	15163	15163	15163
5°	15209	15027	15135
10°	15114	14905	14978
15°	14931	14692	14730
20°	14689	14430	14442
25°	14412	14130	14091
30°	14072	13778	13651
35°	13720	13409	13232
40°	13354	12991	12752
45°	12973	12578	12337
50°	12552	12210	11833
55°	12096	11736	11354
60°	11641	11202	10863
65°	11127	10695	10264
70°	10551	10017	9626
75°	9669	9201	8968
80°	8605	8257	8047
85°	7521	7243	7104



TEST NUMBER: P332864-830

CATALOG NUMBER: S124DIW-S1195D1560U830-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	176.9	1.8
10°-20°	498.4	5.0
20°-30°	733.6	7.4
30°-40°	852.8	8.6
40°-50°	852.8	8.6
50°-60°	746.0	7.5
60°-70°	554.0	5.6
70°-80°	314.7	3.2
80°-90°	96.3	1.0
90°-100°	121.2	1.2
100°-110°	359.1	3.6
110°-120°	609.4	6.1
120°-130°	803.6	8.1
130°-140°	902.4	9.1
140°-150°	886.8	8.9
150°-160°	745.9	7.5
160°-170°	496.2	5.0
170°-180°	173.8	1.8
0°-30°	1408.8	14.2
0°-40°	2261.6	22.8
0°-60°	3860.5	38.9
0°-90°	4825.5	48.6
90°-120°	1089.7	11.0
90°-150°	3682.5	37.1
90°-180°	5098.0	51.4
0°-180°	9923.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1878	1878	1878	1878	1878	
5°	1877	1870	1854	1870	1868	178
15°	1786	1780	1758	1766	1762	503
25°	1618	1607	1586	1587	1582	744
35°	1392	1381	1361	1350	1343	870
45°	1136	1125	1102	1086	1081	876
55°	859	854	834	816	807	769
65°	582	575	560	545	537	577
75°	310	302	295	289	288	329
85°	81	81	78	78	77	90
90°	4	20	31	40	43	10
95°	85	98	108	112	112	95
105°	331	333	338	342	347	351
115°	620	619	617	615	614	611
125°	902	902	901	898	895	804
135°	1164	1172	1172	1170	1165	900
145°	1414	1420	1421	1420	1416	885
155°	1620	1620	1619	1624	1619	745
165°	1764	1760	1757	1764	1759	497
175°	1835	1828	1826	1835	1826	174
180°	1838	1838	1838	1838	1838	



TEST NUMBER: P332864-830

CATALOG NUMBER: S124DIW-S1195D1560U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3
2.5°	1883.1	1882.4	1881.5	1880.7	1879.9	1878.0	1875.1	1872.2	1869.3	1866.3	1869.0
5°	1876.8	1875.5	1874.2	1872.8	1871.5	1869.0	1865.3	1861.6	1857.9	1854.3	1857.9
7.5°	1859.4	1858.0	1856.7	1855.3	1854.0	1851.3	1847.2	1843.1	1839.1	1834.9	1838.0
10°	1843.7	1842.4	1841.1	1839.7	1838.3	1835.5	1831.2	1826.8	1822.5	1818.2	1820.8
12.5°	1823.3	1821.9	1820.5	1819.2	1817.9	1814.9	1810.3	1805.7	1801.1	1796.5	1799.4
15°	1786.5	1785.2	1783.9	1782.5	1781.1	1778.0	1772.9	1767.9	1762.9	1757.9	1759.9
17.5°	1742.3	1740.6	1738.9	1737.3	1735.6	1732.4	1727.6	1722.9	1718.2	1713.4	1714.7
20°	1709.8	1708.1	1706.4	1704.8	1703.1	1699.7	1694.7	1689.7	1684.7	1679.6	1680.6
22.5°	1674.8	1672.6	1670.5	1668.2	1666.0	1662.4	1657.4	1652.4	1647.4	1642.3	1644.2
25°	1618.0	1615.6	1613.3	1610.9	1608.5	1605.1	1600.3	1595.7	1591.0	1586.3	1586.7
27.5°	1552.9	1550.5	1548.1	1545.7	1543.3	1539.9	1535.6	1531.3	1526.9	1522.5	1521.7
30°	1509.6	1506.9	1504.2	1501.6	1498.9	1495.3	1491.0	1486.7	1482.3	1478.0	1476.7
32.5°	1463.9	1461.4	1459.1	1456.6	1454.2	1450.7	1446.0	1441.4	1436.8	1432.2	1430.6
35°	1392.2	1389.9	1387.5	1385.2	1382.8	1379.3	1374.6	1370.0	1365.3	1360.6	1358.2
37.5°	1316.6	1314.5	1312.4	1310.2	1308.1	1304.5	1299.5	1294.5	1289.4	1284.4	1281.9
40°	1267.2	1264.6	1261.9	1259.2	1256.6	1252.7	1247.7	1242.6	1237.7	1232.7	1229.3
42.5°	1214.3	1212.7	1211.1	1209.5	1207.9	1204.3	1198.7	1193.2	1187.6	1182.0	1178.2
45°	1136.3	1134.0	1131.6	1129.3	1127.0	1123.1	1117.8	1112.4	1107.0	1101.7	1098.1
47.5°	1054.7	1053.1	1051.5	1049.9	1048.3	1045.1	1040.1	1035.2	1030.2	1025.3	1021.2
50°	999.4	998.1	996.6	995.3	994.0	991.0	986.3	981.7	976.9	972.2	967.6
52.5°	945.2	943.6	942.0	940.4	938.8	935.5	930.6	925.6	920.7	915.7	911.5
55°	859.4	858.4	857.4	856.4	855.4	852.5	847.8	843.2	838.5	833.8	829.8
57.5°	777.5	776.4	775.2	774.1	773.0	770.1	765.4	760.8	756.2	751.6	747.8
60°	721.0	719.3	717.6	716.0	714.3	711.2	706.9	702.6	698.1	693.8	690.8
62.5°	665.5	664.1	662.7	661.3	660.0	657.0	652.3	647.7	643.1	638.5	635.7
65°	582.5	580.8	579.1	577.4	575.8	573.3	570.0	566.6	563.3	559.9	556.6
67.5°	498.8	497.3	495.7	494.2	492.7	490.2	487.0	483.8	480.6	477.4	474.2
70°	447.0	444.7	442.3	440.0	437.6	435.2	432.4	429.8	427.1	424.4	421.8
72.5°	391.6	389.3	386.9	384.6	382.3	380.0	377.9	375.7	373.6	371.5	369.3
75°	310.0	308.4	306.7	305.0	303.3	301.7	300.0	298.3	296.7	295.0	293.7
77.5°	232.1	231.3	230.6	229.9	229.1	228.0	226.6	225.1	223.7	222.2	221.8
80°	185.1	184.1	183.1	182.1	181.2	180.3	179.6	178.9	178.2	177.6	176.9
82.5°	139.4	138.9	138.5	138.0	137.5	137.2	137.0	137.0	136.8	136.7	136.3
85°	81.2	81.2	81.2	81.2	81.2	81.0	80.3	79.6	78.9	78.2	78.2
87.5°	32.1	32.6	33.0	33.5	33.8	34.2	34.4	34.7	34.9	35.2	35.5
90°	4.2	7.7	11.2	14.7	18.2	21.2	23.7	26.2	28.7	31.3	33.2
92.5°	30.4	34.4	38.4	42.3	46.4	49.2	51.0	52.8	54.5	56.3	57.4
95°	85.3	88.1	91.0	93.8	96.6	99.2	101.4	103.6	105.8	108.0	109.0
97.5°	148.9	151.2	153.4	155.8	158.1	160.5	163.1	165.6	168.2	170.8	171.9
100°	199.0	200.2	201.5	202.7	204.1	206.0	209.0	211.8	214.6	217.4	218.1
102.5°	251.3	251.8	252.3	252.8	253.3	254.9	257.4	260.0	262.6	265.2	266.1
105°	331.1	331.5	331.8	332.1	332.4	333.2	334.4	335.7	337.0	338.3	339.2
107.5°	415.0	415.4	415.8	416.1	416.5	416.8	417.0	417.2	417.4	417.5	418.4
110°	471.8	472.5	473.1	473.7	474.4	474.6	474.2	473.9	473.5	473.3	472.6



TEST NUMBER: P332864-830

CATALOG NUMBER: S124DIW-S1195D1560U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	530.9	531.1	531.2	531.3	531.5	531.2	530.7	530.1	529.5	529.0	528.9
115°	619.6	619.6	619.6	619.6	619.6	619.3	618.7	618.0	617.5	616.8	616.5
117.5°	703.2	703.4	703.7	704.0	704.3	704.2	703.7	703.2	702.8	702.4	701.3
120°	758.9	760.2	761.5	762.7	763.9	764.1	763.2	762.2	761.3	760.3	758.7
122.5°	816.9	817.4	817.9	818.4	818.9	819.0	818.5	818.0	817.7	817.2	816.1
125°	902.5	902.5	902.5	902.5	902.5	902.3	902.0	901.6	901.4	901.1	900.4
127.5°	980.1	981.0	981.9	982.9	983.8	984.1	983.5	983.1	982.6	982.0	981.4
130°	1034.6	1035.6	1036.5	1037.5	1038.4	1038.9	1038.9	1038.9	1038.9	1038.9	1038.3
132.5°	1090.3	1091.1	1091.7	1092.4	1093.2	1093.3	1093.1	1092.9	1092.6	1092.3	1091.7
135°	1163.9	1165.8	1167.7	1169.7	1171.6	1172.5	1172.5	1172.5	1172.5	1172.5	1171.9
137.5°	1244.2	1245.0	1245.9	1246.8	1247.6	1248.4	1248.9	1249.3	1249.9	1250.4	1249.5
140°	1297.6	1298.2	1298.8	1299.5	1300.0	1300.4	1300.4	1300.4	1300.4	1300.4	1300.0
142.5°	1346.4	1347.1	1347.7	1348.3	1349.0	1349.2	1348.9	1348.7	1348.4	1348.1	1348.1
145°	1414.1	1415.3	1416.6	1417.9	1419.2	1419.9	1420.2	1420.6	1420.9	1421.2	1420.9
147.5°	1481.2	1482.7	1484.2	1485.7	1487.2	1487.9	1487.6	1487.3	1487.1	1486.9	1486.6
150°	1522.1	1523.3	1524.7	1525.9	1527.2	1527.8	1527.8	1527.8	1527.8	1527.8	1527.8
152.5°	1560.8	1561.5	1562.3	1563.0	1563.8	1564.3	1564.5	1564.8	1565.1	1565.3	1566.0
155°	1620.1	1620.1	1620.1	1620.1	1620.1	1620.0	1619.7	1619.4	1619.1	1618.7	1620.0
157.5°	1670.2	1669.6	1669.1	1668.5	1667.9	1667.6	1667.5	1667.5	1667.5	1667.4	1668.3
160°	1699.8	1699.4	1699.1	1698.8	1698.5	1698.2	1697.9	1697.5	1697.2	1697.0	1697.9
162.5°	1727.0	1726.3	1725.4	1724.6	1723.7	1723.2	1722.9	1722.6	1722.2	1721.9	1723.6
165°	1763.7	1762.7	1761.8	1760.9	1759.9	1759.2	1758.5	1757.8	1757.3	1756.6	1758.5
167.5°	1791.9	1790.5	1789.2	1787.9	1786.6	1785.9	1786.0	1786.0	1786.1	1786.2	1788.1
170°	1807.8	1806.2	1804.6	1803.0	1801.5	1800.8	1801.1	1801.5	1801.8	1802.0	1803.9
172.5°	1819.1	1817.8	1816.5	1815.1	1813.8	1813.2	1813.3	1813.4	1813.4	1813.5	1815.6
175°	1834.8	1833.2	1831.6	1830.0	1828.4	1827.5	1827.2	1826.8	1826.6	1826.3	1828.4
177.5°	1839.8	1838.6	1837.4	1836.1	1834.8	1834.2	1834.2	1834.2	1834.2	1834.2	1836.0
180°	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6



TEST NUMBER: P332864-830

CATALOG NUMBER: S124DIW-S1195D1560U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3
2.5°	1871.6	1874.3	1877.0	1878.2	1877.9	1877.6	1877.4	1877.1
5°	1861.6	1865.3	1869.0	1870.5	1869.8	1869.2	1868.5	1867.7
7.5°	1840.9	1843.8	1846.7	1848.0	1847.7	1847.2	1846.8	1846.4
10°	1823.4	1826.2	1828.8	1829.9	1829.2	1828.5	1827.8	1827.1
12.5°	1802.3	1805.3	1808.3	1809.2	1808.3	1807.3	1806.4	1805.4
15°	1761.9	1764.0	1765.9	1766.4	1765.5	1764.4	1763.4	1762.5
17.5°	1715.9	1717.2	1718.4	1718.7	1718.1	1717.4	1716.7	1716.1
20°	1681.7	1682.6	1683.7	1683.9	1683.2	1682.5	1681.9	1681.1
22.5°	1646.0	1647.8	1649.5	1649.8	1648.7	1647.5	1646.2	1645.0
25°	1587.1	1587.3	1587.7	1587.1	1585.8	1584.5	1583.2	1581.9
27.5°	1520.9	1520.1	1519.3	1518.1	1516.4	1514.8	1513.1	1511.4
30°	1475.3	1473.9	1472.6	1471.1	1469.4	1467.8	1466.1	1464.4
32.5°	1429.0	1427.4	1425.8	1424.2	1422.5	1420.8	1419.2	1417.5
35°	1355.9	1353.6	1351.2	1349.2	1347.6	1345.9	1344.2	1342.6
37.5°	1279.3	1276.8	1274.2	1271.9	1269.7	1267.4	1265.3	1263.0
40°	1226.0	1222.6	1219.3	1216.7	1215.1	1213.4	1211.7	1210.0
42.5°	1174.3	1170.4	1166.6	1164.0	1162.9	1161.8	1160.6	1159.5
45°	1094.4	1090.7	1087.0	1084.7	1083.6	1082.6	1081.7	1080.6
47.5°	1017.0	1012.9	1008.7	1005.3	1002.8	1000.2	997.7	995.1
50°	962.9	958.2	953.6	950.2	948.2	946.2	944.1	942.2
52.5°	907.4	903.2	899.1	895.8	893.2	890.7	888.2	885.6
55°	825.8	821.8	817.7	814.7	812.8	810.8	808.7	806.7
57.5°	744.0	740.2	736.4	733.5	731.6	729.6	727.6	725.8
60°	687.8	684.9	681.8	679.5	677.8	676.1	674.5	672.8
62.5°	632.9	630.2	627.5	625.3	623.6	621.9	620.3	618.6
65°	553.2	549.9	546.5	544.0	542.3	540.6	538.9	537.3
67.5°	471.0	467.8	464.6	462.7	462.2	461.8	461.3	460.8
70°	419.1	416.4	413.7	411.9	410.9	409.9	408.9	407.8
72.5°	367.2	365.0	362.9	361.3	360.3	359.3	358.3	357.3
75°	292.3	291.0	289.6	288.8	288.5	288.1	287.8	287.5
77.5°	221.3	220.9	220.6	219.9	219.0	218.2	217.3	216.4
80°	176.3	175.6	174.9	174.5	174.1	173.7	173.4	173.1
82.5°	135.8	135.4	135.1	134.7	134.3	134.0	133.7	133.4
85°	78.2	78.2	78.2	78.1	77.8	77.4	77.1	76.7
87.5°	35.9	36.3	36.7	36.9	37.0	37.1	37.3	37.4
90°	35.1	36.9	38.8	40.2	40.7	41.4	42.0	42.6
92.5°	58.5	59.7	60.8	61.5	61.9	62.3	62.7	63.1
95°	109.9	110.8	111.8	112.3	112.3	112.3	112.3	112.3
97.5°	173.1	174.3	175.4	176.0	176.0	176.0	176.0	176.0
100°	218.7	219.3	220.0	220.3	220.3	220.3	220.3	220.3
102.5°	266.9	267.9	268.7	269.3	269.6	269.8	270.0	270.3
105°	340.2	341.1	342.0	343.0	343.9	344.9	345.8	346.8
107.5°	419.3	420.2	421.1	421.5	421.4	421.4	421.3	421.2
110°	472.0	471.4	470.7	470.9	471.8	472.8	473.7	474.7





TEST NUMBER: P332864-830

CATALOG NUMBER: S124DIW-S1195D1560U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	528.7	528.6	528.5	528.5	528.7	528.9	529.0	529.2
115°	616.1	615.9	615.6	615.2	614.9	614.6	614.3	614.0
117.5°	700.2	699.2	698.0	697.2	696.5	696.0	695.3	694.7
120°	757.1	755.6	754.0	753.6	754.2	754.8	755.4	756.1
122.5°	815.0	814.0	812.9	811.8	810.7	809.5	808.4	807.3
125°	899.8	899.2	898.5	897.9	897.2	896.6	896.0	895.3
127.5°	980.8	980.1	979.5	978.9	978.5	978.0	977.4	976.9
130°	1037.6	1037.0	1036.3	1035.4	1034.2	1032.9	1031.6	1030.4
132.5°	1091.1	1090.4	1089.8	1089.2	1088.7	1088.3	1087.7	1087.2
135°	1171.2	1170.6	1170.0	1169.1	1168.2	1167.2	1166.3	1165.4
137.5°	1248.8	1247.9	1247.1	1246.8	1247.0	1247.2	1247.4	1247.5
140°	1299.8	1299.5	1299.1	1298.8	1298.5	1298.2	1297.9	1297.6
142.5°	1348.0	1347.9	1347.9	1347.8	1347.7	1347.7	1347.6	1347.6
145°	1420.6	1420.2	1419.9	1419.3	1418.3	1417.4	1416.5	1415.5
147.5°	1486.4	1486.1	1485.8	1485.5	1485.3	1485.0	1484.6	1484.3
150°	1527.8	1527.8	1527.8	1527.7	1527.3	1527.0	1526.7	1526.4
152.5°	1566.8	1567.5	1568.3	1568.3	1567.4	1566.7	1565.8	1565.0
155°	1621.3	1622.5	1623.8	1623.8	1622.5	1621.3	1620.0	1618.7
157.5°	1669.2	1670.2	1671.1	1671.0	1670.0	1669.0	1667.8	1666.8
160°	1698.8	1699.8	1700.7	1700.3	1698.8	1697.2	1695.6	1694.0
162.5°	1725.3	1727.0	1728.7	1728.8	1727.2	1725.7	1724.1	1722.5
165°	1760.4	1762.3	1764.2	1764.5	1763.2	1762.0	1760.7	1759.4
167.5°	1790.0	1791.9	1793.8	1793.8	1791.8	1789.8	1787.8	1785.8
170°	1805.9	1807.8	1809.7	1809.5	1807.3	1805.1	1802.9	1800.6
172.5°	1817.8	1819.9	1822.0	1822.0	1819.8	1817.6	1815.3	1813.2
175°	1830.7	1832.9	1835.1	1835.1	1832.9	1830.7	1828.4	1826.3
177.5°	1837.8	1839.5	1841.3	1841.2	1839.1	1837.1	1835.1	1833.1
180°	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6

(END OF REPORT)