

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332732-830

Luminaire Tested: **S124DIW-S350D1050U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332732-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S350D1050U830-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1050 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4857.8 lumens
Efficiency: N/A
Efficacy: 127.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 38
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332732-830

CATALOG NUMBER: S124DIW-S350D1050U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332732-830

CATALOG NUMBER: S124DIW-S350D1050U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37	29
1	93	89	85	82	83	80	77	74	63	61	59	47	46	45	33	32	31	25
2	85	78	72	67	76	70	65	61	55	52	49	41	39	37	29	28	26	21
3	77	68	61	55	69	61	55	50	48	44	41	37	34	31	26	24	22	18
4	71	60	53	47	63	54	48	43	43	38	35	33	29	27	23	21	19	15
5	65	53	46	40	58	48	42	36	38	33	30	29	26	23	21	18	17	13
6	59	48	40	34	53	43	36	32	34	30	26	26	23	20	19	16	15	11
7	55	43	35	30	49	39	32	28	31	26	23	24	20	18	17	15	13	10
8	51	39	31	26	45	35	29	24	28	23	20	22	18	16	16	13	12	9
9	47	35	28	23	42	32	26	21	26	21	18	20	17	14	14	12	11	8
10	44	32	25	21	39	29	23	19	24	19	16	18	15	13	13	11	10	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4495	4495	4495
5°	4508	4454	4486
10°	4480	4418	4440
15°	4425	4355	4367
20°	4354	4277	4281
25°	4272	4188	4177
30°	4172	4084	4047
35°	4066	3975	3921
40°	3958	3851	3780
45°	3846	3729	3658
50°	3720	3620	3508
55°	3586	3478	3365
60°	3450	3321	3219
65°	3299	3171	3043
70°	3127	2969	2854
75°	2866	2729	2658
80°	2552	2450	2385
85°	2232	2149	2103



TEST NUMBER: P332732-830

CATALOG NUMBER: S124DIW-S350D1050U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.4	1.1
10°-20°	147.7	3.0
20°-30°	217.4	4.5
30°-40°	252.8	5.2
40°-50°	252.8	5.2
50°-60°	221.1	4.6
60°-70°	164.2	3.4
70°-80°	93.3	1.9
80°-90°	30.6	0.6
90°-100°	81.4	1.7
100°-110°	241.2	5.0
110°-120°	409.4	8.4
120°-130°	539.9	11.1
130°-140°	606.3	12.5
140°-150°	595.8	12.3
150°-160°	501.1	10.3
160°-170°	333.4	6.9
170°-180°	116.7	2.4
0°-30°	417.6	8.6
0°-40°	670.4	13.8
0°-60°	1144.3	23.6
0°-90°	1432.5	29.5
90°-120°	732.1	15.1
90°-150°	2474.1	50.9
90°-180°	3425.0	70.5
0°-180°	4857.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	557	557	557	557	557	
5°	556	554	550	554	554	53
15°	530	528	521	524	522	149
25°	480	476	470	471	469	221
35°	413	409	403	400	398	258
45°	337	333	327	322	320	260
55°	255	253	247	242	239	228
65°	173	170	166	162	159	171
75°	92	90	88	86	85	98
85°	24	24	23	23	23	27
90°	3	13	21	27	29	5
95°	57	66	73	75	75	64
105°	222	224	227	230	233	236
115°	416	416	414	413	412	410
125°	606	606	605	603	602	540
135°	782	787	788	786	783	605
145°	950	954	955	954	951	594
155°	1088	1088	1088	1091	1088	501
165°	1185	1182	1180	1185	1182	334
175°	1233	1228	1227	1233	1227	117
180°	1235	1235	1235	1235	1235	



TEST NUMBER: P332732-830

CATALOG NUMBER: S124DIW-S350D1050U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8
2.5°	558.2	558.0	557.7	557.5	557.2	556.7	555.8	555.0	554.1	553.2	554.0
5°	556.3	555.9	555.5	555.2	554.8	554.0	552.9	551.9	550.7	549.6	550.7
7.5°	551.2	550.7	550.4	550.0	549.6	548.7	547.5	546.4	545.2	543.9	544.8
10°	546.5	546.1	545.7	545.4	545.0	544.1	542.8	541.5	540.3	538.9	539.7
12.5°	540.5	540.1	539.7	539.2	538.9	538.0	536.6	535.3	533.9	532.5	533.4
15°	529.5	529.1	528.8	528.4	528.0	527.1	525.6	524.1	522.5	521.1	521.7
17.5°	516.4	515.9	515.5	515.0	514.4	513.5	512.1	510.7	509.3	507.8	508.2
20°	506.8	506.3	505.9	505.3	504.8	503.9	502.4	500.9	499.4	497.9	498.2
22.5°	496.4	495.8	495.1	494.5	493.8	492.8	491.3	489.8	488.3	486.8	487.4
25°	479.6	478.9	478.2	477.5	476.8	475.8	474.4	473.0	471.6	470.2	470.3
27.5°	460.3	459.6	458.9	458.2	457.5	456.5	455.2	453.9	452.6	451.3	451.1
30°	447.5	446.7	445.9	445.1	444.3	443.3	442.0	440.6	439.4	438.1	437.7
32.5°	433.9	433.2	432.4	431.8	431.0	430.0	428.7	427.3	425.9	424.5	424.0
35°	412.6	412.0	411.3	410.6	409.9	408.9	407.5	406.0	404.7	403.3	402.7
37.5°	390.3	389.6	389.0	388.4	387.8	386.7	385.2	383.7	382.2	380.7	379.9
40°	375.6	374.8	374.1	373.2	372.5	371.4	369.9	368.3	366.8	365.4	364.4
42.5°	360.0	359.5	359.0	358.5	358.1	356.9	355.3	353.6	352.0	350.4	349.2
45°	336.9	336.1	335.5	334.8	334.0	332.9	331.3	329.7	328.2	326.6	325.5
47.5°	312.6	312.2	311.7	311.2	310.8	309.8	308.3	306.8	305.4	303.9	302.7
50°	296.2	295.9	295.5	295.0	294.6	293.8	292.4	291.0	289.5	288.2	286.8
52.5°	280.2	279.7	279.2	278.7	278.2	277.3	275.8	274.4	272.9	271.5	270.2
55°	254.8	254.5	254.1	253.8	253.5	252.7	251.3	250.0	248.5	247.1	246.0
57.5°	230.5	230.2	229.8	229.5	229.1	228.3	226.9	225.6	224.1	222.8	221.7
60°	213.7	213.2	212.7	212.2	211.7	210.8	209.5	208.2	207.0	205.7	204.8
62.5°	197.3	196.9	196.4	196.0	195.6	194.7	193.3	192.0	190.6	189.3	188.4
65°	172.7	172.2	171.6	171.2	170.7	169.9	168.9	168.0	166.9	166.0	164.9
67.5°	147.9	147.4	146.9	146.5	146.0	145.3	144.4	143.5	142.5	141.5	140.5
70°	132.5	131.8	131.1	130.4	129.7	128.9	128.2	127.4	126.6	125.8	125.0
72.5°	116.1	115.4	114.7	114.0	113.3	112.6	112.0	111.4	110.7	110.1	109.4
75°	91.9	91.4	91.0	90.4	89.9	89.4	89.0	88.4	87.9	87.5	87.1
77.5°	68.8	68.6	68.3	68.1	68.0	67.6	67.2	66.7	66.3	65.9	65.7
80°	54.9	54.6	54.3	54.0	53.7	53.4	53.3	53.1	52.9	52.7	52.4
82.5°	41.3	41.2	41.0	40.9	40.7	40.6	40.6	40.6	40.5	40.5	40.4
85°	24.1	24.1	24.1	24.1	24.1	24.0	23.8	23.6	23.4	23.2	23.2
87.5°	9.9	10.3	10.7	11.0	11.4	11.7	12.0	12.3	12.5	12.7	13.0
90°	2.8	5.2	7.5	9.9	12.2	14.2	15.9	17.6	19.3	21.0	22.2
92.5°	20.5	23.1	25.8	28.5	31.1	33.1	34.2	35.4	36.7	37.8	38.5
95°	57.3	59.2	61.1	63.1	64.9	66.6	68.1	69.6	71.1	72.6	73.2
97.5°	100.1	101.6	103.1	104.6	106.2	107.8	109.5	111.3	113.0	114.8	115.6
100°	133.7	134.5	135.3	136.2	137.0	138.5	140.3	142.2	144.2	146.1	146.5
102.5°	168.8	169.2	169.5	169.8	170.1	171.2	173.0	174.7	176.4	178.1	178.8
105°	222.4	222.7	222.9	223.1	223.3	223.9	224.7	225.6	226.4	227.2	227.9
107.5°	278.8	279.1	279.3	279.6	279.8	280.0	280.1	280.3	280.4	280.5	281.2
110°	317.0	317.4	317.8	318.3	318.7	318.8	318.8	318.4	318.2	317.9	317.5



TEST NUMBER: P332732-830

CATALOG NUMBER: S124DIW-S350D1050U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	356.8	356.8	356.9	356.9	357.0	356.9	356.6	356.2	355.8	355.4	355.3
115°	416.3	416.3	416.3	416.3	416.3	416.1	415.7	415.3	414.8	414.4	414.2
117.5°	472.5	472.6	472.8	473.0	473.2	473.1	472.8	472.5	472.2	471.8	471.2
120°	509.9	510.8	511.6	512.5	513.3	513.4	512.7	512.1	511.5	510.9	509.8
122.5°	548.8	549.2	549.5	549.9	550.2	550.3	549.9	549.6	549.3	549.0	548.3
125°	606.3	606.3	606.3	606.3	606.3	606.2	606.0	605.8	605.6	605.4	604.9
127.5°	658.5	659.1	659.7	660.3	661.0	661.2	660.8	660.4	660.2	659.8	659.4
130°	695.1	695.8	696.4	697.0	697.7	698.0	698.0	698.0	698.0	698.0	697.6
132.5°	732.5	733.0	733.5	734.0	734.4	734.5	734.4	734.2	734.1	733.9	733.5
135°	782.0	783.3	784.6	785.8	787.1	787.8	787.8	787.8	787.8	787.8	787.3
137.5°	835.8	836.4	837.1	837.6	838.2	838.7	839.1	839.4	839.7	840.1	839.5
140°	871.8	872.2	872.6	873.1	873.5	873.6	873.6	873.6	873.6	873.6	873.5
142.5°	904.7	905.0	905.5	905.9	906.3	906.4	906.3	906.1	906.0	905.8	905.7
145°	950.1	950.9	951.8	952.6	953.5	953.9	954.2	954.4	954.6	954.8	954.6
147.5°	995.1	996.2	997.2	998.2	999.2	999.7	999.5	999.3	999.1	998.9	998.8
150°	1022.7	1023.5	1024.4	1025.2	1026.1	1026.4	1026.4	1026.4	1026.4	1026.4	1026.4
152.5°	1048.6	1049.1	1049.6	1050.1	1050.7	1050.9	1051.1	1051.3	1051.5	1051.7	1052.2
155°	1088.5	1088.5	1088.5	1088.5	1088.5	1088.4	1088.2	1088.0	1087.8	1087.6	1088.4
157.5°	1122.1	1121.7	1121.3	1121.0	1120.6	1120.4	1120.3	1120.3	1120.2	1120.2	1120.9
160°	1142.0	1141.8	1141.5	1141.3	1141.1	1140.9	1140.7	1140.5	1140.3	1140.1	1140.7
162.5°	1160.3	1159.8	1159.2	1158.7	1158.1	1157.7	1157.5	1157.3	1157.1	1156.9	1158.0
165°	1185.0	1184.3	1183.6	1183.1	1182.4	1181.9	1181.5	1181.0	1180.6	1180.2	1181.5
167.5°	1203.8	1203.0	1202.1	1201.2	1200.3	1199.9	1200.0	1200.0	1200.0	1200.0	1201.3
170°	1214.6	1213.5	1212.4	1211.4	1210.3	1209.8	1210.1	1210.3	1210.5	1210.7	1212.0
172.5°	1222.2	1221.3	1220.4	1219.6	1218.6	1218.2	1218.2	1218.3	1218.3	1218.3	1219.8
175°	1232.7	1231.6	1230.6	1229.5	1228.4	1227.9	1227.6	1227.4	1227.2	1227.0	1228.4
177.5°	1236.1	1235.3	1234.4	1233.6	1232.8	1232.3	1232.3	1232.3	1232.3	1232.3	1233.5
180°	1234.6	1234.6	1234.6	1234.6	1234.6	1234.6	1234.6	1234.6	1234.6	1234.6	1234.6



TEST NUMBER: P332732-830

CATALOG NUMBER: S124DIW-S350D1050U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8
2.5°	554.8	555.6	556.4	556.8	556.7	556.6	556.5	556.4
5°	551.9	552.9	554.0	554.4	554.2	554.0	553.8	553.6
7.5°	545.6	546.6	547.4	547.8	547.7	547.5	547.4	547.3
10°	540.5	541.3	542.2	542.4	542.2	542.0	541.8	541.6
12.5°	534.2	535.1	536.0	536.3	536.0	535.7	535.5	535.2
15°	522.3	522.8	523.5	523.6	523.3	523.0	522.7	522.5
17.5°	508.6	509.0	509.3	509.4	509.3	509.1	508.9	508.7
20°	498.5	498.8	499.1	499.2	498.9	498.7	498.5	498.3
22.5°	487.9	488.4	489.0	489.1	488.7	488.3	488.0	487.7
25°	470.4	470.5	470.6	470.5	470.0	469.7	469.3	468.9
27.5°	450.8	450.6	450.3	450.0	449.5	449.0	448.5	448.0
30°	437.3	437.0	436.5	436.1	435.5	435.1	434.6	434.1
32.5°	423.6	423.1	422.6	422.2	421.7	421.1	420.7	420.2
35°	401.9	401.2	400.5	399.9	399.4	399.0	398.4	397.9
37.5°	379.2	378.4	377.7	377.0	376.4	375.7	375.0	374.4
40°	363.4	362.4	361.5	360.7	360.1	359.7	359.2	358.7
42.5°	348.1	346.9	345.8	345.1	344.7	344.4	344.0	343.7
45°	324.4	323.3	322.3	321.5	321.2	320.9	320.7	320.4
47.5°	301.4	300.2	299.0	298.0	297.3	296.5	295.8	295.0
50°	285.4	284.1	282.7	281.6	281.1	280.5	279.8	279.3
52.5°	269.0	267.8	266.6	265.5	264.8	264.0	263.3	262.5
55°	244.8	243.6	242.4	241.5	240.9	240.3	239.7	239.1
57.5°	220.6	219.4	218.3	217.4	216.9	216.3	215.7	215.1
60°	203.9	203.0	202.1	201.4	201.0	200.4	199.9	199.4
62.5°	187.7	186.8	186.0	185.3	184.8	184.4	183.9	183.3
65°	164.0	163.0	162.0	161.3	160.8	160.2	159.8	159.3
67.5°	139.6	138.6	137.7	137.1	137.0	136.9	136.8	136.6
70°	124.2	123.5	122.6	122.1	121.8	121.5	121.2	120.9
72.5°	108.9	108.2	107.5	107.1	106.8	106.5	106.2	105.9
75°	86.6	86.2	85.9	85.6	85.5	85.4	85.3	85.2
77.5°	65.6	65.5	65.4	65.2	64.9	64.7	64.4	64.2
80°	52.2	52.0	51.8	51.7	51.6	51.5	51.4	51.3
82.5°	40.2	40.2	40.1	40.0	39.9	39.7	39.6	39.5
85°	23.2	23.2	23.2	23.2	23.1	23.0	22.8	22.7
87.5°	13.3	13.6	13.8	13.9	14.0	14.1	14.2	14.3
90°	23.6	24.8	26.1	27.0	27.3	27.8	28.2	28.7
92.5°	39.3	40.1	40.9	41.4	41.7	41.8	42.1	42.4
95°	73.8	74.5	75.1	75.4	75.4	75.4	75.4	75.4
97.5°	116.3	117.1	117.8	118.2	118.2	118.2	118.2	118.2
100°	146.9	147.3	147.8	148.0	148.0	148.0	148.0	148.0
102.5°	179.4	179.9	180.6	181.0	181.1	181.3	181.4	181.6
105°	228.6	229.1	229.8	230.5	231.1	231.7	232.3	233.0
107.5°	281.7	282.3	283.0	283.1	283.1	283.1	283.0	283.0
110°	317.1	316.7	316.2	316.4	317.0	317.6	318.3	319.0



TEST NUMBER: P332732-830

CATALOG NUMBER: S124DIW-S350D1050U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	355.2	355.2	355.1	355.1	355.2	355.3	355.4	355.6
115°	414.0	413.8	413.6	413.3	413.1	412.9	412.7	412.5
117.5°	470.4	469.7	469.0	468.4	468.0	467.6	467.1	466.7
120°	508.7	507.7	506.6	506.2	506.7	507.1	507.6	507.9
122.5°	547.6	546.9	546.1	545.4	544.6	543.8	543.1	542.3
125°	604.5	604.1	603.7	603.2	602.9	602.4	602.0	601.5
127.5°	658.9	658.6	658.1	657.7	657.3	657.0	656.7	656.4
130°	697.1	696.7	696.3	695.7	694.8	694.0	693.1	692.3
132.5°	733.0	732.6	732.2	731.8	731.5	731.1	730.8	730.5
135°	786.9	786.5	786.1	785.5	784.9	784.2	783.6	783.0
137.5°	839.0	838.4	837.8	837.6	837.7	837.9	838.0	838.1
140°	873.3	873.1	872.8	872.6	872.4	872.2	871.9	871.8
142.5°	905.7	905.6	905.6	905.5	905.5	905.5	905.4	905.4
145°	954.4	954.2	953.9	953.6	952.9	952.3	951.7	951.0
147.5°	998.6	998.4	998.2	998.1	997.9	997.7	997.4	997.2
150°	1026.4	1026.4	1026.4	1026.3	1026.1	1026.0	1025.7	1025.5
152.5°	1052.6	1053.2	1053.7	1053.7	1053.1	1052.5	1052.0	1051.5
155°	1089.3	1090.1	1091.0	1091.0	1090.1	1089.3	1088.4	1087.6
157.5°	1121.5	1122.1	1122.8	1122.8	1122.0	1121.2	1120.6	1119.8
160°	1141.3	1142.0	1142.6	1142.4	1141.3	1140.3	1139.3	1138.1
162.5°	1159.1	1160.3	1161.5	1161.5	1160.5	1159.4	1158.3	1157.3
165°	1182.7	1184.0	1185.2	1185.4	1184.6	1183.7	1182.9	1182.0
167.5°	1202.6	1203.8	1205.1	1205.1	1203.8	1202.5	1201.2	1199.9
170°	1213.2	1214.6	1215.8	1215.7	1214.3	1212.8	1211.3	1209.8
172.5°	1221.3	1222.7	1224.2	1224.1	1222.7	1221.2	1219.7	1218.1
175°	1229.9	1231.4	1232.9	1232.9	1231.4	1229.9	1228.4	1227.0
177.5°	1234.7	1235.9	1237.1	1237.0	1235.6	1234.3	1232.9	1231.5
180°	1234.6	1234.6	1234.6	1234.6	1234.6	1234.6	1234.6	1234.6

(END OF REPORT)