

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332737-830

Luminaire Tested: **S124DIW-S350D1340U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332737-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S350D1340U830-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1340 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6489.6 lumens
Efficiency: N/A
Efficacy: 139.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 46.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332737-830

CATALOG NUMBER: S124DIW-S350D1340U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332737-830

CATALOG NUMBER: S124DIW-S350D1340U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	89	89	89	89	68	68	68	48	48	48	30	30	30	22
1	92	87	84	80	81	78	74	72	59	57	55	42	41	40	27	26	26	19
2	83	76	70	65	74	68	63	59	52	49	46	37	35	33	24	22	22	16
3	76	67	60	54	67	60	54	49	46	42	38	33	30	28	21	19	18	13
4	69	59	52	46	61	53	46	41	40	36	33	29	26	24	19	17	16	11
5	63	52	45	39	56	47	40	35	36	31	28	26	23	21	17	15	14	10
6	58	47	39	34	51	42	35	30	32	28	24	23	20	18	15	13	12	9
7	54	42	35	29	48	38	31	26	29	25	21	21	18	16	14	12	11	8
8	50	38	31	26	44	34	28	23	26	22	19	19	16	14	13	11	9	7
9	46	35	27	23	41	31	25	21	24	20	16	18	15	12	12	10	9	6
10	43	32	25	20	38	28	22	18	22	18	15	16	13	11	11	9	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4495	4495	4495
5°	4508	4454	4486
10°	4480	4418	4440
15°	4425	4355	4367
20°	4354	4277	4281
25°	4272	4188	4177
30°	4172	4084	4047
35°	4066	3975	3921
40°	3958	3851	3780
45°	3846	3729	3658
50°	3720	3620	3508
55°	3586	3478	3365
60°	3450	3321	3219
65°	3299	3171	3043
70°	3127	2969	2854
75°	2866	2729	2658
80°	2552	2450	2385
85°	2232	2149	2103



TEST NUMBER: P332737-830

CATALOG NUMBER: S124DIW-S350D1340U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.4	0.8
10°-20°	147.7	2.3
20°-30°	217.4	3.4
30°-40°	252.8	3.9
40°-50°	252.8	3.9
50°-60°	221.1	3.4
60°-70°	164.2	2.5
70°-80°	93.3	1.4
80°-90°	31.6	0.5
90°-100°	55.9	0.9
100°-110°	356.4	5.5
110°-120°	681.9	10.5
120°-130°	865.6	13.3
130°-140°	926.1	14.3
140°-150°	866.0	13.3
150°-160°	698.4	10.8
160°-170°	450.5	6.9
170°-180°	155.3	2.4
0°-30°	417.6	6.4
0°-40°	670.4	10.3
0°-60°	1144.3	17.6
0°-90°	1433.5	22.1
90°-120°	1094.2	16.9
90°-150°	3752.0	57.8
90°-180°	5056.0	77.9
0°-180°	6489.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	557	557	557	557	557	
5°	556	554	550	554	554	53
15°	530	528	521	524	522	149
25°	480	476	470	471	469	221
35°	413	409	403	400	398	258
45°	337	333	327	322	320	260
55°	255	253	247	242	239	228
65°	173	170	166	162	159	171
75°	92	90	88	86	85	98
85°	24	24	23	23	23	27
90°	4	17	27	34	37	4
95°	67	28	27	34	35	86
105°	368	375	381	389	348	385
115°	687	690	690	692	692	676
125°	966	970	968	972	973	862
135°	1198	1197	1202	1204	1207	923
145°	1382	1385	1385	1386	1389	863
155°	1515	1516	1512	1517	1514	698
165°	1598	1592	1592	1600	1590	451
175°	1635	1628	1628	1638	1625	156
180°	1635	1635	1635	1635	1635	



TEST NUMBER: P332737-830

CATALOG NUMBER: S124DIW-S350D1340U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8
2.5°	558.2	558.0	557.7	557.5	557.2	556.7	555.8	555.0	554.1	553.2	554.0
5°	556.3	555.9	555.5	555.2	554.8	554.0	552.9	551.9	550.7	549.6	550.7
7.5°	551.2	550.7	550.4	550.0	549.6	548.7	547.5	546.4	545.2	543.9	544.8
10°	546.5	546.1	545.7	545.4	545.0	544.1	542.8	541.5	540.3	538.9	539.7
12.5°	540.5	540.1	539.7	539.2	538.9	538.0	536.6	535.3	533.9	532.5	533.4
15°	529.5	529.1	528.8	528.4	528.0	527.1	525.6	524.1	522.5	521.1	521.7
17.5°	516.4	515.9	515.5	515.0	514.4	513.5	512.1	510.7	509.3	507.8	508.2
20°	506.8	506.3	505.9	505.3	504.8	503.9	502.4	500.9	499.4	497.9	498.2
22.5°	496.4	495.8	495.1	494.5	493.8	492.8	491.3	489.8	488.3	486.8	487.4
25°	479.6	478.9	478.2	477.5	476.8	475.8	474.4	473.0	471.6	470.2	470.3
27.5°	460.3	459.6	458.9	458.2	457.5	456.5	455.2	453.9	452.6	451.3	451.1
30°	447.5	446.7	445.9	445.1	444.3	443.3	442.0	440.6	439.4	438.1	437.7
32.5°	433.9	433.2	432.4	431.8	431.0	430.0	428.7	427.3	425.9	424.5	424.0
35°	412.6	412.0	411.3	410.6	409.9	408.9	407.5	406.0	404.7	403.3	402.7
37.5°	390.3	389.6	389.0	388.4	387.8	386.7	385.2	383.7	382.2	380.7	379.9
40°	375.6	374.8	374.1	373.2	372.5	371.4	369.9	368.3	366.8	365.4	364.4
42.5°	360.0	359.5	359.0	358.5	358.1	356.9	355.3	353.6	352.0	350.4	349.2
45°	336.9	336.1	335.5	334.8	334.0	332.9	331.3	329.7	328.2	326.6	325.5
47.5°	312.6	312.2	311.7	311.2	310.8	309.8	308.3	306.8	305.4	303.9	302.7
50°	296.2	295.9	295.5	295.0	294.6	293.8	292.4	291.0	289.5	288.2	286.8
52.5°	280.2	279.7	279.2	278.7	278.2	277.3	275.8	274.4	272.9	271.5	270.2
55°	254.8	254.5	254.1	253.8	253.5	252.7	251.3	250.0	248.5	247.1	246.0
57.5°	230.5	230.2	229.8	229.5	229.1	228.3	226.9	225.6	224.1	222.8	221.7
60°	213.7	213.2	212.7	212.2	211.7	210.8	209.5	208.2	207.0	205.7	204.8
62.5°	197.3	196.9	196.4	196.0	195.6	194.7	193.3	192.0	190.6	189.3	188.4
65°	172.7	172.2	171.6	171.2	170.7	169.9	168.9	168.0	166.9	166.0	164.9
67.5°	147.9	147.4	146.9	146.5	146.0	145.3	144.4	143.5	142.5	141.5	140.5
70°	132.5	131.8	131.1	130.4	129.7	128.9	128.2	127.4	126.6	125.8	125.0
72.5°	116.1	115.4	114.7	114.0	113.3	112.6	112.0	111.4	110.7	110.1	109.4
75°	91.9	91.4	91.0	90.4	89.9	89.4	89.0	88.4	87.9	87.5	87.1
77.5°	68.8	68.6	68.3	68.1	68.0	67.6	67.2	66.7	66.3	65.9	65.7
80°	54.9	54.6	54.3	54.0	53.7	53.4	53.3	53.1	52.9	52.7	52.4
82.5°	41.3	41.2	41.0	40.9	40.7	40.6	40.6	40.6	40.5	40.5	40.4
85°	24.1	24.1	24.1	24.1	24.1	24.0	23.8	23.6	23.4	23.2	23.2
87.5°	10.0	10.6	11.0	11.6	12.1	12.5	12.9	13.2	13.6	13.9	14.2
90°	3.7	6.7	9.6	12.6	15.6	18.2	20.4	22.5	24.7	26.9	28.6
92.5°	15.4	15.6	15.7	15.9	16.0	17.2	19.4	21.6	23.8	25.9	27.5
95°	67.2	58.0	48.7	39.5	30.3	25.8	26.1	26.4	26.6	26.9	28.6
97.5°	142.8	148.5	154.3	160.0	165.8	153.5	123.2	92.9	62.6	32.2	32.4
100°	200.5	205.4	210.3	215.2	220.1	203.8	166.3	128.8	91.2	53.8	49.2
102.5°	265.0	268.6	272.2	275.8	279.4	278.7	273.8	269.0	264.1	259.2	209.3
105°	368.0	369.6	371.3	372.9	374.5	376.0	377.4	378.7	380.0	381.4	383.9
107.5°	463.5	464.4	465.2	466.0	466.8	468.2	470.0	471.8	473.7	475.6	476.7
110°	528.1	529.0	529.8	530.6	531.4	532.6	534.2	535.8	537.5	539.1	539.7



TEST NUMBER: P332737-830

CATALOG NUMBER: S124DIW-S350D1340U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	590.7	592.2	593.7	595.1	596.6	597.7	598.5	599.3	600.0	600.8	600.7
115°	687.0	687.9	688.7	689.5	690.3	690.6	690.3	690.0	689.8	689.5	690.0
117.5°	773.8	775.0	776.0	777.1	778.2	779.0	779.7	780.2	780.8	781.5	781.4
120°	832.5	833.6	834.7	835.8	836.9	837.3	837.1	836.8	836.5	836.2	836.8
122.5°	887.3	888.0	888.6	889.3	889.9	890.4	890.8	891.2	891.6	891.9	892.3
125°	965.8	966.9	968.0	969.0	970.2	970.4	969.9	969.3	968.7	968.3	969.0
127.5°	1040.1	1040.4	1040.7	1040.9	1041.2	1042.0	1043.2	1044.4	1045.8	1047.0	1046.8
130°	1088.1	1088.4	1088.6	1088.8	1089.1	1089.7	1090.5	1091.3	1092.1	1093.0	1093.3
132.5°	1132.1	1132.6	1133.0	1133.5	1134.0	1134.8	1135.9	1136.8	1137.8	1138.9	1139.2
135°	1198.1	1197.8	1197.5	1197.3	1197.0	1197.4	1198.4	1199.6	1200.7	1201.7	1202.3
137.5°	1256.5	1256.6	1256.7	1256.9	1257.0	1257.6	1258.8	1260.0	1261.2	1262.3	1263.0
140°	1294.7	1295.2	1295.7	1296.3	1296.8	1297.4	1297.9	1298.4	1299.0	1299.6	1300.3
142.5°	1328.9	1329.8	1330.9	1331.8	1332.8	1333.4	1333.8	1334.1	1334.5	1334.7	1335.4
145°	1381.5	1382.2	1383.1	1383.9	1384.7	1385.2	1385.2	1385.2	1385.2	1385.2	1385.4
147.5°	1423.2	1424.7	1426.3	1427.9	1429.4	1430.0	1429.7	1429.5	1429.2	1428.9	1429.1
150°	1453.6	1454.7	1455.8	1456.9	1457.9	1458.3	1458.1	1457.8	1457.5	1457.3	1457.3
152.5°	1479.0	1479.9	1480.7	1481.6	1482.5	1482.7	1482.2	1481.7	1481.2	1480.7	1481.2
155°	1514.8	1514.9	1515.2	1515.5	1515.8	1515.5	1514.8	1513.9	1513.1	1512.3	1513.3
157.5°	1544.8	1544.6	1544.5	1544.3	1544.2	1543.6	1542.7	1541.7	1540.9	1539.9	1541.3
160°	1562.4	1561.6	1560.8	1559.9	1559.2	1558.6	1558.3	1558.0	1557.7	1557.6	1559.2
162.5°	1578.0	1577.0	1576.0	1575.0	1574.0	1573.3	1573.0	1572.7	1572.4	1572.2	1573.8
165°	1597.9	1596.5	1595.2	1593.7	1592.4	1591.8	1591.8	1591.8	1591.8	1591.8	1593.9
167.5°	1613.5	1612.1	1610.7	1609.3	1607.9	1607.0	1606.9	1606.8	1606.6	1606.4	1608.8
170°	1622.3	1620.7	1619.0	1617.4	1615.8	1615.1	1615.3	1615.6	1615.9	1616.2	1618.3
172.5°	1628.1	1626.5	1624.9	1623.2	1621.6	1621.0	1621.3	1621.6	1621.7	1622.0	1624.2
175°	1634.6	1632.9	1631.3	1629.7	1628.0	1627.3	1627.6	1627.9	1628.1	1628.4	1630.9
177.5°	1637.5	1636.0	1634.4	1632.9	1631.4	1630.8	1631.3	1631.7	1632.1	1632.6	1634.3
180°	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6



TEST NUMBER: P332737-830

CATALOG NUMBER: S124DIW-S350D1340U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8
2.5°	554.8	555.6	556.4	556.8	556.7	556.6	556.5	556.4
5°	551.9	552.9	554.0	554.4	554.2	554.0	553.8	553.6
7.5°	545.6	546.6	547.4	547.8	547.7	547.5	547.4	547.3
10°	540.5	541.3	542.2	542.4	542.2	542.0	541.8	541.6
12.5°	534.2	535.1	536.0	536.3	536.0	535.7	535.5	535.2
15°	522.3	522.8	523.5	523.6	523.3	523.0	522.7	522.5
17.5°	508.6	509.0	509.3	509.4	509.3	509.1	508.9	508.7
20°	498.5	498.8	499.1	499.2	498.9	498.7	498.5	498.3
22.5°	487.9	488.4	489.0	489.1	488.7	488.3	488.0	487.7
25°	470.4	470.5	470.6	470.5	470.0	469.7	469.3	468.9
27.5°	450.8	450.6	450.3	450.0	449.5	449.0	448.5	448.0
30°	437.3	437.0	436.5	436.1	435.5	435.1	434.6	434.1
32.5°	423.6	423.1	422.6	422.2	421.7	421.1	420.7	420.2
35°	401.9	401.2	400.5	399.9	399.4	399.0	398.4	397.9
37.5°	379.2	378.4	377.7	377.0	376.4	375.7	375.0	374.4
40°	363.4	362.4	361.5	360.7	360.1	359.7	359.2	358.7
42.5°	348.1	346.9	345.8	345.1	344.7	344.4	344.0	343.7
45°	324.4	323.3	322.3	321.5	321.2	320.9	320.7	320.4
47.5°	301.4	300.2	299.0	298.0	297.3	296.5	295.8	295.0
50°	285.4	284.1	282.7	281.6	281.1	280.5	279.8	279.3
52.5°	269.0	267.8	266.6	265.5	264.8	264.0	263.3	262.5
55°	244.8	243.6	242.4	241.5	240.9	240.3	239.7	239.1
57.5°	220.6	219.4	218.3	217.4	216.9	216.3	215.7	215.1
60°	203.9	203.0	202.1	201.4	201.0	200.4	199.9	199.4
62.5°	187.7	186.8	186.0	185.3	184.8	184.4	183.9	183.3
65°	164.0	163.0	162.0	161.3	160.8	160.2	159.8	159.3
67.5°	139.6	138.6	137.7	137.1	137.0	136.9	136.8	136.6
70°	124.2	123.5	122.6	122.1	121.8	121.5	121.2	120.9
72.5°	108.9	108.2	107.5	107.1	106.8	106.5	106.2	105.9
75°	86.6	86.2	85.9	85.6	85.5	85.4	85.3	85.2
77.5°	65.6	65.5	65.4	65.2	64.9	64.7	64.4	64.2
80°	52.2	52.0	51.8	51.7	51.6	51.5	51.4	51.3
82.5°	40.2	40.2	40.1	40.0	39.9	39.7	39.6	39.5
85°	23.2	23.2	23.2	23.2	23.1	23.0	22.8	22.7
87.5°	14.6	14.9	15.3	15.5	15.6	15.6	15.8	15.9
90°	30.2	31.8	33.5	34.5	35.1	35.6	36.1	36.7
92.5°	29.2	30.8	32.4	33.3	33.5	33.6	33.6	33.7
95°	30.2	31.8	33.5	34.4	34.6	34.9	35.2	35.4
97.5°	32.6	32.8	32.9	33.2	33.5	33.6	33.9	34.2
100°	44.6	40.0	35.3	33.2	33.5	33.6	33.9	34.2
102.5°	159.6	109.7	59.9	35.0	35.1	35.1	35.2	35.3
105°	386.3	388.8	391.2	387.6	377.8	368.0	358.2	348.5
107.5°	478.0	479.2	480.3	481.5	482.5	483.5	484.6	485.6
110°	540.3	540.7	541.3	542.0	542.8	543.7	544.4	545.3



TEST NUMBER: P332737-830

CATALOG NUMBER: S124DIW-S350D1340U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	600.5	600.4	600.3	600.8	601.8	602.9	603.9	604.9
115°	690.6	691.2	691.6	691.9	691.9	691.9	691.9	691.9
117.5°	781.2	781.1	781.0	780.9	780.8	780.7	780.6	780.4
120°	837.3	837.8	838.4	838.4	837.8	837.3	836.8	836.2
122.5°	892.6	893.0	893.2	893.2	892.6	892.0	891.6	891.0
125°	969.9	970.7	971.5	972.0	972.3	972.6	972.9	973.2
127.5°	1046.7	1046.5	1046.3	1046.1	1045.9	1045.7	1045.5	1045.3
130°	1093.4	1093.7	1094.0	1094.2	1094.2	1094.2	1094.2	1094.2
132.5°	1139.4	1139.7	1140.0	1140.0	1139.8	1139.6	1139.3	1139.2
135°	1202.9	1203.3	1203.9	1204.5	1205.0	1205.5	1206.1	1206.6
137.5°	1263.6	1264.1	1264.8	1265.0	1264.8	1264.7	1264.5	1264.3
140°	1301.2	1302.0	1302.8	1303.3	1303.6	1303.9	1304.2	1304.5
142.5°	1336.0	1336.5	1337.2	1337.5	1337.6	1337.6	1337.7	1337.7
145°	1385.6	1385.9	1386.2	1386.7	1387.1	1387.7	1388.3	1388.8
147.5°	1429.4	1429.6	1429.7	1430.0	1430.3	1430.6	1430.8	1431.1
150°	1457.3	1457.3	1457.3	1457.4	1457.6	1457.9	1458.2	1458.5
152.5°	1481.6	1482.1	1482.4	1482.6	1482.4	1482.2	1482.1	1482.0
155°	1514.5	1515.5	1516.6	1516.7	1516.0	1515.1	1514.3	1513.5
157.5°	1542.8	1544.2	1545.6	1545.6	1544.2	1542.8	1541.3	1539.9
160°	1560.8	1562.4	1564.1	1564.1	1562.4	1560.8	1559.2	1557.6
162.5°	1575.5	1577.1	1578.7	1578.6	1576.8	1574.9	1573.0	1571.2
165°	1596.1	1598.3	1600.4	1600.2	1597.9	1595.4	1593.0	1590.5
167.5°	1611.2	1613.5	1616.0	1615.8	1613.1	1610.3	1607.7	1605.0
170°	1620.5	1622.7	1624.8	1624.6	1621.9	1619.2	1616.5	1613.7
172.5°	1626.4	1628.6	1630.8	1630.4	1627.4	1624.5	1621.6	1618.6
175°	1633.3	1635.8	1638.2	1637.8	1634.6	1631.3	1628.0	1624.8
177.5°	1636.1	1637.8	1639.6	1639.1	1636.4	1633.9	1631.3	1628.6
180°	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6

(END OF REPORT)