

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332106-940

Luminaire Tested: **S123DIW-S340D1030U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332106-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIW-S340D1030U940-4F0-1E-UDD-F  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1030 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4937.0 lumens  
Efficiency: N/A  
Efficacy: 129.9 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 38  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332106-940

CATALOG NUMBER: S123DIW-S340D1030U940-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332106-940

CATALOG NUMBER: S123DIW-S340D1030U940-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34	26
1	92	88	84	81	82	79	75	73	61	59	57	45	43	42	30	29	28	21
2	84	77	71	66	75	69	64	60	53	50	47	39	37	35	26	25	24	18
3	77	67	60	55	68	60	54	50	47	43	39	35	32	30	23	21	20	15
4	70	60	52	46	62	53	47	42	42	37	33	31	28	25	21	19	17	13
5	64	53	45	39	57	47	41	36	37	32	29	27	24	22	18	17	15	11
6	59	47	39	34	52	42	36	31	33	28	25	25	21	19	17	15	13	10
7	54	42	35	30	48	38	32	27	30	25	22	22	19	17	15	13	12	9
8	50	38	31	26	45	35	28	24	27	23	19	20	17	15	14	12	10	8
9	47	35	28	23	42	31	25	21	25	20	17	19	15	13	13	11	9	7
10	43	32	25	20	39	29	23	19	23	18	15	17	14	12	12	10	9	6

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5201	5201	5201
5°	5226	5154	5190
10°	5191	5109	5141
15°	5131	5051	5060
20°	5060	4969	4974
25°	4963	4871	4861
30°	4860	4762	4724
35°	4750	4646	4586
40°	4636	4519	4449
45°	4509	4402	4294
50°	4382	4258	4140
55°	4219	4110	3984
60°	4052	3935	3810
65°	3904	3744	3629
70°	3688	3531	3374
75°	3373	3248	3111
80°	3037	2913	2882
85°	2668	2569	2470



TEST NUMBER: P332106-940

CATALOG NUMBER: S123DIW-S340D1030U940-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	45.5	0.9
10°-20°	128.5	2.6
20°-30°	189.9	3.8
30°-40°	221.8	4.5
40°-50°	223.0	4.5
50°-60°	195.8	4.0
60°-70°	145.9	3.0
70°-80°	83.1	1.7
80°-90°	27.2	0.6
90°-100°	43.8	0.9
100°-110°	208.9	4.2
110°-120°	501.7	10.2
120°-130°	638.9	12.9
130°-140°	682.7	13.8
140°-150°	638.4	12.9
150°-160°	514.9	10.4
160°-170°	332.3	6.7
170°-180°	114.5	2.3
0°-30°	363.9	7.4
0°-40°	585.7	11.9
0°-60°	1004.5	20.3
0°-90°	1260.7	25.5
90°-120°	754.5	15.3
90°-150°	2714.5	55.0
90°-180°	3676.0	74.5
0°-180°	4937.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	483	483	483	483	483	
5°	484	481	477	481	480	46
15°	460	458	453	456	454	130
25°	418	415	410	410	409	192
35°	362	359	354	351	349	226
45°	296	294	289	284	282	229
55°	225	224	219	215	212	201
65°	153	151	147	144	142	151
75°	81	79	78	76	75	87
85°	22	21	21	20	20	24
90°	1	10	22	25	27	4
95°	55	20	28	34	34	68
105°	267	272	196	46	39	283
115°	501	506	514	523	527	494
125°	706	713	716	718	720	630
135°	879	884	888	890	888	676
145°	1014	1020	1022	1024	1024	634
155°	1117	1115	1116	1120	1115	514
165°	1178	1175	1174	1181	1175	333
175°	1206	1201	1202	1208	1201	115
180°	1206	1206	1206	1206	1206	



TEST NUMBER: P332106-940

CATALOG NUMBER: S123DIW-S340D1030U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	483.2	483.2	483.2	483.2	483.2	483.2	483.2	483.2	483.2	483.2	483.2
2.5°	484.9	484.6	484.3	484.0	483.7	483.1	482.3	481.5	480.7	479.9	480.6
5°	483.7	483.1	482.7	482.2	481.8	481.1	480.0	479.0	478.0	477.0	477.9
7.5°	478.9	478.4	478.0	477.5	477.1	476.3	475.3	474.2	473.1	472.1	472.9
10°	474.9	474.5	473.9	473.5	473.1	472.3	471.0	469.8	468.6	467.4	468.2
12.5°	469.6	469.2	468.8	468.4	468.1	467.3	466.2	465.0	463.9	462.8	463.4
15°	460.4	460.0	459.6	459.2	458.9	458.1	456.9	455.7	454.5	453.3	454.1
17.5°	449.6	449.2	448.7	448.2	447.7	446.9	445.7	444.5	443.3	442.1	442.6
20°	441.7	441.1	440.6	440.0	439.4	438.5	437.4	436.1	435.0	433.8	434.2
22.5°	432.7	432.1	431.6	431.1	430.5	429.6	428.4	427.2	426.0	424.8	425.1
25°	417.9	417.4	416.9	416.3	415.8	414.9	413.7	412.5	411.3	410.1	410.2
27.5°	402.3	401.7	401.2	400.6	400.1	399.2	398.0	396.6	395.4	394.0	394.1
30°	391.0	390.5	390.0	389.6	389.1	388.3	387.0	385.7	384.4	383.1	383.1
32.5°	379.7	379.1	378.4	377.8	377.3	376.4	375.4	374.4	373.4	372.5	371.9
35°	361.5	361.0	360.3	359.8	359.3	358.4	357.2	356.0	354.8	353.6	353.0
37.5°	342.9	342.1	341.4	340.7	340.1	339.1	337.9	336.6	335.5	334.2	333.6
40°	329.9	329.3	328.8	328.2	327.7	326.7	325.5	324.1	322.9	321.6	320.8
42.5°	316.9	316.3	315.7	315.0	314.4	313.4	312.2	310.9	309.6	308.3	307.6
45°	296.2	295.9	295.5	295.2	294.8	294.0	292.7	291.6	290.3	289.2	288.1
47.5°	275.7	275.2	274.6	274.1	273.6	272.8	271.6	270.5	269.4	268.2	267.2
50°	261.7	261.3	260.8	260.4	259.9	259.0	257.9	256.7	255.5	254.3	253.2
52.5°	247.1	246.8	246.5	246.2	245.8	245.0	243.8	242.5	241.3	240.0	239.2
55°	224.8	224.7	224.6	224.5	224.4	223.7	222.6	221.3	220.2	219.0	217.9
57.5°	203.5	203.2	202.9	202.6	202.2	201.6	200.6	199.7	198.8	197.8	196.9
60°	188.2	188.2	188.1	188.0	187.9	187.3	186.1	185.0	184.0	182.8	182.0
62.5°	174.6	174.3	174.2	173.9	173.6	173.0	171.8	170.8	169.6	168.5	167.7
65°	153.3	152.8	152.4	151.9	151.5	150.8	149.9	148.9	148.0	147.0	146.3
67.5°	130.8	130.4	130.0	129.6	129.2	128.6	128.0	127.2	126.5	125.8	125.2
70°	117.2	116.6	116.1	115.5	114.9	114.4	113.9	113.2	112.7	112.2	111.6
72.5°	102.9	102.5	102.1	101.7	101.2	100.8	100.1	99.5	98.9	98.3	97.6
75°	81.1	80.6	80.3	79.9	79.5	79.2	78.9	78.6	78.4	78.1	77.7
77.5°	61.6	61.4	61.3	61.1	60.8	60.5	60.3	59.9	59.6	59.2	58.9
80°	49.0	48.8	48.5	48.2	47.9	47.7	47.5	47.3	47.2	47.0	46.8
82.5°	36.7	36.6	36.6	36.6	36.5	36.5	36.4	36.4	36.4	36.3	36.1
85°	21.6	21.4	21.2	21.0	20.9	20.8	20.8	20.8	20.8	20.8	20.6
87.5°	8.8	9.0	9.2	9.4	9.5	9.8	10.3	10.7	11.1	11.6	11.7
90°	0.9	2.9	4.9	6.9	8.8	11.1	13.7	16.3	18.9	21.5	22.3
92.5°	16.7	16.1	15.5	15.0	14.4	15.2	17.1	19.0	21.0	22.9	24.2
95°	54.7	46.5	38.3	30.1	22.0	19.0	21.2	23.4	25.6	27.7	29.2
97.5°	109.8	106.1	102.5	98.8	95.1	86.1	71.9	57.5	43.2	28.8	30.4
100°	151.3	155.3	159.3	163.3	167.3	153.7	122.7	91.7	60.6	29.5	31.1
102.5°	198.7	201.5	204.4	207.2	210.1	194.6	160.7	126.8	92.8	58.9	54.0
105°	266.9	269.1	271.3	273.5	275.6	267.8	249.9	231.9	214.1	196.2	161.0
107.5°	338.9	340.6	342.4	344.2	345.9	348.2	351.1	353.8	356.7	359.5	333.7
110°	386.9	388.5	390.1	391.7	393.2	395.2	397.3	399.6	401.7	403.9	397.3



TEST NUMBER: P332106-940

CATALOG NUMBER: S123DIW-S340D1030U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	432.7	434.2	435.6	437.1	438.5	440.3	442.5	444.7	446.9	449.1	449.2
115°	500.7	501.9	503.0	504.3	505.4	506.9	508.7	510.5	512.3	514.1	516.1
117.5°	566.4	567.8	569.4	570.8	572.3	573.5	574.4	575.3	576.2	577.1	578.7
120°	607.3	609.0	610.8	612.6	614.4	615.6	616.2	616.8	617.4	618.0	619.6
122.5°	648.8	650.2	651.8	653.2	654.7	655.8	656.6	657.3	658.1	658.8	660.0
125°	705.8	707.4	708.9	710.5	712.1	713.4	714.1	714.9	715.7	716.5	716.9
127.5°	760.9	762.5	764.1	765.7	767.3	768.6	769.5	770.5	771.4	772.4	773.0
130°	795.3	796.9	798.5	800.1	801.7	802.9	803.7	804.5	805.3	806.1	806.9
132.5°	828.3	829.9	831.4	833.0	834.6	835.8	836.4	837.0	837.7	838.3	839.1
135°	878.6	879.9	881.0	882.2	883.4	884.4	885.2	886.0	886.8	887.6	888.1
137.5°	921.6	923.1	924.6	926.1	927.6	928.6	929.1	929.5	930.0	930.4	931.3
140°	950.3	951.5	952.7	953.9	955.0	955.9	956.5	957.2	957.7	958.3	959.1
142.5°	976.8	977.9	979.2	980.3	981.6	982.5	983.0	983.6	984.3	984.8	985.5
145°	1013.9	1015.2	1016.6	1018.1	1019.4	1020.3	1020.7	1021.1	1021.5	1021.9	1022.3
147.5°	1048.8	1049.7	1050.6	1051.5	1052.5	1053.1	1053.5	1053.9	1054.3	1054.7	1055.1
150°	1070.3	1070.9	1071.5	1072.1	1072.6	1073.2	1073.5	1074.0	1074.3	1074.8	1075.1
152.5°	1089.7	1089.9	1090.2	1090.5	1090.7	1091.0	1091.3	1091.5	1091.7	1092.0	1092.7
155°	1116.9	1116.4	1116.1	1115.7	1115.3	1115.2	1115.4	1115.5	1115.8	1116.0	1117.0
157.5°	1138.0	1138.0	1137.9	1137.9	1137.8	1137.7	1137.6	1137.3	1137.1	1136.9	1138.1
160°	1150.9	1150.7	1150.5	1150.3	1150.1	1149.9	1149.7	1149.5	1149.3	1149.1	1150.3
162.5°	1163.1	1162.5	1162.1	1161.5	1161.0	1160.7	1160.5	1160.3	1160.0	1159.8	1161.2
165°	1177.8	1177.1	1176.6	1176.0	1175.4	1175.0	1174.7	1174.6	1174.4	1174.2	1175.8
167.5°	1189.2	1188.5	1187.7	1186.9	1186.1	1185.6	1185.6	1185.6	1185.6	1185.6	1187.2
170°	1195.7	1194.9	1194.1	1193.3	1192.5	1192.1	1192.1	1192.1	1192.1	1192.1	1193.6
172.5°	1200.0	1199.0	1198.1	1197.1	1196.1	1195.8	1195.9	1196.1	1196.2	1196.4	1198.0
175°	1205.5	1204.5	1203.5	1202.6	1201.6	1201.1	1201.3	1201.6	1201.8	1201.9	1203.4
177.5°	1206.9	1206.1	1205.4	1204.6	1203.8	1203.5	1203.6	1203.8	1203.9	1204.1	1205.4
180°	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5



TEST NUMBER: P332106-940

CATALOG NUMBER: S123DIW-S340D1030U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	483.2	483.2	483.2	483.2	483.2	483.2	483.2	483.2
2.5°	481.3	482.1	482.9	483.2	483.1	483.0	483.0	482.9
5°	478.8	479.7	480.7	481.1	480.9	480.7	480.5	480.3
7.5°	473.8	474.6	475.4	475.7	475.6	475.5	475.5	475.3
10°	469.1	469.9	470.7	471.1	470.9	470.7	470.6	470.4
12.5°	464.0	464.6	465.2	465.5	465.4	465.2	465.1	465.0
15°	454.8	455.5	456.3	456.4	455.8	455.2	454.7	454.1
17.5°	443.1	443.6	444.2	444.3	444.1	443.9	443.7	443.5
20°	434.5	434.9	435.2	435.3	435.0	434.7	434.4	434.2
22.5°	425.3	425.7	426.0	426.0	425.6	425.3	424.9	424.5
25°	410.3	410.4	410.5	410.4	410.1	409.8	409.6	409.3
27.5°	394.2	394.3	394.3	394.2	393.9	393.5	393.2	392.8
30°	383.1	383.1	383.1	382.7	382.1	381.5	380.8	380.1
32.5°	371.4	370.9	370.4	370.0	369.6	369.3	368.9	368.5
35°	352.5	352.0	351.3	350.9	350.4	349.9	349.5	349.0
37.5°	332.9	332.3	331.5	331.1	330.8	330.5	330.2	329.9
40°	320.1	319.4	318.6	318.1	317.7	317.4	317.0	316.6
42.5°	306.8	306.0	305.3	304.8	304.4	304.1	303.7	303.3
45°	287.0	285.9	284.7	284.0	283.5	283.0	282.6	282.1
47.5°	266.1	265.0	263.9	263.1	262.7	262.3	261.9	261.5
50°	252.3	251.2	250.2	249.4	248.9	248.3	247.8	247.2
52.5°	238.3	237.4	236.5	235.8	235.2	234.7	234.2	233.6
55°	217.0	215.9	214.9	214.2	213.7	213.2	212.8	212.3
57.5°	196.0	195.0	194.1	193.4	192.9	192.3	191.8	191.3
60°	181.2	180.3	179.5	178.9	178.3	177.9	177.5	177.0
62.5°	166.8	166.0	165.2	164.6	164.3	164.0	163.7	163.4
65°	145.6	144.9	144.1	143.7	143.4	143.0	142.8	142.5
67.5°	124.5	123.9	123.2	122.7	122.3	121.9	121.5	121.2
70°	110.9	110.2	109.6	109.1	108.6	108.2	107.6	107.2
72.5°	97.1	96.5	95.9	95.5	95.3	95.1	94.8	94.5
75°	77.2	76.7	76.2	75.9	75.6	75.3	75.1	74.8
77.5°	58.6	58.3	58.0	57.9	57.9	57.9	57.9	57.9
80°	46.7	46.6	46.5	46.5	46.5	46.5	46.5	46.5
82.5°	36.0	35.8	35.7	35.5	35.5	35.4	35.3	35.2
85°	20.4	20.2	20.1	20.0	20.0	20.0	20.0	20.0
87.5°	11.8	11.9	11.9	12.0	12.1	12.2	12.3	12.4
90°	23.1	23.9	24.7	25.2	25.7	26.0	26.5	26.8
92.5°	25.5	26.8	28.0	28.8	29.0	29.2	29.5	29.7
95°	30.6	31.9	33.3	34.1	34.1	34.1	34.1	34.1
97.5°	32.0	33.6	35.2	36.1	36.3	36.5	36.7	36.9
100°	32.7	34.3	35.9	36.8	37.0	37.2	37.5	37.6
102.5°	49.0	44.1	39.1	36.9	37.3	37.6	38.0	38.3
105°	125.7	90.4	55.2	37.8	38.3	38.6	39.0	39.4
107.5°	307.8	282.0	256.2	230.0	203.4	176.9	150.3	123.8
110°	390.8	384.2	377.6	360.2	331.7	303.2	274.7	246.3





TEST NUMBER: P332106-940

CATALOG NUMBER: S123DIW-S340D1030U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	449.3	449.4	449.5	446.6	440.6	434.6	428.6	422.6
115°	518.1	520.0	522.1	523.4	524.2	525.0	525.8	526.6
117.5°	580.3	581.9	583.5	584.4	584.5	584.7	584.9	585.1
120°	621.2	622.8	624.4	625.2	625.2	625.2	625.2	625.2
122.5°	661.0	662.2	663.3	664.0	664.1	664.2	664.4	664.6
125°	717.3	717.7	718.1	718.5	718.9	719.3	719.7	720.1
127.5°	773.6	774.3	775.0	775.1	774.6	774.3	773.9	773.5
130°	807.7	808.4	809.2	809.5	809.0	808.7	808.2	807.9
132.5°	839.9	840.7	841.5	841.6	841.1	840.5	840.0	839.4
135°	888.8	889.4	889.9	889.9	889.4	888.8	888.1	887.6
137.5°	932.3	933.3	934.2	934.5	934.1	933.7	933.3	932.9
140°	959.9	960.7	961.5	961.7	961.4	960.9	960.6	960.1
142.5°	986.1	986.8	987.4	987.4	986.9	986.3	985.8	985.2
145°	1022.7	1023.1	1023.5	1023.7	1023.7	1023.7	1023.7	1023.7
147.5°	1055.5	1055.9	1056.3	1056.1	1055.2	1054.2	1053.3	1052.4
150°	1075.6	1075.9	1076.4	1076.3	1075.7	1075.0	1074.5	1073.9
152.5°	1093.4	1094.1	1094.8	1094.8	1093.8	1092.9	1092.0	1091.1
155°	1117.9	1118.9	1120.0	1119.8	1118.7	1117.5	1116.2	1115.1
157.5°	1139.3	1140.5	1141.7	1141.5	1140.0	1138.4	1136.8	1135.3
160°	1151.5	1152.7	1153.9	1153.8	1152.4	1151.0	1149.6	1148.2
162.5°	1162.5	1164.0	1165.3	1165.3	1164.1	1162.9	1161.6	1160.4
165°	1177.3	1178.9	1180.5	1180.6	1179.3	1177.9	1176.4	1175.1
167.5°	1188.8	1190.4	1192.0	1192.0	1190.4	1188.8	1187.2	1185.6
170°	1195.2	1196.9	1198.5	1198.5	1196.9	1195.2	1193.6	1192.1
172.5°	1199.6	1201.1	1202.7	1202.7	1201.0	1199.2	1197.4	1195.7
175°	1204.7	1206.1	1207.6	1207.5	1205.9	1204.3	1202.7	1201.0
177.5°	1206.7	1207.9	1209.2	1209.1	1207.5	1205.9	1204.3	1202.7
180°	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5

(END OF REPORT)