

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332738-830

Luminaire Tested: **S124DIW-S350D1340U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332738-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIW-S350D1340U830-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5818.5 lumens  
Efficiency: N/A  
Efficacy: 124.9 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 46.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332738-830

CATALOG NUMBER: S124DIW-S350D1340U830-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332738-830

CATALOG NUMBER: S124DIW-S350D1340U830-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	33	33	33	25
1	92	88	84	81	82	78	75	72	60	58	57	44	43	42	29	28	28	21
2	84	77	71	66	74	68	63	59	53	50	47	39	37	35	25	24	23	17
3	76	67	60	55	68	60	54	49	47	43	39	34	31	29	22	21	20	15
4	70	59	52	46	62	53	47	42	41	37	33	30	27	25	20	18	17	13
5	64	53	45	39	57	47	41	36	37	32	29	27	24	22	18	16	15	11
6	59	47	39	34	52	42	36	31	33	28	25	24	21	19	16	14	13	10
7	54	42	35	29	48	38	32	27	30	25	22	22	19	16	15	13	11	9
8	50	38	31	26	45	34	28	24	27	22	19	20	17	15	14	12	10	8
9	47	35	28	23	41	31	25	21	25	20	17	18	15	13	13	11	9	7
10	43	32	25	20	39	29	23	19	23	18	15	17	14	12	12	10	8	6

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	4495	4495	4495
5°	4508	4454	4486
10°	4480	4418	4440
15°	4425	4355	4367
20°	4354	4277	4281
25°	4272	4188	4177
30°	4172	4084	4047
35°	4066	3975	3921
40°	3958	3851	3780
45°	3846	3729	3658
50°	3720	3620	3508
55°	3586	3478	3365
60°	3450	3321	3219
65°	3299	3171	3043
70°	3127	2969	2854
75°	2866	2729	2658
80°	2552	2450	2385
85°	2232	2149	2103



TEST NUMBER: P332738-830

CATALOG NUMBER: S124DIW-S350D1340U830-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	52.4	0.9
10°-20°	147.7	2.5
20°-30°	217.4	3.7
30°-40°	252.8	4.3
40°-50°	252.8	4.3
50°-60°	221.1	3.8
60°-70°	164.2	2.8
70°-80°	93.3	1.6
80°-90°	31.6	0.5
90°-100°	104.3	1.8
100°-110°	308.8	5.3
110°-120°	524.1	9.0
120°-130°	691.1	11.9
130°-140°	776.2	13.3
140°-150°	762.7	13.1
150°-160°	641.5	11.0
160°-170°	426.8	7.3
170°-180°	149.5	2.6
0°-30°	417.6	7.2
0°-40°	670.4	11.5
0°-60°	1144.3	19.7
0°-90°	1433.5	24.6
90°-120°	937.2	16.1
90°-150°	3167.3	54.4
90°-180°	4385.0	75.4
0°-180°	5818.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	557	557	557	557	557	
5°	556	554	550	554	554	53
15°	530	528	521	524	522	149
25°	480	476	470	471	469	221
35°	413	409	403	400	398	258
45°	337	333	327	322	320	260
55°	255	253	247	242	239	228
65°	173	170	166	162	159	171
75°	92	90	88	86	85	98
85°	24	24	23	23	23	27
90°	4	17	27	34	37	6
95°	73	84	93	96	97	82
105°	285	286	291	295	298	302
115°	533	533	530	529	528	525
125°	776	776	775	772	770	692
135°	1001	1008	1008	1006	1002	774
145°	1216	1221	1222	1221	1218	761
155°	1394	1393	1392	1397	1392	641
165°	1517	1513	1511	1518	1513	427
175°	1578	1572	1571	1578	1571	150
180°	1580	1580	1580	1580	1580	



TEST NUMBER: P332738-830

CATALOG NUMBER: S124DIW-S350D1340U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8
2.5°	558.2	558.0	557.7	557.5	557.2	556.7	555.8	555.0	554.1	553.2	554.0
5°	556.3	555.9	555.5	555.2	554.8	554.0	552.9	551.9	550.7	549.6	550.7
7.5°	551.2	550.7	550.4	550.0	549.6	548.7	547.5	546.4	545.2	543.9	544.8
10°	546.5	546.1	545.7	545.4	545.0	544.1	542.8	541.5	540.3	538.9	539.7
12.5°	540.5	540.1	539.7	539.2	538.9	538.0	536.6	535.3	533.9	532.5	533.4
15°	529.5	529.1	528.8	528.4	528.0	527.1	525.6	524.1	522.5	521.1	521.7
17.5°	516.4	515.9	515.5	515.0	514.4	513.5	512.1	510.7	509.3	507.8	508.2
20°	506.8	506.3	505.9	505.3	504.8	503.9	502.4	500.9	499.4	497.9	498.2
22.5°	496.4	495.8	495.1	494.5	493.8	492.8	491.3	489.8	488.3	486.8	487.4
25°	479.6	478.9	478.2	477.5	476.8	475.8	474.4	473.0	471.6	470.2	470.3
27.5°	460.3	459.6	458.9	458.2	457.5	456.5	455.2	453.9	452.6	451.3	451.1
30°	447.5	446.7	445.9	445.1	444.3	443.3	442.0	440.6	439.4	438.1	437.7
32.5°	433.9	433.2	432.4	431.8	431.0	430.0	428.7	427.3	425.9	424.5	424.0
35°	412.6	412.0	411.3	410.6	409.9	408.9	407.5	406.0	404.7	403.3	402.7
37.5°	390.3	389.6	389.0	388.4	387.8	386.7	385.2	383.7	382.2	380.7	379.9
40°	375.6	374.8	374.1	373.2	372.5	371.4	369.9	368.3	366.8	365.4	364.4
42.5°	360.0	359.5	359.0	358.5	358.1	356.9	355.3	353.6	352.0	350.4	349.2
45°	336.9	336.1	335.5	334.8	334.0	332.9	331.3	329.7	328.2	326.6	325.5
47.5°	312.6	312.2	311.7	311.2	310.8	309.8	308.3	306.8	305.4	303.9	302.7
50°	296.2	295.9	295.5	295.0	294.6	293.8	292.4	291.0	289.5	288.2	286.8
52.5°	280.2	279.7	279.2	278.7	278.2	277.3	275.8	274.4	272.9	271.5	270.2
55°	254.8	254.5	254.1	253.8	253.5	252.7	251.3	250.0	248.5	247.1	246.0
57.5°	230.5	230.2	229.8	229.5	229.1	228.3	226.9	225.6	224.1	222.8	221.7
60°	213.7	213.2	212.7	212.2	211.7	210.8	209.5	208.2	207.0	205.7	204.8
62.5°	197.3	196.9	196.4	196.0	195.6	194.7	193.3	192.0	190.6	189.3	188.4
65°	172.7	172.2	171.6	171.2	170.7	169.9	168.9	168.0	166.9	166.0	164.9
67.5°	147.9	147.4	146.9	146.5	146.0	145.3	144.4	143.5	142.5	141.5	140.5
70°	132.5	131.8	131.1	130.4	129.7	128.9	128.2	127.4	126.6	125.8	125.0
72.5°	116.1	115.4	114.7	114.0	113.3	112.6	112.0	111.4	110.7	110.1	109.4
75°	91.9	91.4	91.0	90.4	89.9	89.4	89.0	88.4	87.9	87.5	87.1
77.5°	68.8	68.6	68.3	68.1	68.0	67.6	67.2	66.7	66.3	65.9	65.7
80°	54.9	54.6	54.3	54.0	53.7	53.4	53.3	53.1	52.9	52.7	52.4
82.5°	41.3	41.2	41.0	40.9	40.7	40.6	40.6	40.6	40.5	40.5	40.4
85°	24.1	24.1	24.1	24.1	24.1	24.0	23.8	23.6	23.4	23.2	23.2
87.5°	10.0	10.6	11.0	11.6	12.1	12.5	12.9	13.2	13.6	13.9	14.2
90°	3.7	6.7	9.6	12.6	15.6	18.2	20.4	22.5	24.7	26.9	28.6
92.5°	26.2	29.6	33.0	36.4	39.9	42.3	43.8	45.3	46.8	48.4	49.4
95°	73.3	75.8	78.2	80.7	83.1	85.3	87.2	89.1	91.0	92.9	93.7
97.5°	128.1	130.1	132.1	133.9	135.9	138.0	140.3	142.5	144.7	146.9	147.9
100°	171.2	172.2	173.3	174.4	175.5	177.2	179.6	182.1	184.5	187.0	187.6
102.5°	216.1	216.6	217.0	217.4	217.8	219.1	221.4	223.7	225.8	228.1	228.8
105°	284.8	285.1	285.4	285.6	285.9	286.5	287.7	288.8	289.8	291.0	291.7
107.5°	356.9	357.2	357.6	357.9	358.3	358.4	358.6	358.8	359.0	359.1	359.9
110°	405.9	406.3	406.9	407.5	408.0	408.1	407.8	407.6	407.4	407.1	406.5



TEST NUMBER: P332738-830

CATALOG NUMBER: S124DIW-S350D1340U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	456.7	456.8	456.9	457.0	457.1	456.9	456.5	455.9	455.4	455.0	454.9
115°	532.9	532.9	532.9	532.9	532.9	532.7	532.2	531.6	531.0	530.5	530.3
117.5°	604.8	605.0	605.3	605.5	605.7	605.6	605.2	604.8	604.5	604.1	603.1
120°	652.7	653.8	654.9	656.0	657.0	657.2	656.4	655.6	654.8	653.9	652.6
122.5°	702.6	703.0	703.5	703.9	704.4	704.4	704.0	703.6	703.2	702.9	701.9
125°	776.2	776.2	776.2	776.2	776.2	776.1	775.8	775.5	775.2	775.0	774.4
127.5°	842.9	843.8	844.6	845.4	846.2	846.4	845.9	845.6	845.1	844.6	844.1
130°	889.9	890.7	891.6	892.3	893.2	893.5	893.5	893.5	893.5	893.5	893.0
132.5°	937.8	938.4	939.0	939.6	940.2	940.4	940.2	939.9	939.7	939.5	939.0
135°	1001.1	1002.8	1004.4	1006.0	1007.7	1008.4	1008.4	1008.4	1008.4	1008.4	1008.0
137.5°	1070.1	1070.8	1071.6	1072.3	1073.1	1073.7	1074.1	1074.6	1075.0	1075.4	1074.7
140°	1116.1	1116.5	1117.1	1117.7	1118.2	1118.4	1118.4	1118.4	1118.4	1118.4	1118.2
142.5°	1158.1	1158.6	1159.1	1159.7	1160.3	1160.4	1160.2	1160.0	1159.8	1159.5	1159.5
145°	1216.3	1217.4	1218.4	1219.6	1220.6	1221.3	1221.5	1221.8	1222.1	1222.4	1222.1
147.5°	1273.9	1275.3	1276.6	1277.9	1279.1	1279.7	1279.5	1279.3	1279.0	1278.8	1278.7
150°	1309.2	1310.2	1311.4	1312.4	1313.5	1314.0	1314.0	1314.0	1314.0	1314.0	1314.0
152.5°	1342.4	1343.0	1343.7	1344.3	1345.0	1345.5	1345.7	1345.9	1346.1	1346.3	1347.0
155°	1393.5	1393.5	1393.5	1393.5	1393.5	1393.4	1393.1	1392.8	1392.5	1392.3	1393.4
157.5°	1436.5	1436.1	1435.6	1435.0	1434.5	1434.3	1434.3	1434.2	1434.2	1434.1	1434.9
160°	1462.0	1461.7	1461.4	1461.1	1460.8	1460.6	1460.3	1460.1	1459.8	1459.5	1460.3
162.5°	1485.4	1484.7	1484.0	1483.3	1482.6	1482.1	1481.9	1481.6	1481.3	1481.0	1482.5
165°	1516.9	1516.2	1515.3	1514.5	1513.7	1513.1	1512.5	1511.9	1511.4	1510.8	1512.5
167.5°	1541.2	1540.0	1538.9	1537.8	1536.6	1536.1	1536.2	1536.2	1536.3	1536.3	1537.9
170°	1554.8	1553.5	1552.2	1550.8	1549.4	1548.9	1549.2	1549.4	1549.7	1549.9	1551.6
172.5°	1564.6	1563.5	1562.4	1561.2	1560.1	1559.5	1559.6	1559.6	1559.7	1559.7	1561.6
175°	1578.1	1576.7	1575.4	1574.0	1572.6	1571.8	1571.6	1571.3	1571.0	1570.7	1572.6
177.5°	1582.4	1581.4	1580.3	1579.2	1578.1	1577.6	1577.6	1577.6	1577.6	1577.6	1579.1
180°	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5



TEST NUMBER: P332738-830

CATALOG NUMBER: S124DIW-S350D1340U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8
2.5°	554.8	555.6	556.4	556.8	556.7	556.6	556.5	556.4
5°	551.9	552.9	554.0	554.4	554.2	554.0	553.8	553.6
7.5°	545.6	546.6	547.4	547.8	547.7	547.5	547.4	547.3
10°	540.5	541.3	542.2	542.4	542.2	542.0	541.8	541.6
12.5°	534.2	535.1	536.0	536.3	536.0	535.7	535.5	535.2
15°	522.3	522.8	523.5	523.6	523.3	523.0	522.7	522.5
17.5°	508.6	509.0	509.3	509.4	509.3	509.1	508.9	508.7
20°	498.5	498.8	499.1	499.2	498.9	498.7	498.5	498.3
22.5°	487.9	488.4	489.0	489.1	488.7	488.3	488.0	487.7
25°	470.4	470.5	470.6	470.5	470.0	469.7	469.3	468.9
27.5°	450.8	450.6	450.3	450.0	449.5	449.0	448.5	448.0
30°	437.3	437.0	436.5	436.1	435.5	435.1	434.6	434.1
32.5°	423.6	423.1	422.6	422.2	421.7	421.1	420.7	420.2
35°	401.9	401.2	400.5	399.9	399.4	399.0	398.4	397.9
37.5°	379.2	378.4	377.7	377.0	376.4	375.7	375.0	374.4
40°	363.4	362.4	361.5	360.7	360.1	359.7	359.2	358.7
42.5°	348.1	346.9	345.8	345.1	344.7	344.4	344.0	343.7
45°	324.4	323.3	322.3	321.5	321.2	320.9	320.7	320.4
47.5°	301.4	300.2	299.0	298.0	297.3	296.5	295.8	295.0
50°	285.4	284.1	282.7	281.6	281.1	280.5	279.8	279.3
52.5°	269.0	267.8	266.6	265.5	264.8	264.0	263.3	262.5
55°	244.8	243.6	242.4	241.5	240.9	240.3	239.7	239.1
57.5°	220.6	219.4	218.3	217.4	216.9	216.3	215.7	215.1
60°	203.9	203.0	202.1	201.4	201.0	200.4	199.9	199.4
62.5°	187.7	186.8	186.0	185.3	184.8	184.4	183.9	183.3
65°	164.0	163.0	162.0	161.3	160.8	160.2	159.8	159.3
67.5°	139.6	138.6	137.7	137.1	137.0	136.9	136.8	136.6
70°	124.2	123.5	122.6	122.1	121.8	121.5	121.2	120.9
72.5°	108.9	108.2	107.5	107.1	106.8	106.5	106.2	105.9
75°	86.6	86.2	85.9	85.6	85.5	85.4	85.3	85.2
77.5°	65.6	65.5	65.4	65.2	64.9	64.7	64.4	64.2
80°	52.2	52.0	51.8	51.7	51.6	51.5	51.4	51.3
82.5°	40.2	40.2	40.1	40.0	39.9	39.7	39.6	39.5
85°	23.2	23.2	23.2	23.2	23.1	23.0	22.8	22.7
87.5°	14.6	14.9	15.3	15.5	15.6	15.6	15.8	15.9
90°	30.2	31.8	33.4	34.5	35.1	35.6	36.1	36.7
92.5°	50.3	51.4	52.3	53.0	53.3	53.6	53.9	54.3
95°	94.5	95.4	96.1	96.6	96.6	96.6	96.6	96.6
97.5°	148.9	149.9	150.8	151.4	151.4	151.4	151.4	151.4
100°	188.1	188.7	189.2	189.5	189.5	189.5	189.5	189.5
102.5°	229.6	230.4	231.1	231.6	231.9	232.1	232.2	232.5
105°	292.6	293.4	294.2	295.0	295.8	296.6	297.5	298.2
107.5°	360.6	361.4	362.2	362.5	362.5	362.4	362.4	362.3
110°	406.0	405.4	404.9	405.0	405.9	406.6	407.5	408.3





TEST NUMBER: P332738-830

CATALOG NUMBER: S124DIW-S350D1340U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	454.8	454.7	454.5	454.6	454.7	454.9	455.1	455.2
115°	530.0	529.7	529.4	529.1	528.9	528.6	528.3	528.1
117.5°	602.3	601.3	600.4	599.6	599.1	598.6	598.0	597.5
120°	651.3	649.9	648.6	648.1	648.7	649.2	649.8	650.3
122.5°	701.0	700.1	699.2	698.2	697.2	696.3	695.3	694.3
125°	773.9	773.4	772.8	772.2	771.8	771.2	770.6	770.1
127.5°	843.6	843.0	842.4	842.0	841.6	841.1	840.7	840.3
130°	892.5	891.9	891.4	890.6	889.5	888.3	887.3	886.2
132.5°	938.4	937.9	937.4	936.9	936.4	935.9	935.6	935.1
135°	1007.4	1006.8	1006.3	1005.6	1004.8	1004.0	1003.1	1002.3
137.5°	1074.0	1073.4	1072.6	1072.3	1072.5	1072.7	1072.8	1073.0
140°	1117.9	1117.7	1117.4	1117.1	1116.8	1116.5	1116.3	1116.1
142.5°	1159.4	1159.4	1159.3	1159.2	1159.2	1159.1	1159.1	1159.0
145°	1221.8	1221.5	1221.3	1220.8	1219.9	1219.1	1218.3	1217.5
147.5°	1278.4	1278.2	1278.0	1277.7	1277.4	1277.1	1277.0	1276.7
150°	1314.0	1314.0	1314.0	1313.9	1313.6	1313.3	1313.1	1312.9
152.5°	1347.6	1348.3	1349.0	1348.9	1348.2	1347.5	1346.8	1346.0
155°	1394.5	1395.5	1396.7	1396.7	1395.5	1394.5	1393.4	1392.3
157.5°	1435.7	1436.5	1437.4	1437.3	1436.3	1435.4	1434.5	1433.6
160°	1461.1	1462.0	1462.7	1462.4	1461.1	1459.8	1458.4	1457.1
162.5°	1483.9	1485.4	1486.9	1487.0	1485.5	1484.2	1482.9	1481.5
165°	1514.1	1515.7	1517.4	1517.7	1516.6	1515.4	1514.4	1513.3
167.5°	1539.5	1541.2	1542.8	1542.8	1541.1	1539.4	1537.8	1536.1
170°	1553.2	1554.8	1556.5	1556.3	1554.4	1552.6	1550.7	1548.8
172.5°	1563.4	1565.3	1567.2	1567.1	1565.2	1563.3	1561.4	1559.5
175°	1574.5	1576.4	1578.4	1578.4	1576.4	1574.5	1572.6	1570.7
177.5°	1580.6	1582.2	1583.7	1583.6	1581.9	1580.1	1578.4	1576.6
180°	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5

(END OF REPORT)