

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332107-940

Luminaire Tested: **S123DIW-S340D1030U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332107-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIW-S340D1030U940-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1030 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4447.1 lumens  
Efficiency: N/A  
Efficacy: 117.0 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 38  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332107-940

CATALOG NUMBER: S123DIW-S340D1030U940-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332107-940

CATALOG NUMBER: S123DIW-S340D1030U940-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	28
1	93	89	85	81	83	79	76	73	62	60	58	46	45	44	32	31	30	24
2	85	77	71	66	75	69	64	60	55	51	48	41	39	37	28	27	26	20
3	77	68	61	55	69	61	55	50	48	44	40	36	33	31	25	23	22	17
4	70	60	52	47	63	54	47	42	43	38	34	32	29	26	22	20	19	14
5	64	53	45	40	57	48	41	36	38	33	29	29	25	23	20	18	16	13
6	59	48	40	34	53	43	36	31	34	29	25	26	22	20	18	16	14	11
7	55	43	35	30	49	39	32	27	31	26	22	23	20	17	16	14	13	10
8	51	39	31	26	45	35	29	24	28	23	20	21	18	15	15	13	11	9
9	47	35	28	23	42	32	26	21	26	21	18	20	16	14	14	12	10	8
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	13	11	9	7

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5201	5201	5201
5°	5226	5154	5190
10°	5191	5109	5141
15°	5131	5051	5060
20°	5060	4969	4974
25°	4963	4871	4861
30°	4860	4762	4724
35°	4750	4646	4586
40°	4636	4519	4449
45°	4509	4402	4294
50°	4382	4258	4140
55°	4219	4110	3984
60°	4052	3935	3810
65°	3904	3744	3629
70°	3688	3531	3374
75°	3373	3248	3111
80°	3037	2913	2882
85°	2668	2569	2470



TEST NUMBER: P332107-940

CATALOG NUMBER: S123DIW-S340D1030U940-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	45.5	1.0
10°-20°	128.5	2.9
20°-30°	189.9	4.3
30°-40°	221.8	5.0
40°-50°	223.0	5.0
50°-60°	195.8	4.4
60°-70°	145.9	3.3
70°-80°	83.1	1.9
80°-90°	27.3	0.6
90°-100°	74.9	1.7
100°-110°	224.2	5.0
110°-120°	381.4	8.6
120°-130°	501.7	11.3
130°-140°	563.9	12.7
140°-150°	554.3	12.5
150°-160°	466.6	10.5
160°-170°	310.6	7.0
170°-180°	108.8	2.4
0°-30°	363.9	8.2
0°-40°	585.7	13.2
0°-60°	1004.5	22.6
0°-90°	1260.8	28.4
90°-120°	680.6	15.3
90°-150°	2300.3	51.7
90°-180°	3186.0	71.6
0°-180°	4447.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	483	483	483	483	483	
5°	484	481	477	481	480	46
15°	460	458	453	456	454	130
25°	418	415	410	410	409	192
35°	362	359	354	351	349	226
45°	296	294	289	284	282	229
55°	225	224	219	215	212	201
65°	153	151	147	144	142	151
75°	81	79	78	76	75	87
85°	22	21	21	20	20	24
90°	1	10	22	25	27	4
95°	53	60	67	70	70	60
105°	203	205	213	213	215	218
115°	384	386	385	386	385	380
125°	562	564	563	559	556	501
135°	729	734	734	730	728	562
145°	884	886	889	888	884	552
155°	1013	1013	1014	1017	1011	466
165°	1103	1100	1100	1105	1100	311
175°	1147	1144	1144	1148	1143	109
180°	1150	1150	1150	1150	1150	



TEST NUMBER: P332107-940

CATALOG NUMBER: S123DIW-S340D1030U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	483.2	483.2	483.2	483.2	483.2	483.2	483.2	483.2	483.2	483.2	483.2
2.5°	484.9	484.6	484.3	484.0	483.7	483.1	482.3	481.5	480.7	479.9	480.6
5°	483.7	483.1	482.7	482.2	481.8	481.1	480.0	479.0	478.0	477.0	477.9
7.5°	478.9	478.4	478.0	477.5	477.1	476.3	475.3	474.2	473.1	472.1	472.9
10°	474.9	474.5	473.9	473.5	473.1	472.3	471.0	469.8	468.6	467.4	468.2
12.5°	469.6	469.2	468.8	468.4	468.1	467.3	466.2	465.0	463.9	462.8	463.4
15°	460.4	460.0	459.6	459.2	458.9	458.1	456.9	455.7	454.5	453.3	454.1
17.5°	449.6	449.2	448.7	448.2	447.7	446.9	445.7	444.5	443.3	442.1	442.6
20°	441.7	441.1	440.6	440.0	439.4	438.5	437.4	436.1	435.0	433.8	434.2
22.5°	432.7	432.1	431.6	431.1	430.5	429.6	428.4	427.2	426.0	424.8	425.1
25°	417.9	417.4	416.9	416.3	415.8	414.9	413.7	412.5	411.3	410.1	410.2
27.5°	402.3	401.7	401.2	400.6	400.1	399.2	398.0	396.6	395.4	394.0	394.1
30°	391.0	390.5	390.0	389.6	389.1	388.3	387.0	385.7	384.4	383.1	383.1
32.5°	379.7	379.1	378.4	377.8	377.3	376.4	375.4	374.4	373.4	372.5	371.9
35°	361.5	361.0	360.3	359.8	359.3	358.4	357.2	356.0	354.8	353.6	353.0
37.5°	342.9	342.1	341.4	340.7	340.1	339.1	337.9	336.6	335.5	334.2	333.6
40°	329.9	329.3	328.8	328.2	327.7	326.7	325.5	324.1	322.9	321.6	320.8
42.5°	316.9	316.3	315.7	315.0	314.4	313.4	312.2	310.9	309.6	308.3	307.6
45°	296.2	295.9	295.5	295.2	294.8	294.0	292.7	291.6	290.3	289.2	288.1
47.5°	275.7	275.2	274.6	274.1	273.6	272.8	271.6	270.5	269.4	268.2	267.2
50°	261.7	261.3	260.8	260.4	259.9	259.0	257.9	256.7	255.5	254.3	253.2
52.5°	247.1	246.8	246.5	246.2	245.8	245.0	243.8	242.5	241.3	240.0	239.2
55°	224.8	224.7	224.6	224.5	224.4	223.7	222.6	221.3	220.2	219.0	217.9
57.5°	203.5	203.2	202.9	202.6	202.2	201.6	200.6	199.7	198.8	197.8	196.9
60°	188.2	188.2	188.1	188.0	187.9	187.3	186.1	185.0	184.0	182.8	182.0
62.5°	174.6	174.3	174.2	173.9	173.6	173.0	171.8	170.8	169.6	168.5	167.7
65°	153.3	152.8	152.4	151.9	151.5	150.8	149.9	148.9	148.0	147.0	146.3
67.5°	130.8	130.4	130.0	129.6	129.2	128.6	128.0	127.2	126.5	125.8	125.2
70°	117.2	116.6	116.1	115.5	114.9	114.4	113.9	113.2	112.7	112.2	111.6
72.5°	102.9	102.5	102.1	101.7	101.2	100.8	100.1	99.5	98.9	98.3	97.6
75°	81.1	80.6	80.3	79.9	79.5	79.2	78.9	78.6	78.4	78.1	77.7
77.5°	61.6	61.4	61.3	61.1	60.8	60.5	60.3	59.9	59.6	59.2	58.9
80°	49.0	48.8	48.5	48.2	47.9	47.7	47.5	47.3	47.2	47.0	46.8
82.5°	36.7	36.6	36.6	36.6	36.5	36.5	36.4	36.4	36.4	36.3	36.1
85°	21.6	21.4	21.2	21.0	20.9	20.8	20.8	20.8	20.8	20.8	20.6
87.5°	8.8	9.0	9.2	9.4	9.5	9.9	10.3	10.8	11.2	11.7	11.8
90°	0.9	2.9	4.9	7.0	8.9	11.2	13.8	16.5	19.1	21.7	22.5
92.5°	21.8	23.2	24.6	25.9	27.3	28.7	30.2	31.7	33.2	34.7	35.3
95°	53.3	54.7	56.1	57.5	58.9	60.5	62.1	63.7	65.3	66.9	67.7
97.5°	94.7	95.7	96.8	97.8	98.9	100.0	101.1	102.3	103.4	104.6	105.6
100°	122.9	124.0	125.3	126.4	127.7	128.8	129.8	130.8	131.8	132.8	133.4
102.5°	155.4	156.1	156.9	157.6	158.3	159.3	160.6	161.9	163.3	164.6	165.2
105°	203.3	203.7	204.1	204.5	204.9	206.0	207.8	209.6	211.4	213.2	213.2
107.5°	259.0	259.1	259.4	259.7	259.8	260.4	261.1	261.8	262.5	263.2	263.9
110°	293.6	294.0	294.4	294.8	295.2	295.6	296.0	296.4	296.9	297.2	298.0



TEST NUMBER: P332107-940

CATALOG NUMBER: S123DIW-S340D1030U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	329.8	330.0	330.2	330.5	330.7	330.8	330.9	331.0	331.1	331.2	332.2
115°	384.0	384.5	385.1	385.8	386.4	386.5	386.0	385.7	385.2	384.9	385.0
117.5°	438.5	438.9	439.3	439.7	440.1	440.1	439.5	439.0	438.5	438.0	437.9
120°	472.5	473.7	474.9	476.1	477.3	477.4	476.4	475.4	474.4	473.4	473.1
122.5°	507.9	508.8	509.7	510.5	511.4	511.6	511.1	510.6	510.1	509.5	509.0
125°	562.0	562.5	563.1	563.7	564.4	564.5	564.0	563.7	563.2	562.8	562.0
127.5°	611.8	613.1	614.4	615.6	616.9	617.3	616.9	616.4	616.0	615.5	614.5
130°	645.1	646.7	648.3	649.9	651.5	651.9	651.4	650.8	650.1	649.5	648.7
132.5°	678.2	679.8	681.4	683.1	684.7	685.3	684.8	684.4	683.9	683.5	682.5
135°	729.1	730.2	731.5	732.6	733.9	734.3	734.1	734.0	733.8	733.5	732.7
137.5°	776.1	777.0	778.0	779.0	780.1	780.8	781.3	781.9	782.4	782.9	782.0
140°	808.5	809.6	810.6	811.5	812.5	813.2	813.3	813.6	813.8	814.0	813.8
142.5°	838.2	839.2	840.2	841.2	842.2	842.8	843.2	843.6	844.0	844.4	844.1
145°	884.4	884.8	885.2	885.6	886.0	886.5	887.2	887.8	888.3	888.9	888.8
147.5°	924.9	925.6	926.3	927.1	927.8	928.4	929.0	929.6	930.1	930.7	930.7
150°	953.1	953.5	953.9	954.3	954.7	955.1	955.5	955.9	956.3	956.7	956.7
152.5°	976.2	976.8	977.3	977.9	978.5	978.8	979.1	979.4	979.6	979.8	980.2
155°	1012.7	1012.7	1012.7	1012.7	1012.7	1012.8	1013.0	1013.3	1013.4	1013.6	1014.4
157.5°	1043.8	1043.6	1043.3	1043.0	1042.9	1042.8	1042.9	1043.1	1043.3	1043.4	1044.3
160°	1063.3	1062.9	1062.5	1062.1	1061.7	1061.5	1061.5	1061.5	1061.5	1061.5	1062.5
162.5°	1080.7	1080.1	1079.5	1079.0	1078.4	1078.2	1078.3	1078.5	1078.7	1078.9	1079.9
165°	1103.0	1102.4	1101.9	1101.3	1100.6	1100.4	1100.4	1100.4	1100.4	1100.4	1101.5
167.5°	1121.0	1120.2	1119.4	1118.6	1117.8	1117.4	1117.6	1117.8	1117.9	1118.0	1119.3
170°	1131.0	1130.2	1129.4	1128.6	1127.8	1127.5	1127.5	1127.5	1127.5	1127.5	1128.8
172.5°	1139.0	1138.2	1137.4	1136.6	1135.8	1135.4	1135.4	1135.4	1135.4	1135.4	1136.7
175°	1147.4	1146.6	1145.8	1145.0	1144.2	1143.7	1143.7	1143.7	1143.7	1143.7	1145.0
177.5°	1150.8	1150.1	1149.5	1148.8	1148.2	1147.9	1147.9	1147.9	1147.9	1147.9	1148.8
180°	1150.0	1150.0	1150.0	1150.0	1150.0	1150.0	1150.0	1150.0	1150.0	1150.0	1150.0



TEST NUMBER: P332107-940

CATALOG NUMBER: S123DIW-S340D1030U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	483.2	483.2	483.2	483.2	483.2	483.2	483.2	483.2
2.5°	481.3	482.1	482.9	483.2	483.1	483.0	483.0	482.9
5°	478.8	479.7	480.7	481.1	480.9	480.7	480.5	480.3
7.5°	473.8	474.6	475.4	475.7	475.6	475.5	475.5	475.3
10°	469.1	469.9	470.7	471.1	470.9	470.7	470.6	470.4
12.5°	464.0	464.6	465.2	465.5	465.4	465.2	465.1	465.0
15°	454.8	455.5	456.3	456.4	455.8	455.2	454.7	454.1
17.5°	443.1	443.6	444.2	444.3	444.1	443.9	443.7	443.5
20°	434.5	434.9	435.2	435.3	435.0	434.7	434.4	434.2
22.5°	425.3	425.7	426.0	426.0	425.6	425.3	424.9	424.5
25°	410.3	410.4	410.5	410.4	410.1	409.8	409.6	409.3
27.5°	394.2	394.3	394.3	394.2	393.9	393.5	393.2	392.8
30°	383.1	383.1	383.1	382.7	382.1	381.5	380.8	380.1
32.5°	371.4	370.9	370.4	370.0	369.6	369.3	368.9	368.5
35°	352.5	352.0	351.3	350.9	350.4	349.9	349.5	349.0
37.5°	332.9	332.3	331.5	331.1	330.8	330.5	330.2	329.9
40°	320.1	319.4	318.6	318.1	317.7	317.4	317.0	316.6
42.5°	306.8	306.0	305.3	304.8	304.4	304.1	303.7	303.3
45°	287.0	285.9	284.7	284.0	283.5	283.0	282.6	282.1
47.5°	266.1	265.0	263.9	263.1	262.7	262.3	261.9	261.5
50°	252.3	251.2	250.2	249.4	248.9	248.3	247.8	247.2
52.5°	238.3	237.4	236.5	235.8	235.2	234.7	234.2	233.6
55°	217.0	215.9	214.9	214.2	213.7	213.2	212.8	212.3
57.5°	196.0	195.0	194.1	193.4	192.9	192.3	191.8	191.3
60°	181.2	180.3	179.5	178.9	178.3	177.9	177.5	177.0
62.5°	166.8	166.0	165.2	164.6	164.3	164.0	163.7	163.4
65°	145.6	144.9	144.1	143.7	143.4	143.0	142.8	142.5
67.5°	124.5	123.9	123.2	122.7	122.3	121.9	121.5	121.2
70°	110.9	110.2	109.6	109.1	108.6	108.2	107.6	107.2
72.5°	97.1	96.5	95.9	95.5	95.3	95.1	94.8	94.5
75°	77.2	76.7	76.2	75.9	75.6	75.3	75.1	74.8
77.5°	58.6	58.3	58.0	57.9	57.9	57.9	57.9	57.9
80°	46.7	46.6	46.5	46.5	46.5	46.5	46.5	46.5
82.5°	36.0	35.8	35.7	35.5	35.5	35.4	35.3	35.2
85°	20.4	20.2	20.1	20.0	20.0	20.0	20.0	20.0
87.5°	11.9	11.9	12.0	12.0	12.1	12.2	12.3	12.4
90°	23.3	24.1	24.9	25.5	25.9	26.3	26.7	27.1
92.5°	35.9	36.6	37.3	37.5	37.2	37.0	36.7	36.5
95°	68.5	69.3	70.1	70.4	70.4	70.4	70.4	70.4
97.5°	106.5	107.4	108.3	108.7	108.6	108.6	108.5	108.4
100°	134.0	134.6	135.2	135.7	136.1	136.5	136.9	137.3
102.5°	165.8	166.4	167.0	167.3	167.2	167.1	167.0	166.9
105°	213.2	213.2	213.2	213.4	213.8	214.2	214.6	215.0
107.5°	264.6	265.2	265.8	266.0	265.8	265.6	265.3	265.0
110°	298.8	299.6	300.4	300.6	300.2	299.8	299.4	299.0





TEST NUMBER: P332107-940

CATALOG NUMBER: S123DIW-S340D1030U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	333.1	334.0	335.0	335.5	335.4	335.3	335.3	335.2
115°	385.2	385.5	385.7	385.7	385.5	385.2	385.0	384.9
117.5°	437.9	437.8	437.8	437.5	436.9	436.4	435.8	435.2
120°	473.0	472.8	472.6	472.3	471.9	471.4	471.1	470.6
122.5°	508.5	507.9	507.5	506.8	506.3	505.8	505.2	504.6
125°	561.2	560.4	559.6	558.8	558.0	557.2	556.4	555.6
127.5°	613.3	612.2	611.1	610.0	609.1	608.2	607.3	606.4
130°	647.9	647.1	646.3	645.2	643.8	642.4	641.1	639.6
132.5°	681.6	680.6	679.7	678.7	677.5	676.5	675.4	674.3
135°	731.9	731.1	730.3	729.8	729.3	729.0	728.5	728.2
137.5°	781.2	780.3	779.5	778.7	777.9	777.2	776.4	775.7
140°	813.6	813.3	813.2	812.3	810.9	809.6	808.2	806.7
142.5°	843.9	843.7	843.6	842.8	841.8	840.7	839.6	838.6
145°	888.6	888.3	888.1	887.6	886.8	886.0	885.2	884.4
147.5°	930.7	930.7	930.7	930.1	928.9	927.6	926.5	925.2
150°	956.7	956.7	956.7	956.1	954.9	953.7	952.5	951.3
152.5°	980.4	980.8	981.1	980.8	979.7	978.7	977.6	976.6
155°	1015.2	1016.0	1016.8	1016.6	1015.1	1013.7	1012.4	1010.9
157.5°	1045.1	1046.0	1046.8	1046.7	1045.5	1044.5	1043.3	1042.1
160°	1063.5	1064.5	1065.5	1065.6	1064.8	1064.0	1063.2	1062.4
162.5°	1080.8	1081.8	1082.9	1082.7	1081.5	1080.1	1078.9	1077.5
165°	1102.8	1103.9	1105.2	1105.1	1103.7	1102.2	1100.8	1099.5
167.5°	1120.5	1121.8	1123.0	1123.0	1121.8	1120.5	1119.3	1118.0
170°	1130.2	1131.7	1133.1	1133.1	1131.7	1130.2	1128.8	1127.5
172.5°	1137.9	1139.2	1140.4	1140.3	1138.9	1137.5	1136.0	1134.7
175°	1146.1	1147.4	1148.5	1148.4	1147.0	1145.6	1144.2	1142.8
177.5°	1149.8	1150.8	1151.7	1151.6	1150.5	1149.4	1148.3	1147.2
180°	1150.0	1150.0	1150.0	1150.0	1150.0	1150.0	1150.0	1150.0

(END OF REPORT)