

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332118-940

Luminaire Tested: **S123DIW-S340D1535U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332118-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIW-S340D1535U940-4F0-1E-UDD-F  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1535 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6734.3 lumens  
Efficiency: N/A  
Efficacy: 126.1 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 53.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332118-940

CATALOG NUMBER: S123DIW-S340D1535U940-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332118-940

CATALOG NUMBER: S123DIW-S340D1535U940-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	88	88	88	88	66	66	66	46	46	46	27	27	27	19
1	91	87	83	80	80	76	73	71	58	56	54	40	39	38	24	24	23	16
2	83	76	70	65	73	67	62	58	50	47	44	35	33	32	21	20	19	13
3	75	66	59	54	66	59	53	48	44	40	37	31	29	27	19	17	16	11
4	69	58	51	45	60	52	46	41	39	35	32	28	25	23	17	15	14	10
5	63	52	44	39	55	46	40	35	35	30	27	25	22	20	15	13	12	8
6	58	46	39	33	51	41	35	30	31	27	23	22	19	17	14	12	11	7
7	53	42	34	29	47	37	31	26	28	24	20	20	17	15	12	11	9	6
8	49	38	30	25	43	33	27	23	26	21	18	18	15	13	11	10	8	6
9	46	34	27	22	40	30	24	20	23	19	16	17	14	12	10	9	8	5
10	43	31	24	20	37	28	22	18	21	17	14	15	12	10	10	8	7	5

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5201	5201	5201
5°	5226	5154	5190
10°	5191	5109	5141
15°	5131	5051	5060
20°	5060	4969	4974
25°	4963	4871	4861
30°	4860	4762	4724
35°	4750	4646	4586
40°	4636	4519	4449
45°	4509	4402	4294
50°	4382	4258	4140
55°	4219	4110	3984
60°	4052	3935	3810
65°	3904	3744	3629
70°	3688	3531	3374
75°	3373	3248	3111
80°	3037	2913	2882
85°	2668	2569	2470



TEST NUMBER: P332118-940

CATALOG NUMBER: S123DIW-S340D1535U940-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	45.5	0.7
10°-20°	128.5	1.9
20°-30°	189.9	2.8
30°-40°	221.8	3.3
40°-50°	223.0	3.3
50°-60°	195.8	2.9
60°-70°	145.9	2.2
70°-80°	83.1	1.2
80°-90°	28.9	0.4
90°-100°	65.2	1.0
100°-110°	310.9	4.6
110°-120°	746.8	11.1
120°-130°	951.0	14.1
130°-140°	1016.1	15.1
140°-150°	950.2	14.1
150°-160°	766.5	11.4
160°-170°	494.7	7.3
170°-180°	170.5	2.5
0°-30°	363.9	5.4
0°-40°	585.7	8.7
0°-60°	1004.5	14.9
0°-90°	1262.4	18.7
90°-120°	1123.0	16.7
90°-150°	4040.3	60.0
90°-180°	5472.0	81.3
0°-180°	6734.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	483	483	483	483	483	
5°	484	481	477	481	480	46
15°	460	458	453	456	454	130
25°	418	415	410	410	409	192
35°	362	359	354	351	349	226
45°	296	294	289	284	282	229
55°	225	224	219	215	212	201
65°	153	151	147	144	142	151
75°	81	79	78	76	75	87
85°	22	21	21	20	20	24
90°	1	15	32	37	40	5
95°	81	30	41	50	51	101
105°	397	404	292	69	59	421
115°	745	753	765	778	784	735
125°	1050	1061	1066	1069	1072	938
135°	1308	1316	1321	1325	1321	1006
145°	1509	1518	1521	1524	1524	944
155°	1662	1660	1661	1667	1660	766
165°	1753	1749	1748	1757	1749	495
175°	1794	1788	1789	1797	1788	171
180°	1794	1794	1794	1794	1794	



TEST NUMBER: P332118-940

CATALOG NUMBER: S123DIW-S340D1535U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	483.2	483.2	483.2	483.2	483.2	483.2	483.2	483.2	483.2	483.2	483.2
2.5°	484.9	484.6	484.3	484.0	483.7	483.1	482.3	481.5	480.7	479.9	480.6
5°	483.7	483.1	482.7	482.2	481.8	481.1	480.0	479.0	478.0	477.0	477.9
7.5°	478.9	478.4	478.0	477.5	477.1	476.3	475.3	474.2	473.1	472.1	472.9
10°	474.9	474.5	473.9	473.5	473.1	472.3	471.0	469.8	468.6	467.4	468.2
12.5°	469.6	469.2	468.8	468.4	468.1	467.3	466.2	465.0	463.9	462.8	463.4
15°	460.4	460.0	459.6	459.2	458.9	458.1	456.9	455.7	454.5	453.3	454.1
17.5°	449.6	449.2	448.7	448.2	447.7	446.9	445.7	444.5	443.3	442.1	442.6
20°	441.7	441.1	440.6	440.0	439.4	438.5	437.4	436.1	435.0	433.8	434.2
22.5°	432.7	432.1	431.6	431.1	430.5	429.6	428.4	427.2	426.0	424.8	425.1
25°	417.9	417.4	416.9	416.3	415.8	414.9	413.7	412.5	411.3	410.1	410.2
27.5°	402.3	401.7	401.2	400.6	400.1	399.2	398.0	396.6	395.4	394.0	394.1
30°	391.0	390.5	390.0	389.6	389.1	388.3	387.0	385.7	384.4	383.1	383.1
32.5°	379.7	379.1	378.4	377.8	377.3	376.4	375.4	374.4	373.4	372.5	371.9
35°	361.5	361.0	360.3	359.8	359.3	358.4	357.2	356.0	354.8	353.6	353.0
37.5°	342.9	342.1	341.4	340.7	340.1	339.1	337.9	336.6	335.5	334.2	333.6
40°	329.9	329.3	328.8	328.2	327.7	326.7	325.5	324.1	322.9	321.6	320.8
42.5°	316.9	316.3	315.7	315.0	314.4	313.4	312.2	310.9	309.6	308.3	307.6
45°	296.2	295.9	295.5	295.2	294.8	294.0	292.7	291.6	290.3	289.2	288.1
47.5°	275.7	275.2	274.6	274.1	273.6	272.8	271.6	270.5	269.4	268.2	267.2
50°	261.7	261.3	260.8	260.4	259.9	259.0	257.9	256.7	255.5	254.3	253.2
52.5°	247.1	246.8	246.5	246.2	245.8	245.0	243.8	242.5	241.3	240.0	239.2
55°	224.8	224.7	224.6	224.5	224.4	223.7	222.6	221.3	220.2	219.0	217.9
57.5°	203.5	203.2	202.9	202.6	202.2	201.6	200.6	199.7	198.8	197.8	196.9
60°	188.2	188.2	188.1	188.0	187.9	187.3	186.1	185.0	184.0	182.8	182.0
62.5°	174.6	174.3	174.2	173.9	173.6	173.0	171.8	170.8	169.6	168.5	167.7
65°	153.3	152.8	152.4	151.9	151.5	150.8	149.9	148.9	148.0	147.0	146.3
67.5°	130.8	130.4	130.0	129.6	129.2	128.6	128.0	127.2	126.5	125.8	125.2
70°	117.2	116.6	116.1	115.5	114.9	114.4	113.9	113.2	112.7	112.2	111.6
72.5°	102.9	102.5	102.1	101.7	101.2	100.8	100.1	99.5	98.9	98.3	97.6
75°	81.1	80.6	80.3	79.9	79.5	79.2	78.9	78.6	78.4	78.1	77.7
77.5°	61.6	61.4	61.3	61.1	60.8	60.5	60.3	59.9	59.6	59.2	58.9
80°	49.0	48.8	48.5	48.2	47.9	47.7	47.5	47.3	47.2	47.0	46.8
82.5°	36.7	36.6	36.6	36.6	36.5	36.5	36.4	36.4	36.4	36.3	36.1
85°	21.6	21.4	21.2	21.0	20.9	20.8	20.8	20.8	20.8	20.8	20.6
87.5°	8.9	9.3	9.6	10.0	10.4	11.0	11.6	12.3	13.0	13.7	13.9
90°	1.3	4.3	7.2	10.3	13.2	16.6	20.4	24.3	28.2	32.0	33.2
92.5°	24.8	24.0	23.1	22.3	21.5	22.5	25.4	28.4	31.2	34.2	36.0
95°	81.3	69.2	57.1	44.9	32.7	28.3	31.6	34.8	38.1	41.3	43.4
97.5°	163.5	158.0	152.6	147.0	141.6	128.2	106.9	85.6	64.3	42.9	45.3
100°	225.3	231.2	237.1	243.1	249.0	228.8	182.6	136.4	90.2	44.0	46.4
102.5°	295.7	300.0	304.3	308.4	312.7	289.6	239.2	188.7	138.2	87.7	80.3
105°	397.3	400.6	403.8	407.1	410.3	398.6	371.9	345.3	318.6	291.9	239.5
107.5°	504.4	507.0	509.6	512.3	514.9	518.3	522.5	526.7	530.9	535.1	496.7
110°	575.9	578.3	580.6	583.0	585.4	588.2	591.5	594.7	598.0	601.2	591.5



TEST NUMBER: P332118-940

CATALOG NUMBER: S123DIW-S340D1535U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	644.2	646.3	648.5	650.6	652.6	655.4	658.6	661.9	665.1	668.4	668.6
115°	745.2	747.0	748.8	750.6	752.3	754.6	757.2	759.8	762.5	765.2	768.1
117.5°	843.0	845.3	847.4	849.6	851.9	853.6	855.0	856.3	857.6	859.1	861.4
120°	903.8	906.5	909.2	911.9	914.5	916.3	917.1	918.0	918.9	919.8	922.2
122.5°	965.7	967.9	970.1	972.2	974.5	976.2	977.2	978.4	979.5	980.6	982.3
125°	1050.4	1052.8	1055.3	1057.6	1060.0	1061.8	1062.9	1064.1	1065.3	1066.5	1067.1
127.5°	1132.6	1135.0	1137.4	1139.7	1142.1	1144.0	1145.4	1146.8	1148.3	1149.7	1150.6
130°	1183.7	1186.2	1188.6	1190.9	1193.3	1195.1	1196.2	1197.4	1198.6	1199.8	1201.0
132.5°	1232.9	1235.2	1237.6	1239.9	1242.3	1244.0	1244.9	1245.9	1246.8	1247.8	1248.9
135°	1307.8	1309.6	1311.3	1313.1	1314.9	1316.3	1317.5	1318.8	1319.9	1321.1	1322.0
137.5°	1371.7	1374.0	1376.3	1378.5	1380.7	1382.2	1382.9	1383.5	1384.2	1384.8	1386.3
140°	1414.4	1416.2	1418.0	1419.8	1421.6	1422.8	1423.7	1424.6	1425.5	1426.4	1427.6
142.5°	1453.8	1455.6	1457.4	1459.2	1461.0	1462.3	1463.2	1464.1	1465.0	1465.9	1466.8
145°	1509.0	1511.1	1513.2	1515.3	1517.3	1518.7	1519.3	1519.8	1520.5	1521.1	1521.6
147.5°	1561.0	1562.5	1563.8	1565.1	1566.5	1567.4	1568.1	1568.7	1569.2	1569.9	1570.5
150°	1593.0	1593.9	1594.8	1595.7	1596.6	1597.3	1597.9	1598.6	1599.1	1599.7	1600.3
152.5°	1621.8	1622.3	1622.6	1623.1	1623.5	1623.9	1624.3	1624.6	1625.0	1625.3	1626.4
155°	1662.3	1661.8	1661.2	1660.6	1660.0	1659.8	1660.2	1660.5	1660.7	1661.0	1662.5
157.5°	1693.8	1693.8	1693.7	1693.6	1693.6	1693.4	1693.1	1692.8	1692.6	1692.2	1694.0
160°	1713.1	1712.7	1712.4	1712.2	1711.8	1711.5	1711.3	1710.9	1710.7	1710.4	1712.2
162.5°	1731.2	1730.4	1729.7	1728.8	1728.0	1727.5	1727.2	1727.0	1726.6	1726.4	1728.4
165°	1753.0	1752.1	1751.2	1750.3	1749.4	1748.9	1748.6	1748.3	1748.0	1747.7	1750.1
167.5°	1770.0	1768.9	1767.7	1766.6	1765.3	1764.8	1764.8	1764.8	1764.8	1764.8	1767.1
170°	1779.7	1778.5	1777.3	1776.1	1775.0	1774.3	1774.3	1774.3	1774.3	1774.3	1776.7
172.5°	1786.1	1784.7	1783.2	1781.8	1780.4	1779.8	1780.0	1780.3	1780.5	1780.7	1783.2
175°	1794.3	1792.9	1791.4	1789.9	1788.4	1787.8	1788.1	1788.4	1788.7	1789.0	1791.1
177.5°	1796.4	1795.3	1794.1	1793.0	1791.7	1791.3	1791.5	1791.7	1792.0	1792.2	1794.1
180°	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3



TEST NUMBER: P332118-940

CATALOG NUMBER: S123DIW-S340D1535U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	483.2	483.2	483.2	483.2	483.2	483.2	483.2	483.2
2.5°	481.3	482.1	482.9	483.2	483.1	483.0	483.0	482.9
5°	478.8	479.7	480.7	481.1	480.9	480.7	480.5	480.3
7.5°	473.8	474.6	475.4	475.7	475.6	475.5	475.5	475.3
10°	469.1	469.9	470.7	471.1	470.9	470.7	470.6	470.4
12.5°	464.0	464.6	465.2	465.5	465.4	465.2	465.1	465.0
15°	454.8	455.5	456.3	456.4	455.8	455.2	454.7	454.1
17.5°	443.1	443.6	444.2	444.3	444.1	443.9	443.7	443.5
20°	434.5	434.9	435.2	435.3	435.0	434.7	434.4	434.2
22.5°	425.3	425.7	426.0	426.0	425.6	425.3	424.9	424.5
25°	410.3	410.4	410.5	410.4	410.1	409.8	409.6	409.3
27.5°	394.2	394.3	394.3	394.2	393.9	393.5	393.2	392.8
30°	383.1	383.1	383.1	382.7	382.1	381.5	380.8	380.1
32.5°	371.4	370.9	370.4	370.0	369.6	369.3	368.9	368.5
35°	352.5	352.0	351.3	350.9	350.4	349.9	349.5	349.0
37.5°	332.9	332.3	331.5	331.1	330.8	330.5	330.2	329.9
40°	320.1	319.4	318.6	318.1	317.7	317.4	317.0	316.6
42.5°	306.8	306.0	305.3	304.8	304.4	304.1	303.7	303.3
45°	287.0	285.9	284.7	284.0	283.5	283.0	282.6	282.1
47.5°	266.1	265.0	263.9	263.1	262.7	262.3	261.9	261.5
50°	252.3	251.2	250.2	249.4	248.9	248.3	247.8	247.2
52.5°	238.3	237.4	236.5	235.8	235.2	234.7	234.2	233.6
55°	217.0	215.9	214.9	214.2	213.7	213.2	212.8	212.3
57.5°	196.0	195.0	194.1	193.4	192.9	192.3	191.8	191.3
60°	181.2	180.3	179.5	178.9	178.3	177.9	177.5	177.0
62.5°	166.8	166.0	165.2	164.6	164.3	164.0	163.7	163.4
65°	145.6	144.9	144.1	143.7	143.4	143.0	142.8	142.5
67.5°	124.5	123.9	123.2	122.7	122.3	121.9	121.5	121.2
70°	110.9	110.2	109.6	109.1	108.6	108.2	107.6	107.2
72.5°	97.1	96.5	95.9	95.5	95.3	95.1	94.8	94.5
75°	77.2	76.7	76.2	75.9	75.6	75.3	75.1	74.8
77.5°	58.6	58.3	58.0	57.9	57.9	57.9	57.9	57.9
80°	46.7	46.6	46.5	46.5	46.5	46.5	46.5	46.5
82.5°	36.0	35.8	35.7	35.5	35.5	35.4	35.3	35.2
85°	20.4	20.2	20.1	20.0	20.0	20.0	20.0	20.0
87.5°	14.0	14.2	14.4	14.5	14.6	14.7	14.9	15.0
90°	34.3	35.6	36.7	37.6	38.3	38.8	39.4	39.9
92.5°	37.9	39.9	41.7	42.8	43.2	43.5	43.9	44.2
95°	45.5	47.5	49.6	50.6	50.6	50.6	50.6	50.6
97.5°	47.7	50.0	52.4	53.8	54.0	54.3	54.7	54.9
100°	48.7	51.1	53.5	54.8	55.1	55.4	55.7	56.0
102.5°	73.0	65.7	58.3	54.9	55.5	56.0	56.5	57.1
105°	187.1	134.6	82.2	56.3	56.9	57.5	58.1	58.7
107.5°	458.2	419.7	381.3	342.3	302.8	263.2	223.7	184.2
110°	581.7	571.9	562.1	536.0	493.7	451.3	408.9	366.6





TEST NUMBER: P332118-940

CATALOG NUMBER: S123DIW-S340D1535U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	668.8	669.0	669.1	664.8	655.8	646.8	637.9	628.9
115°	771.2	774.1	777.0	779.1	780.3	781.5	782.7	783.9
117.5°	863.8	866.1	868.5	869.9	870.0	870.3	870.6	870.8
120°	924.6	926.9	929.3	930.5	930.5	930.5	930.5	930.5
122.5°	983.9	985.6	987.3	988.2	988.5	988.6	988.9	989.2
125°	1067.6	1068.3	1068.8	1069.4	1070.1	1070.6	1071.2	1071.8
127.5°	1151.6	1152.5	1153.4	1153.6	1153.1	1152.4	1151.8	1151.3
130°	1202.1	1203.4	1204.5	1204.8	1204.3	1203.6	1203.0	1202.5
132.5°	1250.2	1251.3	1252.5	1252.7	1251.9	1251.1	1250.2	1249.4
135°	1322.9	1323.7	1324.6	1324.6	1323.7	1322.9	1322.0	1321.1
137.5°	1387.7	1389.1	1390.5	1390.9	1390.4	1389.7	1389.1	1388.6
140°	1428.8	1429.9	1431.1	1431.5	1430.8	1430.3	1429.7	1429.1
142.5°	1467.8	1468.7	1469.6	1469.7	1468.9	1468.0	1467.2	1466.4
145°	1522.2	1522.9	1523.4	1523.8	1523.8	1523.8	1523.8	1523.8
147.5°	1571.0	1571.6	1572.3	1571.8	1570.5	1569.1	1567.7	1566.4
150°	1600.9	1601.5	1602.0	1602.0	1601.1	1600.2	1599.3	1598.4
152.5°	1627.5	1628.5	1629.6	1629.4	1628.1	1626.7	1625.3	1624.0
155°	1664.0	1665.4	1667.0	1666.8	1665.0	1663.2	1661.4	1659.7
157.5°	1695.8	1697.5	1699.3	1699.1	1696.7	1694.4	1692.1	1689.8
160°	1714.0	1715.7	1717.4	1717.3	1715.2	1713.2	1711.1	1709.1
162.5°	1730.4	1732.4	1734.4	1734.5	1732.7	1730.8	1729.0	1727.2
165°	1752.4	1754.8	1757.2	1757.3	1755.2	1753.2	1751.1	1749.0
167.5°	1769.5	1771.8	1774.2	1774.2	1771.8	1769.5	1767.1	1764.8
170°	1779.1	1781.5	1783.9	1783.9	1781.5	1779.1	1776.7	1774.3
172.5°	1785.5	1787.9	1790.2	1790.1	1787.5	1784.9	1782.3	1779.7
175°	1793.1	1795.2	1797.3	1797.2	1794.7	1792.4	1790.0	1787.7
177.5°	1796.0	1797.9	1799.8	1799.6	1797.2	1794.8	1792.4	1790.1
180°	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3

(END OF REPORT)