

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332743-830

Luminaire Tested: **S124DIW-S350D1560U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332743-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIW-S350D1560U830-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1560 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7312.8 lumens  
Efficiency: N/A  
Efficacy: 136.9 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 53.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332743-830

CATALOG NUMBER: S124DIW-S350D1560U830-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332743-830

CATALOG NUMBER: S124DIW-S350D1560U830-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	88	88	88	88	66	66	66	47	47	47	28	28	28	20
1	91	87	83	80	80	77	74	71	58	56	54	41	40	38	25	24	24	16
2	83	76	70	65	73	67	62	58	51	48	45	36	34	32	22	21	20	14
3	75	66	60	54	66	59	53	48	45	41	38	32	29	27	19	18	17	12
4	69	59	51	45	61	52	46	41	40	35	32	28	25	23	17	16	15	10
5	63	52	44	39	55	46	40	35	35	31	27	25	22	20	15	14	13	9
6	58	46	39	33	51	41	35	30	32	27	24	23	20	17	14	12	11	8
7	53	42	34	29	47	37	31	26	29	24	21	20	17	15	13	11	10	7
8	49	38	30	25	44	34	27	23	26	21	18	19	16	13	12	10	9	6
9	46	34	27	22	40	31	24	20	24	19	16	17	14	12	11	9	8	5
10	43	31	24	20	38	28	22	18	22	17	14	16	13	11	10	8	7	5

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	4495	4495	4495
5°	4508	4454	4486
10°	4480	4418	4440
15°	4425	4355	4367
20°	4354	4277	4281
25°	4272	4188	4177
30°	4172	4084	4047
35°	4066	3975	3921
40°	3958	3851	3780
45°	3846	3729	3658
50°	3720	3620	3508
55°	3586	3478	3365
60°	3450	3321	3219
65°	3299	3171	3043
70°	3127	2969	2854
75°	2866	2729	2658
80°	2552	2450	2385
85°	2232	2149	2103



TEST NUMBER: P332743-830

CATALOG NUMBER: S124DIW-S350D1560U830-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	52.4	0.7
10°-20°	147.7	2.0
20°-30°	217.4	3.0
30°-40°	252.8	3.5
40°-50°	252.8	3.5
50°-60°	221.1	3.0
60°-70°	164.2	2.2
70°-80°	93.3	1.3
80°-90°	32.4	0.4
90°-100°	65.0	0.9
100°-110°	414.4	5.7
110°-120°	792.8	10.8
120°-130°	1006.4	13.8
130°-140°	1076.8	14.7
140°-150°	1006.9	13.8
150°-160°	812.0	11.1
160°-170°	523.7	7.2
170°-180°	180.5	2.5
0°-30°	417.6	5.7
0°-40°	670.4	9.2
0°-60°	1144.3	15.6
0°-90°	1434.3	19.6
90°-120°	1272.2	17.4
90°-150°	4362.3	59.7
90°-180°	5879.0	80.4
0°-180°	7312.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	557	557	557	557	557	
5°	556	554	550	554	554	53
15°	530	528	521	524	522	149
25°	480	476	470	471	469	221
35°	413	409	403	400	398	258
45°	337	333	327	322	320	260
55°	255	253	247	242	239	228
65°	173	170	166	162	159	171
75°	92	90	88	86	85	98
85°	24	24	23	23	23	27
90°	4	20	31	40	43	5
95°	78	33	31	39	41	100
105°	428	436	444	453	405	448
115°	799	803	802	804	805	786
125°	1123	1128	1126	1130	1131	1002
135°	1393	1392	1397	1400	1403	1073
145°	1606	1610	1610	1612	1615	1003
155°	1761	1762	1758	1763	1760	812
165°	1858	1851	1851	1861	1849	525
175°	1900	1892	1893	1904	1889	181
180°	1900	1900	1900	1900	1900	



TEST NUMBER: P332743-830

CATALOG NUMBER: S124DIW-S350D1560U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8
2.5°	558.2	558.0	557.7	557.5	557.2	556.7	555.8	555.0	554.1	553.2	554.0
5°	556.3	555.9	555.5	555.2	554.8	554.0	552.9	551.9	550.7	549.6	550.7
7.5°	551.2	550.7	550.4	550.0	549.6	548.7	547.5	546.4	545.2	543.9	544.8
10°	546.5	546.1	545.7	545.4	545.0	544.1	542.8	541.5	540.3	538.9	539.7
12.5°	540.5	540.1	539.7	539.2	538.9	538.0	536.6	535.3	533.9	532.5	533.4
15°	529.5	529.1	528.8	528.4	528.0	527.1	525.6	524.1	522.5	521.1	521.7
17.5°	516.4	515.9	515.5	515.0	514.4	513.5	512.1	510.7	509.3	507.8	508.2
20°	506.8	506.3	505.9	505.3	504.8	503.9	502.4	500.9	499.4	497.9	498.2
22.5°	496.4	495.8	495.1	494.5	493.8	492.8	491.3	489.8	488.3	486.8	487.4
25°	479.6	478.9	478.2	477.5	476.8	475.8	474.4	473.0	471.6	470.2	470.3
27.5°	460.3	459.6	458.9	458.2	457.5	456.5	455.2	453.9	452.6	451.3	451.1
30°	447.5	446.7	445.9	445.1	444.3	443.3	442.0	440.6	439.4	438.1	437.7
32.5°	433.9	433.2	432.4	431.8	431.0	430.0	428.7	427.3	425.9	424.5	424.0
35°	412.6	412.0	411.3	410.6	409.9	408.9	407.5	406.0	404.7	403.3	402.7
37.5°	390.3	389.6	389.0	388.4	387.8	386.7	385.2	383.7	382.2	380.7	379.9
40°	375.6	374.8	374.1	373.2	372.5	371.4	369.9	368.3	366.8	365.4	364.4
42.5°	360.0	359.5	359.0	358.5	358.1	356.9	355.3	353.6	352.0	350.4	349.2
45°	336.9	336.1	335.5	334.8	334.0	332.9	331.3	329.7	328.2	326.6	325.5
47.5°	312.6	312.2	311.7	311.2	310.8	309.8	308.3	306.8	305.4	303.9	302.7
50°	296.2	295.9	295.5	295.0	294.6	293.8	292.4	291.0	289.5	288.2	286.8
52.5°	280.2	279.7	279.2	278.7	278.2	277.3	275.8	274.4	272.9	271.5	270.2
55°	254.8	254.5	254.1	253.8	253.5	252.7	251.3	250.0	248.5	247.1	246.0
57.5°	230.5	230.2	229.8	229.5	229.1	228.3	226.9	225.6	224.1	222.8	221.7
60°	213.7	213.2	212.7	212.2	211.7	210.8	209.5	208.2	207.0	205.7	204.8
62.5°	197.3	196.9	196.4	196.0	195.6	194.7	193.3	192.0	190.6	189.3	188.4
65°	172.7	172.2	171.6	171.2	170.7	169.9	168.9	168.0	166.9	166.0	164.9
67.5°	147.9	147.4	146.9	146.5	146.0	145.3	144.4	143.5	142.5	141.5	140.5
70°	132.5	131.8	131.1	130.4	129.7	128.9	128.2	127.4	126.6	125.8	125.0
72.5°	116.1	115.4	114.7	114.0	113.3	112.6	112.0	111.4	110.7	110.1	109.4
75°	91.9	91.4	91.0	90.4	89.9	89.4	89.0	88.4	87.9	87.5	87.1
77.5°	68.8	68.6	68.3	68.1	68.0	67.6	67.2	66.7	66.3	65.9	65.7
80°	54.9	54.6	54.3	54.0	53.7	53.4	53.3	53.1	52.9	52.7	52.4
82.5°	41.3	41.2	41.0	40.9	40.7	40.6	40.6	40.6	40.5	40.5	40.4
85°	24.1	24.1	24.1	24.1	24.1	24.0	23.8	23.6	23.4	23.2	23.2
87.5°	10.2	10.7	11.4	12.0	12.6	13.1	13.6	13.9	14.4	14.8	15.2
90°	4.2	7.7	11.2	14.7	18.2	21.2	23.7	26.2	28.7	31.3	33.2
92.5°	17.9	18.1	18.3	18.5	18.7	20.0	22.5	25.1	27.6	30.2	32.0
95°	78.1	67.4	56.7	46.0	35.3	30.0	30.3	30.6	30.9	31.3	33.2
97.5°	166.0	172.7	179.4	186.2	192.8	178.5	143.3	108.0	72.8	37.5	37.7
100°	233.1	238.8	244.5	250.2	255.8	236.9	193.3	149.7	106.1	62.6	57.2
102.5°	308.1	312.4	316.5	320.7	324.8	324.0	318.4	312.7	307.0	301.3	243.4
105°	427.8	429.7	431.6	433.6	435.5	437.2	438.8	440.4	441.9	443.5	446.3
107.5°	538.9	540.0	540.9	541.9	542.8	544.3	546.5	548.7	550.7	552.9	554.3
110°	614.1	615.0	616.0	616.9	617.8	619.3	621.1	623.0	624.9	626.8	627.5



TEST NUMBER: P332743-830

CATALOG NUMBER: S124DIW-S350D1560U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	686.8	688.5	690.2	691.9	693.6	694.9	695.8	696.7	697.6	698.5	698.3
115°	798.8	799.7	800.7	801.6	802.6	803.0	802.6	802.3	802.0	801.6	802.3
117.5°	899.8	901.0	902.3	903.5	904.8	905.8	906.4	907.2	907.9	908.5	908.4
120°	968.0	969.2	970.5	971.8	973.0	973.5	973.2	972.9	972.5	972.2	972.9
122.5°	1031.6	1032.4	1033.1	1033.9	1034.7	1035.3	1035.8	1036.1	1036.6	1037.1	1037.5
125°	1122.9	1124.2	1125.4	1126.7	1127.9	1128.2	1127.7	1127.0	1126.3	1125.8	1126.7
127.5°	1209.3	1209.7	1209.9	1210.2	1210.6	1211.4	1213.0	1214.4	1215.8	1217.3	1217.1
130°	1265.1	1265.4	1265.6	1266.0	1266.3	1267.0	1267.9	1268.9	1269.8	1270.7	1271.0
132.5°	1316.2	1316.7	1317.4	1318.0	1318.5	1319.4	1320.6	1321.7	1323.0	1324.2	1324.5
135°	1393.0	1392.6	1392.3	1392.0	1391.7	1392.1	1393.5	1394.7	1396.0	1397.2	1397.9
137.5°	1460.9	1461.0	1461.1	1461.3	1461.4	1462.2	1463.6	1465.0	1466.3	1467.7	1468.4
140°	1505.2	1505.9	1506.6	1507.1	1507.8	1508.4	1509.0	1509.7	1510.3	1510.9	1511.9
142.5°	1545.0	1546.1	1547.4	1548.5	1549.6	1550.4	1550.8	1551.1	1551.5	1551.9	1552.6
145°	1606.2	1607.1	1608.1	1609.0	1610.0	1610.4	1610.4	1610.4	1610.4	1610.4	1610.7
147.5°	1654.8	1656.5	1658.3	1660.1	1661.9	1662.6	1662.3	1662.0	1661.6	1661.3	1661.6
150°	1690.1	1691.3	1692.5	1693.8	1695.1	1695.5	1695.3	1695.0	1694.6	1694.3	1694.3
152.5°	1719.6	1720.6	1721.6	1722.6	1723.6	1723.9	1723.3	1722.7	1722.1	1721.6	1722.1
155°	1761.1	1761.4	1761.7	1762.1	1762.4	1762.1	1761.1	1760.2	1759.3	1758.2	1759.5
157.5°	1796.1	1795.9	1795.7	1795.5	1795.4	1794.7	1793.6	1792.5	1791.5	1790.4	1792.1
160°	1816.6	1815.6	1814.7	1813.7	1812.8	1812.1	1811.8	1811.5	1811.2	1810.8	1812.8
162.5°	1834.8	1833.5	1832.3	1831.2	1829.9	1829.2	1828.8	1828.5	1828.2	1827.9	1829.8
165°	1857.8	1856.1	1854.6	1853.0	1851.4	1850.7	1850.7	1850.7	1850.7	1850.7	1853.1
167.5°	1875.9	1874.3	1872.6	1871.0	1869.3	1868.5	1868.3	1868.1	1867.9	1867.7	1870.5
170°	1886.2	1884.3	1882.4	1880.5	1878.6	1877.8	1878.1	1878.5	1878.8	1879.1	1881.6
172.5°	1893.0	1891.1	1889.2	1887.3	1885.5	1884.6	1885.0	1885.3	1885.6	1885.9	1888.4
175°	1900.4	1898.5	1896.6	1894.7	1892.8	1892.1	1892.3	1892.6	1893.0	1893.3	1896.1
177.5°	1903.8	1902.1	1900.3	1898.5	1896.8	1896.1	1896.6	1897.1	1897.6	1898.1	1900.2
180°	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4



TEST NUMBER: P332743-830

CATALOG NUMBER: S124DIW-S350D1560U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8
2.5°	554.8	555.6	556.4	556.8	556.7	556.6	556.5	556.4
5°	551.9	552.9	554.0	554.4	554.2	554.0	553.8	553.6
7.5°	545.6	546.6	547.4	547.8	547.7	547.5	547.4	547.3
10°	540.5	541.3	542.2	542.4	542.2	542.0	541.8	541.6
12.5°	534.2	535.1	536.0	536.3	536.0	535.7	535.5	535.2
15°	522.3	522.8	523.5	523.6	523.3	523.0	522.7	522.5
17.5°	508.6	509.0	509.3	509.4	509.3	509.1	508.9	508.7
20°	498.5	498.8	499.1	499.2	498.9	498.7	498.5	498.3
22.5°	487.9	488.4	489.0	489.1	488.7	488.3	488.0	487.7
25°	470.4	470.5	470.6	470.5	470.0	469.7	469.3	468.9
27.5°	450.8	450.6	450.3	450.0	449.5	449.0	448.5	448.0
30°	437.3	437.0	436.5	436.1	435.5	435.1	434.6	434.1
32.5°	423.6	423.1	422.6	422.2	421.7	421.1	420.7	420.2
35°	401.9	401.2	400.5	399.9	399.4	399.0	398.4	397.9
37.5°	379.2	378.4	377.7	377.0	376.4	375.7	375.0	374.4
40°	363.4	362.4	361.5	360.7	360.1	359.7	359.2	358.7
42.5°	348.1	346.9	345.8	345.1	344.7	344.4	344.0	343.7
45°	324.4	323.3	322.3	321.5	321.2	320.9	320.7	320.4
47.5°	301.4	300.2	299.0	298.0	297.3	296.5	295.8	295.0
50°	285.4	284.1	282.7	281.6	281.1	280.5	279.8	279.3
52.5°	269.0	267.8	266.6	265.5	264.8	264.0	263.3	262.5
55°	244.8	243.6	242.4	241.5	240.9	240.3	239.7	239.1
57.5°	220.6	219.4	218.3	217.4	216.9	216.3	215.7	215.1
60°	203.9	203.0	202.1	201.4	201.0	200.4	199.9	199.4
62.5°	187.7	186.8	186.0	185.3	184.8	184.4	183.9	183.3
65°	164.0	163.0	162.0	161.3	160.8	160.2	159.8	159.3
67.5°	139.6	138.6	137.7	137.1	137.0	136.9	136.8	136.6
70°	124.2	123.5	122.6	122.1	121.8	121.5	121.2	120.9
72.5°	108.9	108.2	107.5	107.1	106.8	106.5	106.2	105.9
75°	86.6	86.2	85.9	85.6	85.5	85.4	85.3	85.2
77.5°	65.6	65.5	65.4	65.2	64.9	64.7	64.4	64.2
80°	52.2	52.0	51.8	51.7	51.6	51.5	51.4	51.3
82.5°	40.2	40.2	40.1	40.0	39.9	39.7	39.6	39.5
85°	23.2	23.2	23.2	23.2	23.1	23.0	22.8	22.7
87.5°	15.6	15.9	16.3	16.6	16.7	16.9	17.0	17.1
90°	35.1	36.9	38.8	40.2	40.7	41.4	42.0	42.6
92.5°	33.9	35.8	37.7	38.7	38.8	39.0	39.1	39.2
95°	35.1	36.9	38.8	40.0	40.2	40.6	40.9	41.2
97.5°	37.9	38.1	38.3	38.5	38.8	39.2	39.5	39.8
100°	51.8	46.5	41.1	38.5	38.8	39.2	39.5	39.8
102.5°	185.5	127.5	69.7	40.7	40.7	40.8	40.9	40.9
105°	449.1	452.0	454.9	450.5	439.2	427.8	416.5	405.1
107.5°	555.7	557.1	558.5	559.8	561.0	562.1	563.4	564.6
110°	628.1	628.8	629.3	630.2	631.1	632.1	633.0	634.0





TEST NUMBER: P332743-830

CATALOG NUMBER: S124DIW-S350D1560U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	698.2	698.0	698.0	698.5	699.7	700.9	702.1	703.3
115°	803.0	803.5	804.2	804.6	804.6	804.6	804.6	804.6
117.5°	908.3	908.1	908.0	908.0	907.8	907.7	907.6	907.4
120°	973.5	974.1	974.8	974.8	974.1	973.5	972.9	972.2
122.5°	1037.8	1038.2	1038.6	1038.4	1037.8	1037.2	1036.5	1035.9
125°	1127.7	1128.6	1129.5	1130.2	1130.5	1130.8	1131.1	1131.4
127.5°	1216.9	1216.7	1216.5	1216.3	1216.1	1215.8	1215.5	1215.3
130°	1271.4	1271.7	1272.0	1272.1	1272.1	1272.1	1272.1	1272.1
132.5°	1324.8	1325.1	1325.4	1325.5	1325.2	1324.9	1324.7	1324.5
135°	1398.5	1399.1	1399.8	1400.4	1401.0	1401.7	1402.3	1402.9
137.5°	1469.1	1469.8	1470.6	1470.7	1470.6	1470.4	1470.2	1470.0
140°	1512.9	1513.8	1514.8	1515.3	1515.7	1516.0	1516.3	1516.6
142.5°	1553.3	1554.0	1554.6	1555.0	1555.1	1555.2	1555.2	1555.3
145°	1611.1	1611.4	1611.7	1612.2	1612.8	1613.4	1614.1	1614.7
147.5°	1661.8	1662.1	1662.4	1662.6	1662.9	1663.2	1663.6	1663.9
150°	1694.3	1694.3	1694.3	1694.5	1694.8	1695.1	1695.4	1695.7
152.5°	1722.6	1723.1	1723.6	1723.7	1723.5	1723.3	1723.2	1723.0
155°	1760.8	1762.1	1763.3	1763.5	1762.6	1761.6	1760.7	1759.7
157.5°	1793.7	1795.4	1797.0	1797.0	1795.4	1793.7	1792.1	1790.4
160°	1814.7	1816.6	1818.4	1818.4	1816.6	1814.7	1812.8	1810.8
162.5°	1831.7	1833.6	1835.5	1835.3	1833.2	1831.1	1828.9	1826.7
165°	1855.7	1858.2	1860.8	1860.6	1857.8	1854.9	1852.1	1849.3
167.5°	1873.3	1876.0	1878.9	1878.7	1875.5	1872.4	1869.2	1866.0
170°	1884.1	1886.7	1889.2	1888.9	1885.7	1882.5	1879.4	1876.2
172.5°	1890.9	1893.5	1896.0	1895.5	1892.2	1888.8	1885.4	1881.9
175°	1898.9	1901.9	1904.7	1904.2	1900.4	1896.6	1892.8	1889.0
177.5°	1902.1	1904.2	1906.2	1905.7	1902.7	1899.6	1896.6	1893.6
180°	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4	1900.4

(END OF REPORT)