

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332119-940

Luminaire Tested: **S123DIW-S340D1535U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332119-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S340D1535U940-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1535 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6005.1 lumens
Efficiency: N/A
Efficacy: 112.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332119-940

CATALOG NUMBER: S123DIW-S340D1535U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332119-940

CATALOG NUMBER: S123DIW-S340D1535U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	89	89	89	89	67	67	67	48	48	48	30	30	30	21
1	91	87	83	80	81	77	74	71	59	57	55	42	40	39	26	25	25	18
2	83	76	70	65	73	67	63	58	51	48	45	37	35	33	23	22	21	15
3	76	67	60	54	67	59	53	49	45	41	38	32	30	28	20	19	18	12
4	69	59	51	46	61	52	46	41	40	36	32	29	26	24	18	16	15	11
5	63	52	45	39	56	46	40	35	36	31	28	26	23	20	16	14	13	9
6	58	47	39	33	51	42	35	30	32	27	24	23	20	18	15	13	12	8
7	54	42	34	29	47	37	31	26	29	24	21	21	18	15	13	12	10	7
8	50	38	30	25	44	34	27	23	26	22	18	19	16	14	12	10	9	6
9	46	34	27	22	41	31	25	20	24	19	16	17	14	12	11	9	8	6
10	43	31	24	20	38	28	22	18	22	17	14	16	13	11	10	9	7	5

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5201	5201	5201
5°	5226	5154	5190
10°	5191	5109	5141
15°	5131	5051	5060
20°	5060	4969	4974
25°	4963	4871	4861
30°	4860	4762	4724
35°	4750	4646	4586
40°	4636	4519	4449
45°	4509	4402	4294
50°	4382	4258	4140
55°	4219	4110	3984
60°	4052	3935	3810
65°	3904	3744	3629
70°	3688	3531	3374
75°	3373	3248	3111
80°	3037	2913	2882
85°	2668	2569	2470



TEST NUMBER: P332119-940

CATALOG NUMBER: S123DIW-S340D1535U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.5	0.8
10°-20°	128.5	2.1
20°-30°	189.9	3.2
30°-40°	221.8	3.7
40°-50°	223.0	3.7
50°-60°	195.8	3.3
60°-70°	145.9	2.4
70°-80°	83.1	1.4
80°-90°	28.9	0.5
90°-100°	111.5	1.9
100°-110°	333.8	5.6
110°-120°	567.7	9.5
120°-130°	746.7	12.4
130°-140°	839.3	14.0
140°-150°	825.0	13.7
150°-160°	694.5	11.6
160°-170°	462.3	7.7
170°-180°	161.9	2.7
0°-30°	363.9	6.1
0°-40°	585.7	9.8
0°-60°	1004.5	16.7
0°-90°	1262.4	21.0
90°-120°	1013.0	16.9
90°-150°	3423.9	57.0
90°-180°	4743.0	79.0
0°-180°	6005.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	483	483	483	483	483	
5°	484	481	477	481	480	46
15°	460	458	453	456	454	130
25°	418	415	410	410	409	192
35°	362	359	354	351	349	226
45°	296	294	289	284	282	229
55°	225	224	219	215	212	201
65°	153	151	147	144	142	151
75°	81	79	78	76	75	87
85°	22	21	21	20	20	24
90°	1	15	32	38	40	6
95°	79	89	100	105	105	89
105°	303	306	317	318	320	324
115°	572	575	573	574	573	565
125°	836	840	838	832	827	746
135°	1085	1093	1092	1087	1084	836
145°	1316	1319	1323	1322	1316	822
155°	1507	1507	1509	1513	1505	694
165°	1642	1638	1638	1645	1636	463
175°	1708	1703	1702	1709	1701	162
180°	1712	1712	1712	1712	1712	



TEST NUMBER: P332119-940

CATALOG NUMBER: S123DIW-S340D1535U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	483.2	483.2	483.2	483.2	483.2	483.2	483.2	483.2	483.2	483.2	483.2
2.5°	484.9	484.6	484.3	484.0	483.7	483.1	482.3	481.5	480.7	479.9	480.6
5°	483.7	483.1	482.7	482.2	481.8	481.1	480.0	479.0	478.0	477.0	477.9
7.5°	478.9	478.4	478.0	477.5	477.1	476.3	475.3	474.2	473.1	472.1	472.9
10°	474.9	474.5	473.9	473.5	473.1	472.3	471.0	469.8	468.6	467.4	468.2
12.5°	469.6	469.2	468.8	468.4	468.1	467.3	466.2	465.0	463.9	462.8	463.4
15°	460.4	460.0	459.6	459.2	458.9	458.1	456.9	455.7	454.5	453.3	454.1
17.5°	449.6	449.2	448.7	448.2	447.7	446.9	445.7	444.5	443.3	442.1	442.6
20°	441.7	441.1	440.6	440.0	439.4	438.5	437.4	436.1	435.0	433.8	434.2
22.5°	432.7	432.1	431.6	431.1	430.5	429.6	428.4	427.2	426.0	424.8	425.1
25°	417.9	417.4	416.9	416.3	415.8	414.9	413.7	412.5	411.3	410.1	410.2
27.5°	402.3	401.7	401.2	400.6	400.1	399.2	398.0	396.6	395.4	394.0	394.1
30°	391.0	390.5	390.0	389.6	389.1	388.3	387.0	385.7	384.4	383.1	383.1
32.5°	379.7	379.1	378.4	377.8	377.3	376.4	375.4	374.4	373.4	372.5	371.9
35°	361.5	361.0	360.3	359.8	359.3	358.4	357.2	356.0	354.8	353.6	353.0
37.5°	342.9	342.1	341.4	340.7	340.1	339.1	337.9	336.6	335.5	334.2	333.6
40°	329.9	329.3	328.8	328.2	327.7	326.7	325.5	324.1	322.9	321.6	320.8
42.5°	316.9	316.3	315.7	315.0	314.4	313.4	312.2	310.9	309.6	308.3	307.6
45°	296.2	295.9	295.5	295.2	294.8	294.0	292.7	291.6	290.3	289.2	288.1
47.5°	275.7	275.2	274.6	274.1	273.6	272.8	271.6	270.5	269.4	268.2	267.2
50°	261.7	261.3	260.8	260.4	259.9	259.0	257.9	256.7	255.5	254.3	253.2
52.5°	247.1	246.8	246.5	246.2	245.8	245.0	243.8	242.5	241.3	240.0	239.2
55°	224.8	224.7	224.6	224.5	224.4	223.7	222.6	221.3	220.2	219.0	217.9
57.5°	203.5	203.2	202.9	202.6	202.2	201.6	200.6	199.7	198.8	197.8	196.9
60°	188.2	188.2	188.1	188.0	187.9	187.3	186.1	185.0	184.0	182.8	182.0
62.5°	174.6	174.3	174.2	173.9	173.6	173.0	171.8	170.8	169.6	168.5	167.7
65°	153.3	152.8	152.4	151.9	151.5	150.8	149.9	148.9	148.0	147.0	146.3
67.5°	130.8	130.4	130.0	129.6	129.2	128.6	128.0	127.2	126.5	125.8	125.2
70°	117.2	116.6	116.1	115.5	114.9	114.4	113.9	113.2	112.7	112.2	111.6
72.5°	102.9	102.5	102.1	101.7	101.2	100.8	100.1	99.5	98.9	98.3	97.6
75°	81.1	80.6	80.3	79.9	79.5	79.2	78.9	78.6	78.4	78.1	77.7
77.5°	61.6	61.4	61.3	61.1	60.8	60.5	60.3	59.9	59.6	59.2	58.9
80°	49.0	48.8	48.5	48.2	47.9	47.7	47.5	47.3	47.2	47.0	46.8
82.5°	36.7	36.6	36.6	36.6	36.5	36.5	36.4	36.4	36.4	36.3	36.1
85°	21.6	21.4	21.2	21.0	20.9	20.8	20.8	20.8	20.8	20.8	20.6
87.5°	8.9	9.3	9.6	10.1	10.4	11.0	11.7	12.4	13.1	13.7	13.9
90°	1.3	4.4	7.3	10.3	13.3	16.8	20.6	24.5	28.4	32.3	33.4
92.5°	32.5	34.6	36.6	38.6	40.7	42.8	45.0	47.2	49.4	51.6	52.6
95°	79.4	81.4	83.6	85.6	87.7	90.0	92.3	94.7	97.1	99.5	100.7
97.5°	140.9	142.5	144.0	145.6	147.1	148.7	150.5	152.2	154.0	155.7	157.1
100°	182.9	184.7	186.5	188.2	190.0	191.7	193.1	194.7	196.2	197.7	198.6
102.5°	231.3	232.4	233.4	234.5	235.6	237.1	239.1	241.0	243.0	245.0	245.9
105°	302.6	303.2	303.7	304.3	305.0	306.6	309.2	311.9	314.7	317.4	317.4
107.5°	385.4	385.8	386.1	386.5	386.8	387.5	388.6	389.7	390.7	391.8	392.8
110°	437.0	437.7	438.2	438.8	439.4	440.0	440.6	441.2	441.8	442.4	443.6



TEST NUMBER: P332119-940

CATALOG NUMBER: S123DIW-S340D1535U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	490.8	491.2	491.5	491.9	492.2	492.5	492.6	492.7	492.8	492.9	494.4
115°	571.5	572.4	573.3	574.2	575.1	575.2	574.6	574.0	573.5	572.8	573.1
117.5°	652.7	653.3	653.9	654.5	655.1	655.0	654.2	653.4	652.6	651.9	651.8
120°	703.3	705.1	706.9	708.6	710.4	710.6	709.1	707.6	706.1	704.6	704.3
122.5°	756.0	757.2	758.6	759.9	761.3	761.5	760.7	759.9	759.2	758.4	757.6
125°	836.3	837.2	838.2	839.1	840.0	840.1	839.5	838.9	838.3	837.8	836.5
127.5°	910.6	912.5	914.4	916.3	918.3	918.9	918.2	917.6	916.9	916.2	914.5
130°	960.1	962.5	964.8	967.2	969.6	970.4	969.5	968.6	967.7	966.8	965.6
132.5°	1009.6	1011.9	1014.3	1016.7	1019.1	1020.0	1019.3	1018.7	1018.0	1017.4	1015.9
135°	1085.1	1086.9	1088.7	1090.5	1092.3	1093.1	1092.8	1092.4	1092.2	1091.9	1090.7
137.5°	1155.0	1156.5	1158.1	1159.6	1161.0	1162.2	1163.0	1163.7	1164.5	1165.3	1164.0
140°	1203.5	1205.0	1206.5	1207.9	1209.4	1210.3	1210.7	1210.9	1211.2	1211.6	1211.2
142.5°	1247.6	1249.0	1250.5	1252.1	1253.6	1254.5	1255.1	1255.6	1256.2	1256.7	1256.4
145°	1316.4	1317.1	1317.6	1318.2	1318.8	1319.6	1320.4	1321.3	1322.2	1323.1	1322.9
147.5°	1376.6	1377.7	1378.8	1379.9	1381.0	1381.9	1382.8	1383.6	1384.4	1385.3	1385.3
150°	1418.6	1419.2	1419.8	1420.4	1421.0	1421.6	1422.2	1422.8	1423.3	1424.0	1424.0
152.5°	1453.0	1453.8	1454.7	1455.5	1456.3	1457.0	1457.3	1457.7	1458.0	1458.4	1458.9
155°	1507.3	1507.3	1507.3	1507.3	1507.3	1507.5	1507.8	1508.1	1508.4	1508.7	1509.9
157.5°	1553.6	1553.3	1552.9	1552.6	1552.2	1552.1	1552.4	1552.6	1552.8	1553.1	1554.3
160°	1582.7	1582.1	1581.4	1580.8	1580.3	1579.9	1579.9	1579.9	1579.9	1579.9	1581.4
162.5°	1608.5	1607.7	1606.8	1606.0	1605.2	1604.8	1605.1	1605.3	1605.5	1605.8	1607.3
165°	1641.8	1640.9	1640.0	1639.1	1638.3	1637.8	1637.8	1637.8	1637.8	1637.8	1639.6
167.5°	1668.5	1667.2	1666.1	1664.8	1663.7	1663.2	1663.4	1663.7	1663.9	1664.1	1666.0
170°	1683.5	1682.3	1681.1	1679.9	1678.7	1678.1	1678.1	1678.1	1678.1	1678.1	1680.3
172.5°	1695.3	1694.2	1692.9	1691.8	1690.6	1690.0	1690.0	1690.0	1690.0	1690.0	1691.8
175°	1707.7	1706.6	1705.3	1704.1	1702.9	1702.4	1702.4	1702.4	1702.4	1702.4	1704.1
177.5°	1712.8	1711.9	1710.9	1709.9	1709.0	1708.5	1708.5	1708.5	1708.5	1708.5	1709.9
180°	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7



TEST NUMBER: P332119-940

CATALOG NUMBER: S123DIW-S340D1535U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	483.2	483.2	483.2	483.2	483.2	483.2	483.2	483.2
2.5°	481.3	482.1	482.9	483.2	483.1	483.0	483.0	482.9
5°	478.8	479.7	480.7	481.1	480.9	480.7	480.5	480.3
7.5°	473.8	474.6	475.4	475.7	475.6	475.5	475.5	475.3
10°	469.1	469.9	470.7	471.1	470.9	470.7	470.6	470.4
12.5°	464.0	464.6	465.2	465.5	465.4	465.2	465.1	465.0
15°	454.8	455.5	456.3	456.4	455.8	455.2	454.7	454.1
17.5°	443.1	443.6	444.2	444.3	444.1	443.9	443.7	443.5
20°	434.5	434.9	435.2	435.3	435.0	434.7	434.4	434.2
22.5°	425.3	425.7	426.0	426.0	425.6	425.3	424.9	424.5
25°	410.3	410.4	410.5	410.4	410.1	409.8	409.6	409.3
27.5°	394.2	394.3	394.3	394.2	393.9	393.5	393.2	392.8
30°	383.1	383.1	383.1	382.7	382.1	381.5	380.8	380.1
32.5°	371.4	370.9	370.4	370.0	369.6	369.3	368.9	368.5
35°	352.5	352.0	351.3	350.9	350.4	349.9	349.5	349.0
37.5°	332.9	332.3	331.5	331.1	330.8	330.5	330.2	329.9
40°	320.1	319.4	318.6	318.1	317.7	317.4	317.0	316.6
42.5°	306.8	306.0	305.3	304.8	304.4	304.1	303.7	303.3
45°	287.0	285.9	284.7	284.0	283.5	283.0	282.6	282.1
47.5°	266.1	265.0	263.9	263.1	262.7	262.3	261.9	261.5
50°	252.3	251.2	250.2	249.4	248.9	248.3	247.8	247.2
52.5°	238.3	237.4	236.5	235.8	235.2	234.7	234.2	233.6
55°	217.0	215.9	214.9	214.2	213.7	213.2	212.8	212.3
57.5°	196.0	195.0	194.1	193.4	192.9	192.3	191.8	191.3
60°	181.2	180.3	179.5	178.9	178.3	177.9	177.5	177.0
62.5°	166.8	166.0	165.2	164.6	164.3	164.0	163.7	163.4
65°	145.6	144.9	144.1	143.7	143.4	143.0	142.8	142.5
67.5°	124.5	123.9	123.2	122.7	122.3	121.9	121.5	121.2
70°	110.9	110.2	109.6	109.1	108.6	108.2	107.6	107.2
72.5°	97.1	96.5	95.9	95.5	95.3	95.1	94.8	94.5
75°	77.2	76.7	76.2	75.9	75.6	75.3	75.1	74.8
77.5°	58.6	58.3	58.0	57.9	57.9	57.9	57.9	57.9
80°	46.7	46.6	46.5	46.5	46.5	46.5	46.5	46.5
82.5°	36.0	35.8	35.7	35.5	35.5	35.4	35.3	35.2
85°	20.4	20.2	20.1	20.0	20.0	20.0	20.0	20.0
87.5°	14.1	14.3	14.4	14.5	14.7	14.8	14.9	15.1
90°	34.7	35.8	37.1	38.0	38.5	39.1	39.8	40.3
92.5°	53.5	54.5	55.5	55.7	55.4	55.0	54.7	54.3
95°	101.9	103.1	104.2	104.9	104.9	104.9	104.9	104.9
97.5°	158.5	159.8	161.2	161.8	161.8	161.6	161.5	161.4
100°	199.5	200.4	201.3	202.0	202.6	203.2	203.8	204.4
102.5°	246.8	247.7	248.6	249.0	248.9	248.7	248.6	248.5
105°	317.4	317.4	317.4	317.6	318.3	318.9	319.4	320.0
107.5°	393.8	394.7	395.7	395.9	395.6	395.2	394.8	394.5
110°	444.8	445.9	447.2	447.5	446.8	446.3	445.7	445.1



TEST NUMBER: P332119-940

CATALOG NUMBER: S123DIW-S340D1535U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	495.8	497.2	498.6	499.4	499.3	499.1	499.0	498.8
115°	573.5	573.7	574.0	574.0	573.7	573.5	573.1	572.8
117.5°	651.8	651.8	651.7	651.2	650.3	649.5	648.7	647.8
120°	704.0	703.7	703.4	702.9	702.4	701.8	701.2	700.5
122.5°	756.8	756.1	755.3	754.5	753.7	752.8	752.0	751.1
125°	835.4	834.1	832.9	831.7	830.5	829.4	828.1	827.0
127.5°	912.9	911.2	909.5	908.0	906.7	905.3	903.9	902.5
130°	964.4	963.2	962.1	960.4	958.3	956.2	954.1	952.0
132.5°	1014.5	1013.1	1011.6	1010.1	1008.5	1006.9	1005.2	1003.6
135°	1089.5	1088.2	1087.1	1086.2	1085.6	1084.9	1084.4	1083.8
137.5°	1162.8	1161.5	1160.3	1159.0	1157.9	1156.8	1155.7	1154.5
140°	1210.9	1210.7	1210.3	1209.2	1207.0	1205.0	1202.8	1200.8
142.5°	1256.2	1255.8	1255.5	1254.5	1252.9	1251.3	1249.7	1248.1
145°	1322.5	1322.2	1322.0	1321.2	1320.0	1318.8	1317.6	1316.4
147.5°	1385.3	1385.3	1385.3	1384.4	1382.6	1380.8	1378.9	1377.2
150°	1424.0	1424.0	1424.0	1423.1	1421.3	1419.5	1417.7	1415.9
152.5°	1459.4	1459.8	1460.4	1459.8	1458.2	1456.7	1455.1	1453.6
155°	1511.1	1512.3	1513.5	1513.1	1510.9	1508.9	1506.7	1504.7
157.5°	1555.6	1556.8	1558.1	1557.9	1556.2	1554.5	1552.8	1551.2
160°	1583.0	1584.5	1585.9	1586.1	1584.9	1583.7	1582.5	1581.3
162.5°	1608.7	1610.3	1611.8	1611.6	1609.6	1607.8	1605.8	1603.9
165°	1641.4	1643.2	1644.9	1644.8	1642.7	1640.7	1638.5	1636.5
167.5°	1667.9	1669.7	1671.5	1671.5	1669.7	1667.9	1666.0	1664.1
170°	1682.3	1684.4	1686.5	1686.5	1684.4	1682.3	1680.3	1678.1
172.5°	1693.6	1695.5	1697.4	1697.3	1695.1	1693.1	1691.0	1688.9
175°	1705.9	1707.7	1709.5	1709.3	1707.3	1705.1	1703.1	1701.0
177.5°	1711.4	1712.8	1714.2	1714.1	1712.4	1710.7	1709.1	1707.4
180°	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7

(END OF REPORT)