

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332725-830

Luminaire Tested: **S124DIW-S350D770U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332725-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S350D770U830-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 770 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4325.0 lumens
Efficiency: N/A
Efficacy: 142.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 30.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332725-830

CATALOG NUMBER: S124DIW-S350D770U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332725-830

CATALOG NUMBER: S124DIW-S350D770U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	33
1	94	90	86	82	85	81	78	75	65	62	60	50	48	47	36	35	34	28
2	86	78	72	67	77	71	66	61	57	53	50	44	41	39	31	30	29	23
3	78	69	62	56	70	62	56	51	50	46	42	38	36	33	28	26	24	20
4	71	61	53	47	64	55	48	43	44	39	36	34	31	28	25	23	21	17
5	65	54	46	40	59	49	42	37	40	34	31	31	27	24	22	20	18	15
6	60	48	40	35	54	44	37	32	36	30	27	28	24	21	20	18	16	13
7	55	44	36	30	50	40	33	28	32	27	23	25	21	19	19	16	14	11
8	51	39	32	27	46	36	29	25	29	24	21	23	19	17	17	15	13	10
9	48	36	29	24	43	33	26	22	27	22	18	21	17	15	16	13	12	9
10	45	33	26	21	40	30	24	20	25	20	16	19	16	13	15	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4495	4495	4495
5°	4508	4454	4486
10°	4480	4418	4440
15°	4425	4355	4367
20°	4354	4277	4281
25°	4272	4188	4177
30°	4172	4084	4047
35°	4066	3975	3921
40°	3958	3851	3780
45°	3846	3729	3658
50°	3720	3620	3508
55°	3586	3478	3365
60°	3450	3321	3219
65°	3299	3171	3043
70°	3127	2969	2854
75°	2866	2729	2658
80°	2552	2450	2385
85°	2232	2149	2103



TEST NUMBER: P332725-830

CATALOG NUMBER: S124DIW-S350D770U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.4	1.2
10°-20°	147.7	3.4
20°-30°	217.4	5.0
30°-40°	252.8	5.8
40°-50°	252.8	5.8
50°-60°	221.1	5.1
60°-70°	164.2	3.8
70°-80°	93.3	2.2
80°-90°	29.6	0.7
90°-100°	32.0	0.7
100°-110°	204.0	4.7
110°-120°	390.2	9.0
120°-130°	495.4	11.5
130°-140°	530.0	12.3
140°-150°	495.6	11.5
150°-160°	399.7	9.2
160°-170°	257.8	6.0
170°-180°	88.8	2.1
0°-30°	417.6	9.7
0°-40°	670.4	15.5
0°-60°	1144.3	26.5
0°-90°	1431.5	33.1
90°-120°	626.2	14.5
90°-150°	2147.2	49.6
90°-180°	2894.0	66.9
0°-180°	4325.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	557	557	557	557	557	
5°	556	554	550	554	554	53
15°	530	528	521	524	522	149
25°	480	476	470	471	469	221
35°	413	409	403	400	398	258
45°	337	333	327	322	320	260
55°	255	253	247	242	239	228
65°	173	170	166	162	159	171
75°	92	90	88	86	85	98
85°	24	24	23	23	23	27
90°	2	10	15	19	21	3
95°	38	16	15	19	20	49
105°	211	215	218	223	199	220
115°	393	395	394	396	396	387
125°	553	555	554	556	557	493
135°	686	685	688	689	690	528
145°	791	793	793	793	795	494
155°	867	867	865	868	866	400
165°	914	911	911	916	910	258
175°	935	932	932	937	930	89
180°	935	935	935	935	935	



TEST NUMBER: P332725-830

CATALOG NUMBER: S124DIW-S350D770U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8
2.5°	558.2	558.0	557.7	557.5	557.2	556.7	555.8	555.0	554.1	553.2	554.0
5°	556.3	555.9	555.5	555.2	554.8	554.0	552.9	551.9	550.7	549.6	550.7
7.5°	551.2	550.7	550.4	550.0	549.6	548.7	547.5	546.4	545.2	543.9	544.8
10°	546.5	546.1	545.7	545.4	545.0	544.1	542.8	541.5	540.3	538.9	539.7
12.5°	540.5	540.1	539.7	539.2	538.9	538.0	536.6	535.3	533.9	532.5	533.4
15°	529.5	529.1	528.8	528.4	528.0	527.1	525.6	524.1	522.5	521.1	521.7
17.5°	516.4	515.9	515.5	515.0	514.4	513.5	512.1	510.7	509.3	507.8	508.2
20°	506.8	506.3	505.9	505.3	504.8	503.9	502.4	500.9	499.4	497.9	498.2
22.5°	496.4	495.8	495.1	494.5	493.8	492.8	491.3	489.8	488.3	486.8	487.4
25°	479.6	478.9	478.2	477.5	476.8	475.8	474.4	473.0	471.6	470.2	470.3
27.5°	460.3	459.6	458.9	458.2	457.5	456.5	455.2	453.9	452.6	451.3	451.1
30°	447.5	446.7	445.9	445.1	444.3	443.3	442.0	440.6	439.4	438.1	437.7
32.5°	433.9	433.2	432.4	431.8	431.0	430.0	428.7	427.3	425.9	424.5	424.0
35°	412.6	412.0	411.3	410.6	409.9	408.9	407.5	406.0	404.7	403.3	402.7
37.5°	390.3	389.6	389.0	388.4	387.8	386.7	385.2	383.7	382.2	380.7	379.9
40°	375.6	374.8	374.1	373.2	372.5	371.4	369.9	368.3	366.8	365.4	364.4
42.5°	360.0	359.5	359.0	358.5	358.1	356.9	355.3	353.6	352.0	350.4	349.2
45°	336.9	336.1	335.5	334.8	334.0	332.9	331.3	329.7	328.2	326.6	325.5
47.5°	312.6	312.2	311.7	311.2	310.8	309.8	308.3	306.8	305.4	303.9	302.7
50°	296.2	295.9	295.5	295.0	294.6	293.8	292.4	291.0	289.5	288.2	286.8
52.5°	280.2	279.7	279.2	278.7	278.2	277.3	275.8	274.4	272.9	271.5	270.2
55°	254.8	254.5	254.1	253.8	253.5	252.7	251.3	250.0	248.5	247.1	246.0
57.5°	230.5	230.2	229.8	229.5	229.1	228.3	226.9	225.6	224.1	222.8	221.7
60°	213.7	213.2	212.7	212.2	211.7	210.8	209.5	208.2	207.0	205.7	204.8
62.5°	197.3	196.9	196.4	196.0	195.6	194.7	193.3	192.0	190.6	189.3	188.4
65°	172.7	172.2	171.6	171.2	170.7	169.9	168.9	168.0	166.9	166.0	164.9
67.5°	147.9	147.4	146.9	146.5	146.0	145.3	144.4	143.5	142.5	141.5	140.5
70°	132.5	131.8	131.1	130.4	129.7	128.9	128.2	127.4	126.6	125.8	125.0
72.5°	116.1	115.4	114.7	114.0	113.3	112.6	112.0	111.4	110.7	110.1	109.4
75°	91.9	91.4	91.0	90.4	89.9	89.4	89.0	88.4	87.9	87.5	87.1
77.5°	68.8	68.6	68.3	68.1	68.0	67.6	67.2	66.7	66.3	65.9	65.7
80°	54.9	54.6	54.3	54.0	53.7	53.4	53.3	53.1	52.9	52.7	52.4
82.5°	41.3	41.2	41.0	40.9	40.7	40.6	40.6	40.6	40.5	40.5	40.4
85°	24.1	24.1	24.1	24.1	24.1	24.0	23.8	23.6	23.4	23.2	23.2
87.5°	9.7	10.0	10.2	10.5	10.7	10.9	11.1	11.3	11.5	11.7	11.9
90°	2.1	3.8	5.6	7.3	9.0	10.5	11.7	12.9	14.1	15.4	16.3
92.5°	8.9	9.0	9.0	9.0	9.1	9.9	11.1	12.3	13.6	14.8	15.7
95°	38.5	33.2	27.9	22.6	17.3	14.8	14.9	15.1	15.3	15.4	16.3
97.5°	81.7	85.0	88.3	91.6	94.9	87.8	70.5	53.2	35.8	18.5	18.6
100°	114.7	117.5	120.4	123.1	125.9	116.6	95.2	73.7	52.2	30.8	28.2
102.5°	151.7	153.7	155.8	157.9	159.9	159.5	156.7	153.9	151.1	148.4	119.8
105°	210.6	211.5	212.4	213.4	214.3	215.2	215.9	216.7	217.5	218.3	219.7
107.5°	265.3	265.8	266.3	266.7	267.2	268.0	269.0	270.0	271.1	272.1	272.9
110°	302.3	302.7	303.2	303.7	304.1	304.8	305.8	306.7	307.6	308.5	308.9



TEST NUMBER: P332725-830

CATALOG NUMBER: S124DIW-S350D770U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	338.1	338.9	339.8	340.5	341.4	342.0	342.5	342.9	343.4	343.8	343.7
115°	393.2	393.7	394.2	394.5	395.0	395.2	395.0	394.9	394.7	394.5	394.9
117.5°	442.9	443.5	444.1	444.7	445.4	445.8	446.2	446.5	446.9	447.2	447.1
120°	476.5	477.1	477.7	478.3	478.9	479.2	479.0	478.9	478.7	478.5	478.9
122.5°	507.8	508.1	508.5	508.9	509.3	509.5	509.8	510.0	510.2	510.5	510.7
125°	552.7	553.4	553.9	554.6	555.2	555.3	555.1	554.8	554.4	554.1	554.6
127.5°	595.2	595.4	595.6	595.7	595.9	596.3	597.0	597.8	598.4	599.2	599.1
130°	622.6	622.8	623.0	623.1	623.3	623.6	624.1	624.5	625.0	625.5	625.7
132.5°	647.9	648.2	648.5	648.7	648.9	649.4	650.0	650.6	651.2	651.8	652.0
135°	685.6	685.5	685.3	685.1	685.0	685.2	685.9	686.5	687.1	687.8	688.1
137.5°	719.1	719.2	719.3	719.3	719.3	719.7	720.4	721.0	721.8	722.5	722.7
140°	740.9	741.2	741.5	741.9	742.2	742.4	742.8	743.1	743.4	743.8	744.1
142.5°	760.5	761.1	761.7	762.1	762.7	763.1	763.3	763.5	763.6	763.8	764.2
145°	790.6	791.1	791.5	792.0	792.5	792.7	792.7	792.7	792.7	792.7	792.9
147.5°	814.5	815.4	816.2	817.1	818.0	818.3	818.2	818.0	817.8	817.7	817.8
150°	831.9	832.5	833.1	833.8	834.3	834.6	834.4	834.2	834.2	834.0	834.0
152.5°	846.4	846.9	847.4	847.9	848.4	848.5	848.2	848.0	847.7	847.4	847.6
155°	866.9	867.0	867.1	867.3	867.5	867.3	866.9	866.4	865.9	865.4	866.1
157.5°	884.1	884.0	883.9	883.8	883.7	883.4	882.9	882.3	881.7	881.3	882.0
160°	894.1	893.6	893.2	892.8	892.3	891.9	891.8	891.6	891.5	891.4	892.3
162.5°	903.1	902.5	901.9	901.4	900.7	900.3	900.2	900.0	899.8	899.8	900.7
165°	914.5	913.6	912.9	912.1	911.3	911.0	911.0	911.0	911.0	911.0	912.2
167.5°	923.4	922.6	921.8	921.0	920.1	919.7	919.6	919.5	919.5	919.4	920.7
170°	928.4	927.5	926.5	925.6	924.7	924.3	924.4	924.6	924.7	924.9	926.1
172.5°	931.8	930.9	929.9	929.0	928.0	927.7	927.8	927.9	928.1	928.3	929.5
175°	935.4	934.4	933.6	932.6	931.7	931.3	931.4	931.6	931.8	931.9	933.3
177.5°	937.1	936.2	935.4	934.4	933.6	933.3	933.6	933.8	934.1	934.2	935.3
180°	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4



TEST NUMBER: P332725-830

CATALOG NUMBER: S124DIW-S350D770U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8
2.5°	554.8	555.6	556.4	556.8	556.7	556.6	556.5	556.4
5°	551.9	552.9	554.0	554.4	554.2	554.0	553.8	553.6
7.5°	545.6	546.6	547.4	547.8	547.7	547.5	547.4	547.3
10°	540.5	541.3	542.2	542.4	542.2	542.0	541.8	541.6
12.5°	534.2	535.1	536.0	536.3	536.0	535.7	535.5	535.2
15°	522.3	522.8	523.5	523.6	523.3	523.0	522.7	522.5
17.5°	508.6	509.0	509.3	509.4	509.3	509.1	508.9	508.7
20°	498.5	498.8	499.1	499.2	498.9	498.7	498.5	498.3
22.5°	487.9	488.4	489.0	489.1	488.7	488.3	488.0	487.7
25°	470.4	470.5	470.6	470.5	470.0	469.7	469.3	468.9
27.5°	450.8	450.6	450.3	450.0	449.5	449.0	448.5	448.0
30°	437.3	437.0	436.5	436.1	435.5	435.1	434.6	434.1
32.5°	423.6	423.1	422.6	422.2	421.7	421.1	420.7	420.2
35°	401.9	401.2	400.5	399.9	399.4	399.0	398.4	397.9
37.5°	379.2	378.4	377.7	377.0	376.4	375.7	375.0	374.4
40°	363.4	362.4	361.5	360.7	360.1	359.7	359.2	358.7
42.5°	348.1	346.9	345.8	345.1	344.7	344.4	344.0	343.7
45°	324.4	323.3	322.3	321.5	321.2	320.9	320.7	320.4
47.5°	301.4	300.2	299.0	298.0	297.3	296.5	295.8	295.0
50°	285.4	284.1	282.7	281.6	281.1	280.5	279.8	279.3
52.5°	269.0	267.8	266.6	265.5	264.8	264.0	263.3	262.5
55°	244.8	243.6	242.4	241.5	240.9	240.3	239.7	239.1
57.5°	220.6	219.4	218.3	217.4	216.9	216.3	215.7	215.1
60°	203.9	203.0	202.1	201.4	201.0	200.4	199.9	199.4
62.5°	187.7	186.8	186.0	185.3	184.8	184.4	183.9	183.3
65°	164.0	163.0	162.0	161.3	160.8	160.2	159.8	159.3
67.5°	139.6	138.6	137.7	137.1	137.0	136.9	136.8	136.6
70°	124.2	123.5	122.6	122.1	121.8	121.5	121.2	120.9
72.5°	108.9	108.2	107.5	107.1	106.8	106.5	106.2	105.9
75°	86.6	86.2	85.9	85.6	85.5	85.4	85.3	85.2
77.5°	65.6	65.5	65.4	65.2	64.9	64.7	64.4	64.2
80°	52.2	52.0	51.8	51.7	51.6	51.5	51.4	51.3
82.5°	40.2	40.2	40.1	40.0	39.9	39.7	39.6	39.5
85°	23.2	23.2	23.2	23.2	23.1	23.0	22.8	22.7
87.5°	12.0	12.2	12.3	12.5	12.5	12.6	12.7	12.7
90°	17.2	18.2	19.1	19.7	20.1	20.4	20.6	21.0
92.5°	16.7	17.6	18.6	19.0	19.1	19.2	19.2	19.3
95°	17.2	18.2	19.1	19.7	19.8	20.0	20.2	20.3
97.5°	18.7	18.8	18.9	18.9	19.1	19.3	19.4	19.6
100°	25.5	22.8	20.2	18.9	19.1	19.3	19.4	19.6
102.5°	91.3	62.8	34.3	20.0	20.1	20.1	20.1	20.2
105°	221.1	222.4	223.9	221.8	216.2	210.6	205.0	199.4
107.5°	273.5	274.2	274.9	275.5	276.2	276.7	277.3	277.9
110°	309.2	309.4	309.8	310.2	310.7	311.1	311.6	312.1



TEST NUMBER: P332725-830

CATALOG NUMBER: S124DIW-S350D770U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	343.7	343.7	343.6	343.8	344.4	345.0	345.6	346.2
115°	395.2	395.5	395.9	396.0	396.0	396.0	396.0	396.0
117.5°	447.0	447.0	447.0	446.9	446.9	446.8	446.7	446.7
120°	479.2	479.5	479.8	479.8	479.5	479.2	478.9	478.5
122.5°	510.9	511.0	511.2	511.1	510.9	510.5	510.2	509.9
125°	555.1	555.5	556.0	556.3	556.5	556.6	556.8	556.9
127.5°	599.0	598.9	598.8	598.7	598.6	598.4	598.3	598.2
130°	625.8	625.9	626.1	626.1	626.1	626.1	626.1	626.1
132.5°	652.1	652.2	652.4	652.4	652.3	652.1	652.1	652.0
135°	688.3	688.7	689.0	689.3	689.6	689.9	690.2	690.5
137.5°	723.1	723.5	723.8	724.0	723.9	723.8	723.7	723.6
140°	744.6	745.1	745.6	745.9	746.0	746.2	746.4	746.5
142.5°	764.6	764.9	765.3	765.4	765.4	765.4	765.5	765.5
145°	793.0	793.1	793.3	793.5	793.8	794.2	794.5	794.8
147.5°	817.9	818.1	818.2	818.4	818.5	818.7	818.9	819.0
150°	834.0	834.0	834.0	834.1	834.2	834.3	834.5	834.6
152.5°	847.9	848.1	848.4	848.5	848.4	848.3	848.2	848.1
155°	866.7	867.3	867.9	868.0	867.5	867.0	866.6	866.2
157.5°	882.9	883.7	884.5	884.5	883.7	882.9	882.0	881.3
160°	893.2	894.1	895.0	895.0	894.1	893.2	892.3	891.4
162.5°	901.6	902.5	903.4	903.4	902.4	901.3	900.2	899.2
165°	913.4	914.6	915.9	915.9	914.5	913.0	911.6	910.2
167.5°	922.1	923.4	924.8	924.7	923.1	921.6	920.0	918.5
170°	927.4	928.7	929.9	929.7	928.2	926.6	925.1	923.5
172.5°	930.8	932.0	933.2	933.0	931.3	929.7	928.0	926.3
175°	934.7	936.1	937.5	937.3	935.4	933.6	931.7	929.8
177.5°	936.3	937.3	938.3	938.0	936.5	935.0	933.6	932.1
180°	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4

(END OF REPORT)