

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332142-940

Luminaire Tested: **S123DIW-S560D1320U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332142-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S560D1320U940-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1320 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6777.8 lumens
Efficiency: N/A
Efficacy: 126.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332142-940

CATALOG NUMBER: S123DIW-S560D1320U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332142-940

CATALOG NUMBER: S123DIW-S560D1320U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	38	38	38	31
1	93	89	85	82	84	80	77	74	63	61	59	48	47	45	34	33	32	26
2	85	78	72	67	76	70	65	61	55	52	49	42	40	38	30	28	27	21
3	77	68	61	56	69	62	56	51	49	45	41	37	34	32	26	24	23	18
4	71	60	53	47	63	54	48	43	43	39	35	33	30	27	23	21	20	16
5	65	54	46	40	58	48	42	37	39	34	30	30	26	23	21	19	17	13
6	60	48	40	34	53	43	37	32	35	30	26	27	23	20	19	17	15	12
7	55	43	35	30	49	39	32	28	31	26	23	24	21	18	17	15	13	10
8	51	39	32	26	46	35	29	24	29	24	20	22	19	16	16	14	12	9
9	47	36	28	23	42	32	26	22	26	21	18	20	17	14	15	12	11	8
10	44	32	25	21	40	30	23	19	24	19	16	19	15	13	14	11	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8551	8551	8551
5°	8590	8473	8532
10°	8534	8400	8451
15°	8433	8304	8320
20°	8317	8168	8176
25°	8162	8007	7991
30°	7988	7828	7768
35°	7808	7638	7540
40°	7620	7429	7314
45°	7415	7237	7060
50°	7206	7000	6805
55°	6934	6756	6549
60°	6661	6469	6265
65°	6421	6159	5968
70°	6061	5803	5545
75°	5540	5340	5115
80°	4996	4785	4742
85°	4384	4224	4051



TEST NUMBER: P332142-940

CATALOG NUMBER: S123DIW-S560D1320U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.8	1.1
10°-20°	211.3	3.1
20°-30°	312.1	4.6
30°-40°	364.6	5.4
40°-50°	366.5	5.4
50°-60°	322.0	4.8
60°-70°	239.9	3.5
70°-80°	136.7	2.0
80°-90°	43.5	0.6
90°-100°	56.1	0.8
100°-110°	267.4	3.9
110°-120°	642.3	9.5
120°-130°	818.0	12.1
130°-140°	874.0	12.9
140°-150°	817.3	12.1
150°-160°	659.2	9.7
160°-170°	425.5	6.3
170°-180°	146.6	2.2
0°-30°	598.2	8.8
0°-40°	962.8	14.2
0°-60°	1651.3	24.4
0°-90°	2071.4	30.6
90°-120°	965.9	14.3
90°-150°	3475.0	51.3
90°-180°	4706.0	69.4
0°-180°	6777.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	794	794	794	794	794	
5°	795	791	784	791	790	75
15°	757	754	745	750	747	213
25°	687	683	674	675	673	316
35°	594	590	581	577	574	372
45°	487	484	475	467	464	376
55°	370	368	360	353	349	331
65°	252	248	242	236	234	249
75°	133	131	128	125	123	142
85°	36	34	34	33	33	39
90°	1	13	28	32	34	5
95°	70	26	36	43	44	86
105°	342	348	251	60	50	362
115°	641	648	658	669	674	632
125°	904	912	917	920	922	807
135°	1125	1132	1136	1139	1136	866
145°	1298	1306	1308	1310	1310	812
155°	1430	1428	1429	1434	1428	658
165°	1508	1504	1503	1511	1504	426
175°	1543	1538	1539	1546	1538	147
180°	1543	1543	1543	1543	1543	



TEST NUMBER: P332142-940

CATALOG NUMBER: S123DIW-S560D1320U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	794.4	794.4	794.4	794.4	794.4	794.4	794.4	794.4	794.4	794.4	794.4
2.5°	797.1	796.7	796.2	795.7	795.2	794.2	792.9	791.6	790.3	789.0	790.1
5°	795.0	794.3	793.5	792.8	792.0	790.9	789.2	787.5	785.9	784.2	785.7
7.5°	787.3	786.6	785.8	785.1	784.3	783.0	781.3	779.5	777.8	776.1	777.5
10°	780.8	780.0	779.3	778.5	777.8	776.3	774.4	772.4	770.4	768.5	769.8
12.5°	772.0	771.3	770.7	770.1	769.5	768.2	766.3	764.5	762.7	760.8	761.8
15°	756.8	756.3	755.6	755.0	754.4	753.1	751.2	749.2	747.2	745.2	746.5
17.5°	739.2	738.4	737.6	736.8	736.0	734.7	732.7	730.8	728.8	726.7	727.6
20°	726.1	725.2	724.2	723.4	722.5	721.0	719.1	717.1	715.1	713.1	713.7
22.5°	711.3	710.4	709.5	708.6	707.7	706.2	704.3	702.3	700.3	698.4	698.8
25°	687.2	686.3	685.4	684.5	683.5	682.1	680.1	678.1	676.2	674.2	674.3
27.5°	661.4	660.5	659.6	658.7	657.8	656.3	654.2	652.1	650.0	647.8	647.9
30°	642.7	642.0	641.2	640.5	639.7	638.3	636.1	634.0	632.0	629.8	629.8
32.5°	624.2	623.2	622.1	621.2	620.2	618.8	617.2	615.5	613.9	612.3	611.4
35°	594.2	593.3	592.5	591.6	590.7	589.2	587.2	585.2	583.3	581.3	580.4
37.5°	563.7	562.5	561.3	560.2	559.0	557.5	555.4	553.5	551.4	549.5	548.4
40°	542.3	541.4	540.6	539.7	538.7	537.2	535.0	533.0	530.8	528.7	527.4
42.5°	521.0	520.0	519.0	517.9	516.9	515.3	513.2	511.1	509.0	506.8	505.6
45°	487.1	486.4	485.8	485.2	484.6	483.3	481.3	479.4	477.4	475.4	473.6
47.5°	453.3	452.4	451.6	450.7	449.8	448.4	446.6	444.7	442.8	441.0	439.2
50°	430.3	429.5	428.8	428.0	427.3	426.0	423.9	422.0	420.0	418.0	416.3
52.5°	406.3	405.7	405.3	404.7	404.2	402.9	400.8	398.8	396.6	394.6	393.2
55°	369.5	369.3	369.3	369.1	368.9	367.8	365.9	363.9	361.9	360.0	358.3
57.5°	334.6	334.0	333.5	333.1	332.5	331.4	329.8	328.3	326.7	325.1	323.7
60°	309.4	309.2	309.2	309.0	308.8	307.8	306.0	304.2	302.4	300.5	299.2
62.5°	287.0	286.6	286.2	285.9	285.4	284.4	282.5	280.7	278.8	277.1	275.7
65°	252.1	251.3	250.6	249.8	249.1	247.9	246.4	244.9	243.3	241.8	240.6
67.5°	215.0	214.4	213.7	213.0	212.3	211.4	210.3	209.1	207.9	206.9	205.8
70°	192.6	191.7	190.8	189.9	189.0	188.1	187.2	186.3	185.3	184.4	183.3
72.5°	169.2	168.4	167.8	167.1	166.5	165.6	164.6	163.5	162.5	161.5	160.5
75°	133.2	132.6	132.0	131.3	130.8	130.3	129.7	129.3	128.9	128.4	127.7
77.5°	101.4	101.0	100.7	100.4	100.0	99.6	99.1	98.5	97.9	97.4	96.9
80°	80.6	80.2	79.7	79.3	78.7	78.4	78.1	77.8	77.5	77.2	77.0
82.5°	60.4	60.3	60.2	60.1	60.0	59.9	59.9	59.8	59.7	59.7	59.4
85°	35.5	35.2	35.0	34.6	34.3	34.2	34.2	34.2	34.2	34.2	33.9
87.5°	14.4	14.6	14.7	14.9	15.0	15.3	15.9	16.4	16.9	17.6	17.6
90°	1.2	3.7	6.2	8.8	11.3	14.3	17.6	20.9	24.2	27.6	28.5
92.5°	21.3	20.6	19.9	19.2	18.5	19.4	21.8	24.3	26.8	29.3	30.9
95°	69.9	59.5	49.0	38.6	28.2	24.3	27.1	30.0	32.7	35.6	37.4
97.5°	140.5	135.9	131.2	126.5	121.8	110.3	91.9	73.7	55.3	36.9	39.0
100°	193.8	198.9	203.9	209.0	214.2	196.8	157.1	117.3	77.6	37.8	39.9
102.5°	254.3	258.0	261.6	265.3	269.0	249.1	205.7	162.3	118.9	75.4	69.1
105°	341.7	344.5	347.3	350.1	352.8	342.9	319.9	296.9	274.0	251.1	206.0
107.5°	433.9	436.1	438.4	440.6	442.8	445.8	449.4	453.0	456.6	460.2	427.1
110°	495.3	497.4	499.4	501.4	503.5	505.9	508.7	511.5	514.3	517.1	508.7



TEST NUMBER: P332142-940

CATALOG NUMBER: S123DIW-S560D1320U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	554.0	555.9	557.7	559.5	561.3	563.7	566.5	569.3	572.1	574.9	575.1
115°	641.0	642.5	644.0	645.5	647.0	649.0	651.2	653.5	655.9	658.2	660.7
117.5°	725.1	727.0	728.9	730.8	732.6	734.1	735.3	736.6	737.7	738.9	740.9
120°	777.4	779.7	781.9	784.3	786.6	788.1	788.8	789.6	790.4	791.1	793.2
122.5°	830.6	832.5	834.4	836.2	838.1	839.5	840.5	841.5	842.5	843.5	844.9
125°	903.5	905.5	907.6	909.6	911.7	913.2	914.2	915.3	916.2	917.3	917.7
127.5°	974.1	976.2	978.2	980.3	982.3	983.9	985.2	986.4	987.6	988.8	989.6
130°	1018.2	1020.2	1022.3	1024.3	1026.4	1027.9	1028.9	1029.9	1030.9	1031.9	1033.0
132.5°	1060.3	1062.4	1064.4	1066.5	1068.5	1070.0	1070.8	1071.6	1072.4	1073.2	1074.2
135°	1124.8	1126.3	1127.8	1129.4	1131.0	1132.2	1133.2	1134.3	1135.2	1136.3	1137.0
137.5°	1179.8	1181.8	1183.7	1185.6	1187.6	1188.8	1189.4	1190.0	1190.5	1191.1	1192.3
140°	1216.6	1218.1	1219.6	1221.1	1222.6	1223.8	1224.6	1225.3	1226.1	1226.8	1227.9
142.5°	1250.4	1252.0	1253.6	1255.1	1256.6	1257.8	1258.5	1259.3	1260.0	1260.8	1261.6
145°	1298.0	1299.8	1301.5	1303.3	1305.1	1306.2	1306.7	1307.2	1307.8	1308.2	1308.8
147.5°	1342.6	1343.8	1345.0	1346.1	1347.4	1348.2	1348.7	1349.2	1349.7	1350.2	1350.8
150°	1370.2	1370.9	1371.7	1372.4	1373.2	1373.9	1374.4	1374.8	1375.4	1375.9	1376.4
152.5°	1394.9	1395.3	1395.6	1396.0	1396.3	1396.7	1397.0	1397.3	1397.6	1397.9	1398.8
155°	1429.8	1429.3	1428.8	1428.3	1427.7	1427.6	1427.9	1428.2	1428.4	1428.6	1429.9
157.5°	1456.9	1456.8	1456.8	1456.7	1456.6	1456.5	1456.3	1456.0	1455.7	1455.5	1457.0
160°	1473.4	1473.1	1472.8	1472.6	1472.3	1472.1	1471.9	1471.6	1471.3	1471.1	1472.6
162.5°	1489.0	1488.3	1487.6	1486.9	1486.3	1485.9	1485.6	1485.3	1485.1	1484.8	1486.6
165°	1507.8	1507.0	1506.2	1505.5	1504.7	1504.2	1504.0	1503.7	1503.4	1503.2	1505.2
167.5°	1522.4	1521.4	1520.4	1519.4	1518.3	1517.9	1517.9	1517.9	1517.9	1517.9	1519.9
170°	1530.7	1529.6	1528.7	1527.7	1526.6	1526.1	1526.1	1526.1	1526.1	1526.1	1528.1
172.5°	1536.2	1535.0	1533.7	1532.5	1531.3	1530.8	1531.0	1531.2	1531.4	1531.6	1533.7
175°	1543.3	1542.0	1540.8	1539.4	1538.2	1537.7	1537.9	1538.2	1538.5	1538.7	1540.5
177.5°	1545.2	1544.1	1543.1	1542.1	1541.1	1540.7	1540.9	1541.1	1541.2	1541.5	1543.1
180°	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3



TEST NUMBER: P332142-940

CATALOG NUMBER: S123DIW-S560D1320U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	794.4	794.4	794.4	794.4	794.4	794.4	794.4	794.4
2.5°	791.4	792.6	793.8	794.3	794.2	794.1	794.0	793.9
5°	787.2	788.7	790.2	790.9	790.5	790.2	790.0	789.6
7.5°	778.8	780.2	781.6	782.1	781.9	781.8	781.6	781.4
10°	771.2	772.6	773.9	774.5	774.2	773.8	773.6	773.2
12.5°	762.8	763.8	764.8	765.2	765.0	764.8	764.6	764.5
15°	747.7	748.9	750.1	750.2	749.3	748.4	747.5	746.6
17.5°	728.5	729.3	730.2	730.4	730.1	729.8	729.4	729.1
20°	714.3	715.0	715.5	715.6	715.2	714.7	714.3	713.8
22.5°	699.4	699.8	700.3	700.3	699.7	699.1	698.6	697.9
25°	674.5	674.7	674.8	674.7	674.2	673.8	673.2	672.8
27.5°	648.1	648.2	648.3	648.1	647.5	646.9	646.3	645.8
30°	629.8	629.8	629.8	629.3	628.2	627.1	626.1	625.0
32.5°	610.6	609.8	608.9	608.1	607.6	607.1	606.5	605.9
35°	579.4	578.5	577.7	576.8	576.0	575.3	574.5	573.8
37.5°	547.2	546.2	545.1	544.3	543.9	543.3	542.9	542.3
40°	526.3	525.0	523.9	522.9	522.3	521.7	521.1	520.5
42.5°	504.4	503.2	501.9	501.1	500.4	499.9	499.3	498.6
45°	471.8	469.9	468.1	466.8	466.1	465.3	464.6	463.8
47.5°	437.4	435.6	433.8	432.6	431.9	431.2	430.6	429.9
50°	414.7	413.0	411.3	410.1	409.1	408.2	407.3	406.4
52.5°	391.7	390.3	388.9	387.6	386.7	385.8	385.0	384.1
55°	356.6	355.0	353.3	352.0	351.3	350.5	349.8	349.0
57.5°	322.2	320.7	319.2	318.0	317.1	316.3	315.4	314.5
60°	297.8	296.5	295.1	294.0	293.3	292.5	291.8	291.0
62.5°	274.3	273.0	271.6	270.6	270.1	269.7	269.1	268.6
65°	239.3	238.2	236.9	236.1	235.7	235.2	234.8	234.3
67.5°	204.7	203.7	202.6	201.7	201.1	200.5	199.8	199.2
70°	182.3	181.3	180.2	179.2	178.5	177.7	177.0	176.2
72.5°	159.6	158.6	157.7	157.0	156.7	156.2	155.9	155.4
75°	126.9	126.2	125.4	124.8	124.3	123.9	123.4	123.0
77.5°	96.4	95.9	95.3	95.1	95.1	95.1	95.1	95.1
80°	76.9	76.7	76.6	76.5	76.5	76.5	76.5	76.5
82.5°	59.1	58.9	58.6	58.4	58.3	58.1	58.1	58.0
85°	33.5	33.3	32.9	32.8	32.8	32.8	32.8	32.8
87.5°	17.7	17.7	17.8	17.9	18.0	18.2	18.3	18.4
90°	29.5	30.6	31.6	32.4	32.9	33.3	33.9	34.4
92.5°	32.6	34.2	35.8	36.8	37.2	37.5	37.7	38.1
95°	39.1	40.9	42.7	43.6	43.6	43.6	43.6	43.6
97.5°	41.0	43.1	45.0	46.2	46.5	46.7	47.0	47.3
100°	41.9	44.0	46.0	47.2	47.3	47.6	47.9	48.2
102.5°	62.8	56.4	50.2	47.3	47.7	48.2	48.6	49.0
105°	160.9	115.8	70.7	48.4	49.0	49.4	49.9	50.5
107.5°	394.1	361.1	328.0	294.4	260.5	226.4	192.4	158.5
110°	500.2	491.9	483.5	461.0	424.6	388.2	351.8	315.3



TEST NUMBER: P332142-940

CATALOG NUMBER: S123DIW-S560D1320U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	575.2	575.3	575.5	571.8	564.0	556.3	548.7	541.0
115°	663.3	665.8	668.3	670.1	671.1	672.2	673.2	674.2
117.5°	743.0	744.9	747.0	748.1	748.3	748.5	748.8	748.9
120°	795.2	797.3	799.3	800.3	800.3	800.3	800.3	800.3
122.5°	846.3	847.7	849.2	850.0	850.2	850.3	850.6	850.8
125°	918.3	918.8	919.3	919.8	920.3	920.9	921.3	921.9
127.5°	990.4	991.2	992.1	992.2	991.8	991.2	990.7	990.2
130°	1033.9	1035.0	1036.0	1036.3	1035.7	1035.3	1034.7	1034.2
132.5°	1075.2	1076.3	1077.3	1077.5	1076.7	1076.0	1075.3	1074.6
135°	1137.8	1138.5	1139.3	1139.3	1138.5	1137.8	1137.0	1136.3
137.5°	1193.6	1194.7	1196.0	1196.3	1195.8	1195.3	1194.8	1194.3
140°	1228.9	1229.9	1230.9	1231.2	1230.7	1230.1	1229.7	1229.1
142.5°	1262.4	1263.2	1264.1	1264.1	1263.4	1262.7	1261.9	1261.2
145°	1309.3	1309.7	1310.3	1310.5	1310.5	1310.5	1310.5	1310.5
147.5°	1351.2	1351.7	1352.3	1351.9	1350.8	1349.6	1348.4	1347.2
150°	1376.9	1377.4	1378.0	1377.8	1377.1	1376.3	1375.6	1374.8
152.5°	1399.7	1400.7	1401.6	1401.5	1400.3	1399.1	1397.9	1396.8
155°	1431.2	1432.4	1433.8	1433.6	1432.1	1430.6	1429.1	1427.5
157.5°	1458.6	1460.1	1461.6	1461.3	1459.4	1457.4	1455.4	1453.4
160°	1474.1	1475.7	1477.2	1477.0	1475.2	1473.5	1471.7	1469.9
162.5°	1488.3	1490.0	1491.7	1491.8	1490.2	1488.7	1487.1	1485.5
165°	1507.3	1509.3	1511.4	1511.4	1509.7	1507.9	1506.1	1504.3
167.5°	1522.0	1523.9	1526.0	1526.0	1523.9	1522.0	1519.9	1517.9
170°	1530.2	1532.2	1534.3	1534.3	1532.2	1530.2	1528.1	1526.1
172.5°	1535.7	1537.8	1539.8	1539.6	1537.4	1535.2	1532.9	1530.7
175°	1542.3	1544.1	1545.9	1545.7	1543.7	1541.7	1539.6	1537.6
177.5°	1544.7	1546.4	1548.0	1547.8	1545.8	1543.7	1541.7	1539.6
180°	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3

(END OF REPORT)