

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332774-830

Luminaire Tested: **S124DIW-S575D1560U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332774-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S575D1560U830-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7452.7 lumens
Efficiency: N/A
Efficacy: 123.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 60.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332774-830

CATALOG NUMBER: S124DIW-S575D1560U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332774-830

CATALOG NUMBER: S124DIW-S575D1560U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39				32
1	94	89	86	82	84	81	77	74	64	62	60	49	47	46	35	34	33				27
2	85	78	72	67	76	70	65	61	56	52	49	43	40	38	30	29	28				22
3	78	69	61	56	70	62	56	51	49	45	41	38	35	32	27	25	24				19
4	71	61	53	47	64	55	48	43	44	39	35	34	30	28	24	22	20				16
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	19	18				14
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	17	16				12
7	55	43	36	30	50	39	33	28	32	27	23	25	21	18	18	16	14				11
8	51	39	32	27	46	36	29	24	29	24	20	22	19	16	16	14	12				10
9	48	36	28	24	43	32	26	22	26	22	18	21	17	15	15	13	11				9
10	44	33	26	21	40	30	24	19	24	19	16	19	16	13	14	12	10				8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7389	7389	7389
5°	7412	7323	7376
10°	7365	7263	7299
15°	7276	7160	7178
20°	7158	7032	7039
25°	7023	6886	6866
30°	6858	6715	6652
35°	6686	6535	6447
40°	6509	6330	6215
45°	6322	6130	6012
50°	6116	5951	5766
55°	5895	5719	5533
60°	5672	5459	5293
65°	5421	5213	5001
70°	5141	4881	4692
75°	4713	4482	4370
80°	4193	4021	3924
85°	3668	3538	3464



TEST NUMBER: P332774-830

CATALOG NUMBER: S124DIW-S575D1560U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.2	1.2
10°-20°	242.9	3.3
20°-30°	357.5	4.8
30°-40°	415.6	5.6
40°-50°	415.6	5.6
50°-60°	363.5	4.9
60°-70°	270.0	3.6
70°-80°	153.4	2.1
80°-90°	49.8	0.7
90°-100°	121.2	1.6
100°-110°	359.1	4.8
110°-120°	609.4	8.2
120°-130°	803.6	10.8
130°-140°	902.4	12.1
140°-150°	886.8	11.9
150°-160°	745.9	10.0
160°-170°	496.2	6.7
170°-180°	173.8	2.3
0°-30°	686.6	9.2
0°-40°	1102.1	14.8
0°-60°	1881.3	25.2
0°-90°	2354.4	31.6
90°-120°	1089.7	14.6
90°-150°	3682.5	49.4
90°-180°	5098.0	68.4
0°-180°	7452.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	915	915	915	915	915	
5°	915	911	904	911	910	87
15°	871	867	857	861	859	245
25°	788	783	773	774	771	363
35°	678	673	663	658	654	424
45°	554	548	537	529	527	427
55°	419	416	406	398	393	375
65°	284	280	273	266	262	281
75°	151	147	144	141	140	161
85°	40	40	38	38	37	44
90°	4	20	31	40	43	8
95°	85	98	108	112	112	95
105°	331	333	338	342	347	351
115°	620	619	617	615	614	611
125°	902	902	901	898	895	804
135°	1164	1172	1172	1170	1165	900
145°	1414	1420	1421	1420	1416	885
155°	1620	1620	1619	1624	1619	745
165°	1764	1760	1757	1764	1759	497
175°	1835	1828	1826	1835	1826	174
180°	1838	1838	1838	1838	1838	



TEST NUMBER: P332774-830

CATALOG NUMBER: S124DIW-S575D1560U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	915.3	915.3	915.3	915.3	915.3	915.3	915.3	915.3	915.3	915.3	915.3
2.5°	917.7	917.3	916.9	916.5	916.2	915.2	913.8	912.4	910.9	909.5	910.8
5°	914.6	914.0	913.3	912.7	912.0	910.8	909.0	907.2	905.4	903.6	905.4
7.5°	906.1	905.4	904.8	904.2	903.5	902.2	900.2	898.2	896.2	894.2	895.7
10°	898.4	897.9	897.2	896.5	895.9	894.5	892.4	890.2	888.2	886.0	887.3
12.5°	888.5	887.9	887.2	886.6	885.9	884.5	882.2	880.0	877.7	875.4	876.8
15°	870.6	870.0	869.3	868.6	868.0	866.5	864.0	861.6	859.1	856.7	857.6
17.5°	849.0	848.2	847.4	846.6	845.7	844.2	841.9	839.6	837.3	835.0	835.6
20°	833.2	832.4	831.6	830.8	829.9	828.3	825.9	823.4	821.0	818.5	819.0
22.5°	816.1	815.1	814.1	812.9	811.9	810.1	807.7	805.2	802.8	800.3	801.3
25°	788.4	787.3	786.2	785.0	783.9	782.2	779.9	777.6	775.3	773.1	773.3
27.5°	756.8	755.6	754.4	753.3	752.1	750.5	748.3	746.2	744.0	742.0	741.6
30°	735.7	734.3	733.0	731.7	730.5	728.7	726.6	724.4	722.4	720.3	719.6
32.5°	713.3	712.2	711.0	709.8	708.7	706.9	704.7	702.5	700.2	698.0	697.2
35°	678.4	677.3	676.2	675.0	673.9	672.1	669.9	667.6	665.3	663.1	661.9
37.5°	641.6	640.6	639.5	638.5	637.4	635.7	633.3	630.8	628.4	625.9	624.7
40°	617.6	616.2	614.9	613.7	612.4	610.5	608.0	605.6	603.1	600.7	599.1
42.5°	591.7	591.0	590.2	589.4	588.6	586.8	584.2	581.5	578.7	576.1	574.2
45°	553.7	552.6	551.5	550.4	549.2	547.3	544.7	542.1	539.5	536.9	535.1
47.5°	514.0	513.2	512.5	511.6	510.9	509.3	506.9	504.4	502.0	499.6	497.6
50°	487.0	486.4	485.7	485.0	484.4	483.0	480.7	478.3	476.1	473.8	471.6
52.5°	460.6	459.9	459.0	458.3	457.5	455.9	453.5	451.1	448.7	446.2	444.2
55°	418.8	418.3	417.8	417.4	416.9	415.5	413.2	410.9	408.6	406.3	404.4
57.5°	378.9	378.3	377.8	377.2	376.6	375.3	373.1	370.8	368.5	366.3	364.4
60°	351.3	350.5	349.7	348.8	348.1	346.6	344.5	342.3	340.3	338.1	336.7
62.5°	324.3	323.7	322.9	322.3	321.6	320.1	317.9	315.7	313.4	311.1	309.8
65°	283.8	283.0	282.2	281.4	280.6	279.4	277.8	276.1	274.5	272.9	271.2
67.5°	243.1	242.3	241.6	240.8	240.1	238.9	237.3	235.8	234.2	232.6	231.1
70°	217.8	216.7	215.6	214.4	213.3	212.1	210.8	209.4	208.1	206.8	205.6
72.5°	190.9	189.7	188.6	187.4	186.2	185.2	184.2	183.1	182.1	181.0	179.9
75°	151.1	150.2	149.5	148.6	147.8	147.0	146.2	145.3	144.6	143.7	143.1
77.5°	113.1	112.7	112.4	112.1	111.7	111.1	110.4	109.7	109.0	108.3	108.0
80°	90.2	89.7	89.3	88.8	88.2	87.8	87.6	87.2	86.9	86.5	86.2
82.5°	68.0	67.7	67.5	67.2	67.0	66.8	66.8	66.7	66.6	66.6	66.4
85°	39.6	39.6	39.6	39.6	39.6	39.4	39.1	38.8	38.5	38.2	38.2
87.5°	16.1	16.7	17.2	17.8	18.4	18.9	19.2	19.6	20.0	20.4	20.7
90°	4.2	7.7	11.2	14.7	18.2	21.2	23.7	26.2	28.7	31.3	33.2
92.5°	30.4	34.4	38.4	42.3	46.4	49.2	51.0	52.8	54.5	56.3	57.4
95°	85.3	88.1	91.0	93.8	96.6	99.2	101.4	103.6	105.8	108.0	109.0
97.5°	148.9	151.2	153.4	155.8	158.1	160.5	163.1	165.6	168.2	170.8	171.9
100°	199.0	200.2	201.5	202.7	204.1	206.0	209.0	211.8	214.6	217.4	218.1
102.5°	251.3	251.8	252.3	252.8	253.3	254.9	257.4	260.0	262.6	265.2	266.1
105°	331.1	331.5	331.8	332.1	332.4	333.2	334.4	335.7	337.0	338.3	339.2
107.5°	415.0	415.4	415.8	416.1	416.5	416.8	417.0	417.2	417.4	417.5	418.4
110°	471.8	472.5	473.1	473.7	474.4	474.6	474.2	473.9	473.5	473.3	472.6



TEST NUMBER: P332774-830

CATALOG NUMBER: S124DIW-S575D1560U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	530.9	531.1	531.2	531.3	531.5	531.2	530.7	530.1	529.5	529.0	528.9
115°	619.6	619.6	619.6	619.6	619.6	619.3	618.7	618.0	617.5	616.8	616.5
117.5°	703.2	703.4	703.7	704.0	704.3	704.2	703.7	703.2	702.8	702.4	701.3
120°	758.9	760.2	761.5	762.7	763.9	764.1	763.2	762.2	761.3	760.3	758.7
122.5°	816.9	817.4	817.9	818.4	818.9	819.0	818.5	818.0	817.7	817.2	816.1
125°	902.5	902.5	902.5	902.5	902.5	902.3	902.0	901.6	901.4	901.1	900.4
127.5°	980.1	981.0	981.9	982.9	983.8	984.1	983.5	983.1	982.6	982.0	981.4
130°	1034.6	1035.6	1036.5	1037.5	1038.4	1038.9	1038.9	1038.9	1038.9	1038.9	1038.3
132.5°	1090.3	1091.1	1091.7	1092.4	1093.2	1093.3	1093.1	1092.9	1092.6	1092.3	1091.7
135°	1163.9	1165.8	1167.7	1169.7	1171.6	1172.5	1172.5	1172.5	1172.5	1172.5	1171.9
137.5°	1244.2	1245.0	1245.9	1246.8	1247.6	1248.4	1248.9	1249.3	1249.9	1250.4	1249.5
140°	1297.6	1298.2	1298.8	1299.5	1300.0	1300.4	1300.4	1300.4	1300.4	1300.4	1300.0
142.5°	1346.4	1347.1	1347.7	1348.3	1349.0	1349.2	1348.9	1348.7	1348.4	1348.1	1348.1
145°	1414.1	1415.3	1416.6	1417.9	1419.2	1419.9	1420.2	1420.6	1420.9	1421.2	1420.9
147.5°	1481.2	1482.7	1484.2	1485.7	1487.2	1487.9	1487.6	1487.3	1487.1	1486.9	1486.6
150°	1522.1	1523.3	1524.7	1525.9	1527.2	1527.8	1527.8	1527.8	1527.8	1527.8	1527.8
152.5°	1560.8	1561.5	1562.3	1563.0	1563.8	1564.3	1564.5	1564.8	1565.1	1565.3	1566.0
155°	1620.1	1620.1	1620.1	1620.1	1620.1	1620.0	1619.7	1619.4	1619.1	1618.7	1620.0
157.5°	1670.2	1669.6	1669.1	1668.5	1667.9	1667.6	1667.5	1667.5	1667.5	1667.4	1668.3
160°	1699.8	1699.4	1699.1	1698.8	1698.5	1698.2	1697.9	1697.5	1697.2	1697.0	1697.9
162.5°	1727.0	1726.3	1725.4	1724.6	1723.7	1723.2	1722.9	1722.6	1722.2	1721.9	1723.6
165°	1763.7	1762.7	1761.8	1760.9	1759.9	1759.2	1758.5	1757.8	1757.3	1756.6	1758.5
167.5°	1791.9	1790.5	1789.2	1787.9	1786.6	1785.9	1786.0	1786.0	1786.1	1786.2	1788.1
170°	1807.8	1806.2	1804.6	1803.0	1801.5	1800.8	1801.1	1801.5	1801.8	1802.0	1803.9
172.5°	1819.1	1817.8	1816.5	1815.1	1813.8	1813.2	1813.3	1813.4	1813.4	1813.5	1815.6
175°	1834.8	1833.2	1831.6	1830.0	1828.4	1827.5	1827.2	1826.8	1826.6	1826.3	1828.4
177.5°	1839.8	1838.6	1837.4	1836.1	1834.8	1834.2	1834.2	1834.2	1834.2	1834.2	1836.0
180°	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6



TEST NUMBER: P332774-830

CATALOG NUMBER: S124DIW-S575D1560U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	915.3	915.3	915.3	915.3	915.3	915.3	915.3	915.3
2.5°	912.1	913.4	914.7	915.3	915.1	915.0	914.9	914.7
5°	907.2	909.0	910.8	911.5	911.2	910.9	910.5	910.2
7.5°	897.1	898.5	899.9	900.6	900.4	900.2	900.0	899.8
10°	888.6	889.9	891.3	891.7	891.4	891.1	890.7	890.4
12.5°	878.4	879.8	881.2	881.7	881.2	880.7	880.3	879.9
15°	858.7	859.6	860.5	860.8	860.4	859.9	859.3	858.8
17.5°	836.2	836.8	837.4	837.5	837.3	836.9	836.6	836.3
20°	819.5	820.0	820.5	820.6	820.2	819.9	819.6	819.3
22.5°	802.1	803.0	803.9	804.0	803.4	802.9	802.3	801.6
25°	773.4	773.5	773.7	773.5	772.8	772.1	771.5	770.8
27.5°	741.2	740.7	740.4	739.8	739.0	738.2	737.4	736.5
30°	719.0	718.3	717.7	716.9	716.0	715.3	714.4	713.6
32.5°	696.4	695.6	694.8	694.0	693.2	692.4	691.5	690.8
35°	660.7	659.6	658.5	657.5	656.7	655.8	655.1	654.2
37.5°	623.5	622.2	620.9	619.8	618.8	617.6	616.6	615.5
40°	597.5	595.8	594.2	593.0	592.1	591.4	590.5	589.7
42.5°	572.3	570.3	568.4	567.2	566.8	566.2	565.6	565.1
45°	533.3	531.5	529.7	528.6	528.1	527.6	527.1	526.6
47.5°	495.6	493.5	491.5	489.9	488.7	487.4	486.2	484.9
50°	469.2	466.9	464.7	463.1	462.0	461.1	460.1	459.1
52.5°	442.1	440.2	438.2	436.5	435.3	434.0	432.8	431.6
55°	402.5	400.5	398.5	397.0	396.1	395.1	394.1	393.1
57.5°	362.6	360.7	358.8	357.4	356.5	355.5	354.6	353.6
60°	335.2	333.8	332.2	331.1	330.3	329.5	328.7	327.8
62.5°	308.5	307.1	305.8	304.7	303.9	303.1	302.3	301.4
65°	269.6	268.0	266.4	265.1	264.3	263.4	262.7	261.8
67.5°	229.5	228.0	226.4	225.5	225.3	225.1	224.8	224.6
70°	204.2	202.9	201.6	200.8	200.2	199.7	199.3	198.8
72.5°	178.9	177.9	176.8	176.1	175.6	175.1	174.7	174.1
75°	142.4	141.8	141.2	140.7	140.5	140.4	140.3	140.1
77.5°	107.8	107.6	107.4	107.2	106.7	106.3	105.8	105.5
80°	85.9	85.6	85.2	85.0	84.8	84.6	84.5	84.4
82.5°	66.2	66.0	65.8	65.6	65.5	65.3	65.1	64.9
85°	38.2	38.2	38.2	38.1	37.9	37.7	37.6	37.4
87.5°	21.1	21.5	21.9	22.1	22.2	22.3	22.5	22.6
90°	35.1	36.9	38.8	40.2	40.7	41.4	42.0	42.6
92.5°	58.5	59.7	60.8	61.5	61.9	62.3	62.7	63.1
95°	109.9	110.8	111.8	112.3	112.3	112.3	112.3	112.3
97.5°	173.1	174.3	175.4	176.0	176.0	176.0	176.0	176.0
100°	218.7	219.3	220.0	220.3	220.3	220.3	220.3	220.3
102.5°	266.9	267.9	268.7	269.3	269.6	269.8	270.0	270.3
105°	340.2	341.1	342.0	343.0	343.9	344.9	345.8	346.8
107.5°	419.3	420.2	421.1	421.5	421.4	421.4	421.3	421.2
110°	472.0	471.4	470.7	470.9	471.8	472.8	473.7	474.7



TEST NUMBER: P332774-830

CATALOG NUMBER: S124DIW-S575D1560U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	528.7	528.6	528.5	528.5	528.7	528.9	529.0	529.2
115°	616.1	615.9	615.6	615.2	614.9	614.6	614.3	614.0
117.5°	700.2	699.2	698.0	697.2	696.5	696.0	695.3	694.7
120°	757.1	755.6	754.0	753.6	754.2	754.8	755.4	756.1
122.5°	815.0	814.0	812.9	811.8	810.7	809.5	808.4	807.3
125°	899.8	899.2	898.5	897.9	897.2	896.6	896.0	895.3
127.5°	980.8	980.1	979.5	978.9	978.5	978.0	977.4	976.9
130°	1037.6	1037.0	1036.3	1035.4	1034.2	1032.9	1031.6	1030.4
132.5°	1091.1	1090.4	1089.8	1089.2	1088.7	1088.3	1087.7	1087.2
135°	1171.2	1170.6	1170.0	1169.1	1168.2	1167.2	1166.3	1165.4
137.5°	1248.8	1247.9	1247.1	1246.8	1247.0	1247.2	1247.4	1247.5
140°	1299.8	1299.5	1299.1	1298.8	1298.5	1298.2	1297.9	1297.6
142.5°	1348.0	1347.9	1347.9	1347.8	1347.7	1347.7	1347.6	1347.6
145°	1420.6	1420.2	1419.9	1419.3	1418.3	1417.4	1416.5	1415.5
147.5°	1486.4	1486.1	1485.8	1485.5	1485.3	1485.0	1484.6	1484.3
150°	1527.8	1527.8	1527.8	1527.7	1527.3	1527.0	1526.7	1526.4
152.5°	1566.8	1567.5	1568.3	1568.3	1567.4	1566.7	1565.8	1565.0
155°	1621.3	1622.5	1623.8	1623.8	1622.5	1621.3	1620.0	1618.7
157.5°	1669.2	1670.2	1671.1	1671.0	1670.0	1669.0	1667.8	1666.8
160°	1698.8	1699.8	1700.7	1700.3	1698.8	1697.2	1695.6	1694.0
162.5°	1725.3	1727.0	1728.7	1728.8	1727.2	1725.7	1724.1	1722.5
165°	1760.4	1762.3	1764.2	1764.5	1763.2	1762.0	1760.7	1759.4
167.5°	1790.0	1791.9	1793.8	1793.8	1791.8	1789.8	1787.8	1785.8
170°	1805.9	1807.8	1809.7	1809.5	1807.3	1805.1	1802.9	1800.6
172.5°	1817.8	1819.9	1822.0	1822.0	1819.8	1817.6	1815.3	1813.2
175°	1830.7	1832.9	1835.1	1835.1	1832.9	1830.7	1828.4	1826.3
177.5°	1837.8	1839.5	1841.3	1841.2	1839.1	1837.1	1835.1	1833.1
180°	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6	1837.6

(END OF REPORT)