

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332148-940

Luminaire Tested: **S123DIW-S560D1535U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332148-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S560D1535U940-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1535 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7544.0 lumens
Efficiency: N/A
Efficacy: 124.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 60.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332148-940

CATALOG NUMBER: S123DIW-S560D1535U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332148-940

CATALOG NUMBER: S123DIW-S560D1535U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	52	52	52	35	35	35	27
1	93	88	85	81	83	79	76	73	62	60	58	46	45	43	31	30	30	23
2	84	77	71	66	75	69	64	60	54	51	48	40	38	36	27	26	25	19
3	77	68	61	55	68	61	55	50	48	44	40	36	33	30	24	23	21	16
4	70	60	52	46	62	54	47	42	42	38	34	32	29	26	22	20	18	14
5	64	53	45	40	57	48	41	36	38	33	29	28	25	22	19	17	16	12
6	59	48	40	34	53	43	36	31	34	29	25	25	22	20	18	16	14	11
7	55	43	35	30	49	39	32	27	31	26	22	23	20	17	16	14	12	9
8	51	39	31	26	45	35	28	24	28	23	20	21	18	15	15	13	11	8
9	47	35	28	23	42	32	25	21	25	21	17	19	16	14	14	11	10	8
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	13	10	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8551	8551	8551
5°	8590	8473	8532
10°	8534	8400	8451
15°	8433	8304	8320
20°	8317	8168	8176
25°	8162	8007	7991
30°	7988	7828	7768
35°	7808	7638	7540
40°	7620	7429	7314
45°	7415	7237	7060
50°	7206	7000	6805
55°	6934	6756	6549
60°	6661	6469	6265
65°	6421	6159	5968
70°	6061	5803	5545
75°	5540	5340	5115
80°	4996	4785	4742
85°	4384	4224	4051



TEST NUMBER: P332148-940

CATALOG NUMBER: S123DIW-S560D1535U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.8	1.0
10°-20°	211.3	2.8
20°-30°	312.1	4.1
30°-40°	364.6	4.8
40°-50°	366.5	4.9
50°-60°	322.0	4.3
60°-70°	239.9	3.2
70°-80°	136.7	1.8
80°-90°	44.2	0.6
90°-100°	65.2	0.9
100°-110°	310.9	4.1
110°-120°	746.8	9.9
120°-130°	951.0	12.6
130°-140°	1016.1	13.5
140°-150°	950.2	12.6
150°-160°	766.5	10.2
160°-170°	494.7	6.6
170°-180°	170.5	2.3
0°-30°	598.2	7.9
0°-40°	962.8	12.8
0°-60°	1651.3	21.9
0°-90°	2072.1	27.5
90°-120°	1123.0	14.9
90°-150°	4040.3	53.6
90°-180°	5472.0	72.5
0°-180°	7544.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	794	794	794	794	794	
5°	795	791	784	791	790	75
15°	757	754	745	750	747	213
25°	687	683	674	675	673	316
35°	594	590	581	577	574	372
45°	487	484	475	467	464	376
55°	370	368	360	353	349	331
65°	252	248	242	236	234	249
75°	133	131	128	125	123	142
85°	36	34	34	33	33	39
90°	1	15	32	37	40	6
95°	81	30	41	50	51	101
105°	397	404	292	69	59	421
115°	745	753	765	778	784	735
125°	1050	1061	1066	1069	1072	938
135°	1308	1316	1321	1325	1321	1006
145°	1509	1518	1521	1524	1524	944
155°	1662	1660	1661	1667	1660	766
165°	1753	1749	1748	1757	1749	495
175°	1794	1788	1789	1797	1788	171
180°	1794	1794	1794	1794	1794	



TEST NUMBER: P332148-940

CATALOG NUMBER: S123DIW-S560D1535U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	794.4	794.4	794.4	794.4	794.4	794.4	794.4	794.4	794.4	794.4	794.4
2.5°	797.1	796.7	796.2	795.7	795.2	794.2	792.9	791.6	790.3	789.0	790.1
5°	795.0	794.3	793.5	792.8	792.0	790.9	789.2	787.5	785.9	784.2	785.7
7.5°	787.3	786.6	785.8	785.1	784.3	783.0	781.3	779.5	777.8	776.1	777.5
10°	780.8	780.0	779.3	778.5	777.8	776.3	774.4	772.4	770.4	768.5	769.8
12.5°	772.0	771.3	770.7	770.1	769.5	768.2	766.3	764.5	762.7	760.8	761.8
15°	756.8	756.3	755.6	755.0	754.4	753.1	751.2	749.2	747.2	745.2	746.5
17.5°	739.2	738.4	737.6	736.8	736.0	734.7	732.7	730.8	728.8	726.7	727.6
20°	726.1	725.2	724.2	723.4	722.5	721.0	719.1	717.1	715.1	713.1	713.7
22.5°	711.3	710.4	709.5	708.6	707.7	706.2	704.3	702.3	700.3	698.4	698.8
25°	687.2	686.3	685.4	684.5	683.5	682.1	680.1	678.1	676.2	674.2	674.3
27.5°	661.4	660.5	659.6	658.7	657.8	656.3	654.2	652.1	650.0	647.8	647.9
30°	642.7	642.0	641.2	640.5	639.7	638.3	636.1	634.0	632.0	629.8	629.8
32.5°	624.2	623.2	622.1	621.2	620.2	618.8	617.2	615.5	613.9	612.3	611.4
35°	594.2	593.3	592.5	591.6	590.7	589.2	587.2	585.2	583.3	581.3	580.4
37.5°	563.7	562.5	561.3	560.2	559.0	557.5	555.4	553.5	551.4	549.5	548.4
40°	542.3	541.4	540.6	539.7	538.7	537.2	535.0	533.0	530.8	528.7	527.4
42.5°	521.0	520.0	519.0	517.9	516.9	515.3	513.2	511.1	509.0	506.8	505.6
45°	487.1	486.4	485.8	485.2	484.6	483.3	481.3	479.4	477.4	475.4	473.6
47.5°	453.3	452.4	451.6	450.7	449.8	448.4	446.6	444.7	442.8	441.0	439.2
50°	430.3	429.5	428.8	428.0	427.3	426.0	423.9	422.0	420.0	418.0	416.3
52.5°	406.3	405.7	405.3	404.7	404.2	402.9	400.8	398.8	396.6	394.6	393.2
55°	369.5	369.3	369.3	369.1	368.9	367.8	365.9	363.9	361.9	360.0	358.3
57.5°	334.6	334.0	333.5	333.1	332.5	331.4	329.8	328.3	326.7	325.1	323.7
60°	309.4	309.2	309.2	309.0	308.8	307.8	306.0	304.2	302.4	300.5	299.2
62.5°	287.0	286.6	286.2	285.9	285.4	284.4	282.5	280.7	278.8	277.1	275.7
65°	252.1	251.3	250.6	249.8	249.1	247.9	246.4	244.9	243.3	241.8	240.6
67.5°	215.0	214.4	213.7	213.0	212.3	211.4	210.3	209.1	207.9	206.9	205.8
70°	192.6	191.7	190.8	189.9	189.0	188.1	187.2	186.3	185.3	184.4	183.3
72.5°	169.2	168.4	167.8	167.1	166.5	165.6	164.6	163.5	162.5	161.5	160.5
75°	133.2	132.6	132.0	131.3	130.8	130.3	129.7	129.3	128.9	128.4	127.7
77.5°	101.4	101.0	100.7	100.4	100.0	99.6	99.1	98.5	97.9	97.4	96.9
80°	80.6	80.2	79.7	79.3	78.7	78.4	78.1	77.8	77.5	77.2	77.0
82.5°	60.4	60.3	60.2	60.1	60.0	59.9	59.9	59.8	59.7	59.7	59.4
85°	35.5	35.2	35.0	34.6	34.3	34.2	34.2	34.2	34.2	34.2	33.9
87.5°	14.4	14.7	14.9	15.2	15.4	15.8	16.5	17.1	17.7	18.5	18.5
90°	1.3	4.3	7.2	10.3	13.2	16.6	20.4	24.3	28.2	32.0	33.2
92.5°	24.8	24.0	23.1	22.3	21.5	22.5	25.4	28.4	31.2	34.2	36.0
95°	81.3	69.2	57.1	44.9	32.7	28.3	31.6	34.8	38.1	41.3	43.4
97.5°	163.5	158.0	152.6	147.0	141.6	128.2	106.9	85.6	64.3	42.9	45.3
100°	225.3	231.2	237.1	243.1	249.0	228.8	182.6	136.4	90.2	44.0	46.4
102.5°	295.7	300.0	304.3	308.4	312.7	289.6	239.2	188.7	138.2	87.7	80.3
105°	397.3	400.6	403.8	407.1	410.3	398.6	371.9	345.3	318.6	291.9	239.5
107.5°	504.4	507.0	509.6	512.3	514.9	518.3	522.5	526.7	530.9	535.1	496.7
110°	575.9	578.3	580.6	583.0	585.4	588.2	591.5	594.7	598.0	601.2	591.5



TEST NUMBER: P332148-940

CATALOG NUMBER: S123DIW-S560D1535U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	644.2	646.3	648.5	650.6	652.6	655.4	658.6	661.9	665.1	668.4	668.6
115°	745.2	747.0	748.8	750.6	752.3	754.6	757.2	759.8	762.5	765.2	768.1
117.5°	843.0	845.3	847.4	849.6	851.9	853.6	855.0	856.3	857.6	859.1	861.4
120°	903.8	906.5	909.2	911.9	914.5	916.3	917.1	918.0	918.9	919.8	922.2
122.5°	965.7	967.9	970.1	972.2	974.5	976.2	977.2	978.4	979.5	980.6	982.3
125°	1050.4	1052.8	1055.3	1057.6	1060.0	1061.8	1062.9	1064.1	1065.3	1066.5	1067.1
127.5°	1132.6	1135.0	1137.4	1139.7	1142.1	1144.0	1145.4	1146.8	1148.3	1149.7	1150.6
130°	1183.7	1186.2	1188.6	1190.9	1193.3	1195.1	1196.2	1197.4	1198.6	1199.8	1201.0
132.5°	1232.9	1235.2	1237.6	1239.9	1242.3	1244.0	1244.9	1245.9	1246.8	1247.8	1248.9
135°	1307.8	1309.6	1311.3	1313.1	1314.9	1316.3	1317.5	1318.8	1319.9	1321.1	1322.0
137.5°	1371.7	1374.0	1376.3	1378.5	1380.7	1382.2	1382.9	1383.5	1384.2	1384.8	1386.3
140°	1414.4	1416.2	1418.0	1419.8	1421.6	1422.8	1423.7	1424.6	1425.5	1426.4	1427.6
142.5°	1453.8	1455.6	1457.4	1459.2	1461.0	1462.3	1463.2	1464.1	1465.0	1465.9	1466.8
145°	1509.0	1511.1	1513.2	1515.3	1517.3	1518.7	1519.3	1519.8	1520.5	1521.1	1521.6
147.5°	1561.0	1562.5	1563.8	1565.1	1566.5	1567.4	1568.1	1568.7	1569.2	1569.9	1570.5
150°	1593.0	1593.9	1594.8	1595.7	1596.6	1597.3	1597.9	1598.6	1599.1	1599.7	1600.3
152.5°	1621.8	1622.3	1622.6	1623.1	1623.5	1623.9	1624.3	1624.6	1625.0	1625.3	1626.4
155°	1662.3	1661.8	1661.2	1660.6	1660.0	1659.8	1660.2	1660.5	1660.7	1661.0	1662.5
157.5°	1693.8	1693.8	1693.7	1693.6	1693.6	1693.4	1693.1	1692.8	1692.6	1692.2	1694.0
160°	1713.1	1712.7	1712.4	1712.2	1711.8	1711.5	1711.3	1710.9	1710.7	1710.4	1712.2
162.5°	1731.2	1730.4	1729.7	1728.8	1728.0	1727.5	1727.2	1727.0	1726.6	1726.4	1728.4
165°	1753.0	1752.1	1751.2	1750.3	1749.4	1748.9	1748.6	1748.3	1748.0	1747.7	1750.1
167.5°	1770.0	1768.9	1767.7	1766.6	1765.3	1764.8	1764.8	1764.8	1764.8	1764.8	1767.1
170°	1779.7	1778.5	1777.3	1776.1	1775.0	1774.3	1774.3	1774.3	1774.3	1774.3	1776.7
172.5°	1786.1	1784.7	1783.2	1781.8	1780.4	1779.8	1780.0	1780.3	1780.5	1780.7	1783.2
175°	1794.3	1792.9	1791.4	1789.9	1788.4	1787.8	1788.1	1788.4	1788.7	1789.0	1791.1
177.5°	1796.4	1795.3	1794.1	1793.0	1791.7	1791.3	1791.5	1791.7	1792.0	1792.2	1794.1
180°	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3



TEST NUMBER: P332148-940

CATALOG NUMBER: S123DIW-S560D1535U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	794.4	794.4	794.4	794.4	794.4	794.4	794.4	794.4
2.5°	791.4	792.6	793.8	794.3	794.2	794.1	794.0	793.9
5°	787.2	788.7	790.2	790.9	790.5	790.2	790.0	789.6
7.5°	778.8	780.2	781.6	782.1	781.9	781.8	781.6	781.4
10°	771.2	772.6	773.9	774.5	774.2	773.8	773.6	773.2
12.5°	762.8	763.8	764.8	765.2	765.0	764.8	764.6	764.5
15°	747.7	748.9	750.1	750.2	749.3	748.4	747.5	746.6
17.5°	728.5	729.3	730.2	730.4	730.1	729.8	729.4	729.1
20°	714.3	715.0	715.5	715.6	715.2	714.7	714.3	713.8
22.5°	699.4	699.8	700.3	700.3	699.7	699.1	698.6	697.9
25°	674.5	674.7	674.8	674.7	674.2	673.8	673.2	672.8
27.5°	648.1	648.2	648.3	648.1	647.5	646.9	646.3	645.8
30°	629.8	629.8	629.8	629.3	628.2	627.1	626.1	625.0
32.5°	610.6	609.8	608.9	608.1	607.6	607.1	606.5	605.9
35°	579.4	578.5	577.7	576.8	576.0	575.3	574.5	573.8
37.5°	547.2	546.2	545.1	544.3	543.9	543.3	542.9	542.3
40°	526.3	525.0	523.9	522.9	522.3	521.7	521.1	520.5
42.5°	504.4	503.2	501.9	501.1	500.4	499.9	499.3	498.6
45°	471.8	469.9	468.1	466.8	466.1	465.3	464.6	463.8
47.5°	437.4	435.6	433.8	432.6	431.9	431.2	430.6	429.9
50°	414.7	413.0	411.3	410.1	409.1	408.2	407.3	406.4
52.5°	391.7	390.3	388.9	387.6	386.7	385.8	385.0	384.1
55°	356.6	355.0	353.3	352.0	351.3	350.5	349.8	349.0
57.5°	322.2	320.7	319.2	318.0	317.1	316.3	315.4	314.5
60°	297.8	296.5	295.1	294.0	293.3	292.5	291.8	291.0
62.5°	274.3	273.0	271.6	270.6	270.1	269.7	269.1	268.6
65°	239.3	238.2	236.9	236.1	235.7	235.2	234.8	234.3
67.5°	204.7	203.7	202.6	201.7	201.1	200.5	199.8	199.2
70°	182.3	181.3	180.2	179.2	178.5	177.7	177.0	176.2
72.5°	159.6	158.6	157.7	157.0	156.7	156.2	155.9	155.4
75°	126.9	126.2	125.4	124.8	124.3	123.9	123.4	123.0
77.5°	96.4	95.9	95.3	95.1	95.1	95.1	95.1	95.1
80°	76.9	76.7	76.6	76.5	76.5	76.5	76.5	76.5
82.5°	59.1	58.9	58.6	58.4	58.3	58.1	58.1	58.0
85°	33.5	33.3	32.9	32.8	32.8	32.8	32.8	32.8
87.5°	18.6	18.7	18.9	19.0	19.1	19.3	19.4	19.4
90°	34.3	35.6	36.7	37.6	38.3	38.8	39.4	39.9
92.5°	37.9	39.9	41.7	42.8	43.2	43.5	43.9	44.2
95°	45.5	47.5	49.6	50.6	50.6	50.6	50.6	50.6
97.5°	47.7	50.0	52.4	53.8	54.0	54.3	54.7	54.9
100°	48.7	51.1	53.5	54.8	55.1	55.4	55.7	56.0
102.5°	73.0	65.7	58.3	54.9	55.5	56.0	56.5	57.1
105°	187.1	134.6	82.2	56.3	56.9	57.5	58.1	58.7
107.5°	458.2	419.7	381.3	342.3	302.8	263.2	223.7	184.2
110°	581.7	571.9	562.1	536.0	493.7	451.3	408.9	366.6



TEST NUMBER: P332148-940

CATALOG NUMBER: S123DIW-S560D1535U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	668.8	669.0	669.1	664.8	655.8	646.8	637.9	628.9
115°	771.2	774.1	777.0	779.1	780.3	781.5	782.7	783.9
117.5°	863.8	866.1	868.5	869.9	870.0	870.3	870.6	870.8
120°	924.6	926.9	929.3	930.5	930.5	930.5	930.5	930.5
122.5°	983.9	985.6	987.3	988.2	988.5	988.6	988.9	989.2
125°	1067.6	1068.3	1068.8	1069.4	1070.1	1070.6	1071.2	1071.8
127.5°	1151.6	1152.5	1153.4	1153.6	1153.1	1152.4	1151.8	1151.3
130°	1202.1	1203.4	1204.5	1204.8	1204.3	1203.6	1203.0	1202.5
132.5°	1250.2	1251.3	1252.5	1252.7	1251.9	1251.1	1250.2	1249.4
135°	1322.9	1323.7	1324.6	1324.6	1323.7	1322.9	1322.0	1321.1
137.5°	1387.7	1389.1	1390.5	1390.9	1390.4	1389.7	1389.1	1388.6
140°	1428.8	1429.9	1431.1	1431.5	1430.8	1430.3	1429.7	1429.1
142.5°	1467.8	1468.7	1469.6	1469.7	1468.9	1468.0	1467.2	1466.4
145°	1522.2	1522.9	1523.4	1523.8	1523.8	1523.8	1523.8	1523.8
147.5°	1571.0	1571.6	1572.3	1571.8	1570.5	1569.1	1567.7	1566.4
150°	1600.9	1601.5	1602.0	1602.0	1601.1	1600.2	1599.3	1598.4
152.5°	1627.5	1628.5	1629.6	1629.4	1628.1	1626.7	1625.3	1624.0
155°	1664.0	1665.4	1667.0	1666.8	1665.0	1663.2	1661.4	1659.7
157.5°	1695.8	1697.5	1699.3	1699.1	1696.7	1694.4	1692.1	1689.8
160°	1714.0	1715.7	1717.4	1717.3	1715.2	1713.2	1711.1	1709.1
162.5°	1730.4	1732.4	1734.4	1734.5	1732.7	1730.8	1729.0	1727.2
165°	1752.4	1754.8	1757.2	1757.3	1755.2	1753.2	1751.1	1749.0
167.5°	1769.5	1771.8	1774.2	1774.2	1771.8	1769.5	1767.1	1764.8
170°	1779.1	1781.5	1783.9	1783.9	1781.5	1779.1	1776.7	1774.3
172.5°	1785.5	1787.9	1790.2	1790.1	1787.5	1784.9	1782.3	1779.7
175°	1793.1	1795.2	1797.3	1797.2	1794.7	1792.4	1790.0	1787.7
177.5°	1796.0	1797.9	1799.8	1799.6	1797.2	1794.8	1792.4	1790.1
180°	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3	1794.3

(END OF REPORT)