

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332782-830

Luminaire Tested: **S124DIW-S795D770U830-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332782-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIW-S795D770U830-4F0-1E-UDD-A1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 795 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5850.9 lumens  
Efficiency: N/A  
Efficacy: 130.0 lumens/watt  
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 45  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332782-830

CATALOG NUMBER: S124DIW-S795D770U830-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P332782-830

CATALOG NUMBER: S124DIW-S795D770U830-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	63	63	63	57
1	100	95	91	88	93	89	86	83	77	74	72	66	64	63	56	55	53	49
2	91	84	77	72	84	78	73	68	68	64	60	58	55	53	49	47	45	41
3	83	74	66	61	77	69	63	57	60	55	51	52	48	45	44	41	39	35
4	76	65	58	52	71	61	54	49	53	48	44	46	42	39	39	36	34	30
5	70	58	50	44	65	55	48	42	48	42	38	42	37	34	36	32	30	27
6	65	53	44	39	60	49	42	37	43	38	33	38	33	30	32	29	26	23
7	60	48	40	34	56	45	38	32	39	34	29	34	30	26	30	26	23	21
8	56	43	35	30	52	41	34	29	36	30	26	32	27	24	27	24	21	19
9	52	40	32	27	48	37	30	26	33	27	23	29	24	21	25	22	19	17
10	48	36	29	24	45	34	28	23	30	25	21	27	22	19	23	20	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	9769	9769	9769	9769
5°	11505	9794	8645	9794
10°	13774	9752	7783	9752
15°	16298	9653	7148	9653
20°	18148	9552	6580	9552
25°	18441	9404	6188	9404
30°	15691	9261	6065	9261
35°	12064	9030	6067	9030
40°	9403	8759	6181	8759
45°	7840	8350	6284	8350
50°	6900	7851	6498	7851
55°	6321	7253	6759	7253
60°	5924	6717	7074	6717
65°	5515	6118	7335	6118
70°	5042	5526	7501	5526
75°	4504	4863	7411	4863
80°	3775	3984	7178	3984
85°	2788	2881	6873	2881



TEST NUMBER: P332782-830

CATALOG NUMBER: S124DIW-S795D770U830-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	117.9	2.0
10°-20°	363.4	6.2
20°-30°	576.2	9.8
30°-40°	641.2	11.0
40°-50°	583.7	10.0
50°-60°	477.0	8.2
60°-70°	340.5	5.8
70°-80°	187.5	3.2
80°-90°	53.9	0.9
90°-100°	59.7	1.0
100°-110°	176.7	3.0
110°-120°	300.0	5.1
120°-130°	395.5	6.8
130°-140°	444.2	7.6
140°-150°	436.5	7.5
150°-160°	367.1	6.3
160°-170°	244.3	4.2
170°-180°	85.5	1.5
0°-30°	1057.5	18.1
0°-40°	1698.7	29.0
0°-60°	2759.4	47.2
0°-90°	3341.4	57.1
90°-120°	536.4	9.2
90°-150°	1812.6	31.0
90°-180°	2510.0	42.9
0°-180°	5850.9	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1210	1210	1210	1210	1210	
5°	1420	1209	1067	1209	1420	144
15°	1950	1155	855	1155	1950	551
25°	2070	1056	695	1056	2070	913
35°	1224	916	616	916	1224	777
45°	687	731	550	731	687	541
55°	449	515	480	515	449	406
65°	289	320	384	320	289	286
75°	144	156	238	156	144	154
85°	30	31	74	31	30	37
90°	21	2	21	2	21	12
95°	55	42	55	42	55	58
105°	171	163	171	163	171	180
115°	302	305	302	305	302	299
125°	441	444	441	444	441	393
135°	574	573	574	573	574	443
145°	697	696	697	696	697	436
155°	797	798	797	798	797	367
165°	866	868	866	868	866	244
175°	899	903	899	903	899	85
180°	904	904	904	904	904	



TEST NUMBER: P332782-830

CATALOG NUMBER: S124DIW-S795D770U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1
2.5°	1287.9	1287.5	1283.5	1282.7	1279.9	1276.3	1275.4	1269.0	1256.2	1250.2	1248.6
5°	1419.7	1429.6	1416.6	1414.1	1412.6	1396.1	1387.5	1377.5	1354.4	1341.0	1330.4
7.5°	1576.9	1578.0	1572.3	1567.7	1555.0	1540.5	1518.9	1495.8	1468.4	1439.7	1418.2
10°	1680.3	1684.3	1677.8	1676.8	1651.2	1635.2	1603.1	1576.0	1544.9	1510.3	1478.8
12.5°	1789.4	1783.8	1780.5	1759.0	1754.3	1725.0	1687.7	1659.8	1611.9	1572.2	1530.1
15°	1950.0	1939.0	1931.9	1902.3	1887.8	1847.2	1807.6	1777.1	1714.4	1654.7	1609.6
17.5°	2044.2	2055.2	2039.0	2026.8	1989.2	1960.8	1920.3	1856.1	1807.1	1733.1	1676.1
20°	2112.4	2113.4	2104.4	2091.9	2062.3	2026.2	1982.1	1911.9	1853.2	1779.5	1701.4
22.5°	2130.8	2131.1	2127.2	2115.5	2093.1	2063.9	2019.4	1960.8	1889.7	1809.6	1731.5
25°	2070.3	2068.3	2072.8	2085.8	2077.3	2068.3	2042.7	1999.1	1933.0	1848.2	1764.0
27.5°	1845.3	1859.2	1884.6	1916.7	1947.6	1971.1	1977.7	1968.8	1927.8	1858.1	1769.9
30°	1683.3	1700.3	1719.4	1751.4	1813.6	1849.3	1888.3	1917.9	1901.4	1845.7	1763.5
32.5°	1505.2	1509.5	1537.8	1574.2	1631.2	1699.7	1761.6	1821.7	1841.6	1812.4	1743.9
35°	1224.1	1231.1	1261.7	1297.8	1367.5	1451.2	1544.5	1627.7	1696.3	1723.9	1688.8
37.5°	998.9	1019.1	1040.7	1079.5	1140.9	1216.2	1313.1	1420.7	1523.1	1591.7	1603.3
40°	892.3	904.8	920.4	949.9	1002.0	1076.3	1159.4	1282.8	1391.6	1489.8	1521.9
42.5°	808.0	815.4	824.9	851.7	891.4	965.2	1041.1	1149.6	1258.9	1376.3	1430.0
45°	686.7	694.3	710.3	725.9	755.9	807.1	877.7	967.0	1076.8	1190.1	1289.3
47.5°	599.2	604.0	613.5	630.1	655.6	689.4	746.9	821.4	923.1	1033.1	1138.9
50°	549.4	553.4	560.9	576.0	595.5	625.6	672.7	742.4	822.1	932.9	1036.6
52.5°	510.1	511.7	517.3	527.4	543.0	568.3	606.9	664.6	738.7	837.4	940.8
55°	449.1	451.2	456.2	463.7	477.2	493.2	522.8	565.9	630.7	716.3	806.1
57.5°	399.0	400.4	404.6	407.6	418.7	431.7	454.5	485.2	534.2	606.9	687.0
60°	366.9	365.9	371.0	373.4	381.0	392.0	409.5	439.1	481.7	540.4	614.1
62.5°	335.6	334.2	338.5	341.8	346.1	355.5	369.9	393.0	427.6	480.6	544.3
65°	288.7	286.7	289.3	293.2	297.3	302.3	312.8	333.4	360.9	399.0	447.6
67.5°	241.6	243.7	244.1	246.1	248.5	255.2	262.5	277.0	296.4	327.0	368.2
70°	213.6	214.1	216.0	216.0	217.5	223.6	229.6	238.1	257.1	285.2	318.8
72.5°	185.5	187.6	186.8	188.4	189.5	193.5	197.9	206.0	222.3	243.1	271.5
75°	144.4	145.9	145.9	146.4	147.9	149.4	152.9	158.9	170.4	186.0	205.6
77.5°	105.3	105.5	106.1	108.0	108.0	110.4	113.0	117.8	123.5	134.1	146.1
80°	81.2	82.2	81.7	82.8	82.8	84.7	85.7	91.7	94.3	101.2	110.7
82.5°	59.6	60.5	60.4	61.8	62.7	63.1	64.5	66.8	69.4	75.6	79.5
85°	30.1	31.1	30.1	31.1	32.6	33.1	34.6	35.1	37.1	38.6	42.1
87.5°	13.0	14.1	14.1	14.4	15.2	15.5	15.6	15.1	16.5	16.7	18.1
90°	21.0	20.6	20.4	20.1	19.7	19.1	18.2	17.2	16.3	15.4	14.1
92.5°	31.1	30.9	30.7	30.5	30.3	30.0	29.4	28.8	28.3	27.7	26.9
95°	55.2	55.2	55.2	55.2	55.2	55.0	54.6	54.1	53.6	53.2	52.1
97.5°	86.6	86.6	86.6	86.6	86.6	86.3	85.8	85.2	84.6	84.1	82.8
100°	108.4	108.4	108.4	108.4	108.4	108.3	107.9	107.6	107.4	107.1	105.7
102.5°	133.1	132.9	132.8	132.7	132.5	132.2	131.9	131.4	131.0	130.5	129.2
105°	170.7	170.2	169.8	169.3	168.8	168.3	167.9	167.4	166.9	166.5	165.9
107.5°	207.4	207.4	207.5	207.5	207.5	207.3	206.8	206.4	205.9	205.6	205.5
110°	233.7	233.2	232.7	232.2	231.8	231.7	232.1	232.3	232.6	232.9	233.1



TEST NUMBER: P332782-830

CATALOG NUMBER: S124DIW-S795D770U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	260.5	260.4	260.3	260.2	260.1	260.1	260.1	260.2	260.3	260.3	260.6
115°	302.2	302.4	302.6	302.7	302.8	302.9	303.1	303.3	303.4	303.6	303.9
117.5°	342.0	342.2	342.5	342.9	343.2	343.6	344.1	344.7	345.2	345.7	345.9
120°	372.1	371.8	371.6	371.3	370.9	371.2	371.9	372.7	373.4	374.3	374.8
122.5°	397.4	397.9	398.4	399.0	399.5	400.1	400.7	401.1	401.7	402.3	402.5
125°	440.7	441.0	441.3	441.7	442.0	442.2	442.6	442.9	443.2	443.5	443.7
127.5°	480.9	481.1	481.4	481.6	481.8	482.1	482.5	482.8	483.1	483.4	483.6
130°	507.2	507.7	508.4	509.1	509.6	510.1	510.4	510.8	511.0	511.3	511.3
132.5°	535.2	535.4	535.6	535.9	536.1	536.4	536.8	537.1	537.3	537.6	537.8
135°	573.6	574.1	574.6	575.0	575.5	575.9	576.2	576.5	576.8	577.1	577.1
137.5°	614.1	614.0	613.9	613.8	613.7	613.9	614.3	614.6	615.0	615.5	615.2
140°	638.7	638.9	638.9	639.1	639.3	639.4	639.6	639.8	639.9	640.1	640.1
142.5°	663.3	663.4	663.4	663.4	663.5	663.5	663.5	663.5	663.5	663.5	663.7
145°	696.7	697.2	697.7	698.1	698.6	698.9	699.1	699.3	699.4	699.6	699.4
147.5°	730.6	730.8	730.9	731.0	731.2	731.3	731.5	731.6	731.7	731.9	732.0
150°	751.3	751.5	751.6	751.8	752.0	752.1	752.1	752.1	752.1	752.1	752.1
152.5°	770.3	770.7	771.2	771.6	771.9	771.9	771.6	771.2	770.8	770.4	770.3
155°	796.8	797.4	798.1	798.6	799.3	799.3	798.6	798.1	797.4	796.8	796.9
157.5°	820.4	821.0	821.5	822.0	822.6	822.6	822.1	821.6	821.1	820.7	820.8
160°	833.9	834.6	835.4	836.2	837.0	837.2	836.7	836.2	835.8	835.3	835.4
162.5°	847.8	848.7	849.4	850.2	850.9	850.9	850.1	849.2	848.4	847.5	847.7
165°	866.0	866.7	867.2	867.9	868.6	868.4	867.4	866.5	865.5	864.6	865.0
167.5°	879.0	880.1	881.0	881.9	882.9	882.9	881.9	881.1	880.1	879.2	879.1
170°	886.4	887.4	888.5	889.6	890.7	890.8	889.9	888.9	888.0	887.0	886.8
172.5°	892.5	893.5	894.7	895.7	896.8	896.8	895.8	894.8	893.7	892.6	892.6
175°	898.9	900.0	901.1	902.2	903.2	903.2	902.2	901.1	900.0	898.9	899.1
177.5°	902.3	903.2	904.3	905.2	906.3	906.3	905.4	904.6	903.7	902.9	902.9
180°	904.5	904.5	904.5	904.5	904.5	904.5	904.5	904.5	904.5	904.5	904.5



TEST NUMBER: P332782-830

CATALOG NUMBER: S124DIW-S795D770U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1
2.5°	1249.0	1243.4	1239.3	1236.1	1227.4	1222.1	1218.1	1212.5	1206.1	1199.3	1190.8
5°	1319.8	1302.8	1290.3	1271.2	1253.2	1238.1	1222.7	1208.6	1191.6	1173.0	1159.4
7.5°	1394.4	1369.0	1336.5	1308.3	1276.7	1249.1	1224.5	1199.2	1172.9	1147.5	1124.1
10°	1441.7	1409.1	1373.0	1330.4	1290.3	1254.7	1221.6	1189.6	1158.5	1127.4	1100.8
12.5°	1492.6	1452.0	1398.6	1348.9	1303.9	1256.3	1216.4	1177.1	1139.6	1106.9	1075.9
15°	1560.9	1502.3	1440.7	1374.0	1314.8	1259.2	1204.6	1155.0	1112.9	1069.7	1039.6
17.5°	1603.0	1530.4	1459.9	1390.3	1318.7	1248.5	1189.6	1132.3	1079.6	1036.7	998.8
20°	1630.7	1558.5	1470.7	1401.1	1315.9	1243.7	1175.5	1111.8	1056.7	1011.1	971.9
22.5°	1654.7	1571.3	1483.6	1391.9	1307.0	1230.5	1155.8	1091.7	1035.5	987.4	949.9
25°	1667.7	1572.0	1476.8	1385.5	1289.3	1198.5	1130.9	1055.7	995.5	944.9	904.8
27.5°	1669.1	1566.8	1459.1	1357.6	1258.3	1173.8	1088.4	1021.2	958.8	905.2	866.7
30°	1664.7	1558.0	1442.2	1332.4	1232.7	1140.9	1066.8	993.5	929.9	876.8	836.6
32.5°	1650.7	1539.5	1420.5	1304.3	1201.0	1111.3	1034.6	965.1	903.1	850.6	808.6
35°	1610.1	1500.3	1373.5	1252.7	1146.9	1056.2	987.0	916.3	854.2	804.6	763.9
37.5°	1546.6	1447.4	1318.4	1193.4	1089.6	998.4	929.9	866.0	809.9	759.5	717.9
40°	1491.3	1404.1	1274.8	1152.9	1040.7	953.9	889.8	831.1	775.5	727.8	688.2
42.5°	1427.6	1351.5	1232.3	1103.2	994.9	907.9	845.3	792.6	740.2	696.2	656.6
45°	1313.8	1263.8	1151.4	1032.2	919.4	837.2	777.5	731.4	687.3	644.1	611.1
47.5°	1183.1	1158.3	1063.8	950.5	843.4	762.3	710.6	668.0	629.3	592.9	563.6
50°	1095.3	1083.3	1001.5	892.3	790.0	713.8	661.7	625.1	592.0	560.0	532.3
52.5°	1008.7	1008.2	934.6	834.5	739.9	666.5	614.7	580.6	552.0	525.8	501.1
55°	876.3	890.2	832.6	743.4	658.6	592.5	545.9	515.3	495.3	473.7	455.2
57.5°	754.6	777.9	730.4	651.8	581.1	520.1	479.6	456.6	435.2	422.2	408.7
60°	675.2	697.3	660.2	594.0	527.4	475.2	436.6	416.0	397.5	388.5	379.0
62.5°	604.6	624.3	596.8	535.5	477.6	427.5	394.9	375.1	362.6	352.8	346.5
65°	503.8	520.3	496.8	452.1	402.6	362.4	335.8	320.3	308.3	304.3	297.3
67.5°	407.3	422.3	409.5	371.6	331.9	301.4	280.7	265.8	258.6	255.1	250.2
70°	349.9	365.0	351.4	318.3	287.8	262.2	242.6	234.1	226.6	225.1	218.0
72.5°	301.3	311.6	298.0	272.2	246.0	224.5	209.3	200.4	196.5	193.8	190.0
75°	226.1	235.1	226.1	206.0	187.5	172.5	159.4	155.9	151.4	149.9	147.4
77.5°	160.0	167.9	160.9	148.4	134.5	122.9	115.9	111.4	110.4	107.7	109.0
80°	122.3	127.3	120.8	112.3	101.2	93.2	88.2	85.7	82.8	81.7	83.7
82.5°	87.8	90.0	86.7	81.0	72.8	67.6	64.2	61.3	60.7	60.9	60.9
85°	45.6	45.1	44.6	39.6	37.1	33.6	31.6	31.1	30.5	31.6	32.6
87.5°	17.8	18.0	17.3	15.5	13.9	12.3	11.6	10.8	11.6	12.3	13.1
90°	12.9	11.7	10.5	9.0	7.3	5.6	3.8	2.1	3.8	5.6	7.3
92.5°	25.9	25.1	24.2	22.8	20.8	18.9	17.0	15.0	17.0	18.9	20.8
95°	51.0	49.9	48.8	47.6	46.2	44.8	43.4	41.9	43.4	44.8	46.2
97.5°	81.5	80.3	79.0	77.8	76.6	75.6	74.5	73.3	74.5	75.6	76.6
100°	104.2	102.8	101.4	100.4	99.8	99.2	98.6	97.9	98.6	99.2	99.8
102.5°	128.0	126.7	125.5	124.7	124.4	124.1	123.9	123.7	123.9	124.1	124.4
105°	165.2	164.7	164.0	163.6	163.4	163.3	163.2	163.0	163.2	163.3	163.4
107.5°	205.4	205.3	205.2	205.0	204.8	204.6	204.4	204.2	204.4	204.6	204.8
110°	233.3	233.4	233.6	233.5	233.2	232.9	232.5	232.2	232.5	232.9	233.2





TEST NUMBER: P332782-830

CATALOG NUMBER: S124DIW-S795D770U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	260.9	261.2	261.5	261.6	261.6	261.5	261.4	261.4	261.4	261.5	261.6
115°	304.3	304.5	304.8	305.0	305.0	305.0	305.0	305.0	305.0	305.0	305.0
117.5°	346.2	346.4	346.6	346.7	346.5	346.4	346.3	346.1	346.3	346.4	346.5
120°	375.2	375.7	376.1	376.1	375.4	374.8	374.2	373.5	374.2	374.8	375.4
122.5°	402.7	402.9	403.1	403.1	402.8	402.6	402.4	402.1	402.4	402.6	402.8
125°	443.8	443.9	444.1	444.2	444.2	444.2	444.2	444.2	444.2	444.2	444.2
127.5°	483.9	484.1	484.4	484.3	483.8	483.3	482.9	482.4	482.9	483.3	483.8
130°	511.3	511.3	511.3	511.1	510.7	510.2	509.7	509.3	509.7	510.2	510.7
132.5°	537.9	538.0	538.2	538.1	537.7	537.3	537.1	536.7	537.1	537.3	537.7
135°	577.1	577.1	577.1	576.6	575.7	574.8	573.8	573.0	573.8	574.8	575.7
137.5°	614.9	614.7	614.4	614.2	613.7	613.2	612.8	612.4	612.8	613.2	613.7
140°	640.1	640.1	640.1	639.9	639.6	639.3	638.9	638.7	638.9	639.3	639.6
142.5°	663.8	663.9	664.1	664.0	663.6	663.4	663.1	662.7	663.1	663.4	663.6
145°	699.3	699.1	698.9	698.5	698.0	697.3	696.6	696.1	696.6	697.3	698.0
147.5°	732.1	732.3	732.4	732.1	731.3	730.6	729.8	729.1	729.8	730.6	731.3
150°	752.1	752.1	752.1	751.7	751.1	750.5	749.8	749.2	749.8	750.5	751.1
152.5°	770.2	770.1	770.0	769.8	769.4	769.0	768.6	768.3	768.6	769.0	769.4
155°	797.1	797.2	797.4	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5
157.5°	820.8	820.8	820.9	821.0	821.2	821.5	821.8	822.1	821.8	821.5	821.2
160°	835.6	835.8	835.8	836.0	836.2	836.3	836.5	836.7	836.5	836.3	836.2
162.5°	847.9	848.0	848.2	848.5	848.9	849.2	849.7	850.1	849.7	849.2	848.9
165°	865.3	865.5	865.9	866.3	866.8	867.2	867.7	868.2	867.7	867.2	866.8
167.5°	879.1	879.1	879.0	879.4	880.1	880.7	881.4	881.9	881.4	880.7	880.1
170°	886.7	886.6	886.4	886.7	887.5	888.3	889.0	889.9	889.0	888.3	887.5
172.5°	892.6	892.5	892.5	892.8	893.4	894.1	894.8	895.4	894.8	894.1	893.4
175°	899.2	899.4	899.6	900.0	900.8	901.5	902.3	903.1	902.3	901.5	900.8
177.5°	902.9	902.9	902.9	903.1	903.8	904.4	905.0	905.6	905.0	904.4	903.8
180°	904.5	904.5	904.5	904.5	904.5	904.5	904.5	904.5	904.5	904.5	904.5



TEST NUMBER: P332782-830

CATALOG NUMBER: S124DIW-S795D770U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1
2.5°	1186.8	1183.3	1178.0	1170.8	1164.8	1158.4	1156.8	1154.3	1159.1	1155.2	1154.0
5°	1147.9	1137.4	1123.9	1108.3	1099.3	1086.3	1083.7	1078.7	1073.7	1073.3	1068.2
7.5°	1106.7	1091.3	1073.6	1057.7	1043.0	1028.8	1019.5	1017.5	1010.1	1005.8	1000.8
10°	1080.2	1061.2	1040.7	1025.6	1008.6	993.5	983.0	977.0	971.9	966.5	961.5
12.5°	1049.0	1028.7	1011.8	995.5	975.2	963.8	946.5	936.1	935.1	935.2	922.2
15°	1012.6	992.5	966.5	943.4	932.4	910.3	900.8	888.7	881.3	873.7	867.7
17.5°	971.0	946.0	925.7	899.2	878.2	860.6	848.1	840.8	829.5	818.9	811.2
20°	944.9	918.3	896.8	868.7	845.6	824.1	813.6	803.5	795.0	786.0	777.5
22.5°	918.4	890.7	864.3	837.1	815.6	792.9	782.7	769.0	760.9	755.9	747.4
25°	876.8	846.7	816.6	790.5	768.5	748.4	734.9	724.3	715.3	711.3	705.8
27.5°	831.4	801.5	772.5	742.9	717.8	703.3	692.5	684.6	679.3	674.0	671.6
30°	802.6	771.5	740.4	712.8	689.8	675.2	665.2	659.7	655.6	653.2	650.6
32.5°	773.3	742.6	709.9	684.8	664.1	651.2	643.6	638.0	636.0	635.1	634.2
35°	726.3	695.3	665.2	642.6	623.1	618.1	611.5	608.6	607.6	611.1	612.6
37.5°	680.9	652.1	624.4	602.6	589.7	582.4	580.1	580.3	583.9	587.0	590.6
40°	651.7	623.6	597.6	578.4	566.5	561.9	560.9	563.5	567.4	571.0	575.0
42.5°	623.2	595.5	571.8	554.0	545.6	541.5	542.1	544.6	550.2	554.5	560.5
45°	579.0	555.9	532.8	518.3	511.3	512.3	512.3	516.8	522.4	528.9	535.4
47.5°	537.3	514.2	495.1	483.0	479.3	478.4	481.3	487.1	495.0	503.1	512.2
50°	509.3	487.2	470.7	459.7	455.6	457.1	461.2	466.7	476.2	486.3	495.8
52.5°	480.8	460.8	445.4	435.2	432.4	435.1	439.1	447.8	456.2	467.0	478.5
55°	436.6	419.5	407.6	400.0	399.0	400.5	405.0	414.5	426.6	440.2	451.2
57.5°	392.6	378.3	367.3	362.1	362.6	364.0	371.5	382.8	395.6	410.0	424.2
60°	363.0	349.9	340.9	336.9	337.3	340.4	349.4	360.0	376.0	390.0	405.0
62.5°	334.9	323.4	314.8	311.2	310.5	317.1	325.7	336.7	352.7	368.3	384.6
65°	289.7	280.7	273.7	271.7	273.2	278.2	289.3	303.8	317.4	333.8	350.9
67.5°	245.6	238.2	233.4	234.3	236.1	243.6	252.8	265.2	280.6	297.7	314.6
70°	217.5	210.6	206.5	207.0	210.0	219.0	227.1	239.6	256.2	273.7	287.8
72.5°	188.7	184.1	180.5	182.6	185.6	191.8	201.8	214.3	228.8	245.2	260.0
75°	144.9	144.9	142.9	144.4	148.9	154.9	162.4	175.4	190.0	203.0	215.1
77.5°	107.4	106.4	107.6	109.5	112.1	119.2	127.8	137.1	148.1	161.1	171.1
80°	82.2	82.8	85.2	88.2	89.3	94.7	103.8	112.3	120.8	131.9	141.4
82.5°	61.7	62.3	63.5	67.4	68.3	74.3	80.1	88.6	96.3	103.8	111.7
85°	33.6	33.6	36.1	37.6	40.1	44.1	47.6	52.6	59.7	64.7	72.2
87.5°	14.6	14.9	16.8	17.8	19.2	21.5	22.5	27.1	28.9	31.1	34.9
90°	9.0	10.5	11.7	12.9	14.1	15.4	16.3	17.2	18.2	19.1	19.7
92.5°	22.8	24.2	25.1	25.9	26.9	27.7	28.3	28.8	29.4	30.0	30.3
95°	47.6	48.8	49.9	51.0	52.1	53.2	53.6	54.1	54.6	55.0	55.2
97.5°	77.8	79.0	80.3	81.5	82.8	84.1	84.6	85.2	85.8	86.3	86.6
100°	100.4	101.4	102.8	104.2	105.7	107.1	107.4	107.6	107.9	108.3	108.4
102.5°	124.7	125.5	126.7	128.0	129.2	130.5	131.0	131.4	131.9	132.2	132.5
105°	163.6	164.0	164.7	165.2	165.9	166.5	166.9	167.4	167.9	168.3	168.8
107.5°	205.0	205.2	205.3	205.4	205.5	205.6	205.9	206.4	206.8	207.3	207.5
110°	233.5	233.6	233.4	233.3	233.1	232.9	232.6	232.3	232.1	231.7	231.8



TEST NUMBER: P332782-830

CATALOG NUMBER: S124DIW-S795D770U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	261.6	261.5	261.2	260.9	260.6	260.3	260.3	260.2	260.1	260.1	260.1
115°	305.0	304.8	304.5	304.3	303.9	303.6	303.4	303.3	303.1	302.9	302.8
117.5°	346.7	346.6	346.4	346.2	345.9	345.7	345.2	344.7	344.1	343.6	343.2
120°	376.1	376.1	375.7	375.2	374.8	374.3	373.4	372.7	371.9	371.2	370.9
122.5°	403.1	403.1	402.9	402.7	402.5	402.3	401.7	401.1	400.7	400.1	399.5
125°	444.2	444.1	443.9	443.8	443.7	443.5	443.2	442.9	442.6	442.2	442.0
127.5°	484.3	484.4	484.1	483.9	483.6	483.4	483.1	482.8	482.5	482.1	481.8
130°	511.1	511.3	511.3	511.3	511.3	511.3	511.0	510.8	510.4	510.1	509.6
132.5°	538.1	538.2	538.0	537.9	537.8	537.6	537.3	537.1	536.8	536.4	536.1
135°	576.6	577.1	577.1	577.1	577.1	577.1	576.8	576.5	576.2	575.9	575.5
137.5°	614.2	614.4	614.7	614.9	615.2	615.5	615.0	614.6	614.3	613.9	613.7
140°	639.9	640.1	640.1	640.1	640.1	640.1	639.9	639.8	639.6	639.4	639.3
142.5°	664.0	664.1	663.9	663.8	663.7	663.5	663.5	663.5	663.5	663.5	663.5
145°	698.5	698.9	699.1	699.3	699.4	699.6	699.4	699.3	699.1	698.9	698.6
147.5°	732.1	732.4	732.3	732.1	732.0	731.9	731.7	731.6	731.5	731.3	731.2
150°	751.7	752.1	752.1	752.1	752.1	752.1	752.1	752.1	752.1	752.1	752.0
152.5°	769.8	770.0	770.1	770.2	770.3	770.4	770.8	771.2	771.6	771.9	771.9
155°	797.5	797.4	797.2	797.1	796.9	796.8	797.4	798.1	798.6	799.3	799.3
157.5°	821.0	820.9	820.8	820.8	820.8	820.7	821.1	821.6	822.1	822.6	822.6
160°	836.0	835.8	835.8	835.6	835.4	835.3	835.8	836.2	836.7	837.2	837.0
162.5°	848.5	848.2	848.0	847.9	847.7	847.5	848.4	849.2	850.1	850.9	850.9
165°	866.3	865.9	865.5	865.3	865.0	864.6	865.5	866.5	867.4	868.4	868.6
167.5°	879.4	879.0	879.1	879.1	879.1	879.2	880.1	881.1	881.9	882.9	882.9
170°	886.7	886.4	886.6	886.7	886.8	887.0	888.0	888.9	889.9	890.8	890.7
172.5°	892.8	892.5	892.5	892.6	892.6	892.6	893.7	894.8	895.8	896.8	896.8
175°	900.0	899.6	899.4	899.2	899.1	898.9	900.0	901.1	902.2	903.2	903.2
177.5°	903.1	902.9	902.9	902.9	902.9	902.9	903.7	904.6	905.4	906.3	906.3
180°	904.5	904.5	904.5	904.5	904.5	904.5	904.5	904.5	904.5	904.5	904.5



TEST NUMBER: P332782-830

CATALOG NUMBER: S124DIW-S795D770U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1
2.5°	1153.1	1152.4	1149.5	1149.1	1149.5	1152.4	1153.1	1154.0	1155.2	1159.1	1154.3
5°	1065.3	1062.7	1061.2	1066.8	1061.2	1062.7	1065.3	1068.2	1073.3	1073.7	1078.7
7.5°	998.9	996.9	992.5	991.2	992.5	996.9	998.9	1000.8	1005.8	1010.1	1017.5
10°	956.4	954.4	950.5	949.4	950.5	954.4	956.4	961.5	966.5	971.9	977.0
12.5°	915.5	911.5	910.7	911.7	910.7	911.5	915.5	922.2	935.2	935.1	936.1
15°	861.2	859.2	853.7	855.2	853.7	859.2	861.2	867.7	873.7	881.3	888.7
17.5°	807.7	805.2	798.5	804.5	798.5	805.2	807.7	811.2	818.9	829.5	840.8
20°	774.0	770.0	766.5	765.9	766.5	770.0	774.0	777.5	786.0	795.0	803.5
22.5°	741.9	738.3	738.0	734.7	738.0	738.3	741.9	747.4	755.9	760.9	769.0
25°	701.8	698.3	697.3	694.7	697.3	698.3	701.8	705.8	711.3	715.3	724.3
27.5°	671.0	669.3	667.5	668.3	667.5	669.3	671.0	671.6	674.0	679.3	684.6
30°	652.1	651.7	650.6	650.6	650.6	651.7	652.1	650.6	653.2	655.6	659.7
32.5°	636.5	636.4	637.1	637.1	637.1	636.4	636.5	634.2	635.1	636.0	638.0
35°	614.5	616.0	617.1	615.6	617.1	616.0	614.5	612.6	611.1	607.6	608.6
37.5°	594.7	596.3	597.7	599.4	597.7	596.3	594.7	590.6	587.0	583.9	580.3
40°	579.5	583.0	584.0	586.5	584.0	583.0	579.5	575.0	571.0	567.4	563.5
42.5°	565.1	568.9	571.6	572.0	571.6	568.9	565.1	560.5	554.5	550.2	544.6
45°	542.9	546.9	550.4	550.4	550.4	546.9	542.9	535.4	528.9	522.4	516.8
47.5°	519.9	525.8	529.2	530.2	529.2	525.8	519.9	512.2	503.1	495.0	487.1
50°	504.3	511.3	514.8	517.4	514.8	511.3	504.3	495.8	486.3	476.2	466.7
52.5°	489.1	496.1	500.8	502.1	500.8	496.1	489.1	478.5	467.0	456.2	447.8
55°	462.7	472.7	478.2	480.2	478.2	472.7	462.7	451.2	440.2	426.6	414.5
57.5°	437.8	447.0	453.5	455.0	453.5	447.0	437.8	424.2	410.0	395.6	382.8
60°	418.6	428.6	436.6	438.1	436.6	428.6	418.6	405.0	390.0	376.0	360.0
62.5°	398.9	409.3	416.6	420.5	416.6	409.3	398.9	384.6	368.3	352.7	336.7
65°	365.0	375.4	382.5	384.0	382.5	375.4	365.0	350.9	333.8	317.4	303.8
67.5°	327.8	338.4	343.0	345.9	343.0	338.4	327.8	314.6	297.7	280.6	265.2
70°	301.8	310.3	315.3	317.8	315.3	310.3	301.8	287.8	273.7	256.2	239.6
72.5°	272.1	281.0	286.8	287.3	286.8	281.0	272.1	260.0	245.2	228.8	214.3
75°	226.6	234.6	237.6	237.6	237.6	234.6	226.6	215.1	203.0	190.0	175.4
77.5°	179.4	183.5	187.3	188.0	187.3	183.5	179.4	171.1	161.1	148.1	137.1
80°	148.9	151.4	154.4	154.4	154.4	151.4	148.9	141.4	131.9	120.8	112.3
82.5°	117.6	119.7	122.7	122.3	122.7	119.7	117.6	111.7	103.8	96.3	88.6
85°	71.2	75.7	75.2	74.2	75.2	75.7	71.2	72.2	64.7	59.7	52.6
87.5°	36.1	36.6	37.8	38.6	37.8	36.6	36.1	34.9	31.1	28.9	27.1
90°	20.1	20.4	20.6	21.0	20.6	20.4	20.1	19.7	19.1	18.2	17.2
92.5°	30.5	30.7	30.9	31.1	30.9	30.7	30.5	30.3	30.0	29.4	28.8
95°	55.2	55.2	55.2	55.2	55.2	55.2	55.2	55.2	55.0	54.6	54.1
97.5°	86.6	86.6	86.6	86.6	86.6	86.6	86.6	86.6	86.3	85.8	85.2
100°	108.4	108.4	108.4	108.4	108.4	108.4	108.4	108.4	108.3	107.9	107.6
102.5°	132.7	132.8	132.9	133.1	132.9	132.8	132.7	132.5	132.2	131.9	131.4
105°	169.3	169.8	170.2	170.7	170.2	169.8	169.3	168.8	168.3	167.9	167.4
107.5°	207.5	207.5	207.4	207.4	207.4	207.5	207.5	207.5	207.3	206.8	206.4
110°	232.2	232.7	233.2	233.7	233.2	232.7	232.2	231.8	231.7	232.1	232.3



TEST NUMBER: P332782-830

CATALOG NUMBER: S124DIW-S795D770U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	260.2	260.3	260.4	260.5	260.4	260.3	260.2	260.1	260.1	260.1	260.2
115°	302.7	302.6	302.4	302.2	302.4	302.6	302.7	302.8	302.9	303.1	303.3
117.5°	342.9	342.5	342.2	342.0	342.2	342.5	342.9	343.2	343.6	344.1	344.7
120°	371.3	371.6	371.8	372.1	371.8	371.6	371.3	370.9	371.2	371.9	372.7
122.5°	399.0	398.4	397.9	397.4	397.9	398.4	399.0	399.5	400.1	400.7	401.1
125°	441.7	441.3	441.0	440.7	441.0	441.3	441.7	442.0	442.2	442.6	442.9
127.5°	481.6	481.4	481.1	480.9	481.1	481.4	481.6	481.8	482.1	482.5	482.8
130°	509.1	508.4	507.7	507.2	507.7	508.4	509.1	509.6	510.1	510.4	510.8
132.5°	535.9	535.6	535.4	535.2	535.4	535.6	535.9	536.1	536.4	536.8	537.1
135°	575.0	574.6	574.1	573.6	574.1	574.6	575.0	575.5	575.9	576.2	576.5
137.5°	613.8	613.9	614.0	614.1	614.0	613.9	613.8	613.7	613.9	614.3	614.6
140°	639.1	638.9	638.9	638.7	638.9	638.9	639.1	639.3	639.4	639.6	639.8
142.5°	663.4	663.4	663.4	663.3	663.4	663.4	663.4	663.5	663.5	663.5	663.5
145°	698.1	697.7	697.2	696.7	697.2	697.7	698.1	698.6	698.9	699.1	699.3
147.5°	731.0	730.9	730.8	730.6	730.8	730.9	731.0	731.2	731.3	731.5	731.6
150°	751.8	751.6	751.5	751.3	751.5	751.6	751.8	752.0	752.1	752.1	752.1
152.5°	771.6	771.2	770.7	770.3	770.7	771.2	771.6	771.9	771.9	771.6	771.2
155°	798.6	798.1	797.4	796.8	797.4	798.1	798.6	799.3	799.3	798.6	798.1
157.5°	822.0	821.5	821.0	820.4	821.0	821.5	822.0	822.6	822.6	822.1	821.6
160°	836.2	835.4	834.6	833.9	834.6	835.4	836.2	837.0	837.2	836.7	836.2
162.5°	850.2	849.4	848.7	847.8	848.7	849.4	850.2	850.9	850.9	850.1	849.2
165°	867.9	867.2	866.7	866.0	866.7	867.2	867.9	868.6	868.4	867.4	866.5
167.5°	881.9	881.0	880.1	879.0	880.1	881.0	881.9	882.9	882.9	881.9	881.1
170°	889.6	888.5	887.4	886.4	887.4	888.5	889.6	890.7	890.8	889.9	888.9
172.5°	895.7	894.7	893.5	892.5	893.5	894.7	895.7	896.8	896.8	895.8	894.8
175°	902.2	901.1	900.0	898.9	900.0	901.1	902.2	903.2	903.2	902.2	901.1
177.5°	905.2	904.3	903.2	902.3	903.2	904.3	905.2	906.3	906.3	905.4	904.6
180°	904.5	904.5	904.5	904.5	904.5	904.5	904.5	904.5	904.5	904.5	904.5



TEST NUMBER: P332782-830

CATALOG NUMBER: S124DIW-S795D770U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1
2.5°	1156.8	1158.4	1164.8	1170.8	1178.0	1183.3	1186.8	1190.8	1199.3	1206.1	1212.5
5°	1083.7	1086.3	1099.3	1108.3	1123.9	1137.4	1147.9	1159.4	1173.0	1191.6	1208.6
7.5°	1019.5	1028.8	1043.0	1057.7	1073.6	1091.3	1106.7	1124.1	1147.5	1172.9	1199.2
10°	983.0	993.5	1008.6	1025.6	1040.7	1061.2	1080.2	1100.8	1127.4	1158.5	1189.6
12.5°	946.5	963.8	975.2	995.5	1011.8	1028.7	1049.0	1075.9	1106.9	1139.6	1177.1
15°	900.8	910.3	932.4	943.4	966.5	992.5	1012.6	1039.6	1069.7	1112.9	1155.0
17.5°	848.1	860.6	878.2	899.2	925.7	946.0	971.0	998.8	1036.7	1079.6	1132.3
20°	813.6	824.1	845.6	868.7	896.8	918.3	944.9	971.9	1011.1	1056.7	1111.8
22.5°	782.7	792.9	815.6	837.1	864.3	890.7	918.4	949.9	987.4	1035.5	1091.7
25°	734.9	748.4	768.5	790.5	816.6	846.7	876.8	904.8	944.9	995.5	1055.7
27.5°	692.5	703.3	717.8	742.9	772.5	801.5	831.4	866.7	905.2	958.8	1021.2
30°	665.2	675.2	689.8	712.8	740.4	771.5	802.6	836.6	876.8	929.9	993.5
32.5°	643.6	651.2	664.1	684.8	709.9	742.6	773.3	808.6	850.6	903.1	965.1
35°	611.5	618.1	623.1	642.6	665.2	695.3	726.3	763.9	804.6	854.2	916.3
37.5°	580.1	582.4	589.7	602.6	624.4	652.1	680.9	717.9	759.5	809.9	866.0
40°	560.9	561.9	566.5	578.4	597.6	623.6	651.7	688.2	727.8	775.5	831.1
42.5°	542.1	541.5	545.6	554.0	571.8	595.5	623.2	656.6	696.2	740.2	792.6
45°	512.3	512.3	511.3	518.3	532.8	555.9	579.0	611.1	644.1	687.3	731.4
47.5°	481.3	478.4	479.3	483.0	495.1	514.2	537.3	563.6	592.9	629.3	668.0
50°	461.2	457.1	455.6	459.7	470.7	487.2	509.3	532.3	560.0	592.0	625.1
52.5°	439.1	435.1	432.4	435.2	445.4	460.8	480.8	501.1	525.8	552.0	580.6
55°	405.0	400.5	399.0	400.0	407.6	419.5	436.6	455.2	473.7	495.3	515.3
57.5°	371.5	364.0	362.6	362.1	367.3	378.3	392.6	408.7	422.2	435.2	456.6
60°	349.4	340.4	337.3	336.9	340.9	349.9	363.0	379.0	388.5	397.5	416.0
62.5°	325.7	317.1	310.5	311.2	314.8	323.4	334.9	346.5	352.8	362.6	375.1
65°	289.3	278.2	273.2	271.7	273.7	280.7	289.7	297.3	304.3	308.3	320.3
67.5°	252.8	243.6	236.1	234.3	233.4	238.2	245.6	250.2	255.1	258.6	265.8
70°	227.1	219.0	210.0	207.0	206.5	210.6	217.5	218.0	225.1	226.6	234.1
72.5°	201.8	191.8	185.6	182.6	180.5	184.1	188.7	190.0	193.8	196.5	200.4
75°	162.4	154.9	148.9	144.4	142.9	144.9	144.9	147.4	149.9	151.4	155.9
77.5°	127.8	119.2	112.1	109.5	107.6	106.4	107.4	109.0	107.7	110.4	111.4
80°	103.8	94.7	89.3	88.2	85.2	82.8	82.2	83.7	81.7	82.8	85.7
82.5°	80.1	74.3	68.3	67.4	63.5	62.3	61.7	60.9	60.9	60.7	61.3
85°	47.6	44.1	40.1	37.6	36.1	33.6	33.6	32.6	31.6	30.5	31.1
87.5°	22.5	21.5	19.2	17.8	16.8	14.9	14.6	13.1	12.3	11.6	10.8
90°	16.3	15.4	14.1	12.9	11.7	10.5	9.0	7.3	5.6	3.8	2.1
92.5°	28.3	27.7	26.9	25.9	25.1	24.2	22.8	20.8	18.9	17.0	15.0
95°	53.6	53.2	52.1	51.0	49.9	48.8	47.6	46.2	44.8	43.4	41.9
97.5°	84.6	84.1	82.8	81.5	80.3	79.0	77.8	76.6	75.6	74.5	73.3
100°	107.4	107.1	105.7	104.2	102.8	101.4	100.4	99.8	99.2	98.6	97.9
102.5°	131.0	130.5	129.2	128.0	126.7	125.5	124.7	124.4	124.1	123.9	123.7
105°	166.9	166.5	165.9	165.2	164.7	164.0	163.6	163.4	163.3	163.2	163.0
107.5°	205.9	205.6	205.5	205.4	205.3	205.2	205.0	204.8	204.6	204.4	204.2
110°	232.6	232.9	233.1	233.3	233.4	233.6	233.5	233.2	232.9	232.5	232.2



TEST NUMBER: P332782-830

CATALOG NUMBER: S124DIW-S795D770U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	260.3	260.3	260.6	260.9	261.2	261.5	261.6	261.6	261.5	261.4	261.4
115°	303.4	303.6	303.9	304.3	304.5	304.8	305.0	305.0	305.0	305.0	305.0
117.5°	345.2	345.7	345.9	346.2	346.4	346.6	346.7	346.5	346.4	346.3	346.1
120°	373.4	374.3	374.8	375.2	375.7	376.1	376.1	375.4	374.8	374.2	373.5
122.5°	401.7	402.3	402.5	402.7	402.9	403.1	403.1	402.8	402.6	402.4	402.1
125°	443.2	443.5	443.7	443.8	443.9	444.1	444.2	444.2	444.2	444.2	444.2
127.5°	483.1	483.4	483.6	483.9	484.1	484.4	484.3	483.8	483.3	482.9	482.4
130°	511.0	511.3	511.3	511.3	511.3	511.3	511.1	510.7	510.2	509.7	509.3
132.5°	537.3	537.6	537.8	537.9	538.0	538.2	538.1	537.7	537.3	537.1	536.7
135°	576.8	577.1	577.1	577.1	577.1	577.1	576.6	575.7	574.8	573.8	573.0
137.5°	615.0	615.5	615.2	614.9	614.7	614.4	614.2	613.7	613.2	612.8	612.4
140°	639.9	640.1	640.1	640.1	640.1	640.1	639.9	639.6	639.3	638.9	638.7
142.5°	663.5	663.5	663.7	663.8	663.9	664.1	664.0	663.6	663.4	663.1	662.7
145°	699.4	699.6	699.4	699.3	699.1	698.9	698.5	698.0	697.3	696.6	696.1
147.5°	731.7	731.9	732.0	732.1	732.3	732.4	732.1	731.3	730.6	729.8	729.1
150°	752.1	752.1	752.1	752.1	752.1	752.1	751.7	751.1	750.5	749.8	749.2
152.5°	770.8	770.4	770.3	770.2	770.1	770.0	769.8	769.4	769.0	768.6	768.3
155°	797.4	796.8	796.9	797.1	797.2	797.4	797.5	797.5	797.5	797.5	797.5
157.5°	821.1	820.7	820.8	820.8	820.8	820.9	821.0	821.2	821.5	821.8	822.1
160°	835.8	835.3	835.4	835.6	835.8	835.8	836.0	836.2	836.3	836.5	836.7
162.5°	848.4	847.5	847.7	847.9	848.0	848.2	848.5	848.9	849.2	849.7	850.1
165°	865.5	864.6	865.0	865.3	865.5	865.9	866.3	866.8	867.2	867.7	868.2
167.5°	880.1	879.2	879.1	879.1	879.1	879.0	879.4	880.1	880.7	881.4	881.9
170°	888.0	887.0	886.8	886.7	886.6	886.4	886.7	887.5	888.3	889.0	889.9
172.5°	893.7	892.6	892.6	892.6	892.5	892.5	892.8	893.4	894.1	894.8	895.4
175°	900.0	898.9	899.1	899.2	899.4	899.6	900.0	900.8	901.5	902.3	903.1
177.5°	903.7	902.9	902.9	902.9	902.9	902.9	903.1	903.8	904.4	905.0	905.6
180°	904.5	904.5	904.5	904.5	904.5	904.5	904.5	904.5	904.5	904.5	904.5



TEST NUMBER: P332782-830

CATALOG NUMBER: S124DIW-S795D770U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1
2.5°	1218.1	1222.1	1227.4	1236.1	1239.3	1243.4	1249.0	1248.6	1250.2	1256.2	1269.0
5°	1222.7	1238.1	1253.2	1271.2	1290.3	1302.8	1319.8	1330.4	1341.0	1354.4	1377.5
7.5°	1224.5	1249.1	1276.7	1308.3	1336.5	1369.0	1394.4	1418.2	1439.7	1468.4	1495.8
10°	1221.6	1254.7	1290.3	1330.4	1373.0	1409.1	1441.7	1478.8	1510.3	1544.9	1576.0
12.5°	1216.4	1256.3	1303.9	1348.9	1398.6	1452.0	1492.6	1530.1	1572.2	1611.9	1659.8
15°	1204.6	1259.2	1314.8	1374.0	1440.7	1502.3	1560.9	1609.6	1654.7	1714.4	1777.1
17.5°	1189.6	1248.5	1318.7	1390.3	1459.9	1530.4	1603.0	1676.1	1733.1	1807.1	1856.1
20°	1175.5	1243.7	1315.9	1401.1	1470.7	1558.5	1630.7	1701.4	1779.5	1853.2	1911.9
22.5°	1155.8	1230.5	1307.0	1391.9	1483.6	1571.3	1654.7	1731.5	1809.6	1889.7	1960.8
25°	1130.9	1198.5	1289.3	1385.5	1476.8	1572.0	1667.7	1764.0	1848.2	1933.0	1999.1
27.5°	1088.4	1173.8	1258.3	1357.6	1459.1	1566.8	1669.1	1769.9	1858.1	1927.8	1968.8
30°	1066.8	1140.9	1232.7	1332.4	1442.2	1558.0	1664.7	1763.5	1845.7	1901.4	1917.9
32.5°	1034.6	1111.3	1201.0	1304.3	1420.5	1539.5	1650.7	1743.9	1812.4	1841.6	1821.7
35°	987.0	1056.2	1146.9	1252.7	1373.5	1500.3	1610.1	1688.8	1723.9	1696.3	1627.7
37.5°	929.9	998.4	1089.6	1193.4	1318.4	1447.4	1546.6	1603.3	1591.7	1523.1	1420.7
40°	889.8	953.9	1040.7	1152.9	1274.8	1404.1	1491.3	1521.9	1489.8	1391.6	1282.8
42.5°	845.3	907.9	994.9	1103.2	1232.3	1351.5	1427.6	1430.0	1376.3	1258.9	1149.6
45°	777.5	837.2	919.4	1032.2	1151.4	1263.8	1313.8	1289.3	1190.1	1076.8	967.0
47.5°	710.6	762.3	843.4	950.5	1063.8	1158.3	1183.1	1138.9	1033.1	923.1	821.4
50°	661.7	713.8	790.0	892.3	1001.5	1083.3	1095.3	1036.6	932.9	822.1	742.4
52.5°	614.7	666.5	739.9	834.5	934.6	1008.2	1008.7	940.8	837.4	738.7	664.6
55°	545.9	592.5	658.6	743.4	832.6	890.2	876.3	806.1	716.3	630.7	565.9
57.5°	479.6	520.1	581.1	651.8	730.4	777.9	754.6	687.0	606.9	534.2	485.2
60°	436.6	475.2	527.4	594.0	660.2	697.3	675.2	614.1	540.4	481.7	439.1
62.5°	394.9	427.5	477.6	535.5	596.8	624.3	604.6	544.3	480.6	427.6	393.0
65°	335.8	362.4	402.6	452.1	496.8	520.3	503.8	447.6	399.0	360.9	333.4
67.5°	280.7	301.4	331.9	371.6	409.5	422.3	407.3	368.2	327.0	296.4	277.0
70°	242.6	262.2	287.8	318.3	351.4	365.0	349.9	318.8	285.2	257.1	238.1
72.5°	209.3	224.5	246.0	272.2	298.0	311.6	301.3	271.5	243.1	222.3	206.0
75°	159.4	172.5	187.5	206.0	226.1	235.1	226.1	205.6	186.0	170.4	158.9
77.5°	115.9	122.9	134.5	148.4	160.9	167.9	160.0	146.1	134.1	123.5	117.8
80°	88.2	93.2	101.2	112.3	120.8	127.3	122.3	110.7	101.2	94.3	91.7
82.5°	64.2	67.6	72.8	81.0	86.7	90.0	87.8	79.5	75.6	69.4	66.8
85°	31.6	33.6	37.1	39.6	44.6	45.1	45.6	42.1	38.6	37.1	35.1
87.5°	11.6	12.3	13.9	15.5	17.3	18.0	17.8	18.1	16.7	16.5	15.1
90°	3.8	5.6	7.3	9.0	10.5	11.7	12.9	14.1	15.4	16.3	17.2
92.5°	17.0	18.9	20.8	22.8	24.2	25.1	25.9	26.9	27.7	28.3	28.8
95°	43.4	44.8	46.2	47.6	48.8	49.9	51.0	52.1	53.2	53.6	54.1
97.5°	74.5	75.6	76.6	77.8	79.0	80.3	81.5	82.8	84.1	84.6	85.2
100°	98.6	99.2	99.8	100.4	101.4	102.8	104.2	105.7	107.1	107.4	107.6
102.5°	123.9	124.1	124.4	124.7	125.5	126.7	128.0	129.2	130.5	131.0	131.4
105°	163.2	163.3	163.4	163.6	164.0	164.7	165.2	165.9	166.5	166.9	167.4
107.5°	204.4	204.6	204.8	205.0	205.2	205.3	205.4	205.5	205.6	205.9	206.4
110°	232.5	232.9	233.2	233.5	233.6	233.4	233.3	233.1	232.9	232.6	232.3





TEST NUMBER: P332782-830

CATALOG NUMBER: S124DIW-S795D770U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	261.4	261.5	261.6	261.6	261.5	261.2	260.9	260.6	260.3	260.3	260.2
115°	305.0	305.0	305.0	305.0	304.8	304.5	304.3	303.9	303.6	303.4	303.3
117.5°	346.3	346.4	346.5	346.7	346.6	346.4	346.2	345.9	345.7	345.2	344.7
120°	374.2	374.8	375.4	376.1	376.1	375.7	375.2	374.8	374.3	373.4	372.7
122.5°	402.4	402.6	402.8	403.1	403.1	402.9	402.7	402.5	402.3	401.7	401.1
125°	444.2	444.2	444.2	444.2	444.1	443.9	443.8	443.7	443.5	443.2	442.9
127.5°	482.9	483.3	483.8	484.3	484.4	484.1	483.9	483.6	483.4	483.1	482.8
130°	509.7	510.2	510.7	511.1	511.3	511.3	511.3	511.3	511.3	511.0	510.8
132.5°	537.1	537.3	537.7	538.1	538.2	538.0	537.9	537.8	537.6	537.3	537.1
135°	573.8	574.8	575.7	576.6	577.1	577.1	577.1	577.1	577.1	576.8	576.5
137.5°	612.8	613.2	613.7	614.2	614.4	614.7	614.9	615.2	615.5	615.0	614.6
140°	638.9	639.3	639.6	639.9	640.1	640.1	640.1	640.1	640.1	639.9	639.8
142.5°	663.1	663.4	663.6	664.0	664.1	663.9	663.8	663.7	663.5	663.5	663.5
145°	696.6	697.3	698.0	698.5	698.9	699.1	699.3	699.4	699.6	699.4	699.3
147.5°	729.8	730.6	731.3	732.1	732.4	732.3	732.1	732.0	731.9	731.7	731.6
150°	749.8	750.5	751.1	751.7	752.1	752.1	752.1	752.1	752.1	752.1	752.1
152.5°	768.6	769.0	769.4	769.8	770.0	770.1	770.2	770.3	770.4	770.8	771.2
155°	797.5	797.5	797.5	797.5	797.4	797.2	797.1	796.9	796.8	797.4	798.1
157.5°	821.8	821.5	821.2	821.0	820.9	820.8	820.8	820.8	820.7	821.1	821.6
160°	836.5	836.3	836.2	836.0	835.8	835.8	835.6	835.4	835.3	835.8	836.2
162.5°	849.7	849.2	848.9	848.5	848.2	848.0	847.9	847.7	847.5	848.4	849.2
165°	867.7	867.2	866.8	866.3	865.9	865.5	865.3	865.0	864.6	865.5	866.5
167.5°	881.4	880.7	880.1	879.4	879.0	879.1	879.1	879.1	879.2	880.1	881.1
170°	889.0	888.3	887.5	886.7	886.4	886.6	886.7	886.8	887.0	888.0	888.9
172.5°	894.8	894.1	893.4	892.8	892.5	892.5	892.6	892.6	892.6	893.7	894.8
175°	902.3	901.5	900.8	900.0	899.6	899.4	899.2	899.1	898.9	900.0	901.1
177.5°	905.0	904.4	903.8	903.1	902.9	902.9	902.9	902.9	902.9	903.7	904.6
180°	904.5	904.5	904.5	904.5	904.5	904.5	904.5	904.5	904.5	904.5	904.5



TEST NUMBER: P332782-830

CATALOG NUMBER: S124DIW-S795D770U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1	1210.1
2.5°	1275.4	1276.3	1279.9	1282.7	1283.5	1287.5	1287.9
5°	1387.5	1396.1	1412.6	1414.1	1416.6	1429.6	1419.7
7.5°	1518.9	1540.5	1555.0	1567.7	1572.3	1578.0	1576.9
10°	1603.1	1635.2	1651.2	1676.8	1677.8	1684.3	1680.3
12.5°	1687.7	1725.0	1754.3	1759.0	1780.5	1783.8	1789.4
15°	1807.6	1847.2	1887.8	1902.3	1931.9	1939.0	1950.0
17.5°	1920.3	1960.8	1989.2	2026.8	2039.0	2055.2	2044.2
20°	1982.1	2026.2	2062.3	2091.9	2104.4	2113.4	2112.4
22.5°	2019.4	2063.9	2093.1	2115.5	2127.2	2131.1	2130.8
25°	2042.7	2068.3	2077.3	2085.8	2072.8	2068.3	2070.3
27.5°	1977.7	1971.1	1947.6	1916.7	1884.6	1859.2	1845.3
30°	1888.3	1849.3	1813.6	1751.4	1719.4	1700.3	1683.3
32.5°	1761.6	1699.7	1631.2	1574.2	1537.8	1509.5	1505.2
35°	1544.5	1451.2	1367.5	1297.8	1261.7	1231.1	1224.1
37.5°	1313.1	1216.2	1140.9	1079.5	1040.7	1019.1	998.9
40°	1159.4	1076.3	1002.0	949.9	920.4	904.8	892.3
42.5°	1041.1	965.2	891.4	851.7	824.9	815.4	808.0
45°	877.7	807.1	755.9	725.9	710.3	694.3	686.7
47.5°	746.9	689.4	655.6	630.1	613.5	604.0	599.2
50°	672.7	625.6	595.5	576.0	560.9	553.4	549.4
52.5°	606.9	568.3	543.0	527.4	517.3	511.7	510.1
55°	522.8	493.2	477.2	463.7	456.2	451.2	449.1
57.5°	454.5	431.7	418.7	407.6	404.6	400.4	399.0
60°	409.5	392.0	381.0	373.4	371.0	365.9	366.9
62.5°	369.9	355.5	346.1	341.8	338.5	334.2	335.6
65°	312.8	302.3	297.3	293.2	289.3	286.7	288.7
67.5°	262.5	255.2	248.5	246.1	244.1	243.7	241.6
70°	229.6	223.6	217.5	216.0	216.0	214.1	213.6
72.5°	197.9	193.5	189.5	188.4	186.8	187.6	185.5
75°	152.9	149.4	147.9	146.4	145.9	145.9	144.4
77.5°	113.0	110.4	108.0	108.0	106.1	105.5	105.3
80°	85.7	84.7	82.8	82.8	81.7	82.2	81.2
82.5°	64.5	63.1	62.7	61.8	60.4	60.5	59.6
85°	34.6	33.1	32.6	31.1	30.1	31.1	30.1
87.5°	15.6	15.5	15.2	14.4	14.1	14.1	13.0
90°	18.2	19.1	19.7	20.1	20.4	20.6	21.0
92.5°	29.4	30.0	30.3	30.5	30.7	30.9	31.1
95°	54.6	55.0	55.2	55.2	55.2	55.2	55.2
97.5°	85.8	86.3	86.6	86.6	86.6	86.6	86.6
100°	107.9	108.3	108.4	108.4	108.4	108.4	108.4
102.5°	131.9	132.2	132.5	132.7	132.8	132.9	133.1
105°	167.9	168.3	168.8	169.3	169.8	170.2	170.7
107.5°	206.8	207.3	207.5	207.5	207.5	207.4	207.4
110°	232.1	231.7	231.8	232.2	232.7	233.2	233.7



TEST NUMBER: P332782-830

CATALOG NUMBER: S124DIW-S795D770U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	260.1	260.1	260.1	260.2	260.3	260.4	260.5
115°	303.1	302.9	302.8	302.7	302.6	302.4	302.2
117.5°	344.1	343.6	343.2	342.9	342.5	342.2	342.0
120°	371.9	371.2	370.9	371.3	371.6	371.8	372.1
122.5°	400.7	400.1	399.5	399.0	398.4	397.9	397.4
125°	442.6	442.2	442.0	441.7	441.3	441.0	440.7
127.5°	482.5	482.1	481.8	481.6	481.4	481.1	480.9
130°	510.4	510.1	509.6	509.1	508.4	507.7	507.2
132.5°	536.8	536.4	536.1	535.9	535.6	535.4	535.2
135°	576.2	575.9	575.5	575.0	574.6	574.1	573.6
137.5°	614.3	613.9	613.7	613.8	613.9	614.0	614.1
140°	639.6	639.4	639.3	639.1	638.9	638.9	638.7
142.5°	663.5	663.5	663.5	663.4	663.4	663.4	663.3
145°	699.1	698.9	698.6	698.1	697.7	697.2	696.7
147.5°	731.5	731.3	731.2	731.0	730.9	730.8	730.6
150°	752.1	752.1	752.0	751.8	751.6	751.5	751.3
152.5°	771.6	771.9	771.9	771.6	771.2	770.7	770.3
155°	798.6	799.3	799.3	798.6	798.1	797.4	796.8
157.5°	822.1	822.6	822.6	822.0	821.5	821.0	820.4
160°	836.7	837.2	837.0	836.2	835.4	834.6	833.9
162.5°	850.1	850.9	850.9	850.2	849.4	848.7	847.8
165°	867.4	868.4	868.6	867.9	867.2	866.7	866.0
167.5°	881.9	882.9	882.9	881.9	881.0	880.1	879.0
170°	889.9	890.8	890.7	889.6	888.5	887.4	886.4
172.5°	895.8	896.8	896.8	895.7	894.7	893.5	892.5
175°	902.2	903.2	903.2	902.2	901.1	900.0	898.9
177.5°	905.4	906.3	906.3	905.2	904.3	903.2	902.3
180°	904.5	904.5	904.5	904.5	904.5	904.5	904.5

(END OF REPORT)