

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332785-830

Luminaire Tested: **S124DIW-S795D770U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332785-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIW-S795D770U830-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 770 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6107.0 lumens  
Efficiency: N/A  
Efficacy: 135.7 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 45  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332785-830

CATALOG NUMBER: S124DIW-S795D770U830-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332785-830

CATALOG NUMBER: S124DIW-S795D770U830-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53
1	98	94	90	86	91	87	84	81	74	72	70	63	61	59	52	50	49	44
2	90	82	76	71	83	76	71	66	65	61	58	55	52	49	45	43	42	37
3	82	72	65	59	75	67	61	55	57	52	48	49	45	42	40	38	35	31
4	75	64	56	50	69	59	52	47	51	46	41	43	39	36	36	33	30	27
5	69	57	49	43	63	53	46	40	46	40	36	39	34	31	32	29	27	23
6	63	51	43	37	58	48	40	35	41	35	31	35	31	27	29	26	23	21
7	58	46	38	32	54	43	36	31	37	32	27	32	27	24	27	23	21	18
8	54	42	34	29	50	39	32	27	34	28	24	29	25	21	25	21	19	16
9	51	38	31	26	47	36	29	24	31	26	22	27	22	19	23	19	17	15
10	47	35	28	23	44	33	26	22	29	23	20	25	21	17	21	18	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	10101	10101	10101
5°	10131	10009	10083
10°	10067	9928	9977
15°	9947	9787	9812
20°	9784	9613	9620
25°	9600	9413	9386
30°	9374	9177	9093
35°	9140	8932	8814
40°	8896	8652	8495
45°	8643	8379	8218
50°	8361	8133	7882
55°	8058	7817	7562
60°	7753	7463	7237
65°	7412	7125	6837
70°	7027	6675	6413
75°	6441	6129	5973
80°	5732	5500	5360
85°	5011	4826	4733



TEST NUMBER: P332785-830

CATALOG NUMBER: S124DIW-S795D770U830-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	117.8	1.9
10°-20°	332.0	5.4
20°-30°	488.6	8.0
30°-40°	568.1	9.3
40°-50°	568.1	9.3
50°-60°	496.9	8.1
60°-70°	369.0	6.0
70°-80°	209.7	3.4
80°-90°	63.2	1.0
90°-100°	32.0	0.5
100°-110°	204.0	3.3
110°-120°	390.2	6.4
120°-130°	495.4	8.1
130°-140°	530.0	8.7
140°-150°	495.6	8.1
150°-160°	399.7	6.5
160°-170°	257.8	4.2
170°-180°	88.8	1.5
0°-30°	938.5	15.4
0°-40°	1506.5	24.7
0°-60°	2571.5	42.1
0°-90°	3213.4	52.6
90°-120°	626.2	10.3
90°-150°	2147.2	35.2
90°-180°	2894.0	47.4
0°-180°	6107.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1251	1251	1251	1251	1251	
5°	1250	1246	1235	1245	1244	119
15°	1190	1185	1171	1176	1174	335
25°	1078	1070	1057	1057	1054	496
35°	927	920	906	899	894	580
45°	757	749	734	723	720	583
55°	572	569	555	544	537	513
65°	388	383	373	363	358	384
75°	206	202	196	193	192	219
85°	54	54	52	52	51	60
90°	2	10	15	19	21	5
95°	38	16	15	19	20	49
105°	211	215	218	223	199	220
115°	393	395	394	396	396	387
125°	553	555	554	556	557	493
135°	686	685	688	689	690	528
145°	791	793	793	793	795	494
155°	867	867	865	868	866	400
165°	914	911	911	916	910	258
175°	935	932	932	937	930	89
180°	935	935	935	935	935	



TEST NUMBER: P332785-830

CATALOG NUMBER: S124DIW-S795D770U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1251.2	1251.2	1251.2	1251.2	1251.2	1251.2	1251.2	1251.2	1251.2	1251.2	1251.2
2.5°	1254.4	1253.9	1253.3	1252.8	1252.3	1251.0	1249.1	1247.1	1245.1	1243.2	1244.9
5°	1250.2	1249.3	1248.4	1247.5	1246.6	1244.9	1242.5	1240.0	1237.6	1235.1	1237.6
7.5°	1238.6	1237.7	1236.8	1235.9	1235.0	1233.2	1230.5	1227.8	1225.0	1222.3	1224.3
10°	1228.1	1227.3	1226.3	1225.5	1224.6	1222.7	1219.7	1216.9	1214.0	1211.1	1212.9
12.5°	1214.5	1213.6	1212.7	1211.8	1211.0	1208.9	1205.9	1202.8	1199.8	1196.7	1198.6
15°	1190.1	1189.1	1188.3	1187.3	1186.5	1184.4	1181.0	1177.7	1174.3	1171.0	1172.3
17.5°	1160.6	1159.4	1158.3	1157.3	1156.1	1154.0	1150.8	1147.6	1144.4	1141.3	1142.2
20°	1138.9	1137.7	1136.7	1135.6	1134.4	1132.2	1128.9	1125.5	1122.2	1118.9	1119.6
22.5°	1115.7	1114.2	1112.7	1111.3	1109.7	1107.4	1104.0	1100.7	1097.3	1094.0	1095.2
25°	1077.7	1076.2	1074.6	1073.1	1071.5	1069.1	1066.0	1062.9	1059.8	1056.7	1056.9
27.5°	1034.4	1032.8	1031.2	1029.6	1028.0	1025.8	1022.8	1020.0	1017.1	1014.2	1013.6
30°	1005.6	1003.8	1002.0	1000.2	998.4	996.1	993.2	990.3	987.4	984.5	983.6
32.5°	975.1	973.5	971.9	970.3	968.7	966.3	963.3	960.2	957.2	954.0	953.0
35°	927.4	925.8	924.3	922.7	921.1	918.8	915.7	912.6	909.5	906.3	904.7
37.5°	877.0	875.6	874.2	872.8	871.3	868.9	865.6	862.2	858.9	855.5	853.8
40°	844.1	842.4	840.6	838.8	837.0	834.4	831.1	827.7	824.4	821.0	818.9
42.5°	808.9	807.8	806.7	805.7	804.6	802.2	798.5	794.8	791.1	787.4	784.9
45°	757.0	755.4	753.8	752.2	750.7	748.1	744.6	741.0	737.4	733.9	731.4
47.5°	702.6	701.5	700.5	699.4	698.3	696.2	692.9	689.6	686.3	683.0	680.1
50°	665.7	664.8	663.9	663.0	662.1	660.2	657.0	653.9	650.7	647.6	644.5
52.5°	629.6	628.6	627.5	626.4	625.3	623.1	619.8	616.5	613.2	609.9	607.2
55°	572.5	571.7	571.1	570.4	569.8	567.9	564.8	561.7	558.6	555.4	552.7
57.5°	517.9	517.2	516.4	515.7	514.9	512.9	509.9	506.8	503.8	500.7	498.1
60°	480.2	479.1	478.0	476.9	475.8	473.7	470.9	468.0	465.1	462.2	460.1
62.5°	443.4	442.4	441.5	440.5	439.6	437.6	434.5	431.4	428.4	425.3	423.5
65°	388.0	386.9	385.8	384.7	383.5	381.8	379.7	377.4	375.1	373.0	370.7
67.5°	332.2	331.2	330.2	329.1	328.2	326.6	324.4	322.3	320.2	318.0	315.8
70°	297.7	296.2	294.6	293.0	291.5	289.8	288.0	286.3	284.5	282.8	281.0
72.5°	260.9	259.3	257.8	256.2	254.6	253.2	251.8	250.2	248.8	247.4	246.0
75°	206.5	205.4	204.3	203.2	202.1	201.0	199.8	198.7	197.7	196.5	195.6
77.5°	154.6	154.1	153.6	153.2	152.6	151.9	150.9	150.0	148.9	148.0	147.7
80°	123.3	122.6	122.0	121.3	120.6	120.1	119.6	119.2	118.8	118.3	117.8
82.5°	92.8	92.6	92.2	91.9	91.6	91.4	91.3	91.2	91.1	91.0	90.8
85°	54.1	54.1	54.1	54.1	54.1	53.9	53.4	53.1	52.6	52.1	52.1
87.5°	21.3	21.4	21.6	21.8	22.0	22.1	22.1	22.1	22.2	22.3	22.5
90°	2.1	3.8	5.6	7.3	9.0	10.5	11.7	12.9	14.1	15.4	16.3
92.5°	8.9	9.0	9.0	9.0	9.1	9.9	11.1	12.3	13.6	14.8	15.7
95°	38.5	33.2	27.9	22.6	17.3	14.8	14.9	15.1	15.3	15.4	16.3
97.5°	81.7	85.0	88.3	91.6	94.9	87.8	70.5	53.2	35.8	18.5	18.6
100°	114.7	117.5	120.4	123.1	125.9	116.6	95.2	73.7	52.2	30.8	28.2
102.5°	151.7	153.7	155.8	157.9	159.9	159.5	156.7	153.9	151.1	148.4	119.8
105°	210.6	211.5	212.4	213.4	214.3	215.2	215.9	216.7	217.5	218.3	219.7
107.5°	265.3	265.8	266.3	266.7	267.2	268.0	269.0	270.0	271.1	272.1	272.9
110°	302.3	302.7	303.2	303.7	304.1	304.8	305.8	306.7	307.6	308.5	308.9



TEST NUMBER: P332785-830

CATALOG NUMBER: S124DIW-S795D770U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	338.1	338.9	339.8	340.5	341.4	342.0	342.5	342.9	343.4	343.8	343.7
115°	393.2	393.7	394.2	394.5	395.0	395.2	395.0	394.9	394.7	394.5	394.9
117.5°	442.9	443.5	444.1	444.7	445.4	445.8	446.2	446.5	446.9	447.2	447.1
120°	476.5	477.1	477.7	478.3	478.9	479.2	479.0	478.9	478.7	478.5	478.9
122.5°	507.8	508.1	508.5	508.9	509.3	509.5	509.8	510.0	510.2	510.5	510.7
125°	552.7	553.4	553.9	554.6	555.2	555.3	555.1	554.8	554.4	554.1	554.6
127.5°	595.2	595.4	595.6	595.7	595.9	596.3	597.0	597.8	598.4	599.2	599.1
130°	622.6	622.8	623.0	623.1	623.3	623.6	624.1	624.5	625.0	625.5	625.7
132.5°	647.9	648.2	648.5	648.7	648.9	649.4	650.0	650.6	651.2	651.8	652.0
135°	685.6	685.5	685.3	685.1	685.0	685.2	685.9	686.5	687.1	687.8	688.1
137.5°	719.1	719.2	719.3	719.3	719.3	719.7	720.4	721.0	721.8	722.5	722.7
140°	740.9	741.2	741.5	741.9	742.2	742.4	742.8	743.1	743.4	743.8	744.1
142.5°	760.5	761.1	761.7	762.1	762.7	763.1	763.3	763.5	763.6	763.8	764.2
145°	790.6	791.1	791.5	792.0	792.5	792.7	792.7	792.7	792.7	792.7	792.9
147.5°	814.5	815.4	816.2	817.1	818.0	818.3	818.2	818.0	817.8	817.7	817.8
150°	831.9	832.5	833.1	833.8	834.3	834.6	834.4	834.2	834.2	834.0	834.0
152.5°	846.4	846.9	847.4	847.9	848.4	848.5	848.2	848.0	847.7	847.4	847.6
155°	866.9	867.0	867.1	867.3	867.5	867.3	866.9	866.4	865.9	865.4	866.1
157.5°	884.1	884.0	883.9	883.8	883.7	883.4	882.9	882.3	881.7	881.3	882.0
160°	894.1	893.6	893.2	892.8	892.3	891.9	891.8	891.6	891.5	891.4	892.3
162.5°	903.1	902.5	901.9	901.4	900.7	900.3	900.2	900.0	899.8	899.8	900.7
165°	914.5	913.6	912.9	912.1	911.3	911.0	911.0	911.0	911.0	911.0	912.2
167.5°	923.4	922.6	921.8	921.0	920.1	919.7	919.6	919.5	919.5	919.4	920.7
170°	928.4	927.5	926.5	925.6	924.7	924.3	924.4	924.6	924.7	924.9	926.1
172.5°	931.8	930.9	929.9	929.0	928.0	927.7	927.8	927.9	928.1	928.3	929.5
175°	935.4	934.4	933.6	932.6	931.7	931.3	931.4	931.6	931.8	931.9	933.3
177.5°	937.1	936.2	935.4	934.4	933.6	933.3	933.6	933.8	934.1	934.2	935.3
180°	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4



TEST NUMBER: P332785-830

CATALOG NUMBER: S124DIW-S795D770U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1251.2	1251.2	1251.2	1251.2	1251.2	1251.2	1251.2	1251.2
2.5°	1246.7	1248.5	1250.3	1251.1	1250.9	1250.8	1250.6	1250.4
5°	1240.0	1242.5	1244.9	1245.9	1245.5	1245.1	1244.6	1244.2
7.5°	1226.2	1228.2	1230.1	1231.0	1230.8	1230.5	1230.2	1229.9
10°	1214.7	1216.4	1218.2	1218.9	1218.4	1218.0	1217.6	1217.1
12.5°	1200.6	1202.5	1204.5	1205.1	1204.6	1203.9	1203.2	1202.7
15°	1173.7	1175.0	1176.3	1176.7	1176.0	1175.4	1174.7	1174.0
17.5°	1143.0	1143.9	1144.7	1144.9	1144.4	1144.0	1143.6	1143.1
20°	1120.2	1120.9	1121.5	1121.6	1121.2	1120.8	1120.3	1119.8
22.5°	1096.4	1097.6	1098.8	1099.0	1098.2	1097.4	1096.6	1095.8
25°	1057.2	1057.3	1057.6	1057.2	1056.4	1055.5	1054.6	1053.7
27.5°	1013.1	1012.6	1012.0	1011.3	1010.1	1009.0	1007.9	1006.7
30°	982.7	981.8	980.9	980.0	978.8	977.7	976.6	975.5
32.5°	951.9	950.8	949.8	948.7	947.5	946.4	945.3	944.2
35°	903.2	901.6	900.0	898.7	897.6	896.5	895.4	894.3
37.5°	852.2	850.5	848.9	847.3	845.7	844.3	842.8	841.3
40°	816.6	814.5	812.2	810.5	809.4	808.3	807.2	806.1
42.5°	782.2	779.7	777.0	775.4	774.7	773.9	773.2	772.4
45°	729.0	726.5	724.1	722.6	721.8	721.1	720.5	719.8
47.5°	677.4	674.7	671.8	669.7	668.0	666.3	664.6	662.9
50°	641.4	638.3	635.2	632.9	631.6	630.3	629.0	627.6
52.5°	604.5	601.6	598.9	596.7	595.0	593.3	591.6	589.9
55°	550.1	547.4	544.7	542.7	541.4	540.1	538.7	537.3
57.5°	495.6	493.0	490.5	488.6	487.3	486.0	484.7	483.4
60°	458.2	456.2	454.1	452.6	451.5	450.3	449.2	448.2
62.5°	421.6	419.8	418.0	416.5	415.4	414.2	413.2	412.1
65°	368.5	366.3	364.0	362.4	361.3	360.1	359.0	357.9
67.5°	313.8	311.6	309.4	308.2	307.9	307.6	307.3	307.0
70°	279.2	277.4	275.6	274.4	273.7	273.1	272.4	271.7
72.5°	244.6	243.2	241.8	240.7	240.0	239.3	238.7	238.0
75°	194.7	193.8	192.9	192.4	192.2	191.9	191.7	191.5
77.5°	147.4	147.1	146.9	146.5	145.9	145.3	144.8	144.2
80°	117.4	117.0	116.5	116.2	115.9	115.7	115.6	115.3
82.5°	90.5	90.2	89.9	89.7	89.5	89.3	89.1	88.8
85°	52.1	52.1	52.1	52.0	51.8	51.6	51.4	51.1
87.5°	22.7	22.9	23.1	23.2	23.3	23.3	23.4	23.5
90°	17.2	18.2	19.1	19.7	20.1	20.4	20.6	21.0
92.5°	16.7	17.6	18.6	19.0	19.1	19.2	19.2	19.3
95°	17.2	18.2	19.1	19.7	19.8	20.0	20.2	20.3
97.5°	18.7	18.8	18.9	18.9	19.1	19.3	19.4	19.6
100°	25.5	22.8	20.2	18.9	19.1	19.3	19.4	19.6
102.5°	91.3	62.8	34.3	20.0	20.1	20.1	20.1	20.2
105°	221.1	222.4	223.9	221.8	216.2	210.6	205.0	199.4
107.5°	273.5	274.2	274.9	275.5	276.2	276.7	277.3	277.9
110°	309.2	309.4	309.8	310.2	310.7	311.1	311.6	312.1





TEST NUMBER: P332785-830

CATALOG NUMBER: S124DIW-S795D770U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	343.7	343.7	343.6	343.8	344.4	345.0	345.6	346.2
115°	395.2	395.5	395.9	396.0	396.0	396.0	396.0	396.0
117.5°	447.0	447.0	447.0	446.9	446.9	446.8	446.7	446.7
120°	479.2	479.5	479.8	479.8	479.5	479.2	478.9	478.5
122.5°	510.9	511.0	511.2	511.1	510.9	510.5	510.2	509.9
125°	555.1	555.5	556.0	556.3	556.5	556.6	556.8	556.9
127.5°	599.0	598.9	598.8	598.7	598.6	598.4	598.3	598.2
130°	625.8	625.9	626.1	626.1	626.1	626.1	626.1	626.1
132.5°	652.1	652.2	652.4	652.4	652.3	652.1	652.1	652.0
135°	688.3	688.7	689.0	689.3	689.6	689.9	690.2	690.5
137.5°	723.1	723.5	723.8	724.0	723.9	723.8	723.7	723.6
140°	744.6	745.1	745.6	745.9	746.0	746.2	746.4	746.5
142.5°	764.6	764.9	765.3	765.4	765.4	765.4	765.5	765.5
145°	793.0	793.1	793.3	793.5	793.8	794.2	794.5	794.8
147.5°	817.9	818.1	818.2	818.4	818.5	818.7	818.9	819.0
150°	834.0	834.0	834.0	834.1	834.2	834.3	834.5	834.6
152.5°	847.9	848.1	848.4	848.5	848.4	848.3	848.2	848.1
155°	866.7	867.3	867.9	868.0	867.5	867.0	866.6	866.2
157.5°	882.9	883.7	884.5	884.5	883.7	882.9	882.0	881.3
160°	893.2	894.1	895.0	895.0	894.1	893.2	892.3	891.4
162.5°	901.6	902.5	903.4	903.4	902.4	901.3	900.2	899.2
165°	913.4	914.6	915.9	915.9	914.5	913.0	911.6	910.2
167.5°	922.1	923.4	924.8	924.7	923.1	921.6	920.0	918.5
170°	927.4	928.7	929.9	929.7	928.2	926.6	925.1	923.5
172.5°	930.8	932.0	933.2	933.0	931.3	929.7	928.0	926.3
175°	934.7	936.1	937.5	937.3	935.4	933.6	931.7	929.8
177.5°	936.3	937.3	938.3	938.0	936.5	935.0	933.6	932.1
180°	935.4	935.4	935.4	935.4	935.4	935.4	935.4	935.4

(END OF REPORT)