

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332125-940

Luminaire Tested: **S123DIW-S560D460U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332125-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIW-S560D460U940-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 460 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3493.9 lumens  
Efficiency: N/A  
Efficacy: 115.7 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 30.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332125-940

CATALOG NUMBER: S123DIW-S560D460U940-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332125-940

CATALOG NUMBER: S123DIW-S560D460U940-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	65	65	65	59
1	100	95	91	88	93	89	86	83	78	75	73	67	65	63	57	56	54	50
2	91	83	77	72	84	78	72	68	68	64	60	59	55	53	50	48	46	42
3	83	73	66	60	77	69	62	57	60	55	50	52	48	45	44	41	39	35
4	76	65	57	51	70	61	54	48	53	48	43	46	42	38	40	36	34	30
5	70	58	49	43	65	54	47	41	48	42	37	41	37	33	36	32	29	26
6	64	52	44	38	60	49	41	36	43	37	32	38	33	29	32	29	26	23
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	30	26	23	20
8	55	43	35	29	51	40	33	28	36	30	25	31	26	23	27	23	20	18
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	19	16
10	48	36	28	24	45	34	27	23	30	24	21	27	22	19	23	20	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8551	8551	8551
5°	8590	8473	8532
10°	8534	8400	8451
15°	8433	8304	8320
20°	8317	8168	8176
25°	8162	8007	7991
30°	7988	7828	7768
35°	7808	7638	7540
40°	7620	7429	7314
45°	7415	7237	7060
50°	7206	7000	6805
55°	6934	6756	6549
60°	6661	6469	6265
65°	6421	6159	5968
70°	6061	5803	5545
75°	5540	5340	5115
80°	4996	4785	4742
85°	4384	4224	4051



TEST NUMBER: P332125-940

CATALOG NUMBER: S123DIW-S560D460U940-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	74.8	2.1
10°-20°	211.3	6.0
20°-30°	312.1	8.9
30°-40°	364.6	10.4
40°-50°	366.5	10.5
50°-60°	322.0	9.2
60°-70°	239.9	6.9
70°-80°	136.7	3.9
80°-90°	40.7	1.2
90°-100°	33.5	1.0
100°-110°	100.3	2.9
110°-120°	170.6	4.9
120°-130°	224.4	6.4
130°-140°	252.2	7.2
140°-150°	247.9	7.1
150°-160°	208.7	6.0
160°-170°	138.9	4.0
170°-180°	48.7	1.4
0°-30°	598.2	17.1
0°-40°	962.8	27.6
0°-60°	1651.3	47.3
0°-90°	2068.6	59.2
90°-120°	304.4	8.7
90°-150°	1029.0	29.5
90°-180°	1425.0	40.8
0°-180°	3493.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	794	794	794	794	794	
5°	795	791	784	791	790	75
15°	757	754	745	750	747	213
25°	687	683	674	675	673	316
35°	594	590	581	577	574	372
45°	487	484	475	467	464	376
55°	370	368	360	353	349	331
65°	252	248	242	236	234	249
75°	133	131	128	125	123	142
85°	36	34	34	33	33	39
90°	0	4	10	11	12	3
95°	24	27	30	31	32	27
105°	91	92	95	95	96	97
115°	172	173	172	172	172	170
125°	251	252	252	250	248	224
135°	326	328	328	327	326	251
145°	396	396	398	397	396	247
155°	453	453	453	455	452	208
165°	493	492	492	494	492	139
175°	513	512	512	514	511	49
180°	514	514	514	514	514	



TEST NUMBER: P332125-940

CATALOG NUMBER: S123DIW-S560D460U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	794.4	794.4	794.4	794.4	794.4	794.4	794.4	794.4	794.4	794.4	794.4
2.5°	797.1	796.7	796.2	795.7	795.2	794.2	792.9	791.6	790.3	789.0	790.1
5°	795.0	794.3	793.5	792.8	792.0	790.9	789.2	787.5	785.9	784.2	785.7
7.5°	787.3	786.6	785.8	785.1	784.3	783.0	781.3	779.5	777.8	776.1	777.5
10°	780.8	780.0	779.3	778.5	777.8	776.3	774.4	772.4	770.4	768.5	769.8
12.5°	772.0	771.3	770.7	770.1	769.5	768.2	766.3	764.5	762.7	760.8	761.8
15°	756.8	756.3	755.6	755.0	754.4	753.1	751.2	749.2	747.2	745.2	746.5
17.5°	739.2	738.4	737.6	736.8	736.0	734.7	732.7	730.8	728.8	726.7	727.6
20°	726.1	725.2	724.2	723.4	722.5	721.0	719.1	717.1	715.1	713.1	713.7
22.5°	711.3	710.4	709.5	708.6	707.7	706.2	704.3	702.3	700.3	698.4	698.8
25°	687.2	686.3	685.4	684.5	683.5	682.1	680.1	678.1	676.2	674.2	674.3
27.5°	661.4	660.5	659.6	658.7	657.8	656.3	654.2	652.1	650.0	647.8	647.9
30°	642.7	642.0	641.2	640.5	639.7	638.3	636.1	634.0	632.0	629.8	629.8
32.5°	624.2	623.2	622.1	621.2	620.2	618.8	617.2	615.5	613.9	612.3	611.4
35°	594.2	593.3	592.5	591.6	590.7	589.2	587.2	585.2	583.3	581.3	580.4
37.5°	563.7	562.5	561.3	560.2	559.0	557.5	555.4	553.5	551.4	549.5	548.4
40°	542.3	541.4	540.6	539.7	538.7	537.2	535.0	533.0	530.8	528.7	527.4
42.5°	521.0	520.0	519.0	517.9	516.9	515.3	513.2	511.1	509.0	506.8	505.6
45°	487.1	486.4	485.8	485.2	484.6	483.3	481.3	479.4	477.4	475.4	473.6
47.5°	453.3	452.4	451.6	450.7	449.8	448.4	446.6	444.7	442.8	441.0	439.2
50°	430.3	429.5	428.8	428.0	427.3	426.0	423.9	422.0	420.0	418.0	416.3
52.5°	406.3	405.7	405.3	404.7	404.2	402.9	400.8	398.8	396.6	394.6	393.2
55°	369.5	369.3	369.3	369.1	368.9	367.8	365.9	363.9	361.9	360.0	358.3
57.5°	334.6	334.0	333.5	333.1	332.5	331.4	329.8	328.3	326.7	325.1	323.7
60°	309.4	309.2	309.2	309.0	308.8	307.8	306.0	304.2	302.4	300.5	299.2
62.5°	287.0	286.6	286.2	285.9	285.4	284.4	282.5	280.7	278.8	277.1	275.7
65°	252.1	251.3	250.6	249.8	249.1	247.9	246.4	244.9	243.3	241.8	240.6
67.5°	215.0	214.4	213.7	213.0	212.3	211.4	210.3	209.1	207.9	206.9	205.8
70°	192.6	191.7	190.8	189.9	189.0	188.1	187.2	186.3	185.3	184.4	183.3
72.5°	169.2	168.4	167.8	167.1	166.5	165.6	164.6	163.5	162.5	161.5	160.5
75°	133.2	132.6	132.0	131.3	130.8	130.3	129.7	129.3	128.9	128.4	127.7
77.5°	101.4	101.0	100.7	100.4	100.0	99.6	99.1	98.5	97.9	97.4	96.9
80°	80.6	80.2	79.7	79.3	78.7	78.4	78.1	77.8	77.5	77.2	77.0
82.5°	60.4	60.3	60.2	60.1	60.0	59.9	59.9	59.8	59.7	59.7	59.4
85°	35.5	35.2	35.0	34.6	34.3	34.2	34.2	34.2	34.2	34.2	33.9
87.5°	14.3	14.1	13.9	13.7	13.6	13.6	13.6	13.7	13.8	14.0	13.9
90°	0.4	1.3	2.2	3.1	4.0	5.0	6.2	7.4	8.6	9.7	10.1
92.5°	9.8	10.4	11.0	11.6	12.2	12.8	13.6	14.2	14.9	15.5	15.8
95°	23.8	24.4	25.1	25.8	26.4	27.0	27.7	28.4	29.2	29.9	30.2
97.5°	42.4	42.8	43.2	43.8	44.2	44.7	45.2	45.7	46.3	46.8	47.2
100°	54.9	55.5	56.0	56.5	57.1	57.6	58.1	58.5	58.9	59.4	59.7
102.5°	69.5	69.8	70.2	70.4	70.8	71.2	71.9	72.4	73.0	73.7	73.9
105°	91.0	91.1	91.3	91.5	91.7	92.1	92.9	93.7	94.5	95.3	95.3
107.5°	115.8	115.9	116.0	116.1	116.3	116.5	116.8	117.1	117.4	117.8	118.1
110°	131.3	131.5	131.7	131.9	132.1	132.2	132.4	132.6	132.8	133.0	133.3



TEST NUMBER: P332125-940

CATALOG NUMBER: S123DIW-S560D460U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	147.5	147.6	147.8	147.8	147.9	148.0	148.0	148.1	148.1	148.1	148.6
115°	171.7	172.0	172.3	172.5	172.8	172.9	172.7	172.5	172.4	172.2	172.3
117.5°	196.2	196.4	196.5	196.7	196.9	196.8	196.6	196.4	196.2	195.9	195.9
120°	211.3	211.9	212.4	212.9	213.5	213.6	213.1	212.7	212.2	211.8	211.7
122.5°	227.2	227.6	228.0	228.4	228.7	228.8	228.6	228.4	228.2	227.9	227.7
125°	251.4	251.6	251.9	252.2	252.4	252.4	252.3	252.1	251.9	251.7	251.4
127.5°	273.7	274.2	274.8	275.4	276.0	276.2	276.0	275.7	275.5	275.4	274.8
130°	288.6	289.3	290.0	290.7	291.4	291.6	291.3	291.1	290.8	290.5	290.2
132.5°	303.4	304.1	304.9	305.6	306.3	306.6	306.3	306.1	305.9	305.8	305.3
135°	326.1	326.6	327.2	327.7	328.2	328.5	328.4	328.3	328.2	328.1	327.8
137.5°	347.1	347.6	348.0	348.5	348.9	349.3	349.5	349.7	350.0	350.2	349.8
140°	361.7	362.1	362.6	363.0	363.5	363.7	363.8	363.9	364.0	364.1	364.0
142.5°	375.0	375.4	375.9	376.3	376.7	377.0	377.2	377.4	377.6	377.6	377.6
145°	395.7	395.8	396.0	396.2	396.4	396.5	396.8	397.1	397.3	397.6	397.5
147.5°	413.8	414.0	414.4	414.6	415.0	415.3	415.5	415.8	416.1	416.3	416.3
150°	426.3	426.5	426.7	426.9	427.0	427.2	427.4	427.6	427.8	427.9	427.9
152.5°	436.7	436.9	437.2	437.4	437.7	437.8	437.9	438.1	438.2	438.3	438.5
155°	453.0	453.0	453.0	453.0	453.0	453.1	453.2	453.3	453.3	453.4	453.8
157.5°	466.9	466.8	466.7	466.5	466.5	466.5	466.5	466.6	466.6	466.7	467.1
160°	475.6	475.5	475.3	475.1	474.9	474.8	474.8	474.8	474.8	474.8	475.3
162.5°	483.4	483.1	482.9	482.6	482.4	482.3	482.3	482.4	482.5	482.6	483.0
165°	493.4	493.1	492.8	492.6	492.3	492.2	492.2	492.2	492.2	492.2	492.8
167.5°	501.4	501.1	500.7	500.3	500.0	499.8	499.9	500.0	500.1	500.1	500.7
170°	506.0	505.6	505.2	504.9	504.5	504.4	504.4	504.4	504.4	504.4	505.0
172.5°	509.5	509.2	508.8	508.5	508.0	507.8	507.8	507.8	507.8	507.8	508.5
175°	513.2	512.8	512.5	512.1	511.8	511.6	511.6	511.6	511.6	511.6	512.1
177.5°	514.8	514.4	514.2	513.9	513.6	513.4	513.4	513.4	513.4	513.4	513.9
180°	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4



TEST NUMBER: P332125-940

CATALOG NUMBER: S123DIW-S560D460U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	794.4	794.4	794.4	794.4	794.4	794.4	794.4	794.4
2.5°	791.4	792.6	793.8	794.3	794.2	794.1	794.0	793.9
5°	787.2	788.7	790.2	790.9	790.5	790.2	790.0	789.6
7.5°	778.8	780.2	781.6	782.1	781.9	781.8	781.6	781.4
10°	771.2	772.6	773.9	774.5	774.2	773.8	773.6	773.2
12.5°	762.8	763.8	764.8	765.2	765.0	764.8	764.6	764.5
15°	747.7	748.9	750.1	750.2	749.3	748.4	747.5	746.6
17.5°	728.5	729.3	730.2	730.4	730.1	729.8	729.4	729.1
20°	714.3	715.0	715.5	715.6	715.2	714.7	714.3	713.8
22.5°	699.4	699.8	700.3	700.3	699.7	699.1	698.6	697.9
25°	674.5	674.7	674.8	674.7	674.2	673.8	673.2	672.8
27.5°	648.1	648.2	648.3	648.1	647.5	646.9	646.3	645.8
30°	629.8	629.8	629.8	629.3	628.2	627.1	626.1	625.0
32.5°	610.6	609.8	608.9	608.1	607.6	607.1	606.5	605.9
35°	579.4	578.5	577.7	576.8	576.0	575.3	574.5	573.8
37.5°	547.2	546.2	545.1	544.3	543.9	543.3	542.9	542.3
40°	526.3	525.0	523.9	522.9	522.3	521.7	521.1	520.5
42.5°	504.4	503.2	501.9	501.1	500.4	499.9	499.3	498.6
45°	471.8	469.9	468.1	466.8	466.1	465.3	464.6	463.8
47.5°	437.4	435.6	433.8	432.6	431.9	431.2	430.6	429.9
50°	414.7	413.0	411.3	410.1	409.1	408.2	407.3	406.4
52.5°	391.7	390.3	388.9	387.6	386.7	385.8	385.0	384.1
55°	356.6	355.0	353.3	352.0	351.3	350.5	349.8	349.0
57.5°	322.2	320.7	319.2	318.0	317.1	316.3	315.4	314.5
60°	297.8	296.5	295.1	294.0	293.3	292.5	291.8	291.0
62.5°	274.3	273.0	271.6	270.6	270.1	269.7	269.1	268.6
65°	239.3	238.2	236.9	236.1	235.7	235.2	234.8	234.3
67.5°	204.7	203.7	202.6	201.7	201.1	200.5	199.8	199.2
70°	182.3	181.3	180.2	179.2	178.5	177.7	177.0	176.2
72.5°	159.6	158.6	157.7	157.0	156.7	156.2	155.9	155.4
75°	126.9	126.2	125.4	124.8	124.3	123.9	123.4	123.0
77.5°	96.4	95.9	95.3	95.1	95.1	95.1	95.1	95.1
80°	76.9	76.7	76.6	76.5	76.5	76.5	76.5	76.5
82.5°	59.1	58.9	58.6	58.4	58.3	58.1	58.1	58.0
85°	33.5	33.3	32.9	32.8	32.8	32.8	32.8	32.8
87.5°	13.8	13.8	13.7	13.7	13.8	13.8	13.8	13.9
90°	10.4	10.8	11.1	11.4	11.6	11.8	11.9	12.1
92.5°	16.1	16.4	16.7	16.8	16.7	16.5	16.4	16.3
95°	30.6	30.9	31.3	31.5	31.5	31.5	31.5	31.5
97.5°	47.6	48.1	48.4	48.6	48.6	48.6	48.5	48.5
100°	59.9	60.2	60.5	60.7	60.9	61.1	61.3	61.4
102.5°	74.2	74.5	74.7	74.8	74.8	74.7	74.7	74.6
105°	95.3	95.3	95.3	95.4	95.7	95.9	96.0	96.2
107.5°	118.3	118.6	118.9	119.0	118.9	118.8	118.7	118.6
110°	133.7	134.0	134.4	134.5	134.3	134.1	133.9	133.8





TEST NUMBER: P332125-940

CATALOG NUMBER: S123DIW-S560D460U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	149.0	149.5	149.9	150.1	150.0	150.0	150.0	149.9
115°	172.4	172.5	172.5	172.5	172.5	172.4	172.3	172.2
117.5°	195.9	195.8	195.8	195.7	195.5	195.2	194.9	194.7
120°	211.6	211.5	211.4	211.2	211.1	210.9	210.7	210.5
122.5°	227.5	227.2	226.9	226.8	226.5	226.2	226.0	225.7
125°	251.0	250.7	250.3	249.9	249.6	249.2	248.9	248.5
127.5°	274.4	273.8	273.3	272.9	272.5	272.1	271.6	271.3
130°	289.8	289.4	289.1	288.6	288.0	287.4	286.8	286.1
132.5°	304.9	304.4	304.0	303.5	303.1	302.6	302.1	301.6
135°	327.4	327.1	326.7	326.5	326.3	326.1	325.9	325.7
137.5°	349.5	349.1	348.7	348.3	347.9	347.7	347.3	347.0
140°	363.9	363.8	363.7	363.4	362.7	362.1	361.5	360.9
142.5°	377.5	377.4	377.3	377.0	376.6	376.0	375.6	375.1
145°	397.4	397.3	397.3	397.1	396.7	396.4	396.0	395.7
147.5°	416.3	416.3	416.3	416.1	415.5	414.9	414.4	413.8
150°	427.9	427.9	427.9	427.7	427.1	426.6	426.1	425.5
152.5°	438.5	438.7	438.9	438.7	438.3	437.7	437.3	436.8
155°	454.1	454.5	454.9	454.7	454.1	453.4	452.8	452.2
157.5°	467.5	467.9	468.2	468.1	467.7	467.2	466.6	466.2
160°	475.7	476.2	476.6	476.6	476.3	475.9	475.5	475.2
162.5°	483.5	483.9	484.4	484.3	483.8	483.1	482.6	482.0
165°	493.3	493.8	494.4	494.3	493.7	493.0	492.4	491.8
167.5°	501.2	501.8	502.3	502.3	501.8	501.2	500.7	500.1
170°	505.6	506.2	506.8	506.8	506.2	505.6	505.0	504.4
172.5°	509.0	509.5	510.1	510.1	509.4	508.8	508.2	507.6
175°	512.6	513.2	513.7	513.7	513.1	512.5	511.8	511.2
177.5°	514.3	514.8	515.1	515.1	514.6	514.2	513.6	513.1
180°	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4

(END OF REPORT)