

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333085-830

Luminaire Tested: **S124RDIW-S1020D1050U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333085-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S1020D1050U830-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1050 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7885.4 lumens
Efficiency: N/A
Efficacy: 128.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 61.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333085-830

CATALOG NUMBER: S124RDIW-S1020D1050U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333085-830

CATALOG NUMBER: S124RDIW-S1020D1050U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50				
1	98	94	90	87	90	87	83	81	73	71	69	61	60	58	50	49	48	43				
2	89	82	76	71	82	76	71	66	65	61	57	54	51	49	44	42	41	36				
3	82	72	65	60	75	67	61	56	57	53	49	48	45	42	39	37	35	31				
4	75	64	57	51	69	60	53	48	51	46	42	43	39	36	35	33	30	27				
5	69	57	49	43	63	53	46	41	46	40	36	39	34	31	32	29	27	23				
6	63	52	44	38	58	48	41	36	41	36	32	35	31	27	29	26	23	21				
7	59	47	39	33	54	43	36	31	37	32	28	32	28	24	27	23	21	18				
8	55	42	35	29	50	40	33	28	34	29	25	29	25	22	25	21	19	16				
9	51	39	31	26	47	36	30	25	31	26	22	27	23	20	23	19	17	15				
10	48	36	28	24	44	33	27	22	29	24	20	25	21	18	21	18	16	14				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13739	13739	13739
5°	13771	13602	13686
10°	13684	13439	13439
15°	13527	13157	13059
20°	13311	12785	12550
25°	13036	12351	12038
30°	12767	11893	11395
35°	12471	11417	10749
40°	12113	10877	10053
45°	11783	10340	9344
50°	11408	9722	8593
55°	11005	9080	7776
60°	10563	8375	6944
65°	10157	7494	6124
70°	9567	6522	5200
75°	8821	5405	4226
80°	7694	4119	3877
85°	6521	3742	3501



TEST NUMBER: P333085-830

CATALOG NUMBER: S124RDIW-S1020D1050U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.9	2.0
10°-20°	445.8	5.7
20°-30°	643.8	8.2
30°-40°	729.7	9.3
40°-50°	704.7	8.9
50°-60°	586.0	7.4
60°-70°	404.6	5.1
70°-80°	205.1	2.6
80°-90°	56.3	0.7
90°-100°	43.7	0.6
100°-110°	278.4	3.5
110°-120°	532.6	6.8
120°-130°	676.2	8.6
130°-140°	723.4	9.2
140°-150°	676.5	8.6
150°-160°	545.5	6.9
160°-170°	351.9	4.5
170°-180°	121.3	1.5
0°-30°	1249.5	15.8
0°-40°	1979.2	25.1
0°-60°	3269.8	41.5
0°-90°	3935.9	49.9
90°-120°	854.7	10.8
90°-150°	2930.8	37.2
90°-180°	3949.0	50.1
0°-180°	7885.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1702	1702	1702	1702	1702	
5°	1699	1694	1678	1691	1689	161
15°	1618	1606	1574	1571	1562	456
25°	1464	1438	1387	1365	1351	674
35°	1265	1222	1158	1115	1091	790
45°	1032	982	906	844	818	795
55°	782	728	645	580	552	699
65°	532	474	392	338	321	525
75°	283	234	173	145	136	299
85°	70	46	40	38	38	79
90°	3	13	21	27	29	6
95°	52	22	21	26	28	68
105°	288	293	298	304	272	301
115°	537	539	539	540	540	528
125°	754	758	756	759	760	673
135°	936	935	939	941	942	721
145°	1079	1082	1082	1083	1085	674
155°	1183	1184	1181	1185	1182	545
165°	1248	1244	1243	1250	1242	353
175°	1277	1271	1272	1280	1269	122
180°	1277	1277	1277	1277	1277	



TEST NUMBER: P333085-830

CATALOG NUMBER: S124RDIW-S1020D1050U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9
2.5°	1706.1	1705.2	1704.2	1703.4	1702.4	1700.6	1698.1	1695.5	1693.0	1690.5	1693.0
5°	1699.3	1698.2	1697.0	1695.8	1694.7	1692.3	1688.9	1685.5	1682.0	1678.5	1681.4
7.5°	1683.9	1682.7	1681.5	1680.3	1679.0	1676.2	1671.7	1667.2	1662.6	1658.1	1660.0
10°	1669.3	1667.9	1666.4	1665.0	1663.6	1660.2	1655.0	1649.8	1644.5	1639.4	1640.5
12.5°	1650.6	1648.9	1647.2	1645.6	1643.9	1639.9	1633.8	1627.7	1621.6	1615.4	1616.1
15°	1618.5	1615.9	1613.4	1610.7	1608.1	1603.2	1595.9	1588.7	1581.5	1574.2	1573.7
17.5°	1579.7	1575.9	1572.2	1568.4	1564.6	1558.4	1549.7	1541.1	1532.4	1523.6	1522.0
20°	1549.4	1545.7	1541.9	1538.1	1534.4	1527.6	1517.8	1507.9	1498.1	1488.2	1485.9
22.5°	1516.1	1511.8	1507.6	1503.4	1499.2	1491.8	1481.3	1470.7	1460.2	1449.6	1446.1
25°	1463.5	1458.2	1453.0	1447.8	1442.6	1434.1	1422.2	1410.3	1398.5	1386.6	1381.7
27.5°	1408.2	1401.7	1395.2	1388.6	1382.1	1372.4	1359.7	1347.1	1334.4	1321.6	1315.6
30°	1369.6	1362.4	1355.2	1347.9	1340.7	1330.2	1316.6	1303.0	1289.4	1275.8	1268.6
32.5°	1329.0	1320.8	1312.6	1304.5	1296.3	1285.2	1271.1	1257.1	1242.9	1228.9	1220.5
35°	1265.4	1256.1	1246.8	1237.6	1228.3	1216.4	1201.9	1187.5	1173.0	1158.5	1148.7
37.5°	1197.3	1187.8	1178.3	1168.7	1159.1	1146.3	1130.3	1114.3	1098.2	1082.1	1071.1
40°	1149.4	1139.8	1130.3	1120.7	1111.2	1098.2	1081.7	1065.1	1048.6	1032.1	1019.9
42.5°	1103.5	1093.5	1083.5	1073.5	1063.5	1049.8	1032.6	1015.4	998.2	981.0	968.7
45°	1032.1	1021.4	1010.7	999.9	989.2	975.2	957.8	940.5	923.0	905.7	891.6
47.5°	958.4	947.3	936.2	925.2	914.1	899.6	881.5	863.4	845.3	827.3	812.6
50°	908.3	897.0	885.7	874.4	863.1	848.2	829.7	811.2	792.6	774.1	759.6
52.5°	857.2	846.1	835.1	824.1	812.9	798.0	778.9	760.0	740.9	722.0	707.3
55°	781.9	770.3	758.7	747.2	735.6	720.4	701.5	682.7	663.9	645.1	630.0
57.5°	707.4	695.3	683.2	671.2	659.2	643.9	625.4	606.8	588.2	569.8	554.5
60°	654.2	642.6	631.0	619.4	607.8	592.8	574.3	555.7	537.2	518.7	503.6
62.5°	606.2	594.2	582.1	570.0	558.1	542.5	523.5	504.5	485.5	466.6	452.6
65°	531.7	519.2	506.8	494.4	481.9	466.4	447.9	429.3	410.8	392.3	379.8
67.5°	454.3	442.3	430.5	418.5	406.5	392.0	374.8	357.6	340.4	323.2	312.5
70°	405.3	393.1	381.0	368.8	356.7	342.3	325.8	309.2	292.8	276.3	266.7
72.5°	353.2	342.1	331.1	320.2	309.2	295.9	280.3	264.7	249.1	233.6	225.4
75°	282.8	272.1	261.4	250.6	240.0	227.7	214.1	200.6	186.9	173.3	166.6
77.5°	211.4	202.3	193.2	184.1	175.0	164.9	153.9	143.0	132.0	120.9	117.1
80°	165.5	157.1	148.7	140.3	132.0	123.4	114.7	106.0	97.3	88.6	87.8
82.5°	125.9	118.2	110.5	102.7	95.1	88.7	83.8	78.8	73.8	68.8	68.1
85°	70.4	64.6	58.8	53.0	47.2	43.8	43.0	42.1	41.3	40.4	39.8
87.5°	24.5	23.2	21.8	20.4	19.0	18.4	18.5	18.6	18.7	18.8	18.9
90°	2.8	5.2	7.5	9.9	12.2	14.2	15.9	17.6	19.3	21.0	22.2
92.5°	12.1	12.2	12.3	12.4	12.5	13.5	15.2	16.9	18.6	20.3	21.5
95°	52.5	45.3	38.1	30.9	23.7	20.2	20.4	20.5	20.8	21.0	22.2
97.5°	111.5	116.0	120.6	125.1	129.5	120.0	96.2	72.6	48.9	25.2	25.4
100°	156.7	160.4	164.3	168.1	171.9	159.2	129.9	100.6	71.4	42.0	38.5
102.5°	207.1	209.8	212.6	215.5	218.2	217.7	214.0	210.1	206.2	202.5	163.5
105°	287.5	288.7	290.0	291.2	292.6	293.7	294.7	295.9	296.9	297.9	299.8
107.5°	362.1	362.8	363.4	364.0	364.7	365.7	367.1	368.6	370.0	371.5	372.4
110°	412.6	413.2	413.8	414.4	415.1	416.0	417.4	418.6	419.9	421.1	421.6



TEST NUMBER: P333085-830

CATALOG NUMBER: S124RDIW-S1020D1050U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	461.5	462.6	463.7	464.9	466.0	466.9	467.5	468.1	468.6	469.3	469.2
115°	536.7	537.3	538.0	538.6	539.2	539.4	539.2	539.0	538.9	538.6	539.0
117.5°	604.5	605.3	606.1	607.0	607.8	608.5	609.0	609.4	609.9	610.4	610.3
120°	650.4	651.2	652.1	652.9	653.7	654.0	653.8	653.7	653.4	653.2	653.7
122.5°	693.1	693.6	694.1	694.7	695.1	695.6	695.9	696.2	696.4	696.7	697.0
125°	754.4	755.3	756.1	757.0	757.8	758.0	757.6	757.1	756.8	756.3	757.0
127.5°	812.5	812.7	812.9	813.1	813.3	813.9	814.9	815.9	816.8	817.8	817.7
130°	849.9	850.2	850.4	850.6	850.7	851.2	851.9	852.4	853.1	853.8	853.9
132.5°	884.3	884.7	885.0	885.4	885.8	886.5	887.2	888.1	888.8	889.7	889.9
135°	935.9	935.7	935.5	935.2	935.0	935.4	936.2	937.1	937.9	938.8	939.1
137.5°	981.5	981.6	981.7	981.8	981.8	982.3	983.3	984.2	985.1	986.1	986.6
140°	1011.3	1011.7	1012.2	1012.6	1013.0	1013.4	1013.9	1014.3	1014.7	1015.1	1015.8
142.5°	1038.0	1038.8	1039.5	1040.4	1041.1	1041.6	1041.9	1042.1	1042.4	1042.6	1043.1
145°	1079.1	1079.8	1080.3	1081.0	1081.7	1081.9	1081.9	1081.9	1081.9	1081.9	1082.2
147.5°	1111.7	1113.0	1114.2	1115.3	1116.5	1117.0	1116.8	1116.6	1116.3	1116.2	1116.3
150°	1135.5	1136.3	1137.2	1138.0	1138.9	1139.2	1139.0	1138.8	1138.5	1138.3	1138.3
152.5°	1155.3	1156.0	1156.7	1157.3	1158.0	1158.2	1157.8	1157.4	1157.1	1156.7	1157.0
155°	1183.2	1183.5	1183.6	1183.8	1184.0	1183.8	1183.2	1182.6	1181.9	1181.3	1182.1
157.5°	1206.7	1206.5	1206.5	1206.3	1206.2	1205.8	1205.0	1204.3	1203.6	1202.9	1204.0
160°	1220.4	1219.8	1219.2	1218.5	1217.9	1217.5	1217.3	1217.0	1216.8	1216.6	1217.9
162.5°	1232.7	1231.9	1231.1	1230.2	1229.5	1228.9	1228.7	1228.5	1228.3	1228.0	1229.4
165°	1248.1	1247.1	1246.0	1244.9	1243.9	1243.4	1243.4	1243.4	1243.4	1243.4	1245.1
167.5°	1260.4	1259.2	1258.2	1257.1	1255.9	1255.4	1255.2	1255.1	1255.0	1254.8	1256.7
170°	1267.2	1265.9	1264.7	1263.4	1262.2	1261.6	1261.8	1262.1	1262.3	1262.4	1264.1
172.5°	1271.8	1270.5	1269.2	1268.0	1266.7	1266.2	1266.4	1266.6	1266.9	1267.1	1268.8
175°	1276.8	1275.5	1274.2	1273.0	1271.7	1271.2	1271.4	1271.6	1271.8	1272.1	1273.9
177.5°	1279.0	1277.9	1276.7	1275.5	1274.3	1273.9	1274.2	1274.6	1274.9	1275.3	1276.6
180°	1276.8	1276.8	1276.8	1276.8	1276.8	1276.8	1276.8	1276.8	1276.8	1276.8	1276.8



TEST NUMBER: P333085-830

CATALOG NUMBER: S124RDIW-S1020D1050U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9	1701.9
2.5°	1695.5	1698.1	1700.6	1701.9	1701.6	1701.4	1701.1	1700.9
5°	1684.2	1687.2	1690.1	1691.2	1690.6	1690.1	1689.5	1688.9
7.5°	1661.9	1663.7	1665.6	1666.0	1665.1	1664.2	1663.2	1662.3
10°	1641.7	1642.9	1644.0	1644.0	1642.9	1641.7	1640.5	1639.4
12.5°	1616.7	1617.5	1618.2	1617.7	1616.1	1614.5	1612.9	1611.3
15°	1573.1	1572.4	1571.9	1570.6	1568.6	1566.5	1564.5	1562.5
17.5°	1520.4	1518.8	1517.2	1514.9	1511.7	1508.7	1505.6	1502.5
20°	1483.6	1481.3	1478.9	1475.9	1472.2	1468.4	1464.6	1460.8
22.5°	1442.7	1439.2	1435.8	1432.5	1429.4	1426.3	1423.2	1420.2
25°	1376.7	1371.8	1366.9	1362.9	1360.1	1357.2	1354.2	1351.4
27.5°	1309.5	1303.4	1297.3	1292.2	1288.1	1283.8	1279.7	1275.5
30°	1261.3	1254.1	1246.8	1240.9	1236.2	1231.6	1227.0	1222.4
32.5°	1212.1	1203.7	1195.3	1188.9	1184.5	1180.1	1175.7	1171.3
35°	1138.8	1129.0	1119.1	1111.6	1106.4	1101.2	1096.0	1090.7
37.5°	1060.2	1049.1	1038.1	1030.0	1024.8	1019.5	1014.4	1009.2
40°	1007.8	995.6	983.4	974.8	969.6	964.3	959.1	953.9
42.5°	956.2	943.9	931.4	922.6	917.1	911.6	906.2	900.8
45°	877.3	863.1	848.9	839.2	834.1	828.8	823.6	818.4
47.5°	797.9	783.2	768.4	758.2	752.4	746.7	740.9	735.3
50°	745.1	730.7	716.1	706.2	700.7	695.1	689.7	684.2
52.5°	692.5	677.8	663.1	652.9	647.1	641.4	635.7	630.0
55°	614.9	599.9	584.8	574.6	569.0	563.5	558.1	552.5
57.5°	539.1	523.9	508.6	498.9	494.6	490.5	486.4	482.2
60°	488.5	473.4	458.5	448.6	443.9	439.3	434.7	430.1
62.5°	438.8	424.8	410.9	402.1	398.4	394.7	391.0	387.3
65°	367.3	354.9	342.4	334.5	331.0	327.5	324.0	320.6
67.5°	301.7	291.1	280.3	273.1	269.2	265.4	261.6	257.8
70°	257.1	247.6	238.1	231.8	228.9	226.0	223.1	220.3
72.5°	217.2	209.1	200.9	195.5	192.7	190.1	187.5	184.8
75°	160.0	153.4	146.7	142.5	140.7	139.0	137.2	135.5
77.5°	113.2	109.3	105.4	103.2	102.6	102.2	101.6	101.1
80°	86.9	86.1	85.1	84.5	84.3	84.0	83.7	83.4
82.5°	67.5	66.9	66.3	65.8	65.5	65.2	64.9	64.7
85°	39.2	38.6	38.1	37.8	37.8	37.8	37.8	37.8
87.5°	18.9	18.9	18.9	19.0	19.4	19.7	20.0	20.4
90°	23.6	24.8	26.1	27.0	27.3	27.8	28.2	28.7
92.5°	22.8	24.0	25.4	26.0	26.1	26.2	26.3	26.4
95°	23.6	24.8	26.1	26.9	27.1	27.2	27.5	27.7
97.5°	25.4	25.6	25.7	25.9	26.1	26.3	26.5	26.8
100°	34.8	31.2	27.6	25.9	26.1	26.3	26.5	26.8
102.5°	124.6	85.7	46.8	27.3	27.3	27.4	27.4	27.5
105°	301.8	303.7	305.6	302.7	295.1	287.5	279.8	272.2
107.5°	373.3	374.3	375.2	376.1	376.9	377.7	378.5	379.3
110°	422.0	422.4	422.8	423.4	424.0	424.6	425.3	425.9



TEST NUMBER: P333085-830

CATALOG NUMBER: S124RDIW-S1020D1050U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	469.1	469.0	468.9	469.3	470.1	470.9	471.7	472.5
115°	539.4	539.9	540.3	540.5	540.5	540.5	540.5	540.5
117.5°	610.2	610.2	610.1	610.0	609.9	609.8	609.7	609.6
120°	654.0	654.5	654.9	654.9	654.5	654.0	653.7	653.2
122.5°	697.3	697.5	697.8	697.7	697.3	696.8	696.4	696.0
125°	757.6	758.3	758.8	759.3	759.5	759.7	760.0	760.2
127.5°	817.6	817.5	817.3	817.2	817.0	816.8	816.6	816.5
130°	854.1	854.4	854.6	854.7	854.7	854.7	854.7	854.7
132.5°	890.0	890.3	890.5	890.5	890.3	890.1	890.0	889.9
135°	939.6	940.0	940.5	940.8	941.3	941.7	942.2	942.5
137.5°	987.0	987.5	988.0	988.2	988.0	987.9	987.8	987.6
140°	1016.4	1017.0	1017.7	1018.1	1018.3	1018.5	1018.7	1019.0
142.5°	1043.6	1044.1	1044.5	1044.7	1044.8	1044.8	1044.9	1044.9
145°	1082.4	1082.6	1082.8	1083.2	1083.5	1084.0	1084.4	1084.9
147.5°	1116.5	1116.6	1116.8	1117.0	1117.3	1117.5	1117.7	1117.9
150°	1138.3	1138.3	1138.3	1138.4	1138.6	1138.9	1139.1	1139.3
152.5°	1157.3	1157.6	1158.0	1158.1	1158.0	1157.8	1157.7	1157.6
155°	1183.0	1183.8	1184.7	1184.8	1184.1	1183.6	1182.9	1182.2
157.5°	1205.0	1206.2	1207.3	1207.3	1206.2	1205.0	1204.0	1202.9
160°	1219.2	1220.4	1221.7	1221.7	1220.4	1219.2	1217.9	1216.6
162.5°	1230.6	1231.9	1233.1	1233.1	1231.6	1230.2	1228.8	1227.3
165°	1246.8	1248.5	1250.2	1250.0	1248.1	1246.2	1244.3	1242.4
167.5°	1258.6	1260.5	1262.3	1262.2	1260.1	1257.9	1255.8	1253.7
170°	1265.8	1267.5	1269.2	1269.0	1266.9	1264.8	1262.6	1260.6
172.5°	1270.5	1272.1	1273.8	1273.6	1271.2	1268.9	1266.7	1264.3
175°	1275.8	1277.7	1279.7	1279.3	1276.8	1274.2	1271.7	1269.1
177.5°	1278.0	1279.3	1280.7	1280.3	1278.3	1276.3	1274.2	1272.2
180°	1276.8	1276.8	1276.8	1276.8	1276.8	1276.8	1276.8	1276.8

(END OF REPORT)