

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332173-940

Luminaire Tested: **S123DIW-S775D1320U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332173-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S775D1320U940-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1320 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6909.1 lumens
Efficiency: N/A
Efficacy: 112.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 61.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332173-940

CATALOG NUMBER: S123DIW-S775D1320U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332173-940

CATALOG NUMBER: S123DIW-S775D1320U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48	41
1	96	91	88	84	87	83	80	77	68	66	64	55	53	52	42	41	40	34
2	87	80	74	69	79	73	68	63	60	56	53	48	45	43	37	35	34	29
3	79	70	63	57	72	64	58	53	53	48	44	42	39	36	33	31	29	24
4	73	62	54	48	66	57	50	45	47	42	38	38	34	31	29	27	25	21
5	67	55	47	41	60	51	44	38	42	37	33	34	30	27	26	24	22	18
6	61	49	41	36	56	45	38	33	38	32	28	31	27	24	24	21	19	16
7	57	44	37	31	51	41	34	29	34	29	25	28	24	21	22	19	17	14
8	52	40	33	27	48	37	30	26	31	26	22	25	21	19	20	17	15	13
9	49	37	29	24	44	34	27	23	28	23	20	23	19	17	18	16	14	11
10	46	34	27	22	42	31	25	20	26	21	18	22	18	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11689	11689	11689
5°	11743	11581	11662
10°	11664	11481	11552
15°	11529	11352	11373
20°	11369	11165	11176
25°	11156	10946	10923
30°	10920	10700	10618
35°	10674	10441	10306
40°	10418	10153	9997
45°	10135	9893	9651
50°	9851	9568	9302
55°	9481	9233	8955
60°	9104	8844	8564
65°	8777	8420	8155
70°	8286	7934	7582
75°	7573	7303	6991
80°	6831	6540	6484
85°	5990	5768	5545



TEST NUMBER: P332173-940

CATALOG NUMBER: S123DIW-S775D1320U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.3	1.5
10°-20°	288.8	4.2
20°-30°	426.6	6.2
30°-40°	498.4	7.2
40°-50°	501.0	7.3
50°-60°	440.1	6.4
60°-70°	327.9	4.7
70°-80°	186.8	2.7
80°-90°	58.0	0.8
90°-100°	95.9	1.4
100°-110°	287.1	4.2
110°-120°	488.2	7.1
120°-130°	642.2	9.3
130°-140°	721.9	10.4
140°-150°	709.6	10.3
150°-160°	597.3	8.6
160°-170°	397.6	5.8
170°-180°	139.2	2.0
0°-30°	817.7	11.8
0°-40°	1316.1	19.0
0°-60°	2257.3	32.7
0°-90°	2829.9	41.0
90°-120°	871.3	12.6
90°-150°	2944.9	42.6
90°-180°	4079.0	59.0
0°-180°	6909.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1086	1086	1086	1086	1086	
5°	1087	1082	1072	1081	1079	103
15°	1035	1030	1019	1025	1021	292
25°	939	933	922	922	920	432
35°	812	806	795	789	784	508
45°	666	662	650	639	634	514
55°	505	504	492	482	477	452
65°	345	340	331	323	320	340
75°	182	178	176	171	168	195
85°	48	47	47	45	45	53
90°	1	13	28	32	35	7
95°	68	76	86	90	90	77
105°	260	263	273	273	275	279
115°	492	495	493	494	493	486
125°	719	723	720	716	711	641
135°	933	940	939	935	932	719
145°	1132	1135	1138	1137	1132	707
155°	1296	1297	1298	1302	1294	597
165°	1412	1409	1409	1415	1408	398
175°	1469	1464	1464	1470	1463	139
180°	1472	1472	1472	1472	1472	



TEST NUMBER: P332173-940

CATALOG NUMBER: S123DIW-S775D1320U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9
2.5°	1089.6	1089.0	1088.3	1087.6	1087.0	1085.7	1083.9	1082.1	1080.2	1078.4	1080.0
5°	1086.8	1085.7	1084.8	1083.7	1082.6	1081.0	1078.7	1076.5	1074.2	1071.8	1074.0
7.5°	1076.2	1075.1	1074.1	1073.1	1072.0	1070.3	1067.9	1065.6	1063.2	1060.9	1062.7
10°	1067.2	1066.1	1065.1	1064.1	1063.1	1061.2	1058.5	1055.8	1053.1	1050.4	1052.3
12.5°	1055.3	1054.4	1053.6	1052.7	1051.8	1050.1	1047.6	1045.0	1042.5	1039.9	1041.3
15°	1034.6	1033.7	1032.9	1032.1	1031.2	1029.5	1026.7	1024.0	1021.4	1018.7	1020.3
17.5°	1010.4	1009.3	1008.3	1007.2	1006.1	1004.2	1001.6	998.8	996.1	993.5	994.6
20°	992.5	991.2	990.1	988.8	987.6	985.5	982.8	980.2	977.5	974.7	975.6
22.5°	972.3	971.1	969.8	968.6	967.3	965.4	962.7	960.0	957.3	954.6	955.3
25°	939.3	938.1	936.8	935.6	934.3	932.4	929.6	926.9	924.3	921.6	921.8
27.5°	904.0	902.8	901.6	900.4	899.2	897.2	894.2	891.4	888.4	885.5	885.6
30°	878.6	877.5	876.6	875.5	874.4	872.4	869.6	866.7	863.8	860.9	860.9
32.5°	853.2	851.9	850.4	849.1	847.7	846.0	843.6	841.4	839.2	837.0	835.8
35°	812.3	811.1	809.9	808.6	807.4	805.4	802.6	800.0	797.3	794.6	793.4
37.5°	770.4	768.9	767.3	765.7	764.2	762.1	759.3	756.5	753.8	751.1	749.6
40°	741.4	740.1	738.9	737.6	736.4	734.3	731.4	728.5	725.6	722.6	721.0
42.5°	712.2	710.8	709.4	708.0	706.6	704.5	701.5	698.6	695.7	692.8	691.2
45°	665.8	664.9	664.1	663.3	662.4	660.7	657.9	655.2	652.6	649.9	647.4
47.5°	619.6	618.4	617.2	616.0	614.7	612.9	610.4	607.9	605.3	602.8	600.3
50°	588.3	587.2	586.1	585.1	584.1	582.2	579.5	576.8	574.1	571.4	569.2
52.5°	555.4	554.6	553.9	553.2	552.5	550.7	547.9	545.0	542.2	539.3	537.3
55°	505.2	504.9	504.7	504.5	504.3	502.8	500.2	497.5	494.7	492.0	489.8
57.5°	457.4	456.6	455.9	455.2	454.5	453.1	450.9	448.7	446.6	444.4	442.4
60°	422.9	422.8	422.6	422.3	422.1	420.8	418.3	415.8	413.3	410.8	408.9
62.5°	392.4	391.8	391.3	390.7	390.2	388.7	386.2	383.7	381.2	378.7	376.8
65°	344.6	343.5	342.4	341.4	340.4	338.9	336.7	334.7	332.6	330.6	328.9
67.5°	293.9	293.0	292.1	291.1	290.3	289.0	287.5	285.9	284.3	282.8	281.2
70°	263.3	262.1	260.8	259.6	258.3	257.1	255.8	254.6	253.3	252.1	250.7
72.5°	231.2	230.2	229.3	228.5	227.6	226.4	225.0	223.6	222.1	220.7	219.5
75°	182.1	181.2	180.4	179.6	178.8	178.0	177.4	176.7	176.1	175.6	174.5
77.5°	138.6	138.1	137.7	137.2	136.7	136.2	135.4	134.6	133.9	133.1	132.4
80°	110.2	109.6	109.0	108.3	107.7	107.2	106.7	106.4	105.9	105.5	105.3
82.5°	82.6	82.4	82.3	82.1	82.0	81.9	81.9	81.8	81.7	81.6	81.2
85°	48.5	48.2	47.7	47.3	46.9	46.7	46.7	46.7	46.7	46.7	46.3
87.5°	19.6	19.7	19.7	19.7	19.7	20.0	20.5	21.0	21.5	22.0	22.0
90°	1.2	3.7	6.3	8.8	11.4	14.4	17.7	21.0	24.4	27.7	28.8
92.5°	28.0	29.7	31.5	33.3	35.0	36.8	38.7	40.6	42.5	44.4	45.2
95°	68.2	70.0	71.9	73.7	75.4	77.4	79.5	81.5	83.6	85.6	86.6
97.5°	121.2	122.5	123.9	125.2	126.5	128.0	129.5	130.9	132.4	133.9	135.1
100°	157.3	158.8	160.3	161.9	163.5	164.9	166.1	167.5	168.7	170.0	170.8
102.5°	198.9	199.8	200.8	201.7	202.6	203.9	205.6	207.3	209.0	210.7	211.5
105°	260.2	260.7	261.3	261.7	262.3	263.7	266.0	268.3	270.6	273.0	273.0
107.5°	331.4	331.8	332.1	332.4	332.7	333.3	334.2	335.2	336.1	337.0	337.9
110°	375.9	376.4	376.9	377.4	377.9	378.4	379.0	379.5	380.0	380.5	381.6



TEST NUMBER: P332173-940

CATALOG NUMBER: S123DIW-S775D1320U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	422.1	422.4	422.8	423.0	423.4	423.6	423.7	423.7	423.9	424.0	425.3
115°	491.5	492.3	493.0	493.8	494.6	494.7	494.2	493.7	493.2	492.7	492.9
117.5°	561.4	561.9	562.4	562.9	563.5	563.4	562.7	562.0	561.3	560.7	560.6
120°	604.8	606.4	608.0	609.5	611.0	611.2	609.8	608.6	607.3	606.0	605.7
122.5°	650.2	651.3	652.5	653.6	654.7	655.0	654.2	653.6	652.9	652.3	651.6
125°	719.3	720.1	720.9	721.7	722.5	722.6	722.0	721.6	721.0	720.5	719.5
127.5°	783.2	784.9	786.5	788.1	789.8	790.3	789.8	789.2	788.6	788.1	786.6
130°	825.7	827.8	829.9	832.0	834.0	834.6	833.8	833.1	832.3	831.5	830.5
132.5°	868.3	870.4	872.4	874.5	876.6	877.3	876.7	876.2	875.6	875.0	873.8
135°	933.4	934.9	936.4	937.9	939.5	940.1	939.9	939.6	939.3	939.1	938.1
137.5°	993.5	994.7	996.0	997.3	998.6	999.6	1000.2	1000.9	1001.6	1002.3	1001.1
140°	1035.1	1036.3	1037.7	1038.9	1040.3	1041.0	1041.3	1041.5	1041.8	1042.1	1041.8
142.5°	1073.0	1074.3	1075.6	1076.9	1078.2	1079.1	1079.5	1080.0	1080.4	1080.9	1080.7
145°	1132.2	1132.7	1133.3	1133.8	1134.3	1135.0	1135.7	1136.5	1137.3	1138.0	1137.7
147.5°	1184.0	1185.0	1185.9	1186.9	1187.8	1188.6	1189.3	1190.0	1190.7	1191.4	1191.4
150°	1220.1	1220.7	1221.2	1221.6	1222.2	1222.7	1223.2	1223.7	1224.2	1224.8	1224.8
152.5°	1249.7	1250.4	1251.2	1251.9	1252.6	1253.1	1253.5	1253.7	1254.1	1254.4	1254.8
155°	1296.5	1296.5	1296.5	1296.5	1296.5	1296.6	1296.8	1297.1	1297.4	1297.6	1298.7
157.5°	1336.2	1336.0	1335.6	1335.3	1335.0	1335.0	1335.2	1335.3	1335.6	1335.8	1336.9
160°	1361.2	1360.8	1360.2	1359.7	1359.1	1358.9	1358.9	1358.9	1358.9	1358.9	1360.2
162.5°	1383.4	1382.7	1382.0	1381.3	1380.5	1380.3	1380.5	1380.7	1380.9	1381.1	1382.4
165°	1412.1	1411.3	1410.6	1409.8	1409.1	1408.6	1408.6	1408.6	1408.6	1408.6	1410.2
167.5°	1435.0	1434.0	1433.0	1431.9	1430.9	1430.5	1430.7	1430.9	1431.1	1431.3	1432.9
170°	1448.0	1447.0	1445.9	1444.9	1443.9	1443.3	1443.3	1443.3	1443.3	1443.3	1445.1
172.5°	1458.1	1457.1	1456.1	1455.1	1454.0	1453.5	1453.5	1453.5	1453.5	1453.5	1455.1
175°	1468.8	1467.8	1466.8	1465.7	1464.6	1464.2	1464.2	1464.2	1464.2	1464.2	1465.7
177.5°	1473.2	1472.4	1471.5	1470.7	1469.9	1469.5	1469.5	1469.5	1469.5	1469.5	1470.7
180°	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3



TEST NUMBER: P332173-940

CATALOG NUMBER: S123DIW-S775D1320U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9
2.5°	1081.7	1083.4	1085.0	1085.8	1085.7	1085.5	1085.3	1085.1
5°	1076.0	1078.1	1080.2	1081.0	1080.6	1080.2	1079.8	1079.3
7.5°	1064.6	1066.5	1068.4	1069.2	1068.9	1068.6	1068.4	1068.2
10°	1054.2	1056.0	1057.8	1058.6	1058.2	1057.7	1057.4	1056.9
12.5°	1042.7	1044.0	1045.4	1046.0	1045.7	1045.4	1045.3	1045.0
15°	1022.0	1023.6	1025.3	1025.5	1024.2	1023.0	1021.8	1020.6
17.5°	995.8	996.9	998.1	998.4	998.0	997.6	997.1	996.7
20°	976.4	977.2	978.1	978.2	977.6	977.0	976.3	975.7
22.5°	955.9	956.6	957.3	957.2	956.4	955.6	954.8	954.0
25°	921.9	922.2	922.4	922.2	921.6	921.0	920.3	919.7
27.5°	885.8	886.0	886.2	885.8	885.1	884.3	883.5	882.7
30°	860.9	860.9	860.9	860.1	858.7	857.2	855.8	854.3
32.5°	834.6	833.5	832.3	831.3	830.5	829.7	828.9	828.2
35°	792.1	790.9	789.6	788.5	787.4	786.4	785.3	784.3
37.5°	748.1	746.5	745.1	744.0	743.3	742.7	742.0	741.4
40°	719.3	717.7	716.0	714.8	714.0	713.1	712.3	711.5
42.5°	689.5	687.8	686.2	684.9	684.1	683.2	682.4	681.6
45°	644.9	642.4	639.9	638.1	637.1	636.1	635.0	634.0
47.5°	597.9	595.5	593.0	591.3	590.4	589.5	588.6	587.6
50°	566.9	564.5	562.3	560.5	559.3	558.0	556.8	555.5
52.5°	535.4	533.4	531.5	529.9	528.7	527.4	526.2	525.0
55°	487.5	485.2	483.0	481.3	480.2	479.2	478.1	477.2
57.5°	440.3	438.4	436.3	434.7	433.5	432.3	431.1	429.9
60°	407.1	405.2	403.3	401.9	400.8	399.8	398.8	397.8
62.5°	375.0	373.1	371.2	370.0	369.3	368.5	367.8	367.1
65°	327.2	325.6	323.9	322.7	322.1	321.5	320.8	320.2
67.5°	279.8	278.4	276.9	275.7	274.9	274.0	273.1	272.2
70°	249.2	247.7	246.3	245.0	244.0	243.0	241.9	240.9
72.5°	218.1	216.9	215.6	214.6	214.1	213.6	213.0	212.5
75°	173.4	172.5	171.4	170.6	170.0	169.3	168.7	168.1
77.5°	131.7	131.0	130.3	130.0	130.0	130.0	130.0	130.0
80°	105.1	104.9	104.7	104.6	104.6	104.6	104.6	104.6
82.5°	80.9	80.5	80.1	79.8	79.7	79.5	79.4	79.2
85°	45.8	45.5	45.0	44.9	44.9	44.9	44.9	44.9
87.5°	22.0	22.1	22.1	22.2	22.3	22.4	22.6	22.6
90°	29.8	30.9	31.8	32.6	33.2	33.7	34.2	34.7
92.5°	46.0	46.9	47.7	48.0	47.6	47.3	47.0	46.7
95°	87.7	88.6	89.7	90.2	90.2	90.2	90.2	90.2
97.5°	136.3	137.5	138.7	139.2	139.1	139.0	138.9	138.8
100°	171.6	172.3	173.1	173.7	174.2	174.8	175.3	175.8
102.5°	212.2	213.0	213.8	214.1	214.0	213.9	213.8	213.7
105°	273.0	273.0	273.0	273.2	273.8	274.2	274.7	275.3
107.5°	338.7	339.5	340.3	340.5	340.3	339.9	339.7	339.3
110°	382.5	383.6	384.6	384.9	384.3	383.9	383.3	382.8



TEST NUMBER: P332173-940

CATALOG NUMBER: S123DIW-S775D1320U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	426.4	427.7	428.9	429.4	429.4	429.3	429.2	429.1
115°	493.2	493.5	493.7	493.7	493.5	493.2	492.9	492.7
117.5°	560.6	560.5	560.4	560.1	559.4	558.7	557.9	557.2
120°	605.5	605.3	605.0	604.6	604.1	603.6	603.1	602.5
122.5°	650.9	650.2	649.6	648.9	648.2	647.5	646.8	646.0
125°	718.5	717.5	716.4	715.4	714.3	713.3	712.3	711.2
127.5°	785.2	783.7	782.3	781.0	779.8	778.6	777.5	776.2
130°	829.5	828.5	827.4	826.0	824.2	822.4	820.6	818.9
132.5°	872.5	871.3	870.1	868.8	867.4	866.0	864.6	863.3
135°	937.0	936.0	935.0	934.2	933.7	933.2	932.6	932.2
137.5°	1000.1	999.0	997.9	996.9	996.0	995.0	994.0	993.0
140°	1041.5	1041.3	1041.0	1040.0	1038.2	1036.3	1034.6	1032.8
142.5°	1080.4	1080.1	1079.9	1079.1	1077.6	1076.3	1074.9	1073.5
145°	1137.5	1137.3	1137.0	1136.4	1135.3	1134.3	1133.3	1132.2
147.5°	1191.4	1191.4	1191.4	1190.7	1189.2	1187.6	1186.1	1184.5
150°	1224.8	1224.8	1224.8	1224.0	1222.4	1220.9	1219.3	1217.8
152.5°	1255.2	1255.6	1256.0	1255.5	1254.2	1252.9	1251.5	1250.2
155°	1299.7	1300.7	1301.7	1301.4	1299.6	1297.8	1295.9	1294.1
157.5°	1337.9	1339.0	1340.2	1339.9	1338.5	1337.0	1335.6	1334.2
160°	1361.5	1362.8	1364.1	1364.2	1363.2	1362.2	1361.1	1360.0
162.5°	1383.7	1385.0	1386.3	1386.1	1384.5	1382.8	1381.2	1379.5
165°	1411.8	1413.3	1414.8	1414.7	1412.9	1411.1	1409.3	1407.5
167.5°	1434.5	1436.1	1437.7	1437.7	1436.1	1434.5	1432.9	1431.3
170°	1447.0	1448.8	1450.5	1450.5	1448.8	1447.0	1445.1	1443.3
172.5°	1456.7	1458.3	1459.9	1459.8	1458.0	1456.2	1454.4	1452.6
175°	1467.2	1468.8	1470.3	1470.2	1468.4	1466.6	1464.8	1463.0
177.5°	1471.9	1473.2	1474.4	1474.4	1472.8	1471.4	1470.0	1468.6
180°	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3	1472.3

(END OF REPORT)