

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333110-830

Luminaire Tested: **S124RDIW-S1195D1340U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333110-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S1195D1340U830-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8931.1 lumens
Efficiency: N/A
Efficacy: 117.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333110-830

CATALOG NUMBER: S124RDIW-S1195D1340U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333110-830

CATALOG NUMBER: S124RDIW-S1195D1340U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	107	107	107	107	99	99	99	99	84	84	84		70	70	70		57	57	57	51
1	98	94	90	87	91	87	84	81	74	72	69		62	60	59		51	50	49	43
2	90	82	76	71	83	76	71	67	65	61	58		55	52	49		45	43	41	37
3	82	73	65	60	75	67	61	56	58	53	49		49	45	42		40	38	35	31
4	75	64	57	51	69	60	53	48	51	46	42		43	39	36		36	33	31	27
5	69	58	50	44	64	54	46	41	46	41	36		39	35	32		33	29	27	24
6	64	52	44	38	59	48	41	36	42	36	32		35	31	28		30	26	24	21
7	59	47	39	33	54	44	37	32	38	32	28		32	28	25		27	24	21	19
8	55	43	35	30	51	40	33	28	34	29	25		30	25	22		25	22	19	17
9	51	39	31	26	47	36	30	25	32	26	22		27	23	20		23	20	17	15
10	48	36	29	24	44	33	27	23	29	24	20		25	21	18		21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15868	15868	15868
5°	15904	15709	15807
10°	15805	15521	15521
15°	15623	15195	15082
20°	15374	14766	14495
25°	15055	14264	13903
30°	14746	13736	13160
35°	14402	13186	12415
40°	13990	12562	11610
45°	13609	11942	10791
50°	13175	11228	9923
55°	12711	10486	8981
60°	12198	9671	8018
65°	11731	8653	7072
70°	11049	7532	6005
75°	10187	6245	4885
80°	8884	4761	4477
85°	7521	4326	4039



TEST NUMBER: P333110-830

CATALOG NUMBER: S124RDIW-S1195D1340U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	184.6	2.1
10°-20°	514.9	5.8
20°-30°	743.5	8.3
30°-40°	842.8	9.4
40°-50°	813.8	9.1
50°-60°	676.7	7.6
60°-70°	467.3	5.2
70°-80°	236.9	2.7
80°-90°	65.5	0.7
90°-100°	104.3	1.2
100°-110°	308.8	3.5
110°-120°	524.1	5.9
120°-130°	691.1	7.7
130°-140°	776.2	8.7
140°-150°	762.7	8.5
150°-160°	641.5	7.2
160°-170°	426.8	4.8
170°-180°	149.5	1.7
0°-30°	1443.1	16.2
0°-40°	2285.8	25.6
0°-60°	3776.4	42.3
0°-90°	4546.1	50.9
90°-120°	937.2	10.5
90°-150°	3167.3	35.5
90°-180°	4385.0	49.1
0°-180°	8931.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1966	1966	1966	1966	1966	
5°	1963	1956	1938	1953	1951	186
15°	1869	1854	1818	1815	1805	526
25°	1690	1661	1601	1576	1561	778
35°	1461	1412	1338	1288	1260	913
45°	1192	1134	1046	975	945	919
55°	903	841	745	669	638	807
65°	614	548	453	391	370	606
75°	327	270	200	167	157	345
85°	81	53	47	44	44	91
90°	4	17	27	34	37	9
95°	73	84	93	96	97	82
105°	285	286	291	295	298	302
115°	533	533	530	529	528	525
125°	776	776	775	772	770	692
135°	1001	1008	1008	1006	1002	774
145°	1216	1221	1222	1221	1218	761
155°	1394	1393	1392	1397	1392	641
165°	1517	1513	1511	1518	1513	427
175°	1578	1572	1571	1578	1571	150
180°	1580	1580	1580	1580	1580	



TEST NUMBER: P333110-830

CATALOG NUMBER: S124RDIW-S1195D1340U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6
2.5°	1970.4	1969.3	1968.3	1967.2	1966.1	1964.2	1961.2	1958.2	1955.3	1952.4	1955.3
5°	1962.6	1961.2	1959.9	1958.6	1957.3	1954.6	1950.6	1946.5	1942.6	1938.5	1941.8
7.5°	1944.8	1943.4	1942.0	1940.6	1939.2	1935.9	1930.7	1925.5	1920.2	1915.1	1917.2
10°	1928.0	1926.3	1924.7	1923.0	1921.3	1917.4	1911.5	1905.4	1899.4	1893.4	1894.7
12.5°	1906.3	1904.4	1902.4	1900.4	1898.6	1894.0	1887.0	1879.9	1872.7	1865.7	1866.5
15°	1869.3	1866.2	1863.3	1860.3	1857.3	1851.5	1843.2	1834.8	1826.5	1818.1	1817.4
17.5°	1824.5	1820.0	1815.7	1811.4	1807.0	1799.9	1789.8	1779.8	1769.7	1759.7	1757.8
20°	1789.5	1785.2	1780.8	1776.5	1772.2	1764.3	1752.9	1741.5	1730.1	1718.8	1716.1
22.5°	1751.0	1746.2	1741.3	1736.4	1731.5	1723.0	1710.7	1698.6	1686.4	1674.2	1670.2
25°	1690.2	1684.1	1678.1	1672.2	1666.1	1656.2	1642.6	1628.8	1615.1	1601.4	1595.7
27.5°	1626.4	1618.8	1611.3	1603.7	1596.1	1585.1	1570.4	1555.8	1541.1	1526.4	1519.4
30°	1581.9	1573.5	1565.1	1556.7	1548.4	1536.3	1520.6	1504.9	1489.2	1473.5	1465.1
32.5°	1534.8	1525.4	1516.0	1506.6	1497.1	1484.3	1468.0	1451.8	1435.5	1419.3	1409.6
35°	1461.4	1450.7	1440.0	1429.3	1418.6	1404.9	1388.2	1371.5	1354.7	1338.0	1326.6
37.5°	1382.9	1371.8	1360.7	1349.7	1338.7	1323.9	1305.4	1286.9	1268.4	1249.8	1237.1
40°	1327.5	1316.4	1305.4	1294.4	1283.3	1268.3	1249.2	1230.1	1211.1	1192.0	1178.0
42.5°	1274.5	1262.9	1251.3	1239.7	1228.2	1212.5	1192.6	1172.7	1152.9	1133.0	1118.7
45°	1192.0	1179.6	1167.2	1154.9	1142.6	1126.2	1106.3	1086.2	1066.1	1046.0	1029.6
47.5°	1106.8	1094.0	1081.3	1068.5	1055.7	1038.9	1018.0	997.1	976.3	955.5	938.4
50°	1049.0	1035.9	1022.9	1009.9	996.8	979.6	958.2	936.8	915.4	894.0	877.3
52.5°	990.0	977.2	964.5	951.7	939.0	921.5	899.7	877.7	855.7	833.8	816.8
55°	903.1	889.7	876.3	862.9	849.5	832.0	810.2	788.5	766.8	745.0	727.6
57.5°	816.9	803.0	789.1	775.2	761.3	743.7	722.3	700.8	679.4	658.0	640.4
60°	755.5	742.2	728.8	715.4	702.0	684.7	663.3	641.9	620.4	599.0	581.6
62.5°	700.1	686.3	672.3	658.5	644.5	626.6	604.6	582.7	560.7	538.9	522.7
65°	614.1	599.6	585.3	570.9	556.6	538.7	517.3	495.9	474.5	453.0	438.7
67.5°	524.6	510.9	497.1	483.3	469.6	452.7	432.8	413.0	393.1	373.2	360.9
70°	468.1	454.0	440.0	425.9	411.9	395.3	376.3	357.2	338.2	319.1	308.0
72.5°	407.8	395.2	382.5	369.8	357.0	341.7	323.7	305.7	287.7	269.7	260.2
75°	326.6	314.2	301.8	289.5	277.1	263.1	247.3	231.6	215.9	200.2	192.5
77.5°	244.1	233.7	223.1	212.6	202.1	190.5	177.8	165.1	152.4	139.7	135.2
80°	191.1	181.4	171.7	162.0	152.3	142.5	132.4	122.4	112.4	102.4	101.3
82.5°	145.4	136.5	127.6	118.7	109.8	102.5	96.7	91.0	85.2	79.5	78.7
85°	81.2	74.6	67.9	61.2	54.5	50.7	49.7	48.6	47.7	46.7	46.0
87.5°	28.5	26.9	25.4	23.8	22.2	21.6	21.8	21.9	22.1	22.2	22.3
90°	3.7	6.7	9.6	12.6	15.6	18.2	20.4	22.5	24.7	26.9	28.6
92.5°	26.2	29.6	33.0	36.4	39.9	42.3	43.8	45.3	46.8	48.4	49.4
95°	73.3	75.8	78.2	80.7	83.1	85.3	87.2	89.1	91.0	92.9	93.7
97.5°	128.1	130.1	132.1	133.9	135.9	138.0	140.3	142.5	144.7	146.9	147.9
100°	171.2	172.2	173.3	174.4	175.5	177.2	179.6	182.1	184.5	187.0	187.6
102.5°	216.1	216.6	217.0	217.4	217.8	219.1	221.4	223.7	225.8	228.1	228.8
105°	284.8	285.1	285.4	285.6	285.9	286.5	287.7	288.8	289.8	291.0	291.7
107.5°	356.9	357.2	357.6	357.9	358.3	358.4	358.6	358.8	359.0	359.1	359.9
110°	405.9	406.3	406.9	407.5	408.0	408.1	407.8	407.6	407.4	407.1	406.5



TEST NUMBER: P333110-830

CATALOG NUMBER: S124RDIW-S1195D1340U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	456.7	456.8	456.9	457.0	457.1	456.9	456.5	455.9	455.4	455.0	454.9
115°	532.9	532.9	532.9	532.9	532.9	532.7	532.2	531.6	531.0	530.5	530.3
117.5°	604.8	605.0	605.3	605.5	605.7	605.6	605.2	604.8	604.5	604.1	603.1
120°	652.7	653.8	654.9	656.0	657.0	657.2	656.4	655.6	654.8	653.9	652.6
122.5°	702.6	703.0	703.5	703.9	704.4	704.4	704.0	703.6	703.2	702.9	701.9
125°	776.2	776.2	776.2	776.2	776.2	776.1	775.8	775.5	775.2	775.0	774.4
127.5°	842.9	843.8	844.6	845.4	846.2	846.4	845.9	845.6	845.1	844.6	844.1
130°	889.9	890.7	891.6	892.3	893.2	893.5	893.5	893.5	893.5	893.5	893.0
132.5°	937.8	938.4	939.0	939.6	940.2	940.4	940.2	939.9	939.7	939.5	939.0
135°	1001.1	1002.8	1004.4	1006.0	1007.7	1008.4	1008.4	1008.4	1008.4	1008.4	1008.0
137.5°	1070.1	1070.8	1071.6	1072.3	1073.1	1073.7	1074.1	1074.6	1075.0	1075.4	1074.7
140°	1116.1	1116.5	1117.1	1117.7	1118.2	1118.4	1118.4	1118.4	1118.4	1118.4	1118.2
142.5°	1158.1	1158.6	1159.1	1159.7	1160.3	1160.4	1160.2	1160.0	1159.8	1159.5	1159.5
145°	1216.3	1217.4	1218.4	1219.6	1220.6	1221.3	1221.5	1221.8	1222.1	1222.4	1222.1
147.5°	1273.9	1275.3	1276.6	1277.9	1279.1	1279.7	1279.5	1279.3	1279.0	1278.8	1278.7
150°	1309.2	1310.2	1311.4	1312.4	1313.5	1314.0	1314.0	1314.0	1314.0	1314.0	1314.0
152.5°	1342.4	1343.0	1343.7	1344.3	1345.0	1345.5	1345.7	1345.9	1346.1	1346.3	1347.0
155°	1393.5	1393.5	1393.5	1393.5	1393.5	1393.4	1393.1	1392.8	1392.5	1392.3	1393.4
157.5°	1436.5	1436.1	1435.6	1435.0	1434.5	1434.3	1434.3	1434.2	1434.2	1434.1	1434.9
160°	1462.0	1461.7	1461.4	1461.1	1460.8	1460.6	1460.3	1460.1	1459.8	1459.5	1460.3
162.5°	1485.4	1484.7	1484.0	1483.3	1482.6	1482.1	1481.9	1481.6	1481.3	1481.0	1482.5
165°	1516.9	1516.2	1515.3	1514.5	1513.7	1513.1	1512.5	1511.9	1511.4	1510.8	1512.5
167.5°	1541.2	1540.0	1538.9	1537.8	1536.6	1536.1	1536.2	1536.2	1536.3	1536.3	1537.9
170°	1554.8	1553.5	1552.2	1550.8	1549.4	1548.9	1549.2	1549.4	1549.7	1549.9	1551.6
172.5°	1564.6	1563.5	1562.4	1561.2	1560.1	1559.5	1559.6	1559.6	1559.7	1559.7	1561.6
175°	1578.1	1576.7	1575.4	1574.0	1572.6	1571.8	1571.6	1571.3	1571.0	1570.7	1572.6
177.5°	1582.4	1581.4	1580.3	1579.2	1578.1	1577.6	1577.6	1577.6	1577.6	1577.6	1579.1
180°	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5



TEST NUMBER: P333110-830

CATALOG NUMBER: S124RDIW-S1195D1340U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6
2.5°	1958.2	1961.2	1964.2	1965.5	1965.2	1964.9	1964.6	1964.4
5°	1945.2	1948.5	1951.9	1953.2	1952.6	1951.9	1951.3	1950.6
7.5°	1919.3	1921.5	1923.6	1924.1	1923.1	1922.0	1920.9	1919.9
10°	1896.0	1897.3	1898.8	1898.8	1897.3	1896.0	1894.7	1893.4
12.5°	1867.3	1868.1	1868.9	1868.3	1866.5	1864.6	1862.7	1860.9
15°	1816.8	1816.1	1815.4	1813.9	1811.6	1809.2	1806.9	1804.6
17.5°	1756.0	1754.1	1752.2	1749.5	1746.0	1742.4	1738.9	1735.3
20°	1713.4	1710.7	1708.1	1704.6	1700.3	1695.9	1691.5	1687.2
22.5°	1666.2	1662.2	1658.2	1654.4	1650.9	1647.3	1643.8	1640.2
25°	1590.0	1584.3	1578.7	1574.1	1570.7	1567.4	1564.1	1560.8
27.5°	1512.4	1505.3	1498.4	1492.4	1487.6	1482.8	1478.0	1473.2
30°	1456.7	1448.4	1440.0	1433.1	1427.8	1422.5	1417.1	1411.7
32.5°	1399.9	1390.2	1380.4	1373.1	1368.0	1362.9	1357.8	1352.7
35°	1315.2	1303.9	1292.5	1283.8	1277.8	1271.8	1265.7	1259.7
37.5°	1224.4	1211.6	1199.0	1189.6	1183.6	1177.5	1171.6	1165.5
40°	1163.9	1149.9	1135.9	1125.8	1119.7	1113.7	1107.8	1101.7
42.5°	1104.4	1090.1	1075.7	1065.5	1059.1	1052.9	1046.6	1040.3
45°	1013.2	996.8	980.4	969.2	963.3	957.2	951.2	945.2
47.5°	921.4	904.5	887.5	875.6	869.0	862.4	855.7	849.1
50°	860.5	843.9	827.1	815.6	809.3	802.9	796.5	790.1
52.5°	799.8	782.9	765.8	754.0	747.4	740.8	734.1	727.5
55°	710.2	692.9	675.4	663.5	657.2	650.8	644.5	638.1
57.5°	622.7	605.0	587.4	576.2	571.4	566.5	561.7	556.9
60°	564.2	546.9	529.4	518.1	512.7	507.4	502.0	496.6
62.5°	506.7	490.7	474.6	464.4	460.1	455.9	451.6	447.3
65°	424.2	409.9	395.5	386.3	382.3	378.2	374.3	370.2
67.5°	348.6	336.1	323.8	315.4	310.9	306.5	302.1	297.7
70°	297.0	286.0	274.9	267.8	264.4	261.1	257.7	254.4
72.5°	250.8	241.4	232.0	225.7	222.6	219.6	216.5	213.4
75°	184.8	177.1	169.4	164.6	162.6	160.5	158.5	156.6
77.5°	130.7	126.2	121.8	119.2	118.6	118.0	117.4	116.8
80°	100.4	99.3	98.3	97.6	97.4	97.0	96.7	96.3
82.5°	78.0	77.3	76.5	76.0	75.7	75.3	75.0	74.6
85°	45.3	44.7	44.0	43.6	43.6	43.6	43.6	43.6
87.5°	22.3	22.4	22.4	22.7	23.1	23.5	23.8	24.2
90°	30.2	31.8	33.4	34.5	35.1	35.6	36.1	36.7
92.5°	50.3	51.4	52.3	53.0	53.3	53.6	53.9	54.3
95°	94.5	95.4	96.1	96.6	96.6	96.6	96.6	96.6
97.5°	148.9	149.9	150.8	151.4	151.4	151.4	151.4	151.4
100°	188.1	188.7	189.2	189.5	189.5	189.5	189.5	189.5
102.5°	229.6	230.4	231.1	231.6	231.9	232.1	232.2	232.5
105°	292.6	293.4	294.2	295.0	295.8	296.6	297.5	298.2
107.5°	360.6	361.4	362.2	362.5	362.5	362.4	362.4	362.3
110°	406.0	405.4	404.9	405.0	405.9	406.6	407.5	408.3



TEST NUMBER: P333110-830

CATALOG NUMBER: S124RDIW-S1195D1340U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	454.8	454.7	454.5	454.6	454.7	454.9	455.1	455.2
115°	530.0	529.7	529.4	529.1	528.9	528.6	528.3	528.1
117.5°	602.3	601.3	600.4	599.6	599.1	598.6	598.0	597.5
120°	651.3	649.9	648.6	648.1	648.7	649.2	649.8	650.3
122.5°	701.0	700.1	699.2	698.2	697.2	696.3	695.3	694.3
125°	773.9	773.4	772.8	772.2	771.8	771.2	770.6	770.1
127.5°	843.6	843.0	842.4	842.0	841.6	841.1	840.7	840.3
130°	892.5	891.9	891.4	890.6	889.5	888.3	887.3	886.2
132.5°	938.4	937.9	937.4	936.9	936.4	935.9	935.6	935.1
135°	1007.4	1006.8	1006.3	1005.6	1004.8	1004.0	1003.1	1002.3
137.5°	1074.0	1073.4	1072.6	1072.3	1072.5	1072.7	1072.8	1073.0
140°	1117.9	1117.7	1117.4	1117.1	1116.8	1116.5	1116.3	1116.1
142.5°	1159.4	1159.4	1159.3	1159.2	1159.2	1159.1	1159.1	1159.0
145°	1221.8	1221.5	1221.3	1220.8	1219.9	1219.1	1218.3	1217.5
147.5°	1278.4	1278.2	1278.0	1277.7	1277.4	1277.1	1277.0	1276.7
150°	1314.0	1314.0	1314.0	1313.9	1313.6	1313.3	1313.1	1312.9
152.5°	1347.6	1348.3	1349.0	1348.9	1348.2	1347.5	1346.8	1346.0
155°	1394.5	1395.5	1396.7	1396.7	1395.5	1394.5	1393.4	1392.3
157.5°	1435.7	1436.5	1437.4	1437.3	1436.3	1435.4	1434.5	1433.6
160°	1461.1	1462.0	1462.7	1462.4	1461.1	1459.8	1458.4	1457.1
162.5°	1483.9	1485.4	1486.9	1487.0	1485.5	1484.2	1482.9	1481.5
165°	1514.1	1515.7	1517.4	1517.7	1516.6	1515.4	1514.4	1513.3
167.5°	1539.5	1541.2	1542.8	1542.8	1541.1	1539.4	1537.8	1536.1
170°	1553.2	1554.8	1556.5	1556.3	1554.4	1552.6	1550.7	1548.8
172.5°	1563.4	1565.3	1567.2	1567.1	1565.2	1563.3	1561.4	1559.5
175°	1574.5	1576.4	1578.4	1578.4	1576.4	1574.5	1572.6	1570.7
177.5°	1580.6	1582.2	1583.7	1583.6	1581.9	1580.1	1578.4	1576.6
180°	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5

(END OF REPORT)