

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332161-940

Luminaire Tested: **S123DIW-S775D755U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332161-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S775D755U940-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 755 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5162.5 lumens
Efficiency: N/A
Efficacy: 114.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332161-940

CATALOG NUMBER: S123DIW-S775D755U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332161-940

CATALOG NUMBER: S123DIW-S775D755U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55
1	99	94	90	87	92	88	84	81	75	73	71	64	62	60	53	52	51	46
2	90	82	76	71	83	77	71	67	66	62	58	56	53	50	47	45	43	38
3	82	72	65	59	76	67	61	56	58	53	49	50	46	43	42	39	36	33
4	75	64	56	50	69	60	53	47	52	46	42	44	40	37	37	34	31	28
5	69	57	49	43	64	53	46	41	46	40	36	40	35	32	33	30	27	24
6	63	51	43	37	59	48	41	35	42	36	31	36	31	28	30	27	24	21
7	59	46	38	33	54	43	36	31	38	32	28	33	28	25	28	24	21	19
8	54	42	34	29	50	39	32	27	34	29	25	30	25	22	25	22	19	17
9	51	38	31	26	47	36	29	25	32	26	22	27	23	20	24	20	17	15
10	47	35	28	23	44	33	27	22	29	24	20	25	21	18	22	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11689	11689	11689
5°	11743	11581	11662
10°	11664	11481	11552
15°	11529	11352	11373
20°	11369	11165	11176
25°	11156	10946	10923
30°	10920	10700	10618
35°	10674	10441	10306
40°	10418	10153	9997
45°	10135	9893	9651
50°	9851	9568	9302
55°	9481	9233	8955
60°	9104	8844	8564
65°	8777	8420	8155
70°	8286	7934	7582
75°	7573	7303	6991
80°	6831	6540	6484
85°	5990	5768	5545



TEST NUMBER: P332161-940

CATALOG NUMBER: S123DIW-S775D755U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.3	2.0
10°-20°	288.8	5.6
20°-30°	426.6	8.3
30°-40°	498.4	9.7
40°-50°	501.0	9.7
50°-60°	440.1	8.5
60°-70°	327.9	6.4
70°-80°	186.8	3.6
80°-90°	56.1	1.1
90°-100°	54.9	1.1
100°-110°	164.3	3.2
110°-120°	279.4	5.4
120°-130°	367.5	7.1
130°-140°	413.1	8.0
140°-150°	406.1	7.9
150°-160°	341.9	6.6
160°-170°	227.6	4.4
170°-180°	79.7	1.5
0°-30°	817.7	15.8
0°-40°	1316.1	25.5
0°-60°	2257.3	43.7
0°-90°	2828.1	54.8
90°-120°	498.6	9.7
90°-150°	1685.3	32.6
90°-180°	2334.0	45.2
0°-180°	5162.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1086	1086	1086	1086	1086	
5°	1087	1082	1072	1081	1079	103
15°	1035	1030	1019	1025	1021	292
25°	939	933	922	922	920	432
35°	812	806	795	789	784	508
45°	666	662	650	639	634	514
55°	505	504	492	482	477	452
65°	345	340	331	323	320	340
75°	182	178	176	171	168	195
85°	48	47	47	45	45	53
90°	1	7	16	18	20	5
95°	39	44	49	52	52	44
105°	149	150	156	156	158	159
115°	281	283	282	283	282	278
125°	412	414	412	410	407	367
135°	534	538	537	535	533	411
145°	648	649	651	650	648	405
155°	742	742	743	745	741	341
165°	808	806	806	810	806	228
175°	840	838	838	841	837	80
180°	843	843	843	843	843	



TEST NUMBER: P332161-940

CATALOG NUMBER: S123DIW-S775D755U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9
2.5°	1089.6	1089.0	1088.3	1087.6	1087.0	1085.7	1083.9	1082.1	1080.2	1078.4	1080.0
5°	1086.8	1085.7	1084.8	1083.7	1082.6	1081.0	1078.7	1076.5	1074.2	1071.8	1074.0
7.5°	1076.2	1075.1	1074.1	1073.1	1072.0	1070.3	1067.9	1065.6	1063.2	1060.9	1062.7
10°	1067.2	1066.1	1065.1	1064.1	1063.1	1061.2	1058.5	1055.8	1053.1	1050.4	1052.3
12.5°	1055.3	1054.4	1053.6	1052.7	1051.8	1050.1	1047.6	1045.0	1042.5	1039.9	1041.3
15°	1034.6	1033.7	1032.9	1032.1	1031.2	1029.5	1026.7	1024.0	1021.4	1018.7	1020.3
17.5°	1010.4	1009.3	1008.3	1007.2	1006.1	1004.2	1001.6	998.8	996.1	993.5	994.6
20°	992.5	991.2	990.1	988.8	987.6	985.5	982.8	980.2	977.5	974.7	975.6
22.5°	972.3	971.1	969.8	968.6	967.3	965.4	962.7	960.0	957.3	954.6	955.3
25°	939.3	938.1	936.8	935.6	934.3	932.4	929.6	926.9	924.3	921.6	921.8
27.5°	904.0	902.8	901.6	900.4	899.2	897.2	894.2	891.4	888.4	885.5	885.6
30°	878.6	877.5	876.6	875.5	874.4	872.4	869.6	866.7	863.8	860.9	860.9
32.5°	853.2	851.9	850.4	849.1	847.7	846.0	843.6	841.4	839.2	837.0	835.8
35°	812.3	811.1	809.9	808.6	807.4	805.4	802.6	800.0	797.3	794.6	793.4
37.5°	770.4	768.9	767.3	765.7	764.2	762.1	759.3	756.5	753.8	751.1	749.6
40°	741.4	740.1	738.9	737.6	736.4	734.3	731.4	728.5	725.6	722.6	721.0
42.5°	712.2	710.8	709.4	708.0	706.6	704.5	701.5	698.6	695.7	692.8	691.2
45°	665.8	664.9	664.1	663.3	662.4	660.7	657.9	655.2	652.6	649.9	647.4
47.5°	619.6	618.4	617.2	616.0	614.7	612.9	610.4	607.9	605.3	602.8	600.3
50°	588.3	587.2	586.1	585.1	584.1	582.2	579.5	576.8	574.1	571.4	569.2
52.5°	555.4	554.6	553.9	553.2	552.5	550.7	547.9	545.0	542.2	539.3	537.3
55°	505.2	504.9	504.7	504.5	504.3	502.8	500.2	497.5	494.7	492.0	489.8
57.5°	457.4	456.6	455.9	455.2	454.5	453.1	450.9	448.7	446.6	444.4	442.4
60°	422.9	422.8	422.6	422.3	422.1	420.8	418.3	415.8	413.3	410.8	408.9
62.5°	392.4	391.8	391.3	390.7	390.2	388.7	386.2	383.7	381.2	378.7	376.8
65°	344.6	343.5	342.4	341.4	340.4	338.9	336.7	334.7	332.6	330.6	328.9
67.5°	293.9	293.0	292.1	291.1	290.3	289.0	287.5	285.9	284.3	282.8	281.2
70°	263.3	262.1	260.8	259.6	258.3	257.1	255.8	254.6	253.3	252.1	250.7
72.5°	231.2	230.2	229.3	228.5	227.6	226.4	225.0	223.6	222.1	220.7	219.5
75°	182.1	181.2	180.4	179.6	178.8	178.0	177.4	176.7	176.1	175.6	174.5
77.5°	138.6	138.1	137.7	137.2	136.7	136.2	135.4	134.6	133.9	133.1	132.4
80°	110.2	109.6	109.0	108.3	107.7	107.2	106.7	106.4	105.9	105.5	105.3
82.5°	82.6	82.4	82.3	82.1	82.0	81.9	81.9	81.8	81.7	81.6	81.2
85°	48.5	48.2	47.7	47.3	46.9	46.7	46.7	46.7	46.7	46.7	46.3
87.5°	19.5	19.4	19.2	18.9	18.7	18.7	19.0	19.2	19.4	19.6	19.5
90°	0.6	2.1	3.6	5.1	6.5	8.2	10.2	12.0	14.0	15.9	16.5
92.5°	16.1	17.0	18.0	19.0	20.0	21.0	22.1	23.3	24.3	25.4	25.9
95°	39.1	40.0	41.1	42.2	43.2	44.2	45.5	46.6	47.8	49.0	49.6
97.5°	69.4	70.1	70.9	71.7	72.4	73.2	74.1	74.9	75.8	76.7	77.3
100°	90.0	90.9	91.8	92.6	93.5	94.3	95.1	95.9	96.6	97.3	97.7
102.5°	113.9	114.4	114.9	115.4	115.9	116.7	117.7	118.7	119.6	120.6	121.0
105°	148.9	149.2	149.5	149.8	150.1	150.9	152.2	153.6	154.9	156.2	156.2
107.5°	189.7	189.8	190.0	190.2	190.4	190.7	191.3	191.8	192.3	192.9	193.3
110°	215.1	215.4	215.7	216.0	216.2	216.6	216.9	217.1	217.5	217.8	218.4



TEST NUMBER: P332161-940

CATALOG NUMBER: S123DIW-S775D755U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	241.6	241.7	241.9	242.1	242.3	242.4	242.5	242.5	242.5	242.6	243.3
115°	281.3	281.7	282.1	282.6	283.0	283.1	282.9	282.6	282.2	282.0	282.1
117.5°	321.3	321.6	321.8	322.2	322.4	322.4	322.0	321.6	321.3	320.8	320.8
120°	346.2	347.1	347.9	348.8	349.7	349.7	349.0	348.3	347.6	346.8	346.7
122.5°	372.1	372.7	373.4	374.1	374.7	374.8	374.4	374.1	373.7	373.3	372.9
125°	411.7	412.1	412.6	413.0	413.5	413.5	413.2	413.0	412.6	412.3	411.8
127.5°	448.2	449.2	450.1	451.0	452.0	452.3	452.0	451.7	451.3	451.0	450.1
130°	472.6	473.8	474.9	476.1	477.2	477.7	477.2	476.8	476.4	475.9	475.3
132.5°	497.0	498.1	499.3	500.4	501.7	502.0	501.8	501.4	501.1	500.8	500.1
135°	534.1	535.0	535.9	536.8	537.6	538.1	537.9	537.7	537.6	537.4	536.8
137.5°	568.6	569.3	570.0	570.8	571.5	572.0	572.4	572.8	573.2	573.5	572.9
140°	592.4	593.1	593.9	594.6	595.3	595.8	595.9	596.0	596.2	596.4	596.2
142.5°	614.1	614.8	615.5	616.3	617.0	617.5	617.8	618.0	618.3	618.6	618.4
145°	648.0	648.3	648.5	648.8	649.2	649.5	650.0	650.4	650.9	651.3	651.1
147.5°	677.6	678.1	678.7	679.2	679.8	680.2	680.6	681.0	681.4	681.9	681.9
150°	698.3	698.6	698.8	699.2	699.5	699.7	700.0	700.3	700.6	700.9	700.9
152.5°	715.2	715.6	716.0	716.5	716.8	717.1	717.3	717.5	717.6	717.8	718.1
155°	742.0	742.0	742.0	742.0	742.0	742.0	742.2	742.3	742.4	742.6	743.2
157.5°	764.7	764.6	764.4	764.2	764.0	764.0	764.1	764.2	764.4	764.5	765.1
160°	779.0	778.7	778.5	778.1	777.8	777.7	777.7	777.7	777.7	777.7	778.5
162.5°	791.8	791.3	790.9	790.5	790.1	790.0	790.1	790.1	790.3	790.4	791.1
165°	808.2	807.7	807.3	806.8	806.4	806.1	806.1	806.1	806.1	806.1	807.0
167.5°	821.3	820.6	820.1	819.5	818.9	818.7	818.8	818.9	819.0	819.1	820.0
170°	828.7	828.0	827.5	826.9	826.3	826.0	826.0	826.0	826.0	826.0	827.1
172.5°	834.5	833.9	833.3	832.7	832.1	831.8	831.8	831.8	831.8	831.8	832.8
175°	840.5	840.0	839.4	838.8	838.2	837.9	837.9	837.9	837.9	837.9	838.8
177.5°	843.1	842.6	842.1	841.7	841.2	841.0	841.0	841.0	841.0	841.0	841.7
180°	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6



TEST NUMBER: P332161-940

CATALOG NUMBER: S123DIW-S775D755U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9
2.5°	1081.7	1083.4	1085.0	1085.8	1085.7	1085.5	1085.3	1085.1
5°	1076.0	1078.1	1080.2	1081.0	1080.6	1080.2	1079.8	1079.3
7.5°	1064.6	1066.5	1068.4	1069.2	1068.9	1068.6	1068.4	1068.2
10°	1054.2	1056.0	1057.8	1058.6	1058.2	1057.7	1057.4	1056.9
12.5°	1042.7	1044.0	1045.4	1046.0	1045.7	1045.4	1045.3	1045.0
15°	1022.0	1023.6	1025.3	1025.5	1024.2	1023.0	1021.8	1020.6
17.5°	995.8	996.9	998.1	998.4	998.0	997.6	997.1	996.7
20°	976.4	977.2	978.1	978.2	977.6	977.0	976.3	975.7
22.5°	955.9	956.6	957.3	957.2	956.4	955.6	954.8	954.0
25°	921.9	922.2	922.4	922.2	921.6	921.0	920.3	919.7
27.5°	885.8	886.0	886.2	885.8	885.1	884.3	883.5	882.7
30°	860.9	860.9	860.9	860.1	858.7	857.2	855.8	854.3
32.5°	834.6	833.5	832.3	831.3	830.5	829.7	828.9	828.2
35°	792.1	790.9	789.6	788.5	787.4	786.4	785.3	784.3
37.5°	748.1	746.5	745.1	744.0	743.3	742.7	742.0	741.4
40°	719.3	717.7	716.0	714.8	714.0	713.1	712.3	711.5
42.5°	689.5	687.8	686.2	684.9	684.1	683.2	682.4	681.6
45°	644.9	642.4	639.9	638.1	637.1	636.1	635.0	634.0
47.5°	597.9	595.5	593.0	591.3	590.4	589.5	588.6	587.6
50°	566.9	564.5	562.3	560.5	559.3	558.0	556.8	555.5
52.5°	535.4	533.4	531.5	529.9	528.7	527.4	526.2	525.0
55°	487.5	485.2	483.0	481.3	480.2	479.2	478.1	477.2
57.5°	440.3	438.4	436.3	434.7	433.5	432.3	431.1	429.9
60°	407.1	405.2	403.3	401.9	400.8	399.8	398.8	397.8
62.5°	375.0	373.1	371.2	370.0	369.3	368.5	367.8	367.1
65°	327.2	325.6	323.9	322.7	322.1	321.5	320.8	320.2
67.5°	279.8	278.4	276.9	275.7	274.9	274.0	273.1	272.2
70°	249.2	247.7	246.3	245.0	244.0	243.0	241.9	240.9
72.5°	218.1	216.9	215.6	214.6	214.1	213.6	213.0	212.5
75°	173.4	172.5	171.4	170.6	170.0	169.3	168.7	168.1
77.5°	131.7	131.0	130.3	130.0	130.0	130.0	130.0	130.0
80°	105.1	104.9	104.7	104.6	104.6	104.6	104.6	104.6
82.5°	80.9	80.5	80.1	79.8	79.7	79.5	79.4	79.2
85°	45.8	45.5	45.0	44.9	44.9	44.9	44.9	44.9
87.5°	19.5	19.4	19.4	19.4	19.4	19.5	19.6	19.6
90°	17.0	17.7	18.3	18.6	19.0	19.3	19.5	19.9
92.5°	26.4	26.8	27.3	27.5	27.3	27.1	26.9	26.8
95°	50.1	50.7	51.4	51.6	51.6	51.6	51.6	51.6
97.5°	78.0	78.6	79.4	79.6	79.6	79.5	79.5	79.5
100°	98.2	98.6	99.1	99.4	99.7	100.0	100.3	100.6
102.5°	121.5	121.9	122.3	122.5	122.5	122.4	122.3	122.3
105°	156.2	156.2	156.2	156.3	156.7	156.9	157.2	157.6
107.5°	193.8	194.3	194.7	194.9	194.7	194.6	194.4	194.2
110°	218.9	219.5	220.1	220.3	220.0	219.6	219.4	219.1



TEST NUMBER: P332161-940

CATALOG NUMBER: S123DIW-S775D755U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	244.1	244.8	245.5	245.8	245.8	245.7	245.6	245.6
115°	282.2	282.4	282.6	282.6	282.4	282.2	282.1	282.0
117.5°	320.8	320.7	320.7	320.6	320.1	319.7	319.3	318.9
120°	346.5	346.3	346.3	346.0	345.7	345.4	345.1	344.8
122.5°	372.6	372.1	371.8	371.4	371.0	370.5	370.1	369.7
125°	411.2	410.5	410.0	409.4	408.8	408.2	407.6	407.1
127.5°	449.3	448.5	447.7	446.9	446.3	445.6	445.0	444.3
130°	474.7	474.1	473.5	472.7	471.7	470.6	469.7	468.6
132.5°	499.4	498.6	497.9	497.2	496.4	495.6	494.8	494.0
135°	536.3	535.7	535.1	534.7	534.3	534.0	533.8	533.4
137.5°	572.3	571.7	571.1	570.5	570.0	569.4	568.8	568.3
140°	596.0	595.9	595.8	595.1	594.1	593.1	592.1	591.0
142.5°	618.3	618.1	618.0	617.5	616.7	615.9	615.1	614.3
145°	650.9	650.9	650.7	650.3	649.7	649.2	648.5	648.0
147.5°	681.9	681.9	681.9	681.4	680.6	679.7	678.8	677.9
150°	700.9	700.9	700.9	700.4	699.5	698.7	697.9	697.0
152.5°	718.4	718.5	718.8	718.5	717.7	717.0	716.2	715.5
155°	743.8	744.4	744.9	744.8	743.7	742.7	741.6	740.7
157.5°	765.7	766.3	767.0	766.8	766.0	765.2	764.4	763.5
160°	779.2	779.9	780.6	780.7	780.2	779.5	778.9	778.4
162.5°	791.8	792.6	793.4	793.3	792.3	791.4	790.4	789.4
165°	807.9	808.8	809.7	809.6	808.6	807.5	806.6	805.5
167.5°	820.9	821.9	822.8	822.8	821.9	820.9	820.0	819.1
170°	828.0	829.1	830.1	830.1	829.1	828.0	827.1	826.0
172.5°	833.7	834.6	835.4	835.4	834.4	833.4	832.3	831.3
175°	839.7	840.5	841.4	841.4	840.3	839.3	838.3	837.2
177.5°	842.4	843.1	843.8	843.7	842.9	842.0	841.2	840.4
180°	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6

(END OF REPORT)